

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331357-940

Luminaire Tested: **SA2XXDIP-C675D925U940-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331357-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U940-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5914.2 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331357-940
CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331357-940

CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	81	76	71	81	75	70	66	63	59	56	51	49	46	41	39	37	33
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	36	34	32	28
4	74	64	56	51	68	59	52	47	50	45	41	41	37	34	33	30	28	24
5	68	57	49	44	62	53	46	41	45	39	35	37	33	30	30	27	25	22
6	63	51	44	38	58	48	41	36	40	35	31	33	30	27	27	24	22	19
7	58	47	39	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	33	28	25	28	24	21	23	20	18	15
9	51	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16	14
10	47	36	28	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19125	19125	19125	19125
5°	21441	19248	17057	19248
10°	24568	19090	14762	19090
15°	27178	18740	13041	18740
20°	26764	18364	11888	18364
25°	24134	17865	11158	17865
30°	19943	17066	10625	17066
35°	14534	16232	10247	16232
40°	11609	15247	10037	15247
45°	10145	14104	9750	14104
50°	9535	12999	9560	12999
55°	8791	11879	9303	11879
60°	8054	10685	8909	10685
65°	7339	9616	8520	9616
70°	6661	8573	7950	8573
75°	5908	7411	7043	7411
80°	5086	6137	5672	6137
85°	4557	4557	3372	4557



TEST NUMBER: P331357-940

CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	1.9
10°-20°	327.9	5.5
20°-30°	475.9	8.0
30°-40°	502.2	8.5
40°-50°	444.7	7.5
50°-60°	354.9	6.0
60°-70°	241.2	4.1
70°-80°	123.7	2.1
80°-90°	32.6	0.6
90°-100°	37.5	0.6
100°-110°	137.7	2.3
110°-120°	368.0	6.2
120°-130°	607.5	10.3
130°-140°	646.1	10.9
140°-150°	600.5	10.2
150°-160°	482.8	8.2
160°-170°	311.1	5.3
170°-180°	107.1	1.8
0°-30°	916.7	15.5
0°-40°	1418.9	24.0
0°-60°	2218.4	37.5
0°-90°	2615.9	44.2
90°-120°	543.2	9.2
90°-150°	2397.3	40.5
90°-180°	3298.0	55.8
0°-180°	5914.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1184	1184	1184	1184	1184	
5°	1323	1188	1052	1188	1323	132
15°	1626	1121	780	1121	1626	449
25°	1355	1003	626	1003	1355	612
35°	737	824	520	824	737	480
45°	444	618	427	618	444	349
55°	312	422	330	422	312	280
65°	192	252	223	252	192	191
75°	95	119	113	119	95	101
85°	25	25	18	25	25	28
90°	22	1	22	1	22	11
95°	35	53	35	53	35	33
105°	62	248	62	248	62	64
115°	67	468	67	468	67	167
125°	696	662	696	662	696	602
135°	846	819	846	819	846	652
145°	965	950	965	950	965	604
155°	1047	1046	1047	1046	1047	483
165°	1100	1103	1100	1103	1100	311
175°	1121	1128	1121	1128	1121	107
180°	1126	1126	1126	1126	1126	



TEST NUMBER: P331357-940

CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1239.0	1239.4	1240.2	1234.3	1233.6	1233.6	1228.5	1224.1	1219.1	1212.1	1212.8
5°	1322.9	1327.8	1329.6	1324.2	1316.0	1315.1	1307.3	1294.6	1282.7	1273.2	1266.4
7.5°	1422.8	1424.8	1420.3	1413.1	1407.0	1396.2	1381.7	1367.6	1347.8	1329.7	1316.3
10°	1498.5	1501.3	1493.5	1483.1	1474.4	1461.7	1440.7	1419.3	1393.4	1368.3	1348.3
12.5°	1556.0	1562.8	1552.9	1551.5	1536.7	1519.2	1494.2	1483.5	1446.9	1412.0	1390.5
15°	1625.9	1625.5	1626.5	1617.8	1606.9	1604.1	1577.7	1549.1	1497.6	1477.1	1441.6
17.5°	1605.8	1612.7	1615.9	1615.8	1615.5	1613.8	1605.3	1587.2	1561.5	1528.2	1487.2
20°	1557.7	1566.8	1568.2	1578.7	1584.6	1592.3	1595.4	1590.5	1574.6	1546.8	1511.3
22.5°	1483.5	1485.9	1490.2	1506.5	1519.4	1538.7	1548.9	1565.8	1559.6	1546.0	1516.4
25°	1354.7	1350.1	1366.1	1374.2	1403.8	1434.8	1457.1	1481.7	1503.5	1516.7	1508.1
27.5°	1200.1	1193.3	1217.1	1238.9	1262.9	1296.5	1331.2	1372.3	1406.4	1449.1	1463.7
30°	1069.7	1073.8	1096.6	1119.8	1156.2	1203.5	1242.7	1287.8	1336.5	1384.3	1417.5
32.5°	929.2	944.9	959.3	994.9	1026.9	1079.8	1137.1	1193.5	1254.2	1308.5	1359.9
35°	737.4	755.6	775.7	801.6	846.7	899.0	955.0	1031.0	1113.9	1188.1	1249.1
37.5°	620.7	617.8	629.3	648.0	684.6	726.7	791.2	866.4	963.9	1051.1	1137.1
40°	550.8	548.9	557.1	574.4	602.3	633.2	689.6	755.6	846.2	952.7	1055.2
42.5°	502.7	503.8	508.4	520.6	539.6	565.1	607.3	663.5	746.5	846.8	956.8
45°	444.3	447.5	452.5	458.4	469.3	490.3	513.9	554.0	619.6	703.3	811.6
47.5°	402.3	402.3	407.4	412.6	419.1	430.9	450.2	475.3	521.6	589.8	682.9
50°	379.6	376.5	380.1	384.1	391.0	399.2	412.0	435.6	466.5	521.7	599.5
52.5°	352.0	352.0	355.3	356.9	363.0	371.1	382.8	399.2	427.2	470.3	534.3
55°	312.3	314.5	316.4	319.1	324.6	330.5	339.6	350.5	372.4	404.7	452.0
57.5°	274.9	275.6	277.5	282.7	286.1	291.6	300.2	310.1	324.4	348.3	383.9
60°	249.4	249.4	253.1	255.4	259.9	265.4	272.2	281.8	294.5	314.1	342.8
62.5°	226.1	225.8	227.2	231.0	234.4	239.5	246.4	254.5	266.4	283.8	307.5
65°	192.1	191.2	193.9	194.8	198.5	203.5	208.9	217.6	227.1	239.9	260.8
67.5°	159.3	160.4	161.8	163.6	165.6	170.9	174.5	180.7	188.7	199.3	213.5
70°	141.1	141.1	141.1	142.5	145.2	147.9	151.6	156.6	164.3	173.4	186.2
72.5°	120.7	122.2	123.6	122.8	126.3	127.9	132.2	135.1	142.5	148.3	159.6
75°	94.7	94.7	94.7	96.9	98.4	99.7	102.5	105.1	108.8	116.1	122.0
77.5°	70.6	70.4	70.9	71.4	72.9	74.5	75.3	77.8	81.2	84.5	89.6
80°	54.7	55.6	56.0	56.9	56.9	57.8	58.2	61.4	63.8	66.0	69.2
82.5°	42.3	42.4	42.5	42.7	43.1	43.6	44.8	45.8	46.6	48.5	51.0
85°	24.6	24.2	24.2	25.1	24.6	24.6	25.5	26.4	26.4	26.8	28.2
87.5°	13.8	13.8	14.1	13.6	13.6	13.8	13.6	13.1	13.3	13.5	13.6
90°	22.0	21.7	21.2	20.9	20.5	19.9	19.0	18.1	17.2	16.3	14.8
92.5°	22.0	21.8	21.6	21.3	21.1	20.8	20.3	19.8	19.4	18.9	18.2
95°	35.0	35.2	35.4	35.6	35.8	35.4	34.5	33.5	32.6	31.7	30.5
97.5°	46.7	46.5	46.3	46.1	45.8	45.4	44.7	44.0	43.2	42.5	39.6
100°	54.6	54.2	53.9	53.5	53.1	52.3	50.7	49.3	47.9	46.5	43.3
102.5°	58.5	58.0	57.4	57.0	56.4	55.3	53.4	51.5	49.6	47.7	73.5
105°	61.9	61.2	60.5	59.7	59.0	57.6	55.6	53.7	51.6	49.7	99.1
107.5°	63.7	63.0	62.2	61.5	60.8	61.4	63.5	65.5	67.5	69.6	128.8
110°	64.4	63.6	62.9	62.2	61.4	70.1	88.2	106.3	124.4	142.5	194.8



TEST NUMBER: P331357-940

CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	65.0	64.4	63.8	63.2	62.7	95.4	161.4	227.5	293.5	359.4	372.4
115°	66.8	79.8	92.8	105.8	118.9	167.3	251.1	334.9	418.7	502.5	497.9
117.5°	272.7	315.5	358.3	401.1	443.9	475.5	495.8	516.0	536.3	556.5	553.5
120°	496.8	521.2	545.6	570.1	594.5	605.6	603.5	601.3	599.1	596.9	593.7
122.5°	619.9	624.6	629.4	634.2	638.9	640.6	639.3	638.0	636.7	635.4	631.9
125°	696.3	695.8	695.2	694.6	694.1	693.2	692.0	690.7	689.5	688.1	684.7
127.5°	744.5	744.4	744.3	744.2	744.0	743.2	741.3	739.4	737.5	735.8	733.2
130°	774.5	774.6	774.8	775.1	775.3	774.3	772.3	770.3	768.3	766.3	764.4
132.5°	803.8	804.0	804.1	804.3	804.5	803.8	802.1	800.4	798.7	796.9	795.0
135°	846.1	846.5	846.9	847.2	847.6	846.9	845.1	843.3	841.4	839.6	838.0
137.5°	884.8	885.4	886.0	886.6	887.3	886.6	884.8	883.1	881.3	879.6	877.7
140°	908.8	909.8	910.7	911.6	912.5	912.1	910.5	908.8	907.2	905.6	903.7
142.5°	932.3	933.3	934.2	935.0	935.9	935.7	934.2	932.6	931.2	929.7	927.5
145°	965.1	966.0	966.9	967.8	968.7	968.5	967.2	966.0	964.7	963.4	960.4
147.5°	993.9	994.6	995.4	996.1	996.9	996.8	995.9	995.0	994.0	993.1	990.1
150°	1011.5	1012.4	1013.3	1014.2	1015.1	1015.0	1014.0	1012.8	1011.7	1010.7	1007.8
152.5°	1026.4	1027.7	1028.9	1030.0	1031.3	1031.3	1030.2	1029.1	1028.1	1027.0	1024.2
155°	1047.3	1048.7	1050.2	1051.7	1053.1	1053.3	1052.2	1051.1	1050.0	1048.9	1046.8
157.5°	1066.4	1067.7	1069.2	1070.6	1072.0	1072.1	1070.9	1069.6	1068.4	1067.2	1065.7
160°	1077.5	1078.7	1080.0	1081.2	1082.5	1082.6	1081.6	1080.4	1079.3	1078.3	1077.2
162.5°	1086.5	1088.2	1089.7	1091.3	1092.8	1093.0	1091.7	1090.5	1089.2	1088.1	1087.1
165°	1100.3	1101.5	1102.8	1104.0	1105.3	1105.3	1104.0	1102.8	1101.5	1100.3	1099.7
167.5°	1108.8	1110.5	1112.1	1113.7	1115.4	1115.6	1114.3	1113.0	1111.8	1110.5	1110.0
170°	1114.1	1115.7	1117.3	1119.0	1120.6	1120.8	1119.5	1118.3	1117.0	1115.7	1115.4
172.5°	1118.0	1119.6	1121.2	1122.8	1124.5	1124.7	1123.5	1122.1	1120.9	1119.6	1119.3
175°	1121.4	1123.2	1125.1	1126.9	1128.6	1128.9	1127.7	1126.4	1125.2	1123.8	1123.5
177.5°	1123.6	1124.8	1126.1	1127.5	1128.7	1128.9	1127.9	1126.9	1125.9	1124.8	1124.7
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331357-940
 CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1215.4	1212.5	1210.7	1204.1	1198.3	1192.5	1190.6	1191.3	1183.4	1175.7	1172.4
5°	1262.8	1253.7	1245.0	1232.7	1218.2	1202.2	1194.0	1187.6	1171.7	1154.4	1144.4
7.5°	1305.2	1292.2	1275.5	1252.3	1231.2	1206.1	1190.2	1176.1	1152.7	1128.4	1113.4
10°	1331.1	1313.2	1291.8	1263.6	1237.7	1207.2	1185.8	1164.4	1137.1	1108.0	1089.8
12.5°	1353.3	1329.3	1308.2	1272.0	1241.4	1203.2	1177.8	1147.6	1118.9	1084.3	1066.5
15°	1406.1	1362.0	1321.9	1280.9	1243.1	1189.9	1161.7	1121.1	1083.3	1040.6	1020.1
17.5°	1447.0	1397.4	1334.3	1282.2	1238.1	1179.2	1137.7	1089.2	1044.6	995.6	967.8
20°	1470.3	1413.4	1345.6	1283.7	1230.8	1163.5	1118.5	1068.8	1016.5	961.4	931.3
22.5°	1484.2	1424.3	1357.3	1278.2	1216.3	1150.8	1094.0	1039.6	986.6	927.2	895.6
25°	1488.5	1433.9	1362.9	1273.6	1198.1	1123.9	1055.6	1002.8	938.6	883.1	837.1
27.5°	1466.9	1427.7	1359.4	1265.1	1177.1	1090.3	1014.2	954.4	886.6	826.3	780.2
30°	1440.3	1417.5	1351.0	1256.3	1160.3	1067.0	983.2	915.4	848.0	787.0	739.7
32.5°	1399.1	1394.2	1335.8	1243.9	1142.5	1037.5	950.8	882.3	807.6	747.7	702.6
35°	1318.3	1340.2	1303.2	1216.3	1108.8	995.5	901.8	823.5	746.1	688.8	646.4
37.5°	1210.0	1264.2	1254.5	1175.8	1063.5	949.9	846.3	764.5	690.7	632.8	591.3
40°	1135.2	1204.4	1214.5	1144.9	1031.5	914.5	804.8	723.4	651.4	598.6	556.7
42.5°	1055.2	1136.0	1163.5	1107.7	996.5	877.4	767.7	683.2	612.1	560.7	523.6
45°	920.9	1027.9	1077.5	1045.6	938.2	816.2	703.3	617.7	553.0	504.8	476.2
47.5°	795.3	912.2	978.9	967.7	873.3	752.4	640.9	558.7	495.8	457.3	431.6
50°	706.5	826.6	907.2	910.9	826.6	706.9	594.9	517.5	459.8	423.8	402.9
52.5°	629.3	744.0	831.9	851.1	774.5	659.6	553.8	476.8	425.9	392.8	374.1
55°	528.5	625.4	722.8	758.4	696.9	587.6	489.8	422.0	374.2	351.4	335.0
57.5°	439.3	520.2	610.2	649.4	611.5	518.0	426.2	367.4	328.6	308.6	296.0
60°	392.4	456.1	536.2	583.1	550.4	467.1	386.9	330.9	299.1	281.3	269.5
62.5°	348.7	405.1	472.9	515.8	497.9	419.4	347.6	298.2	270.6	254.0	245.5
65°	287.7	332.3	384.7	424.3	412.4	352.8	294.1	251.7	229.9	216.7	209.8
67.5°	236.9	269.1	305.4	340.1	330.6	288.3	241.2	208.2	191.9	180.6	176.5
70°	204.8	229.4	261.7	289.5	281.8	247.2	209.8	181.6	167.6	157.9	153.8
72.5°	174.2	194.5	219.1	241.8	236.6	207.9	176.7	155.4	144.5	135.7	132.3
75°	131.5	147.0	162.0	177.1	175.7	153.4	135.2	118.8	110.1	103.3	101.9
77.5°	97.1	105.8	116.0	124.9	122.4	109.7	95.4	86.1	79.6	75.1	74.4
80°	74.2	79.2	86.5	92.8	89.7	84.2	72.9	66.0	61.4	56.9	55.1
82.5°	53.8	58.9	63.2	66.6	64.2	59.1	52.1	47.4	44.7	41.6	40.8
85°	28.2	30.9	32.8	33.7	32.8	29.6	26.4	24.6	22.3	21.0	20.5
87.5°	13.6	13.3	13.0	13.4	11.9	11.5	9.6	8.2	8.2	8.2	7.9
90°	13.4	11.9	10.5	8.7	6.8	4.8	2.8	0.8	2.8	4.8	6.8
92.5°	17.5	16.8	16.0	15.7	15.9	16.1	16.2	16.4	16.2	16.1	15.9
95°	29.2	28.0	26.7	29.1	35.0	41.0	47.0	53.0	47.0	41.0	35.0
97.5°	36.6	33.7	30.8	37.7	54.6	71.4	88.2	105.0	88.2	71.4	54.6
100°	40.3	37.2	34.2	44.9	69.7	94.5	119.3	144.2	119.3	94.5	69.7
102.5°	99.2	124.9	150.7	166.1	171.4	176.6	181.9	187.2	181.9	176.6	171.4
105°	148.5	197.9	247.3	269.3	263.9	258.4	253.0	247.5	253.0	258.4	263.9
107.5°	188.1	247.3	306.6	334.0	329.6	325.2	320.8	316.5	320.8	325.2	329.6
110°	247.1	299.4	351.7	375.9	372.2	368.4	364.6	360.8	364.6	368.4	372.2



TEST NUMBER: P331357-940

CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	385.3	398.2	411.2	415.9	412.6	409.2	405.8	402.4	405.8	409.2	412.6
115°	493.5	488.9	484.4	480.5	477.5	474.4	471.4	468.2	471.4	474.4	477.5
117.5°	550.4	547.2	544.1	540.8	537.4	534.0	530.5	527.1	530.5	534.0	537.4
120°	590.4	587.2	583.9	580.9	578.2	575.5	572.7	570.1	572.7	575.5	578.2
122.5°	628.3	624.7	621.2	618.0	615.1	612.2	609.4	606.5	609.4	612.2	615.1
125°	681.3	677.9	674.4	671.5	669.1	666.8	664.4	662.1	664.4	666.8	669.1
127.5°	730.6	728.0	725.4	722.8	720.2	717.6	715.1	712.4	715.1	717.6	720.2
130°	762.3	760.4	758.4	755.9	753.0	750.1	747.3	744.4	747.3	750.1	753.0
132.5°	793.0	791.0	789.0	786.8	784.3	781.9	779.4	776.9	779.4	781.9	784.3
135°	836.4	834.7	833.1	830.9	828.0	825.1	822.2	819.3	822.2	825.1	828.0
137.5°	875.8	874.0	872.2	870.2	868.2	866.2	864.2	862.1	864.2	866.2	868.2
140°	901.6	899.6	897.7	895.9	894.5	893.0	891.6	890.1	891.6	893.0	894.5
142.5°	925.1	922.8	920.6	918.8	917.5	916.2	914.9	913.6	914.9	916.2	917.5
145°	957.3	954.2	951.1	949.7	949.9	950.0	950.2	950.4	950.2	950.0	949.9
147.5°	987.0	983.9	980.9	979.7	980.4	981.1	981.8	982.5	981.8	981.1	980.4
150°	1004.9	1002.0	999.1	998.3	999.5	1000.8	1002.1	1003.4	1002.1	1000.8	999.5
152.5°	1021.5	1018.7	1015.9	1015.3	1016.7	1018.1	1019.5	1020.9	1019.5	1018.1	1016.7
155°	1044.6	1042.4	1040.3	1040.0	1041.6	1043.2	1044.9	1046.5	1044.9	1043.2	1041.6
157.5°	1064.2	1062.7	1061.1	1061.0	1062.4	1063.8	1065.1	1066.5	1065.1	1063.8	1062.4
160°	1076.1	1075.0	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3	1077.2	1076.1	1075.0
162.5°	1086.1	1085.2	1084.2	1084.3	1085.4	1086.5	1087.6	1088.7	1087.6	1086.5	1085.4
165°	1099.1	1098.6	1098.1	1098.3	1099.4	1100.5	1101.6	1102.7	1101.6	1100.5	1099.4
167.5°	1109.5	1109.0	1108.5	1108.8	1109.8	1111.0	1112.1	1113.1	1112.1	1111.0	1109.8
170°	1115.0	1114.6	1114.3	1114.6	1115.7	1116.8	1117.8	1119.0	1117.8	1116.8	1115.7
172.5°	1118.9	1118.6	1118.2	1118.6	1119.6	1120.7	1121.8	1122.8	1121.8	1120.7	1119.6
175°	1123.1	1122.8	1122.4	1122.8	1124.1	1125.4	1126.7	1127.9	1126.7	1125.4	1124.1
177.5°	1124.5	1124.4	1124.3	1124.7	1125.7	1126.8	1127.7	1128.7	1127.7	1126.8	1125.7
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331357-940

CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1168.8	1166.6	1159.0	1154.9	1148.3	1142.2	1138.2	1140.1	1141.5	1140.8	1139.6
5°	1135.2	1126.6	1113.4	1102.1	1093.9	1078.8	1072.5	1069.3	1066.6	1063.4	1060.2
7.5°	1095.4	1081.7	1062.8	1046.6	1031.3	1012.6	1002.0	995.6	989.1	981.9	975.5
10°	1067.0	1047.8	1027.9	1005.0	986.9	970.0	955.0	945.0	935.9	927.3	920.9
12.5°	1037.1	1015.1	990.3	959.2	939.1	915.1	912.8	895.1	880.9	875.6	868.1
15°	989.6	958.7	927.3	890.4	874.4	852.6	838.9	825.3	813.0	804.3	802.1
17.5°	935.6	895.5	864.3	837.9	811.7	789.3	776.8	765.8	755.7	744.1	742.6
20°	894.5	859.9	825.7	802.5	775.7	752.9	737.4	726.5	717.8	711.1	705.1
22.5°	855.5	817.6	786.4	761.0	734.5	716.1	703.9	693.4	686.2	678.6	673.1
25°	793.0	763.4	729.2	700.5	678.7	666.9	656.8	647.7	643.2	638.2	631.9
27.5°	738.2	705.3	673.4	651.2	632.0	621.5	614.4	608.2	604.0	601.0	597.4
30°	699.6	666.4	641.4	619.6	603.6	593.2	588.6	585.0	580.0	578.1	576.3
32.5°	662.5	632.6	611.2	592.2	577.0	570.2	566.0	562.8	558.8	557.0	553.3
35°	609.9	585.0	564.0	553.5	541.3	535.3	532.2	527.5	524.0	522.1	521.7
37.5°	560.5	538.8	525.0	511.6	506.4	502.7	498.4	495.3	494.2	493.9	493.5
40°	528.5	510.8	498.5	487.5	485.3	479.7	476.2	473.4	473.4	473.9	473.4
42.5°	499.4	483.4	472.6	463.2	460.5	457.2	453.5	453.3	454.1	455.7	454.1
45°	455.2	443.8	436.0	431.5	426.5	423.3	422.8	424.3	424.7	425.2	426.5
47.5°	414.6	407.1	400.0	395.0	392.8	392.3	391.7	394.1	396.3	397.1	399.2
50°	390.6	381.9	376.0	372.8	371.0	370.1	371.0	373.7	375.5	377.8	379.2
52.5°	363.6	357.5	353.4	351.0	350.3	350.8	351.0	354.1	357.0	357.8	358.5
55°	326.4	321.8	320.9	316.8	318.6	318.2	320.5	322.3	325.0	327.7	328.2
57.5°	289.3	285.6	283.1	283.5	284.0	286.1	287.9	291.1	294.1	296.9	297.2
60°	264.5	262.6	261.3	261.3	262.2	264.9	267.2	270.4	272.2	274.0	275.4
62.5°	241.9	240.0	238.7	239.4	241.8	243.4	246.1	247.8	249.6	251.5	252.1
65°	206.2	205.3	206.7	207.6	208.0	210.3	213.5	214.8	216.7	217.6	220.8
67.5°	173.3	173.5	173.3	174.6	177.3	177.8	180.8	184.0	184.3	186.1	188.2
70°	151.1	152.0	152.9	153.8	156.1	157.0	159.3	160.7	162.5	163.9	165.2
72.5°	130.7	130.9	131.8	131.6	133.6	135.5	137.5	138.8	140.6	142.4	143.7
75°	100.6	100.6	101.5	101.9	104.2	106.6	106.0	107.0	108.8	110.6	111.6
77.5°	73.5	72.5	73.5	73.9	74.6	76.6	77.0	78.2	80.3	79.6	80.7
80°	56.0	54.7	56.0	56.4	56.4	58.8	58.8	59.7	61.0	59.7	61.0
82.5°	39.9	39.3	40.3	40.4	41.1	41.2	42.0	42.2	43.5	42.9	43.5
85°	20.1	19.6	20.1	19.6	20.1	20.5	20.5	20.1	20.1	21.0	19.6
87.5°	7.9	7.9	7.8	8.1	8.0	8.0	7.8	8.0	8.2	7.6	7.8
90°	8.7	10.5	11.9	13.4	14.8	16.3	17.2	18.1	19.0	19.9	20.5
92.5°	15.7	16.0	16.8	17.5	18.2	18.9	19.4	19.8	20.3	20.8	21.1
95°	29.1	26.7	28.0	29.2	30.5	31.7	32.6	33.5	34.5	35.4	35.8
97.5°	37.7	30.8	33.7	36.6	39.6	42.5	43.2	44.0	44.7	45.4	45.8
100°	44.9	34.2	37.2	40.3	43.3	46.5	47.9	49.3	50.7	52.3	53.1
102.5°	166.1	150.7	124.9	99.2	73.5	47.7	49.6	51.5	53.4	55.3	56.4
105°	269.3	247.3	197.9	148.5	99.1	49.7	51.6	53.7	55.6	57.6	59.0
107.5°	334.0	306.6	247.3	188.1	128.8	69.6	67.5	65.5	63.5	61.4	60.8
110°	375.9	351.7	299.4	247.1	194.8	142.5	124.4	106.3	88.2	70.1	61.4



TEST NUMBER: P331357-940

CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	415.9	411.2	398.2	385.3	372.4	359.4	293.5	227.5	161.4	95.4	62.7
115°	480.5	484.4	488.9	493.5	497.9	502.5	418.7	334.9	251.1	167.3	118.9
117.5°	540.8	544.1	547.2	550.4	553.5	556.5	536.3	516.0	495.8	475.5	443.9
120°	580.9	583.9	587.2	590.4	593.7	596.9	599.1	601.3	603.5	605.6	594.5
122.5°	618.0	621.2	624.7	628.3	631.9	635.4	636.7	638.0	639.3	640.6	638.9
125°	671.5	674.4	677.9	681.3	684.7	688.1	689.5	690.7	692.0	693.2	694.1
127.5°	722.8	725.4	728.0	730.6	733.2	735.8	737.5	739.4	741.3	743.2	744.0
130°	755.9	758.4	760.4	762.3	764.4	766.3	768.3	770.3	772.3	774.3	775.3
132.5°	786.8	789.0	791.0	793.0	795.0	796.9	798.7	800.4	802.1	803.8	804.5
135°	830.9	833.1	834.7	836.4	838.0	839.6	841.4	843.3	845.1	846.9	847.6
137.5°	870.2	872.2	874.0	875.8	877.7	879.6	881.3	883.1	884.8	886.6	887.3
140°	895.9	897.7	899.6	901.6	903.7	905.6	907.2	908.8	910.5	912.1	912.5
142.5°	918.8	920.6	922.8	925.1	927.5	929.7	931.2	932.6	934.2	935.7	935.9
145°	949.7	951.1	954.2	957.3	960.4	963.4	964.7	966.0	967.2	968.5	968.7
147.5°	979.7	980.9	983.9	987.0	990.1	993.1	994.0	995.0	995.9	996.8	996.9
150°	998.3	999.1	1002.0	1004.9	1007.8	1010.7	1011.7	1012.8	1014.0	1015.0	1015.1
152.5°	1015.3	1015.9	1018.7	1021.5	1024.2	1027.0	1028.1	1029.1	1030.2	1031.3	1031.3
155°	1040.0	1040.3	1042.4	1044.6	1046.8	1048.9	1050.0	1051.1	1052.2	1053.3	1053.1
157.5°	1061.0	1061.1	1062.7	1064.2	1065.7	1067.2	1068.4	1069.6	1070.9	1072.1	1072.0
160°	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3	1079.3	1080.4	1081.6	1082.6	1082.5
162.5°	1084.3	1084.2	1085.2	1086.1	1087.1	1088.1	1089.2	1090.5	1091.7	1093.0	1092.8
165°	1098.3	1098.1	1098.6	1099.1	1099.7	1100.3	1101.5	1102.8	1104.0	1105.3	1105.3
167.5°	1108.8	1108.5	1109.0	1109.5	1110.0	1110.5	1111.8	1113.0	1114.3	1115.6	1115.4
170°	1114.6	1114.3	1114.6	1115.0	1115.4	1115.7	1117.0	1118.3	1119.5	1120.8	1120.6
172.5°	1118.6	1118.2	1118.6	1118.9	1119.3	1119.6	1120.9	1122.1	1123.5	1124.7	1124.5
175°	1122.8	1122.4	1122.8	1123.1	1123.5	1123.8	1125.2	1126.4	1127.7	1128.9	1128.6
177.5°	1124.7	1124.3	1124.4	1124.5	1124.7	1124.8	1125.9	1126.9	1127.9	1128.9	1128.7
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331357-940
 CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1136.0	1135.2	1135.2	1132.0	1135.2	1135.2	1136.0	1139.6	1140.8	1141.5	1140.1
5°	1053.8	1052.4	1050.2	1052.4	1050.2	1052.4	1053.8	1060.2	1063.4	1066.6	1069.3
7.5°	972.5	967.1	966.3	960.8	966.3	967.1	972.5	975.5	981.9	989.1	995.6
10°	913.1	909.5	909.0	900.4	909.0	909.5	913.1	920.9	927.3	935.9	945.0
12.5°	868.0	859.3	860.9	856.0	860.9	859.3	868.0	868.1	875.6	880.9	895.1
15°	789.8	789.8	787.9	780.2	787.9	789.8	789.8	802.1	804.3	813.0	825.3
17.5°	733.6	732.7	728.3	730.5	728.3	732.7	733.6	742.6	744.1	755.7	765.8
20°	700.1	697.4	691.9	691.9	691.9	697.4	700.1	705.1	711.1	717.8	726.5
22.5°	668.4	668.2	662.5	664.2	662.5	668.2	668.4	673.1	678.6	686.2	693.4
25°	631.3	627.8	625.0	626.3	625.0	627.8	631.3	631.9	638.2	643.2	647.7
27.5°	596.2	594.2	594.1	590.3	594.1	594.2	596.2	597.4	601.0	604.0	608.2
30°	575.9	571.3	572.2	569.9	572.2	571.3	575.9	576.3	578.1	580.0	585.0
32.5°	552.5	550.9	550.0	548.0	550.0	550.9	552.5	553.3	557.0	558.8	562.8
35°	520.8	521.2	519.0	519.9	519.0	521.2	520.8	521.7	522.1	524.0	527.5
37.5°	493.0	494.5	493.4	493.7	493.4	494.5	493.0	493.5	493.9	494.2	495.3
40°	474.7	474.7	474.7	476.2	474.7	474.7	474.7	473.4	473.9	473.4	473.4
42.5°	457.3	456.6	455.8	455.8	455.8	456.6	457.3	454.1	455.7	454.1	453.3
45°	427.4	428.8	429.3	427.0	429.3	428.8	427.4	426.5	425.2	424.7	424.3
47.5°	400.4	400.6	400.4	402.4	400.4	400.6	400.4	399.2	397.1	396.3	394.1
50°	381.5	380.6	381.5	380.6	381.5	380.6	381.5	379.2	377.8	375.5	373.7
52.5°	361.4	361.6	361.1	360.9	361.1	361.6	361.4	358.5	357.8	357.0	354.1
55°	330.0	330.9	330.5	330.5	330.5	330.9	330.0	328.2	327.7	325.0	322.3
57.5°	297.6	298.4	299.0	296.9	299.0	298.4	297.6	297.2	296.9	294.1	291.1
60°	274.9	277.2	276.8	275.9	276.8	277.2	274.9	275.4	274.0	272.2	270.4
62.5°	254.2	255.0	254.9	254.8	254.9	255.0	254.2	252.1	251.5	249.6	247.8
65°	222.1	223.0	221.7	223.0	221.7	223.0	222.1	220.8	217.6	216.7	214.8
67.5°	187.6	187.9	189.0	189.6	189.0	187.9	187.6	188.2	186.1	184.3	184.0
70°	166.1	165.7	167.0	168.4	167.0	165.7	166.1	165.2	163.9	162.5	160.7
72.5°	143.6	144.5	144.1	145.1	144.1	144.5	143.6	143.7	142.4	140.6	138.8
75°	110.6	112.0	111.6	112.9	111.6	112.0	110.6	111.6	110.6	108.8	107.0
77.5°	79.9	80.1	79.9	80.7	79.9	80.1	79.9	80.7	79.6	80.3	78.2
80°	61.0	60.1	59.2	61.0	59.2	60.1	61.0	61.0	59.7	61.0	59.7
82.5°	42.4	43.0	42.1	42.1	42.1	43.0	42.4	43.5	42.9	43.5	42.2
85°	19.6	19.1	18.2	18.2	18.2	19.1	19.6	19.6	21.0	20.1	20.1
87.5°	7.8	7.5	7.6	7.3	7.6	7.5	7.8	7.8	7.6	8.2	8.0
90°	20.9	21.2	21.7	22.0	21.7	21.2	20.9	20.5	19.9	19.0	18.1
92.5°	21.3	21.6	21.8	22.0	21.8	21.6	21.3	21.1	20.8	20.3	19.8
95°	35.6	35.4	35.2	35.0	35.2	35.4	35.6	35.8	35.4	34.5	33.5
97.5°	46.1	46.3	46.5	46.7	46.5	46.3	46.1	45.8	45.4	44.7	44.0
100°	53.5	53.9	54.2	54.6	54.2	53.9	53.5	53.1	52.3	50.7	49.3
102.5°	57.0	57.4	58.0	58.5	58.0	57.4	57.0	56.4	55.3	53.4	51.5
105°	59.7	60.5	61.2	61.9	61.2	60.5	59.7	59.0	57.6	55.6	53.7
107.5°	61.5	62.2	63.0	63.7	63.0	62.2	61.5	60.8	61.4	63.5	65.5
110°	62.2	62.9	63.6	64.4	63.6	62.9	62.2	61.4	70.1	88.2	106.3



TEST NUMBER: P331357-940

CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	63.2	63.8	64.4	65.0	64.4	63.8	63.2	62.7	95.4	161.4	227.5
115°	105.8	92.8	79.8	66.8	79.8	92.8	105.8	118.9	167.3	251.1	334.9
117.5°	401.1	358.3	315.5	272.7	315.5	358.3	401.1	443.9	475.5	495.8	516.0
120°	570.1	545.6	521.2	496.8	521.2	545.6	570.1	594.5	605.6	603.5	601.3
122.5°	634.2	629.4	624.6	619.9	624.6	629.4	634.2	638.9	640.6	639.3	638.0
125°	694.6	695.2	695.8	696.3	695.8	695.2	694.6	694.1	693.2	692.0	690.7
127.5°	744.2	744.3	744.4	744.5	744.4	744.3	744.2	744.0	743.2	741.3	739.4
130°	775.1	774.8	774.6	774.5	774.6	774.8	775.1	775.3	774.3	772.3	770.3
132.5°	804.3	804.1	804.0	803.8	804.0	804.1	804.3	804.5	803.8	802.1	800.4
135°	847.2	846.9	846.5	846.1	846.5	846.9	847.2	847.6	846.9	845.1	843.3
137.5°	886.6	886.0	885.4	884.8	885.4	886.0	886.6	887.3	886.6	884.8	883.1
140°	911.6	910.7	909.8	908.8	909.8	910.7	911.6	912.5	912.1	910.5	908.8
142.5°	935.0	934.2	933.3	932.3	933.3	934.2	935.0	935.9	935.7	934.2	932.6
145°	967.8	966.9	966.0	965.1	966.0	966.9	967.8	968.7	968.5	967.2	966.0
147.5°	996.1	995.4	994.6	993.9	994.6	995.4	996.1	996.9	996.8	995.9	995.0
150°	1014.2	1013.3	1012.4	1011.5	1012.4	1013.3	1014.2	1015.1	1015.0	1014.0	1012.8
152.5°	1030.0	1028.9	1027.7	1026.4	1027.7	1028.9	1030.0	1031.3	1031.3	1030.2	1029.1
155°	1051.7	1050.2	1048.7	1047.3	1048.7	1050.2	1051.7	1053.1	1053.3	1052.2	1051.1
157.5°	1070.6	1069.2	1067.7	1066.4	1067.7	1069.2	1070.6	1072.0	1072.1	1070.9	1069.6
160°	1081.2	1080.0	1078.7	1077.5	1078.7	1080.0	1081.2	1082.5	1082.6	1081.6	1080.4
162.5°	1091.3	1089.7	1088.2	1086.5	1088.2	1089.7	1091.3	1092.8	1093.0	1091.7	1090.5
165°	1104.0	1102.8	1101.5	1100.3	1101.5	1102.8	1104.0	1105.3	1105.3	1104.0	1102.8
167.5°	1113.7	1112.1	1110.5	1108.8	1110.5	1112.1	1113.7	1115.4	1115.6	1114.3	1113.0
170°	1119.0	1117.3	1115.7	1114.1	1115.7	1117.3	1119.0	1120.6	1120.8	1119.5	1118.3
172.5°	1122.8	1121.2	1119.6	1118.0	1119.6	1121.2	1122.8	1124.5	1124.7	1123.5	1122.1
175°	1126.9	1125.1	1123.2	1121.4	1123.2	1125.1	1126.9	1128.6	1128.9	1127.7	1126.4
177.5°	1127.5	1126.1	1124.8	1123.6	1124.8	1126.1	1127.5	1128.7	1128.9	1127.9	1126.9
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331357-940
 CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1138.2	1142.2	1148.3	1154.9	1159.0	1166.6	1168.8	1172.4	1175.7	1183.4	1191.3
5°	1072.5	1078.8	1093.9	1102.1	1113.4	1126.6	1135.2	1144.4	1154.4	1171.7	1187.6
7.5°	1002.0	1012.6	1031.3	1046.6	1062.8	1081.7	1095.4	1113.4	1128.4	1152.7	1176.1
10°	955.0	970.0	986.9	1005.0	1027.9	1047.8	1067.0	1089.8	1108.0	1137.1	1164.4
12.5°	912.8	915.1	939.1	959.2	990.3	1015.1	1037.1	1066.5	1084.3	1118.9	1147.6
15°	838.9	852.6	874.4	890.4	927.3	958.7	989.6	1020.1	1040.6	1083.3	1121.1
17.5°	776.8	789.3	811.7	837.9	864.3	895.5	935.6	967.8	995.6	1044.6	1089.2
20°	737.4	752.9	775.7	802.5	825.7	859.9	894.5	931.3	961.4	1016.5	1068.8
22.5°	703.9	716.1	734.5	761.0	786.4	817.6	855.5	895.6	927.2	986.6	1039.6
25°	656.8	666.9	678.7	700.5	729.2	763.4	793.0	837.1	883.1	938.6	1002.8
27.5°	614.4	621.5	632.0	651.2	673.4	705.3	738.2	780.2	826.3	886.6	954.4
30°	588.6	593.2	603.6	619.6	641.4	666.4	699.6	739.7	787.0	848.0	915.4
32.5°	566.0	570.2	577.0	592.2	611.2	632.6	662.5	702.6	747.7	807.6	882.3
35°	532.2	535.3	541.3	553.5	564.0	585.0	609.9	646.4	688.8	746.1	823.5
37.5°	498.4	502.7	506.4	511.6	525.0	538.8	560.5	591.3	632.8	690.7	764.5
40°	476.2	479.7	485.3	487.5	498.5	510.8	528.5	556.7	598.6	651.4	723.4
42.5°	453.5	457.2	460.5	463.2	472.6	483.4	499.4	523.6	560.7	612.1	683.2
45°	422.8	423.3	426.5	431.5	436.0	443.8	455.2	476.2	504.8	553.0	617.7
47.5°	391.7	392.3	392.8	395.0	400.0	407.1	414.6	431.6	457.3	495.8	558.7
50°	371.0	370.1	371.0	372.8	376.0	381.9	390.6	402.9	423.8	459.8	517.5
52.5°	351.0	350.8	350.3	351.0	353.4	357.5	363.6	374.1	392.8	425.9	476.8
55°	320.5	318.2	318.6	316.8	320.9	321.8	326.4	335.0	351.4	374.2	422.0
57.5°	287.9	286.1	284.0	283.5	283.1	285.6	289.3	296.0	308.6	328.6	367.4
60°	267.2	264.9	262.2	261.3	261.3	262.6	264.5	269.5	281.3	299.1	330.9
62.5°	246.1	243.4	241.8	239.4	238.7	240.0	241.9	245.5	254.0	270.6	298.2
65°	213.5	210.3	208.0	207.6	206.7	205.3	206.2	209.8	216.7	229.9	251.7
67.5°	180.8	177.8	177.3	174.6	173.3	173.5	173.3	176.5	180.6	191.9	208.2
70°	159.3	157.0	156.1	153.8	152.9	152.0	151.1	153.8	157.9	167.6	181.6
72.5°	137.5	135.5	133.6	131.6	131.8	130.9	130.7	132.3	135.7	144.5	155.4
75°	106.0	106.6	104.2	101.9	101.5	100.6	100.6	101.9	103.3	110.1	118.8
77.5°	77.0	76.6	74.6	73.9	73.5	72.5	73.5	74.4	75.1	79.6	86.1
80°	58.8	58.8	56.4	56.4	56.0	54.7	56.0	55.1	56.9	61.4	66.0
82.5°	42.0	41.2	41.1	40.4	40.3	39.3	39.9	40.8	41.6	44.7	47.4
85°	20.5	20.5	20.1	19.6	20.1	19.6	20.1	20.5	21.0	22.3	24.6
87.5°	7.8	8.0	8.0	8.1	7.8	7.9	7.9	7.9	8.2	8.2	8.2
90°	17.2	16.3	14.8	13.4	11.9	10.5	8.7	6.8	4.8	2.8	0.8
92.5°	19.4	18.9	18.2	17.5	16.8	16.0	15.7	15.9	16.1	16.2	16.4
95°	32.6	31.7	30.5	29.2	28.0	26.7	29.1	35.0	41.0	47.0	53.0
97.5°	43.2	42.5	39.6	36.6	33.7	30.8	37.7	54.6	71.4	88.2	105.0
100°	47.9	46.5	43.3	40.3	37.2	34.2	44.9	69.7	94.5	119.3	144.2
102.5°	49.6	47.7	73.5	99.2	124.9	150.7	166.1	171.4	176.6	181.9	187.2
105°	51.6	49.7	99.1	148.5	197.9	247.3	269.3	263.9	258.4	253.0	247.5
107.5°	67.5	69.6	128.8	188.1	247.3	306.6	334.0	329.6	325.2	320.8	316.5
110°	124.4	142.5	194.8	247.1	299.4	351.7	375.9	372.2	368.4	364.6	360.8



TEST NUMBER: P331357-940

CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	293.5	359.4	372.4	385.3	398.2	411.2	415.9	412.6	409.2	405.8	402.4
115°	418.7	502.5	497.9	493.5	488.9	484.4	480.5	477.5	474.4	471.4	468.2
117.5°	536.3	556.5	553.5	550.4	547.2	544.1	540.8	537.4	534.0	530.5	527.1
120°	599.1	596.9	593.7	590.4	587.2	583.9	580.9	578.2	575.5	572.7	570.1
122.5°	636.7	635.4	631.9	628.3	624.7	621.2	618.0	615.1	612.2	609.4	606.5
125°	689.5	688.1	684.7	681.3	677.9	674.4	671.5	669.1	666.8	664.4	662.1
127.5°	737.5	735.8	733.2	730.6	728.0	725.4	722.8	720.2	717.6	715.1	712.4
130°	768.3	766.3	764.4	762.3	760.4	758.4	755.9	753.0	750.1	747.3	744.4
132.5°	798.7	796.9	795.0	793.0	791.0	789.0	786.8	784.3	781.9	779.4	776.9
135°	841.4	839.6	838.0	836.4	834.7	833.1	830.9	828.0	825.1	822.2	819.3
137.5°	881.3	879.6	877.7	875.8	874.0	872.2	870.2	868.2	866.2	864.2	862.1
140°	907.2	905.6	903.7	901.6	899.6	897.7	895.9	894.5	893.0	891.6	890.1
142.5°	931.2	929.7	927.5	925.1	922.8	920.6	918.8	917.5	916.2	914.9	913.6
145°	964.7	963.4	960.4	957.3	954.2	951.1	949.7	949.9	950.0	950.2	950.4
147.5°	994.0	993.1	990.1	987.0	983.9	980.9	979.7	980.4	981.1	981.8	982.5
150°	1011.7	1010.7	1007.8	1004.9	1002.0	999.1	998.3	999.5	1000.8	1002.1	1003.4
152.5°	1028.1	1027.0	1024.2	1021.5	1018.7	1015.9	1015.3	1016.7	1018.1	1019.5	1020.9
155°	1050.0	1048.9	1046.8	1044.6	1042.4	1040.3	1040.0	1041.6	1043.2	1044.9	1046.5
157.5°	1068.4	1067.2	1065.7	1064.2	1062.7	1061.1	1061.0	1062.4	1063.8	1065.1	1066.5
160°	1079.3	1078.3	1077.2	1076.1	1075.0	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3
162.5°	1089.2	1088.1	1087.1	1086.1	1085.2	1084.2	1084.3	1085.4	1086.5	1087.6	1088.7
165°	1101.5	1100.3	1099.7	1099.1	1098.6	1098.1	1098.3	1099.4	1100.5	1101.6	1102.7
167.5°	1111.8	1110.5	1110.0	1109.5	1109.0	1108.5	1108.8	1109.8	1111.0	1112.1	1113.1
170°	1117.0	1115.7	1115.4	1115.0	1114.6	1114.3	1114.6	1115.7	1116.8	1117.8	1119.0
172.5°	1120.9	1119.6	1119.3	1118.9	1118.6	1118.2	1118.6	1119.6	1120.7	1121.8	1122.8
175°	1125.2	1123.8	1123.5	1123.1	1122.8	1122.4	1122.8	1124.1	1125.4	1126.7	1127.9
177.5°	1125.9	1124.8	1124.7	1124.5	1124.4	1124.3	1124.7	1125.7	1126.8	1127.7	1128.7
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331357-940

CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1190.6	1192.5	1198.3	1204.1	1210.7	1212.5	1215.4	1212.8	1212.1	1219.1	1224.1
5°	1194.0	1202.2	1218.2	1232.7	1245.0	1253.7	1262.8	1266.4	1273.2	1282.7	1294.6
7.5°	1190.2	1206.1	1231.2	1252.3	1275.5	1292.2	1305.2	1316.3	1329.7	1347.8	1367.6
10°	1185.8	1207.2	1237.7	1263.6	1291.8	1313.2	1331.1	1348.3	1368.3	1393.4	1419.3
12.5°	1177.8	1203.2	1241.4	1272.0	1308.2	1329.3	1353.3	1390.5	1412.0	1446.9	1483.5
15°	1161.7	1189.9	1243.1	1280.9	1321.9	1362.0	1406.1	1441.6	1477.1	1497.6	1549.1
17.5°	1137.7	1179.2	1238.1	1282.2	1334.3	1397.4	1447.0	1487.2	1528.2	1561.5	1587.2
20°	1118.5	1163.5	1230.8	1283.7	1345.6	1413.4	1470.3	1511.3	1546.8	1574.6	1590.5
22.5°	1094.0	1150.8	1216.3	1278.2	1357.3	1424.3	1484.2	1516.4	1546.0	1559.6	1565.8
25°	1055.6	1123.9	1198.1	1273.6	1362.9	1433.9	1488.5	1508.1	1516.7	1503.5	1481.7
27.5°	1014.2	1090.3	1177.1	1265.1	1359.4	1427.7	1466.9	1463.7	1449.1	1406.4	1372.3
30°	983.2	1067.0	1160.3	1256.3	1351.0	1417.5	1440.3	1417.5	1384.3	1336.5	1287.8
32.5°	950.8	1037.5	1142.5	1243.9	1335.8	1394.2	1399.1	1359.9	1308.5	1254.2	1193.5
35°	901.8	995.5	1108.8	1216.3	1303.2	1340.2	1318.3	1249.1	1188.1	1113.9	1031.0
37.5°	846.3	949.9	1063.5	1175.8	1254.5	1264.2	1210.0	1137.1	1051.1	963.9	866.4
40°	804.8	914.5	1031.5	1144.9	1214.5	1204.4	1135.2	1055.2	952.7	846.2	755.6
42.5°	767.7	877.4	996.5	1107.7	1163.5	1136.0	1055.2	956.8	846.8	746.5	663.5
45°	703.3	816.2	938.2	1045.6	1077.5	1027.9	920.9	811.6	703.3	619.6	554.0
47.5°	640.9	752.4	873.3	967.7	978.9	912.2	795.3	682.9	589.8	521.6	475.3
50°	594.9	706.9	826.6	910.9	907.2	826.6	706.5	599.5	521.7	466.5	435.6
52.5°	553.8	659.6	774.5	851.1	831.9	744.0	629.3	534.3	470.3	427.2	399.2
55°	489.8	587.6	696.9	758.4	722.8	625.4	528.5	452.0	404.7	372.4	350.5
57.5°	426.2	518.0	611.5	649.4	610.2	520.2	439.3	383.9	348.3	324.4	310.1
60°	386.9	467.1	550.4	583.1	536.2	456.1	392.4	342.8	314.1	294.5	281.8
62.5°	347.6	419.4	497.9	515.8	472.9	405.1	348.7	307.5	283.8	266.4	254.5
65°	294.1	352.8	412.4	424.3	384.7	332.3	287.7	260.8	239.9	227.1	217.6
67.5°	241.2	288.3	330.6	340.1	305.4	269.1	236.9	213.5	199.3	188.7	180.7
70°	209.8	247.2	281.8	289.5	261.7	229.4	204.8	186.2	173.4	164.3	156.6
72.5°	176.7	207.9	236.6	241.8	219.1	194.5	174.2	159.6	148.3	142.5	135.1
75°	135.2	153.4	175.7	177.1	162.0	147.0	131.5	122.0	116.1	108.8	105.1
77.5°	95.4	109.7	122.4	124.9	116.0	105.8	97.1	89.6	84.5	81.2	77.8
80°	72.9	84.2	89.7	92.8	86.5	79.2	74.2	69.2	66.0	63.8	61.4
82.5°	52.1	59.1	64.2	66.6	63.2	58.9	53.8	51.0	48.5	46.6	45.8
85°	26.4	29.6	32.8	33.7	32.8	30.9	28.2	28.2	26.8	26.4	26.4
87.5°	9.6	11.5	11.9	13.4	13.0	13.3	13.6	13.6	13.5	13.3	13.1
90°	2.8	4.8	6.8	8.7	10.5	11.9	13.4	14.8	16.3	17.2	18.1
92.5°	16.2	16.1	15.9	15.7	16.0	16.8	17.5	18.2	18.9	19.4	19.8
95°	47.0	41.0	35.0	29.1	26.7	28.0	29.2	30.5	31.7	32.6	33.5
97.5°	88.2	71.4	54.6	37.7	30.8	33.7	36.6	39.6	42.5	43.2	44.0
100°	119.3	94.5	69.7	44.9	34.2	37.2	40.3	43.3	46.5	47.9	49.3
102.5°	181.9	176.6	171.4	166.1	150.7	124.9	99.2	73.5	47.7	49.6	51.5
105°	253.0	258.4	263.9	269.3	247.3	197.9	148.5	99.1	49.7	51.6	53.7
107.5°	320.8	325.2	329.6	334.0	306.6	247.3	188.1	128.8	69.6	67.5	65.5
110°	364.6	368.4	372.2	375.9	351.7	299.4	247.1	194.8	142.5	124.4	106.3



TEST NUMBER: P331357-940
 CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	405.8	409.2	412.6	415.9	411.2	398.2	385.3	372.4	359.4	293.5	227.5
115°	471.4	474.4	477.5	480.5	484.4	488.9	493.5	497.9	502.5	418.7	334.9
117.5°	530.5	534.0	537.4	540.8	544.1	547.2	550.4	553.5	556.5	536.3	516.0
120°	572.7	575.5	578.2	580.9	583.9	587.2	590.4	593.7	596.9	599.1	601.3
122.5°	609.4	612.2	615.1	618.0	621.2	624.7	628.3	631.9	635.4	636.7	638.0
125°	664.4	666.8	669.1	671.5	674.4	677.9	681.3	684.7	688.1	689.5	690.7
127.5°	715.1	717.6	720.2	722.8	725.4	728.0	730.6	733.2	735.8	737.5	739.4
130°	747.3	750.1	753.0	755.9	758.4	760.4	762.3	764.4	766.3	768.3	770.3
132.5°	779.4	781.9	784.3	786.8	789.0	791.0	793.0	795.0	796.9	798.7	800.4
135°	822.2	825.1	828.0	830.9	833.1	834.7	836.4	838.0	839.6	841.4	843.3
137.5°	864.2	866.2	868.2	870.2	872.2	874.0	875.8	877.7	879.6	881.3	883.1
140°	891.6	893.0	894.5	895.9	897.7	899.6	901.6	903.7	905.6	907.2	908.8
142.5°	914.9	916.2	917.5	918.8	920.6	922.8	925.1	927.5	929.7	931.2	932.6
145°	950.2	950.0	949.9	949.7	951.1	954.2	957.3	960.4	963.4	964.7	966.0
147.5°	981.8	981.1	980.4	979.7	980.9	983.9	987.0	990.1	993.1	994.0	995.0
150°	1002.1	1000.8	999.5	998.3	999.1	1002.0	1004.9	1007.8	1010.7	1011.7	1012.8
152.5°	1019.5	1018.1	1016.7	1015.3	1015.9	1018.7	1021.5	1024.2	1027.0	1028.1	1029.1
155°	1044.9	1043.2	1041.6	1040.0	1040.3	1042.4	1044.6	1046.8	1048.9	1050.0	1051.1
157.5°	1065.1	1063.8	1062.4	1061.0	1061.1	1062.7	1064.2	1065.7	1067.2	1068.4	1069.6
160°	1077.2	1076.1	1075.0	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3	1079.3	1080.4
162.5°	1087.6	1086.5	1085.4	1084.3	1084.2	1085.2	1086.1	1087.1	1088.1	1089.2	1090.5
165°	1101.6	1100.5	1099.4	1098.3	1098.1	1098.6	1099.1	1099.7	1100.3	1101.5	1102.8
167.5°	1112.1	1111.0	1109.8	1108.8	1108.5	1109.0	1109.5	1110.0	1110.5	1111.8	1113.0
170°	1117.8	1116.8	1115.7	1114.6	1114.3	1114.6	1115.0	1115.4	1115.7	1117.0	1118.3
172.5°	1121.8	1120.7	1119.6	1118.6	1118.2	1118.6	1118.9	1119.3	1119.6	1120.9	1122.1
175°	1126.7	1125.4	1124.1	1122.8	1122.4	1122.8	1123.1	1123.5	1123.8	1125.2	1126.4
177.5°	1127.7	1126.8	1125.7	1124.7	1124.3	1124.4	1124.5	1124.7	1124.8	1125.9	1126.9
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331357-940

CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1228.5	1233.6	1233.6	1234.3	1240.2	1239.4	1239.0
5°	1307.3	1315.1	1316.0	1324.2	1329.6	1327.8	1322.9
7.5°	1381.7	1396.2	1407.0	1413.1	1420.3	1424.8	1422.8
10°	1440.7	1461.7	1474.4	1483.1	1493.5	1501.3	1498.5
12.5°	1494.2	1519.2	1536.7	1551.5	1552.9	1562.8	1556.0
15°	1577.7	1604.1	1606.9	1617.8	1626.5	1625.5	1625.9
17.5°	1605.3	1613.8	1615.5	1615.8	1615.9	1612.7	1605.8
20°	1595.4	1592.3	1584.6	1578.7	1568.2	1566.8	1557.7
22.5°	1548.9	1538.7	1519.4	1506.5	1490.2	1485.9	1483.5
25°	1457.1	1434.8	1403.8	1374.2	1366.1	1350.1	1354.7
27.5°	1331.2	1296.5	1262.9	1238.9	1217.1	1193.3	1200.1
30°	1242.7	1203.5	1156.2	1119.8	1096.6	1073.8	1069.7
32.5°	1137.1	1079.8	1026.9	994.9	959.3	944.9	929.2
35°	955.0	899.0	846.7	801.6	775.7	755.6	737.4
37.5°	791.2	726.7	684.6	648.0	629.3	617.8	620.7
40°	689.6	633.2	602.3	574.4	557.1	548.9	550.8
42.5°	607.3	565.1	539.6	520.6	508.4	503.8	502.7
45°	513.9	490.3	469.3	458.4	452.5	447.5	444.3
47.5°	450.2	430.9	419.1	412.6	407.4	402.3	402.3
50°	412.0	399.2	391.0	384.1	380.1	376.5	379.6
52.5°	382.8	371.1	363.0	356.9	355.3	352.0	352.0
55°	339.6	330.5	324.6	319.1	316.4	314.5	312.3
57.5°	300.2	291.6	286.1	282.7	277.5	275.6	274.9
60°	272.2	265.4	259.9	255.4	253.1	249.4	249.4
62.5°	246.4	239.5	234.4	231.0	227.2	225.8	226.1
65°	208.9	203.5	198.5	194.8	193.9	191.2	192.1
67.5°	174.5	170.9	165.6	163.6	161.8	160.4	159.3
70°	151.6	147.9	145.2	142.5	141.1	141.1	141.1
72.5°	132.2	127.9	126.3	122.8	123.6	122.2	120.7
75°	102.5	99.7	98.4	96.9	94.7	94.7	94.7
77.5°	75.3	74.5	72.9	71.4	70.9	70.4	70.6
80°	58.2	57.8	56.9	56.9	56.0	55.6	54.7
82.5°	44.8	43.6	43.1	42.7	42.5	42.4	42.3
85°	25.5	24.6	24.6	25.1	24.2	24.2	24.6
87.5°	13.6	13.8	13.6	13.6	14.1	13.8	13.8
90°	19.0	19.9	20.5	20.9	21.2	21.7	22.0
92.5°	20.3	20.8	21.1	21.3	21.6	21.8	22.0
95°	34.5	35.4	35.8	35.6	35.4	35.2	35.0
97.5°	44.7	45.4	45.8	46.1	46.3	46.5	46.7
100°	50.7	52.3	53.1	53.5	53.9	54.2	54.6
102.5°	53.4	55.3	56.4	57.0	57.4	58.0	58.5
105°	55.6	57.6	59.0	59.7	60.5	61.2	61.9
107.5°	63.5	61.4	60.8	61.5	62.2	63.0	63.7
110°	88.2	70.1	61.4	62.2	62.9	63.6	64.4



TEST NUMBER: P331357-940
 CATALOG NUMBER: SA2XXDIP-C675D925U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	161.4	95.4	62.7	63.2	63.8	64.4	65.0
115°	251.1	167.3	118.9	105.8	92.8	79.8	66.8
117.5°	495.8	475.5	443.9	401.1	358.3	315.5	272.7
120°	603.5	605.6	594.5	570.1	545.6	521.2	496.8
122.5°	639.3	640.6	638.9	634.2	629.4	624.6	619.9
125°	692.0	693.2	694.1	694.6	695.2	695.8	696.3
127.5°	741.3	743.2	744.0	744.2	744.3	744.4	744.5
130°	772.3	774.3	775.3	775.1	774.8	774.6	774.5
132.5°	802.1	803.8	804.5	804.3	804.1	804.0	803.8
135°	845.1	846.9	847.6	847.2	846.9	846.5	846.1
137.5°	884.8	886.6	887.3	886.6	886.0	885.4	884.8
140°	910.5	912.1	912.5	911.6	910.7	909.8	908.8
142.5°	934.2	935.7	935.9	935.0	934.2	933.3	932.3
145°	967.2	968.5	968.7	967.8	966.9	966.0	965.1
147.5°	995.9	996.8	996.9	996.1	995.4	994.6	993.9
150°	1014.0	1015.0	1015.1	1014.2	1013.3	1012.4	1011.5
152.5°	1030.2	1031.3	1031.3	1030.0	1028.9	1027.7	1026.4
155°	1052.2	1053.3	1053.1	1051.7	1050.2	1048.7	1047.3
157.5°	1070.9	1072.1	1072.0	1070.6	1069.2	1067.7	1066.4
160°	1081.6	1082.6	1082.5	1081.2	1080.0	1078.7	1077.5
162.5°	1091.7	1093.0	1092.8	1091.3	1089.7	1088.2	1086.5
165°	1104.0	1105.3	1105.3	1104.0	1102.8	1101.5	1100.3
167.5°	1114.3	1115.6	1115.4	1113.7	1112.1	1110.5	1108.8
170°	1119.5	1120.8	1120.6	1119.0	1117.3	1115.7	1114.1
172.5°	1123.5	1124.7	1124.5	1122.8	1121.2	1119.6	1118.0
175°	1127.7	1128.9	1128.6	1126.9	1125.1	1123.2	1121.4
177.5°	1127.9	1128.9	1128.7	1127.5	1126.1	1124.8	1123.6
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5

(END OF REPORT)