

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331417-940

Luminaire Tested: **SA2XXDIP-C865D1080U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331417-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6973.1 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331417-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331417-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	71	68	66	57	56	54	45	44	43	38
2	88	81	75	69	80	74	69	64	62	58	55	50	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19869	19869	19869
5°	19945	19656	19772
10°	19825	19457	19556
15°	19580	19206	19184
20°	19234	18826	18806
25°	18887	18360	18360
30°	18442	17935	17780
35°	18027	17422	17164
40°	17506	16910	16583
45°	16993	16401	15995
50°	16435	15872	15307
55°	15854	15254	14688
60°	15206	14518	13986
65°	14514	13788	13154
70°	13629	12902	12288
75°	12402	11884	11584
80°	11000	10674	10126
85°	8985	8559	7669



TEST NUMBER: P331417-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.7	1.7
10°-20°	325.6	4.7
20°-30°	478.6	6.9
30°-40°	555.9	8.0
40°-50°	555.3	8.0
50°-60°	484.3	6.9
60°-70°	358.1	5.1
70°-80°	202.8	2.9
80°-90°	57.8	0.8
90°-100°	43.7	0.6
100°-110°	160.2	2.3
110°-120°	428.4	6.1
120°-130°	707.1	10.1
130°-140°	752.0	10.8
140°-150°	699.0	10.0
150°-160°	562.0	8.1
160°-170°	362.1	5.2
170°-180°	124.6	1.8
0°-30°	919.9	13.2
0°-40°	1475.8	21.2
0°-60°	2515.4	36.1
0°-90°	3134.0	44.9
90°-120°	632.3	9.1
90°-150°	2790.4	40.0
90°-180°	3839.0	55.1
0°-180°	6973.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1231	1225	1213	1222	1220	117
15°	1171	1164	1149	1153	1148	330
25°	1060	1050	1031	1033	1031	488
35°	915	902	884	877	871	571
45°	744	735	718	706	700	574
55°	563	556	542	528	522	503
65°	380	372	361	350	344	376
75°	199	196	190	184	186	212
85°	48	47	46	43	41	56
90°	1	11	19	24	26	5
95°	62	32	37	41	41	75
105°	288	301	58	68	72	308
115°	545	562	585	167	78	537
125°	771	783	801	807	810	687
135°	954	968	977	986	985	736
145°	1106	1106	1121	1127	1123	692
155°	1218	1211	1221	1226	1219	561
165°	1284	1278	1281	1287	1281	362
175°	1313	1307	1308	1314	1305	125
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P331417-940
 CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1236.3	1235.2	1234.1	1233.1	1232.1	1230.4	1228.1	1225.7	1223.4	1221.1	1223.2
5°	1230.6	1229.5	1228.5	1227.4	1226.4	1224.4	1221.6	1218.6	1215.8	1212.8	1215.0
7.5°	1219.7	1218.1	1216.5	1214.8	1213.2	1210.9	1207.9	1205.0	1202.0	1199.1	1201.2
10°	1209.2	1207.5	1205.6	1203.7	1201.9	1199.4	1196.2	1193.1	1190.0	1186.8	1188.9
12.5°	1195.1	1193.5	1191.9	1190.2	1188.6	1186.2	1183.0	1179.8	1176.7	1173.6	1175.0
15°	1171.4	1169.8	1168.2	1166.7	1165.1	1162.6	1159.2	1155.7	1152.4	1149.0	1150.0
17.5°	1141.1	1139.5	1138.0	1136.4	1134.8	1132.3	1128.8	1125.3	1121.9	1118.4	1119.6
20°	1119.4	1117.8	1116.2	1114.6	1113.0	1110.4	1106.7	1103.0	1099.4	1095.7	1096.4
22.5°	1097.6	1095.4	1093.1	1090.9	1088.8	1085.9	1082.4	1079.0	1075.5	1072.0	1072.2
25°	1060.2	1058.1	1056.0	1053.9	1051.8	1048.5	1044.0	1039.6	1035.1	1030.6	1031.2
27.5°	1017.6	1015.7	1013.8	1011.9	1010.0	1007.3	1003.8	1000.2	996.8	993.2	992.5
30°	989.2	987.1	985.0	982.9	980.8	977.8	973.8	969.9	965.9	962.0	961.2
32.5°	958.9	957.3	955.6	953.9	952.2	949.2	945.1	940.9	936.8	932.6	931.2
35°	914.6	912.0	909.4	906.8	904.1	900.7	896.5	892.3	888.1	883.9	882.3
37.5°	864.7	862.4	860.1	857.7	855.5	852.2	848.0	843.8	839.5	835.4	833.4
40°	830.6	828.6	826.4	824.3	822.2	819.0	814.8	810.7	806.5	802.3	799.9
42.5°	797.5	795.4	793.3	791.2	789.1	786.0	781.8	777.6	773.3	769.1	766.5
45°	744.2	742.4	740.6	738.8	736.9	734.0	730.0	726.1	722.2	718.3	715.3
47.5°	691.3	689.6	687.8	686.1	684.3	681.4	677.3	673.2	669.1	664.9	661.9
50°	654.3	653.0	651.8	650.4	649.1	646.6	642.9	639.2	635.5	631.9	628.2
52.5°	618.4	616.6	614.9	613.1	611.4	608.9	605.4	601.9	598.4	594.9	591.9
55°	563.2	561.7	560.1	558.5	556.9	554.6	551.4	548.2	545.1	541.9	538.8
57.5°	507.8	506.6	505.3	504.1	502.8	500.4	497.0	493.5	490.0	486.5	483.5
60°	470.9	469.8	468.9	467.8	466.7	464.4	460.7	457.0	453.3	449.6	446.7
62.5°	435.0	433.3	431.6	429.9	428.2	426.0	423.1	420.3	417.4	414.6	412.0
65°	379.9	378.3	376.7	375.1	373.5	371.4	368.8	366.1	363.6	360.9	358.6
67.5°	323.8	322.4	321.2	319.9	318.7	316.9	314.5	312.1	309.8	307.4	305.6
70°	288.7	287.7	286.6	285.5	284.5	282.8	280.4	278.0	275.7	273.3	271.5
72.5°	252.7	251.7	250.7	249.6	248.5	247.3	245.8	244.2	242.6	241.1	239.3
75°	198.8	198.2	197.7	197.2	196.7	195.7	194.5	193.1	191.8	190.5	189.0
77.5°	150.5	149.6	148.7	147.8	147.0	146.2	145.7	145.2	144.6	144.1	143.3
80°	118.3	118.1	117.8	117.5	117.3	116.9	116.4	115.8	115.3	114.8	114.0
82.5°	88.0	88.0	87.9	87.8	87.8	87.7	87.3	87.0	86.7	86.4	85.3
85°	48.5	48.2	48.0	47.7	47.4	47.2	46.9	46.6	46.4	46.2	45.4
87.5°	17.2	17.3	17.3	17.4	17.4	17.4	17.3	17.2	17.1	17.0	16.6
90°	1.0	3.3	5.6	7.9	10.3	12.2	13.9	15.6	17.3	19.0	20.0
92.5°	19.2	18.9	18.7	18.5	18.3	18.6	19.4	20.3	21.1	22.0	22.6
95°	61.6	54.7	47.7	40.8	33.8	31.0	32.5	34.1	35.5	37.0	38.0
97.5°	122.3	102.7	83.1	63.5	44.0	35.8	39.2	42.6	46.1	49.5	50.3
100°	167.8	138.9	110.0	81.2	52.3	39.7	43.2	46.9	50.5	54.0	55.7
102.5°	217.8	211.7	205.6	199.5	193.4	175.4	145.4	115.5	85.5	55.6	57.8
105°	288.2	294.5	300.8	307.1	313.4	287.8	230.3	172.8	115.3	57.8	60.1
107.5°	368.4	373.4	378.5	383.6	388.8	356.9	287.8	218.9	149.9	81.0	78.6
110°	419.9	424.4	428.8	433.2	437.7	409.4	348.5	287.7	226.8	165.9	144.8



TEST NUMBER: P331417-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	468.5	472.4	476.3	480.2	484.1	478.6	463.5	448.5	433.5	418.4	341.6
115°	545.1	548.7	552.2	555.8	559.4	563.8	569.1	574.4	579.6	584.9	487.3
117.5°	613.5	617.5	621.5	625.5	629.5	633.3	636.9	640.6	644.2	647.8	624.2
120°	663.5	666.7	669.9	673.1	676.2	679.7	683.5	687.2	691.1	694.8	697.3
122.5°	706.1	709.4	712.7	716.0	719.3	723.1	727.2	731.3	735.5	739.6	741.1
125°	770.7	773.4	776.1	778.9	781.6	785.0	789.0	793.0	797.0	801.0	802.5
127.5°	829.3	832.3	835.4	838.4	841.4	844.4	847.4	850.3	853.4	856.4	858.5
130°	866.4	869.8	873.2	876.6	879.9	882.7	885.0	887.3	889.7	892.0	894.3
132.5°	904.3	907.2	910.1	912.9	915.8	918.4	920.7	923.0	925.3	927.6	929.6
135°	953.6	957.0	960.4	963.8	967.1	969.7	971.6	973.5	975.4	977.3	979.5
137.5°	1003.4	1005.8	1008.2	1010.6	1012.9	1015.1	1017.4	1019.5	1021.6	1023.8	1025.8
140°	1036.1	1037.8	1039.5	1041.2	1042.9	1044.8	1047.1	1049.5	1051.8	1054.1	1056.0
142.5°	1063.4	1064.9	1066.4	1067.9	1069.4	1071.6	1074.2	1076.8	1079.5	1082.2	1083.9
145°	1106.3	1106.0	1105.8	1105.6	1105.4	1107.1	1110.6	1114.2	1117.8	1121.4	1122.8
147.5°	1143.6	1142.8	1142.0	1141.2	1140.4	1141.7	1145.3	1148.8	1152.4	1155.9	1157.0
150°	1167.9	1166.4	1164.9	1163.4	1162.0	1162.9	1166.3	1169.7	1173.0	1176.3	1177.7
152.5°	1188.3	1186.7	1185.0	1183.4	1181.8	1182.5	1185.7	1188.9	1192.1	1195.3	1196.6
155°	1218.1	1216.2	1214.3	1212.4	1210.5	1210.9	1213.4	1215.8	1218.4	1220.9	1222.2
157.5°	1241.4	1239.8	1238.2	1236.6	1235.0	1235.1	1236.9	1238.6	1240.4	1242.2	1243.6
160°	1255.1	1253.8	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1256.3
162.5°	1267.2	1266.0	1264.6	1263.4	1262.1	1262.0	1263.1	1264.3	1265.3	1266.4	1267.8
165°	1283.5	1282.2	1280.9	1279.7	1278.4	1278.1	1278.7	1279.4	1280.1	1280.7	1282.1
167.5°	1295.7	1294.4	1293.1	1291.8	1290.6	1290.2	1290.8	1291.4	1292.0	1292.6	1294.1
170°	1302.4	1301.2	1299.9	1298.7	1297.4	1297.0	1297.4	1297.8	1298.2	1298.7	1300.1
172.5°	1307.0	1305.7	1304.5	1303.2	1302.0	1301.5	1302.0	1302.3	1302.8	1303.2	1304.7
175°	1312.9	1311.4	1309.9	1308.5	1307.0	1306.4	1306.9	1307.3	1307.7	1308.1	1309.7
177.5°	1313.8	1312.7	1311.4	1310.3	1309.1	1308.6	1308.8	1308.9	1309.1	1309.3	1310.5
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331417-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1225.3	1227.4	1229.5	1230.4	1229.9	1229.5	1229.1	1228.7
5°	1217.0	1219.1	1221.3	1222.0	1221.6	1221.0	1220.5	1219.9
7.5°	1203.3	1205.4	1207.6	1208.3	1207.7	1207.1	1206.6	1205.9
10°	1191.0	1193.1	1195.2	1195.9	1195.1	1194.3	1193.5	1192.8
12.5°	1176.5	1177.9	1179.5	1179.9	1179.3	1178.8	1178.1	1177.6
15°	1151.0	1152.1	1153.2	1153.0	1151.7	1150.4	1149.1	1147.7
17.5°	1120.8	1122.0	1123.3	1123.2	1122.0	1120.7	1119.5	1118.2
20°	1097.3	1098.1	1098.9	1098.7	1097.7	1096.6	1095.6	1094.5
22.5°	1072.4	1072.5	1072.6	1072.5	1071.7	1071.1	1070.5	1069.9
25°	1031.7	1032.2	1032.7	1032.7	1032.2	1031.7	1031.2	1030.6
27.5°	991.7	990.9	990.1	989.1	987.7	986.5	985.3	984.0
30°	960.4	959.7	958.9	957.9	956.9	955.8	954.8	953.7
32.5°	929.8	928.4	926.9	925.7	924.7	923.6	922.6	921.5
35°	880.7	879.1	877.6	876.1	874.9	873.5	872.2	870.8
37.5°	831.5	829.6	827.6	826.0	824.7	823.5	822.2	820.9
40°	797.5	795.1	792.8	791.0	790.1	789.0	787.9	786.8
42.5°	763.9	761.3	758.8	756.8	755.3	753.9	752.3	750.9
45°	712.5	709.5	706.7	704.7	703.6	702.6	701.5	700.5
47.5°	658.9	655.9	652.8	650.5	649.0	647.5	646.0	644.4
50°	624.5	620.8	617.2	614.7	613.3	612.0	610.7	609.4
52.5°	588.8	585.8	582.7	580.3	578.6	576.8	575.2	573.4
55°	535.7	532.4	529.3	527.1	525.8	524.4	523.2	521.8
57.5°	480.4	477.2	474.1	472.1	471.1	470.1	469.1	468.1
60°	443.9	441.0	438.1	436.2	435.4	434.6	433.8	433.1
62.5°	409.2	406.5	403.9	402.1	401.0	400.0	399.0	398.1
65°	356.1	353.8	351.4	349.6	348.3	347.0	345.6	344.3
67.5°	303.7	301.8	300.1	298.6	297.6	296.5	295.4	294.4
70°	269.7	267.8	266.0	264.5	263.5	262.4	261.4	260.3
72.5°	237.5	235.6	233.8	232.5	231.6	230.8	229.9	229.1
75°	187.3	185.7	184.2	183.7	184.2	184.8	185.2	185.7
77.5°	142.6	141.8	141.0	140.2	139.5	138.8	138.0	137.2
80°	113.2	112.4	111.6	110.9	110.4	109.9	109.4	108.9
82.5°	84.4	83.4	82.4	81.9	81.7	81.6	81.5	81.4
85°	44.6	43.8	43.0	42.4	42.2	41.9	41.6	41.4
87.5°	16.2	15.8	15.3	15.1	15.0	14.8	14.7	14.6
90°	21.0	22.1	23.2	23.9	24.3	24.8	25.1	25.6
92.5°	23.1	23.6	24.2	24.6	24.9	25.1	25.3	25.6
95°	39.1	40.1	41.2	41.6	41.4	41.2	40.9	40.8
97.5°	51.2	52.0	52.9	53.4	53.7	53.9	54.1	54.4
100°	57.4	59.1	60.8	61.8	62.2	62.7	63.1	63.5
102.5°	59.9	62.2	64.3	65.7	66.3	66.9	67.5	68.0
105°	62.4	64.7	67.1	68.7	69.6	70.4	71.2	72.1
107.5°	76.2	73.8	71.5	70.8	71.6	72.4	73.3	74.1
110°	123.8	102.7	81.6	71.5	72.3	73.2	74.0	74.9



TEST NUMBER: P331417-940

CATALOG NUMBER: SA2XXDIP-C865D1080U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	264.7	187.9	111.0	72.9	73.7	74.3	75.0	75.6
115°	389.8	292.3	194.7	138.4	123.2	108.1	92.9	77.8
117.5°	600.7	577.0	553.5	516.7	466.9	417.1	367.2	317.4
120°	699.9	702.4	705.0	692.0	663.5	635.1	606.6	578.3
122.5°	742.6	744.1	745.6	743.6	738.2	732.6	727.1	721.6
125°	804.0	805.4	806.9	808.0	808.6	809.2	809.9	810.5
127.5°	860.7	862.8	865.0	866.1	866.2	866.4	866.5	866.6
130°	896.6	898.9	901.3	902.3	902.1	901.9	901.7	901.5
132.5°	931.6	933.6	935.6	936.5	936.2	936.0	935.9	935.6
135°	981.5	983.6	985.7	986.6	986.1	985.7	985.3	984.9
137.5°	1027.9	1029.9	1032.0	1032.7	1032.0	1031.3	1030.6	1029.8
140°	1057.9	1059.8	1061.7	1062.1	1061.0	1060.0	1058.9	1057.9
142.5°	1085.6	1087.4	1089.0	1089.4	1088.3	1087.3	1086.3	1085.2
145°	1124.4	1125.8	1127.3	1127.5	1126.5	1125.4	1124.4	1123.3
147.5°	1158.1	1159.2	1160.3	1160.4	1159.5	1158.6	1157.7	1156.8
150°	1178.9	1180.2	1181.4	1181.5	1180.4	1179.5	1178.4	1177.3
152.5°	1197.8	1199.2	1200.4	1200.3	1198.9	1197.6	1196.1	1194.8
155°	1223.4	1224.8	1226.0	1225.7	1224.1	1222.4	1220.8	1219.1
157.5°	1245.0	1246.4	1247.9	1247.8	1246.2	1244.5	1242.9	1241.2
160°	1257.6	1258.8	1260.1	1260.0	1258.6	1257.0	1255.6	1254.1
162.5°	1269.3	1270.7	1272.2	1271.9	1270.2	1268.4	1266.5	1264.7
165°	1283.6	1285.0	1286.6	1286.6	1285.0	1283.6	1282.1	1280.7
167.5°	1295.6	1297.0	1298.5	1298.2	1296.4	1294.5	1292.6	1290.7
170°	1301.6	1303.1	1304.6	1304.3	1302.4	1300.6	1298.7	1296.7
172.5°	1306.2	1307.6	1309.1	1308.9	1307.0	1305.1	1303.2	1301.3
175°	1311.1	1312.6	1314.0	1313.8	1311.6	1309.5	1307.4	1305.3
177.5°	1311.6	1312.8	1314.0	1313.8	1312.3	1310.8	1309.3	1307.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0

(END OF REPORT)