

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331382-940

Luminaire Tested: **SA2XXDIP-C865D330U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331382-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D330U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4176.1 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331382-940
CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331382-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	103	99	95	91	98	94	91	87	85	83	80	77	75	73	70	68	67	63
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	62	59	56	53
3	86	76	68	62	81	73	66	60	66	61	56	60	56	52	55	51	48	45
4	79	67	59	53	75	64	57	51	59	53	48	54	49	45	49	45	41	38
5	72	60	52	45	69	58	50	44	53	46	41	48	43	39	44	40	36	33
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	35	32	29
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	37	32	28	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	25	23
9	54	41	33	28	51	39	32	27	36	30	26	34	28	24	31	26	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19869	19869	19869
5°	19945	19656	19772
10°	19825	19457	19556
15°	19580	19206	19184
20°	19234	18826	18806
25°	18887	18360	18360
30°	18442	17935	17780
35°	18027	17422	17164
40°	17506	16910	16583
45°	16993	16401	15995
50°	16435	15872	15307
55°	15854	15254	14688
60°	15206	14518	13986
65°	14514	13788	13154
70°	13629	12902	12288
75°	12402	11884	11584
80°	11000	10674	10126
85°	8985	8559	7669



TEST NUMBER: P331382-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.7	2.8
10°-20°	325.6	7.8
20°-30°	478.6	11.5
30°-40°	555.9	13.3
40°-50°	555.3	13.3
50°-60°	484.3	11.6
60°-70°	358.1	8.6
70°-80°	202.8	4.9
80°-90°	56.0	1.3
90°-100°	23.7	0.6
100°-110°	73.5	1.8
110°-120°	125.6	3.0
120°-130°	165.1	4.0
130°-140°	185.4	4.4
140°-150°	181.8	4.4
150°-160°	152.4	3.7
160°-170°	101.1	2.4
170°-180°	35.3	0.8
0°-30°	919.9	22.0
0°-40°	1475.8	35.3
0°-60°	2515.4	60.2
0°-90°	3132.3	75.0
90°-120°	222.7	5.3
90°-150°	755.0	18.1
90°-180°	1044.0	25.0
0°-180°	4176.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1231	1225	1213	1222	1220	117
15°	1171	1164	1149	1153	1148	330
25°	1060	1050	1031	1033	1031	488
35°	915	902	884	877	871	571
45°	744	735	718	706	700	574
55°	563	556	542	528	522	503
65°	380	372	361	350	344	376
75°	199	196	190	184	186	212
85°	48	47	46	43	41	56
90°	0	4	11	10	11	3
95°	16	19	20	20	20	19
105°	68	69	69	70	70	72
115°	126	128	127	127	126	125
125°	183	186	185	184	184	164
135°	237	241	241	241	240	183
145°	288	290	292	292	291	180
155°	329	330	331	333	332	151
165°	358	358	358	360	359	101
175°	373	372	371	373	371	35
180°	373	373	373	373	373	



TEST NUMBER: P331382-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1236.3	1235.2	1234.1	1233.1	1232.1	1230.4	1228.1	1225.7	1223.4	1221.1	1223.2
5°	1230.6	1229.5	1228.5	1227.4	1226.4	1224.4	1221.6	1218.6	1215.8	1212.8	1215.0
7.5°	1219.7	1218.1	1216.5	1214.8	1213.2	1210.9	1207.9	1205.0	1202.0	1199.1	1201.2
10°	1209.2	1207.5	1205.6	1203.7	1201.9	1199.4	1196.2	1193.1	1190.0	1186.8	1188.9
12.5°	1195.1	1193.5	1191.9	1190.2	1188.6	1186.2	1183.0	1179.8	1176.7	1173.6	1175.0
15°	1171.4	1169.8	1168.2	1166.7	1165.1	1162.6	1159.2	1155.7	1152.4	1149.0	1150.0
17.5°	1141.1	1139.5	1138.0	1136.4	1134.8	1132.3	1128.8	1125.3	1121.9	1118.4	1119.6
20°	1119.4	1117.8	1116.2	1114.6	1113.0	1110.4	1106.7	1103.0	1099.4	1095.7	1096.4
22.5°	1097.6	1095.4	1093.1	1090.9	1088.8	1085.9	1082.4	1079.0	1075.5	1072.0	1072.2
25°	1060.2	1058.1	1056.0	1053.9	1051.8	1048.5	1044.0	1039.6	1035.1	1030.6	1031.2
27.5°	1017.6	1015.7	1013.8	1011.9	1010.0	1007.3	1003.8	1000.2	996.8	993.2	992.5
30°	989.2	987.1	985.0	982.9	980.8	977.8	973.8	969.9	965.9	962.0	961.2
32.5°	958.9	957.3	955.6	953.9	952.2	949.2	945.1	940.9	936.8	932.6	931.2
35°	914.6	912.0	909.4	906.8	904.1	900.7	896.5	892.3	888.1	883.9	882.3
37.5°	864.7	862.4	860.1	857.7	855.5	852.2	848.0	843.8	839.5	835.4	833.4
40°	830.6	828.6	826.4	824.3	822.2	819.0	814.8	810.7	806.5	802.3	799.9
42.5°	797.5	795.4	793.3	791.2	789.1	786.0	781.8	777.6	773.3	769.1	766.5
45°	744.2	742.4	740.6	738.8	736.9	734.0	730.0	726.1	722.2	718.3	715.3
47.5°	691.3	689.6	687.8	686.1	684.3	681.4	677.3	673.2	669.1	664.9	661.9
50°	654.3	653.0	651.8	650.4	649.1	646.6	642.9	639.2	635.5	631.9	628.2
52.5°	618.4	616.6	614.9	613.1	611.4	608.9	605.4	601.9	598.4	594.9	591.9
55°	563.2	561.7	560.1	558.5	556.9	554.6	551.4	548.2	545.1	541.9	538.8
57.5°	507.8	506.6	505.3	504.1	502.8	500.4	497.0	493.5	490.0	486.5	483.5
60°	470.9	469.8	468.9	467.8	466.7	464.4	460.7	457.0	453.3	449.6	446.7
62.5°	435.0	433.3	431.6	429.9	428.2	426.0	423.1	420.3	417.4	414.6	412.0
65°	379.9	378.3	376.7	375.1	373.5	371.4	368.8	366.1	363.6	360.9	358.6
67.5°	323.8	322.4	321.2	319.9	318.7	316.9	314.5	312.1	309.8	307.4	305.6
70°	288.7	287.7	286.6	285.5	284.5	282.8	280.4	278.0	275.7	273.3	271.5
72.5°	252.7	251.7	250.7	249.6	248.5	247.3	245.8	244.2	242.6	241.1	239.3
75°	198.8	198.2	197.7	197.2	196.7	195.7	194.5	193.1	191.8	190.5	189.0
77.5°	150.5	149.6	148.7	147.8	147.0	146.2	145.7	145.2	144.6	144.1	143.3
80°	118.3	118.1	117.8	117.5	117.3	116.9	116.4	115.8	115.3	114.8	114.0
82.5°	88.0	88.0	87.9	87.8	87.8	87.7	87.3	87.0	86.7	86.4	85.3
85°	48.5	48.2	48.0	47.7	47.4	47.2	46.9	46.6	46.4	46.2	45.4
87.5°	17.1	16.9	16.6	16.3	16.1	15.9	15.8	15.7	15.6	15.4	14.8
90°	0.4	1.2	2.0	2.9	3.7	4.9	6.4	7.9	9.5	11.1	10.9
92.5°	5.6	6.2	6.9	7.5	8.1	8.6	8.9	9.3	9.6	10.0	10.1
95°	16.4	17.1	17.7	18.5	19.2	19.6	19.7	19.9	20.1	20.2	20.2
97.5°	30.0	30.6	31.1	31.7	32.4	32.8	33.1	33.3	33.6	33.9	33.9
100°	40.0	40.6	41.1	41.7	42.3	42.6	42.8	43.1	43.2	43.5	43.5
102.5°	50.6	51.0	51.5	51.9	52.3	52.8	53.0	53.2	53.5	53.8	53.9
105°	67.8	67.9	68.1	68.4	68.6	68.8	68.9	69.0	69.2	69.3	69.5
107.5°	85.0	85.3	85.6	86.0	86.2	86.4	86.4	86.4	86.4	86.4	86.4
110°	96.1	96.5	96.9	97.4	97.7	98.0	98.0	98.0	98.0	98.0	98.0



TEST NUMBER: P331382-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	108.2	108.6	109.1	109.4	109.9	110.0	109.9	109.9	109.9	109.9	109.7
115°	126.0	126.4	126.9	127.2	127.7	127.9	127.7	127.5	127.4	127.2	127.2
117.5°	143.7	144.4	144.9	145.4	146.1	146.2	145.7	145.3	144.9	144.5	144.4
120°	155.6	156.2	156.8	157.3	157.8	157.8	157.3	156.8	156.2	155.6	155.6
122.5°	166.5	167.1	167.8	168.4	169.2	169.3	168.9	168.5	168.1	167.7	167.6
125°	183.3	184.0	184.6	185.2	185.8	186.1	185.8	185.7	185.5	185.2	185.0
127.5°	199.8	200.6	201.4	202.2	203.0	203.2	203.0	202.8	202.5	202.2	202.0
130°	210.2	211.1	212.0	212.9	213.7	214.2	214.0	213.9	213.7	213.6	213.5
132.5°	221.8	222.5	223.2	223.9	224.7	225.1	225.1	225.2	225.2	225.2	224.9
135°	237.2	238.0	238.8	239.5	240.3	240.8	240.9	241.0	241.2	241.3	241.2
137.5°	253.5	254.1	254.8	255.5	256.1	256.5	256.6	256.8	257.0	257.2	257.2
140°	263.4	264.0	264.7	265.3	265.9	266.4	266.7	267.1	267.4	267.8	267.8
142.5°	273.5	274.1	274.7	275.4	276.0	276.4	276.6	276.9	277.1	277.3	277.4
145°	287.9	288.5	288.9	289.4	289.9	290.3	290.8	291.2	291.6	292.0	292.1
147.5°	300.9	301.5	302.0	302.6	303.2	303.6	303.9	304.3	304.5	304.8	305.0
150°	309.7	310.1	310.5	310.9	311.4	311.7	312.0	312.3	312.5	312.8	313.1
152.5°	317.5	317.9	318.3	318.8	319.1	319.6	319.9	320.2	320.6	320.9	321.2
155°	329.2	329.4	329.7	329.8	330.0	330.3	330.5	330.6	330.9	331.1	331.4
157.5°	339.2	339.4	339.5	339.7	339.8	339.9	340.1	340.2	340.3	340.5	340.9
160°	345.3	345.4	345.5	345.7	345.8	346.0	346.0	346.1	346.2	346.3	346.6
162.5°	350.8	350.9	350.9	350.9	351.0	351.0	351.1	351.2	351.2	351.2	351.8
165°	358.2	358.1	358.0	358.0	357.9	357.8	357.8	357.8	357.8	357.8	358.4
167.5°	364.4	364.2	364.0	363.7	363.6	363.5	363.4	363.4	363.4	363.4	363.8
170°	367.7	367.5	367.2	367.0	366.8	366.7	366.6	366.5	366.5	366.4	366.8
172.5°	369.9	369.7	369.5	369.3	369.1	368.9	368.9	368.8	368.7	368.6	369.2
175°	372.7	372.5	372.3	372.0	371.8	371.7	371.6	371.4	371.2	371.1	371.6
177.5°	373.8	373.6	373.4	373.4	373.2	373.0	372.9	372.8	372.6	372.6	372.9
180°	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4



TEST NUMBER: P331382-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1225.3	1227.4	1229.5	1230.4	1229.9	1229.5	1229.1	1228.7
5°	1217.0	1219.1	1221.3	1222.0	1221.6	1221.0	1220.5	1219.9
7.5°	1203.3	1205.4	1207.6	1208.3	1207.7	1207.1	1206.6	1205.9
10°	1191.0	1193.1	1195.2	1195.9	1195.1	1194.3	1193.5	1192.8
12.5°	1176.5	1177.9	1179.5	1179.9	1179.3	1178.8	1178.1	1177.6
15°	1151.0	1152.1	1153.2	1153.0	1151.7	1150.4	1149.1	1147.7
17.5°	1120.8	1122.0	1123.3	1123.2	1122.0	1120.7	1119.5	1118.2
20°	1097.3	1098.1	1098.9	1098.7	1097.7	1096.6	1095.6	1094.5
22.5°	1072.4	1072.5	1072.6	1072.5	1071.7	1071.1	1070.5	1069.9
25°	1031.7	1032.2	1032.7	1032.7	1032.2	1031.7	1031.2	1030.6
27.5°	991.7	990.9	990.1	989.1	987.7	986.5	985.3	984.0
30°	960.4	959.7	958.9	957.9	956.9	955.8	954.8	953.7
32.5°	929.8	928.4	926.9	925.7	924.7	923.6	922.6	921.5
35°	880.7	879.1	877.6	876.1	874.9	873.5	872.2	870.8
37.5°	831.5	829.6	827.6	826.0	824.7	823.5	822.2	820.9
40°	797.5	795.1	792.8	791.0	790.1	789.0	787.9	786.8
42.5°	763.9	761.3	758.8	756.8	755.3	753.9	752.3	750.9
45°	712.5	709.5	706.7	704.7	703.6	702.6	701.5	700.5
47.5°	658.9	655.9	652.8	650.5	649.0	647.5	646.0	644.4
50°	624.5	620.8	617.2	614.7	613.3	612.0	610.7	609.4
52.5°	588.8	585.8	582.7	580.3	578.6	576.8	575.2	573.4
55°	535.7	532.4	529.3	527.1	525.8	524.4	523.2	521.8
57.5°	480.4	477.2	474.1	472.1	471.1	470.1	469.1	468.1
60°	443.9	441.0	438.1	436.2	435.4	434.6	433.8	433.1
62.5°	409.2	406.5	403.9	402.1	401.0	400.0	399.0	398.1
65°	356.1	353.8	351.4	349.6	348.3	347.0	345.6	344.3
67.5°	303.7	301.8	300.1	298.6	297.6	296.5	295.4	294.4
70°	269.7	267.8	266.0	264.5	263.5	262.4	261.4	260.3
72.5°	237.5	235.6	233.8	232.5	231.6	230.8	229.9	229.1
75°	187.3	185.7	184.2	183.7	184.2	184.8	185.2	185.7
77.5°	142.6	141.8	141.0	140.2	139.5	138.8	138.0	137.2
80°	113.2	112.4	111.6	110.9	110.4	109.9	109.4	108.9
82.5°	84.4	83.4	82.4	81.9	81.7	81.6	81.5	81.4
85°	44.6	43.8	43.0	42.4	42.2	41.9	41.6	41.4
87.5°	14.2	13.5	12.8	12.4	12.2	12.0	11.8	11.6
90°	10.8	10.6	10.4	10.4	10.5	10.6	10.6	10.7
92.5°	10.1	10.1	10.2	10.2	10.2	10.2	10.2	10.2
95°	20.2	20.2	20.2	20.1	20.0	19.8	19.7	19.5
97.5°	33.9	33.9	33.9	33.9	33.9	33.9	33.9	33.8
100°	43.5	43.5	43.5	43.4	43.3	43.3	43.2	43.2
102.5°	53.9	53.9	54.0	54.0	53.9	53.9	53.9	53.8
105°	69.6	69.7	69.9	69.9	69.9	69.9	69.9	69.9
107.5°	86.5	86.6	86.6	86.5	86.1	85.9	85.5	85.2
110°	98.0	98.0	98.0	97.9	97.6	97.5	97.3	97.0



TEST NUMBER: P331382-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	109.5	109.3	109.1	109.0	108.9	108.7	108.5	108.3
115°	127.2	127.1	127.0	126.9	126.6	126.4	126.3	126.0
117.5°	144.2	144.0	143.8	143.7	143.5	143.3	143.0	142.9
120°	155.6	155.6	155.6	155.5	155.3	155.1	154.9	154.7
122.5°	167.4	167.2	167.0	166.9	166.7	166.6	166.4	166.3
125°	184.9	184.6	184.4	184.2	184.2	184.1	184.0	184.0
127.5°	201.8	201.5	201.3	201.0	200.8	200.5	200.4	200.1
130°	213.3	213.2	213.0	212.9	212.6	212.2	212.0	211.7
132.5°	224.5	224.3	224.0	223.7	223.5	223.3	223.0	222.8
135°	241.2	241.1	241.0	240.9	240.7	240.5	240.3	240.0
137.5°	257.1	257.0	257.0	256.8	256.5	256.3	256.0	255.7
140°	267.8	267.8	267.8	267.6	267.3	267.1	266.8	266.5
142.5°	277.5	277.5	277.6	277.5	277.2	276.9	276.6	276.3
145°	292.2	292.2	292.3	292.2	291.9	291.7	291.4	291.1
147.5°	305.1	305.2	305.4	305.3	305.1	304.8	304.5	304.3
150°	313.3	313.4	313.7	313.7	313.4	313.3	313.1	312.8
152.5°	321.5	321.7	322.0	322.0	321.7	321.5	321.2	320.9
155°	331.8	332.2	332.5	332.6	332.3	332.2	332.0	331.7
157.5°	341.3	341.9	342.3	342.4	342.1	341.7	341.4	341.1
160°	347.1	347.5	347.9	347.9	347.7	347.4	347.1	346.9
162.5°	352.2	352.7	353.2	353.2	352.9	352.6	352.2	351.9
165°	358.8	359.4	359.8	359.9	359.5	359.2	358.8	358.6
167.5°	364.4	364.8	365.3	365.4	365.1	364.6	364.3	363.9
170°	367.4	367.8	368.4	368.4	368.0	367.6	367.1	366.7
172.5°	369.6	370.1	370.6	370.7	370.2	369.8	369.4	369.0
175°	372.1	372.6	373.1	373.1	372.7	372.3	371.8	371.4
177.5°	373.3	373.5	373.9	373.9	373.5	373.3	372.9	372.6
180°	373.4	373.4	373.4	373.4	373.4	373.4	373.4	373.4

(END OF REPORT)