

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332611-930

Luminaire Tested: **SA4XXDIP-C795D1035U930-4F0-1E-UDD-D1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332611-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C795D1035U930-4F0-1E-UDD-D1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5562.4 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332611-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P332611-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	96	91	87	83	87	83	80	76	69	66	64	55	54	52	43	42	41	35
2	87	79	72	67	79	72	67	62	60	56	52	48	45	43	38	35	34	29
3	79	69	61	55	72	63	57	51	52	47	43	42	39	36	33	30	28	24
4	72	61	53	46	65	56	49	43	46	41	37	37	33	30	29	26	24	20
5	66	54	46	39	60	50	42	37	41	36	31	33	29	26	26	23	21	17
6	61	48	40	34	55	44	37	32	37	31	27	30	26	23	24	21	18	15
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	22	18	16	13
8	52	39	31	26	47	36	29	24	30	25	21	25	21	18	20	17	14	12
9	48	36	28	23	44	33	26	22	28	22	19	23	19	16	18	15	13	11
10	45	33	25	21	41	30	24	19	26	20	17	21	17	14	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6252	6252	6252
5°	6271	6110	6128
10°	6233	6010	6006
15°	6177	5894	5862
20°	6093	5766	5723
25°	5998	5624	5569
30°	5895	5481	5411
35°	5779	5336	5274
40°	5685	5196	5129
45°	5547	5069	5005
50°	5430	4922	4876
55°	5310	4783	4722
60°	5121	4605	4583
65°	4915	4414	4411
70°	4666	4197	4210
75°	4318	3960	4029
80°	3929	3731	3851
85°	3441	3526	3748



TEST NUMBER: P332611-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	1.3
10°-20°	210.1	3.8
20°-30°	317.7	5.7
30°-40°	384.4	6.9
40°-50°	406.4	7.3
50°-60°	382.5	6.9
60°-70°	317.3	5.7
70°-80°	222.9	4.0
80°-90°	129.2	2.3
90°-100°	144.2	2.6
100°-110°	261.0	4.7
110°-120°	386.1	6.9
120°-130°	481.1	8.6
130°-140°	525.8	9.5
140°-150°	509.6	9.2
150°-160°	427.1	7.7
160°-170°	284.1	5.1
170°-180°	99.5	1.8
0°-30°	601.2	10.8
0°-40°	985.6	17.7
0°-60°	1774.4	31.9
0°-90°	2443.8	43.9
90°-120°	791.3	14.2
90°-150°	2307.8	41.5
90°-180°	3119.0	56.1
0°-180°	5562.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	774	774	774	774	774	
5°	775	772	767	773	773	74
15°	743	744	741	749	748	209
25°	680	685	688	697	698	313
35°	595	605	614	626	629	372
45°	496	513	529	543	548	383
55°	388	407	433	449	455	346
65°	269	297	326	347	355	266
75°	149	182	218	241	250	159
85°	46	83	121	146	156	49
90°	16	60	104	133	142	12
95°	60	96	137	162	171	63
105°	197	216	251	274	284	210
115°	360	369	394	412	417	355
125°	520	521	540	554	559	464
135°	668	673	679	691	694	517
145°	811	813	814	818	819	507
155°	928	928	927	930	927	427
165°	1010	1008	1006	1010	1008	285
175°	1051	1047	1046	1051	1046	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332611-930
 CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	774.5	774.5	774.5	774.5	774.5	774.5	774.5	774.5	774.5	774.5	774.5
2.5°	777.2	776.7	776.2	775.8	775.3	774.5	773.2	772.0	770.8	769.6	770.6
5°	775.3	774.7	774.1	773.6	773.0	772.0	770.6	769.3	767.9	766.6	768.2
7.5°	768.7	768.3	768.0	767.7	767.3	766.5	765.5	764.3	763.2	762.1	763.9
10°	763.1	763.0	762.8	762.5	762.4	761.8	760.8	759.9	758.9	757.9	759.7
12.5°	755.5	755.5	755.5	755.4	755.4	755.0	754.4	753.7	753.0	752.4	754.0
15°	743.2	743.4	743.6	743.8	744.0	743.8	743.2	742.7	742.0	741.4	743.2
17.5°	726.4	726.9	727.5	728.1	728.7	728.9	728.8	728.7	728.6	728.5	730.3
20°	714.6	715.2	715.8	716.3	716.9	717.3	717.5	717.6	717.9	718.0	720.0
22.5°	701.4	702.1	702.9	703.6	704.3	704.9	705.2	705.6	705.9	706.3	708.2
25°	679.9	681.0	682.2	683.4	684.5	685.4	686.0	686.6	687.1	687.7	689.8
27.5°	656.0	657.6	659.3	661.0	662.8	664.1	665.0	665.8	666.7	667.6	669.5
30°	640.0	641.6	643.1	644.7	646.2	647.6	649.0	650.3	651.7	653.0	655.1
32.5°	622.6	624.5	626.4	628.2	630.1	631.7	633.2	634.7	636.3	637.7	640.2
35°	594.9	597.2	599.6	601.9	604.1	606.3	608.2	610.2	612.0	614.0	616.7
37.5°	567.0	569.6	572.3	574.9	577.6	580.2	582.5	584.9	587.3	589.7	592.5
40°	548.9	551.5	553.9	556.4	559.0	561.6	564.3	567.0	569.6	572.3	575.3
42.5°	528.2	530.9	533.8	536.5	539.4	542.3	545.5	548.7	551.9	555.0	558.2
45°	496.0	499.7	503.4	507.0	510.7	514.4	518.0	521.7	525.3	529.0	532.3
47.5°	465.4	469.1	472.9	476.7	480.5	484.5	488.7	492.9	497.2	501.4	504.8
50°	443.1	447.4	451.6	455.8	460.1	464.3	468.6	472.8	477.0	481.3	485.2
52.5°	420.9	425.2	429.4	433.7	437.9	442.5	447.3	452.2	457.1	461.9	465.7
55°	388.5	392.6	396.6	400.6	404.7	409.6	415.4	421.2	427.0	432.8	436.6
57.5°	352.3	357.3	362.3	367.3	372.3	377.6	383.4	389.1	394.9	400.6	405.2
60°	328.6	333.7	338.7	343.7	348.7	354.4	360.8	367.1	373.5	379.8	384.3
62.5°	305.7	311.3	316.7	322.2	327.7	333.6	340.0	346.3	352.7	359.1	363.5
65°	268.8	275.0	281.2	287.3	293.5	299.9	306.4	313.0	319.5	326.0	330.8
67.5°	233.3	239.9	246.4	252.9	259.5	266.3	273.3	280.3	287.3	294.3	299.2
70°	209.0	215.6	222.1	228.7	235.2	242.1	249.5	256.8	264.1	271.4	276.6
72.5°	185.4	192.1	198.9	205.5	212.2	219.5	227.3	235.1	242.9	250.6	255.7
75°	149.2	156.3	163.4	170.6	177.7	185.3	193.4	201.5	209.6	217.7	223.1
77.5°	115.4	122.9	130.4	138.0	145.5	153.6	162.1	170.6	179.0	187.5	193.0
80°	94.5	102.2	109.9	117.6	125.4	133.5	141.9	150.4	158.9	167.4	173.2
82.5°	73.7	81.7	89.8	97.8	105.7	114.1	122.5	131.0	139.5	148.0	153.8
85°	46.0	54.1	62.1	70.3	78.4	86.7	95.4	104.0	112.8	121.4	127.2
87.5°	26.2	34.4	42.6	51.0	59.2	67.7	76.4	85.1	93.9	102.6	108.4
90°	16.3	26.0	35.7	45.4	55.1	64.8	74.5	84.3	94.0	103.8	110.4
92.5°	30.6	39.8	49.0	58.2	67.4	76.7	86.0	95.3	104.6	113.9	120.0
95°	60.1	68.1	76.1	84.1	92.0	100.6	109.8	119.0	128.2	137.3	143.0
97.5°	95.6	102.3	109.1	115.9	122.6	130.7	140.0	149.3	158.6	167.9	173.6
100°	123.4	129.2	134.9	140.6	146.4	153.8	163.0	172.1	181.2	190.5	196.0
102.5°	153.4	158.1	162.8	167.5	172.1	178.9	187.8	196.6	205.5	214.3	219.9
105°	197.4	201.5	205.5	209.5	213.5	219.5	227.4	235.2	243.0	250.9	256.2
107.5°	245.2	248.7	252.0	255.4	258.8	263.9	270.8	277.6	284.5	291.3	296.5
110°	277.1	280.1	283.2	286.3	289.3	294.2	300.8	307.3	313.9	320.4	324.5



TEST NUMBER: P332611-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	310.3	312.7	315.2	317.6	320.1	324.4	330.5	336.6	342.8	348.9	353.0
115°	360.0	361.7	363.5	365.3	367.0	370.7	376.5	382.3	388.2	394.0	398.0
117.5°	407.6	408.9	410.1	411.2	412.5	415.8	421.3	426.7	432.3	437.7	441.2
120°	438.9	440.2	441.5	442.8	444.1	447.3	452.3	457.4	462.4	467.5	470.4
122.5°	472.1	472.5	472.9	473.3	473.7	476.5	481.4	486.5	491.5	496.5	499.8
125°	520.2	520.0	519.8	519.7	519.4	521.7	526.3	530.9	535.6	540.2	543.5
127.5°	564.5	564.8	565.2	565.5	565.9	567.8	571.2	574.5	578.0	581.4	584.5
130°	595.0	595.4	595.7	596.1	596.5	598.2	601.2	604.3	607.4	610.5	613.6
132.5°	627.0	627.1	627.4	627.5	627.8	629.0	631.4	633.7	636.0	638.3	641.2
135°	668.2	669.3	670.4	671.5	672.5	673.8	675.1	676.5	677.8	679.1	681.9
137.5°	714.1	714.4	714.8	715.1	715.3	716.0	717.0	717.9	718.8	719.7	722.1
140°	744.7	744.9	745.0	745.2	745.4	745.6	745.8	745.9	746.2	746.3	748.7
142.5°	772.0	772.3	772.7	773.0	773.3	773.3	773.1	772.8	772.6	772.3	774.5
145°	810.6	811.1	811.6	812.2	812.7	813.0	813.3	813.4	813.6	813.8	814.7
147.5°	849.0	849.6	850.4	851.0	851.7	852.0	851.8	851.7	851.5	851.4	851.4
150°	872.5	872.9	873.5	874.0	874.6	874.8	874.8	874.8	874.8	874.8	874.8
152.5°	893.9	894.3	894.6	895.0	895.4	895.7	895.9	896.0	896.2	896.3	896.7
155°	927.7	927.7	927.7	927.7	927.7	927.6	927.4	927.2	927.1	926.9	927.6
157.5°	956.3	956.0	955.7	955.4	955.0	954.9	954.8	954.8	954.8	954.7	955.3
160°	973.3	973.1	972.9	972.7	972.6	972.4	972.2	972.0	971.8	971.7	972.2
162.5°	988.9	988.5	988.0	987.5	987.0	986.7	986.5	986.3	986.2	985.9	986.9
165°	1009.9	1009.3	1008.9	1008.3	1007.7	1007.3	1006.9	1006.6	1006.2	1005.8	1006.9
167.5°	1026.1	1025.2	1024.5	1023.8	1023.0	1022.6	1022.6	1022.7	1022.7	1022.8	1023.9
170°	1035.1	1034.2	1033.3	1032.4	1031.5	1031.1	1031.4	1031.5	1031.7	1031.8	1033.0
172.5°	1041.6	1040.9	1040.2	1039.3	1038.6	1038.2	1038.3	1038.3	1038.4	1038.4	1039.6
175°	1050.6	1049.7	1048.8	1047.9	1047.0	1046.4	1046.3	1046.0	1045.9	1045.7	1047.0
177.5°	1053.5	1052.8	1052.1	1051.3	1050.6	1050.3	1050.3	1050.3	1050.3	1050.3	1051.2
180°	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2



TEST NUMBER: P332611-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	774.5	774.5	774.5	774.5	774.5	774.5	774.5	774.5
2.5°	771.7	772.8	773.9	774.4	774.2	774.0	773.9	773.7
5°	769.7	771.3	772.7	773.5	773.2	773.1	772.9	772.7
7.5°	765.6	767.3	769.1	769.8	769.6	769.4	769.2	769.1
10°	761.4	763.1	764.9	765.6	765.5	765.2	765.1	764.9
12.5°	755.5	757.2	758.7	759.5	759.5	759.4	759.4	759.3
15°	744.9	746.7	748.4	749.2	749.0	748.8	748.6	748.4
17.5°	732.0	733.8	735.6	736.4	736.2	736.1	735.9	735.7
20°	721.9	723.8	725.8	726.8	726.8	726.8	726.8	726.8
22.5°	710.1	712.0	714.0	715.1	715.4	715.7	716.0	716.3
25°	691.9	694.1	696.2	697.3	697.5	697.7	697.9	698.1
27.5°	671.5	673.4	675.5	676.5	676.8	677.0	677.3	677.4
30°	657.2	659.3	661.5	662.8	663.2	663.5	663.9	664.3
32.5°	642.6	645.1	647.4	648.9	649.2	649.6	650.0	650.4
35°	619.4	622.1	624.8	626.4	627.0	627.5	628.2	628.8
37.5°	595.2	597.9	600.6	602.3	602.9	603.6	604.1	604.8
40°	578.1	581.1	583.9	585.7	586.5	587.3	588.1	588.8
42.5°	561.4	564.6	567.8	569.7	570.3	571.0	571.6	572.2
45°	535.6	538.8	542.1	544.2	545.2	546.2	547.1	548.0
47.5°	508.2	511.6	515.0	517.2	518.4	519.6	520.7	521.9
50°	489.0	492.8	496.7	499.2	500.3	501.6	502.7	503.9
52.5°	469.6	473.4	477.3	479.8	480.9	482.1	483.2	484.5
55°	440.4	444.3	448.2	450.7	451.8	453.0	454.1	455.3
57.5°	409.9	414.4	419.0	421.8	422.9	424.0	425.1	426.2
60°	388.7	393.1	397.5	400.6	402.1	403.7	405.2	406.8
62.5°	367.9	372.3	376.7	379.8	381.3	382.9	384.3	385.9
65°	335.7	340.6	345.4	348.5	350.1	351.6	353.1	354.7
67.5°	304.1	309.0	313.9	317.1	318.6	320.1	321.6	323.1
70°	281.8	287.1	292.3	295.5	296.9	298.2	299.5	300.9
72.5°	260.7	265.8	270.8	274.1	275.6	277.1	278.6	280.1
75°	228.4	233.8	239.3	242.8	244.6	246.3	248.0	249.7
77.5°	198.4	203.9	209.4	213.0	214.9	216.7	218.6	220.5
80°	179.0	184.7	190.5	194.1	195.7	197.2	198.8	200.3
82.5°	159.8	165.8	171.7	175.5	177.2	178.9	180.6	182.3
85°	133.0	138.8	144.6	148.4	150.3	152.2	154.2	156.1
87.5°	114.2	120.0	125.8	129.6	131.4	133.1	134.9	136.7
90°	117.1	123.8	130.4	134.8	136.6	138.5	140.5	142.4
92.5°	126.1	132.2	138.3	142.2	143.9	145.7	147.5	149.2
95°	148.8	154.5	160.3	164.0	165.8	167.5	169.3	171.0
97.5°	179.3	185.0	190.7	194.4	196.0	197.7	199.3	201.0
100°	201.5	207.1	212.7	216.1	217.5	218.8	220.2	221.5
102.5°	225.4	231.0	236.5	240.1	241.7	243.4	245.1	246.7
105°	261.6	267.0	272.4	276.1	278.2	280.2	282.3	284.4
107.5°	301.8	307.0	312.3	315.6	316.9	318.3	319.6	321.0
110°	328.6	332.6	336.7	339.8	341.9	344.0	346.0	348.1



TEST NUMBER: P332611-930

CATALOG NUMBER: SA4XXDIP-C795D1035U930-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	357.3	361.5	365.7	368.6	370.2	371.9	373.6	375.2
115°	402.0	406.1	410.2	412.8	413.9	415.2	416.3	417.4
117.5°	444.5	447.9	451.3	453.6	454.8	455.9	457.1	458.3
120°	473.4	476.3	479.2	481.7	483.6	485.5	487.4	489.3
122.5°	503.0	506.2	509.5	511.5	512.3	513.0	513.7	514.5
125°	546.8	550.1	553.4	555.5	556.3	557.1	557.8	558.6
127.5°	587.6	590.7	593.9	595.9	596.9	597.9	598.9	600.0
130°	616.7	619.8	622.9	624.7	625.1	625.6	626.0	626.4
132.5°	644.2	647.2	650.1	652.0	652.9	653.8	654.6	655.5
135°	684.6	687.4	690.1	691.7	692.4	692.9	693.6	694.1
137.5°	724.5	726.8	729.1	730.8	731.9	733.0	734.1	735.2
140°	751.0	753.3	755.6	757.2	758.0	758.8	759.5	760.3
142.5°	776.7	778.8	781.0	782.4	783.2	784.0	784.7	785.5
145°	815.7	816.7	817.7	818.3	818.5	818.7	819.0	819.2
147.5°	851.4	851.4	851.4	851.7	852.1	852.5	853.0	853.4
150°	874.8	874.8	874.8	874.7	874.6	874.3	874.2	874.0
152.5°	897.2	897.6	898.1	898.1	897.6	897.1	896.6	896.1
155°	928.4	929.0	929.8	929.8	929.0	928.4	927.6	926.9
157.5°	955.8	956.3	956.9	956.8	956.3	955.6	955.0	954.4
160°	972.7	973.3	973.8	973.6	972.7	971.8	970.9	970.0
162.5°	987.9	988.9	989.9	989.9	989.0	988.1	987.2	986.3
165°	1008.0	1009.1	1010.2	1010.3	1009.7	1008.9	1008.2	1007.5
167.5°	1024.9	1026.1	1027.1	1027.1	1026.0	1024.8	1023.7	1022.6
170°	1034.0	1035.1	1036.2	1036.1	1034.9	1033.6	1032.3	1031.0
172.5°	1040.8	1042.0	1043.3	1043.3	1042.0	1040.7	1039.5	1038.2
175°	1048.2	1049.5	1050.8	1050.8	1049.5	1048.2	1047.0	1045.7
177.5°	1052.3	1053.3	1054.3	1054.3	1053.1	1051.9	1050.8	1049.6
180°	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2

(END OF REPORT)