

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331383-940

Luminaire Tested: **SA2XXDIP-C865D330U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331383-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D330U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4272.3 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331383-940
CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331383-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	87	87	87	78	78	78	73
1	103	99	94	91	98	94	90	87	85	82	79	76	74	72	69	67	66	62
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	58	55	52
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	54	50	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	41	38
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	35	33
6	67	54	46	39	63	52	44	38	47	41	36	43	38	34	39	35	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	45	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	23	21
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19869	19869	19869
5°	19945	19656	19772
10°	19825	19457	19556
15°	19580	19206	19184
20°	19234	18826	18806
25°	18887	18360	18360
30°	18442	17935	17780
35°	18027	17422	17164
40°	17506	16910	16583
45°	16993	16401	15995
50°	16435	15872	15307
55°	15854	15254	14688
60°	15206	14518	13986
65°	14514	13788	13154
70°	13629	12902	12288
75°	12402	11884	11584
80°	11000	10674	10126
85°	8985	8559	7669



TEST NUMBER: P331383-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.7	2.7
10°-20°	325.6	7.6
20°-30°	478.6	11.2
30°-40°	555.9	13.0
40°-50°	555.3	13.0
50°-60°	484.3	11.3
60°-70°	358.1	8.4
70°-80°	202.8	4.7
80°-90°	56.0	1.3
90°-100°	65.5	1.5
100°-110°	222.3	5.2
110°-120°	236.2	5.5
120°-130°	194.4	4.6
130°-140°	156.1	3.7
140°-150°	118.0	2.8
150°-160°	82.9	1.9
160°-170°	48.8	1.1
170°-180°	15.9	0.4
0°-30°	919.9	21.5
0°-40°	1475.8	34.5
0°-60°	2515.4	58.9
0°-90°	3132.2	73.3
90°-120°	524.0	12.3
90°-150°	992.5	23.2
90°-180°	1140.0	26.7
0°-180°	4272.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1231	1225	1213	1222	1220	117
15°	1171	1164	1149	1153	1148	330
25°	1060	1050	1031	1033	1031	488
35°	915	902	884	877	871	571
45°	744	735	718	706	700	574
55°	563	556	542	528	522	503
65°	380	372	361	350	344	376
75°	199	196	190	184	186	212
85°	48	47	46	43	41	56
90°	0	4	11	10	10	3
95°	11	27	124	47	36	12
105°	38	58	233	417	355	41
115°	68	86	195	403	467	67
125°	94	112	188	327	379	84
135°	111	132	186	274	314	86
145°	127	146	185	229	251	79
155°	144	155	179	203	211	66
165°	157	162	172	182	185	44
175°	164	164	165	167	167	16
180°	164	164	164	164	164	



TEST NUMBER: P331383-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1236.3	1235.2	1234.1	1233.1	1232.1	1230.4	1228.1	1225.7	1223.4	1221.1	1223.2
5°	1230.6	1229.5	1228.5	1227.4	1226.4	1224.4	1221.6	1218.6	1215.8	1212.8	1215.0
7.5°	1219.7	1218.1	1216.5	1214.8	1213.2	1210.9	1207.9	1205.0	1202.0	1199.1	1201.2
10°	1209.2	1207.5	1205.6	1203.7	1201.9	1199.4	1196.2	1193.1	1190.0	1186.8	1188.9
12.5°	1195.1	1193.5	1191.9	1190.2	1188.6	1186.2	1183.0	1179.8	1176.7	1173.6	1175.0
15°	1171.4	1169.8	1168.2	1166.7	1165.1	1162.6	1159.2	1155.7	1152.4	1149.0	1150.0
17.5°	1141.1	1139.5	1138.0	1136.4	1134.8	1132.3	1128.8	1125.3	1121.9	1118.4	1119.6
20°	1119.4	1117.8	1116.2	1114.6	1113.0	1110.4	1106.7	1103.0	1099.4	1095.7	1096.4
22.5°	1097.6	1095.4	1093.1	1090.9	1088.8	1085.9	1082.4	1079.0	1075.5	1072.0	1072.2
25°	1060.2	1058.1	1056.0	1053.9	1051.8	1048.5	1044.0	1039.6	1035.1	1030.6	1031.2
27.5°	1017.6	1015.7	1013.8	1011.9	1010.0	1007.3	1003.8	1000.2	996.8	993.2	992.5
30°	989.2	987.1	985.0	982.9	980.8	977.8	973.8	969.9	965.9	962.0	961.2
32.5°	958.9	957.3	955.6	953.9	952.2	949.2	945.1	940.9	936.8	932.6	931.2
35°	914.6	912.0	909.4	906.8	904.1	900.7	896.5	892.3	888.1	883.9	882.3
37.5°	864.7	862.4	860.1	857.7	855.5	852.2	848.0	843.8	839.5	835.4	833.4
40°	830.6	828.6	826.4	824.3	822.2	819.0	814.8	810.7	806.5	802.3	799.9
42.5°	797.5	795.4	793.3	791.2	789.1	786.0	781.8	777.6	773.3	769.1	766.5
45°	744.2	742.4	740.6	738.8	736.9	734.0	730.0	726.1	722.2	718.3	715.3
47.5°	691.3	689.6	687.8	686.1	684.3	681.4	677.3	673.2	669.1	664.9	661.9
50°	654.3	653.0	651.8	650.4	649.1	646.6	642.9	639.2	635.5	631.9	628.2
52.5°	618.4	616.6	614.9	613.1	611.4	608.9	605.4	601.9	598.4	594.9	591.9
55°	563.2	561.7	560.1	558.5	556.9	554.6	551.4	548.2	545.1	541.9	538.8
57.5°	507.8	506.6	505.3	504.1	502.8	500.4	497.0	493.5	490.0	486.5	483.5
60°	470.9	469.8	468.9	467.8	466.7	464.4	460.7	457.0	453.3	449.6	446.7
62.5°	435.0	433.3	431.6	429.9	428.2	426.0	423.1	420.3	417.4	414.6	412.0
65°	379.9	378.3	376.7	375.1	373.5	371.4	368.8	366.1	363.6	360.9	358.6
67.5°	323.8	322.4	321.2	319.9	318.7	316.9	314.5	312.1	309.8	307.4	305.6
70°	288.7	287.7	286.6	285.5	284.5	282.8	280.4	278.0	275.7	273.3	271.5
72.5°	252.7	251.7	250.7	249.6	248.5	247.3	245.8	244.2	242.6	241.1	239.3
75°	198.8	198.2	197.7	197.2	196.7	195.7	194.5	193.1	191.8	190.5	189.0
77.5°	150.5	149.6	148.7	147.8	147.0	146.2	145.7	145.2	144.6	144.1	143.3
80°	118.3	118.1	117.8	117.5	117.3	116.9	116.4	115.8	115.3	114.8	114.0
82.5°	88.0	88.0	87.9	87.8	87.8	87.7	87.3	87.0	86.7	86.4	85.3
85°	48.5	48.2	48.0	47.7	47.4	47.2	46.9	46.6	46.4	46.2	45.4
87.5°	17.1	16.9	16.7	16.4	16.1	15.9	15.8	15.8	15.8	15.4	14.7
90°	0.4	1.2	2.5	3.1	3.7	4.7	6.3	8.5	10.4	10.7	10.4
92.5°	3.8	5.5	7.8	9.2	11.3	14.3	21.4	31.5	40.4	40.9	34.6
95°	11.1	12.3	15.4	18.3	23.3	30.9	45.4	72.8	109.3	123.5	108.1
97.5°	17.9	19.6	23.0	27.3	33.1	41.6	59.8	98.1	158.8	210.8	221.1
100°	24.3	25.2	28.0	33.1	39.4	48.2	64.9	103.3	171.4	248.9	294.3
102.5°	30.1	30.8	33.6	38.6	45.2	54.0	69.5	103.6	166.6	250.1	321.5
105°	38.4	39.7	41.9	46.6	53.6	62.4	77.2	105.2	157.2	233.4	317.3
107.5°	47.5	48.5	50.6	55.0	61.9	70.8	85.2	109.6	152.6	215.5	289.6
110°	53.6	54.8	56.7	60.8	67.4	76.6	90.4	113.1	151.6	207.0	272.2



TEST NUMBER: P331383-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	59.1	60.4	62.5	66.3	72.7	82.1	95.5	116.9	151.8	201.4	260.1
115°	67.8	69.3	71.2	75.0	81.3	89.8	103.3	122.5	153.1	195.4	245.1
117.5°	76.7	77.9	79.8	83.2	89.3	98.1	110.6	128.6	155.4	192.3	235.7
120°	82.2	83.5	85.4	88.2	94.5	103.3	115.7	132.7	156.9	190.6	230.6
122.5°	87.6	88.5	90.4	93.5	99.8	108.9	120.4	136.2	158.6	189.6	226.3
125°	94.5	95.5	97.4	101.1	107.5	116.3	127.6	141.8	161.3	187.8	220.3
127.5°	100.0	101.3	104.0	108.2	114.1	123.2	134.3	147.0	164.0	186.7	214.5
130°	103.3	104.6	107.7	112.2	118.5	127.2	138.3	150.3	166.0	186.2	210.8
132.5°	106.4	107.9	111.3	115.9	122.5	131.3	141.9	153.6	168.1	185.9	207.8
135°	110.9	112.2	115.9	120.6	128.0	136.7	146.9	157.8	170.5	185.6	203.5
137.5°	115.2	116.7	120.5	125.6	132.7	140.9	150.9	161.1	172.6	185.5	200.5
140°	118.5	119.8	123.5	128.6	135.5	143.7	153.1	162.9	173.6	185.3	198.8
142.5°	121.7	122.8	126.3	131.3	138.0	145.7	154.9	164.4	174.3	185.3	197.1
145°	126.6	128.0	131.1	135.8	142.1	149.0	157.6	166.4	175.1	184.6	194.7
147.5°	132.0	132.9	135.9	140.3	145.5	151.7	159.7	167.5	175.4	183.5	192.3
150°	135.5	136.4	138.9	143.0	147.8	153.5	160.7	167.9	175.1	182.7	190.3
152.5°	139.0	139.5	142.0	145.5	150.1	155.2	161.7	168.2	174.7	181.5	188.5
155°	144.0	144.3	146.2	149.6	153.1	157.8	163.2	168.5	173.9	179.2	185.3
157.5°	148.1	148.5	150.0	153.0	155.8	159.7	164.3	168.5	172.5	177.0	182.2
160°	150.9	151.2	152.5	155.0	157.6	161.0	164.8	168.5	171.7	175.5	179.9
162.5°	153.7	153.5	154.8	156.8	159.1	161.8	165.1	168.3	170.9	174.2	177.9
165°	156.9	156.6	157.2	159.1	160.7	162.6	165.4	167.6	169.5	171.7	174.5
167.5°	159.5	159.2	159.7	161.0	162.1	163.3	165.3	167.2	168.1	169.5	171.3
170°	161.3	160.7	161.0	161.9	162.6	163.5	165.1	166.7	167.3	168.3	169.5
172.5°	162.3	161.9	161.8	162.7	163.1	163.8	164.9	165.9	166.3	166.7	167.7
175°	163.5	163.2	162.9	163.5	163.5	163.8	164.4	165.1	164.8	165.1	165.4
177.5°	164.1	163.5	163.4	163.8	163.8	163.8	164.1	164.6	164.1	163.8	164.1
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8



TEST NUMBER: P331383-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1225.3	1227.4	1229.5	1230.4	1229.9	1229.5	1229.1	1228.7
5°	1217.0	1219.1	1221.3	1222.0	1221.6	1221.0	1220.5	1219.9
7.5°	1203.3	1205.4	1207.6	1208.3	1207.7	1207.1	1206.6	1205.9
10°	1191.0	1193.1	1195.2	1195.9	1195.1	1194.3	1193.5	1192.8
12.5°	1176.5	1177.9	1179.5	1179.9	1179.3	1178.8	1178.1	1177.6
15°	1151.0	1152.1	1153.2	1153.0	1151.7	1150.4	1149.1	1147.7
17.5°	1120.8	1122.0	1123.3	1123.2	1122.0	1120.7	1119.5	1118.2
20°	1097.3	1098.1	1098.9	1098.7	1097.7	1096.6	1095.6	1094.5
22.5°	1072.4	1072.5	1072.6	1072.5	1071.7	1071.1	1070.5	1069.9
25°	1031.7	1032.2	1032.7	1032.7	1032.2	1031.7	1031.2	1030.6
27.5°	991.7	990.9	990.1	989.1	987.7	986.5	985.3	984.0
30°	960.4	959.7	958.9	957.9	956.9	955.8	954.8	953.7
32.5°	929.8	928.4	926.9	925.7	924.7	923.6	922.6	921.5
35°	880.7	879.1	877.6	876.1	874.9	873.5	872.2	870.8
37.5°	831.5	829.6	827.6	826.0	824.7	823.5	822.2	820.9
40°	797.5	795.1	792.8	791.0	790.1	789.0	787.9	786.8
42.5°	763.9	761.3	758.8	756.8	755.3	753.9	752.3	750.9
45°	712.5	709.5	706.7	704.7	703.6	702.6	701.5	700.5
47.5°	658.9	655.9	652.8	650.5	649.0	647.5	646.0	644.4
50°	624.5	620.8	617.2	614.7	613.3	612.0	610.7	609.4
52.5°	588.8	585.8	582.7	580.3	578.6	576.8	575.2	573.4
55°	535.7	532.4	529.3	527.1	525.8	524.4	523.2	521.8
57.5°	480.4	477.2	474.1	472.1	471.1	470.1	469.1	468.1
60°	443.9	441.0	438.1	436.2	435.4	434.6	433.8	433.1
62.5°	409.2	406.5	403.9	402.1	401.0	400.0	399.0	398.1
65°	356.1	353.8	351.4	349.6	348.3	347.0	345.6	344.3
67.5°	303.7	301.8	300.1	298.6	297.6	296.5	295.4	294.4
70°	269.7	267.8	266.0	264.5	263.5	262.4	261.4	260.3
72.5°	237.5	235.6	233.8	232.5	231.6	230.8	229.9	229.1
75°	187.3	185.7	184.2	183.7	184.2	184.8	185.2	185.7
77.5°	142.6	141.8	141.0	140.2	139.5	138.8	138.0	137.2
80°	113.2	112.4	111.6	110.9	110.4	109.9	109.4	108.9
82.5°	84.4	83.4	82.4	81.9	81.7	81.6	81.5	81.4
85°	44.6	43.8	43.0	42.4	42.2	41.9	41.6	41.4
87.5°	14.0	13.3	12.8	12.4	12.2	11.9	11.8	11.5
90°	10.1	9.5	10.1	10.4	10.4	10.4	10.4	10.4
92.5°	27.5	23.5	21.0	19.0	18.7	17.7	17.9	17.5
95°	82.6	63.3	50.1	43.2	39.1	36.6	35.6	35.9
97.5°	192.6	157.6	123.5	100.8	85.7	77.9	73.4	70.7
100°	287.7	248.6	205.5	167.3	141.2	127.6	118.5	112.8
102.5°	349.9	341.1	309.5	269.1	240.7	217.6	206.2	198.5
105°	382.8	418.4	422.5	412.1	392.5	373.0	359.4	355.1
107.5°	359.1	412.8	445.5	460.7	463.2	462.2	459.4	453.6
110°	338.7	395.1	435.4	461.3	474.8	480.8	483.7	483.3



TEST NUMBER: P331383-940

CATALOG NUMBER: SA2XXDIP-C865D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	320.0	374.2	417.2	446.9	465.7	475.7	481.1	482.8
115°	297.1	345.6	386.9	419.4	441.8	456.2	464.4	467.3
117.5°	279.8	322.4	359.9	390.3	413.1	428.5	437.0	439.4
120°	271.3	310.3	343.8	372.4	394.5	409.3	418.4	421.6
122.5°	264.5	300.2	331.9	357.8	377.6	392.2	400.3	402.9
125°	254.6	287.0	314.8	338.4	356.7	368.6	376.5	379.1
127.5°	244.8	274.2	300.3	322.1	338.0	349.3	356.1	358.1
130°	238.5	265.6	290.5	311.3	326.7	337.4	343.8	346.3
132.5°	232.5	257.5	280.4	300.0	315.1	325.8	331.6	333.9
135°	224.0	244.8	265.6	283.2	296.8	307.2	312.9	314.1
137.5°	217.3	234.7	251.2	266.5	278.9	287.8	292.8	294.7
140°	212.9	228.1	242.6	256.5	266.5	274.7	279.5	281.3
142.5°	209.5	222.3	234.8	246.4	255.9	263.4	267.6	268.0
145°	204.5	214.9	224.6	233.8	241.3	246.7	249.9	250.7
147.5°	200.6	208.8	216.4	223.1	229.3	233.6	235.8	236.4
150°	197.9	204.8	211.4	217.0	221.8	225.6	227.5	227.8
152.5°	195.1	201.5	207.1	212.0	215.8	219.0	220.4	220.5
155°	191.3	196.3	201.0	204.5	207.9	210.2	211.4	210.8
157.5°	186.8	191.0	194.9	197.7	200.1	202.0	202.5	202.5
160°	184.0	187.4	190.9	193.1	195.4	196.9	197.2	197.2
162.5°	181.2	184.2	187.2	188.9	191.1	192.2	192.4	192.2
165°	177.1	179.2	181.5	182.7	184.0	185.3	185.3	184.9
167.5°	173.1	174.8	176.3	177.5	178.0	178.7	178.6	178.3
170°	171.1	172.0	173.3	173.9	174.2	175.1	174.9	174.2
172.5°	168.8	169.5	170.5	170.9	171.2	171.7	171.3	170.9
175°	166.4	166.7	167.0	167.3	167.3	167.6	167.3	166.7
177.5°	164.6	164.6	164.9	164.9	164.9	164.9	164.6	164.1
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8

(END OF REPORT)