

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331386-940

Luminaire Tested: **SA2XXDIP-C865D530U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331386-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5239.1 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331386-940
CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65				
1	102	98	94	90	96	92	89	86	81	79	77	72	70	68	63	61	60	56				
2	93	86	80	75	87	81	76	71	72	68	64	64	61	58	56	54	52	48				
3	85	76	69	63	80	72	66	60	64	59	55	57	53	50	50	47	45	41				
4	79	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39	36				
5	72	61	53	47	68	58	51	45	52	46	41	46	42	38	41	37	34	32				
6	67	55	47	41	63	52	45	40	47	41	37	42	37	34	38	34	31	28				
7	62	50	42	36	58	48	40	35	43	37	33	39	34	30	34	31	28	25				
8	58	46	38	33	54	43	36	31	39	33	29	35	31	27	32	28	25	23				
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	29	26	23	21				
10	51	39	31	27	48	37	30	26	34	28	24	30	26	22	27	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	24857	24857	24857	24857
5°	27869	25020	22172	25020
10°	31936	24815	19189	24815
15°	35328	24359	16951	24359
20°	34790	23871	15454	23871
25°	31370	23222	14503	23222
30°	25922	22184	13811	22184
35°	18892	21098	13318	21098
40°	15091	19816	13044	19816
45°	13186	18333	12673	18333
50°	12396	16900	12424	16900
55°	11426	15440	12090	15440
60°	10469	13892	11580	13892
65°	9540	12500	11075	12500
70°	8658	11146	10334	11146
75°	7679	9632	9158	9632
80°	6602	7978	7373	7978
85°	5910	5910	4372	5910



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.6	2.8
10°-20°	426.3	8.1
20°-30°	618.6	11.8
30°-40°	652.8	12.5
40°-50°	578.0	11.0
50°-60°	461.3	8.8
60°-70°	313.5	6.0
70°-80°	160.7	3.1
80°-90°	41.1	0.8
90°-100°	105.7	2.0
100°-110°	358.8	6.8
110°-120°	381.2	7.3
120°-130°	313.8	6.0
130°-140°	252.0	4.8
140°-150°	190.4	3.6
150°-160°	133.8	2.6
160°-170°	78.8	1.5
170°-180°	25.6	0.5
0°-30°	1191.5	22.7
0°-40°	1844.3	35.2
0°-60°	2883.6	55.0
0°-90°	3399.0	64.9
90°-120°	845.7	16.1
90°-150°	1601.9	30.6
90°-180°	1840.0	35.1
0°-180°	5239.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1540	1540	1540	1540	1540	
5°	1720	1544	1368	1544	1720	172
15°	2114	1457	1014	1457	2114	583
25°	1761	1304	814	1304	1761	796
35°	958	1070	676	1070	958	623
45°	578	803	555	803	578	454
55°	406	548	430	548	406	364
65°	250	327	290	327	250	248
75°	123	154	147	154	123	132
85°	32	32	24	32	32	35
90°	17	0	17	0	17	11
95°	58	18	58	18	58	75
105°	573	62	573	62	573	555
115°	754	109	754	109	754	738
125°	612	153	612	153	612	553
135°	507	179	507	179	507	394
145°	405	204	405	204	405	257
155°	340	232	340	232	340	159
165°	298	253	298	253	298	85
175°	269	264	269	264	269	26
180°	264	264	264	264	264	



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1610.6	1611.1	1612.0	1604.5	1603.5	1603.5	1596.9	1591.2	1584.6	1575.6	1576.5
5°	1719.5	1726.0	1728.3	1721.3	1710.6	1709.4	1699.3	1682.7	1667.4	1654.9	1646.1
7.5°	1849.4	1852.0	1846.2	1836.8	1828.9	1814.7	1796.0	1777.7	1752.0	1728.5	1710.9
10°	1947.9	1951.4	1941.3	1927.7	1916.5	1899.9	1872.7	1844.9	1811.2	1778.6	1752.6
12.5°	2022.7	2031.4	2018.5	2016.7	1997.4	1974.7	1942.3	1928.2	1880.8	1835.4	1807.5
15°	2113.5	2112.9	2114.2	2102.8	2088.7	2085.1	2050.8	2013.6	1946.7	1920.0	1873.9
17.5°	2087.2	2096.2	2100.4	2100.2	2099.9	2097.7	2086.7	2063.2	2029.6	1986.5	1933.1
20°	2024.8	2036.6	2038.4	2052.0	2059.7	2069.7	2073.9	2067.3	2046.7	2010.5	1964.4
22.5°	1928.2	1931.5	1937.1	1958.3	1975.0	2000.2	2013.3	2035.2	2027.2	2009.6	1971.0
25°	1760.9	1755.0	1775.7	1786.3	1824.8	1865.0	1894.0	1925.9	1954.4	1971.5	1960.2
27.5°	1560.0	1551.0	1582.1	1610.3	1641.6	1685.2	1730.4	1783.7	1828.1	1883.6	1902.6
30°	1390.4	1395.8	1425.4	1455.5	1502.9	1564.4	1615.3	1673.9	1737.2	1799.3	1842.5
32.5°	1207.7	1228.2	1247.0	1293.2	1334.9	1403.5	1478.0	1551.3	1630.2	1700.8	1767.7
35°	958.5	982.2	1008.3	1042.0	1100.5	1168.6	1241.4	1340.2	1447.9	1544.4	1623.6
37.5°	806.8	803.1	818.0	842.3	889.7	944.7	1028.5	1126.1	1252.9	1366.2	1478.0
40°	716.0	713.5	724.2	746.7	782.8	823.0	896.4	982.2	1099.9	1238.4	1371.5
42.5°	653.4	654.9	660.8	676.6	701.4	734.5	789.4	862.5	970.3	1100.6	1243.8
45°	577.5	581.7	588.2	595.8	610.0	637.2	668.0	720.1	805.3	914.2	1055.0
47.5°	522.8	522.9	529.6	536.3	544.7	560.1	585.1	617.9	678.0	766.6	887.7
50°	493.5	489.4	494.1	499.4	508.3	518.9	535.5	566.2	606.5	678.1	779.3
52.5°	457.5	457.6	461.9	463.9	471.8	482.5	497.6	518.9	555.4	611.4	694.6
55°	405.9	408.8	411.3	414.7	421.9	429.5	441.4	455.6	484.0	526.0	587.5
57.5°	357.4	358.3	360.7	367.5	371.9	379.1	390.3	403.1	421.6	452.7	499.0
60°	324.2	324.2	329.0	331.9	337.9	344.9	353.8	366.2	382.8	408.2	445.6
62.5°	294.0	293.5	295.3	300.2	304.7	311.4	320.2	330.7	346.3	369.0	399.7
65°	249.7	248.5	252.1	253.2	258.0	264.5	271.6	282.9	295.2	311.8	339.0
67.5°	207.1	208.5	210.4	212.7	215.3	222.1	226.9	234.8	245.3	259.0	277.5
70°	183.4	183.4	183.4	185.2	188.8	192.3	197.1	203.6	213.6	225.4	242.0
72.5°	156.9	158.8	160.7	159.6	164.2	166.3	171.9	175.6	185.2	192.8	207.4
75°	123.1	123.1	123.1	126.0	127.8	129.6	133.1	136.7	141.4	150.9	158.5
77.5°	91.8	91.6	92.2	92.9	94.8	96.9	98.0	101.2	105.6	109.9	116.5
80°	71.0	72.2	72.8	73.9	73.9	75.2	75.7	79.9	82.8	85.8	90.0
82.5°	54.9	55.1	55.3	55.5	56.0	56.7	58.2	59.6	60.5	63.0	66.3
85°	31.9	31.4	31.4	32.5	31.9	31.9	33.2	34.3	34.3	34.9	36.6
87.5°	15.7	15.7	16.1	15.7	15.7	16.1	15.9	15.6	16.1	16.7	17.1
90°	16.8	16.8	16.8	16.8	16.8	16.2	15.2	16.2	16.8	17.3	16.8
92.5°	28.2	29.0	28.6	30.2	30.6	33.8	38.1	44.3	55.8	66.1	65.2
95°	58.0	57.4	59.0	63.0	69.6	80.9	102.2	133.2	174.4	199.4	176.5
97.5°	114.1	118.4	125.8	138.3	162.6	199.4	254.4	310.9	357.0	340.3	256.3
100°	182.1	191.2	206.0	227.8	270.0	331.5	401.3	464.3	474.9	401.7	276.6
102.5°	320.4	332.8	351.2	388.5	434.4	499.6	550.5	564.8	518.9	403.8	268.9
105°	573.1	580.2	602.1	633.6	665.1	682.0	675.3	617.9	512.1	376.8	253.8
107.5°	732.1	741.5	745.9	747.6	743.7	719.1	666.2	579.6	467.4	347.9	246.2
110°	780.1	780.6	776.1	766.3	744.5	702.8	637.7	546.7	439.3	334.1	244.6



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	779.3	776.5	767.9	751.7	721.3	673.5	604.0	516.6	419.8	325.1	245.0
115°	754.1	749.6	736.4	712.9	676.9	624.5	557.9	479.6	395.7	315.3	247.2
117.5°	709.3	705.4	691.5	666.8	630.0	580.9	520.4	451.7	380.4	310.5	250.8
120°	680.4	675.3	660.6	636.7	601.1	554.8	500.9	437.8	372.3	307.6	253.2
122.5°	650.3	646.0	632.9	609.4	577.5	535.7	484.6	426.9	365.3	306.0	256.1
125°	611.8	607.7	594.9	575.7	546.2	508.0	463.2	410.9	355.4	303.1	260.4
127.5°	578.0	574.7	563.7	545.6	520.0	484.7	442.6	395.1	346.3	301.4	264.7
130°	558.8	554.8	544.7	527.4	502.4	468.9	428.7	385.0	340.2	300.5	268.0
132.5°	539.0	535.3	525.9	508.6	484.1	452.6	415.7	375.2	335.3	300.1	271.3
135°	507.0	505.0	495.8	479.0	457.2	428.7	395.1	361.6	328.5	299.5	275.1
137.5°	475.6	472.6	464.6	450.1	430.3	405.4	378.8	350.7	323.7	299.4	278.6
140°	454.1	451.0	443.4	430.3	413.9	391.6	368.2	343.8	320.9	299.0	280.2
142.5°	432.6	431.9	425.2	413.1	397.7	379.0	358.8	338.0	318.1	299.0	281.4
145°	404.7	403.2	398.1	389.5	377.4	362.6	346.8	330.0	314.2	298.0	282.8
147.5°	381.5	380.6	377.1	370.2	360.2	349.4	337.1	323.9	310.4	296.1	283.1
150°	367.7	367.1	364.1	358.0	350.4	341.3	330.6	319.3	307.2	295.0	282.8
152.5°	355.9	355.8	353.6	348.2	342.2	334.3	325.3	314.9	304.3	292.9	282.0
155°	340.2	341.3	339.2	335.6	330.0	324.4	316.8	308.7	299.0	289.4	280.7
157.5°	326.9	326.9	326.0	323.0	319.1	314.7	308.3	301.5	294.0	285.7	278.4
160°	318.3	318.3	317.8	315.3	311.7	308.2	302.6	296.9	290.3	283.3	277.1
162.5°	310.2	310.6	310.1	308.4	304.8	302.1	297.3	292.5	287.1	281.2	275.9
165°	298.5	299.0	299.0	296.9	295.0	292.9	289.4	285.8	281.7	277.1	273.6
167.5°	287.8	288.4	288.5	287.3	286.4	284.5	282.1	279.4	276.4	273.6	271.3
170°	281.2	282.2	282.8	281.2	280.7	279.7	277.7	276.2	273.6	271.5	270.0
172.5°	275.9	276.5	277.1	276.3	275.8	275.2	273.6	272.5	270.7	269.1	268.4
175°	269.0	270.0	270.5	270.0	270.0	269.6	269.0	268.5	267.0	266.4	266.0
177.5°	264.8	265.6	266.1	266.1	266.1	266.1	265.6	265.6	264.8	264.4	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1579.8	1576.0	1573.7	1565.1	1557.6	1550.0	1547.7	1548.5	1538.2	1528.2	1523.9
5°	1641.4	1629.5	1618.3	1602.3	1583.4	1562.6	1552.0	1543.7	1523.0	1500.6	1487.6
7.5°	1696.5	1679.5	1658.0	1627.9	1600.3	1567.7	1547.0	1528.7	1498.4	1466.7	1447.2
10°	1730.1	1707.0	1679.2	1642.5	1608.8	1569.1	1541.3	1513.6	1478.0	1440.2	1416.5
12.5°	1759.0	1727.9	1700.5	1653.4	1613.6	1564.0	1531.0	1491.7	1454.4	1409.4	1386.3
15°	1827.7	1770.3	1718.2	1665.0	1615.9	1546.7	1510.0	1457.3	1408.2	1352.6	1326.0
17.5°	1880.9	1816.4	1734.4	1666.7	1609.4	1532.8	1478.9	1415.8	1357.7	1294.1	1257.9
20°	1911.2	1837.2	1749.0	1668.6	1599.9	1512.3	1453.8	1389.3	1321.2	1249.6	1210.6
22.5°	1929.1	1851.4	1764.2	1661.4	1581.0	1495.8	1422.1	1351.4	1282.5	1205.1	1164.2
25°	1934.8	1863.9	1771.6	1655.6	1557.4	1460.9	1372.2	1303.5	1220.0	1147.9	1088.2
27.5°	1906.7	1855.7	1767.0	1644.4	1530.0	1417.2	1318.3	1240.5	1152.5	1074.2	1014.1
30°	1872.1	1842.5	1756.1	1633.1	1508.2	1387.0	1278.1	1189.9	1102.3	1023.1	961.5
32.5°	1818.6	1812.2	1736.3	1616.9	1485.1	1348.6	1235.9	1146.8	1049.8	971.9	913.2
35°	1713.5	1742.0	1694.0	1581.0	1441.4	1294.1	1172.2	1070.4	969.8	895.2	840.2
37.5°	1572.7	1643.2	1630.7	1528.3	1382.4	1234.7	1100.1	993.7	897.9	822.6	768.6
40°	1475.7	1565.6	1578.6	1488.1	1340.8	1188.7	1046.2	940.2	846.7	778.1	723.6
42.5°	1371.5	1476.6	1512.3	1439.8	1295.3	1140.4	997.8	888.1	795.6	728.9	680.6
45°	1197.0	1336.1	1400.5	1359.1	1219.5	1060.9	914.2	802.9	718.9	656.2	618.9
47.5°	1033.8	1185.7	1272.5	1257.8	1135.1	978.0	832.9	726.2	644.4	594.4	561.1
50°	918.3	1074.5	1179.2	1184.0	1074.5	918.9	773.4	672.8	597.6	550.9	523.6
52.5°	818.0	967.1	1081.3	1106.3	1006.8	857.4	719.9	619.7	553.6	510.6	486.2
55°	687.0	813.0	939.6	985.8	905.9	763.8	636.7	548.5	486.3	456.8	435.5
57.5°	571.1	676.2	793.1	844.1	794.9	673.3	554.0	477.5	427.0	401.2	384.9
60°	510.1	592.9	697.1	758.0	715.3	607.1	502.9	430.2	388.8	365.7	350.3
62.5°	453.3	526.6	614.7	670.4	647.2	545.1	451.8	387.5	351.8	330.2	319.1
65°	374.0	431.9	500.0	551.4	536.1	458.5	382.3	327.2	298.8	281.6	272.8
67.5°	307.9	349.8	397.0	442.1	429.7	374.8	313.4	270.6	249.5	234.7	229.3
70°	266.3	298.2	340.2	376.3	366.2	321.3	272.8	236.1	217.8	205.4	200.0
72.5°	226.5	252.8	284.8	314.3	307.6	270.2	229.7	202.0	187.9	176.5	172.1
75°	171.0	191.1	210.6	230.2	228.4	199.4	175.8	154.4	143.2	134.3	132.5
77.5°	126.3	137.5	150.8	162.4	159.2	142.6	124.0	111.8	103.5	97.6	96.7
80°	96.5	103.0	112.4	120.7	116.5	109.5	94.7	85.8	79.9	73.9	71.6
82.5°	69.9	76.4	82.1	86.6	83.5	76.8	67.7	61.6	58.1	54.0	53.1
85°	36.6	40.2	42.6	43.8	42.6	38.4	34.3	31.9	29.0	27.2	26.7
87.5°	16.9	16.2	15.7	16.4	14.7	14.5	12.2	10.5	10.3	10.3	9.5
90°	13.7	10.2	7.7	6.1	5.1	4.1	2.1	0.5	2.1	4.1	5.1
92.5°	50.7	34.6	23.1	18.3	14.9	12.6	8.9	6.2	8.9	12.6	14.9
95°	117.4	73.2	49.8	37.6	29.5	24.9	19.8	17.8	19.8	24.9	29.5
97.5°	158.3	96.7	67.2	53.4	44.1	37.1	31.7	29.0	31.7	37.1	44.1
100°	166.8	104.8	77.8	63.6	53.4	45.3	40.7	39.1	40.7	45.3	53.4
102.5°	167.2	112.1	87.1	72.9	62.3	54.2	49.7	48.5	49.7	54.2	62.3
105°	169.9	124.6	100.7	86.4	75.3	67.6	64.1	62.1	64.1	67.6	75.3
107.5°	176.8	137.4	114.2	99.9	88.8	81.8	78.3	76.7	78.3	81.8	88.8
110°	182.5	146.0	123.6	108.8	98.2	91.6	88.5	86.4	88.5	91.6	98.2



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	188.7	154.1	132.5	117.3	107.1	100.9	97.5	95.4	97.5	100.9	107.1
115°	197.8	166.8	144.9	131.2	121.0	114.9	111.9	109.3	111.9	114.9	121.0
117.5°	207.6	178.5	158.3	144.0	134.3	128.9	125.8	123.8	125.8	128.9	134.3
120°	214.1	186.6	166.8	152.6	142.4	137.8	134.7	132.7	134.7	137.8	142.4
122.5°	219.8	194.4	175.8	161.1	151.0	146.0	142.9	141.2	142.9	146.0	151.0
125°	228.8	206.0	187.6	173.4	163.3	157.1	154.1	152.6	154.1	157.1	163.3
127.5°	237.3	216.8	198.9	184.3	174.5	167.8	163.5	161.5	163.5	167.8	174.5
130°	242.5	223.3	205.5	191.2	181.0	173.9	168.8	166.8	168.8	173.9	181.0
132.5°	247.9	228.9	212.0	197.7	187.2	179.6	174.2	171.7	174.2	179.6	187.2
135°	254.8	237.0	220.7	206.4	194.7	187.2	181.0	179.0	181.0	187.2	194.7
137.5°	260.0	243.5	227.4	214.2	202.6	194.5	188.3	185.9	188.3	194.5	202.6
140°	262.9	247.2	231.9	218.6	207.5	199.4	193.2	191.2	193.2	199.4	207.5
142.5°	265.4	250.0	235.1	222.7	212.0	203.8	198.1	196.5	198.1	203.8	212.0
145°	268.5	254.2	240.5	229.3	219.2	211.5	206.4	204.5	206.4	211.5	219.2
147.5°	270.3	257.7	244.8	234.9	226.4	219.4	214.5	212.9	214.5	219.4	226.4
150°	271.1	259.3	247.6	238.5	230.9	224.3	220.2	218.6	220.2	224.3	230.9
152.5°	271.4	261.0	250.5	242.2	235.0	229.2	225.1	224.4	225.1	229.2	235.0
155°	272.1	263.4	254.8	247.2	241.6	235.9	232.9	232.4	232.9	235.9	241.6
157.5°	272.1	265.1	257.8	251.5	246.9	242.1	239.6	239.1	239.6	242.1	246.9
160°	272.1	266.0	259.8	254.2	250.2	246.1	244.1	243.6	244.1	246.1	250.2
162.5°	271.6	266.4	261.1	256.7	253.1	249.8	247.7	248.1	247.7	249.8	253.1
165°	270.5	267.0	262.4	259.3	256.8	253.8	252.7	253.2	252.7	253.8	256.8
167.5°	269.8	266.9	263.5	261.6	259.8	257.8	256.9	257.5	256.9	257.8	259.8
170°	269.0	266.4	263.9	262.4	261.4	259.8	259.3	260.4	259.3	259.8	261.4
172.5°	267.8	266.1	264.3	263.2	262.6	261.1	261.4	262.0	261.4	261.1	262.6
175°	266.4	265.5	264.4	263.9	263.9	262.9	263.4	263.9	263.4	262.9	263.9
177.5°	265.6	264.8	264.4	264.4	264.4	263.6	264.0	264.8	264.0	263.6	264.4
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1519.2	1516.4	1506.5	1501.3	1492.7	1484.7	1479.4	1481.8	1483.7	1482.7	1481.4
5°	1475.7	1464.5	1447.2	1432.4	1421.8	1402.3	1394.0	1389.9	1386.3	1382.2	1378.0
7.5°	1423.9	1406.1	1381.4	1360.4	1340.5	1316.3	1302.4	1294.1	1285.7	1276.3	1268.0
10°	1387.0	1362.1	1336.1	1306.4	1282.8	1260.9	1241.4	1228.3	1216.6	1205.2	1197.0
12.5°	1348.1	1319.5	1287.3	1246.8	1220.8	1189.5	1186.4	1163.5	1145.0	1138.1	1128.4
15°	1286.4	1246.1	1205.2	1157.4	1136.7	1108.2	1090.5	1072.7	1056.8	1045.5	1042.6
17.5°	1216.2	1164.1	1123.5	1089.0	1055.1	1026.0	1009.7	995.5	982.3	967.3	965.3
20°	1162.7	1117.7	1073.4	1043.1	1008.3	978.7	958.5	944.3	933.1	924.3	916.5
22.5°	1112.1	1062.8	1022.2	989.2	954.8	930.9	915.0	901.3	891.9	882.1	874.9
25°	1030.7	992.3	947.9	910.6	882.2	866.8	853.8	842.0	836.1	829.6	821.3
27.5°	959.6	916.9	875.4	846.5	821.5	807.9	798.7	790.6	785.1	781.2	776.5
30°	909.5	866.2	833.7	805.3	784.6	771.0	765.1	760.4	753.9	751.4	749.1
32.5°	861.1	822.2	794.4	769.8	750.0	741.2	735.8	731.5	726.4	724.0	719.3
35°	792.9	760.4	733.1	719.5	703.6	695.8	691.7	685.8	681.0	678.7	678.1
37.5°	728.6	700.3	682.4	664.9	658.2	653.4	647.8	643.7	642.3	641.9	641.4
40°	687.0	663.9	647.9	633.7	630.7	623.7	618.9	615.4	615.4	616.0	615.4
42.5°	649.1	628.4	614.3	602.0	598.5	594.3	589.6	589.3	590.3	592.3	590.3
45°	591.7	576.9	566.9	560.9	554.4	550.3	549.7	551.4	552.1	552.7	554.4
47.5°	539.0	529.1	520.0	513.4	510.6	509.9	509.2	512.3	515.1	516.2	518.9
50°	507.7	496.4	488.7	484.6	482.2	481.1	482.2	485.8	488.1	491.1	492.8
52.5°	472.6	464.7	459.4	456.2	455.2	455.9	456.2	460.2	464.0	465.0	465.9
55°	424.3	418.3	417.1	411.8	414.2	413.6	416.5	418.9	422.5	426.1	426.6
57.5°	375.9	371.2	368.0	368.5	369.3	371.8	374.3	378.4	382.3	386.0	386.4
60°	343.8	341.4	339.7	339.7	340.8	344.4	347.3	351.4	353.8	356.2	357.9
62.5°	314.4	312.1	310.3	311.2	314.3	316.5	319.9	322.1	324.5	326.8	327.7
65°	268.0	266.9	268.7	269.8	270.4	273.4	277.5	279.3	281.6	282.9	287.0
67.5°	225.3	225.5	225.3	226.9	230.4	231.1	235.1	239.2	239.6	241.9	244.6
70°	196.4	197.6	198.9	200.0	203.0	204.1	207.1	208.8	211.2	213.0	214.8
72.5°	170.0	170.1	171.4	171.1	173.6	176.2	178.7	180.5	182.8	185.1	186.8
75°	130.7	130.7	132.0	132.5	135.5	138.5	137.9	139.0	141.4	143.7	145.0
77.5°	95.5	94.2	95.5	96.1	97.0	99.5	100.0	101.7	104.3	103.5	104.9
80°	72.8	71.0	72.8	73.4	73.4	76.3	76.3	77.5	79.3	77.5	79.3
82.5°	52.0	51.1	52.4	52.5	53.5	53.6	54.6	54.8	56.5	55.7	56.5
85°	26.0	25.4	26.0	25.4	26.0	26.7	26.7	26.0	26.0	27.2	25.4
87.5°	9.3	9.1	9.1	9.8	10.0	9.6	9.0	8.9	8.7	8.0	8.1
90°	6.1	7.7	10.2	13.7	16.8	17.3	16.8	16.2	15.2	16.2	16.8
92.5°	18.3	23.1	34.6	50.7	65.2	66.1	55.8	44.3	38.1	33.8	30.6
95°	37.6	49.8	73.2	117.4	176.5	199.4	174.4	133.2	102.2	80.9	69.6
97.5°	53.4	67.2	96.7	158.3	256.3	340.3	357.0	310.9	254.4	199.4	162.6
100°	63.6	77.8	104.8	166.8	276.6	401.7	474.9	464.3	401.3	331.5	270.0
102.5°	72.9	87.1	112.1	167.2	268.9	403.8	518.9	564.8	550.5	499.6	434.4
105°	86.4	100.7	124.6	169.9	253.8	376.8	512.1	617.9	675.3	682.0	665.1
107.5°	99.9	114.2	137.4	176.8	246.2	347.9	467.4	579.6	666.2	719.1	743.7
110°	108.8	123.6	146.0	182.5	244.6	334.1	439.3	546.7	637.7	702.8	744.5



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	117.3	132.5	154.1	188.7	245.0	325.1	419.8	516.6	604.0	673.5	721.3
115°	131.2	144.9	166.8	197.8	247.2	315.3	395.7	479.6	557.9	624.5	676.9
117.5°	144.0	158.3	178.5	207.6	250.8	310.5	380.4	451.7	520.4	580.9	630.0
120°	152.6	166.8	186.6	214.1	253.2	307.6	372.3	437.8	500.9	554.8	601.1
122.5°	161.1	175.8	194.4	219.8	256.1	306.0	365.3	426.9	484.6	535.7	577.5
125°	173.4	187.6	206.0	228.8	260.4	303.1	355.4	410.9	463.2	508.0	546.2
127.5°	184.3	198.9	216.8	237.3	264.7	301.4	346.3	395.1	442.6	484.7	520.0
130°	191.2	205.5	223.3	242.5	268.0	300.5	340.2	385.0	428.7	468.9	502.4
132.5°	197.7	212.0	228.9	247.9	271.3	300.1	335.3	375.2	415.7	452.6	484.1
135°	206.4	220.7	237.0	254.8	275.1	299.5	328.5	361.6	395.1	428.7	457.2
137.5°	214.2	227.4	243.5	260.0	278.6	299.4	323.7	350.7	378.8	405.4	430.3
140°	218.6	231.9	247.2	262.9	280.2	299.0	320.9	343.8	368.2	391.6	413.9
142.5°	222.7	235.1	250.0	265.4	281.4	299.0	318.1	338.0	358.8	379.0	397.7
145°	229.3	240.5	254.2	268.5	282.8	298.0	314.2	330.0	346.8	362.6	377.4
147.5°	234.9	244.8	257.7	270.3	283.1	296.1	310.4	323.9	337.1	349.4	360.2
150°	238.5	247.6	259.3	271.1	282.8	295.0	307.2	319.3	330.6	341.3	350.4
152.5°	242.2	250.5	261.0	271.4	282.0	292.9	304.3	314.9	325.3	334.3	342.2
155°	247.2	254.8	263.4	272.1	280.7	289.4	299.0	308.7	316.8	324.4	330.0
157.5°	251.5	257.8	265.1	272.1	278.4	285.7	294.0	301.5	308.3	314.7	319.1
160°	254.2	259.8	266.0	272.1	277.1	283.3	290.3	296.9	302.6	308.2	311.7
162.5°	256.7	261.1	266.4	271.6	275.9	281.2	287.1	292.5	297.3	302.1	304.8
165°	259.3	262.4	267.0	270.5	273.6	277.1	281.7	285.8	289.4	292.9	295.0
167.5°	261.6	263.5	266.9	269.8	271.3	273.6	276.4	279.4	282.1	284.5	286.4
170°	262.4	263.9	266.4	269.0	270.0	271.5	273.6	276.2	277.7	279.7	280.7
172.5°	263.2	264.3	266.1	267.8	268.4	269.1	270.7	272.5	273.6	275.2	275.8
175°	263.9	264.4	265.5	266.4	266.0	266.4	267.0	268.5	269.0	269.6	270.0
177.5°	264.4	264.4	264.8	265.6	264.8	264.4	264.8	265.6	265.6	266.1	266.1
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331386-940
 CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1476.6	1475.7	1475.7	1471.4	1475.7	1475.7	1476.6	1481.4	1482.7	1483.7	1481.8
5°	1369.8	1368.0	1365.0	1368.0	1365.0	1368.0	1369.8	1378.0	1382.2	1386.3	1389.9
7.5°	1264.1	1257.0	1255.9	1248.9	1255.9	1257.0	1264.1	1268.0	1276.3	1285.7	1294.1
10°	1187.0	1182.2	1181.6	1170.4	1181.6	1182.2	1187.0	1197.0	1205.2	1216.6	1228.3
12.5°	1128.3	1116.9	1119.1	1112.6	1119.1	1116.9	1128.3	1128.4	1138.1	1145.0	1163.5
15°	1026.6	1026.6	1024.2	1014.1	1024.2	1026.6	1026.6	1042.6	1045.5	1056.8	1072.7
17.5°	953.6	952.3	946.7	949.6	946.7	952.3	953.6	965.3	967.3	982.3	995.5
20°	910.0	906.5	899.4	899.4	899.4	906.5	910.0	916.5	924.3	933.1	944.3
22.5°	868.9	868.6	861.0	863.4	861.0	868.6	868.9	874.9	882.1	891.9	901.3
25°	820.6	815.9	812.4	814.1	812.4	815.9	820.6	821.3	829.6	836.1	842.0
27.5°	775.0	772.4	772.1	767.3	772.1	772.4	775.0	776.5	781.2	785.1	790.6
30°	748.5	742.6	743.8	740.8	743.8	742.6	748.5	749.1	751.4	753.9	760.4
32.5°	718.2	716.0	714.9	712.4	714.9	716.0	718.2	719.3	724.0	726.4	731.5
35°	676.9	677.5	674.5	675.7	674.5	677.5	676.9	678.1	678.7	681.0	685.8
37.5°	640.8	642.7	641.3	641.7	641.3	642.7	640.8	641.4	641.9	642.3	643.7
40°	617.2	617.2	617.2	618.9	617.2	617.2	617.2	615.4	616.0	615.4	615.4
42.5°	594.4	593.4	592.5	592.4	592.5	593.4	594.4	590.3	592.3	590.3	589.3
45°	555.6	557.4	557.9	555.0	557.9	557.4	555.6	554.4	552.7	552.1	551.4
47.5°	520.5	520.7	520.5	523.1	520.5	520.7	520.5	518.9	516.2	515.1	512.3
50°	495.9	494.6	495.9	494.6	495.9	494.6	495.9	492.8	491.1	488.1	485.8
52.5°	469.8	470.0	469.3	469.1	469.3	470.0	469.8	465.9	465.0	464.0	460.2
55°	429.0	430.2	429.5	429.5	429.5	430.2	429.0	426.6	426.1	422.5	418.9
57.5°	386.7	387.8	388.6	386.0	388.6	387.8	386.7	386.4	386.0	382.3	378.4
60°	357.4	360.3	359.7	358.6	359.7	360.3	357.4	357.9	356.2	353.8	351.4
62.5°	330.4	331.4	331.4	331.1	331.4	331.4	330.4	327.7	326.8	324.5	322.1
65°	288.7	289.9	288.1	289.9	288.1	289.9	288.7	287.0	282.9	281.6	279.3
67.5°	243.9	244.2	245.6	246.4	245.6	244.2	243.9	244.6	241.9	239.6	239.2
70°	216.0	215.3	217.1	218.9	217.1	215.3	216.0	214.8	213.0	211.2	208.8
72.5°	186.6	187.9	187.3	188.6	187.3	187.9	186.6	186.8	185.1	182.8	180.5
75°	143.7	145.5	145.0	146.8	145.0	145.5	143.7	145.0	143.7	141.4	139.0
77.5°	103.9	104.2	103.9	104.9	103.9	104.2	103.9	104.9	103.5	104.3	101.7
80°	79.3	78.1	77.0	79.3	77.0	78.1	79.3	79.3	77.5	79.3	77.5
82.5°	55.1	55.8	54.7	54.7	54.7	55.8	55.1	56.5	55.7	56.5	54.8
85°	25.4	24.9	23.6	23.6	23.6	24.9	25.4	25.4	27.2	26.0	26.0
87.5°	8.1	7.6	7.6	7.1	7.6	7.6	8.1	8.1	8.0	8.7	8.9
90°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.2	15.2	16.2
92.5°	30.2	28.6	29.0	28.2	29.0	28.6	30.2	30.6	33.8	38.1	44.3
95°	63.0	59.0	57.4	58.0	57.4	59.0	63.0	69.6	80.9	102.2	133.2
97.5°	138.3	125.8	118.4	114.1	118.4	125.8	138.3	162.6	199.4	254.4	310.9
100°	227.8	206.0	191.2	182.1	191.2	206.0	227.8	270.0	331.5	401.3	464.3
102.5°	388.5	351.2	332.8	320.4	332.8	351.2	388.5	434.4	499.6	550.5	564.8
105°	633.6	602.1	580.2	573.1	580.2	602.1	633.6	665.1	682.0	675.3	617.9
107.5°	747.6	745.9	741.5	732.1	741.5	745.9	747.6	743.7	719.1	666.2	579.6
110°	766.3	776.1	780.6	780.1	780.6	776.1	766.3	744.5	702.8	637.7	546.7



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	751.7	767.9	776.5	779.3	776.5	767.9	751.7	721.3	673.5	604.0	516.6
115°	712.9	736.4	749.6	754.1	749.6	736.4	712.9	676.9	624.5	557.9	479.6
117.5°	666.8	691.5	705.4	709.3	705.4	691.5	666.8	630.0	580.9	520.4	451.7
120°	636.7	660.6	675.3	680.4	675.3	660.6	636.7	601.1	554.8	500.9	437.8
122.5°	609.4	632.9	646.0	650.3	646.0	632.9	609.4	577.5	535.7	484.6	426.9
125°	575.7	594.9	607.7	611.8	607.7	594.9	575.7	546.2	508.0	463.2	410.9
127.5°	545.6	563.7	574.7	578.0	574.7	563.7	545.6	520.0	484.7	442.6	395.1
130°	527.4	544.7	554.8	558.8	554.8	544.7	527.4	502.4	468.9	428.7	385.0
132.5°	508.6	525.9	535.3	539.0	535.3	525.9	508.6	484.1	452.6	415.7	375.2
135°	479.0	495.8	505.0	507.0	505.0	495.8	479.0	457.2	428.7	395.1	361.6
137.5°	450.1	464.6	472.6	475.6	472.6	464.6	450.1	430.3	405.4	378.8	350.7
140°	430.3	443.4	451.0	454.1	451.0	443.4	430.3	413.9	391.6	368.2	343.8
142.5°	413.1	425.2	431.9	432.6	431.9	425.2	413.1	397.7	379.0	358.8	338.0
145°	389.5	398.1	403.2	404.7	403.2	398.1	389.5	377.4	362.6	346.8	330.0
147.5°	370.2	377.1	380.6	381.5	380.6	377.1	370.2	360.2	349.4	337.1	323.9
150°	358.0	364.1	367.1	367.7	367.1	364.1	358.0	350.4	341.3	330.6	319.3
152.5°	348.2	353.6	355.8	355.9	355.8	353.6	348.2	342.2	334.3	325.3	314.9
155°	335.6	339.2	341.3	340.2	341.3	339.2	335.6	330.0	324.4	316.8	308.7
157.5°	323.0	326.0	326.9	326.9	326.9	326.0	323.0	319.1	314.7	308.3	301.5
160°	315.3	317.8	318.3	318.3	318.3	317.8	315.3	311.7	308.2	302.6	296.9
162.5°	308.4	310.1	310.6	310.2	310.6	310.1	308.4	304.8	302.1	297.3	292.5
165°	296.9	299.0	299.0	298.5	299.0	299.0	296.9	295.0	292.9	289.4	285.8
167.5°	287.3	288.5	288.4	287.8	288.4	288.5	287.3	286.4	284.5	282.1	279.4
170°	281.2	282.8	282.2	281.2	282.2	282.8	281.2	280.7	279.7	277.7	276.2
172.5°	276.3	277.1	276.5	275.9	276.5	277.1	276.3	275.8	275.2	273.6	272.5
175°	270.0	270.5	270.0	269.0	270.0	270.5	270.0	270.0	269.6	269.0	268.5
177.5°	266.1	266.1	265.6	264.8	265.6	266.1	266.1	266.1	266.1	265.6	265.6
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1479.4	1484.7	1492.7	1501.3	1506.5	1516.4	1519.2	1523.9	1528.2	1538.2	1548.5
5°	1394.0	1402.3	1421.8	1432.4	1447.2	1464.5	1475.7	1487.6	1500.6	1523.0	1543.7
7.5°	1302.4	1316.3	1340.5	1360.4	1381.4	1406.1	1423.9	1447.2	1466.7	1498.4	1528.7
10°	1241.4	1260.9	1282.8	1306.4	1336.1	1362.1	1387.0	1416.5	1440.2	1478.0	1513.6
12.5°	1186.4	1189.5	1220.8	1246.8	1287.3	1319.5	1348.1	1386.3	1409.4	1454.4	1491.7
15°	1090.5	1108.2	1136.7	1157.4	1205.2	1246.1	1286.4	1326.0	1352.6	1408.2	1457.3
17.5°	1009.7	1026.0	1055.1	1089.0	1123.5	1164.1	1216.2	1257.9	1294.1	1357.7	1415.8
20°	958.5	978.7	1008.3	1043.1	1073.4	1117.7	1162.7	1210.6	1249.6	1321.2	1389.3
22.5°	915.0	930.9	954.8	989.2	1022.2	1062.8	1112.1	1164.2	1205.1	1282.5	1351.4
25°	853.8	866.8	882.2	910.6	947.9	992.3	1030.7	1088.2	1147.9	1220.0	1303.5
27.5°	798.7	807.9	821.5	846.5	875.4	916.9	959.6	1014.1	1074.2	1152.5	1240.5
30°	765.1	771.0	784.6	805.3	833.7	866.2	909.5	961.5	1023.1	1102.3	1189.9
32.5°	735.8	741.2	750.0	769.8	794.4	822.2	861.1	913.2	971.9	1049.8	1146.8
35°	691.7	695.8	703.6	719.5	733.1	760.4	792.9	840.2	895.2	969.8	1070.4
37.5°	647.8	653.4	658.2	664.9	682.4	700.3	728.6	768.6	822.6	897.9	993.7
40°	618.9	623.7	630.7	633.7	647.9	663.9	687.0	723.6	778.1	846.7	940.2
42.5°	589.6	594.3	598.5	602.0	614.3	628.4	649.1	680.6	728.9	795.6	888.1
45°	549.7	550.3	554.4	560.9	566.9	576.9	591.7	618.9	656.2	718.9	802.9
47.5°	509.2	509.9	510.6	513.4	520.0	529.1	539.0	561.1	594.4	644.4	726.2
50°	482.2	481.1	482.2	484.6	488.7	496.4	507.7	523.6	550.9	597.6	672.8
52.5°	456.2	455.9	455.2	456.2	459.4	464.7	472.6	486.2	510.6	553.6	619.7
55°	416.5	413.6	414.2	411.8	417.1	418.3	424.3	435.5	456.8	486.3	548.5
57.5°	374.3	371.8	369.3	368.5	368.0	371.2	375.9	384.9	401.2	427.0	477.5
60°	347.3	344.4	340.8	339.7	339.7	341.4	343.8	350.3	365.7	388.8	430.2
62.5°	319.9	316.5	314.3	311.2	310.3	312.1	314.4	319.1	330.2	351.8	387.5
65°	277.5	273.4	270.4	269.8	268.7	266.9	268.0	272.8	281.6	298.8	327.2
67.5°	235.1	231.1	230.4	226.9	225.3	225.5	225.3	229.3	234.7	249.5	270.6
70°	207.1	204.1	203.0	200.0	198.9	197.6	196.4	200.0	205.4	217.8	236.1
72.5°	178.7	176.2	173.6	171.1	171.4	170.1	170.0	172.1	176.5	187.9	202.0
75°	137.9	138.5	135.5	132.5	132.0	130.7	130.7	132.5	134.3	143.2	154.4
77.5°	100.0	99.5	97.0	96.1	95.5	94.2	95.5	96.7	97.6	103.5	111.8
80°	76.3	76.3	73.4	73.4	72.8	71.0	72.8	71.6	73.9	79.9	85.8
82.5°	54.6	53.6	53.5	52.5	52.4	51.1	52.0	53.1	54.0	58.1	61.6
85°	26.7	26.7	26.0	25.4	26.0	25.4	26.0	26.7	27.2	29.0	31.9
87.5°	9.0	9.6	10.0	9.8	9.1	9.1	9.3	9.5	10.3	10.3	10.5
90°	16.8	17.3	16.8	13.7	10.2	7.7	6.1	5.1	4.1	2.1	0.5
92.5°	55.8	66.1	65.2	50.7	34.6	23.1	18.3	14.9	12.6	8.9	6.2
95°	174.4	199.4	176.5	117.4	73.2	49.8	37.6	29.5	24.9	19.8	17.8
97.5°	357.0	340.3	256.3	158.3	96.7	67.2	53.4	44.1	37.1	31.7	29.0
100°	474.9	401.7	276.6	166.8	104.8	77.8	63.6	53.4	45.3	40.7	39.1
102.5°	518.9	403.8	268.9	167.2	112.1	87.1	72.9	62.3	54.2	49.7	48.5
105°	512.1	376.8	253.8	169.9	124.6	100.7	86.4	75.3	67.6	64.1	62.1
107.5°	467.4	347.9	246.2	176.8	137.4	114.2	99.9	88.8	81.8	78.3	76.7
110°	439.3	334.1	244.6	182.5	146.0	123.6	108.8	98.2	91.6	88.5	86.4



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	419.8	325.1	245.0	188.7	154.1	132.5	117.3	107.1	100.9	97.5	95.4
115°	395.7	315.3	247.2	197.8	166.8	144.9	131.2	121.0	114.9	111.9	109.3
117.5°	380.4	310.5	250.8	207.6	178.5	158.3	144.0	134.3	128.9	125.8	123.8
120°	372.3	307.6	253.2	214.1	186.6	166.8	152.6	142.4	137.8	134.7	132.7
122.5°	365.3	306.0	256.1	219.8	194.4	175.8	161.1	151.0	146.0	142.9	141.2
125°	355.4	303.1	260.4	228.8	206.0	187.6	173.4	163.3	157.1	154.1	152.6
127.5°	346.3	301.4	264.7	237.3	216.8	198.9	184.3	174.5	167.8	163.5	161.5
130°	340.2	300.5	268.0	242.5	223.3	205.5	191.2	181.0	173.9	168.8	166.8
132.5°	335.3	300.1	271.3	247.9	228.9	212.0	197.7	187.2	179.6	174.2	171.7
135°	328.5	299.5	275.1	254.8	237.0	220.7	206.4	194.7	187.2	181.0	179.0
137.5°	323.7	299.4	278.6	260.0	243.5	227.4	214.2	202.6	194.5	188.3	185.9
140°	320.9	299.0	280.2	262.9	247.2	231.9	218.6	207.5	199.4	193.2	191.2
142.5°	318.1	299.0	281.4	265.4	250.0	235.1	222.7	212.0	203.8	198.1	196.5
145°	314.2	298.0	282.8	268.5	254.2	240.5	229.3	219.2	211.5	206.4	204.5
147.5°	310.4	296.1	283.1	270.3	257.7	244.8	234.9	226.4	219.4	214.5	212.9
150°	307.2	295.0	282.8	271.1	259.3	247.6	238.5	230.9	224.3	220.2	218.6
152.5°	304.3	292.9	282.0	271.4	261.0	250.5	242.2	235.0	229.2	225.1	224.4
155°	299.0	289.4	280.7	272.1	263.4	254.8	247.2	241.6	235.9	232.9	232.4
157.5°	294.0	285.7	278.4	272.1	265.1	257.8	251.5	246.9	242.1	239.6	239.1
160°	290.3	283.3	277.1	272.1	266.0	259.8	254.2	250.2	246.1	244.1	243.6
162.5°	287.1	281.2	275.9	271.6	266.4	261.1	256.7	253.1	249.8	247.7	248.1
165°	281.7	277.1	273.6	270.5	267.0	262.4	259.3	256.8	253.8	252.7	253.2
167.5°	276.4	273.6	271.3	269.8	266.9	263.5	261.6	259.8	257.8	256.9	257.5
170°	273.6	271.5	270.0	269.0	266.4	263.9	262.4	261.4	259.8	259.3	260.4
172.5°	270.7	269.1	268.4	267.8	266.1	264.3	263.2	262.6	261.1	261.4	262.0
175°	267.0	266.4	266.0	266.4	265.5	264.4	263.9	263.9	262.9	263.4	263.9
177.5°	264.8	264.4	264.8	265.6	264.8	264.4	264.4	264.4	263.6	264.0	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331386-940
 CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1547.7	1550.0	1557.6	1565.1	1573.7	1576.0	1579.8	1576.5	1575.6	1584.6	1591.2
5°	1552.0	1562.6	1583.4	1602.3	1618.3	1629.5	1641.4	1646.1	1654.9	1667.4	1682.7
7.5°	1547.0	1567.7	1600.3	1627.9	1658.0	1679.5	1696.5	1710.9	1728.5	1752.0	1777.7
10°	1541.3	1569.1	1608.8	1642.5	1679.2	1707.0	1730.1	1752.6	1778.6	1811.2	1844.9
12.5°	1531.0	1564.0	1613.6	1653.4	1700.5	1727.9	1759.0	1807.5	1835.4	1880.8	1928.2
15°	1510.0	1546.7	1615.9	1665.0	1718.2	1770.3	1827.7	1873.9	1920.0	1946.7	2013.6
17.5°	1478.9	1532.8	1609.4	1666.7	1734.4	1816.4	1880.9	1933.1	1986.5	2029.6	2063.2
20°	1453.8	1512.3	1599.9	1668.6	1749.0	1837.2	1911.2	1964.4	2010.5	2046.7	2067.3
22.5°	1422.1	1495.8	1581.0	1661.4	1764.2	1851.4	1929.1	1971.0	2009.6	2027.2	2035.2
25°	1372.2	1460.9	1557.4	1655.6	1771.6	1863.9	1934.8	1960.2	1971.5	1954.4	1925.9
27.5°	1318.3	1417.2	1530.0	1644.4	1767.0	1855.7	1906.7	1902.6	1883.6	1828.1	1783.7
30°	1278.1	1387.0	1508.2	1633.1	1756.1	1842.5	1872.1	1842.5	1799.3	1737.2	1673.9
32.5°	1235.9	1348.6	1485.1	1616.9	1736.3	1812.2	1818.6	1767.7	1700.8	1630.2	1551.3
35°	1172.2	1294.1	1441.4	1581.0	1694.0	1742.0	1713.5	1623.6	1544.4	1447.9	1340.2
37.5°	1100.1	1234.7	1382.4	1528.3	1630.7	1643.2	1572.7	1478.0	1366.2	1252.9	1126.1
40°	1046.2	1188.7	1340.8	1488.1	1578.6	1565.6	1475.7	1371.5	1238.4	1099.9	982.2
42.5°	997.8	1140.4	1295.3	1439.8	1512.3	1476.6	1371.5	1243.8	1100.6	970.3	862.5
45°	914.2	1060.9	1219.5	1359.1	1400.5	1336.1	1197.0	1055.0	914.2	805.3	720.1
47.5°	832.9	978.0	1135.1	1257.8	1272.5	1185.7	1033.8	887.7	766.6	678.0	617.9
50°	773.4	918.9	1074.5	1184.0	1179.2	1074.5	918.3	779.3	678.1	606.5	566.2
52.5°	719.9	857.4	1006.8	1106.3	1081.3	967.1	818.0	694.6	611.4	555.4	518.9
55°	636.7	763.8	905.9	985.8	939.6	813.0	687.0	587.5	526.0	484.0	455.6
57.5°	554.0	673.3	794.9	844.1	793.1	676.2	571.1	499.0	452.7	421.6	403.1
60°	502.9	607.1	715.3	758.0	697.1	592.9	510.1	445.6	408.2	382.8	366.2
62.5°	451.8	545.1	647.2	670.4	614.7	526.6	453.3	399.7	369.0	346.3	330.7
65°	382.3	458.5	536.1	551.4	500.0	431.9	374.0	339.0	311.8	295.2	282.9
67.5°	313.4	374.8	429.7	442.1	397.0	349.8	307.9	277.5	259.0	245.3	234.8
70°	272.8	321.3	366.2	376.3	340.2	298.2	266.3	242.0	225.4	213.6	203.6
72.5°	229.7	270.2	307.6	314.3	284.8	252.8	226.5	207.4	192.8	185.2	175.6
75°	175.8	199.4	228.4	230.2	210.6	191.1	171.0	158.5	150.9	141.4	136.7
77.5°	124.0	142.6	159.2	162.4	150.8	137.5	126.3	116.5	109.9	105.6	101.2
80°	94.7	109.5	116.5	120.7	112.4	103.0	96.5	90.0	85.8	82.8	79.9
82.5°	67.7	76.8	83.5	86.6	82.1	76.4	69.9	66.3	63.0	60.5	59.6
85°	34.3	38.4	42.6	43.8	42.6	40.2	36.6	36.6	34.9	34.3	34.3
87.5°	12.2	14.5	14.7	16.4	15.7	16.2	16.9	17.1	16.7	16.1	15.6
90°	2.1	4.1	5.1	6.1	7.7	10.2	13.7	16.8	17.3	16.8	16.2
92.5°	8.9	12.6	14.9	18.3	23.1	34.6	50.7	65.2	66.1	55.8	44.3
95°	19.8	24.9	29.5	37.6	49.8	73.2	117.4	176.5	199.4	174.4	133.2
97.5°	31.7	37.1	44.1	53.4	67.2	96.7	158.3	256.3	340.3	357.0	310.9
100°	40.7	45.3	53.4	63.6	77.8	104.8	166.8	276.6	401.7	474.9	464.3
102.5°	49.7	54.2	62.3	72.9	87.1	112.1	167.2	268.9	403.8	518.9	564.8
105°	64.1	67.6	75.3	86.4	100.7	124.6	169.9	253.8	376.8	512.1	617.9
107.5°	78.3	81.8	88.8	99.9	114.2	137.4	176.8	246.2	347.9	467.4	579.6
110°	88.5	91.6	98.2	108.8	123.6	146.0	182.5	244.6	334.1	439.3	546.7



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	97.5	100.9	107.1	117.3	132.5	154.1	188.7	245.0	325.1	419.8	516.6
115°	111.9	114.9	121.0	131.2	144.9	166.8	197.8	247.2	315.3	395.7	479.6
117.5°	125.8	128.9	134.3	144.0	158.3	178.5	207.6	250.8	310.5	380.4	451.7
120°	134.7	137.8	142.4	152.6	166.8	186.6	214.1	253.2	307.6	372.3	437.8
122.5°	142.9	146.0	151.0	161.1	175.8	194.4	219.8	256.1	306.0	365.3	426.9
125°	154.1	157.1	163.3	173.4	187.6	206.0	228.8	260.4	303.1	355.4	410.9
127.5°	163.5	167.8	174.5	184.3	198.9	216.8	237.3	264.7	301.4	346.3	395.1
130°	168.8	173.9	181.0	191.2	205.5	223.3	242.5	268.0	300.5	340.2	385.0
132.5°	174.2	179.6	187.2	197.7	212.0	228.9	247.9	271.3	300.1	335.3	375.2
135°	181.0	187.2	194.7	206.4	220.7	237.0	254.8	275.1	299.5	328.5	361.6
137.5°	188.3	194.5	202.6	214.2	227.4	243.5	260.0	278.6	299.4	323.7	350.7
140°	193.2	199.4	207.5	218.6	231.9	247.2	262.9	280.2	299.0	320.9	343.8
142.5°	198.1	203.8	212.0	222.7	235.1	250.0	265.4	281.4	299.0	318.1	338.0
145°	206.4	211.5	219.2	229.3	240.5	254.2	268.5	282.8	298.0	314.2	330.0
147.5°	214.5	219.4	226.4	234.9	244.8	257.7	270.3	283.1	296.1	310.4	323.9
150°	220.2	224.3	230.9	238.5	247.6	259.3	271.1	282.8	295.0	307.2	319.3
152.5°	225.1	229.2	235.0	242.2	250.5	261.0	271.4	282.0	292.9	304.3	314.9
155°	232.9	235.9	241.6	247.2	254.8	263.4	272.1	280.7	289.4	299.0	308.7
157.5°	239.6	242.1	246.9	251.5	257.8	265.1	272.1	278.4	285.7	294.0	301.5
160°	244.1	246.1	250.2	254.2	259.8	266.0	272.1	277.1	283.3	290.3	296.9
162.5°	247.7	249.8	253.1	256.7	261.1	266.4	271.6	275.9	281.2	287.1	292.5
165°	252.7	253.8	256.8	259.3	262.4	267.0	270.5	273.6	277.1	281.7	285.8
167.5°	256.9	257.8	259.8	261.6	263.5	266.9	269.8	271.3	273.6	276.4	279.4
170°	259.3	259.8	261.4	262.4	263.9	266.4	269.0	270.0	271.5	273.6	276.2
172.5°	261.4	261.1	262.6	263.2	264.3	266.1	267.8	268.4	269.1	270.7	272.5
175°	263.4	262.9	263.9	263.9	264.4	265.5	266.4	266.0	266.4	267.0	268.5
177.5°	264.0	263.6	264.4	264.4	264.4	264.8	265.6	264.8	264.4	264.8	265.6
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5	1539.5
2.5°	1596.9	1603.5	1603.5	1604.5	1612.0	1611.1	1610.6
5°	1699.3	1709.4	1710.6	1721.3	1728.3	1726.0	1719.5
7.5°	1796.0	1814.7	1828.9	1836.8	1846.2	1852.0	1849.4
10°	1872.7	1899.9	1916.5	1927.7	1941.3	1951.4	1947.9
12.5°	1942.3	1974.7	1997.4	2016.7	2018.5	2031.4	2022.7
15°	2050.8	2085.1	2088.7	2102.8	2114.2	2112.9	2113.5
17.5°	2086.7	2097.7	2099.9	2100.2	2100.4	2096.2	2087.2
20°	2073.9	2069.7	2059.7	2052.0	2038.4	2036.6	2024.8
22.5°	2013.3	2000.2	1975.0	1958.3	1937.1	1931.5	1928.2
25°	1894.0	1865.0	1824.8	1786.3	1775.7	1755.0	1760.9
27.5°	1730.4	1685.2	1641.6	1610.3	1582.1	1551.0	1560.0
30°	1615.3	1564.4	1502.9	1455.5	1425.4	1395.8	1390.4
32.5°	1478.0	1403.5	1334.9	1293.2	1247.0	1228.2	1207.7
35°	1241.4	1168.6	1100.5	1042.0	1008.3	982.2	958.5
37.5°	1028.5	944.7	889.7	842.3	818.0	803.1	806.8
40°	896.4	823.0	782.8	746.7	724.2	713.5	716.0
42.5°	789.4	734.5	701.4	676.6	660.8	654.9	653.4
45°	668.0	637.2	610.0	595.8	588.2	581.7	577.5
47.5°	585.1	560.1	544.7	536.3	529.6	522.9	522.8
50°	535.5	518.9	508.3	499.4	494.1	489.4	493.5
52.5°	497.6	482.5	471.8	463.9	461.9	457.6	457.5
55°	441.4	429.5	421.9	414.7	411.3	408.8	405.9
57.5°	390.3	379.1	371.9	367.5	360.7	358.3	357.4
60°	353.8	344.9	337.9	331.9	329.0	324.2	324.2
62.5°	320.2	311.4	304.7	300.2	295.3	293.5	294.0
65°	271.6	264.5	258.0	253.2	252.1	248.5	249.7
67.5°	226.9	222.1	215.3	212.7	210.4	208.5	207.1
70°	197.1	192.3	188.8	185.2	183.4	183.4	183.4
72.5°	171.9	166.3	164.2	159.6	160.7	158.8	156.9
75°	133.1	129.6	127.8	126.0	123.1	123.1	123.1
77.5°	98.0	96.9	94.8	92.9	92.2	91.6	91.8
80°	75.7	75.2	73.9	73.9	72.8	72.2	71.0
82.5°	58.2	56.7	56.0	55.5	55.3	55.1	54.9
85°	33.2	31.9	31.9	32.5	31.4	31.4	31.9
87.5°	15.9	16.1	15.7	15.7	16.1	15.7	15.7
90°	15.2	16.2	16.8	16.8	16.8	16.8	16.8
92.5°	38.1	33.8	30.6	30.2	28.6	29.0	28.2
95°	102.2	80.9	69.6	63.0	59.0	57.4	58.0
97.5°	254.4	199.4	162.6	138.3	125.8	118.4	114.1
100°	401.3	331.5	270.0	227.8	206.0	191.2	182.1
102.5°	550.5	499.6	434.4	388.5	351.2	332.8	320.4
105°	675.3	682.0	665.1	633.6	602.1	580.2	573.1
107.5°	666.2	719.1	743.7	747.6	745.9	741.5	732.1
110°	637.7	702.8	744.5	766.3	776.1	780.6	780.1



TEST NUMBER: P331386-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	604.0	673.5	721.3	751.7	767.9	776.5	779.3
115°	557.9	624.5	676.9	712.9	736.4	749.6	754.1
117.5°	520.4	580.9	630.0	666.8	691.5	705.4	709.3
120°	500.9	554.8	601.1	636.7	660.6	675.3	680.4
122.5°	484.6	535.7	577.5	609.4	632.9	646.0	650.3
125°	463.2	508.0	546.2	575.7	594.9	607.7	611.8
127.5°	442.6	484.7	520.0	545.6	563.7	574.7	578.0
130°	428.7	468.9	502.4	527.4	544.7	554.8	558.8
132.5°	415.7	452.6	484.1	508.6	525.9	535.3	539.0
135°	395.1	428.7	457.2	479.0	495.8	505.0	507.0
137.5°	378.8	405.4	430.3	450.1	464.6	472.6	475.6
140°	368.2	391.6	413.9	430.3	443.4	451.0	454.1
142.5°	358.8	379.0	397.7	413.1	425.2	431.9	432.6
145°	346.8	362.6	377.4	389.5	398.1	403.2	404.7
147.5°	337.1	349.4	360.2	370.2	377.1	380.6	381.5
150°	330.6	341.3	350.4	358.0	364.1	367.1	367.7
152.5°	325.3	334.3	342.2	348.2	353.6	355.8	355.9
155°	316.8	324.4	330.0	335.6	339.2	341.3	340.2
157.5°	308.3	314.7	319.1	323.0	326.0	326.9	326.9
160°	302.6	308.2	311.7	315.3	317.8	318.3	318.3
162.5°	297.3	302.1	304.8	308.4	310.1	310.6	310.2
165°	289.4	292.9	295.0	296.9	299.0	299.0	298.5
167.5°	282.1	284.5	286.4	287.3	288.5	288.4	287.8
170°	277.7	279.7	280.7	281.2	282.8	282.2	281.2
172.5°	273.6	275.2	275.8	276.3	277.1	276.5	275.9
175°	269.0	269.6	270.0	270.0	270.5	270.0	269.0
177.5°	265.6	266.1	266.1	266.1	266.1	265.6	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4

(END OF REPORT)