

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331392-940

Luminaire Tested: **SA2XXDIP-C865D530U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331392-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D530U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4973.3 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331392-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331392-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	68	66	60	59	57	53
2	92	84	78	73	86	79	74	69	70	65	62	61	58	55	53	51	48	44
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41	38
4	77	66	57	51	72	62	55	49	55	49	44	48	44	40	42	38	36	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	34	39	34	30	34	30	27	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19869	19869	19869
5°	19945	19656	19772
10°	19825	19457	19556
15°	19580	19206	19184
20°	19234	18826	18806
25°	18887	18360	18360
30°	18442	17935	17780
35°	18027	17422	17164
40°	17506	16910	16583
45°	16993	16401	15995
50°	16435	15872	15307
55°	15854	15254	14688
60°	15206	14518	13986
65°	14514	13788	13154
70°	13629	12902	12288
75°	12402	11884	11584
80°	11000	10674	10126
85°	8985	8559	7669



TEST NUMBER: P331392-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.7	2.3
10°-20°	325.6	6.5
20°-30°	478.6	9.6
30°-40°	555.9	11.2
40°-50°	555.3	11.2
50°-60°	484.3	9.7
60°-70°	358.1	7.2
70°-80°	202.8	4.1
80°-90°	56.9	1.1
90°-100°	105.7	2.1
100°-110°	358.8	7.2
110°-120°	381.2	7.7
120°-130°	313.8	6.3
130°-140°	252.0	5.1
140°-150°	190.4	3.8
150°-160°	133.8	2.7
160°-170°	78.8	1.6
170°-180°	25.6	0.5
0°-30°	919.9	18.5
0°-40°	1475.8	29.7
0°-60°	2515.4	50.6
0°-90°	3133.1	63.0
90°-120°	845.7	17.0
90°-150°	1601.9	32.2
90°-180°	1840.0	37.0
0°-180°	4973.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1231	1225	1213	1222	1220	117
15°	1171	1164	1149	1153	1148	330
25°	1060	1050	1031	1033	1031	488
35°	915	902	884	877	871	571
45°	744	735	718	706	700	574
55°	563	556	542	528	522	503
65°	380	372	361	350	344	376
75°	199	196	190	184	186	212
85°	48	47	46	43	41	56
90°	0	7	17	16	17	3
95°	18	44	199	75	58	19
105°	62	94	377	674	573	66
115°	109	138	315	651	754	108
125°	153	180	303	527	612	135
135°	179	214	300	443	507	138
145°	204	235	298	370	405	128
155°	232	251	289	327	340	107
165°	253	261	277	294	298	71
175°	264	264	266	270	269	25
180°	264	264	264	264	264	



TEST NUMBER: P331392-940
 CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1236.3	1235.2	1234.1	1233.1	1232.1	1230.4	1228.1	1225.7	1223.4	1221.1	1223.2
5°	1230.6	1229.5	1228.5	1227.4	1226.4	1224.4	1221.6	1218.6	1215.8	1212.8	1215.0
7.5°	1219.7	1218.1	1216.5	1214.8	1213.2	1210.9	1207.9	1205.0	1202.0	1199.1	1201.2
10°	1209.2	1207.5	1205.6	1203.7	1201.9	1199.4	1196.2	1193.1	1190.0	1186.8	1188.9
12.5°	1195.1	1193.5	1191.9	1190.2	1188.6	1186.2	1183.0	1179.8	1176.7	1173.6	1175.0
15°	1171.4	1169.8	1168.2	1166.7	1165.1	1162.6	1159.2	1155.7	1152.4	1149.0	1150.0
17.5°	1141.1	1139.5	1138.0	1136.4	1134.8	1132.3	1128.8	1125.3	1121.9	1118.4	1119.6
20°	1119.4	1117.8	1116.2	1114.6	1113.0	1110.4	1106.7	1103.0	1099.4	1095.7	1096.4
22.5°	1097.6	1095.4	1093.1	1090.9	1088.8	1085.9	1082.4	1079.0	1075.5	1072.0	1072.2
25°	1060.2	1058.1	1056.0	1053.9	1051.8	1048.5	1044.0	1039.6	1035.1	1030.6	1031.2
27.5°	1017.6	1015.7	1013.8	1011.9	1010.0	1007.3	1003.8	1000.2	996.8	993.2	992.5
30°	989.2	987.1	985.0	982.9	980.8	977.8	973.8	969.9	965.9	962.0	961.2
32.5°	958.9	957.3	955.6	953.9	952.2	949.2	945.1	940.9	936.8	932.6	931.2
35°	914.6	912.0	909.4	906.8	904.1	900.7	896.5	892.3	888.1	883.9	882.3
37.5°	864.7	862.4	860.1	857.7	855.5	852.2	848.0	843.8	839.5	835.4	833.4
40°	830.6	828.6	826.4	824.3	822.2	819.0	814.8	810.7	806.5	802.3	799.9
42.5°	797.5	795.4	793.3	791.2	789.1	786.0	781.8	777.6	773.3	769.1	766.5
45°	744.2	742.4	740.6	738.8	736.9	734.0	730.0	726.1	722.2	718.3	715.3
47.5°	691.3	689.6	687.8	686.1	684.3	681.4	677.3	673.2	669.1	664.9	661.9
50°	654.3	653.0	651.8	650.4	649.1	646.6	642.9	639.2	635.5	631.9	628.2
52.5°	618.4	616.6	614.9	613.1	611.4	608.9	605.4	601.9	598.4	594.9	591.9
55°	563.2	561.7	560.1	558.5	556.9	554.6	551.4	548.2	545.1	541.9	538.8
57.5°	507.8	506.6	505.3	504.1	502.8	500.4	497.0	493.5	490.0	486.5	483.5
60°	470.9	469.8	468.9	467.8	466.7	464.4	460.7	457.0	453.3	449.6	446.7
62.5°	435.0	433.3	431.6	429.9	428.2	426.0	423.1	420.3	417.4	414.6	412.0
65°	379.9	378.3	376.7	375.1	373.5	371.4	368.8	366.1	363.6	360.9	358.6
67.5°	323.8	322.4	321.2	319.9	318.7	316.9	314.5	312.1	309.8	307.4	305.6
70°	288.7	287.7	286.6	285.5	284.5	282.8	280.4	278.0	275.7	273.3	271.5
72.5°	252.7	251.7	250.7	249.6	248.5	247.3	245.8	244.2	242.6	241.1	239.3
75°	198.8	198.2	197.7	197.2	196.7	195.7	194.5	193.1	191.8	190.5	189.0
77.5°	150.5	149.6	148.7	147.8	147.0	146.2	145.7	145.2	144.6	144.1	143.3
80°	118.3	118.1	117.8	117.5	117.3	116.9	116.4	115.8	115.3	114.8	114.0
82.5°	88.0	88.0	87.9	87.8	87.8	87.7	87.3	87.0	86.7	86.4	85.3
85°	48.5	48.2	48.0	47.7	47.4	47.2	46.9	46.6	46.4	46.2	45.4
87.5°	17.1	17.0	17.0	16.8	16.6	16.5	16.6	16.9	17.0	16.7	16.0
90°	0.5	2.1	4.1	5.1	6.1	7.7	10.2	13.7	16.8	17.3	16.8
92.5°	6.2	8.9	12.6	14.9	18.3	23.1	34.6	50.7	65.2	66.1	55.8
95°	17.8	19.8	24.9	29.5	37.6	49.8	73.2	117.4	176.5	199.4	174.4
97.5°	29.0	31.7	37.1	44.1	53.4	67.2	96.7	158.3	256.3	340.3	357.0
100°	39.1	40.7	45.3	53.4	63.6	77.8	104.8	166.8	276.6	401.7	474.9
102.5°	48.5	49.7	54.2	62.3	72.9	87.1	112.1	167.2	268.9	403.8	518.9
105°	62.1	64.1	67.6	75.3	86.4	100.7	124.6	169.9	253.8	376.8	512.1
107.5°	76.7	78.3	81.8	88.8	99.9	114.2	137.4	176.8	246.2	347.9	467.4
110°	86.4	88.5	91.6	98.2	108.8	123.6	146.0	182.5	244.6	334.1	439.3



TEST NUMBER: P331392-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	95.4	97.5	100.9	107.1	117.3	132.5	154.1	188.7	245.0	325.1	419.8
115°	109.3	111.9	114.9	121.0	131.2	144.9	166.8	197.8	247.2	315.3	395.7
117.5°	123.8	125.8	128.9	134.3	144.0	158.3	178.5	207.6	250.8	310.5	380.4
120°	132.7	134.7	137.8	142.4	152.6	166.8	186.6	214.1	253.2	307.6	372.3
122.5°	141.2	142.9	146.0	151.0	161.1	175.8	194.4	219.8	256.1	306.0	365.3
125°	152.6	154.1	157.1	163.3	173.4	187.6	206.0	228.8	260.4	303.1	355.4
127.5°	161.5	163.5	167.8	174.5	184.3	198.9	216.8	237.3	264.7	301.4	346.3
130°	166.8	168.8	173.9	181.0	191.2	205.5	223.3	242.5	268.0	300.5	340.2
132.5°	171.7	174.2	179.6	187.2	197.7	212.0	228.9	247.9	271.3	300.1	335.3
135°	179.0	181.0	187.2	194.7	206.4	220.7	237.0	254.8	275.1	299.5	328.5
137.5°	185.9	188.3	194.5	202.6	214.2	227.4	243.5	260.0	278.6	299.4	323.7
140°	191.2	193.2	199.4	207.5	218.6	231.9	247.2	262.9	280.2	299.0	320.9
142.5°	196.5	198.1	203.8	212.0	222.7	235.1	250.0	265.4	281.4	299.0	318.1
145°	204.5	206.4	211.5	219.2	229.3	240.5	254.2	268.5	282.8	298.0	314.2
147.5°	212.9	214.5	219.4	226.4	234.9	244.8	257.7	270.3	283.1	296.1	310.4
150°	218.6	220.2	224.3	230.9	238.5	247.6	259.3	271.1	282.8	295.0	307.2
152.5°	224.4	225.1	229.2	235.0	242.2	250.5	261.0	271.4	282.0	292.9	304.3
155°	232.4	232.9	235.9	241.6	247.2	254.8	263.4	272.1	280.7	289.4	299.0
157.5°	239.1	239.6	242.1	246.9	251.5	257.8	265.1	272.1	278.4	285.7	294.0
160°	243.6	244.1	246.1	250.2	254.2	259.8	266.0	272.1	277.1	283.3	290.3
162.5°	248.1	247.7	249.8	253.1	256.7	261.1	266.4	271.6	275.9	281.2	287.1
165°	253.2	252.7	253.8	256.8	259.3	262.4	267.0	270.5	273.6	277.1	281.7
167.5°	257.5	256.9	257.8	259.8	261.6	263.5	266.9	269.8	271.3	273.6	276.4
170°	260.4	259.3	259.8	261.4	262.4	263.9	266.4	269.0	270.0	271.5	273.6
172.5°	262.0	261.4	261.1	262.6	263.2	264.3	266.1	267.8	268.4	269.1	270.7
175°	263.9	263.4	262.9	263.9	263.9	264.4	265.5	266.4	266.0	266.4	267.0
177.5°	264.8	264.0	263.6	264.4	264.4	264.4	264.8	265.6	264.8	264.4	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331392-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6	1230.6
2.5°	1225.3	1227.4	1229.5	1230.4	1229.9	1229.5	1229.1	1228.7
5°	1217.0	1219.1	1221.3	1222.0	1221.6	1221.0	1220.5	1219.9
7.5°	1203.3	1205.4	1207.6	1208.3	1207.7	1207.1	1206.6	1205.9
10°	1191.0	1193.1	1195.2	1195.9	1195.1	1194.3	1193.5	1192.8
12.5°	1176.5	1177.9	1179.5	1179.9	1179.3	1178.8	1178.1	1177.6
15°	1151.0	1152.1	1153.2	1153.0	1151.7	1150.4	1149.1	1147.7
17.5°	1120.8	1122.0	1123.3	1123.2	1122.0	1120.7	1119.5	1118.2
20°	1097.3	1098.1	1098.9	1098.7	1097.7	1096.6	1095.6	1094.5
22.5°	1072.4	1072.5	1072.6	1072.5	1071.7	1071.1	1070.5	1069.9
25°	1031.7	1032.2	1032.7	1032.7	1032.2	1031.7	1031.2	1030.6
27.5°	991.7	990.9	990.1	989.1	987.7	986.5	985.3	984.0
30°	960.4	959.7	958.9	957.9	956.9	955.8	954.8	953.7
32.5°	929.8	928.4	926.9	925.7	924.7	923.6	922.6	921.5
35°	880.7	879.1	877.6	876.1	874.9	873.5	872.2	870.8
37.5°	831.5	829.6	827.6	826.0	824.7	823.5	822.2	820.9
40°	797.5	795.1	792.8	791.0	790.1	789.0	787.9	786.8
42.5°	763.9	761.3	758.8	756.8	755.3	753.9	752.3	750.9
45°	712.5	709.5	706.7	704.7	703.6	702.6	701.5	700.5
47.5°	658.9	655.9	652.8	650.5	649.0	647.5	646.0	644.4
50°	624.5	620.8	617.2	614.7	613.3	612.0	610.7	609.4
52.5°	588.8	585.8	582.7	580.3	578.6	576.8	575.2	573.4
55°	535.7	532.4	529.3	527.1	525.8	524.4	523.2	521.8
57.5°	480.4	477.2	474.1	472.1	471.1	470.1	469.1	468.1
60°	443.9	441.0	438.1	436.2	435.4	434.6	433.8	433.1
62.5°	409.2	406.5	403.9	402.1	401.0	400.0	399.0	398.1
65°	356.1	353.8	351.4	349.6	348.3	347.0	345.6	344.3
67.5°	303.7	301.8	300.1	298.6	297.6	296.5	295.4	294.4
70°	269.7	267.8	266.0	264.5	263.5	262.4	261.4	260.3
72.5°	237.5	235.6	233.8	232.5	231.6	230.8	229.9	229.1
75°	187.3	185.7	184.2	183.7	184.2	184.8	185.2	185.7
77.5°	142.6	141.8	141.0	140.2	139.5	138.8	138.0	137.2
80°	113.2	112.4	111.6	110.9	110.4	109.9	109.4	108.9
82.5°	84.4	83.4	82.4	81.9	81.7	81.6	81.5	81.4
85°	44.6	43.8	43.0	42.4	42.2	41.9	41.6	41.4
87.5°	15.2	14.4	14.0	13.6	13.5	13.3	13.0	12.8
90°	16.2	15.2	16.2	16.8	16.8	16.8	16.8	16.8
92.5°	44.3	38.1	33.8	30.6	30.2	28.6	29.0	28.2
95°	133.2	102.2	80.9	69.6	63.0	59.0	57.4	58.0
97.5°	310.9	254.4	199.4	162.6	138.3	125.8	118.4	114.1
100°	464.3	401.3	331.5	270.0	227.8	206.0	191.2	182.1
102.5°	564.8	550.5	499.6	434.4	388.5	351.2	332.8	320.4
105°	617.9	675.3	682.0	665.1	633.6	602.1	580.2	573.1
107.5°	579.6	666.2	719.1	743.7	747.6	745.9	741.5	732.1
110°	546.7	637.7	702.8	744.5	766.3	776.1	780.6	780.1



TEST NUMBER: P331392-940

CATALOG NUMBER: SA2XXDIP-C865D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	516.6	604.0	673.5	721.3	751.7	767.9	776.5	779.3
115°	479.6	557.9	624.5	676.9	712.9	736.4	749.6	754.1
117.5°	451.7	520.4	580.9	630.0	666.8	691.5	705.4	709.3
120°	437.8	500.9	554.8	601.1	636.7	660.6	675.3	680.4
122.5°	426.9	484.6	535.7	577.5	609.4	632.9	646.0	650.3
125°	410.9	463.2	508.0	546.2	575.7	594.9	607.7	611.8
127.5°	395.1	442.6	484.7	520.0	545.6	563.7	574.7	578.0
130°	385.0	428.7	468.9	502.4	527.4	544.7	554.8	558.8
132.5°	375.2	415.7	452.6	484.1	508.6	525.9	535.3	539.0
135°	361.6	395.1	428.7	457.2	479.0	495.8	505.0	507.0
137.5°	350.7	378.8	405.4	430.3	450.1	464.6	472.6	475.6
140°	343.8	368.2	391.6	413.9	430.3	443.4	451.0	454.1
142.5°	338.0	358.8	379.0	397.7	413.1	425.2	431.9	432.6
145°	330.0	346.8	362.6	377.4	389.5	398.1	403.2	404.7
147.5°	323.9	337.1	349.4	360.2	370.2	377.1	380.6	381.5
150°	319.3	330.6	341.3	350.4	358.0	364.1	367.1	367.7
152.5°	314.9	325.3	334.3	342.2	348.2	353.6	355.8	355.9
155°	308.7	316.8	324.4	330.0	335.6	339.2	341.3	340.2
157.5°	301.5	308.3	314.7	319.1	323.0	326.0	326.9	326.9
160°	296.9	302.6	308.2	311.7	315.3	317.8	318.3	318.3
162.5°	292.5	297.3	302.1	304.8	308.4	310.1	310.6	310.2
165°	285.8	289.4	292.9	295.0	296.9	299.0	299.0	298.5
167.5°	279.4	282.1	284.5	286.4	287.3	288.5	288.4	287.8
170°	276.2	277.7	279.7	280.7	281.2	282.8	282.2	281.2
172.5°	272.5	273.6	275.2	275.8	276.3	277.1	276.5	275.9
175°	268.5	269.0	269.6	270.0	270.0	270.5	270.0	269.0
177.5°	265.6	265.6	266.1	266.1	266.1	266.1	265.6	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4

(END OF REPORT)