

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332979-930

Luminaire Tested: **SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332979-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7457.7 lumens  
Efficiency: N/A  
Efficacy: 114.0 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	98	94	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26
5	69	58	50	44	63	53	46	41	46	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	47	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11293	11293	11293	11293
5°	13100	11327	10011	11327
10°	15497	11278	8936	11278
15°	17901	11173	7678	11173
20°	19930	11030	6943	11030
25°	20574	10889	6446	10889
30°	18011	10718	6147	10718
35°	14020	10464	5966	10464
40°	10513	10175	5868	10175
45°	8301	9710	5817	9710
50°	7008	9173	5649	9173
55°	6108	8583	5346	8583
60°	5496	7971	4732	7971
65°	4844	7310	4069	7310
70°	4362	6626	3673	6626
75°	3656	5873	3132	5873
80°	3092	5002	2934	5002
85°	2612	3909	2612	3909



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.5	1.8
10°-20°	408.9	5.5
20°-30°	639.5	8.6
30°-40°	710.9	9.5
40°-50°	630.7	8.5
50°-60°	491.5	6.6
60°-70°	321.8	4.3
70°-80°	158.2	2.1
80°-90°	42.7	0.6
90°-100°	43.3	0.6
100°-110°	276.2	3.7
110°-120°	528.4	7.1
120°-130°	670.8	9.0
130°-140°	717.7	9.6
140°-150°	671.1	9.0
150°-160°	541.2	7.3
160°-170°	349.1	4.7
170°-180°	120.3	1.6
0°-30°	1183.9	15.9
0°-40°	1894.8	25.4
0°-60°	3017.0	40.5
0°-90°	3539.7	47.5
90°-120°	847.9	11.4
90°-150°	2907.4	39.0
90°-180°	3918.0	52.5
0°-180°	7457.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1399	1399	1399	1399	1399	
5°	1616	1398	1235	1398	1616	164
15°	2142	1337	919	1337	2142	609
25°	2310	1222	724	1222	2310	1025
35°	1423	1062	605	1062	1423	892
45°	727	850	510	850	727	576
55°	434	610	380	610	434	395
65°	254	383	213	383	254	255
75°	117	188	100	188	117	129
85°	28	42	28	42	28	33
90°	28	3	28	3	28	14
95°	28	52	28	52	28	22
105°	270	285	270	285	270	236
115°	536	532	536	532	536	531
125°	754	748	754	748	754	672
135°	935	928	935	928	935	720
145°	1076	1070	1076	1070	1076	673
155°	1173	1174	1173	1174	1173	541
165°	1232	1238	1232	1238	1232	348
175°	1259	1267	1259	1267	1259	120
180°	1267	1267	1267	1267	1267	



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1475.5	1479.6	1475.5	1475.1	1470.6	1469.3	1467.5	1461.6	1450.7	1444.5	1445.8
5°	1616.5	1630.5	1622.7	1621.5	1609.2	1596.8	1588.9	1570.8	1551.7	1538.7	1528.0
7.5°	1779.5	1787.5	1782.7	1774.7	1754.7	1743.3	1725.0	1701.2	1666.9	1640.5	1616.6
10°	1890.4	1897.1	1894.9	1880.2	1865.6	1835.7	1818.8	1785.6	1742.1	1707.8	1675.6
12.5°	1999.5	2006.7	1986.9	1987.5	1959.8	1936.3	1909.4	1867.6	1817.5	1773.1	1732.9
15°	2141.8	2132.7	2132.7	2121.5	2090.4	2057.8	2030.2	1986.2	1923.0	1870.1	1814.3
17.5°	2253.2	2256.3	2251.7	2225.0	2200.7	2166.9	2116.3	2065.0	2006.4	1935.3	1878.2
20°	2319.9	2319.9	2314.8	2296.8	2265.2	2229.1	2174.5	2118.6	2044.3	1972.7	1908.5
22.5°	2346.9	2348.7	2342.8	2327.8	2299.5	2264.2	2217.7	2161.0	2084.4	2003.8	1924.2
25°	2309.7	2320.4	2321.6	2317.6	2309.2	2287.7	2247.7	2189.6	2120.9	2033.5	1947.8
27.5°	2120.6	2134.1	2145.9	2165.4	2191.4	2204.9	2206.7	2177.2	2117.2	2033.1	1946.9
30°	1932.1	1943.3	1980.0	2027.9	2065.1	2098.9	2128.3	2136.1	2102.3	2026.8	1936.0
32.5°	1722.9	1738.2	1774.8	1826.4	1888.3	1945.6	2011.4	2045.0	2044.1	1998.8	1914.8
35°	1422.6	1433.9	1467.7	1521.8	1596.2	1681.3	1785.6	1866.7	1921.9	1918.0	1866.7
37.5°	1147.3	1160.0	1194.2	1239.1	1311.2	1416.6	1517.5	1629.3	1731.5	1788.8	1771.6
40°	997.6	998.2	1031.4	1077.7	1145.3	1237.1	1347.0	1471.0	1584.9	1677.9	1695.9
42.5°	879.5	879.5	901.6	951.4	1000.1	1086.5	1191.5	1314.6	1447.8	1555.3	1603.0
45°	727.1	732.1	750.2	780.1	818.4	891.6	975.6	1090.1	1239.4	1366.8	1446.3
47.5°	615.7	623.1	634.6	659.0	689.5	738.3	807.8	910.6	1032.1	1172.2	1285.3
50°	558.0	559.1	573.7	587.3	613.8	652.6	713.5	799.2	910.8	1045.5	1171.2
52.5°	508.4	508.2	517.0	534.1	555.6	586.0	635.1	713.1	812.0	932.8	1062.5
55°	434.0	436.8	443.6	457.1	473.4	494.9	533.8	592.4	670.2	773.3	891.1
57.5°	377.4	378.9	384.2	389.9	404.9	420.4	449.6	490.3	556.0	640.4	750.2
60°	340.4	341.0	342.7	351.1	363.0	377.6	397.4	431.7	487.0	564.2	651.0
62.5°	304.4	305.3	307.9	314.1	323.3	333.5	354.1	381.7	427.5	493.4	571.6
65°	253.6	254.2	258.1	260.4	267.7	276.7	292.0	310.5	342.1	397.4	456.6
67.5°	211.9	211.9	212.1	215.2	220.3	226.2	235.4	250.2	274.0	307.9	360.1
70°	184.8	184.8	186.0	187.7	190.5	195.6	200.6	211.9	229.4	257.0	297.0
72.5°	159.6	160.0	161.2	161.5	163.0	167.1	170.9	178.1	191.1	211.9	244.3
75°	117.2	119.0	121.7	124.0	126.8	126.3	130.2	134.7	138.7	151.1	169.7
77.5°	87.2	86.3	86.7	88.6	88.9	89.5	92.3	95.8	98.7	104.6	111.3
80°	66.5	66.5	68.2	68.7	68.2	68.7	71.6	73.3	74.4	76.6	82.8
82.5°	50.3	51.2	50.6	51.2	51.5	52.1	54.5	54.8	55.9	56.8	59.4
85°	28.2	28.8	29.3	28.2	28.2	28.2	29.3	29.8	31.0	30.4	31.6
87.5°	15.6	15.1	15.4	15.3	15.7	15.1	15.3	16.0	14.8	15.0	14.7
90°	28.5	28.0	27.6	27.1	26.7	25.9	24.6	23.4	22.1	20.9	19.2
92.5°	26.2	26.1	26.0	25.9	25.8	25.1	23.9	22.6	21.4	20.1	18.4
95°	27.5	27.2	27.1	26.8	26.7	25.9	24.6	23.4	22.1	20.9	20.6
97.5°	26.5	26.3	26.1	25.9	25.7	25.5	25.4	25.3	25.1	25.0	48.5
100°	26.5	26.3	26.1	25.9	25.7	27.4	31.0	34.5	38.1	41.7	70.8
102.5°	27.3	27.2	27.2	27.1	27.1	46.4	85.0	123.6	162.2	200.8	204.6
105°	270.0	277.6	285.1	292.7	300.3	303.1	301.3	299.4	297.5	295.5	294.5
107.5°	376.3	375.4	374.7	373.9	373.1	372.2	371.3	370.4	369.4	368.5	367.0
110°	422.5	421.9	421.3	420.6	420.0	419.5	419.1	418.7	418.2	417.8	416.5



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	468.7	468.0	467.2	466.4	465.5	465.2	465.3	465.4	465.5	465.5	465.0
115°	536.2	536.2	536.2	536.2	536.2	536.0	535.6	535.2	534.8	534.3	534.5
117.5°	604.8	604.9	605.0	605.0	605.1	605.2	605.3	605.4	605.4	605.5	605.1
120°	648.0	648.4	648.8	649.2	649.6	649.6	649.2	648.8	648.4	648.0	648.2
122.5°	690.4	690.8	691.3	691.7	692.1	692.2	691.9	691.7	691.5	691.2	690.9
125°	754.1	753.9	753.7	753.4	753.3	752.8	752.2	751.5	750.9	750.3	750.7
127.5°	810.0	810.2	810.3	810.5	810.7	810.8	810.9	811.1	811.1	811.3	810.3
130°	847.8	847.8	847.8	847.8	847.8	847.7	847.6	847.3	847.1	846.9	846.3
132.5°	882.7	882.9	883.1	883.2	883.4	883.4	883.2	883.0	882.7	882.6	881.7
135°	935.0	934.6	934.2	933.8	933.4	932.9	932.5	932.1	931.6	931.2	930.4
137.5°	979.7	979.8	980.0	980.2	980.2	980.1	979.6	979.2	978.7	978.2	977.3
140°	1010.8	1010.6	1010.4	1010.2	1010.0	1009.6	1008.9	1008.3	1007.6	1007.1	1006.6
142.5°	1036.6	1036.6	1036.5	1036.5	1036.4	1036.2	1035.7	1035.3	1034.8	1034.3	1034.0
145°	1076.2	1075.8	1075.3	1074.9	1074.5	1074.2	1074.0	1073.7	1073.6	1073.3	1073.3
147.5°	1109.0	1108.7	1108.6	1108.3	1108.1	1107.9	1107.7	1107.6	1107.4	1107.3	1107.4
150°	1130.2	1130.0	1129.8	1129.5	1129.4	1129.2	1129.2	1129.2	1129.2	1129.2	1129.4
152.5°	1148.3	1148.5	1148.6	1148.8	1148.8	1148.8	1148.4	1148.1	1147.8	1147.5	1147.8
155°	1172.8	1173.5	1174.0	1174.7	1175.3	1175.3	1174.4	1173.5	1172.7	1171.8	1172.5
157.5°	1193.3	1194.3	1195.5	1196.5	1197.7	1197.7	1196.5	1195.5	1194.3	1193.3	1194.0
160°	1206.9	1208.2	1209.4	1210.7	1211.9	1211.9	1210.7	1209.4	1208.2	1206.9	1207.1
162.5°	1217.5	1219.0	1220.4	1221.8	1223.3	1223.4	1222.1	1220.8	1219.5	1218.3	1218.5
165°	1232.5	1234.4	1236.2	1238.2	1240.1	1240.2	1238.5	1236.8	1235.1	1233.5	1233.5
167.5°	1243.7	1245.8	1247.9	1250.0	1252.1	1252.2	1250.3	1248.5	1246.7	1244.8	1245.0
170°	1250.5	1252.6	1254.7	1256.8	1258.9	1259.1	1257.4	1255.7	1254.1	1252.4	1252.1
172.5°	1254.3	1256.5	1258.8	1261.1	1263.4	1263.6	1262.0	1260.3	1258.6	1256.9	1256.7
175°	1259.0	1261.5	1264.0	1266.6	1269.1	1269.4	1267.5	1265.7	1263.7	1261.8	1261.7
177.5°	1262.1	1264.0	1266.1	1268.1	1270.2	1270.5	1269.1	1267.8	1266.4	1265.1	1264.8
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1441.3	1435.0	1431.8	1424.6	1416.0	1411.5	1407.5	1401.6	1393.9	1385.8	1380.0
5°	1514.4	1500.9	1484.0	1463.7	1445.7	1428.2	1413.0	1397.7	1380.3	1362.3	1344.3
7.5°	1589.5	1562.9	1534.1	1500.9	1468.6	1439.2	1412.1	1386.2	1356.8	1330.6	1306.7
10°	1641.8	1605.7	1565.7	1523.5	1481.2	1444.5	1408.5	1375.8	1339.7	1307.6	1280.5
12.5°	1684.2	1641.8	1593.7	1541.1	1490.2	1445.9	1404.4	1361.8	1320.8	1286.0	1249.9
15°	1754.5	1696.5	1631.7	1568.6	1502.6	1442.3	1386.5	1336.9	1290.1	1241.1	1206.7
17.5°	1802.9	1734.1	1655.2	1579.4	1501.5	1430.4	1366.0	1306.9	1253.0	1202.9	1162.0
20°	1831.7	1755.7	1668.3	1582.1	1494.7	1418.6	1349.3	1283.9	1228.2	1174.0	1131.7
22.5°	1848.0	1763.8	1668.3	1578.0	1487.5	1405.1	1329.0	1260.9	1200.2	1146.1	1099.3
25°	1853.2	1763.0	1665.5	1561.8	1462.6	1375.2	1296.3	1222.5	1154.9	1100.7	1051.2
27.5°	1846.0	1739.8	1639.9	1533.5	1431.2	1339.0	1256.2	1178.7	1110.9	1052.9	1002.0
30°	1835.2	1721.3	1614.2	1503.7	1400.0	1311.6	1224.2	1149.8	1079.3	1019.0	967.8
32.5°	1811.7	1698.8	1583.6	1470.4	1365.3	1274.1	1191.2	1116.4	1047.3	985.7	931.2
35°	1765.3	1650.8	1525.8	1409.7	1306.4	1211.8	1134.0	1061.8	995.9	930.0	872.5
37.5°	1704.1	1587.1	1462.7	1335.5	1232.3	1142.9	1071.5	1003.8	939.5	879.2	815.5
40°	1646.3	1539.8	1411.3	1285.1	1179.1	1092.8	1027.0	965.5	900.7	840.9	777.2
42.5°	1576.5	1485.7	1355.8	1229.1	1124.5	1041.5	980.0	919.9	861.0	803.1	736.6
45°	1459.8	1391.0	1269.3	1147.5	1042.1	959.9	903.5	850.5	798.7	743.4	680.9
47.5°	1326.1	1279.5	1174.4	1049.8	952.3	878.2	823.8	780.5	736.6	681.4	626.6
50°	1233.2	1203.3	1101.9	988.1	895.0	826.8	771.0	730.4	693.8	640.8	591.8
52.5°	1134.0	1118.1	1032.4	923.6	833.7	766.9	719.2	682.7	645.6	601.6	555.7
55°	982.9	991.4	918.7	824.6	740.0	683.7	640.3	609.8	578.3	541.1	505.6
57.5°	828.5	859.4	810.6	728.0	648.7	596.6	563.9	538.3	511.8	481.0	450.7
60°	736.1	762.0	734.4	661.7	592.4	543.9	513.5	493.7	467.2	439.0	416.0
62.5°	645.9	673.6	657.3	598.6	534.2	492.5	465.7	447.3	427.5	403.0	379.0
65°	532.6	550.7	542.7	502.2	456.6	421.0	396.2	382.7	364.7	346.7	325.2
67.5°	408.0	442.8	438.1	416.6	377.2	349.4	333.2	321.2	304.8	291.4	276.9
70°	335.3	367.5	366.9	349.4	328.0	302.1	290.8	280.7	266.0	253.1	241.2
72.5°	274.5	303.9	308.3	294.9	280.2	260.7	249.8	242.8	228.6	219.7	210.1
75°	192.2	213.6	219.2	219.2	212.5	202.4	192.7	188.3	178.1	170.2	164.6
77.5°	126.0	139.6	148.4	150.3	151.4	148.0	140.1	137.0	129.1	126.4	121.0
80°	89.0	98.1	108.2	111.6	114.4	113.3	109.9	107.6	100.4	97.5	95.2
82.5°	61.6	66.5	74.8	82.3	81.5	84.5	81.5	79.7	74.2	73.1	70.9
85°	32.1	32.7	33.8	38.9	41.7	42.8	43.4	42.2	40.6	40.6	36.6
87.5°	14.3	13.5	14.1	13.7	13.7	15.0	15.9	15.9	15.0	14.1	13.2
90°	17.4	15.8	14.1	12.1	9.8	7.5	5.1	2.9	5.1	7.5	9.8
92.5°	16.7	15.0	13.4	12.5	12.3	12.2	12.1	11.9	12.1	12.2	12.3
95°	20.4	20.2	20.0	23.5	30.7	37.7	44.9	52.1	44.9	37.7	30.7
97.5°	72.0	95.5	119.0	128.5	124.0	119.6	115.1	110.6	115.1	119.6	124.0
100°	99.8	128.8	157.9	170.6	166.7	163.0	159.1	155.4	159.1	163.0	166.7
102.5°	208.4	212.2	216.0	216.5	213.7	210.9	208.1	205.4	208.1	210.9	213.7
105°	293.4	292.4	291.4	290.2	288.9	287.6	286.4	285.1	286.4	287.6	288.9
107.5°	365.7	364.2	362.8	361.7	361.1	360.5	359.9	359.2	359.9	360.5	361.1
110°	415.2	414.0	412.7	411.8	411.2	410.5	409.9	409.3	409.9	410.5	411.2





TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	464.3	463.7	463.2	462.3	461.1	460.0	458.9	457.8	458.9	460.0	461.1
115°	534.8	534.9	535.2	534.9	534.3	533.7	533.0	532.4	533.0	533.7	534.3
117.5°	604.6	604.1	603.6	603.0	602.2	601.4	600.5	599.7	600.5	601.4	602.2
120°	648.4	648.7	648.8	648.5	647.7	646.9	646.0	645.1	646.0	646.9	647.7
122.5°	690.6	690.3	690.0	689.6	689.1	688.6	688.1	687.5	688.1	688.6	689.1
125°	751.1	751.5	752.0	751.8	750.9	750.1	749.3	748.4	749.3	750.1	750.9
127.5°	809.3	808.4	807.4	806.8	806.7	806.4	806.2	806.0	806.2	806.4	806.7
130°	845.6	845.1	844.4	844.0	843.8	843.6	843.3	843.1	843.3	843.6	843.8
132.5°	880.9	880.1	879.4	878.7	878.4	878.0	877.6	877.3	877.6	878.0	878.4
135°	929.5	928.7	927.9	927.6	927.7	928.0	928.2	928.4	928.2	928.0	927.7
137.5°	976.4	975.4	974.5	974.0	974.0	973.9	973.8	973.7	973.8	973.9	974.0
140°	1006.2	1005.8	1005.3	1004.9	1004.5	1004.0	1003.6	1003.2	1003.6	1004.0	1004.5
142.5°	1033.8	1033.6	1033.3	1032.8	1032.0	1031.3	1030.5	1029.7	1030.5	1031.3	1032.0
145°	1073.3	1073.3	1073.3	1073.0	1072.4	1071.8	1071.1	1070.5	1071.1	1071.8	1072.4
147.5°	1107.7	1107.9	1108.1	1107.6	1106.4	1105.2	1104.1	1102.9	1104.1	1105.2	1106.4
150°	1129.7	1129.8	1130.1	1129.8	1128.9	1128.0	1127.2	1126.4	1127.2	1128.0	1128.9
152.5°	1148.2	1148.6	1148.9	1148.8	1148.1	1147.5	1146.8	1146.1	1146.8	1147.5	1148.1
155°	1173.1	1173.8	1174.4	1174.6	1174.4	1174.2	1173.9	1173.8	1173.9	1174.2	1174.4
157.5°	1194.7	1195.4	1196.1	1196.5	1196.7	1196.8	1196.9	1197.0	1196.9	1196.8	1196.7
160°	1207.3	1207.5	1207.8	1208.2	1208.8	1209.4	1210.1	1210.7	1210.1	1209.4	1208.8
162.5°	1218.7	1218.9	1219.1	1219.6	1220.4	1221.2	1222.1	1222.8	1222.1	1221.2	1220.4
165°	1233.5	1233.5	1233.5	1234.0	1235.0	1236.1	1237.1	1238.2	1237.1	1236.1	1235.0
167.5°	1245.0	1245.2	1245.3	1245.9	1247.0	1248.1	1249.2	1250.3	1249.2	1248.1	1247.0
170°	1252.0	1251.7	1251.6	1252.1	1253.4	1254.6	1255.9	1257.1	1255.9	1254.6	1253.4
172.5°	1256.5	1256.3	1256.1	1256.6	1257.8	1259.1	1260.4	1261.7	1260.4	1259.1	1257.8
175°	1261.4	1261.2	1261.0	1261.5	1262.8	1264.0	1265.3	1266.6	1265.3	1264.0	1262.8
177.5°	1264.4	1264.0	1263.7	1264.1	1265.3	1266.5	1267.7	1268.9	1267.7	1266.5	1265.3
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1373.6	1369.1	1363.3	1356.5	1348.4	1341.2	1338.1	1340.8	1342.1	1338.5	1338.1
5°	1331.9	1317.8	1306.4	1289.6	1276.0	1264.8	1256.9	1253.5	1254.6	1245.6	1243.3
7.5°	1284.8	1268.1	1249.7	1229.6	1210.9	1194.3	1185.6	1180.9	1171.3	1167.3	1160.4
10°	1254.6	1232.1	1214.1	1190.3	1169.0	1149.2	1139.6	1131.7	1122.2	1117.7	1108.1
12.5°	1223.5	1197.3	1177.5	1152.9	1131.1	1107.3	1098.1	1083.5	1068.5	1059.1	1046.8
15°	1179.7	1148.1	1123.9	1094.5	1068.6	1041.5	1017.3	990.3	980.2	958.7	946.3
17.5°	1128.4	1096.3	1066.3	1027.0	987.0	953.4	927.6	901.6	886.1	872.5	866.2
20°	1094.5	1065.3	1023.5	977.9	933.4	896.2	875.3	858.4	841.5	831.9	825.2
22.5°	1062.5	1025.1	976.6	927.4	882.9	853.8	836.1	818.7	804.9	795.8	786.8
25°	1008.9	959.9	908.6	852.2	821.7	796.4	777.2	763.1	754.7	742.8	738.3
27.5°	953.7	894.4	837.8	799.9	768.2	745.0	728.3	717.7	707.0	699.4	693.6
30°	911.3	851.1	800.4	764.3	732.1	713.0	699.4	687.1	678.6	672.4	667.9
32.5°	869.4	809.1	766.5	727.7	702.4	683.7	669.3	660.0	653.4	645.3	642.6
35°	808.8	755.2	718.0	683.1	657.2	640.3	629.0	619.4	613.8	611.6	609.8
37.5°	750.5	706.7	666.7	638.1	614.9	601.6	588.3	583.6	579.8	575.7	577.5
40°	713.5	672.4	636.9	606.4	587.8	573.2	565.3	559.7	556.3	556.3	556.3
42.5°	681.5	641.3	606.7	579.4	560.8	548.4	539.6	534.8	533.8	533.3	536.0
45°	631.9	594.6	559.7	537.1	521.4	508.9	503.9	499.9	499.9	502.2	502.7
47.5°	582.5	547.7	519.7	494.4	480.0	472.2	467.8	465.8	466.0	468.2	470.8
50°	552.4	518.0	490.3	467.8	454.3	446.9	443.0	441.9	443.0	443.0	446.9
52.5°	519.4	488.7	461.5	442.5	427.2	420.4	418.2	416.6	417.3	419.1	420.8
55°	471.2	443.6	417.7	399.6	388.3	383.8	378.8	379.3	378.2	379.3	379.3
57.5°	422.8	398.0	373.9	359.6	349.7	343.2	337.6	339.2	337.5	337.3	336.4
60°	391.8	364.7	345.5	332.6	321.2	315.6	310.5	311.7	310.0	308.8	306.6
62.5°	357.9	335.3	317.1	304.6	295.5	289.0	284.0	282.8	278.9	275.1	270.1
65°	308.8	290.2	273.9	262.1	253.6	248.6	244.6	241.2	232.8	223.7	219.2
67.5°	261.2	247.8	232.5	222.5	215.6	209.0	201.5	195.7	187.8	182.9	180.0
70°	230.5	217.5	204.6	195.0	187.7	181.5	173.0	169.1	163.5	161.2	158.4
72.5°	201.2	189.1	177.1	168.4	160.6	155.8	149.1	145.2	142.7	141.8	139.0
75°	156.7	147.1	138.1	130.2	124.0	120.6	117.8	115.0	113.8	108.8	106.0
77.5°	114.3	108.0	102.3	96.7	92.3	90.1	84.6	81.4	79.5	77.1	76.6
80°	89.0	84.5	78.9	75.5	69.3	67.1	64.8	64.2	63.7	63.1	62.5
82.5°	66.9	62.5	56.8	54.8	53.1	51.8	50.4	49.8	49.2	49.6	49.5
85°	33.8	31.6	31.6	31.0	30.4	29.8	29.3	29.3	28.8	29.3	28.8
87.5°	13.7	13.6	13.9	13.5	14.2	14.5	14.3	14.6	15.3	14.7	14.8
90°	12.1	14.1	15.8	17.4	19.2	20.9	22.1	23.4	24.6	25.9	26.7
92.5°	12.5	13.4	15.0	16.7	18.4	20.1	21.4	22.6	23.9	25.1	25.8
95°	23.5	20.0	20.2	20.4	20.6	20.9	22.1	23.4	24.6	25.9	26.7
97.5°	128.5	119.0	95.5	72.0	48.5	25.0	25.1	25.3	25.4	25.5	25.7
100°	170.6	157.9	128.8	99.8	70.8	41.7	38.1	34.5	31.0	27.4	25.7
102.5°	216.5	216.0	212.2	208.4	204.6	200.8	162.2	123.6	85.0	46.4	27.1
105°	290.2	291.4	292.4	293.4	294.5	295.5	297.5	299.4	301.3	303.1	300.3
107.5°	361.7	362.8	364.2	365.7	367.0	368.5	369.4	370.4	371.3	372.2	373.1
110°	411.8	412.7	414.0	415.2	416.5	417.8	418.2	418.7	419.1	419.5	420.0



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	462.3	463.2	463.7	464.3	465.0	465.5	465.5	465.4	465.3	465.2	465.5
115°	534.9	535.2	534.9	534.8	534.5	534.3	534.8	535.2	535.6	536.0	536.2
117.5°	603.0	603.6	604.1	604.6	605.1	605.5	605.4	605.4	605.3	605.2	605.1
120°	648.5	648.8	648.7	648.4	648.2	648.0	648.4	648.8	649.2	649.6	649.6
122.5°	689.6	690.0	690.3	690.6	690.9	691.2	691.5	691.7	691.9	692.2	692.1
125°	751.8	752.0	751.5	751.1	750.7	750.3	750.9	751.5	752.2	752.8	753.3
127.5°	806.8	807.4	808.4	809.3	810.3	811.3	811.1	811.1	810.9	810.8	810.7
130°	844.0	844.4	845.1	845.6	846.3	846.9	847.1	847.3	847.6	847.7	847.8
132.5°	878.7	879.4	880.1	880.9	881.7	882.6	882.7	883.0	883.2	883.4	883.4
135°	927.6	927.9	928.7	929.5	930.4	931.2	931.6	932.1	932.5	932.9	933.4
137.5°	974.0	974.5	975.4	976.4	977.3	978.2	978.7	979.2	979.6	980.1	980.2
140°	1004.9	1005.3	1005.8	1006.2	1006.6	1007.1	1007.6	1008.3	1008.9	1009.6	1010.0
142.5°	1032.8	1033.3	1033.6	1033.8	1034.0	1034.3	1034.8	1035.3	1035.7	1036.2	1036.4
145°	1073.0	1073.3	1073.3	1073.3	1073.3	1073.3	1073.6	1073.7	1074.0	1074.2	1074.5
147.5°	1107.6	1108.1	1107.9	1107.7	1107.4	1107.3	1107.4	1107.6	1107.7	1107.9	1108.1
150°	1129.8	1130.1	1129.8	1129.7	1129.4	1129.2	1129.2	1129.2	1129.2	1129.2	1129.4
152.5°	1148.8	1148.9	1148.6	1148.2	1147.8	1147.5	1147.8	1148.1	1148.4	1148.8	1148.8
155°	1174.6	1174.4	1173.8	1173.1	1172.5	1171.8	1172.7	1173.5	1174.4	1175.3	1175.3
157.5°	1196.5	1196.1	1195.4	1194.7	1194.0	1193.3	1194.3	1195.5	1196.5	1197.7	1197.7
160°	1208.2	1207.8	1207.5	1207.3	1207.1	1206.9	1208.2	1209.4	1210.7	1211.9	1211.9
162.5°	1219.6	1219.1	1218.9	1218.7	1218.5	1218.3	1219.5	1220.8	1222.1	1223.4	1223.3
165°	1234.0	1233.5	1233.5	1233.5	1233.5	1233.5	1235.1	1236.8	1238.5	1240.2	1240.1
167.5°	1245.9	1245.3	1245.2	1245.0	1245.0	1244.8	1246.7	1248.5	1250.3	1252.2	1252.1
170°	1252.1	1251.6	1251.7	1252.0	1252.1	1252.4	1254.1	1255.7	1257.4	1259.1	1258.9
172.5°	1256.6	1256.1	1256.3	1256.5	1256.7	1256.9	1258.6	1260.3	1262.0	1263.6	1263.4
175°	1261.5	1261.0	1261.2	1261.4	1261.7	1261.8	1263.7	1265.7	1267.5	1269.4	1269.1
177.5°	1264.1	1263.7	1264.0	1264.4	1264.8	1265.1	1266.4	1267.8	1269.1	1270.5	1270.2
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1335.3	1336.2	1333.1	1332.2	1333.1	1336.2	1335.3	1338.1	1338.5	1342.1	1340.8
5°	1238.8	1237.7	1234.9	1235.4	1234.9	1237.7	1238.8	1243.3	1245.6	1254.6	1253.5
7.5°	1156.3	1151.9	1153.2	1148.7	1153.2	1151.9	1156.3	1160.4	1167.3	1171.3	1180.9
10°	1105.8	1099.6	1094.5	1090.1	1094.5	1099.6	1105.8	1108.1	1117.7	1122.2	1131.7
12.5°	1036.8	1031.5	1024.7	1026.1	1024.7	1031.5	1036.8	1046.8	1059.1	1068.5	1083.5
15°	939.0	930.5	917.0	918.7	917.0	930.5	939.0	946.3	958.7	980.2	990.3
17.5°	856.1	856.2	850.0	851.5	850.0	856.2	856.1	866.2	872.5	886.1	901.6
20°	813.3	809.3	809.9	808.2	809.9	809.3	813.3	825.2	831.9	841.5	858.4
22.5°	783.6	778.7	774.8	771.3	774.8	778.7	783.6	786.8	795.8	804.9	818.7
25°	733.3	729.9	724.8	723.7	724.8	729.9	733.3	738.3	742.8	754.7	763.1
27.5°	689.1	688.4	686.4	683.8	686.4	688.4	689.1	693.6	699.4	707.0	717.7
30°	663.4	662.3	661.1	659.4	661.1	662.3	663.4	667.9	672.4	678.6	687.1
32.5°	640.4	639.7	638.5	638.7	638.5	639.7	640.4	642.6	645.3	653.4	660.0
35°	607.6	607.0	605.9	605.4	605.9	607.0	607.6	609.8	611.6	613.8	619.4
37.5°	576.9	578.4	577.7	577.6	577.7	578.4	576.9	577.5	575.7	579.8	583.6
40°	555.7	556.3	557.4	556.8	557.4	556.3	555.7	556.3	556.3	556.3	559.7
42.5°	538.2	538.3	539.8	537.9	539.8	538.3	538.2	536.0	533.3	533.8	534.8
45°	506.7	510.1	509.5	509.5	509.5	510.1	506.7	502.7	502.2	499.9	499.9
47.5°	472.3	475.2	476.1	475.9	476.1	475.2	472.3	470.8	468.2	466.0	465.8
50°	449.8	448.7	450.4	449.8	450.4	448.7	449.8	446.9	443.0	443.0	441.9
52.5°	422.2	422.5	422.4	421.8	422.4	422.5	422.2	420.8	419.1	417.3	416.6
55°	379.8	380.4	379.3	379.8	379.3	380.4	379.8	379.3	379.3	378.2	379.3
57.5°	333.9	331.2	332.3	330.9	332.3	331.2	333.9	336.4	337.3	337.5	339.2
60°	301.0	296.4	295.3	293.1	295.3	296.4	301.0	306.6	308.8	310.0	311.7
62.5°	264.0	260.8	257.0	258.8	257.0	260.8	264.0	270.1	275.1	278.9	282.8
65°	214.7	212.5	210.8	213.0	210.8	212.5	214.7	219.2	223.7	232.8	241.2
67.5°	177.7	176.5	176.5	175.4	176.5	176.5	177.7	180.0	182.9	187.8	195.7
70°	158.4	156.7	156.7	155.6	156.7	156.7	158.4	158.4	161.2	163.5	169.1
72.5°	138.5	136.8	137.3	136.6	137.3	136.8	138.5	139.0	141.8	142.7	145.2
75°	102.6	99.8	99.8	100.4	99.8	99.8	102.6	106.0	108.8	113.8	115.0
77.5°	76.6	76.0	76.8	75.7	76.8	76.0	76.6	76.6	77.1	79.5	81.4
80°	62.5	62.0	61.5	63.1	61.5	62.0	62.5	62.5	63.1	63.7	64.2
82.5°	48.6	48.5	48.3	50.5	48.3	48.5	48.6	49.5	49.6	49.2	49.8
85°	29.3	28.2	29.3	28.2	29.3	28.2	29.3	28.8	29.3	28.8	29.3
87.5°	15.8	15.4	15.1	15.6	15.1	15.4	15.8	14.8	14.7	15.3	14.6
90°	27.1	27.6	28.0	28.5	28.0	27.6	27.1	26.7	25.9	24.6	23.4
92.5°	25.9	26.0	26.1	26.2	26.1	26.0	25.9	25.8	25.1	23.9	22.6
95°	26.8	27.1	27.2	27.5	27.2	27.1	26.8	26.7	25.9	24.6	23.4
97.5°	25.9	26.1	26.3	26.5	26.3	26.1	25.9	25.7	25.5	25.4	25.3
100°	25.9	26.1	26.3	26.5	26.3	26.1	25.9	25.7	27.4	31.0	34.5
102.5°	27.1	27.2	27.2	27.3	27.2	27.2	27.1	27.1	46.4	85.0	123.6
105°	292.7	285.1	277.6	270.0	277.6	285.1	292.7	300.3	303.1	301.3	299.4
107.5°	373.9	374.7	375.4	376.3	375.4	374.7	373.9	373.1	372.2	371.3	370.4
110°	420.6	421.3	421.9	422.5	421.9	421.3	420.6	420.0	419.5	419.1	418.7



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	466.4	467.2	468.0	468.7	468.0	467.2	466.4	465.5	465.2	465.3	465.4
115°	536.2	536.2	536.2	536.2	536.2	536.2	536.2	536.2	536.0	535.6	535.2
117.5°	605.0	605.0	604.9	604.8	604.9	605.0	605.0	605.1	605.2	605.3	605.4
120°	649.2	648.8	648.4	648.0	648.4	648.8	649.2	649.6	649.6	649.2	648.8
122.5°	691.7	691.3	690.8	690.4	690.8	691.3	691.7	692.1	692.2	691.9	691.7
125°	753.4	753.7	753.9	754.1	753.9	753.7	753.4	753.3	752.8	752.2	751.5
127.5°	810.5	810.3	810.2	810.0	810.2	810.3	810.5	810.7	810.8	810.9	811.1
130°	847.8	847.8	847.8	847.8	847.8	847.8	847.8	847.8	847.7	847.6	847.3
132.5°	883.2	883.1	882.9	882.7	882.9	883.1	883.2	883.4	883.4	883.2	883.0
135°	933.8	934.2	934.6	935.0	934.6	934.2	933.8	933.4	932.9	932.5	932.1
137.5°	980.2	980.0	979.8	979.7	979.8	980.0	980.2	980.2	980.1	979.6	979.2
140°	1010.2	1010.4	1010.6	1010.8	1010.6	1010.4	1010.2	1010.0	1009.6	1008.9	1008.3
142.5°	1036.5	1036.5	1036.6	1036.6	1036.6	1036.5	1036.5	1036.4	1036.2	1035.7	1035.3
145°	1074.9	1075.3	1075.8	1076.2	1075.8	1075.3	1074.9	1074.5	1074.2	1074.0	1073.7
147.5°	1108.3	1108.6	1108.7	1109.0	1108.7	1108.6	1108.3	1108.1	1107.9	1107.7	1107.6
150°	1129.5	1129.8	1130.0	1130.2	1130.0	1129.8	1129.5	1129.4	1129.2	1129.2	1129.2
152.5°	1148.8	1148.6	1148.5	1148.3	1148.5	1148.6	1148.8	1148.8	1148.8	1148.4	1148.1
155°	1174.7	1174.0	1173.5	1172.8	1173.5	1174.0	1174.7	1175.3	1175.3	1174.4	1173.5
157.5°	1196.5	1195.5	1194.3	1193.3	1194.3	1195.5	1196.5	1197.7	1197.7	1196.5	1195.5
160°	1210.7	1209.4	1208.2	1206.9	1208.2	1209.4	1210.7	1211.9	1211.9	1210.7	1209.4
162.5°	1221.8	1220.4	1219.0	1217.5	1219.0	1220.4	1221.8	1223.3	1223.4	1222.1	1220.8
165°	1238.2	1236.2	1234.4	1232.5	1234.4	1236.2	1238.2	1240.1	1240.2	1238.5	1236.8
167.5°	1250.0	1247.9	1245.8	1243.7	1245.8	1247.9	1250.0	1252.1	1252.2	1250.3	1248.5
170°	1256.8	1254.7	1252.6	1250.5	1252.6	1254.7	1256.8	1258.9	1259.1	1257.4	1255.7
172.5°	1261.1	1258.8	1256.5	1254.3	1256.5	1258.8	1261.1	1263.4	1263.6	1262.0	1260.3
175°	1266.6	1264.0	1261.5	1259.0	1261.5	1264.0	1266.6	1269.1	1269.4	1267.5	1265.7
177.5°	1268.1	1266.1	1264.0	1262.1	1264.0	1266.1	1268.1	1270.2	1270.5	1269.1	1267.8
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1338.1	1341.2	1348.4	1356.5	1363.3	1369.1	1373.6	1380.0	1385.8	1393.9	1401.6
5°	1256.9	1264.8	1276.0	1289.6	1306.4	1317.8	1331.9	1344.3	1362.3	1380.3	1397.7
7.5°	1185.6	1194.3	1210.9	1229.6	1249.7	1268.1	1284.8	1306.7	1330.6	1356.8	1386.2
10°	1139.6	1149.2	1169.0	1190.3	1214.1	1232.1	1254.6	1280.5	1307.6	1339.7	1375.8
12.5°	1098.1	1107.3	1131.1	1152.9	1177.5	1197.3	1223.5	1249.9	1286.0	1320.8	1361.8
15°	1017.3	1041.5	1068.6	1094.5	1123.9	1148.1	1179.7	1206.7	1241.1	1290.1	1336.9
17.5°	927.6	953.4	987.0	1027.0	1066.3	1096.3	1128.4	1162.0	1202.9	1253.0	1306.9
20°	875.3	896.2	933.4	977.9	1023.5	1065.3	1094.5	1131.7	1174.0	1228.2	1283.9
22.5°	836.1	853.8	882.9	927.4	976.6	1025.1	1062.5	1099.3	1146.1	1200.2	1260.9
25°	777.2	796.4	821.7	852.2	908.6	959.9	1008.9	1051.2	1100.7	1154.9	1222.5
27.5°	728.3	745.0	768.2	799.9	837.8	894.4	953.7	1002.0	1052.9	1110.9	1178.7
30°	699.4	713.0	732.1	764.3	800.4	851.1	911.3	967.8	1019.0	1079.3	1149.8
32.5°	669.3	683.7	702.4	727.7	766.5	809.1	869.4	931.2	985.7	1047.3	1116.4
35°	629.0	640.3	657.2	683.1	718.0	755.2	808.8	872.5	930.0	995.9	1061.8
37.5°	588.3	601.6	614.9	638.1	666.7	706.7	750.5	815.5	879.2	939.5	1003.8
40°	565.3	573.2	587.8	606.4	636.9	672.4	713.5	777.2	840.9	900.7	965.5
42.5°	539.6	548.4	560.8	579.4	606.7	641.3	681.5	736.6	803.1	861.0	919.9
45°	503.9	508.9	521.4	537.1	559.7	594.6	631.9	680.9	743.4	798.7	850.5
47.5°	467.8	472.2	480.0	494.4	519.7	547.7	582.5	626.6	681.4	736.6	780.5
50°	443.0	446.9	454.3	467.8	490.3	518.0	552.4	591.8	640.8	693.8	730.4
52.5°	418.2	420.4	427.2	442.5	461.5	488.7	519.4	555.7	601.6	645.6	682.7
55°	378.8	383.8	388.3	399.6	417.7	443.6	471.2	505.6	541.1	578.3	609.8
57.5°	337.6	343.2	349.7	359.6	373.9	398.0	422.8	450.7	481.0	511.8	538.3
60°	310.5	315.6	321.2	332.6	345.5	364.7	391.8	416.0	439.0	467.2	493.7
62.5°	284.0	289.0	295.5	304.6	317.1	335.3	357.9	379.0	403.0	427.5	447.3
65°	244.6	248.6	253.6	262.1	273.9	290.2	308.8	325.2	346.7	364.7	382.7
67.5°	201.5	209.0	215.6	222.5	232.5	247.8	261.2	276.9	291.4	304.8	321.2
70°	173.0	181.5	187.7	195.0	204.6	217.5	230.5	241.2	253.1	266.0	280.7
72.5°	149.1	155.8	160.6	168.4	177.1	189.1	201.2	210.1	219.7	228.6	242.8
75°	117.8	120.6	124.0	130.2	138.1	147.1	156.7	164.6	170.2	178.1	188.3
77.5°	84.6	90.1	92.3	96.7	102.3	108.0	114.3	121.0	126.4	129.1	137.0
80°	64.8	67.1	69.3	75.5	78.9	84.5	89.0	95.2	97.5	100.4	107.6
82.5°	50.4	51.8	53.1	54.8	56.8	62.5	66.9	70.9	73.1	74.2	79.7
85°	29.3	29.8	30.4	31.0	31.6	31.6	33.8	36.6	40.6	40.6	42.2
87.5°	14.3	14.5	14.2	13.5	13.9	13.6	13.7	13.2	14.1	15.0	15.9
90°	22.1	20.9	19.2	17.4	15.8	14.1	12.1	9.8	7.5	5.1	2.9
92.5°	21.4	20.1	18.4	16.7	15.0	13.4	12.5	12.3	12.2	12.1	11.9
95°	22.1	20.9	20.6	20.4	20.2	20.0	23.5	30.7	37.7	44.9	52.1
97.5°	25.1	25.0	48.5	72.0	95.5	119.0	128.5	124.0	119.6	115.1	110.6
100°	38.1	41.7	70.8	99.8	128.8	157.9	170.6	166.7	163.0	159.1	155.4
102.5°	162.2	200.8	204.6	208.4	212.2	216.0	216.5	213.7	210.9	208.1	205.4
105°	297.5	295.5	294.5	293.4	292.4	291.4	290.2	288.9	287.6	286.4	285.1
107.5°	369.4	368.5	367.0	365.7	364.2	362.8	361.7	361.1	360.5	359.9	359.2
110°	418.2	417.8	416.5	415.2	414.0	412.7	411.8	411.2	410.5	409.9	409.3



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	465.5	465.5	465.0	464.3	463.7	463.2	462.3	461.1	460.0	458.9	457.8
115°	534.8	534.3	534.5	534.8	534.9	535.2	534.9	534.3	533.7	533.0	532.4
117.5°	605.4	605.5	605.1	604.6	604.1	603.6	603.0	602.2	601.4	600.5	599.7
120°	648.4	648.0	648.2	648.4	648.7	648.8	648.5	647.7	646.9	646.0	645.1
122.5°	691.5	691.2	690.9	690.6	690.3	690.0	689.6	689.1	688.6	688.1	687.5
125°	750.9	750.3	750.7	751.1	751.5	752.0	751.8	750.9	750.1	749.3	748.4
127.5°	811.1	811.3	810.3	809.3	808.4	807.4	806.8	806.7	806.4	806.2	806.0
130°	847.1	846.9	846.3	845.6	845.1	844.4	844.0	843.8	843.6	843.3	843.1
132.5°	882.7	882.6	881.7	880.9	880.1	879.4	878.7	878.4	878.0	877.6	877.3
135°	931.6	931.2	930.4	929.5	928.7	927.9	927.6	927.7	928.0	928.2	928.4
137.5°	978.7	978.2	977.3	976.4	975.4	974.5	974.0	974.0	973.9	973.8	973.7
140°	1007.6	1007.1	1006.6	1006.2	1005.8	1005.3	1004.9	1004.5	1004.0	1003.6	1003.2
142.5°	1034.8	1034.3	1034.0	1033.8	1033.6	1033.3	1032.8	1032.0	1031.3	1030.5	1029.7
145°	1073.6	1073.3	1073.3	1073.3	1073.3	1073.3	1073.0	1072.4	1071.8	1071.1	1070.5
147.5°	1107.4	1107.3	1107.4	1107.7	1107.9	1108.1	1107.6	1106.4	1105.2	1104.1	1102.9
150°	1129.2	1129.2	1129.4	1129.7	1129.8	1130.1	1129.8	1128.9	1128.0	1127.2	1126.4
152.5°	1147.8	1147.5	1147.8	1148.2	1148.6	1148.9	1148.8	1148.1	1147.5	1146.8	1146.1
155°	1172.7	1171.8	1172.5	1173.1	1173.8	1174.4	1174.6	1174.4	1174.2	1173.9	1173.8
157.5°	1194.3	1193.3	1194.0	1194.7	1195.4	1196.1	1196.5	1196.7	1196.8	1196.9	1197.0
160°	1208.2	1206.9	1207.1	1207.3	1207.5	1207.8	1208.2	1208.8	1209.4	1210.1	1210.7
162.5°	1219.5	1218.3	1218.5	1218.7	1218.9	1219.1	1219.6	1220.4	1221.2	1222.1	1222.8
165°	1235.1	1233.5	1233.5	1233.5	1233.5	1233.5	1234.0	1235.0	1236.1	1237.1	1238.2
167.5°	1246.7	1244.8	1245.0	1245.0	1245.2	1245.3	1245.9	1247.0	1248.1	1249.2	1250.3
170°	1254.1	1252.4	1252.1	1252.0	1251.7	1251.6	1252.1	1253.4	1254.6	1255.9	1257.1
172.5°	1258.6	1256.9	1256.7	1256.5	1256.3	1256.1	1256.6	1257.8	1259.1	1260.4	1261.7
175°	1263.7	1261.8	1261.7	1261.4	1261.2	1261.0	1261.5	1262.8	1264.0	1265.3	1266.6
177.5°	1266.4	1265.1	1264.8	1264.4	1264.0	1263.7	1264.1	1265.3	1266.5	1267.7	1268.9
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1407.5	1411.5	1416.0	1424.6	1431.8	1435.0	1441.3	1445.8	1444.5	1450.7	1461.6
5°	1413.0	1428.2	1445.7	1463.7	1484.0	1500.9	1514.4	1528.0	1538.7	1551.7	1570.8
7.5°	1412.1	1439.2	1468.6	1500.9	1534.1	1562.9	1589.5	1616.6	1640.5	1666.9	1701.2
10°	1408.5	1444.5	1481.2	1523.5	1565.7	1605.7	1641.8	1675.6	1707.8	1742.1	1785.6
12.5°	1404.4	1445.9	1490.2	1541.1	1593.7	1641.8	1684.2	1732.9	1773.1	1817.5	1867.6
15°	1386.5	1442.3	1502.6	1568.6	1631.7	1696.5	1754.5	1814.3	1870.1	1923.0	1986.2
17.5°	1366.0	1430.4	1501.5	1579.4	1655.2	1734.1	1802.9	1878.2	1935.3	2006.4	2065.0
20°	1349.3	1418.6	1494.7	1582.1	1668.3	1755.7	1831.7	1908.5	1972.7	2044.3	2118.6
22.5°	1329.0	1405.1	1487.5	1578.0	1668.3	1763.8	1848.0	1924.2	2003.8	2084.4	2161.0
25°	1296.3	1375.2	1462.6	1561.8	1665.5	1763.0	1853.2	1947.8	2033.5	2120.9	2189.6
27.5°	1256.2	1339.0	1431.2	1533.5	1639.9	1739.8	1846.0	1946.9	2033.1	2117.2	2177.2
30°	1224.2	1311.6	1400.0	1503.7	1614.2	1721.3	1835.2	1936.0	2026.8	2102.3	2136.1
32.5°	1191.2	1274.1	1365.3	1470.4	1583.6	1698.8	1811.7	1914.8	1998.8	2044.1	2045.0
35°	1134.0	1211.8	1306.4	1409.7	1525.8	1650.8	1765.3	1866.7	1918.0	1921.9	1866.7
37.5°	1071.5	1142.9	1232.3	1335.5	1462.7	1587.1	1704.1	1771.6	1788.8	1731.5	1629.3
40°	1027.0	1092.8	1179.1	1285.1	1411.3	1539.8	1646.3	1695.9	1677.9	1584.9	1471.0
42.5°	980.0	1041.5	1124.5	1229.1	1355.8	1485.7	1576.5	1603.0	1555.3	1447.8	1314.6
45°	903.5	959.9	1042.1	1147.5	1269.3	1391.0	1459.8	1446.3	1366.8	1239.4	1090.1
47.5°	823.8	878.2	952.3	1049.8	1174.4	1279.5	1326.1	1285.3	1172.2	1032.1	910.6
50°	771.0	826.8	895.0	988.1	1101.9	1203.3	1233.2	1171.2	1045.5	910.8	799.2
52.5°	719.2	766.9	833.7	923.6	1032.4	1118.1	1134.0	1062.5	932.8	812.0	713.1
55°	640.3	683.7	740.0	824.6	918.7	991.4	982.9	891.1	773.3	670.2	592.4
57.5°	563.9	596.6	648.7	728.0	810.6	859.4	828.5	750.2	640.4	556.0	490.3
60°	513.5	543.9	592.4	661.7	734.4	762.0	736.1	651.0	564.2	487.0	431.7
62.5°	465.7	492.5	534.2	598.6	657.3	673.6	645.9	571.6	493.4	427.5	381.7
65°	396.2	421.0	456.6	502.2	542.7	550.7	532.6	456.6	397.4	342.1	310.5
67.5°	333.2	349.4	377.2	416.6	438.1	442.8	408.0	360.1	307.9	274.0	250.2
70°	290.8	302.1	328.0	349.4	366.9	367.5	335.3	297.0	257.0	229.4	211.9
72.5°	249.8	260.7	280.2	294.9	308.3	303.9	274.5	244.3	211.9	191.1	178.1
75°	192.7	202.4	212.5	219.2	219.2	213.6	192.2	169.7	151.1	138.7	134.7
77.5°	140.1	148.0	151.4	150.3	148.4	139.6	126.0	111.3	104.6	98.7	95.8
80°	109.9	113.3	114.4	111.6	108.2	98.1	89.0	82.8	76.6	74.4	73.3
82.5°	81.5	84.5	81.5	82.3	74.8	66.5	61.6	59.4	56.8	55.9	54.8
85°	43.4	42.8	41.7	38.9	33.8	32.7	32.1	31.6	30.4	31.0	29.8
87.5°	15.9	15.0	13.7	13.7	14.1	13.5	14.3	14.7	15.0	14.8	16.0
90°	5.1	7.5	9.8	12.1	14.1	15.8	17.4	19.2	20.9	22.1	23.4
92.5°	12.1	12.2	12.3	12.5	13.4	15.0	16.7	18.4	20.1	21.4	22.6
95°	44.9	37.7	30.7	23.5	20.0	20.2	20.4	20.6	20.9	22.1	23.4
97.5°	115.1	119.6	124.0	128.5	119.0	95.5	72.0	48.5	25.0	25.1	25.3
100°	159.1	163.0	166.7	170.6	157.9	128.8	99.8	70.8	41.7	38.1	34.5
102.5°	208.1	210.9	213.7	216.5	216.0	212.2	208.4	204.6	200.8	162.2	123.6
105°	286.4	287.6	288.9	290.2	291.4	292.4	293.4	294.5	295.5	297.5	299.4
107.5°	359.9	360.5	361.1	361.7	362.8	364.2	365.7	367.0	368.5	369.4	370.4
110°	409.9	410.5	411.2	411.8	412.7	414.0	415.2	416.5	417.8	418.2	418.7





TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	458.9	460.0	461.1	462.3	463.2	463.7	464.3	465.0	465.5	465.5	465.4
115°	533.0	533.7	534.3	534.9	535.2	534.9	534.8	534.5	534.3	534.8	535.2
117.5°	600.5	601.4	602.2	603.0	603.6	604.1	604.6	605.1	605.5	605.4	605.4
120°	646.0	646.9	647.7	648.5	648.8	648.7	648.4	648.2	648.0	648.4	648.8
122.5°	688.1	688.6	689.1	689.6	690.0	690.3	690.6	690.9	691.2	691.5	691.7
125°	749.3	750.1	750.9	751.8	752.0	751.5	751.1	750.7	750.3	750.9	751.5
127.5°	806.2	806.4	806.7	806.8	807.4	808.4	809.3	810.3	811.3	811.1	811.1
130°	843.3	843.6	843.8	844.0	844.4	845.1	845.6	846.3	846.9	847.1	847.3
132.5°	877.6	878.0	878.4	878.7	879.4	880.1	880.9	881.7	882.6	882.7	883.0
135°	928.2	928.0	927.7	927.6	927.9	928.7	929.5	930.4	931.2	931.6	932.1
137.5°	973.8	973.9	974.0	974.0	974.5	975.4	976.4	977.3	978.2	978.7	979.2
140°	1003.6	1004.0	1004.5	1004.9	1005.3	1005.8	1006.2	1006.6	1007.1	1007.6	1008.3
142.5°	1030.5	1031.3	1032.0	1032.8	1033.3	1033.6	1033.8	1034.0	1034.3	1034.8	1035.3
145°	1071.1	1071.8	1072.4	1073.0	1073.3	1073.3	1073.3	1073.3	1073.3	1073.6	1073.7
147.5°	1104.1	1105.2	1106.4	1107.6	1108.1	1107.9	1107.7	1107.4	1107.3	1107.4	1107.6
150°	1127.2	1128.0	1128.9	1129.8	1130.1	1129.8	1129.7	1129.4	1129.2	1129.2	1129.2
152.5°	1146.8	1147.5	1148.1	1148.8	1148.9	1148.6	1148.2	1147.8	1147.5	1147.8	1148.1
155°	1173.9	1174.2	1174.4	1174.6	1174.4	1173.8	1173.1	1172.5	1171.8	1172.7	1173.5
157.5°	1196.9	1196.8	1196.7	1196.5	1196.1	1195.4	1194.7	1194.0	1193.3	1194.3	1195.5
160°	1210.1	1209.4	1208.8	1208.2	1207.8	1207.5	1207.3	1207.1	1206.9	1208.2	1209.4
162.5°	1222.1	1221.2	1220.4	1219.6	1219.1	1218.9	1218.7	1218.5	1218.3	1219.5	1220.8
165°	1237.1	1236.1	1235.0	1234.0	1233.5	1233.5	1233.5	1233.5	1233.5	1235.1	1236.8
167.5°	1249.2	1248.1	1247.0	1245.9	1245.3	1245.2	1245.0	1245.0	1244.8	1246.7	1248.5
170°	1255.9	1254.6	1253.4	1252.1	1251.6	1251.7	1252.0	1252.1	1252.4	1254.1	1255.7
172.5°	1260.4	1259.1	1257.8	1256.6	1256.1	1256.3	1256.5	1256.7	1256.9	1258.6	1260.3
175°	1265.3	1264.0	1262.8	1261.5	1261.0	1261.2	1261.4	1261.7	1261.8	1263.7	1265.7
177.5°	1267.7	1266.5	1265.3	1264.1	1263.7	1264.0	1264.4	1264.8	1265.1	1266.4	1267.8
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1467.5	1469.3	1470.6	1475.1	1475.5	1479.6	1475.5
5°	1588.9	1596.8	1609.2	1621.5	1622.7	1630.5	1616.5
7.5°	1725.0	1743.3	1754.7	1774.7	1782.7	1787.5	1779.5
10°	1818.8	1835.7	1865.6	1880.2	1894.9	1897.1	1890.4
12.5°	1909.4	1936.3	1959.8	1987.5	1986.9	2006.7	1999.5
15°	2030.2	2057.8	2090.4	2121.5	2132.7	2132.7	2141.8
17.5°	2116.3	2166.9	2200.7	2225.0	2251.7	2256.3	2253.2
20°	2174.5	2229.1	2265.2	2296.8	2314.8	2319.9	2319.9
22.5°	2217.7	2264.2	2299.5	2327.8	2342.8	2348.7	2346.9
25°	2247.7	2287.7	2309.2	2317.6	2321.6	2320.4	2309.7
27.5°	2206.7	2204.9	2191.4	2165.4	2145.9	2134.1	2120.6
30°	2128.3	2098.9	2065.1	2027.9	1980.0	1943.3	1932.1
32.5°	2011.4	1945.6	1888.3	1826.4	1774.8	1738.2	1722.9
35°	1785.6	1681.3	1596.2	1521.8	1467.7	1433.9	1422.6
37.5°	1517.5	1416.6	1311.2	1239.1	1194.2	1160.0	1147.3
40°	1347.0	1237.1	1145.3	1077.7	1031.4	998.2	997.6
42.5°	1191.5	1086.5	1000.1	951.4	901.6	879.5	879.5
45°	975.6	891.6	818.4	780.1	750.2	732.1	727.1
47.5°	807.8	738.3	689.5	659.0	634.6	623.1	615.7
50°	713.5	652.6	613.8	587.3	573.7	559.1	558.0
52.5°	635.1	586.0	555.6	534.1	517.0	508.2	508.4
55°	533.8	494.9	473.4	457.1	443.6	436.8	434.0
57.5°	449.6	420.4	404.9	389.9	384.2	378.9	377.4
60°	397.4	377.6	363.0	351.1	342.7	341.0	340.4
62.5°	354.1	333.5	323.3	314.1	307.9	305.3	304.4
65°	292.0	276.7	267.7	260.4	258.1	254.2	253.6
67.5°	235.4	226.2	220.3	215.2	212.1	211.9	211.9
70°	200.6	195.6	190.5	187.7	186.0	184.8	184.8
72.5°	170.9	167.1	163.0	161.5	161.2	160.0	159.6
75°	130.2	126.3	126.8	124.0	121.7	119.0	117.2
77.5°	92.3	89.5	88.9	88.6	86.7	86.3	87.2
80°	71.6	68.7	68.2	68.7	68.2	66.5	66.5
82.5°	54.5	52.1	51.5	51.2	50.6	51.2	50.3
85°	29.3	28.2	28.2	28.2	29.3	28.8	28.2
87.5°	15.3	15.1	15.7	15.3	15.4	15.1	15.6
90°	24.6	25.9	26.7	27.1	27.6	28.0	28.5
92.5°	23.9	25.1	25.8	25.9	26.0	26.1	26.2
95°	24.6	25.9	26.7	26.8	27.1	27.2	27.5
97.5°	25.4	25.5	25.7	25.9	26.1	26.3	26.5
100°	31.0	27.4	25.7	25.9	26.1	26.3	26.5
102.5°	85.0	46.4	27.1	27.1	27.2	27.2	27.3
105°	301.3	303.1	300.3	292.7	285.1	277.6	270.0
107.5°	371.3	372.2	373.1	373.9	374.7	375.4	376.3
110°	419.1	419.5	420.0	420.6	421.3	421.9	422.5



TEST NUMBER: P332979-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	465.3	465.2	465.5	466.4	467.2	468.0	468.7
115°	535.6	536.0	536.2	536.2	536.2	536.2	536.2
117.5°	605.3	605.2	605.1	605.0	605.0	604.9	604.8
120°	649.2	649.6	649.6	649.2	648.8	648.4	648.0
122.5°	691.9	692.2	692.1	691.7	691.3	690.8	690.4
125°	752.2	752.8	753.3	753.4	753.7	753.9	754.1
127.5°	810.9	810.8	810.7	810.5	810.3	810.2	810.0
130°	847.6	847.7	847.8	847.8	847.8	847.8	847.8
132.5°	883.2	883.4	883.4	883.2	883.1	882.9	882.7
135°	932.5	932.9	933.4	933.8	934.2	934.6	935.0
137.5°	979.6	980.1	980.2	980.2	980.0	979.8	979.7
140°	1008.9	1009.6	1010.0	1010.2	1010.4	1010.6	1010.8
142.5°	1035.7	1036.2	1036.4	1036.5	1036.5	1036.6	1036.6
145°	1074.0	1074.2	1074.5	1074.9	1075.3	1075.8	1076.2
147.5°	1107.7	1107.9	1108.1	1108.3	1108.6	1108.7	1109.0
150°	1129.2	1129.2	1129.4	1129.5	1129.8	1130.0	1130.2
152.5°	1148.4	1148.8	1148.8	1148.8	1148.6	1148.5	1148.3
155°	1174.4	1175.3	1175.3	1174.7	1174.0	1173.5	1172.8
157.5°	1196.5	1197.7	1197.7	1196.5	1195.5	1194.3	1193.3
160°	1210.7	1211.9	1211.9	1210.7	1209.4	1208.2	1206.9
162.5°	1222.1	1223.4	1223.3	1221.8	1220.4	1219.0	1217.5
165°	1238.5	1240.2	1240.1	1238.2	1236.2	1234.4	1232.5
167.5°	1250.3	1252.2	1252.1	1250.0	1247.9	1245.8	1243.7
170°	1257.4	1259.1	1258.9	1256.8	1254.7	1252.6	1250.5
172.5°	1262.0	1263.6	1263.4	1261.1	1258.8	1256.5	1254.3
175°	1267.5	1269.4	1269.1	1266.6	1264.0	1261.5	1259.0
177.5°	1269.1	1270.5	1270.2	1268.1	1266.1	1264.0	1262.1
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6

(END OF REPORT)