

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332981-930

Luminaire Tested: **SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332981-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7045.9 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332981-930
CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	49	48	43
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	43	40	38	36	32
4	75	65	57	51	69	60	54	48	52	47	43	44	40	37	36	33	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	39	59	49	42	37	42	36	32	36	32	28	30	27	24	21
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	27	24	22	19
8	55	43	35	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11293	11293	11293	11293
5°	13100	11327	10011	11327
10°	15497	11278	8936	11278
15°	17901	11173	7678	11173
20°	19930	11030	6943	11030
25°	20574	10889	6446	10889
30°	18011	10718	6147	10718
35°	14020	10464	5966	10464
40°	10513	10175	5868	10175
45°	8301	9710	5817	9710
50°	7008	9173	5649	9173
55°	6108	8583	5346	8583
60°	5496	7971	4732	7971
65°	4844	7310	4069	7310
70°	4362	6626	3673	6626
75°	3656	5873	3132	5873
80°	3092	5002	2934	5002
85°	2612	3909	2612	3909



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.5	1.9
10°-20°	408.9	5.8
20°-30°	639.5	9.1
30°-40°	710.9	10.1
40°-50°	630.7	9.0
50°-60°	491.5	7.0
60°-70°	321.8	4.6
70°-80°	158.2	2.2
80°-90°	41.7	0.6
90°-100°	348.3	4.9
100°-110°	724.9	10.3
110°-120°	649.3	9.2
120°-130°	546.2	7.8
130°-140°	455.4	6.5
140°-150°	347.9	4.9
150°-160°	244.5	3.5
160°-170°	143.8	2.0
170°-180°	46.8	0.7
0°-30°	1183.9	16.8
0°-40°	1894.8	26.9
0°-60°	3017.0	42.8
0°-90°	3538.8	50.2
90°-120°	1722.5	24.4
90°-150°	3071.9	43.6
90°-180°	3507.0	49.8
0°-180°	7045.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1399	1399	1399	1399	1399	
5°	1616	1398	1235	1398	1616	164
15°	2142	1337	919	1337	2142	609
25°	2310	1222	724	1222	2310	1025
35°	1423	1062	605	1062	1423	892
45°	727	850	510	850	727	576
55°	434	610	380	610	434	395
65°	254	383	213	383	254	255
75°	117	188	100	188	117	129
85°	28	42	28	42	28	32
90°	20	1	20	1	20	17
95°	231	31	231	31	231	359
105°	1333	111	1333	111	1333	1318
115°	1280	195	1280	195	1280	1271
125°	1021	272	1021	272	1021	928
135°	913	323	913	323	913	705
145°	746	372	746	372	746	473
155°	624	424	624	424	624	291
165°	545	461	545	461	545	156
175°	491	481	491	481	491	48
180°	482	482	482	482	482	



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1475.5	1479.6	1475.5	1475.1	1470.6	1469.3	1467.5	1461.6	1450.7	1444.5	1445.8
5°	1616.5	1630.5	1622.7	1621.5	1609.2	1596.8	1588.9	1570.8	1551.7	1538.7	1528.0
7.5°	1779.5	1787.5	1782.7	1774.7	1754.7	1743.3	1725.0	1701.2	1666.9	1640.5	1616.6
10°	1890.4	1897.1	1894.9	1880.2	1865.6	1835.7	1818.8	1785.6	1742.1	1707.8	1675.6
12.5°	1999.5	2006.7	1986.9	1987.5	1959.8	1936.3	1909.4	1867.6	1817.5	1773.1	1732.9
15°	2141.8	2132.7	2132.7	2121.5	2090.4	2057.8	2030.2	1986.2	1923.0	1870.1	1814.3
17.5°	2253.2	2256.3	2251.7	2225.0	2200.7	2166.9	2116.3	2065.0	2006.4	1935.3	1878.2
20°	2319.9	2319.9	2314.8	2296.8	2265.2	2229.1	2174.5	2118.6	2044.3	1972.7	1908.5
22.5°	2346.9	2348.7	2342.8	2327.8	2299.5	2264.2	2217.7	2161.0	2084.4	2003.8	1924.2
25°	2309.7	2320.4	2321.6	2317.6	2309.2	2287.7	2247.7	2189.6	2120.9	2033.5	1947.8
27.5°	2120.6	2134.1	2145.9	2165.4	2191.4	2204.9	2206.7	2177.2	2117.2	2033.1	1946.9
30°	1932.1	1943.3	1980.0	2027.9	2065.1	2098.9	2128.3	2136.1	2102.3	2026.8	1936.0
32.5°	1722.9	1738.2	1774.8	1826.4	1888.3	1945.6	2011.4	2045.0	2044.1	1998.8	1914.8
35°	1422.6	1433.9	1467.7	1521.8	1596.2	1681.3	1785.6	1866.7	1921.9	1918.0	1866.7
37.5°	1147.3	1160.0	1194.2	1239.1	1311.2	1416.6	1517.5	1629.3	1731.5	1788.8	1771.6
40°	997.6	998.2	1031.4	1077.7	1145.3	1237.1	1347.0	1471.0	1584.9	1677.9	1695.9
42.5°	879.5	879.5	901.6	951.4	1000.1	1086.5	1191.5	1314.6	1447.8	1555.3	1603.0
45°	727.1	732.1	750.2	780.1	818.4	891.6	975.6	1090.1	1239.4	1366.8	1446.3
47.5°	615.7	623.1	634.6	659.0	689.5	738.3	807.8	910.6	1032.1	1172.2	1285.3
50°	558.0	559.1	573.7	587.3	613.8	652.6	713.5	799.2	910.8	1045.5	1171.2
52.5°	508.4	508.2	517.0	534.1	555.6	586.0	635.1	713.1	812.0	932.8	1062.5
55°	434.0	436.8	443.6	457.1	473.4	494.9	533.8	592.4	670.2	773.3	891.1
57.5°	377.4	378.9	384.2	389.9	404.9	420.4	449.6	490.3	556.0	640.4	750.2
60°	340.4	341.0	342.7	351.1	363.0	377.6	397.4	431.7	487.0	564.2	651.0
62.5°	304.4	305.3	307.9	314.1	323.3	333.5	354.1	381.7	427.5	493.4	571.6
65°	253.6	254.2	258.1	260.4	267.7	276.7	292.0	310.5	342.1	397.4	456.6
67.5°	211.9	211.9	212.1	215.2	220.3	226.2	235.4	250.2	274.0	307.9	360.1
70°	184.8	184.8	186.0	187.7	190.5	195.6	200.6	211.9	229.4	257.0	297.0
72.5°	159.6	160.0	161.2	161.5	163.0	167.1	170.9	178.1	191.1	211.9	244.3
75°	117.2	119.0	121.7	124.0	126.8	126.3	130.2	134.7	138.7	151.1	169.7
77.5°	87.2	86.3	86.7	88.6	88.9	89.5	92.3	95.8	98.7	104.6	111.3
80°	66.5	66.5	68.2	68.7	68.2	68.7	71.6	73.3	74.4	76.6	82.8
82.5°	50.3	51.2	50.6	51.2	51.5	52.1	54.5	54.8	55.9	56.8	59.4
85°	28.2	28.8	29.3	28.2	28.2	28.2	29.3	29.8	31.0	30.4	31.6
87.5°	13.9	13.5	14.1	13.9	14.2	13.7	13.9	14.7	13.6	14.3	13.9
90°	19.9	19.9	20.9	19.9	18.9	18.9	18.0	17.0	16.1	17.0	15.2
92.5°	73.0	73.0	76.1	81.3	92.5	111.5	140.0	186.1	250.3	300.5	263.0
95°	231.1	243.4	260.6	289.9	336.3	428.2	555.1	702.0	793.9	772.1	582.6
97.5°	617.9	637.6	666.0	723.0	791.1	890.0	982.6	1037.2	997.4	813.3	545.3
100°	868.8	876.4	904.7	962.5	1045.0	1115.1	1161.5	1142.6	1004.2	761.7	494.6
102.5°	1087.0	1093.1	1123.0	1164.9	1215.4	1244.6	1231.2	1137.3	947.4	697.2	460.4
105°	1332.9	1338.6	1351.9	1359.5	1357.6	1318.7	1225.0	1061.0	844.1	621.5	431.0
107.5°	1424.3	1421.8	1412.3	1390.7	1343.9	1259.5	1127.4	952.8	760.8	579.0	425.7
110°	1425.8	1417.3	1400.2	1360.4	1293.1	1189.0	1051.6	887.7	719.1	564.7	427.3



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1381.1	1367.3	1343.4	1295.3	1218.9	1114.7	984.9	839.9	695.5	557.8	431.8
115°	1279.9	1272.4	1242.0	1185.2	1110.4	1019.4	908.6	792.0	673.6	554.2	440.5
117.5°	1177.4	1171.5	1140.8	1093.1	1029.2	952.1	865.0	768.5	663.7	553.3	449.8
120°	1119.8	1109.4	1084.8	1043.1	989.0	921.8	846.0	757.9	658.4	553.3	456.6
122.5°	1074.3	1063.9	1043.1	1007.5	961.8	902.9	833.9	748.8	652.4	552.5	463.5
125°	1021.2	1015.6	997.6	970.1	932.2	880.1	814.7	733.3	642.3	551.4	473.7
127.5°	990.2	984.6	969.4	944.9	906.9	857.4	792.2	714.3	628.8	549.3	481.8
130°	972.0	966.3	951.1	927.5	888.7	838.5	774.0	699.2	620.5	548.5	487.9
132.5°	951.5	945.8	931.5	904.7	866.7	816.4	753.6	683.2	612.9	547.8	493.2
135°	913.3	907.6	892.4	865.9	828.0	780.6	722.8	661.3	601.6	546.7	501.2
137.5°	865.9	859.1	846.6	820.4	785.0	742.2	693.5	641.4	591.7	546.4	505.9
140°	831.8	824.2	811.0	790.1	756.9	717.1	674.5	630.0	586.4	545.7	509.7
142.5°	795.4	790.1	778.4	759.0	729.7	695.2	658.6	619.4	581.9	545.7	512.7
145°	745.6	740.9	731.4	715.3	691.6	665.0	636.7	604.5	574.1	543.8	514.5
147.5°	701.4	699.8	692.5	678.7	661.3	640.4	617.7	592.2	567.1	540.4	515.4
150°	676.5	675.5	669.8	657.5	642.3	625.3	606.3	584.6	561.8	538.1	515.4
152.5°	653.7	652.7	649.3	639.3	626.4	612.4	594.9	576.2	555.7	534.3	513.9
155°	624.4	624.4	621.5	613.9	604.5	593.0	578.9	563.7	546.7	528.6	511.6
157.5°	598.6	598.6	596.9	591.2	584.0	574.9	563.0	550.2	537.4	522.8	509.2
160°	582.6	582.6	581.7	576.0	570.3	562.7	552.3	541.9	530.5	518.2	506.9
162.5°	567.4	568.3	567.3	561.6	557.4	550.7	542.5	533.5	524.5	513.6	504.6
165°	544.8	545.7	546.7	542.8	539.1	534.3	527.7	522.0	514.5	506.9	500.2
167.5°	526.8	527.5	527.7	525.2	523.3	520.5	515.2	510.9	505.3	500.0	495.7
170°	515.4	515.4	516.3	515.4	513.5	510.6	506.9	504.0	499.3	495.5	492.6
172.5°	504.0	505.5	506.5	505.5	504.3	502.3	500.0	497.9	494.0	490.9	489.6
175°	490.7	492.6	494.6	492.6	492.6	492.6	490.7	489.8	487.9	486.0	486.0
177.5°	483.0	484.5	486.0	485.3	486.0	485.3	485.3	484.5	483.7	483.0	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1441.3	1435.0	1431.8	1424.6	1416.0	1411.5	1407.5	1401.6	1393.9	1385.8	1380.0
5°	1514.4	1500.9	1484.0	1463.7	1445.7	1428.2	1413.0	1397.7	1380.3	1362.3	1344.3
7.5°	1589.5	1562.9	1534.1	1500.9	1468.6	1439.2	1412.1	1386.2	1356.8	1330.6	1306.7
10°	1641.8	1605.7	1565.7	1523.5	1481.2	1444.5	1408.5	1375.8	1339.7	1307.6	1280.5
12.5°	1684.2	1641.8	1593.7	1541.1	1490.2	1445.9	1404.4	1361.8	1320.8	1286.0	1249.9
15°	1754.5	1696.5	1631.7	1568.6	1502.6	1442.3	1386.5	1336.9	1290.1	1241.1	1206.7
17.5°	1802.9	1734.1	1655.2	1579.4	1501.5	1430.4	1366.0	1306.9	1253.0	1202.9	1162.0
20°	1831.7	1755.7	1668.3	1582.1	1494.7	1418.6	1349.3	1283.9	1228.2	1174.0	1131.7
22.5°	1848.0	1763.8	1668.3	1578.0	1487.5	1405.1	1329.0	1260.9	1200.2	1146.1	1099.3
25°	1853.2	1763.0	1665.5	1561.8	1462.6	1375.2	1296.3	1222.5	1154.9	1100.7	1051.2
27.5°	1846.0	1739.8	1639.9	1533.5	1431.2	1339.0	1256.2	1178.7	1110.9	1052.9	1002.0
30°	1835.2	1721.3	1614.2	1503.7	1400.0	1311.6	1224.2	1149.8	1079.3	1019.0	967.8
32.5°	1811.7	1698.8	1583.6	1470.4	1365.3	1274.1	1191.2	1116.4	1047.3	985.7	931.2
35°	1765.3	1650.8	1525.8	1409.7	1306.4	1211.8	1134.0	1061.8	995.9	930.0	872.5
37.5°	1704.1	1587.1	1462.7	1335.5	1232.3	1142.9	1071.5	1003.8	939.5	879.2	815.5
40°	1646.3	1539.8	1411.3	1285.1	1179.1	1092.8	1027.0	965.5	900.7	840.9	777.2
42.5°	1576.5	1485.7	1355.8	1229.1	1124.5	1041.5	980.0	919.9	861.0	803.1	736.6
45°	1459.8	1391.0	1269.3	1147.5	1042.1	959.9	903.5	850.5	798.7	743.4	680.9
47.5°	1326.1	1279.5	1174.4	1049.8	952.3	878.2	823.8	780.5	736.6	681.4	626.6
50°	1233.2	1203.3	1101.9	988.1	895.0	826.8	771.0	730.4	693.8	640.8	591.8
52.5°	1134.0	1118.1	1032.4	923.6	833.7	766.9	719.2	682.7	645.6	601.6	555.7
55°	982.9	991.4	918.7	824.6	740.0	683.7	640.3	609.8	578.3	541.1	505.6
57.5°	828.5	859.4	810.6	728.0	648.7	596.6	563.9	538.3	511.8	481.0	450.7
60°	736.1	762.0	734.4	661.7	592.4	543.9	513.5	493.7	467.2	439.0	416.0
62.5°	645.9	673.6	657.3	598.6	534.2	492.5	465.7	447.3	427.5	403.0	379.0
65°	532.6	550.7	542.7	502.2	456.6	421.0	396.2	382.7	364.7	346.7	325.2
67.5°	408.0	442.8	438.1	416.6	377.2	349.4	333.2	321.2	304.8	291.4	276.9
70°	335.3	367.5	366.9	349.4	328.0	302.1	290.8	280.7	266.0	253.1	241.2
72.5°	274.5	303.9	308.3	294.9	280.2	260.7	249.8	242.8	228.6	219.7	210.1
75°	192.2	213.6	219.2	219.2	212.5	202.4	192.7	188.3	178.1	170.2	164.6
77.5°	126.0	139.6	148.4	150.3	151.4	148.0	140.1	137.0	129.1	126.4	121.0
80°	89.0	98.1	108.2	111.6	114.4	113.3	109.9	107.6	100.4	97.5	95.2
82.5°	61.6	66.5	74.8	82.3	81.5	84.5	81.5	79.7	74.2	73.1	70.9
85°	32.1	32.7	33.8	38.9	41.7	42.8	43.4	42.2	40.6	40.6	36.6
87.5°	13.5	13.0	12.8	12.8	13.0	14.7	15.4	15.5	14.5	13.8	12.6
90°	13.3	13.3	7.6	7.6	6.6	5.7	2.9	1.0	2.9	5.7	6.6
92.5°	191.4	117.9	69.7	50.1	36.2	24.6	15.7	10.8	15.7	24.6	36.2
95°	356.2	200.8	118.5	78.6	55.9	43.6	34.1	31.2	34.1	43.6	55.9
97.5°	320.2	191.9	128.5	95.1	75.6	64.2	56.1	56.1	56.1	64.2	75.6
100°	301.3	194.2	138.4	108.0	90.0	78.6	72.0	72.0	72.0	78.6	90.0
102.5°	296.0	201.8	151.2	122.4	105.2	94.6	88.7	87.2	88.7	94.6	105.2
105°	298.4	219.8	174.3	146.8	129.8	118.5	113.7	110.9	113.7	118.5	129.8
107.5°	312.4	240.8	199.2	172.0	155.7	143.7	138.8	137.0	138.8	143.7	155.7
110°	323.0	256.7	215.1	189.5	172.4	161.0	156.3	154.4	156.3	161.0	172.4



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.4	271.9	231.7	206.2	189.1	178.5	173.0	171.1	173.0	178.5	189.1
115°	352.5	295.5	257.7	232.1	214.1	204.6	198.0	195.2	198.0	204.6	214.1
117.5°	370.8	318.5	282.5	256.0	239.1	228.7	222.8	220.1	222.8	228.7	239.1
120°	383.7	334.4	298.4	271.9	255.8	245.4	238.7	236.8	238.7	245.4	255.8
122.5°	395.8	349.6	313.6	287.8	270.2	260.6	253.9	252.0	253.9	260.6	270.2
125°	414.0	370.4	336.3	309.8	291.8	281.4	275.7	271.9	275.7	281.4	291.8
127.5°	429.7	389.7	356.8	330.0	311.3	299.4	292.5	289.5	292.5	299.4	311.3
130°	439.6	402.7	370.4	342.9	325.0	310.7	303.1	299.4	303.1	310.7	325.0
132.5°	449.5	413.3	381.1	355.1	335.6	322.1	312.3	309.2	312.3	322.1	335.6
135°	462.4	428.2	397.0	372.3	352.5	336.3	326.9	323.0	326.9	336.3	352.5
137.5°	471.4	439.6	410.4	386.9	366.2	350.9	340.5	336.9	340.5	350.9	366.2
140°	477.4	447.2	418.7	396.0	376.1	360.0	349.6	346.7	349.6	360.0	376.1
142.5°	482.0	454.0	426.3	404.3	385.2	369.8	360.2	357.3	360.2	369.8	385.2
145°	487.0	461.4	436.8	415.9	397.9	384.7	375.2	372.3	375.2	384.7	397.9
147.5°	491.3	469.0	445.8	427.1	412.1	398.4	390.1	389.1	390.1	398.4	412.1
150°	493.6	472.7	451.9	433.9	419.7	408.3	400.7	399.8	400.7	408.3	419.7
152.5°	495.1	475.8	457.2	440.8	428.0	417.4	409.9	409.6	409.9	417.4	428.0
155°	496.4	480.3	464.2	450.0	439.6	430.1	424.4	423.5	424.4	430.1	439.6
157.5°	496.4	483.6	469.9	458.7	449.6	442.2	436.9	436.9	436.9	442.2	449.6
160°	496.4	485.0	473.7	463.3	455.7	449.1	445.2	445.2	445.2	449.1	455.7
162.5°	496.4	486.6	476.0	467.8	461.0	455.1	452.1	452.8	452.1	455.1	461.0
165°	494.6	487.0	478.4	472.7	468.0	463.3	461.4	461.4	461.4	463.3	468.0
167.5°	492.3	486.7	480.5	476.1	473.5	469.9	469.0	469.9	469.0	469.9	473.5
170°	490.7	486.0	481.3	478.4	476.5	473.7	472.7	473.7	472.7	473.7	476.5
172.5°	489.3	485.3	482.0	480.0	478.8	476.7	476.5	477.4	476.5	476.7	478.8
175°	487.0	484.1	482.2	482.2	481.3	480.3	480.3	481.3	480.3	480.3	481.3
177.5°	484.5	483.0	482.2	482.2	482.2	481.4	482.2	483.0	482.2	481.4	482.2
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1373.6	1369.1	1363.3	1356.5	1348.4	1341.2	1338.1	1340.8	1342.1	1338.5	1338.1
5°	1331.9	1317.8	1306.4	1289.6	1276.0	1264.8	1256.9	1253.5	1254.6	1245.6	1243.3
7.5°	1284.8	1268.1	1249.7	1229.6	1210.9	1194.3	1185.6	1180.9	1171.3	1167.3	1160.4
10°	1254.6	1232.1	1214.1	1190.3	1169.0	1149.2	1139.6	1131.7	1122.2	1117.7	1108.1
12.5°	1223.5	1197.3	1177.5	1152.9	1131.1	1107.3	1098.1	1083.5	1068.5	1059.1	1046.8
15°	1179.7	1148.1	1123.9	1094.5	1068.6	1041.5	1017.3	990.3	980.2	958.7	946.3
17.5°	1128.4	1096.3	1066.3	1027.0	987.0	953.4	927.6	901.6	886.1	872.5	866.2
20°	1094.5	1065.3	1023.5	977.9	933.4	896.2	875.3	858.4	841.5	831.9	825.2
22.5°	1062.5	1025.1	976.6	927.4	882.9	853.8	836.1	818.7	804.9	795.8	786.8
25°	1008.9	959.9	908.6	852.2	821.7	796.4	777.2	763.1	754.7	742.8	738.3
27.5°	953.7	894.4	837.8	799.9	768.2	745.0	728.3	717.7	707.0	699.4	693.6
30°	911.3	851.1	800.4	764.3	732.1	713.0	699.4	687.1	678.6	672.4	667.9
32.5°	869.4	809.1	766.5	727.7	702.4	683.7	669.3	660.0	653.4	645.3	642.6
35°	808.8	755.2	718.0	683.1	657.2	640.3	629.0	619.4	613.8	611.6	609.8
37.5°	750.5	706.7	666.7	638.1	614.9	601.6	588.3	583.6	579.8	575.7	577.5
40°	713.5	672.4	636.9	606.4	587.8	573.2	565.3	559.7	556.3	556.3	556.3
42.5°	681.5	641.3	606.7	579.4	560.8	548.4	539.6	534.8	533.8	533.3	536.0
45°	631.9	594.6	559.7	537.1	521.4	508.9	503.9	499.9	499.9	502.2	502.7
47.5°	582.5	547.7	519.7	494.4	480.0	472.2	467.8	465.8	466.0	468.2	470.8
50°	552.4	518.0	490.3	467.8	454.3	446.9	443.0	441.9	443.0	443.0	446.9
52.5°	519.4	488.7	461.5	442.5	427.2	420.4	418.2	416.6	417.3	419.1	420.8
55°	471.2	443.6	417.7	399.6	388.3	383.8	378.8	379.3	378.2	379.3	379.3
57.5°	422.8	398.0	373.9	359.6	349.7	343.2	337.6	339.2	337.5	337.3	336.4
60°	391.8	364.7	345.5	332.6	321.2	315.6	310.5	311.7	310.0	308.8	306.6
62.5°	357.9	335.3	317.1	304.6	295.5	289.0	284.0	282.8	278.9	275.1	270.1
65°	308.8	290.2	273.9	262.1	253.6	248.6	244.6	241.2	232.8	223.7	219.2
67.5°	261.2	247.8	232.5	222.5	215.6	209.0	201.5	195.7	187.8	182.9	180.0
70°	230.5	217.5	204.6	195.0	187.7	181.5	173.0	169.1	163.5	161.2	158.4
72.5°	201.2	189.1	177.1	168.4	160.6	155.8	149.1	145.2	142.7	141.8	139.0
75°	156.7	147.1	138.1	130.2	124.0	120.6	117.8	115.0	113.8	108.8	106.0
77.5°	114.3	108.0	102.3	96.7	92.3	90.1	84.6	81.4	79.5	77.1	76.6
80°	89.0	84.5	78.9	75.5	69.3	67.1	64.8	64.2	63.7	63.1	62.5
82.5°	66.9	62.5	56.8	54.8	53.1	51.8	50.4	49.8	49.2	49.6	49.5
85°	33.8	31.6	31.6	31.0	30.4	29.8	29.3	29.3	28.8	29.3	28.8
87.5°	12.8	12.3	13.5	12.6	13.4	13.8	13.1	13.4	13.9	13.3	13.3
90°	7.6	7.6	13.3	13.3	15.2	17.0	16.1	17.0	18.0	18.9	18.9
92.5°	50.1	69.7	117.9	191.4	263.0	300.5	250.3	186.1	140.0	111.5	92.5
95°	78.6	118.5	200.8	356.2	582.6	772.1	793.9	702.0	555.1	428.2	336.3
97.5°	95.1	128.5	191.9	320.2	545.3	813.3	997.4	1037.2	982.6	890.0	791.1
100°	108.0	138.4	194.2	301.3	494.6	761.7	1004.2	1142.6	1161.5	1115.1	1045.0
102.5°	122.4	151.2	201.8	296.0	460.4	697.2	947.4	1137.3	1231.2	1244.6	1215.4
105°	146.8	174.3	219.8	298.4	431.0	621.5	844.1	1061.0	1225.0	1318.7	1357.6
107.5°	172.0	199.2	240.8	312.4	425.7	579.0	760.8	952.8	1127.4	1259.5	1343.9
110°	189.5	215.1	256.7	323.0	427.3	564.7	719.1	887.7	1051.6	1189.0	1293.1



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	206.2	231.7	271.9	334.4	431.8	557.8	695.5	839.9	984.9	1114.7	1218.9
115°	232.1	257.7	295.5	352.5	440.5	554.2	673.6	792.0	908.6	1019.4	1110.4
117.5°	256.0	282.5	318.5	370.8	449.8	553.3	663.7	768.5	865.0	952.1	1029.2
120°	271.9	298.4	334.4	383.7	456.6	553.3	658.4	757.9	846.0	921.8	989.0
122.5°	287.8	313.6	349.6	395.8	463.5	552.5	652.4	748.8	833.9	902.9	961.8
125°	309.8	336.3	370.4	414.0	473.7	551.4	642.3	733.3	814.7	880.1	932.2
127.5°	330.0	356.8	389.7	429.7	481.8	549.3	628.8	714.3	792.2	857.4	906.9
130°	342.9	370.4	402.7	439.6	487.9	548.5	620.5	699.2	774.0	838.5	888.7
132.5°	355.1	381.1	413.3	449.5	493.2	547.8	612.9	683.2	753.6	816.4	866.7
135°	372.3	397.0	428.2	462.4	501.2	546.7	601.6	661.3	722.8	780.6	828.0
137.5°	386.9	410.4	439.6	471.4	505.9	546.4	591.7	641.4	693.5	742.2	785.0
140°	396.0	418.7	447.2	477.4	509.7	545.7	586.4	630.0	674.5	717.1	756.9
142.5°	404.3	426.3	454.0	482.0	512.7	545.7	581.9	619.4	658.6	695.2	729.7
145°	415.9	436.8	461.4	487.0	514.5	543.8	574.1	604.5	636.7	665.0	691.6
147.5°	427.1	445.8	469.0	491.3	515.4	540.4	567.1	592.2	617.7	640.4	661.3
150°	433.9	451.9	472.7	493.6	515.4	538.1	561.8	584.6	606.3	625.3	642.3
152.5°	440.8	457.2	475.8	495.1	513.9	534.3	555.7	576.2	594.9	612.4	626.4
155°	450.0	464.2	480.3	496.4	511.6	528.6	546.7	563.7	578.9	593.0	604.5
157.5°	458.7	469.9	483.6	496.4	509.2	522.8	537.4	550.2	563.0	574.9	584.0
160°	463.3	473.7	485.0	496.4	506.9	518.2	530.5	541.9	552.3	562.7	570.3
162.5°	467.8	476.0	486.6	496.4	504.6	513.6	524.5	533.5	542.5	550.7	557.4
165°	472.7	478.4	487.0	494.6	500.2	506.9	514.5	522.0	527.7	534.3	539.1
167.5°	476.1	480.5	486.7	492.3	495.7	500.0	505.3	510.9	515.2	520.5	523.3
170°	478.4	481.3	486.0	490.7	492.6	495.5	499.3	504.0	506.9	510.6	513.5
172.5°	480.0	482.0	485.3	489.3	489.6	490.9	494.0	497.9	500.0	502.3	504.3
175°	482.2	482.2	484.1	487.0	486.0	486.0	487.9	489.8	490.7	492.6	492.6
177.5°	482.2	482.2	483.0	484.5	483.0	483.0	483.7	484.5	485.3	485.3	486.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1335.3	1336.2	1333.1	1332.2	1333.1	1336.2	1335.3	1338.1	1338.5	1342.1	1340.8
5°	1238.8	1237.7	1234.9	1235.4	1234.9	1237.7	1238.8	1243.3	1245.6	1254.6	1253.5
7.5°	1156.3	1151.9	1153.2	1148.7	1153.2	1151.9	1156.3	1160.4	1167.3	1171.3	1180.9
10°	1105.8	1099.6	1094.5	1090.1	1094.5	1099.6	1105.8	1108.1	1117.7	1122.2	1131.7
12.5°	1036.8	1031.5	1024.7	1026.1	1024.7	1031.5	1036.8	1046.8	1059.1	1068.5	1083.5
15°	939.0	930.5	917.0	918.7	917.0	930.5	939.0	946.3	958.7	980.2	990.3
17.5°	856.1	856.2	850.0	851.5	850.0	856.2	856.1	866.2	872.5	886.1	901.6
20°	813.3	809.3	809.9	808.2	809.9	809.3	813.3	825.2	831.9	841.5	858.4
22.5°	783.6	778.7	774.8	771.3	774.8	778.7	783.6	786.8	795.8	804.9	818.7
25°	733.3	729.9	724.8	723.7	724.8	729.9	733.3	738.3	742.8	754.7	763.1
27.5°	689.1	688.4	686.4	683.8	686.4	688.4	689.1	693.6	699.4	707.0	717.7
30°	663.4	662.3	661.1	659.4	661.1	662.3	663.4	667.9	672.4	678.6	687.1
32.5°	640.4	639.7	638.5	638.7	638.5	639.7	640.4	642.6	645.3	653.4	660.0
35°	607.6	607.0	605.9	605.4	605.9	607.0	607.6	609.8	611.6	613.8	619.4
37.5°	576.9	578.4	577.7	577.6	577.7	578.4	576.9	577.5	575.7	579.8	583.6
40°	555.7	556.3	557.4	556.8	557.4	556.3	555.7	556.3	556.3	556.3	559.7
42.5°	538.2	538.3	539.8	537.9	539.8	538.3	538.2	536.0	533.3	533.8	534.8
45°	506.7	510.1	509.5	509.5	509.5	510.1	506.7	502.7	502.2	499.9	499.9
47.5°	472.3	475.2	476.1	475.9	476.1	475.2	472.3	470.8	468.2	466.0	465.8
50°	449.8	448.7	450.4	449.8	450.4	448.7	449.8	446.9	443.0	443.0	441.9
52.5°	422.2	422.5	422.4	421.8	422.4	422.5	422.2	420.8	419.1	417.3	416.6
55°	379.8	380.4	379.3	379.8	379.3	380.4	379.8	379.3	379.3	378.2	379.3
57.5°	333.9	331.2	332.3	330.9	332.3	331.2	333.9	336.4	337.3	337.5	339.2
60°	301.0	296.4	295.3	293.1	295.3	296.4	301.0	306.6	308.8	310.0	311.7
62.5°	264.0	260.8	257.0	258.8	257.0	260.8	264.0	270.1	275.1	278.9	282.8
65°	214.7	212.5	210.8	213.0	210.8	212.5	214.7	219.2	223.7	232.8	241.2
67.5°	177.7	176.5	176.5	175.4	176.5	176.5	177.7	180.0	182.9	187.8	195.7
70°	158.4	156.7	156.7	155.6	156.7	156.7	158.4	158.4	161.2	163.5	169.1
72.5°	138.5	136.8	137.3	136.6	137.3	136.8	138.5	139.0	141.8	142.7	145.2
75°	102.6	99.8	99.8	100.4	99.8	99.8	102.6	106.0	108.8	113.8	115.0
77.5°	76.6	76.0	76.8	75.7	76.8	76.0	76.6	76.6	77.1	79.5	81.4
80°	62.5	62.0	61.5	63.1	61.5	62.0	62.5	62.5	63.1	63.7	64.2
82.5°	48.6	48.5	48.3	50.5	48.3	48.5	48.6	49.5	49.6	49.2	49.8
85°	29.3	28.2	29.3	28.2	29.3	28.2	29.3	28.8	29.3	28.8	29.3
87.5°	14.3	14.1	13.5	13.9	13.5	14.1	14.3	13.3	13.3	13.9	13.4
90°	19.9	20.9	19.9	19.9	19.9	20.9	19.9	18.9	18.9	18.0	17.0
92.5°	81.3	76.1	73.0	73.0	73.0	76.1	81.3	92.5	111.5	140.0	186.1
95°	289.9	260.6	243.4	231.1	243.4	260.6	289.9	336.3	428.2	555.1	702.0
97.5°	723.0	666.0	637.6	617.9	637.6	666.0	723.0	791.1	890.0	982.6	1037.2
100°	962.5	904.7	876.4	868.8	876.4	904.7	962.5	1045.0	1115.1	1161.5	1142.6
102.5°	1164.9	1123.0	1093.1	1087.0	1093.1	1123.0	1164.9	1215.4	1244.6	1231.2	1137.3
105°	1359.5	1351.9	1338.6	1332.9	1338.6	1351.9	1359.5	1357.6	1318.7	1225.0	1061.0
107.5°	1390.7	1412.3	1421.8	1424.3	1421.8	1412.3	1390.7	1343.9	1259.5	1127.4	952.8
110°	1360.4	1400.2	1417.3	1425.8	1417.3	1400.2	1360.4	1293.1	1189.0	1051.6	887.7



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1295.3	1343.4	1367.3	1381.1	1367.3	1343.4	1295.3	1218.9	1114.7	984.9	839.9
115°	1185.2	1242.0	1272.4	1279.9	1272.4	1242.0	1185.2	1110.4	1019.4	908.6	792.0
117.5°	1093.1	1140.8	1171.5	1177.4	1171.5	1140.8	1093.1	1029.2	952.1	865.0	768.5
120°	1043.1	1084.8	1109.4	1119.8	1109.4	1084.8	1043.1	989.0	921.8	846.0	757.9
122.5°	1007.5	1043.1	1063.9	1074.3	1063.9	1043.1	1007.5	961.8	902.9	833.9	748.8
125°	970.1	997.6	1015.6	1021.2	1015.6	997.6	970.1	932.2	880.1	814.7	733.3
127.5°	944.9	969.4	984.6	990.2	984.6	969.4	944.9	906.9	857.4	792.2	714.3
130°	927.5	951.1	966.3	972.0	966.3	951.1	927.5	888.7	838.5	774.0	699.2
132.5°	904.7	931.5	945.8	951.5	945.8	931.5	904.7	866.7	816.4	753.6	683.2
135°	865.9	892.4	907.6	913.3	907.6	892.4	865.9	828.0	780.6	722.8	661.3
137.5°	820.4	846.6	859.1	865.9	859.1	846.6	820.4	785.0	742.2	693.5	641.4
140°	790.1	811.0	824.2	831.8	824.2	811.0	790.1	756.9	717.1	674.5	630.0
142.5°	759.0	778.4	790.1	795.4	790.1	778.4	759.0	729.7	695.2	658.6	619.4
145°	715.3	731.4	740.9	745.6	740.9	731.4	715.3	691.6	665.0	636.7	604.5
147.5°	678.7	692.5	699.8	701.4	699.8	692.5	678.7	661.3	640.4	617.7	592.2
150°	657.5	669.8	675.5	676.5	675.5	669.8	657.5	642.3	625.3	606.3	584.6
152.5°	639.3	649.3	652.7	653.7	652.7	649.3	639.3	626.4	612.4	594.9	576.2
155°	613.9	621.5	624.4	624.4	624.4	621.5	613.9	604.5	593.0	578.9	563.7
157.5°	591.2	596.9	598.6	598.6	598.6	596.9	591.2	584.0	574.9	563.0	550.2
160°	576.0	581.7	582.6	582.6	582.6	581.7	576.0	570.3	562.7	552.3	541.9
162.5°	561.6	567.3	568.3	567.4	568.3	567.3	561.6	557.4	550.7	542.5	533.5
165°	542.8	546.7	545.7	544.8	545.7	546.7	542.8	539.1	534.3	527.7	522.0
167.5°	525.2	527.7	527.5	526.8	527.5	527.7	525.2	523.3	520.5	515.2	510.9
170°	515.4	516.3	515.4	515.4	515.4	516.3	515.4	513.5	510.6	506.9	504.0
172.5°	505.5	506.5	505.5	504.0	505.5	506.5	505.5	504.3	502.3	500.0	497.9
175°	492.6	494.6	492.6	490.7	492.6	494.6	492.6	492.6	492.6	490.7	489.8
177.5°	485.3	486.0	484.5	483.0	484.5	486.0	485.3	486.0	485.3	485.3	484.5
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1338.1	1341.2	1348.4	1356.5	1363.3	1369.1	1373.6	1380.0	1385.8	1393.9	1401.6
5°	1256.9	1264.8	1276.0	1289.6	1306.4	1317.8	1331.9	1344.3	1362.3	1380.3	1397.7
7.5°	1185.6	1194.3	1210.9	1229.6	1249.7	1268.1	1284.8	1306.7	1330.6	1356.8	1386.2
10°	1139.6	1149.2	1169.0	1190.3	1214.1	1232.1	1254.6	1280.5	1307.6	1339.7	1375.8
12.5°	1098.1	1107.3	1131.1	1152.9	1177.5	1197.3	1223.5	1249.9	1286.0	1320.8	1361.8
15°	1017.3	1041.5	1068.6	1094.5	1123.9	1148.1	1179.7	1206.7	1241.1	1290.1	1336.9
17.5°	927.6	953.4	987.0	1027.0	1066.3	1096.3	1128.4	1162.0	1202.9	1253.0	1306.9
20°	875.3	896.2	933.4	977.9	1023.5	1065.3	1094.5	1131.7	1174.0	1228.2	1283.9
22.5°	836.1	853.8	882.9	927.4	976.6	1025.1	1062.5	1099.3	1146.1	1200.2	1260.9
25°	777.2	796.4	821.7	852.2	908.6	959.9	1008.9	1051.2	1100.7	1154.9	1222.5
27.5°	728.3	745.0	768.2	799.9	837.8	894.4	953.7	1002.0	1052.9	1110.9	1178.7
30°	699.4	713.0	732.1	764.3	800.4	851.1	911.3	967.8	1019.0	1079.3	1149.8
32.5°	669.3	683.7	702.4	727.7	766.5	809.1	869.4	931.2	985.7	1047.3	1116.4
35°	629.0	640.3	657.2	683.1	718.0	755.2	808.8	872.5	930.0	995.9	1061.8
37.5°	588.3	601.6	614.9	638.1	666.7	706.7	750.5	815.5	879.2	939.5	1003.8
40°	565.3	573.2	587.8	606.4	636.9	672.4	713.5	777.2	840.9	900.7	965.5
42.5°	539.6	548.4	560.8	579.4	606.7	641.3	681.5	736.6	803.1	861.0	919.9
45°	503.9	508.9	521.4	537.1	559.7	594.6	631.9	680.9	743.4	798.7	850.5
47.5°	467.8	472.2	480.0	494.4	519.7	547.7	582.5	626.6	681.4	736.6	780.5
50°	443.0	446.9	454.3	467.8	490.3	518.0	552.4	591.8	640.8	693.8	730.4
52.5°	418.2	420.4	427.2	442.5	461.5	488.7	519.4	555.7	601.6	645.6	682.7
55°	378.8	383.8	388.3	399.6	417.7	443.6	471.2	505.6	541.1	578.3	609.8
57.5°	337.6	343.2	349.7	359.6	373.9	398.0	422.8	450.7	481.0	511.8	538.3
60°	310.5	315.6	321.2	332.6	345.5	364.7	391.8	416.0	439.0	467.2	493.7
62.5°	284.0	289.0	295.5	304.6	317.1	335.3	357.9	379.0	403.0	427.5	447.3
65°	244.6	248.6	253.6	262.1	273.9	290.2	308.8	325.2	346.7	364.7	382.7
67.5°	201.5	209.0	215.6	222.5	232.5	247.8	261.2	276.9	291.4	304.8	321.2
70°	173.0	181.5	187.7	195.0	204.6	217.5	230.5	241.2	253.1	266.0	280.7
72.5°	149.1	155.8	160.6	168.4	177.1	189.1	201.2	210.1	219.7	228.6	242.8
75°	117.8	120.6	124.0	130.2	138.1	147.1	156.7	164.6	170.2	178.1	188.3
77.5°	84.6	90.1	92.3	96.7	102.3	108.0	114.3	121.0	126.4	129.1	137.0
80°	64.8	67.1	69.3	75.5	78.9	84.5	89.0	95.2	97.5	100.4	107.6
82.5°	50.4	51.8	53.1	54.8	56.8	62.5	66.9	70.9	73.1	74.2	79.7
85°	29.3	29.8	30.4	31.0	31.6	31.6	33.8	36.6	40.6	40.6	42.2
87.5°	13.1	13.8	13.4	12.6	13.5	12.3	12.8	12.6	13.8	14.5	15.5
90°	16.1	17.0	15.2	13.3	13.3	7.6	7.6	6.6	5.7	2.9	1.0
92.5°	250.3	300.5	263.0	191.4	117.9	69.7	50.1	36.2	24.6	15.7	10.8
95°	793.9	772.1	582.6	356.2	200.8	118.5	78.6	55.9	43.6	34.1	31.2
97.5°	997.4	813.3	545.3	320.2	191.9	128.5	95.1	75.6	64.2	56.1	56.1
100°	1004.2	761.7	494.6	301.3	194.2	138.4	108.0	90.0	78.6	72.0	72.0
102.5°	947.4	697.2	460.4	296.0	201.8	151.2	122.4	105.2	94.6	88.7	87.2
105°	844.1	621.5	431.0	298.4	219.8	174.3	146.8	129.8	118.5	113.7	110.9
107.5°	760.8	579.0	425.7	312.4	240.8	199.2	172.0	155.7	143.7	138.8	137.0
110°	719.1	564.7	427.3	323.0	256.7	215.1	189.5	172.4	161.0	156.3	154.4



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	695.5	557.8	431.8	334.4	271.9	231.7	206.2	189.1	178.5	173.0	171.1
115°	673.6	554.2	440.5	352.5	295.5	257.7	232.1	214.1	204.6	198.0	195.2
117.5°	663.7	553.3	449.8	370.8	318.5	282.5	256.0	239.1	228.7	222.8	220.1
120°	658.4	553.3	456.6	383.7	334.4	298.4	271.9	255.8	245.4	238.7	236.8
122.5°	652.4	552.5	463.5	395.8	349.6	313.6	287.8	270.2	260.6	253.9	252.0
125°	642.3	551.4	473.7	414.0	370.4	336.3	309.8	291.8	281.4	275.7	271.9
127.5°	628.8	549.3	481.8	429.7	389.7	356.8	330.0	311.3	299.4	292.5	289.5
130°	620.5	548.5	487.9	439.6	402.7	370.4	342.9	325.0	310.7	303.1	299.4
132.5°	612.9	547.8	493.2	449.5	413.3	381.1	355.1	335.6	322.1	312.3	309.2
135°	601.6	546.7	501.2	462.4	428.2	397.0	372.3	352.5	336.3	326.9	323.0
137.5°	591.7	546.4	505.9	471.4	439.6	410.4	386.9	366.2	350.9	340.5	336.9
140°	586.4	545.7	509.7	477.4	447.2	418.7	396.0	376.1	360.0	349.6	346.7
142.5°	581.9	545.7	512.7	482.0	454.0	426.3	404.3	385.2	369.8	360.2	357.3
145°	574.1	543.8	514.5	487.0	461.4	436.8	415.9	397.9	384.7	375.2	372.3
147.5°	567.1	540.4	515.4	491.3	469.0	445.8	427.1	412.1	398.4	390.1	389.1
150°	561.8	538.1	515.4	493.6	472.7	451.9	433.9	419.7	408.3	400.7	399.8
152.5°	555.7	534.3	513.9	495.1	475.8	457.2	440.8	428.0	417.4	409.9	409.6
155°	546.7	528.6	511.6	496.4	480.3	464.2	450.0	439.6	430.1	424.4	423.5
157.5°	537.4	522.8	509.2	496.4	483.6	469.9	458.7	449.6	442.2	436.9	436.9
160°	530.5	518.2	506.9	496.4	485.0	473.7	463.3	455.7	449.1	445.2	445.2
162.5°	524.5	513.6	504.6	496.4	486.6	476.0	467.8	461.0	455.1	452.1	452.8
165°	514.5	506.9	500.2	494.6	487.0	478.4	472.7	468.0	463.3	461.4	461.4
167.5°	505.3	500.0	495.7	492.3	486.7	480.5	476.1	473.5	469.9	469.0	469.9
170°	499.3	495.5	492.6	490.7	486.0	481.3	478.4	476.5	473.7	472.7	473.7
172.5°	494.0	490.9	489.6	489.3	485.3	482.0	480.0	478.8	476.7	476.5	477.4
175°	487.9	486.0	486.0	487.0	484.1	482.2	482.2	481.3	480.3	480.3	481.3
177.5°	483.7	483.0	483.0	484.5	483.0	482.2	482.2	482.2	481.4	482.2	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1407.5	1411.5	1416.0	1424.6	1431.8	1435.0	1441.3	1445.8	1444.5	1450.7	1461.6
5°	1413.0	1428.2	1445.7	1463.7	1484.0	1500.9	1514.4	1528.0	1538.7	1551.7	1570.8
7.5°	1412.1	1439.2	1468.6	1500.9	1534.1	1562.9	1589.5	1616.6	1640.5	1666.9	1701.2
10°	1408.5	1444.5	1481.2	1523.5	1565.7	1605.7	1641.8	1675.6	1707.8	1742.1	1785.6
12.5°	1404.4	1445.9	1490.2	1541.1	1593.7	1641.8	1684.2	1732.9	1773.1	1817.5	1867.6
15°	1386.5	1442.3	1502.6	1568.6	1631.7	1696.5	1754.5	1814.3	1870.1	1923.0	1986.2
17.5°	1366.0	1430.4	1501.5	1579.4	1655.2	1734.1	1802.9	1878.2	1935.3	2006.4	2065.0
20°	1349.3	1418.6	1494.7	1582.1	1668.3	1755.7	1831.7	1908.5	1972.7	2044.3	2118.6
22.5°	1329.0	1405.1	1487.5	1578.0	1668.3	1763.8	1848.0	1924.2	2003.8	2084.4	2161.0
25°	1296.3	1375.2	1462.6	1561.8	1665.5	1763.0	1853.2	1947.8	2033.5	2120.9	2189.6
27.5°	1256.2	1339.0	1431.2	1533.5	1639.9	1739.8	1846.0	1946.9	2033.1	2117.2	2177.2
30°	1224.2	1311.6	1400.0	1503.7	1614.2	1721.3	1835.2	1936.0	2026.8	2102.3	2136.1
32.5°	1191.2	1274.1	1365.3	1470.4	1583.6	1698.8	1811.7	1914.8	1998.8	2044.1	2045.0
35°	1134.0	1211.8	1306.4	1409.7	1525.8	1650.8	1765.3	1866.7	1918.0	1921.9	1866.7
37.5°	1071.5	1142.9	1232.3	1335.5	1462.7	1587.1	1704.1	1771.6	1788.8	1731.5	1629.3
40°	1027.0	1092.8	1179.1	1285.1	1411.3	1539.8	1646.3	1695.9	1677.9	1584.9	1471.0
42.5°	980.0	1041.5	1124.5	1229.1	1355.8	1485.7	1576.5	1603.0	1555.3	1447.8	1314.6
45°	903.5	959.9	1042.1	1147.5	1269.3	1391.0	1459.8	1446.3	1366.8	1239.4	1090.1
47.5°	823.8	878.2	952.3	1049.8	1174.4	1279.5	1326.1	1285.3	1172.2	1032.1	910.6
50°	771.0	826.8	895.0	988.1	1101.9	1203.3	1233.2	1171.2	1045.5	910.8	799.2
52.5°	719.2	766.9	833.7	923.6	1032.4	1118.1	1134.0	1062.5	932.8	812.0	713.1
55°	640.3	683.7	740.0	824.6	918.7	991.4	982.9	891.1	773.3	670.2	592.4
57.5°	563.9	596.6	648.7	728.0	810.6	859.4	828.5	750.2	640.4	556.0	490.3
60°	513.5	543.9	592.4	661.7	734.4	762.0	736.1	651.0	564.2	487.0	431.7
62.5°	465.7	492.5	534.2	598.6	657.3	673.6	645.9	571.6	493.4	427.5	381.7
65°	396.2	421.0	456.6	502.2	542.7	550.7	532.6	456.6	397.4	342.1	310.5
67.5°	333.2	349.4	377.2	416.6	438.1	442.8	408.0	360.1	307.9	274.0	250.2
70°	290.8	302.1	328.0	349.4	366.9	367.5	335.3	297.0	257.0	229.4	211.9
72.5°	249.8	260.7	280.2	294.9	308.3	303.9	274.5	244.3	211.9	191.1	178.1
75°	192.7	202.4	212.5	219.2	219.2	213.6	192.2	169.7	151.1	138.7	134.7
77.5°	140.1	148.0	151.4	150.3	148.4	139.6	126.0	111.3	104.6	98.7	95.8
80°	109.9	113.3	114.4	111.6	108.2	98.1	89.0	82.8	76.6	74.4	73.3
82.5°	81.5	84.5	81.5	82.3	74.8	66.5	61.6	59.4	56.8	55.9	54.8
85°	43.4	42.8	41.7	38.9	33.8	32.7	32.1	31.6	30.4	31.0	29.8
87.5°	15.4	14.7	13.0	12.8	12.8	13.0	13.5	13.9	14.3	13.6	14.7
90°	2.9	5.7	6.6	7.6	7.6	13.3	13.3	15.2	17.0	16.1	17.0
92.5°	15.7	24.6	36.2	50.1	69.7	117.9	191.4	263.0	300.5	250.3	186.1
95°	34.1	43.6	55.9	78.6	118.5	200.8	356.2	582.6	772.1	793.9	702.0
97.5°	56.1	64.2	75.6	95.1	128.5	191.9	320.2	545.3	813.3	997.4	1037.2
100°	72.0	78.6	90.0	108.0	138.4	194.2	301.3	494.6	761.7	1004.2	1142.6
102.5°	88.7	94.6	105.2	122.4	151.2	201.8	296.0	460.4	697.2	947.4	1137.3
105°	113.7	118.5	129.8	146.8	174.3	219.8	298.4	431.0	621.5	844.1	1061.0
107.5°	138.8	143.7	155.7	172.0	199.2	240.8	312.4	425.7	579.0	760.8	952.8
110°	156.3	161.0	172.4	189.5	215.1	256.7	323.0	427.3	564.7	719.1	887.7



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.0	178.5	189.1	206.2	231.7	271.9	334.4	431.8	557.8	695.5	839.9
115°	198.0	204.6	214.1	232.1	257.7	295.5	352.5	440.5	554.2	673.6	792.0
117.5°	222.8	228.7	239.1	256.0	282.5	318.5	370.8	449.8	553.3	663.7	768.5
120°	238.7	245.4	255.8	271.9	298.4	334.4	383.7	456.6	553.3	658.4	757.9
122.5°	253.9	260.6	270.2	287.8	313.6	349.6	395.8	463.5	552.5	652.4	748.8
125°	275.7	281.4	291.8	309.8	336.3	370.4	414.0	473.7	551.4	642.3	733.3
127.5°	292.5	299.4	311.3	330.0	356.8	389.7	429.7	481.8	549.3	628.8	714.3
130°	303.1	310.7	325.0	342.9	370.4	402.7	439.6	487.9	548.5	620.5	699.2
132.5°	312.3	322.1	335.6	355.1	381.1	413.3	449.5	493.2	547.8	612.9	683.2
135°	326.9	336.3	352.5	372.3	397.0	428.2	462.4	501.2	546.7	601.6	661.3
137.5°	340.5	350.9	366.2	386.9	410.4	439.6	471.4	505.9	546.4	591.7	641.4
140°	349.6	360.0	376.1	396.0	418.7	447.2	477.4	509.7	545.7	586.4	630.0
142.5°	360.2	369.8	385.2	404.3	426.3	454.0	482.0	512.7	545.7	581.9	619.4
145°	375.2	384.7	397.9	415.9	436.8	461.4	487.0	514.5	543.8	574.1	604.5
147.5°	390.1	398.4	412.1	427.1	445.8	469.0	491.3	515.4	540.4	567.1	592.2
150°	400.7	408.3	419.7	433.9	451.9	472.7	493.6	515.4	538.1	561.8	584.6
152.5°	409.9	417.4	428.0	440.8	457.2	475.8	495.1	513.9	534.3	555.7	576.2
155°	424.4	430.1	439.6	450.0	464.2	480.3	496.4	511.6	528.6	546.7	563.7
157.5°	436.9	442.2	449.6	458.7	469.9	483.6	496.4	509.2	522.8	537.4	550.2
160°	445.2	449.1	455.7	463.3	473.7	485.0	496.4	506.9	518.2	530.5	541.9
162.5°	452.1	455.1	461.0	467.8	476.0	486.6	496.4	504.6	513.6	524.5	533.5
165°	461.4	463.3	468.0	472.7	478.4	487.0	494.6	500.2	506.9	514.5	522.0
167.5°	469.0	469.9	473.5	476.1	480.5	486.7	492.3	495.7	500.0	505.3	510.9
170°	472.7	473.7	476.5	478.4	481.3	486.0	490.7	492.6	495.5	499.3	504.0
172.5°	476.5	476.7	478.8	480.0	482.0	485.3	489.3	489.6	490.9	494.0	497.9
175°	480.3	480.3	481.3	482.2	482.2	484.1	487.0	486.0	486.0	487.9	489.8
177.5°	482.2	481.4	482.2	482.2	482.2	483.0	484.5	483.0	483.0	483.7	484.5
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2	482.2



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9	1398.9
2.5°	1467.5	1469.3	1470.6	1475.1	1475.5	1479.6	1475.5
5°	1588.9	1596.8	1609.2	1621.5	1622.7	1630.5	1616.5
7.5°	1725.0	1743.3	1754.7	1774.7	1782.7	1787.5	1779.5
10°	1818.8	1835.7	1865.6	1880.2	1894.9	1897.1	1890.4
12.5°	1909.4	1936.3	1959.8	1987.5	1986.9	2006.7	1999.5
15°	2030.2	2057.8	2090.4	2121.5	2132.7	2132.7	2141.8
17.5°	2116.3	2166.9	2200.7	2225.0	2251.7	2256.3	2253.2
20°	2174.5	2229.1	2265.2	2296.8	2314.8	2319.9	2319.9
22.5°	2217.7	2264.2	2299.5	2327.8	2342.8	2348.7	2346.9
25°	2247.7	2287.7	2309.2	2317.6	2321.6	2320.4	2309.7
27.5°	2206.7	2204.9	2191.4	2165.4	2145.9	2134.1	2120.6
30°	2128.3	2098.9	2065.1	2027.9	1980.0	1943.3	1932.1
32.5°	2011.4	1945.6	1888.3	1826.4	1774.8	1738.2	1722.9
35°	1785.6	1681.3	1596.2	1521.8	1467.7	1433.9	1422.6
37.5°	1517.5	1416.6	1311.2	1239.1	1194.2	1160.0	1147.3
40°	1347.0	1237.1	1145.3	1077.7	1031.4	998.2	997.6
42.5°	1191.5	1086.5	1000.1	951.4	901.6	879.5	879.5
45°	975.6	891.6	818.4	780.1	750.2	732.1	727.1
47.5°	807.8	738.3	689.5	659.0	634.6	623.1	615.7
50°	713.5	652.6	613.8	587.3	573.7	559.1	558.0
52.5°	635.1	586.0	555.6	534.1	517.0	508.2	508.4
55°	533.8	494.9	473.4	457.1	443.6	436.8	434.0
57.5°	449.6	420.4	404.9	389.9	384.2	378.9	377.4
60°	397.4	377.6	363.0	351.1	342.7	341.0	340.4
62.5°	354.1	333.5	323.3	314.1	307.9	305.3	304.4
65°	292.0	276.7	267.7	260.4	258.1	254.2	253.6
67.5°	235.4	226.2	220.3	215.2	212.1	211.9	211.9
70°	200.6	195.6	190.5	187.7	186.0	184.8	184.8
72.5°	170.9	167.1	163.0	161.5	161.2	160.0	159.6
75°	130.2	126.3	126.8	124.0	121.7	119.0	117.2
77.5°	92.3	89.5	88.9	88.6	86.7	86.3	87.2
80°	71.6	68.7	68.2	68.7	68.2	66.5	66.5
82.5°	54.5	52.1	51.5	51.2	50.6	51.2	50.3
85°	29.3	28.2	28.2	28.2	29.3	28.8	28.2
87.5°	13.9	13.7	14.2	13.9	14.1	13.5	13.9
90°	18.0	18.9	18.9	19.9	20.9	19.9	19.9
92.5°	140.0	111.5	92.5	81.3	76.1	73.0	73.0
95°	555.1	428.2	336.3	289.9	260.6	243.4	231.1
97.5°	982.6	890.0	791.1	723.0	666.0	637.6	617.9
100°	1161.5	1115.1	1045.0	962.5	904.7	876.4	868.8
102.5°	1231.2	1244.6	1215.4	1164.9	1123.0	1093.1	1087.0
105°	1225.0	1318.7	1357.6	1359.5	1351.9	1338.6	1332.9
107.5°	1127.4	1259.5	1343.9	1390.7	1412.3	1421.8	1424.3
110°	1051.6	1189.0	1293.1	1360.4	1400.2	1417.3	1425.8



TEST NUMBER: P332981-930

CATALOG NUMBER: SA4XXRDIP-C1020D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	984.9	1114.7	1218.9	1295.3	1343.4	1367.3	1381.1
115°	908.6	1019.4	1110.4	1185.2	1242.0	1272.4	1279.9
117.5°	865.0	952.1	1029.2	1093.1	1140.8	1171.5	1177.4
120°	846.0	921.8	989.0	1043.1	1084.8	1109.4	1119.8
122.5°	833.9	902.9	961.8	1007.5	1043.1	1063.9	1074.3
125°	814.7	880.1	932.2	970.1	997.6	1015.6	1021.2
127.5°	792.2	857.4	906.9	944.9	969.4	984.6	990.2
130°	774.0	838.5	888.7	927.5	951.1	966.3	972.0
132.5°	753.6	816.4	866.7	904.7	931.5	945.8	951.5
135°	722.8	780.6	828.0	865.9	892.4	907.6	913.3
137.5°	693.5	742.2	785.0	820.4	846.6	859.1	865.9
140°	674.5	717.1	756.9	790.1	811.0	824.2	831.8
142.5°	658.6	695.2	729.7	759.0	778.4	790.1	795.4
145°	636.7	665.0	691.6	715.3	731.4	740.9	745.6
147.5°	617.7	640.4	661.3	678.7	692.5	699.8	701.4
150°	606.3	625.3	642.3	657.5	669.8	675.5	676.5
152.5°	594.9	612.4	626.4	639.3	649.3	652.7	653.7
155°	578.9	593.0	604.5	613.9	621.5	624.4	624.4
157.5°	563.0	574.9	584.0	591.2	596.9	598.6	598.6
160°	552.3	562.7	570.3	576.0	581.7	582.6	582.6
162.5°	542.5	550.7	557.4	561.6	567.3	568.3	567.4
165°	527.7	534.3	539.1	542.8	546.7	545.7	544.8
167.5°	515.2	520.5	523.3	525.2	527.7	527.5	526.8
170°	506.9	510.6	513.5	515.4	516.3	515.4	515.4
172.5°	500.0	502.3	504.3	505.5	506.5	505.5	504.0
175°	490.7	492.6	492.6	492.6	494.6	492.6	490.7
177.5°	485.3	485.3	486.0	485.3	486.0	484.5	483.0
180°	482.2	482.2	482.2	482.2	482.2	482.2	482.2

(END OF REPORT)