

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333005-930

Luminaire Tested: **SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P333005-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7099.3 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333005-930
CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58
1	100	96	92	89	93	90	86	83	78	75	73	67	65	63	57	55	54	50
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47	42
3	84	75	67	62	78	70	64	58	61	56	52	53	49	46	45	42	40	36
4	77	66	59	53	71	62	55	50	55	49	45	47	43	40	41	38	35	32
5	71	59	51	45	66	56	49	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	40	61	50	43	38	44	39	34	39	34	31	34	30	27	25
7	61	48	41	35	56	46	39	33	40	35	30	35	31	27	31	27	24	22
8	56	44	36	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	23	20	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13043	13043	13043	13043
5°	15129	13083	11563	13083
10°	17898	13025	10320	13025
15°	20674	12904	8868	12904
20°	23018	12740	8019	12740
25°	23762	12577	7445	12577
30°	20801	12379	7100	12379
35°	16192	12086	6890	12086
40°	12142	11751	6777	11751
45°	9587	11215	6719	11215
50°	8093	10595	6523	10595
55°	7054	9913	6175	9913
60°	6347	9206	5465	9206
65°	5595	8443	4701	8443
70°	5039	7652	4242	7652
75°	4223	6781	3615	6781
80°	3570	5779	3389	5779
85°	3010	4520	3010	4520



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.5	2.2
10°-20°	472.2	6.7
20°-30°	738.6	10.4
30°-40°	821.0	11.6
40°-50°	728.5	10.3
50°-60°	567.6	8.0
60°-70°	371.6	5.2
70°-80°	182.8	2.6
80°-90°	47.4	0.7
90°-100°	299.2	4.2
100°-110°	622.8	8.8
110°-120°	557.8	7.9
120°-130°	469.2	6.6
130°-140°	391.2	5.5
140°-150°	298.9	4.2
150°-160°	210.1	3.0
160°-170°	123.6	1.7
170°-180°	40.2	0.6
0°-30°	1367.3	19.3
0°-40°	2188.4	30.8
0°-60°	3484.5	49.1
0°-90°	4086.2	57.6
90°-120°	1479.8	20.8
90°-150°	2639.2	37.2
90°-180°	3013.0	42.4
0°-180°	7099.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1616	1616	1616	1616	1616	
5°	1867	1614	1427	1614	1867	189
15°	2474	1544	1061	1544	2474	703
25°	2668	1412	836	1412	2668	1183
35°	1643	1226	699	1226	1643	1030
45°	840	982	588	982	840	665
55°	501	704	439	704	501	456
65°	293	442	246	442	293	295
75°	135	217	116	217	135	149
85°	32	49	32	49	32	37
90°	17	1	17	1	17	15
95°	199	27	199	27	199	308
105°	1145	95	1145	95	1145	1132
115°	1100	168	1100	168	1100	1092
125°	877	234	877	234	877	797
135°	785	278	785	278	785	606
145°	641	320	641	320	641	406
155°	536	364	536	364	536	250
165°	468	396	468	396	468	134
175°	422	413	422	413	422	41
180°	414	414	414	414	414	



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1704.1	1708.9	1704.1	1703.6	1698.4	1696.9	1694.8	1688.0	1675.5	1668.3	1669.8
5°	1866.9	1883.2	1874.0	1872.7	1858.5	1844.1	1835.0	1814.2	1792.0	1777.1	1764.7
7.5°	2055.1	2064.5	2058.8	2049.7	2026.5	2013.4	1992.3	1964.8	1925.1	1894.8	1867.0
10°	2183.3	2191.0	2188.5	2171.5	2154.6	2120.1	2100.6	2062.2	2012.1	1972.4	1935.3
12.5°	2309.3	2317.7	2294.7	2295.5	2263.4	2236.3	2205.3	2157.0	2099.1	2047.9	2001.4
15°	2473.6	2463.2	2463.2	2450.1	2414.3	2376.6	2344.7	2293.9	2221.0	2159.8	2095.4
17.5°	2602.2	2605.9	2600.5	2569.8	2541.7	2502.6	2444.2	2384.9	2317.2	2235.1	2169.2
20°	2679.3	2679.3	2673.4	2652.6	2616.1	2574.5	2511.4	2446.9	2360.9	2278.3	2204.1
22.5°	2710.5	2712.6	2705.7	2688.5	2655.8	2615.1	2561.3	2495.9	2407.3	2314.2	2222.3
25°	2667.6	2680.0	2681.2	2676.7	2666.9	2642.1	2596.0	2528.9	2449.5	2348.6	2249.7
27.5°	2449.1	2464.7	2478.4	2500.9	2530.9	2546.5	2548.5	2514.5	2445.2	2348.1	2248.5
30°	2231.4	2244.4	2286.8	2342.1	2385.1	2424.1	2458.0	2467.1	2428.0	2340.8	2236.0
32.5°	1989.8	2007.5	2049.8	2109.3	2180.9	2247.0	2323.1	2361.8	2360.9	2308.5	2211.5
35°	1643.0	1656.0	1695.1	1757.5	1843.5	1941.8	2062.2	2155.9	2219.7	2215.2	2155.9
37.5°	1325.0	1339.8	1379.2	1431.0	1514.3	1636.1	1752.6	1881.7	1999.7	2066.0	2046.2
40°	1152.2	1152.8	1191.2	1244.6	1322.7	1428.8	1555.8	1698.9	1830.4	1937.9	1958.7
42.5°	1015.7	1015.9	1041.2	1098.8	1155.0	1254.9	1376.1	1518.3	1672.2	1796.2	1851.4
45°	839.7	845.5	866.4	900.9	945.2	1029.8	1126.7	1258.9	1431.4	1578.5	1670.3
47.5°	711.1	719.7	733.0	761.1	796.4	852.7	932.9	1051.7	1192.0	1353.8	1484.4
50°	644.4	645.7	662.7	678.2	708.9	753.8	824.1	923.0	1051.9	1207.5	1352.7
52.5°	587.2	586.9	597.0	616.9	641.7	676.7	733.4	823.5	937.8	1077.3	1227.2
55°	501.2	504.5	512.3	527.9	546.8	571.5	616.4	684.1	774.0	893.1	1029.2
57.5°	435.9	437.6	443.7	450.3	467.7	485.6	519.3	566.3	642.1	739.6	866.4
60°	393.1	393.8	395.7	405.5	419.2	436.1	458.9	498.6	562.4	651.6	751.9
62.5°	351.5	352.7	355.7	362.8	373.4	385.1	409.0	440.8	493.7	569.8	660.1
65°	292.9	293.6	298.2	300.8	309.2	319.6	337.2	358.7	395.1	458.9	527.3
67.5°	244.8	244.8	245.0	248.5	254.4	261.3	271.8	289.0	316.5	355.7	416.0
70°	213.5	213.5	214.8	216.8	220.0	225.8	231.7	244.8	265.0	296.9	343.1
72.5°	184.3	184.8	186.1	186.5	188.3	193.1	197.4	205.7	220.7	244.8	282.1
75°	135.4	137.4	140.6	143.2	146.4	145.8	150.3	155.6	160.1	174.5	195.9
77.5°	100.8	99.7	100.1	102.3	102.7	103.4	106.6	110.6	114.1	120.8	128.5
80°	76.8	76.8	78.8	79.4	78.8	79.4	82.7	84.6	85.9	88.5	95.7
82.5°	58.0	59.1	58.5	59.1	59.5	60.2	62.9	63.3	64.6	65.6	68.6
85°	32.5	33.2	33.8	32.5	32.5	32.5	33.8	34.5	35.8	35.1	36.4
87.5°	14.8	14.3	15.0	14.8	15.2	14.7	15.1	16.0	14.8	15.4	15.1
90°	17.1	17.1	17.9	17.1	16.3	16.3	15.5	14.7	13.9	14.7	13.0
92.5°	62.7	62.7	65.5	69.9	79.4	95.7	120.3	159.9	215.1	258.2	225.9
95°	198.6	209.2	223.8	249.1	288.9	367.9	477.0	603.1	682.1	663.3	500.6
97.5°	530.8	547.8	572.2	621.2	679.6	764.6	844.2	891.1	856.9	698.6	468.5
100°	746.4	752.8	777.3	827.0	897.7	958.0	997.8	981.6	862.7	654.4	424.9
102.5°	933.9	939.1	964.8	1000.8	1044.2	1069.3	1057.8	977.1	813.9	599.1	395.6
105°	1145.2	1150.1	1161.5	1168.0	1166.4	1132.9	1052.4	911.6	725.2	533.9	370.3
107.5°	1223.7	1221.6	1213.4	1194.8	1154.6	1082.1	968.6	818.6	653.5	497.5	365.7
110°	1225.0	1217.6	1203.0	1168.8	1111.0	1021.5	903.4	762.6	617.8	485.1	367.0



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1186.5	1174.7	1154.1	1112.8	1047.2	957.7	846.1	721.6	597.6	479.2	371.0
115°	1099.6	1093.1	1067.1	1018.2	953.9	875.8	780.6	680.4	578.7	476.1	378.5
117.5°	1011.5	1006.5	980.2	939.1	884.3	818.0	743.1	660.2	570.2	475.3	386.5
120°	962.1	953.1	932.0	896.1	849.7	792.0	726.8	651.1	565.7	475.3	392.3
122.5°	923.0	914.0	896.1	865.5	826.3	775.7	716.4	643.4	560.4	474.7	398.2
125°	877.4	872.5	857.0	833.5	800.9	756.1	699.9	630.0	551.9	473.7	407.0
127.5°	850.7	845.8	832.8	811.8	779.1	736.6	680.6	613.7	540.3	471.9	413.9
130°	835.1	830.2	817.2	796.8	763.4	720.3	665.0	600.7	533.1	471.2	419.1
132.5°	817.5	812.6	800.2	777.3	744.6	701.4	647.4	587.0	526.6	470.6	423.7
135°	784.6	779.8	766.7	744.0	711.3	670.7	621.0	568.1	516.8	469.6	430.6
137.5°	744.0	738.1	727.3	704.8	674.4	637.6	595.8	551.1	508.3	469.4	434.6
140°	714.6	708.1	696.8	678.8	650.3	616.1	579.5	541.3	503.9	468.8	437.9
142.5°	683.4	678.8	668.7	652.1	626.9	597.3	565.8	532.1	499.9	468.8	440.5
145°	640.6	636.5	628.4	614.5	594.2	571.4	547.0	519.3	493.3	467.2	442.0
147.5°	602.6	601.2	595.0	583.1	568.1	550.2	530.7	508.7	487.2	464.2	442.8
150°	581.1	580.3	575.4	564.8	551.9	537.2	520.9	502.2	482.7	462.3	442.8
152.5°	561.6	560.8	557.8	549.3	538.2	526.1	511.1	495.0	477.4	459.0	441.5
155°	536.4	536.4	533.9	527.4	519.3	509.5	497.3	484.3	469.6	454.2	439.5
157.5°	514.2	514.2	512.7	507.8	501.7	493.9	483.6	472.7	461.6	449.1	437.4
160°	500.6	500.6	499.8	494.9	490.0	483.5	474.5	465.5	455.8	445.2	435.5
162.5°	487.5	488.2	487.4	482.5	478.9	473.0	466.0	458.4	450.6	441.3	433.5
165°	468.0	468.8	469.6	466.4	463.1	459.0	453.4	448.5	442.0	435.5	429.7
167.5°	452.6	453.2	453.4	451.3	449.6	447.2	442.6	438.9	434.1	429.6	425.8
170°	442.8	442.8	443.6	442.8	441.2	438.7	435.5	433.0	428.9	425.7	423.2
172.5°	433.0	434.3	435.1	434.3	433.3	431.5	429.6	427.8	424.4	421.8	420.6
175°	421.6	423.2	424.9	423.2	423.2	423.2	421.6	420.8	419.1	417.5	417.5
177.5°	414.9	416.2	417.5	416.9	417.5	416.9	416.9	416.2	415.6	414.9	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1664.6	1657.3	1653.7	1645.4	1635.4	1630.2	1625.5	1618.8	1609.9	1600.5	1593.7
5°	1749.1	1733.5	1713.9	1690.5	1669.7	1649.5	1631.9	1614.4	1594.2	1573.4	1552.5
7.5°	1835.8	1805.1	1771.9	1733.5	1696.1	1662.2	1630.8	1600.9	1567.1	1536.8	1509.1
10°	1896.2	1854.6	1808.3	1759.5	1710.7	1668.3	1626.7	1588.9	1547.3	1510.2	1479.0
12.5°	1945.1	1896.2	1840.6	1779.8	1721.1	1669.9	1622.0	1572.8	1525.4	1485.2	1443.6
15°	2026.3	1959.3	1884.5	1811.6	1735.4	1665.7	1601.3	1544.0	1490.0	1433.4	1393.7
17.5°	2082.3	2002.7	1911.7	1824.1	1734.1	1652.0	1577.6	1509.4	1447.1	1389.3	1342.0
20°	2115.5	2027.6	1926.8	1827.2	1726.3	1638.4	1558.4	1482.9	1418.4	1355.9	1307.1
22.5°	2134.3	2037.0	1926.8	1822.5	1718.0	1622.8	1534.9	1456.3	1386.1	1323.6	1269.6
25°	2140.3	2036.1	1923.5	1803.8	1689.2	1588.3	1497.1	1411.9	1333.7	1271.3	1214.0
27.5°	2132.0	2009.3	1894.0	1771.1	1652.9	1546.5	1450.8	1361.2	1283.0	1215.9	1157.2
30°	2119.5	1987.9	1864.3	1736.8	1616.9	1514.7	1413.8	1328.0	1246.6	1176.9	1117.7
32.5°	2092.4	1961.9	1828.9	1698.2	1576.9	1471.5	1375.8	1289.4	1209.6	1138.4	1075.5
35°	2038.7	1906.6	1762.1	1628.0	1508.9	1399.5	1309.7	1226.4	1150.2	1074.1	1007.6
37.5°	1968.1	1833.0	1689.3	1542.5	1423.2	1320.0	1237.5	1159.4	1085.0	1015.5	941.9
40°	1901.4	1778.4	1629.9	1484.2	1361.8	1262.2	1186.0	1115.1	1040.2	971.2	897.6
42.5°	1820.7	1715.9	1565.9	1419.6	1298.8	1202.8	1131.9	1062.5	994.4	927.5	850.8
45°	1686.0	1606.5	1465.9	1325.4	1203.6	1108.6	1043.5	982.3	922.3	858.6	786.4
47.5°	1531.5	1477.7	1356.4	1212.4	1099.8	1014.3	951.5	901.4	850.8	787.0	723.6
50°	1424.2	1389.8	1272.6	1141.1	1033.7	955.0	890.5	843.6	801.3	740.1	683.5
52.5°	1309.7	1291.4	1192.4	1066.7	962.9	885.7	830.6	788.4	745.6	694.8	641.8
55°	1135.2	1145.0	1061.0	952.4	854.7	789.6	739.5	704.3	667.9	624.9	583.9
57.5°	956.9	992.5	936.2	840.7	749.3	689.1	651.3	621.7	591.2	555.5	520.5
60°	850.1	880.0	848.2	764.2	684.1	628.2	593.0	570.2	539.6	507.1	480.4
62.5°	746.0	778.0	759.1	691.3	616.9	568.8	537.8	516.6	493.8	465.5	437.7
65°	615.1	635.9	626.9	580.0	527.3	486.2	457.6	442.0	421.2	400.3	375.6
67.5°	471.2	511.4	506.1	481.2	435.6	403.6	384.8	371.0	352.0	336.6	319.8
70°	387.3	424.4	423.8	403.6	378.9	348.9	335.9	324.2	307.2	292.3	278.6
72.5°	317.0	351.0	356.0	340.6	323.7	301.0	288.5	280.5	264.0	253.7	242.6
75°	222.0	246.7	253.2	253.2	245.4	233.7	222.7	217.4	205.7	196.6	190.0
77.5°	145.5	161.2	171.3	173.7	174.9	171.0	161.8	158.2	149.2	145.9	139.7
80°	102.8	113.2	125.0	128.9	132.2	130.9	126.9	124.3	115.9	112.6	110.0
82.5°	71.1	76.8	86.4	95.1	94.1	97.5	94.1	92.0	85.7	84.5	81.9
85°	37.1	37.7	39.1	44.9	48.2	49.5	50.1	48.8	46.9	46.9	42.3
87.5°	14.8	14.3	14.3	14.3	14.7	16.6	17.7	17.9	16.6	15.6	14.2
90°	11.4	11.4	6.5	6.5	5.7	4.9	2.4	0.8	2.4	4.9	5.7
92.5°	164.4	101.3	59.9	43.0	31.1	21.2	13.5	9.3	13.5	21.2	31.1
95°	306.1	172.5	101.7	67.6	48.0	37.4	29.3	26.8	29.3	37.4	48.0
97.5°	275.1	164.9	110.4	81.7	65.0	55.2	48.2	48.2	48.2	55.2	65.0
100°	258.9	166.9	118.9	92.8	77.3	67.6	61.9	61.9	61.9	67.6	77.3
102.5°	254.3	173.3	129.9	105.2	90.3	81.2	76.1	74.8	76.1	81.2	90.3
105°	256.4	188.8	149.8	126.1	111.5	101.7	97.7	95.2	97.7	101.7	111.5
107.5°	268.4	206.9	171.0	147.8	133.8	123.4	119.4	117.7	119.4	123.4	133.8
110°	277.5	220.5	184.7	162.8	148.1	138.4	134.3	132.6	134.3	138.4	148.1



TEST NUMBER: P333005-930
 CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	287.3	233.6	199.1	177.1	162.5	153.4	148.6	147.0	148.6	153.4	162.5
115°	302.8	254.0	221.4	199.4	183.9	175.8	170.1	167.7	170.1	175.8	183.9
117.5°	318.5	273.6	242.7	219.9	205.5	196.5	191.4	189.1	191.4	196.5	205.5
120°	329.6	287.3	256.4	233.6	219.7	210.8	205.1	203.5	205.1	210.8	219.7
122.5°	340.1	300.4	269.4	247.3	232.1	223.8	218.1	216.5	218.1	223.8	232.1
125°	355.7	318.2	288.9	266.1	250.7	241.7	236.8	233.6	236.8	241.7	250.7
127.5°	369.2	334.8	306.6	283.6	267.4	257.2	251.4	248.7	251.4	257.2	267.4
130°	377.6	345.9	318.2	294.6	279.2	266.9	260.5	257.2	260.5	266.9	279.2
132.5°	386.1	355.1	327.3	305.1	288.3	276.7	268.2	265.6	268.2	276.7	288.3
135°	397.2	367.9	341.0	319.8	302.8	288.9	280.8	277.5	280.8	288.9	302.8
137.5°	405.0	377.6	352.6	332.4	314.6	301.5	292.5	289.4	292.5	301.5	314.6
140°	410.2	384.2	359.8	340.2	323.1	309.3	300.4	297.9	300.4	309.3	323.1
142.5°	414.1	390.0	366.2	347.4	330.9	317.7	309.5	307.0	309.5	317.7	330.9
145°	418.3	396.4	375.2	357.3	341.9	330.4	322.3	319.8	322.3	330.4	341.9
147.5°	422.1	402.9	383.0	366.9	354.1	342.3	335.2	334.4	335.2	342.3	354.1
150°	424.0	406.2	388.2	372.8	360.6	350.8	344.3	343.5	344.3	350.8	360.6
152.5°	425.3	408.8	392.8	378.6	367.7	358.7	352.1	352.0	352.1	358.7	367.7
155°	426.5	412.6	398.8	386.6	377.6	369.5	364.6	363.8	364.6	369.5	377.6
157.5°	426.5	415.4	403.7	394.1	386.3	379.9	375.4	375.4	375.4	379.9	386.3
160°	426.5	416.7	407.0	398.0	391.5	385.8	382.5	382.5	382.5	385.8	391.5
162.5°	426.5	418.0	409.0	401.9	396.1	391.0	388.4	389.1	388.4	391.0	396.1
165°	424.9	418.3	411.0	406.2	402.1	398.0	396.4	396.4	396.4	398.0	402.1
167.5°	422.9	418.2	412.8	409.1	406.8	403.7	402.9	403.7	402.9	403.7	406.8
170°	421.6	417.5	413.4	411.0	409.4	407.0	406.2	407.0	406.2	407.0	409.4
172.5°	420.3	416.9	414.1	412.3	411.3	409.5	409.4	410.2	409.4	409.5	411.3
175°	418.3	415.9	414.3	414.3	413.4	412.6	412.6	413.4	412.6	412.6	413.4
177.5°	416.2	414.9	414.3	414.3	414.3	413.6	414.3	414.9	414.3	413.6	414.3
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1586.5	1581.3	1574.5	1566.7	1557.3	1549.0	1545.3	1548.5	1550.0	1545.9	1545.3
5°	1538.1	1521.9	1508.9	1489.4	1473.7	1460.7	1451.6	1447.7	1449.0	1438.6	1436.0
7.5°	1483.9	1464.6	1443.2	1420.1	1398.5	1379.3	1369.3	1363.8	1352.8	1348.1	1340.2
10°	1449.0	1422.9	1402.2	1374.8	1350.1	1327.3	1316.2	1307.1	1296.0	1290.8	1279.8
12.5°	1413.1	1382.8	1359.9	1331.5	1306.3	1278.9	1268.3	1251.4	1234.0	1223.1	1208.9
15°	1362.4	1326.0	1298.0	1264.1	1234.2	1203.0	1174.9	1143.7	1132.0	1107.3	1092.9
17.5°	1303.2	1266.2	1231.6	1186.2	1140.0	1101.1	1071.3	1041.4	1023.4	1007.6	1000.4
20°	1264.1	1230.3	1182.1	1129.4	1078.0	1035.0	1010.9	991.4	971.8	960.8	953.0
22.5°	1227.2	1183.9	1128.0	1071.1	1019.6	986.0	965.6	945.6	929.7	919.2	908.7
25°	1165.2	1108.6	1049.3	984.2	949.1	919.8	897.6	881.3	871.6	857.9	852.7
27.5°	1101.6	1032.9	967.6	923.8	887.2	860.4	841.1	828.9	816.5	807.8	801.0
30°	1052.6	982.9	924.3	882.6	845.5	823.5	807.8	793.5	783.7	776.6	771.4
32.5°	1004.1	934.5	885.3	840.5	811.2	789.6	772.9	762.2	754.6	745.3	742.2
35°	934.1	872.3	829.3	789.0	759.0	739.5	726.4	715.4	708.9	706.3	704.3
37.5°	866.8	816.1	770.0	736.9	710.2	694.8	679.5	674.0	669.5	664.9	667.0
40°	824.1	776.6	735.6	700.4	678.9	662.0	652.9	646.4	642.5	642.5	642.5
42.5°	787.1	740.6	700.7	669.2	647.7	633.4	623.2	617.8	616.4	616.0	619.1
45°	729.7	686.7	646.4	620.4	602.1	587.8	582.0	577.4	577.4	580.0	580.7
47.5°	672.8	632.6	600.1	571.0	554.3	545.4	540.3	537.9	538.2	540.8	543.8
50°	637.9	598.2	566.3	540.3	524.6	516.2	511.6	510.4	511.6	511.6	516.2
52.5°	599.9	564.4	533.0	511.1	493.4	485.5	483.0	481.2	481.9	484.0	486.0
55°	544.2	512.3	482.3	461.5	448.5	443.3	437.4	438.1	436.8	438.1	438.1
57.5°	488.4	459.7	431.9	415.3	403.8	396.3	389.9	391.8	389.8	389.6	388.5
60°	452.4	421.2	399.0	384.1	371.0	364.5	358.7	360.0	358.0	356.7	354.1
62.5°	413.4	387.3	366.2	351.8	341.4	333.8	327.9	326.6	322.1	317.6	311.9
65°	356.7	335.3	316.3	302.7	292.9	287.1	282.5	278.6	268.8	258.4	253.2
67.5°	301.7	286.2	268.6	257.0	249.1	241.4	232.7	226.0	216.9	211.2	207.9
70°	266.2	251.3	236.3	225.2	216.8	209.6	199.8	195.3	188.7	186.1	183.0
72.5°	232.4	218.4	204.6	194.5	185.5	179.9	172.3	167.7	164.9	163.8	160.5
75°	181.0	169.9	159.5	150.3	143.2	139.3	136.1	132.8	131.5	125.6	122.4
77.5°	132.0	124.7	118.2	111.7	106.6	104.0	97.8	94.0	91.8	89.0	88.4
80°	102.8	97.7	91.2	87.2	80.1	77.5	74.8	74.2	73.5	72.9	72.2
82.5°	77.4	72.2	65.6	63.3	61.3	59.8	58.2	57.6	56.9	57.3	57.2
85°	39.1	36.4	36.4	35.8	35.1	34.5	33.8	33.8	33.2	33.8	33.2
87.5°	14.3	13.8	14.8	13.7	14.6	14.9	14.2	14.3	15.1	14.2	14.2
90°	6.5	6.5	11.4	11.4	13.0	14.7	13.9	14.7	15.5	16.3	16.3
92.5°	43.0	59.9	101.3	164.4	225.9	258.2	215.1	159.9	120.3	95.7	79.4
95°	67.6	101.7	172.5	306.1	500.6	663.3	682.1	603.1	477.0	367.9	288.9
97.5°	81.7	110.4	164.9	275.1	468.5	698.6	856.9	891.1	844.2	764.6	679.6
100°	92.8	118.9	166.9	258.9	424.9	654.4	862.7	981.6	997.8	958.0	897.7
102.5°	105.2	129.9	173.3	254.3	395.6	599.1	813.9	977.1	1057.8	1069.3	1044.2
105°	126.1	149.8	188.8	256.4	370.3	533.9	725.2	911.6	1052.4	1132.9	1166.4
107.5°	147.8	171.0	206.9	268.4	365.7	497.5	653.5	818.6	968.6	1082.1	1154.6
110°	162.8	184.7	220.5	277.5	367.0	485.1	617.8	762.6	903.4	1021.5	1111.0



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	177.1	199.1	233.6	287.3	371.0	479.2	597.6	721.6	846.1	957.7	1047.2
115°	199.4	221.4	254.0	302.8	378.5	476.1	578.7	680.4	780.6	875.8	953.9
117.5°	219.9	242.7	273.6	318.5	386.5	475.3	570.2	660.2	743.1	818.0	884.3
120°	233.6	256.4	287.3	329.6	392.3	475.3	565.7	651.1	726.8	792.0	849.7
122.5°	247.3	269.4	300.4	340.1	398.2	474.7	560.4	643.4	716.4	775.7	826.3
125°	266.1	288.9	318.2	355.7	407.0	473.7	551.9	630.0	699.9	756.1	800.9
127.5°	283.6	306.6	334.8	369.2	413.9	471.9	540.3	613.7	680.6	736.6	779.1
130°	294.6	318.2	345.9	377.6	419.1	471.2	533.1	600.7	665.0	720.3	763.4
132.5°	305.1	327.3	355.1	386.1	423.7	470.6	526.6	587.0	647.4	701.4	744.6
135°	319.8	341.0	367.9	397.2	430.6	469.6	516.8	568.1	621.0	670.7	711.3
137.5°	332.4	352.6	377.6	405.0	434.6	469.4	508.3	551.1	595.8	637.6	674.4
140°	340.2	359.8	384.2	410.2	437.9	468.8	503.9	541.3	579.5	616.1	650.3
142.5°	347.4	366.2	390.0	414.1	440.5	468.8	499.9	532.1	565.8	597.3	626.9
145°	357.3	375.2	396.4	418.3	442.0	467.2	493.3	519.3	547.0	571.4	594.2
147.5°	366.9	383.0	402.9	422.1	442.8	464.2	487.2	508.7	530.7	550.2	568.1
150°	372.8	388.2	406.2	424.0	442.8	462.3	482.7	502.2	520.9	537.2	551.9
152.5°	378.6	392.8	408.8	425.3	441.5	459.0	477.4	495.0	511.1	526.1	538.2
155°	386.6	398.8	412.6	426.5	439.5	454.2	469.6	484.3	497.3	509.5	519.3
157.5°	394.1	403.7	415.4	426.5	437.4	449.1	461.6	472.7	483.6	493.9	501.7
160°	398.0	407.0	416.7	426.5	435.5	445.2	455.8	465.5	474.5	483.5	490.0
162.5°	401.9	409.0	418.0	426.5	433.5	441.3	450.6	458.4	466.0	473.0	478.9
165°	406.2	411.0	418.3	424.9	429.7	435.5	442.0	448.5	453.4	459.0	463.1
167.5°	409.1	412.8	418.2	422.9	425.8	429.6	434.1	438.9	442.6	447.2	449.6
170°	411.0	413.4	417.5	421.6	423.2	425.7	428.9	433.0	435.5	438.7	441.2
172.5°	412.3	414.1	416.9	420.3	420.6	421.8	424.4	427.8	429.6	431.5	433.3
175°	414.3	414.3	415.9	418.3	417.5	417.5	419.1	420.8	421.6	423.2	423.2
177.5°	414.3	414.3	414.9	416.2	414.9	414.9	415.6	416.2	416.9	416.9	417.5
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1542.2	1543.3	1539.6	1538.6	1539.6	1543.3	1542.2	1545.3	1545.9	1550.0	1548.5
5°	1430.8	1429.5	1426.2	1426.9	1426.2	1429.5	1430.8	1436.0	1438.6	1449.0	1447.7
7.5°	1335.5	1330.4	1331.8	1326.7	1331.8	1330.4	1335.5	1340.2	1348.1	1352.8	1363.8
10°	1277.2	1270.0	1264.1	1258.9	1264.1	1270.0	1277.2	1279.8	1290.8	1296.0	1307.1
12.5°	1197.5	1191.3	1183.4	1185.0	1183.4	1191.3	1197.5	1208.9	1223.1	1234.0	1251.4
15°	1084.4	1074.7	1059.1	1061.0	1059.1	1074.7	1084.4	1092.9	1107.3	1132.0	1143.7
17.5°	988.8	988.9	981.8	983.4	981.8	988.9	988.8	1000.4	1007.6	1023.4	1041.4
20°	939.3	934.7	935.4	933.4	935.4	934.7	939.3	953.0	960.8	971.8	991.4
22.5°	904.9	899.4	894.8	890.7	894.8	899.4	904.9	908.7	919.2	929.7	945.6
25°	846.9	842.9	837.1	835.8	837.1	842.9	846.9	852.7	857.9	871.6	881.3
27.5°	795.8	795.1	792.7	789.7	792.7	795.1	795.8	801.0	807.8	816.5	828.9
30°	766.1	764.8	763.5	761.6	763.5	764.8	766.1	771.4	776.6	783.7	793.5
32.5°	739.6	738.8	737.5	737.7	737.5	738.8	739.6	742.2	745.3	754.6	762.2
35°	701.7	701.1	699.8	699.1	699.8	701.1	701.7	704.3	706.3	708.9	715.4
37.5°	666.3	668.0	667.2	667.1	667.2	668.0	666.3	667.0	664.9	669.5	674.0
40°	641.8	642.5	643.8	643.1	643.8	642.5	641.8	642.5	642.5	642.5	646.4
42.5°	621.5	621.7	623.5	621.3	623.5	621.7	621.5	619.1	616.0	616.4	617.8
45°	585.2	589.1	588.5	588.5	588.5	589.1	585.2	580.7	580.0	577.4	577.4
47.5°	545.5	548.9	549.8	549.7	549.8	548.9	545.5	543.8	540.8	538.2	537.9
50°	519.4	518.1	520.1	519.4	520.1	518.1	519.4	516.2	511.6	511.6	510.4
52.5°	487.7	488.0	487.8	487.1	487.8	488.0	487.7	486.0	484.0	481.9	481.2
55°	438.7	439.4	438.1	438.7	438.1	439.4	438.7	438.1	438.1	436.8	438.1
57.5°	385.6	382.5	383.8	382.2	383.8	382.5	385.6	388.5	389.6	389.8	391.8
60°	347.6	342.4	341.1	338.5	341.1	342.4	347.6	354.1	356.7	358.0	360.0
62.5°	304.9	301.3	296.9	298.9	296.9	301.3	304.9	311.9	317.6	322.1	326.6
65°	248.0	245.4	243.4	246.1	243.4	245.4	248.0	253.2	258.4	268.8	278.6
67.5°	205.3	203.9	203.9	202.6	203.9	203.9	205.3	207.9	211.2	216.9	226.0
70°	183.0	181.0	181.0	179.7	181.0	181.0	183.0	183.0	186.1	188.7	195.3
72.5°	160.0	158.1	158.6	157.8	158.6	158.1	160.0	160.5	163.8	164.9	167.7
75°	118.5	115.2	115.2	115.9	115.2	115.2	118.5	122.4	125.6	131.5	132.8
77.5°	88.4	87.7	88.6	87.5	88.6	87.7	88.4	88.4	89.0	91.8	94.0
80°	72.2	71.6	70.9	72.9	70.9	71.6	72.2	72.2	72.9	73.5	74.2
82.5°	56.1	56.0	55.8	58.3	55.8	56.0	56.1	57.2	57.3	56.9	57.6
85°	33.8	32.5	33.8	32.5	33.8	32.5	33.8	33.2	33.8	33.2	33.8
87.5°	15.4	15.0	14.3	14.8	14.3	15.0	15.4	14.2	14.2	15.1	14.3
90°	17.1	17.9	17.1	17.1	17.1	17.9	17.1	16.3	16.3	15.5	14.7
92.5°	69.9	65.5	62.7	62.7	62.7	65.5	69.9	79.4	95.7	120.3	159.9
95°	249.1	223.8	209.2	198.6	209.2	223.8	249.1	288.9	367.9	477.0	603.1
97.5°	621.2	572.2	547.8	530.8	547.8	572.2	621.2	679.6	764.6	844.2	891.1
100°	827.0	777.3	752.8	746.4	752.8	777.3	827.0	897.7	958.0	997.8	981.6
102.5°	1000.8	964.8	939.1	933.9	939.1	964.8	1000.8	1044.2	1069.3	1057.8	977.1
105°	1168.0	1161.5	1150.1	1145.2	1150.1	1161.5	1168.0	1166.4	1132.9	1052.4	911.6
107.5°	1194.8	1213.4	1221.6	1223.7	1221.6	1213.4	1194.8	1154.6	1082.1	968.6	818.6
110°	1168.8	1203.0	1217.6	1225.0	1217.6	1203.0	1168.8	1111.0	1021.5	903.4	762.6



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1112.8	1154.1	1174.7	1186.5	1174.7	1154.1	1112.8	1047.2	957.7	846.1	721.6
115°	1018.2	1067.1	1093.1	1099.6	1093.1	1067.1	1018.2	953.9	875.8	780.6	680.4
117.5°	939.1	980.2	1006.5	1011.5	1006.5	980.2	939.1	884.3	818.0	743.1	660.2
120°	896.1	932.0	953.1	962.1	953.1	932.0	896.1	849.7	792.0	726.8	651.1
122.5°	865.5	896.1	914.0	923.0	914.0	896.1	865.5	826.3	775.7	716.4	643.4
125°	833.5	857.0	872.5	877.4	872.5	857.0	833.5	800.9	756.1	699.9	630.0
127.5°	811.8	832.8	845.8	850.7	845.8	832.8	811.8	779.1	736.6	680.6	613.7
130°	796.8	817.2	830.2	835.1	830.2	817.2	796.8	763.4	720.3	665.0	600.7
132.5°	777.3	800.2	812.6	817.5	812.6	800.2	777.3	744.6	701.4	647.4	587.0
135°	744.0	766.7	779.8	784.6	779.8	766.7	744.0	711.3	670.7	621.0	568.1
137.5°	704.8	727.3	738.1	744.0	738.1	727.3	704.8	674.4	637.6	595.8	551.1
140°	678.8	696.8	708.1	714.6	708.1	696.8	678.8	650.3	616.1	579.5	541.3
142.5°	652.1	668.7	678.8	683.4	678.8	668.7	652.1	626.9	597.3	565.8	532.1
145°	614.5	628.4	636.5	640.6	636.5	628.4	614.5	594.2	571.4	547.0	519.3
147.5°	583.1	595.0	601.2	602.6	601.2	595.0	583.1	568.1	550.2	530.7	508.7
150°	564.8	575.4	580.3	581.1	580.3	575.4	564.8	551.9	537.2	520.9	502.2
152.5°	549.3	557.8	560.8	561.6	560.8	557.8	549.3	538.2	526.1	511.1	495.0
155°	527.4	533.9	536.4	536.4	536.4	533.9	527.4	519.3	509.5	497.3	484.3
157.5°	507.8	512.7	514.2	514.2	514.2	512.7	507.8	501.7	493.9	483.6	472.7
160°	494.9	499.8	500.6	500.6	500.6	499.8	494.9	490.0	483.5	474.5	465.5
162.5°	482.5	487.4	488.2	487.5	488.2	487.4	482.5	478.9	473.0	466.0	458.4
165°	466.4	469.6	468.8	468.0	468.8	469.6	466.4	463.1	459.0	453.4	448.5
167.5°	451.3	453.4	453.2	452.6	453.2	453.4	451.3	449.6	447.2	442.6	438.9
170°	442.8	443.6	442.8	442.8	442.8	443.6	442.8	441.2	438.7	435.5	433.0
172.5°	434.3	435.1	434.3	433.0	434.3	435.1	434.3	433.3	431.5	429.6	427.8
175°	423.2	424.9	423.2	421.6	423.2	424.9	423.2	423.2	423.2	421.6	420.8
177.5°	416.9	417.5	416.2	414.9	416.2	417.5	416.9	417.5	416.9	416.9	416.2
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1545.3	1549.0	1557.3	1566.7	1574.5	1581.3	1586.5	1593.7	1600.5	1609.9	1618.8
5°	1451.6	1460.7	1473.7	1489.4	1508.9	1521.9	1538.1	1552.5	1573.4	1594.2	1614.4
7.5°	1369.3	1379.3	1398.5	1420.1	1443.2	1464.6	1483.9	1509.1	1536.8	1567.1	1600.9
10°	1316.2	1327.3	1350.1	1374.8	1402.2	1422.9	1449.0	1479.0	1510.2	1547.3	1588.9
12.5°	1268.3	1278.9	1306.3	1331.5	1359.9	1382.8	1413.1	1443.6	1485.2	1525.4	1572.8
15°	1174.9	1203.0	1234.2	1264.1	1298.0	1326.0	1362.4	1393.7	1433.4	1490.0	1544.0
17.5°	1071.3	1101.1	1140.0	1186.2	1231.6	1266.2	1303.2	1342.0	1389.3	1447.1	1509.4
20°	1010.9	1035.0	1078.0	1129.4	1182.1	1230.3	1264.1	1307.1	1355.9	1418.4	1482.9
22.5°	965.6	986.0	1019.6	1071.1	1128.0	1183.9	1227.2	1269.6	1323.6	1386.1	1456.3
25°	897.6	919.8	949.1	984.2	1049.3	1108.6	1165.2	1214.0	1271.3	1333.7	1411.9
27.5°	841.1	860.4	887.2	923.8	967.6	1032.9	1101.6	1157.2	1215.9	1283.0	1361.2
30°	807.8	823.5	845.5	882.6	924.3	982.9	1052.6	1117.7	1176.9	1246.6	1328.0
32.5°	772.9	789.6	811.2	840.5	885.3	934.5	1004.1	1075.5	1138.4	1209.6	1289.4
35°	726.4	739.5	759.0	789.0	829.3	872.3	934.1	1007.6	1074.1	1150.2	1226.4
37.5°	679.5	694.8	710.2	736.9	770.0	816.1	866.8	941.9	1015.5	1085.0	1159.4
40°	652.9	662.0	678.9	700.4	735.6	776.6	824.1	897.6	971.2	1040.2	1115.1
42.5°	623.2	633.4	647.7	669.2	700.7	740.6	787.1	850.8	927.5	994.4	1062.5
45°	582.0	587.8	602.1	620.4	646.4	686.7	729.7	786.4	858.6	922.3	982.3
47.5°	540.3	545.4	554.3	571.0	600.1	632.6	672.8	723.6	787.0	850.8	901.4
50°	511.6	516.2	524.6	540.3	566.3	598.2	637.9	683.5	740.1	801.3	843.6
52.5°	483.0	485.5	493.4	511.1	533.0	564.4	599.9	641.8	694.8	745.6	788.4
55°	437.4	443.3	448.5	461.5	482.3	512.3	544.2	583.9	624.9	667.9	704.3
57.5°	389.9	396.3	403.8	415.3	431.9	459.7	488.4	520.5	555.5	591.2	621.7
60°	358.7	364.5	371.0	384.1	399.0	421.2	452.4	480.4	507.1	539.6	570.2
62.5°	327.9	333.8	341.4	351.8	366.2	387.3	413.4	437.7	465.5	493.8	516.6
65°	282.5	287.1	292.9	302.7	316.3	335.3	356.7	375.6	400.3	421.2	442.0
67.5°	232.7	241.4	249.1	257.0	268.6	286.2	301.7	319.8	336.6	352.0	371.0
70°	199.8	209.6	216.8	225.2	236.3	251.3	266.2	278.6	292.3	307.2	324.2
72.5°	172.3	179.9	185.5	194.5	204.6	218.4	232.4	242.6	253.7	264.0	280.5
75°	136.1	139.3	143.2	150.3	159.5	169.9	181.0	190.0	196.6	205.7	217.4
77.5°	97.8	104.0	106.6	111.7	118.2	124.7	132.0	139.7	145.9	149.2	158.2
80°	74.8	77.5	80.1	87.2	91.2	97.7	102.8	110.0	112.6	115.9	124.3
82.5°	58.2	59.8	61.3	63.3	65.6	72.2	77.4	81.9	84.5	85.7	92.0
85°	33.8	34.5	35.1	35.8	36.4	36.4	39.1	42.3	46.9	46.9	48.8
87.5°	14.2	14.9	14.6	13.7	14.8	13.8	14.3	14.2	15.6	16.6	17.9
90°	13.9	14.7	13.0	11.4	11.4	6.5	6.5	5.7	4.9	2.4	0.8
92.5°	215.1	258.2	225.9	164.4	101.3	59.9	43.0	31.1	21.2	13.5	9.3
95°	682.1	663.3	500.6	306.1	172.5	101.7	67.6	48.0	37.4	29.3	26.8
97.5°	856.9	698.6	468.5	275.1	164.9	110.4	81.7	65.0	55.2	48.2	48.2
100°	862.7	654.4	424.9	258.9	166.9	118.9	92.8	77.3	67.6	61.9	61.9
102.5°	813.9	599.1	395.6	254.3	173.3	129.9	105.2	90.3	81.2	76.1	74.8
105°	725.2	533.9	370.3	256.4	188.8	149.8	126.1	111.5	101.7	97.7	95.2
107.5°	653.5	497.5	365.7	268.4	206.9	171.0	147.8	133.8	123.4	119.4	117.7
110°	617.8	485.1	367.0	277.5	220.5	184.7	162.8	148.1	138.4	134.3	132.6



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	597.6	479.2	371.0	287.3	233.6	199.1	177.1	162.5	153.4	148.6	147.0
115°	578.7	476.1	378.5	302.8	254.0	221.4	199.4	183.9	175.8	170.1	167.7
117.5°	570.2	475.3	386.5	318.5	273.6	242.7	219.9	205.5	196.5	191.4	189.1
120°	565.7	475.3	392.3	329.6	287.3	256.4	233.6	219.7	210.8	205.1	203.5
122.5°	560.4	474.7	398.2	340.1	300.4	269.4	247.3	232.1	223.8	218.1	216.5
125°	551.9	473.7	407.0	355.7	318.2	288.9	266.1	250.7	241.7	236.8	233.6
127.5°	540.3	471.9	413.9	369.2	334.8	306.6	283.6	267.4	257.2	251.4	248.7
130°	533.1	471.2	419.1	377.6	345.9	318.2	294.6	279.2	266.9	260.5	257.2
132.5°	526.6	470.6	423.7	386.1	355.1	327.3	305.1	288.3	276.7	268.2	265.6
135°	516.8	469.6	430.6	397.2	367.9	341.0	319.8	302.8	288.9	280.8	277.5
137.5°	508.3	469.4	434.6	405.0	377.6	352.6	332.4	314.6	301.5	292.5	289.4
140°	503.9	468.8	437.9	410.2	384.2	359.8	340.2	323.1	309.3	300.4	297.9
142.5°	499.9	468.8	440.5	414.1	390.0	366.2	347.4	330.9	317.7	309.5	307.0
145°	493.3	467.2	442.0	418.3	396.4	375.2	357.3	341.9	330.4	322.3	319.8
147.5°	487.2	464.2	442.8	422.1	402.9	383.0	366.9	354.1	342.3	335.2	334.4
150°	482.7	462.3	442.8	424.0	406.2	388.2	372.8	360.6	350.8	344.3	343.5
152.5°	477.4	459.0	441.5	425.3	408.8	392.8	378.6	367.7	358.7	352.1	352.0
155°	469.6	454.2	439.5	426.5	412.6	398.8	386.6	377.6	369.5	364.6	363.8
157.5°	461.6	449.1	437.4	426.5	415.4	403.7	394.1	386.3	379.9	375.4	375.4
160°	455.8	445.2	435.5	426.5	416.7	407.0	398.0	391.5	385.8	382.5	382.5
162.5°	450.6	441.3	433.5	426.5	418.0	409.0	401.9	396.1	391.0	388.4	389.1
165°	442.0	435.5	429.7	424.9	418.3	411.0	406.2	402.1	398.0	396.4	396.4
167.5°	434.1	429.6	425.8	422.9	418.2	412.8	409.1	406.8	403.7	402.9	403.7
170°	428.9	425.7	423.2	421.6	417.5	413.4	411.0	409.4	407.0	406.2	407.0
172.5°	424.4	421.8	420.6	420.3	416.9	414.1	412.3	411.3	409.5	409.4	410.2
175°	419.1	417.5	417.5	418.3	415.9	414.3	414.3	413.4	412.6	412.6	413.4
177.5°	415.6	414.9	414.9	416.2	414.9	414.3	414.3	414.3	413.6	414.3	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1625.5	1630.2	1635.4	1645.4	1653.7	1657.3	1664.6	1669.8	1668.3	1675.5	1688.0
5°	1631.9	1649.5	1669.7	1690.5	1713.9	1733.5	1749.1	1764.7	1777.1	1792.0	1814.2
7.5°	1630.8	1662.2	1696.1	1733.5	1771.9	1805.1	1835.8	1867.0	1894.8	1925.1	1964.8
10°	1626.7	1668.3	1710.7	1759.5	1808.3	1854.6	1896.2	1935.3	1972.4	2012.1	2062.2
12.5°	1622.0	1669.9	1721.1	1779.8	1840.6	1896.2	1945.1	2001.4	2047.9	2099.1	2157.0
15°	1601.3	1665.7	1735.4	1811.6	1884.5	1959.3	2026.3	2095.4	2159.8	2221.0	2293.9
17.5°	1577.6	1652.0	1734.1	1824.1	1911.7	2002.7	2082.3	2169.2	2235.1	2317.2	2384.9
20°	1558.4	1638.4	1726.3	1827.2	1926.8	2027.6	2115.5	2204.1	2278.3	2360.9	2446.9
22.5°	1534.9	1622.8	1718.0	1822.5	1926.8	2037.0	2134.3	2222.3	2314.2	2407.3	2495.9
25°	1497.1	1588.3	1689.2	1803.8	1923.5	2036.1	2140.3	2249.7	2348.6	2449.5	2528.9
27.5°	1450.8	1546.5	1652.9	1771.1	1894.0	2009.3	2132.0	2248.5	2348.1	2445.2	2514.5
30°	1413.8	1514.7	1616.9	1736.8	1864.3	1987.9	2119.5	2236.0	2340.8	2428.0	2467.1
32.5°	1375.8	1471.5	1576.9	1698.2	1828.9	1961.9	2092.4	2211.5	2308.5	2360.9	2361.8
35°	1309.7	1399.5	1508.9	1628.0	1762.1	1906.6	2038.7	2155.9	2215.2	2219.7	2155.9
37.5°	1237.5	1320.0	1423.2	1542.5	1689.3	1833.0	1968.1	2046.2	2066.0	1999.7	1881.7
40°	1186.0	1262.2	1361.8	1484.2	1629.9	1778.4	1901.4	1958.7	1937.9	1830.4	1698.9
42.5°	1131.9	1202.8	1298.8	1419.6	1565.9	1715.9	1820.7	1851.4	1796.2	1672.2	1518.3
45°	1043.5	1108.6	1203.6	1325.4	1465.9	1606.5	1686.0	1670.3	1578.5	1431.4	1258.9
47.5°	951.5	1014.3	1099.8	1212.4	1356.4	1477.7	1531.5	1484.4	1353.8	1192.0	1051.7
50°	890.5	955.0	1033.7	1141.1	1272.6	1389.8	1424.2	1352.7	1207.5	1051.9	923.0
52.5°	830.6	885.7	962.9	1066.7	1192.4	1291.4	1309.7	1227.2	1077.3	937.8	823.5
55°	739.5	789.6	854.7	952.4	1061.0	1145.0	1135.2	1029.2	893.1	774.0	684.1
57.5°	651.3	689.1	749.3	840.7	936.2	992.5	956.9	866.4	739.6	642.1	566.3
60°	593.0	628.2	684.1	764.2	848.2	880.0	850.1	751.9	651.6	562.4	498.6
62.5°	537.8	568.8	616.9	691.3	759.1	778.0	746.0	660.1	569.8	493.7	440.8
65°	457.6	486.2	527.3	580.0	626.9	635.9	615.1	527.3	458.9	395.1	358.7
67.5°	384.8	403.6	435.6	481.2	506.1	511.4	471.2	416.0	355.7	316.5	289.0
70°	335.9	348.9	378.9	403.6	423.8	424.4	387.3	343.1	296.9	265.0	244.8
72.5°	288.5	301.0	323.7	340.6	356.0	351.0	317.0	282.1	244.8	220.7	205.7
75°	222.7	233.7	245.4	253.2	253.2	246.7	222.0	195.9	174.5	160.1	155.6
77.5°	161.8	171.0	174.9	173.7	171.3	161.2	145.5	128.5	120.8	114.1	110.6
80°	126.9	130.9	132.2	128.9	125.0	113.2	102.8	95.7	88.5	85.9	84.6
82.5°	94.1	97.5	94.1	95.1	86.4	76.8	71.1	68.6	65.6	64.6	63.3
85°	50.1	49.5	48.2	44.9	39.1	37.7	37.1	36.4	35.1	35.8	34.5
87.5°	17.7	16.6	14.7	14.3	14.3	14.3	14.8	15.1	15.4	14.8	16.0
90°	2.4	4.9	5.7	6.5	6.5	11.4	11.4	13.0	14.7	13.9	14.7
92.5°	13.5	21.2	31.1	43.0	59.9	101.3	164.4	225.9	258.2	215.1	159.9
95°	29.3	37.4	48.0	67.6	101.7	172.5	306.1	500.6	663.3	682.1	603.1
97.5°	48.2	55.2	65.0	81.7	110.4	164.9	275.1	468.5	698.6	856.9	891.1
100°	61.9	67.6	77.3	92.8	118.9	166.9	258.9	424.9	654.4	862.7	981.6
102.5°	76.1	81.2	90.3	105.2	129.9	173.3	254.3	395.6	599.1	813.9	977.1
105°	97.7	101.7	111.5	126.1	149.8	188.8	256.4	370.3	533.9	725.2	911.6
107.5°	119.4	123.4	133.8	147.8	171.0	206.9	268.4	365.7	497.5	653.5	818.6
110°	134.3	138.4	148.1	162.8	184.7	220.5	277.5	367.0	485.1	617.8	762.6



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	148.6	153.4	162.5	177.1	199.1	233.6	287.3	371.0	479.2	597.6	721.6
115°	170.1	175.8	183.9	199.4	221.4	254.0	302.8	378.5	476.1	578.7	680.4
117.5°	191.4	196.5	205.5	219.9	242.7	273.6	318.5	386.5	475.3	570.2	660.2
120°	205.1	210.8	219.7	233.6	256.4	287.3	329.6	392.3	475.3	565.7	651.1
122.5°	218.1	223.8	232.1	247.3	269.4	300.4	340.1	398.2	474.7	560.4	643.4
125°	236.8	241.7	250.7	266.1	288.9	318.2	355.7	407.0	473.7	551.9	630.0
127.5°	251.4	257.2	267.4	283.6	306.6	334.8	369.2	413.9	471.9	540.3	613.7
130°	260.5	266.9	279.2	294.6	318.2	345.9	377.6	419.1	471.2	533.1	600.7
132.5°	268.2	276.7	288.3	305.1	327.3	355.1	386.1	423.7	470.6	526.6	587.0
135°	280.8	288.9	302.8	319.8	341.0	367.9	397.2	430.6	469.6	516.8	568.1
137.5°	292.5	301.5	314.6	332.4	352.6	377.6	405.0	434.6	469.4	508.3	551.1
140°	300.4	309.3	323.1	340.2	359.8	384.2	410.2	437.9	468.8	503.9	541.3
142.5°	309.5	317.7	330.9	347.4	366.2	390.0	414.1	440.5	468.8	499.9	532.1
145°	322.3	330.4	341.9	357.3	375.2	396.4	418.3	442.0	467.2	493.3	519.3
147.5°	335.2	342.3	354.1	366.9	383.0	402.9	422.1	442.8	464.2	487.2	508.7
150°	344.3	350.8	360.6	372.8	388.2	406.2	424.0	442.8	462.3	482.7	502.2
152.5°	352.1	358.7	367.7	378.6	392.8	408.8	425.3	441.5	459.0	477.4	495.0
155°	364.6	369.5	377.6	386.6	398.8	412.6	426.5	439.5	454.2	469.6	484.3
157.5°	375.4	379.9	386.3	394.1	403.7	415.4	426.5	437.4	449.1	461.6	472.7
160°	382.5	385.8	391.5	398.0	407.0	416.7	426.5	435.5	445.2	455.8	465.5
162.5°	388.4	391.0	396.1	401.9	409.0	418.0	426.5	433.5	441.3	450.6	458.4
165°	396.4	398.0	402.1	406.2	411.0	418.3	424.9	429.7	435.5	442.0	448.5
167.5°	402.9	403.7	406.8	409.1	412.8	418.2	422.9	425.8	429.6	434.1	438.9
170°	406.2	407.0	409.4	411.0	413.4	417.5	421.6	423.2	425.7	428.9	433.0
172.5°	409.4	409.5	411.3	412.3	414.1	416.9	420.3	420.6	421.8	424.4	427.8
175°	412.6	412.6	413.4	414.3	414.3	415.9	418.3	417.5	417.5	419.1	420.8
177.5°	414.3	413.6	414.3	414.3	414.3	414.9	416.2	414.9	414.9	415.6	416.2
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3	414.3



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1694.8	1696.9	1698.4	1703.6	1704.1	1708.9	1704.1
5°	1835.0	1844.1	1858.5	1872.7	1874.0	1883.2	1866.9
7.5°	1992.3	2013.4	2026.5	2049.7	2058.8	2064.5	2055.1
10°	2100.6	2120.1	2154.6	2171.5	2188.5	2191.0	2183.3
12.5°	2205.3	2236.3	2263.4	2295.5	2294.7	2317.7	2309.3
15°	2344.7	2376.6	2414.3	2450.1	2463.2	2463.2	2473.6
17.5°	2444.2	2502.6	2541.7	2569.8	2600.5	2605.9	2602.2
20°	2511.4	2574.5	2616.1	2652.6	2673.4	2679.3	2679.3
22.5°	2561.3	2615.1	2655.8	2688.5	2705.7	2712.6	2710.5
25°	2596.0	2642.1	2666.9	2676.7	2681.2	2680.0	2667.6
27.5°	2548.5	2546.5	2530.9	2500.9	2478.4	2464.7	2449.1
30°	2458.0	2424.1	2385.1	2342.1	2286.8	2244.4	2231.4
32.5°	2323.1	2247.0	2180.9	2109.3	2049.8	2007.5	1989.8
35°	2062.2	1941.8	1843.5	1757.5	1695.1	1656.0	1643.0
37.5°	1752.6	1636.1	1514.3	1431.0	1379.2	1339.8	1325.0
40°	1555.8	1428.8	1322.7	1244.6	1191.2	1152.8	1152.2
42.5°	1376.1	1254.9	1155.0	1098.8	1041.2	1015.9	1015.7
45°	1126.7	1029.8	945.2	900.9	866.4	845.5	839.7
47.5°	932.9	852.7	796.4	761.1	733.0	719.7	711.1
50°	824.1	753.8	708.9	678.2	662.7	645.7	644.4
52.5°	733.4	676.7	641.7	616.9	597.0	586.9	587.2
55°	616.4	571.5	546.8	527.9	512.3	504.5	501.2
57.5°	519.3	485.6	467.7	450.3	443.7	437.6	435.9
60°	458.9	436.1	419.2	405.5	395.7	393.8	393.1
62.5°	409.0	385.1	373.4	362.8	355.7	352.7	351.5
65°	337.2	319.6	309.2	300.8	298.2	293.6	292.9
67.5°	271.8	261.3	254.4	248.5	245.0	244.8	244.8
70°	231.7	225.8	220.0	216.8	214.8	213.5	213.5
72.5°	197.4	193.1	188.3	186.5	186.1	184.8	184.3
75°	150.3	145.8	146.4	143.2	140.6	137.4	135.4
77.5°	106.6	103.4	102.7	102.3	100.1	99.7	100.8
80°	82.7	79.4	78.8	79.4	78.8	76.8	76.8
82.5°	62.9	60.2	59.5	59.1	58.5	59.1	58.0
85°	33.8	32.5	32.5	32.5	33.8	33.2	32.5
87.5°	15.1	14.7	15.2	14.8	15.0	14.3	14.8
90°	15.5	16.3	16.3	17.1	17.9	17.1	17.1
92.5°	120.3	95.7	79.4	69.9	65.5	62.7	62.7
95°	477.0	367.9	288.9	249.1	223.8	209.2	198.6
97.5°	844.2	764.6	679.6	621.2	572.2	547.8	530.8
100°	997.8	958.0	897.7	827.0	777.3	752.8	746.4
102.5°	1057.8	1069.3	1044.2	1000.8	964.8	939.1	933.9
105°	1052.4	1132.9	1166.4	1168.0	1161.5	1150.1	1145.2
107.5°	968.6	1082.1	1154.6	1194.8	1213.4	1221.6	1223.7
110°	903.4	1021.5	1111.0	1168.8	1203.0	1217.6	1225.0



TEST NUMBER: P333005-930

CATALOG NUMBER: SA4XXRDIP-C1195D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	846.1	957.7	1047.2	1112.8	1154.1	1174.7	1186.5
115°	780.6	875.8	953.9	1018.2	1067.1	1093.1	1099.6
117.5°	743.1	818.0	884.3	939.1	980.2	1006.5	1011.5
120°	726.8	792.0	849.7	896.1	932.0	953.1	962.1
122.5°	716.4	775.7	826.3	865.5	896.1	914.0	923.0
125°	699.9	756.1	800.9	833.5	857.0	872.5	877.4
127.5°	680.6	736.6	779.1	811.8	832.8	845.8	850.7
130°	665.0	720.3	763.4	796.8	817.2	830.2	835.1
132.5°	647.4	701.4	744.6	777.3	800.2	812.6	817.5
135°	621.0	670.7	711.3	744.0	766.7	779.8	784.6
137.5°	595.8	637.6	674.4	704.8	727.3	738.1	744.0
140°	579.5	616.1	650.3	678.8	696.8	708.1	714.6
142.5°	565.8	597.3	626.9	652.1	668.7	678.8	683.4
145°	547.0	571.4	594.2	614.5	628.4	636.5	640.6
147.5°	530.7	550.2	568.1	583.1	595.0	601.2	602.6
150°	520.9	537.2	551.9	564.8	575.4	580.3	581.1
152.5°	511.1	526.1	538.2	549.3	557.8	560.8	561.6
155°	497.3	509.5	519.3	527.4	533.9	536.4	536.4
157.5°	483.6	493.9	501.7	507.8	512.7	514.2	514.2
160°	474.5	483.5	490.0	494.9	499.8	500.6	500.6
162.5°	466.0	473.0	478.9	482.5	487.4	488.2	487.5
165°	453.4	459.0	463.1	466.4	469.6	468.8	468.0
167.5°	442.6	447.2	449.6	451.3	453.4	453.2	452.6
170°	435.5	438.7	441.2	442.8	443.6	442.8	442.8
172.5°	429.6	431.5	433.3	434.3	435.1	434.3	433.0
175°	421.6	423.2	423.2	423.2	424.9	423.2	421.6
177.5°	416.9	416.9	417.5	416.9	417.5	416.2	414.9
180°	414.3	414.3	414.3	414.3	414.3	414.3	414.3

(END OF REPORT)