

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333012-930

Luminaire Tested: **SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P333012-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7849.9 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333012-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333012-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43				
2	90	82	76	71	82	76	71	67	65	61	58	54	51	49	44	43	41	36				
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31				
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	30	27				
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	23				
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	24	21				
7	59	47	39	33	54	44	36	31	38	32	28	32	28	24	27	23	21	18				
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17				
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15				
10	48	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13726	13726	13726
5°	13757	13588	13674
10°	13671	13426	13426
15°	13514	13143	13046
20°	13298	12773	12538
25°	13023	12339	12026
30°	12755	11882	11384
35°	12458	11406	10738
40°	12101	10866	10043
45°	11772	10330	9334
50°	11396	9712	8584
55°	10994	9070	7769
60°	10551	8365	6936
65°	10147	7484	6117
70°	9557	6515	5193
75°	8812	5402	4223
80°	7685	4114	3873
85°	6512	3742	3492



TEST NUMBER: P333012-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	2.0
10°-20°	445.4	5.7
20°-30°	643.1	8.2
30°-40°	729.0	9.3
40°-50°	704.0	9.0
50°-60°	585.4	7.5
60°-70°	404.2	5.1
70°-80°	204.9	2.6
80°-90°	56.2	0.7
90°-100°	43.3	0.6
100°-110°	276.2	3.5
110°-120°	528.4	6.7
120°-130°	670.8	8.5
130°-140°	717.7	9.1
140°-150°	671.1	8.5
150°-160°	541.2	6.9
160°-170°	349.1	4.4
170°-180°	120.3	1.5
0°-30°	1248.2	15.9
0°-40°	1977.3	25.2
0°-60°	3266.6	41.6
0°-90°	3931.9	50.1
90°-120°	847.9	10.8
90°-150°	2907.4	37.0
90°-180°	3918.0	49.9
0°-180°	7849.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1698	1692	1677	1689	1687	161
15°	1617	1604	1573	1570	1561	455
25°	1462	1437	1385	1364	1350	673
35°	1264	1221	1157	1114	1090	790
45°	1031	981	905	843	818	795
55°	781	727	644	579	552	698
65°	531	474	392	338	320	524
75°	282	234	173	144	135	298
85°	70	46	40	38	38	79
90°	3	13	21	26	28	6
95°	52	22	21	26	28	67
105°	285	291	296	302	270	298
115°	532	535	534	536	536	524
125°	748	752	750	753	754	668
135°	928	928	931	933	935	715
145°	1070	1073	1073	1074	1076	669
155°	1174	1174	1172	1175	1173	541
165°	1238	1234	1234	1240	1232	350
175°	1267	1261	1262	1269	1259	121
180°	1267	1267	1267	1267	1267	



TEST NUMBER: P333012-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1704.4	1703.5	1702.6	1701.6	1700.7	1699.0	1696.5	1693.9	1691.3	1688.8	1691.3
5°	1697.6	1696.5	1695.3	1694.2	1693.1	1690.7	1687.3	1683.8	1680.3	1676.8	1679.7
7.5°	1682.3	1681.1	1679.8	1678.6	1677.4	1674.5	1670.1	1665.6	1661.0	1656.5	1658.4
10°	1667.7	1666.2	1664.8	1663.4	1661.9	1658.6	1653.4	1648.2	1643.0	1637.8	1638.9
12.5°	1648.9	1647.3	1645.6	1643.9	1642.3	1638.3	1632.2	1626.1	1619.9	1613.8	1614.5
15°	1616.9	1614.3	1611.8	1609.2	1606.5	1601.6	1594.4	1587.1	1579.9	1572.6	1572.1
17.5°	1578.2	1574.3	1570.6	1566.8	1563.1	1556.9	1548.2	1539.5	1530.8	1522.2	1520.5
20°	1547.9	1544.2	1540.4	1536.7	1532.9	1526.1	1516.3	1506.4	1496.6	1486.8	1484.4
22.5°	1514.6	1510.4	1506.2	1501.9	1497.7	1490.4	1479.8	1469.3	1458.7	1448.2	1444.7
25°	1462.0	1456.8	1451.6	1446.4	1441.2	1432.6	1420.8	1408.9	1397.1	1385.2	1380.3
27.5°	1406.8	1400.3	1393.8	1387.2	1380.6	1371.1	1358.4	1345.7	1333.0	1320.4	1314.3
30°	1368.3	1361.1	1353.8	1346.5	1339.4	1328.9	1315.3	1301.7	1288.2	1274.6	1267.3
32.5°	1327.6	1319.5	1311.3	1303.2	1295.0	1283.9	1269.8	1255.8	1241.7	1227.7	1219.3
35°	1264.1	1254.8	1245.6	1236.3	1227.1	1215.2	1200.8	1186.3	1171.8	1157.4	1147.5
37.5°	1196.2	1186.6	1177.0	1167.5	1158.0	1145.2	1129.2	1113.1	1097.1	1081.1	1070.1
40°	1148.3	1138.7	1129.2	1119.7	1110.0	1097.1	1080.6	1064.0	1047.6	1031.1	1019.0
42.5°	1102.4	1092.4	1082.4	1072.4	1062.4	1048.8	1031.6	1014.4	997.3	980.1	967.7
45°	1031.1	1020.3	1009.7	999.0	988.3	974.2	956.9	939.6	922.2	904.8	890.6
47.5°	957.4	946.3	935.3	924.2	913.2	898.6	880.6	862.5	844.5	826.5	811.7
50°	907.4	896.1	884.8	873.6	862.3	847.3	828.8	810.3	791.8	773.3	758.9
52.5°	856.4	845.3	834.3	823.2	812.2	797.1	778.2	759.2	740.2	721.2	706.5
55°	781.1	769.6	758.0	746.4	734.8	719.7	700.8	682.1	663.2	644.4	629.4
57.5°	706.6	694.6	682.6	670.6	658.5	643.3	624.8	606.2	587.7	569.2	553.9
60°	653.5	642.0	630.4	618.8	607.2	592.2	573.7	555.2	536.6	518.1	503.1
62.5°	605.6	593.6	581.6	569.6	557.5	542.0	523.0	504.0	485.0	466.1	452.2
65°	531.2	518.7	506.3	493.8	481.4	465.9	447.4	428.9	410.4	391.8	379.4
67.5°	453.8	441.9	430.0	418.1	406.2	391.6	374.4	357.3	340.1	322.9	312.2
70°	404.9	392.7	380.6	368.4	356.3	341.9	325.5	309.0	292.5	276.0	266.4
72.5°	352.8	341.9	330.8	319.8	308.8	295.5	280.0	264.4	248.8	233.3	225.1
75°	282.5	271.8	261.1	250.4	239.7	227.6	213.9	200.3	186.8	173.2	166.5
77.5°	211.2	202.1	193.0	183.9	174.8	164.8	153.8	142.8	131.8	120.8	116.9
80°	165.3	156.9	148.5	140.1	131.8	123.3	114.5	105.9	97.2	88.5	87.6
82.5°	125.8	118.1	110.4	102.6	95.0	88.6	83.6	78.7	73.7	68.7	68.1
85°	70.3	64.5	58.7	52.9	47.1	43.9	43.0	42.1	41.3	40.4	39.8
87.5°	24.5	23.2	21.8	20.4	19.0	18.3	18.4	18.5	18.7	18.8	18.8
90°	2.9	5.1	7.5	9.8	12.1	14.1	15.8	17.4	19.2	20.9	22.1
92.5°	11.9	12.1	12.2	12.3	12.5	13.4	15.0	16.7	18.4	20.1	21.4
95°	52.1	44.9	37.7	30.7	23.5	20.0	20.2	20.4	20.6	20.9	22.1
97.5°	110.6	115.1	119.6	124.0	128.5	119.0	95.5	72.0	48.5	25.0	25.1
100°	155.4	159.1	163.0	166.7	170.6	157.9	128.8	99.8	70.8	41.7	38.1
102.5°	205.4	208.1	210.9	213.7	216.5	216.0	212.2	208.4	204.6	200.8	162.2
105°	285.1	286.4	287.6	288.9	290.2	291.4	292.4	293.4	294.5	295.5	297.5
107.5°	359.2	359.9	360.5	361.1	361.7	362.8	364.2	365.7	367.0	368.5	369.4
110°	409.3	409.9	410.5	411.2	411.8	412.7	414.0	415.2	416.5	417.8	418.2



TEST NUMBER: P333012-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	457.8	458.9	460.0	461.1	462.3	463.2	463.7	464.3	465.0	465.5	465.5
115°	532.4	533.0	533.7	534.3	534.9	535.2	534.9	534.8	534.5	534.3	534.8
117.5°	599.7	600.5	601.4	602.2	603.0	603.6	604.1	604.6	605.1	605.5	605.4
120°	645.1	646.0	646.9	647.7	648.5	648.8	648.7	648.4	648.2	648.0	648.4
122.5°	687.5	688.1	688.6	689.1	689.6	690.0	690.3	690.6	690.9	691.2	691.5
125°	748.4	749.3	750.1	750.9	751.8	752.0	751.5	751.1	750.7	750.3	750.9
127.5°	806.0	806.2	806.4	806.7	806.8	807.4	808.4	809.3	810.3	811.3	811.1
130°	843.1	843.3	843.6	843.8	844.0	844.4	845.1	845.6	846.3	846.9	847.1
132.5°	877.3	877.6	878.0	878.4	878.7	879.4	880.1	880.9	881.7	882.6	882.7
135°	928.4	928.2	928.0	927.7	927.6	927.9	928.7	929.5	930.4	931.2	931.6
137.5°	973.7	973.8	973.9	974.0	974.0	974.5	975.4	976.4	977.3	978.2	978.7
140°	1003.2	1003.6	1004.0	1004.5	1004.9	1005.3	1005.8	1006.2	1006.6	1007.1	1007.6
142.5°	1029.7	1030.5	1031.3	1032.0	1032.8	1033.3	1033.6	1033.8	1034.0	1034.3	1034.8
145°	1070.5	1071.1	1071.8	1072.4	1073.0	1073.3	1073.3	1073.3	1073.3	1073.3	1073.6
147.5°	1102.9	1104.1	1105.2	1106.4	1107.6	1108.1	1107.9	1107.7	1107.4	1107.3	1107.4
150°	1126.4	1127.2	1128.0	1128.9	1129.8	1130.1	1129.8	1129.7	1129.4	1129.2	1129.2
152.5°	1146.1	1146.8	1147.5	1148.1	1148.8	1148.9	1148.6	1148.2	1147.8	1147.5	1147.8
155°	1173.8	1173.9	1174.2	1174.4	1174.6	1174.4	1173.8	1173.1	1172.5	1171.8	1172.7
157.5°	1197.0	1196.9	1196.8	1196.7	1196.5	1196.1	1195.4	1194.7	1194.0	1193.3	1194.3
160°	1210.7	1210.1	1209.4	1208.8	1208.2	1207.8	1207.5	1207.3	1207.1	1206.9	1208.2
162.5°	1222.8	1222.1	1221.2	1220.4	1219.6	1219.1	1218.9	1218.7	1218.5	1218.3	1219.5
165°	1238.2	1237.1	1236.1	1235.0	1234.0	1233.5	1233.5	1233.5	1233.5	1233.5	1235.1
167.5°	1250.3	1249.2	1248.1	1247.0	1245.9	1245.3	1245.2	1245.0	1245.0	1244.8	1246.7
170°	1257.1	1255.9	1254.6	1253.4	1252.1	1251.6	1251.7	1252.0	1252.1	1252.4	1254.1
172.5°	1261.7	1260.4	1259.1	1257.8	1256.6	1256.1	1256.3	1256.5	1256.7	1256.9	1258.6
175°	1266.6	1265.3	1264.0	1262.8	1261.5	1261.0	1261.2	1261.4	1261.7	1261.8	1263.7
177.5°	1268.9	1267.7	1266.5	1265.3	1264.1	1263.7	1264.0	1264.4	1264.8	1265.1	1266.4
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P333012-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1693.9	1696.5	1699.0	1700.1	1699.9	1699.7	1699.4	1699.2
5°	1682.6	1685.5	1688.4	1689.5	1689.0	1688.4	1687.8	1687.3
7.5°	1660.2	1662.1	1663.9	1664.4	1663.5	1662.6	1661.6	1660.7
10°	1640.1	1641.2	1642.4	1642.4	1641.2	1640.1	1638.9	1637.8
12.5°	1615.2	1615.9	1616.6	1616.1	1614.5	1612.9	1611.3	1609.6
15°	1571.5	1570.9	1570.3	1569.0	1567.0	1565.0	1563.0	1561.0
17.5°	1518.9	1517.3	1515.6	1513.4	1510.3	1507.2	1504.1	1501.0
20°	1482.1	1479.8	1477.5	1474.5	1470.7	1467.0	1463.1	1459.4
22.5°	1441.3	1437.8	1434.4	1431.1	1428.0	1424.9	1421.9	1418.8
25°	1375.3	1370.4	1365.5	1361.6	1358.7	1355.8	1352.9	1350.1
27.5°	1308.2	1302.1	1296.1	1290.9	1286.8	1282.6	1278.5	1274.3
30°	1260.0	1252.9	1245.6	1239.7	1235.0	1230.4	1225.8	1221.2
32.5°	1210.9	1202.5	1194.1	1187.7	1183.3	1178.9	1174.5	1170.1
35°	1137.7	1127.9	1118.0	1110.5	1105.3	1100.1	1094.9	1089.6
37.5°	1059.1	1048.1	1037.1	1029.0	1023.8	1018.6	1013.4	1008.2
40°	1006.8	994.7	982.5	973.8	968.6	963.4	958.2	953.0
42.5°	955.3	942.9	930.5	921.6	916.2	910.8	905.3	899.8
45°	876.4	862.3	848.1	838.4	833.2	828.0	822.8	817.6
47.5°	797.0	782.4	767.7	757.4	751.7	746.0	740.2	734.5
50°	744.4	729.9	715.4	705.5	700.0	694.5	689.0	683.5
52.5°	691.9	677.2	662.4	652.2	646.5	640.8	635.0	629.3
55°	614.3	599.3	584.2	574.0	568.5	563.0	557.5	552.0
57.5°	538.7	523.3	508.1	498.4	494.2	490.0	485.8	481.7
60°	488.0	473.0	458.0	448.2	443.5	438.9	434.2	429.6
62.5°	438.3	424.4	410.5	401.7	398.0	394.4	390.6	386.9
65°	367.0	354.6	342.1	334.1	330.7	327.2	323.8	320.2
67.5°	301.5	290.7	280.1	272.8	269.0	265.1	261.3	257.5
70°	256.9	247.4	237.8	231.6	228.7	225.8	222.9	220.0
72.5°	217.0	208.8	200.6	195.3	192.6	190.0	187.3	184.6
75°	159.9	153.2	146.5	142.4	140.6	138.8	137.1	135.4
77.5°	113.1	109.2	105.3	103.1	102.6	102.1	101.6	101.0
80°	86.8	85.9	85.0	84.5	84.2	83.9	83.6	83.3
82.5°	67.5	66.9	66.2	65.7	65.5	65.1	64.9	64.6
85°	39.2	38.6	38.1	37.7	37.7	37.7	37.7	37.7
87.5°	18.8	18.8	18.8	19.0	19.3	19.6	20.0	20.3
90°	23.4	24.6	25.9	26.7	27.1	27.6	28.0	28.5
92.5°	22.6	23.9	25.1	25.8	25.9	26.0	26.1	26.2
95°	23.4	24.6	25.9	26.7	26.8	27.1	27.2	27.5
97.5°	25.3	25.4	25.5	25.7	25.9	26.1	26.3	26.5
100°	34.5	31.0	27.4	25.7	25.9	26.1	26.3	26.5
102.5°	123.6	85.0	46.4	27.1	27.1	27.2	27.2	27.3
105°	299.4	301.3	303.1	300.3	292.7	285.1	277.6	270.0
107.5°	370.4	371.3	372.2	373.1	373.9	374.7	375.4	376.3
110°	418.7	419.1	419.5	420.0	420.6	421.3	421.9	422.5



TEST NUMBER: P333012-930

CATALOG NUMBER: SA4XXRDIP-C1195D1205U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	465.4	465.3	465.2	465.5	466.4	467.2	468.0	468.7
115°	535.2	535.6	536.0	536.2	536.2	536.2	536.2	536.2
117.5°	605.4	605.3	605.2	605.1	605.0	605.0	604.9	604.8
120°	648.8	649.2	649.6	649.6	649.2	648.8	648.4	648.0
122.5°	691.7	691.9	692.2	692.1	691.7	691.3	690.8	690.4
125°	751.5	752.2	752.8	753.3	753.4	753.7	753.9	754.1
127.5°	811.1	810.9	810.8	810.7	810.5	810.3	810.2	810.0
130°	847.3	847.6	847.7	847.8	847.8	847.8	847.8	847.8
132.5°	883.0	883.2	883.4	883.4	883.2	883.1	882.9	882.7
135°	932.1	932.5	932.9	933.4	933.8	934.2	934.6	935.0
137.5°	979.2	979.6	980.1	980.2	980.2	980.0	979.8	979.7
140°	1008.3	1008.9	1009.6	1010.0	1010.2	1010.4	1010.6	1010.8
142.5°	1035.3	1035.7	1036.2	1036.4	1036.5	1036.5	1036.6	1036.6
145°	1073.7	1074.0	1074.2	1074.5	1074.9	1075.3	1075.8	1076.2
147.5°	1107.6	1107.7	1107.9	1108.1	1108.3	1108.6	1108.7	1109.0
150°	1129.2	1129.2	1129.2	1129.4	1129.5	1129.8	1130.0	1130.2
152.5°	1148.1	1148.4	1148.8	1148.8	1148.8	1148.6	1148.5	1148.3
155°	1173.5	1174.4	1175.3	1175.3	1174.7	1174.0	1173.5	1172.8
157.5°	1195.5	1196.5	1197.7	1197.7	1196.5	1195.5	1194.3	1193.3
160°	1209.4	1210.7	1211.9	1211.9	1210.7	1209.4	1208.2	1206.9
162.5°	1220.8	1222.1	1223.4	1223.3	1221.8	1220.4	1219.0	1217.5
165°	1236.8	1238.5	1240.2	1240.1	1238.2	1236.2	1234.4	1232.5
167.5°	1248.5	1250.3	1252.2	1252.1	1250.0	1247.9	1245.8	1243.7
170°	1255.7	1257.4	1259.1	1258.9	1256.8	1254.7	1252.6	1250.5
172.5°	1260.3	1262.0	1263.6	1263.4	1261.1	1258.8	1256.5	1254.3
175°	1265.7	1267.5	1269.4	1269.1	1266.6	1264.0	1261.5	1259.0
177.5°	1267.8	1269.1	1270.5	1270.2	1268.1	1266.1	1264.0	1262.1
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6

(END OF REPORT)