

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331620-940

Luminaire Tested: **SA2XXRDIP-C290D330U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331620-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2062.2 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331620-940
CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331620-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33				33
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	34	33	28				28
4	74	64	56	51	68	59	52	47	50	45	41	41	38	35	33	31	28	25				25
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25	22				22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19				19
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20	17				17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				16
9	51	39	31	27	46	36	30	25	31	26	22	26	22	19	21	19	16	14				14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7227	7227	7227
5°	7254	7136	7175
10°	7199	7020	6960
15°	7116	6812	6614
20°	7002	6515	6189
25°	6885	6178	5772
30°	6721	5830	5243
35°	6564	5454	4776
40°	6403	5063	4234
45°	6215	4624	3747
50°	6023	4182	3265
55°	5827	3704	2806
60°	5596	3203	2328
65°	5337	2690	2120
70°	5032	2219	1950
75°	4648	2021	1822
80°	4100	1804	1655
85°	3223	1426	1426



TEST NUMBER: P331620-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	2.0
10°-20°	115.0	5.6
20°-30°	161.6	7.8
30°-40°	176.2	8.5
40°-50°	162.0	7.9
50°-60°	127.2	6.2
60°-70°	82.9	4.0
70°-80°	42.8	2.1
80°-90°	12.6	0.6
90°-100°	65.5	3.2
100°-110°	222.3	10.8
110°-120°	236.2	11.5
120°-130°	194.4	9.4
130°-140°	156.1	7.6
140°-150°	118.0	5.7
150°-160°	82.9	4.0
160°-170°	48.8	2.4
170°-180°	15.9	0.8
0°-30°	318.5	15.4
0°-40°	494.7	24.0
0°-60°	783.8	38.0
0°-90°	922.1	44.7
90°-120°	524.0	25.4
90°-150°	992.5	48.1
90°-180°	1140.0	55.3
0°-180°	2062.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	448	448	448	448	448	
5°	448	445	440	444	443	42
15°	426	421	408	400	396	120
25°	386	373	347	331	324	178
35°	333	312	277	252	242	208
45°	272	244	202	175	164	210
55°	207	175	132	108	100	185
65°	140	107	70	57	56	138
75°	74	47	32	30	29	79
85°	17	9	8	8	8	21
90°	0	4	11	10	10	1
95°	11	27	124	47	36	12
105°	38	58	233	417	355	41
115°	68	86	195	403	467	67
125°	94	112	188	327	379	84
135°	111	132	186	274	314	86
145°	127	146	185	229	251	79
155°	144	155	179	203	211	66
165°	157	162	172	182	185	44
175°	164	164	165	167	167	16
180°	164	164	164	164	164	



TEST NUMBER: P331620-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	449.2	448.9	448.5	448.2	447.8	447.2	446.4	445.7	444.9	444.1	444.8
5°	447.6	447.2	446.7	446.3	445.9	445.0	443.8	442.6	441.5	440.3	441.1
7.5°	443.0	442.5	441.8	441.3	440.8	439.8	438.5	437.0	435.7	434.4	434.5
10°	439.1	438.5	437.8	437.2	436.6	435.3	433.5	431.8	430.0	428.2	427.9
12.5°	434.3	433.5	432.7	431.9	431.1	429.6	427.3	425.0	422.7	420.4	419.9
15°	425.7	424.7	423.7	422.8	421.8	419.7	416.7	413.7	410.5	407.5	405.8
17.5°	415.3	413.8	412.2	410.7	409.2	406.5	402.6	398.7	394.8	390.8	388.8
20°	407.5	405.7	403.9	402.1	400.3	397.2	392.6	388.2	383.7	379.2	376.9
22.5°	399.1	397.1	395.0	393.1	391.0	387.4	382.4	377.3	372.3	367.2	364.3
25°	386.5	383.5	380.7	377.8	375.0	370.5	364.5	358.6	352.7	346.8	343.0
27.5°	371.2	368.1	365.0	361.9	358.6	353.7	347.1	340.4	333.7	327.0	322.7
30°	360.5	357.1	353.7	350.3	346.9	341.5	334.3	327.2	319.9	312.7	308.2
32.5°	350.2	346.2	342.1	338.1	334.1	328.5	321.2	313.8	306.5	299.1	293.9
35°	333.0	328.4	323.8	319.2	314.6	308.4	300.4	292.5	284.6	276.7	271.0
37.5°	315.8	310.8	305.7	300.7	295.6	288.9	280.4	272.0	263.6	255.1	248.9
40°	303.8	298.5	293.0	287.6	282.2	275.2	266.4	257.7	249.0	240.2	233.8
42.5°	291.5	285.8	280.1	274.5	268.8	261.4	252.4	243.3	234.3	225.3	218.7
45°	272.2	266.2	260.1	254.1	248.1	240.3	230.9	221.4	212.0	202.5	196.2
47.5°	253.4	247.0	240.7	234.3	227.8	219.8	210.0	200.3	190.5	180.7	174.4
50°	239.8	233.4	227.0	220.6	214.3	206.1	196.2	186.3	176.4	166.5	160.2
52.5°	226.5	219.8	213.2	206.5	199.8	191.6	181.9	172.3	162.6	152.8	146.9
55°	207.0	200.0	193.0	185.9	178.9	170.6	160.8	151.1	141.3	131.6	126.3
57.5°	187.0	179.8	172.5	165.4	158.2	149.9	140.5	131.3	121.9	112.5	107.5
60°	173.3	166.2	159.0	151.8	144.5	136.3	127.1	117.8	108.5	99.2	94.6
62.5°	160.1	152.9	145.7	138.5	131.3	123.2	114.4	105.6	96.8	87.9	83.6
65°	139.7	132.4	125.2	117.9	110.6	102.9	94.8	86.7	78.6	70.4	67.4
67.5°	120.1	112.9	105.7	98.4	91.2	83.9	76.6	69.4	62.1	54.8	53.3
70°	106.6	99.5	92.5	85.5	78.5	71.9	65.6	59.4	53.2	47.0	46.1
72.5°	93.5	86.9	80.1	73.4	66.6	60.8	55.8	50.8	45.8	40.8	40.0
75°	74.5	68.2	62.0	55.6	49.3	44.7	41.6	38.5	35.5	32.4	31.7
77.5°	55.8	50.3	44.8	39.2	33.7	30.2	28.7	27.3	25.8	24.3	24.0
80°	44.1	39.6	35.0	30.4	25.8	23.0	22.1	21.2	20.3	19.4	19.1
82.5°	33.4	29.9	26.3	22.7	19.2	17.0	16.4	15.8	15.2	14.6	14.4
85°	17.4	15.5	13.6	11.8	9.9	8.7	8.5	8.2	7.9	7.7	7.7
87.5°	5.3	4.9	4.5	4.1	3.7	3.6	3.8	4.3	4.6	4.7	4.6
90°	0.4	1.2	2.5	3.1	3.7	4.7	6.3	8.5	10.4	10.7	10.4
92.5°	3.8	5.5	7.8	9.2	11.3	14.3	21.4	31.5	40.4	40.9	34.6
95°	11.1	12.3	15.4	18.3	23.3	30.9	45.4	72.8	109.3	123.5	108.1
97.5°	17.9	19.6	23.0	27.3	33.1	41.6	59.8	98.1	158.8	210.8	221.1
100°	24.3	25.2	28.0	33.1	39.4	48.2	64.9	103.3	171.4	248.9	294.3
102.5°	30.1	30.8	33.6	38.6	45.2	54.0	69.5	103.6	166.6	250.1	321.5
105°	38.4	39.7	41.9	46.6	53.6	62.4	77.2	105.2	157.2	233.4	317.3
107.5°	47.5	48.5	50.6	55.0	61.9	70.8	85.2	109.6	152.6	215.5	289.6
110°	53.6	54.8	56.7	60.8	67.4	76.6	90.4	113.1	151.6	207.0	272.2



TEST NUMBER: P331620-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	59.1	60.4	62.5	66.3	72.7	82.1	95.5	116.9	151.8	201.4	260.1
115°	67.8	69.3	71.2	75.0	81.3	89.8	103.3	122.5	153.1	195.4	245.1
117.5°	76.7	77.9	79.8	83.2	89.3	98.1	110.6	128.6	155.4	192.3	235.7
120°	82.2	83.5	85.4	88.2	94.5	103.3	115.7	132.7	156.9	190.6	230.6
122.5°	87.6	88.5	90.4	93.5	99.8	108.9	120.4	136.2	158.6	189.6	226.3
125°	94.5	95.5	97.4	101.1	107.5	116.3	127.6	141.8	161.3	187.8	220.3
127.5°	100.0	101.3	104.0	108.2	114.1	123.2	134.3	147.0	164.0	186.7	214.5
130°	103.3	104.6	107.7	112.2	118.5	127.2	138.3	150.3	166.0	186.2	210.8
132.5°	106.4	107.9	111.3	115.9	122.5	131.3	141.9	153.6	168.1	185.9	207.8
135°	110.9	112.2	115.9	120.6	128.0	136.7	146.9	157.8	170.5	185.6	203.5
137.5°	115.2	116.7	120.5	125.6	132.7	140.9	150.9	161.1	172.6	185.5	200.5
140°	118.5	119.8	123.5	128.6	135.5	143.7	153.1	162.9	173.6	185.3	198.8
142.5°	121.7	122.8	126.3	131.3	138.0	145.7	154.9	164.4	174.3	185.3	197.1
145°	126.6	128.0	131.1	135.8	142.1	149.0	157.6	166.4	175.1	184.6	194.7
147.5°	132.0	132.9	135.9	140.3	145.5	151.7	159.7	167.5	175.4	183.5	192.3
150°	135.5	136.4	138.9	143.0	147.8	153.5	160.7	167.9	175.1	182.7	190.3
152.5°	139.0	139.5	142.0	145.5	150.1	155.2	161.7	168.2	174.7	181.5	188.5
155°	144.0	144.3	146.2	149.6	153.1	157.8	163.2	168.5	173.9	179.2	185.3
157.5°	148.1	148.5	150.0	153.0	155.8	159.7	164.3	168.5	172.5	177.0	182.2
160°	150.9	151.2	152.5	155.0	157.6	161.0	164.8	168.5	171.7	175.5	179.9
162.5°	153.7	153.5	154.8	156.8	159.1	161.8	165.1	168.3	170.9	174.2	177.9
165°	156.9	156.6	157.2	159.1	160.7	162.6	165.4	167.6	169.5	171.7	174.5
167.5°	159.5	159.2	159.7	161.0	162.1	163.3	165.3	167.2	168.1	169.5	171.3
170°	161.3	160.7	161.0	161.9	162.6	163.5	165.1	166.7	167.3	168.3	169.5
172.5°	162.3	161.9	161.8	162.7	163.1	163.8	164.9	165.9	166.3	166.7	167.7
175°	163.5	163.2	162.9	163.5	163.5	163.8	164.4	165.1	164.8	165.1	165.4
177.5°	164.1	163.5	163.4	163.8	163.8	163.8	164.1	164.6	164.1	163.8	164.1
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8



TEST NUMBER: P331620-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	445.5	446.2	446.9	447.2	447.1	446.9	446.7	446.7
5°	441.9	442.7	443.5	443.8	443.5	443.3	443.0	442.7
7.5°	434.8	435.1	435.2	435.2	434.7	434.2	433.7	433.3
10°	427.7	427.4	427.1	426.7	426.1	425.6	425.1	424.5
12.5°	419.5	418.9	418.5	417.8	416.9	416.0	415.1	414.2
15°	404.1	402.3	400.6	399.4	398.5	397.5	396.6	395.7
17.5°	386.7	384.7	382.7	380.9	379.3	377.8	376.2	374.7
20°	374.7	372.4	370.1	368.0	366.0	364.1	362.1	360.2
22.5°	361.4	358.5	355.6	353.4	351.9	350.4	348.9	347.5
25°	339.4	335.6	332.0	329.5	328.1	326.7	325.4	324.0
27.5°	318.3	314.1	309.8	306.6	304.4	302.3	300.1	298.0
30°	303.5	299.0	294.4	290.9	288.4	286.0	283.6	281.2
32.5°	288.6	283.4	278.1	274.4	272.2	269.8	267.5	265.3
35°	265.4	259.7	254.0	250.1	248.2	246.2	244.2	242.3
37.5°	242.6	236.4	230.2	225.9	223.6	221.3	219.1	216.8
40°	227.5	221.1	214.6	210.3	207.9	205.6	203.2	200.9
42.5°	212.0	205.5	198.9	194.5	192.2	189.9	187.6	185.4
45°	189.8	183.3	177.0	172.7	170.6	168.4	166.2	164.1
47.5°	168.0	161.7	155.3	151.1	149.2	147.2	145.3	143.3
50°	154.1	147.8	141.6	137.6	135.7	133.8	131.9	130.0
52.5°	140.9	134.9	128.9	125.0	123.3	121.5	119.8	118.1
55°	120.8	115.5	110.0	106.5	104.8	103.1	101.4	99.7
57.5°	102.6	97.6	92.7	89.5	88.1	86.7	85.2	83.7
60°	90.1	85.5	80.9	77.8	76.4	75.0	73.6	72.1
62.5°	79.2	74.8	70.4	67.8	66.9	66.1	65.2	64.3
65°	64.4	61.3	58.2	56.5	56.3	56.0	55.7	55.5
67.5°	52.0	50.6	49.1	48.3	48.0	47.7	47.4	47.2
70°	45.2	44.3	43.4	42.8	42.4	42.0	41.6	41.3
72.5°	39.3	38.5	37.8	37.4	37.1	36.9	36.6	36.5
75°	31.1	30.5	29.9	29.5	29.4	29.3	29.2	29.2
77.5°	23.5	23.2	22.8	22.6	22.5	22.3	22.2	22.0
80°	18.7	18.4	18.0	17.8	17.8	17.8	17.8	17.8
82.5°	14.2	13.9	13.7	13.6	13.6	13.6	13.6	13.6
85°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	4.5	4.3	4.3	4.4	4.4	4.4	4.4	4.4
90°	10.1	9.5	10.1	10.4	10.4	10.4	10.4	10.4
92.5°	27.5	23.5	21.0	19.0	18.7	17.7	17.9	17.5
95°	82.6	63.3	50.1	43.2	39.1	36.6	35.6	35.9
97.5°	192.6	157.6	123.5	100.8	85.7	77.9	73.4	70.7
100°	287.7	248.6	205.5	167.3	141.2	127.6	118.5	112.8
102.5°	349.9	341.1	309.5	269.1	240.7	217.6	206.2	198.5
105°	382.8	418.4	422.5	412.1	392.5	373.0	359.4	355.1
107.5°	359.1	412.8	445.5	460.7	463.2	462.2	459.4	453.6
110°	338.7	395.1	435.4	461.3	474.8	480.8	483.7	483.3



TEST NUMBER: P331620-940

CATALOG NUMBER: SA2XXRDIP-C290D330U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	320.0	374.2	417.2	446.9	465.7	475.7	481.1	482.8
115°	297.1	345.6	386.9	419.4	441.8	456.2	464.4	467.3
117.5°	279.8	322.4	359.9	390.3	413.1	428.5	437.0	439.4
120°	271.3	310.3	343.8	372.4	394.5	409.3	418.4	421.6
122.5°	264.5	300.2	331.9	357.8	377.6	392.2	400.3	402.9
125°	254.6	287.0	314.8	338.4	356.7	368.6	376.5	379.1
127.5°	244.8	274.2	300.3	322.1	338.0	349.3	356.1	358.1
130°	238.5	265.6	290.5	311.3	326.7	337.4	343.8	346.3
132.5°	232.5	257.5	280.4	300.0	315.1	325.8	331.6	333.9
135°	224.0	244.8	265.6	283.2	296.8	307.2	312.9	314.1
137.5°	217.3	234.7	251.2	266.5	278.9	287.8	292.8	294.7
140°	212.9	228.1	242.6	256.5	266.5	274.7	279.5	281.3
142.5°	209.5	222.3	234.8	246.4	255.9	263.4	267.6	268.0
145°	204.5	214.9	224.6	233.8	241.3	246.7	249.9	250.7
147.5°	200.6	208.8	216.4	223.1	229.3	233.6	235.8	236.4
150°	197.9	204.8	211.4	217.0	221.8	225.6	227.5	227.8
152.5°	195.1	201.5	207.1	212.0	215.8	219.0	220.4	220.5
155°	191.3	196.3	201.0	204.5	207.9	210.2	211.4	210.8
157.5°	186.8	191.0	194.9	197.7	200.1	202.0	202.5	202.5
160°	184.0	187.4	190.9	193.1	195.4	196.9	197.2	197.2
162.5°	181.2	184.2	187.2	188.9	191.1	192.2	192.4	192.2
165°	177.1	179.2	181.5	182.7	184.0	185.3	185.3	184.9
167.5°	173.1	174.8	176.3	177.5	178.0	178.7	178.6	178.3
170°	171.1	172.0	173.3	173.9	174.2	175.1	174.9	174.2
172.5°	168.8	169.5	170.5	170.9	171.2	171.7	171.3	170.9
175°	166.4	166.7	167.0	167.3	167.3	167.6	167.3	166.7
177.5°	164.6	164.6	164.9	164.9	164.9	164.9	164.6	164.1
180°	163.8	163.8	163.8	163.8	163.8	163.8	163.8	163.8

(END OF REPORT)