

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331625-940

Luminaire Tested: **SA2XXRDIP-C290D530U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331625-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2607.9 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331625-940
CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331625-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	58	71	64	58	53	52	48	44	41	38	35	30	29	27	22
4	73	62	55	49	65	57	50	45	46	42	38	36	33	31	27	25	24	20
5	67	56	48	42	60	51	44	39	41	37	33	33	29	27	25	23	21	17
6	61	50	42	37	55	46	39	34	37	32	29	30	26	23	23	20	18	15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	16	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	13	11
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7227	7227	7227
5°	7254	7136	7175
10°	7199	7020	6960
15°	7116	6812	6614
20°	7002	6515	6189
25°	6885	6178	5772
30°	6721	5830	5243
35°	6564	5454	4776
40°	6403	5063	4234
45°	6215	4624	3747
50°	6023	4182	3265
55°	5827	3704	2806
60°	5596	3203	2328
65°	5337	2690	2120
70°	5032	2219	1950
75°	4648	2021	1822
80°	4100	1804	1655
85°	3223	1426	1426



TEST NUMBER: P331625-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	1.6
10°-20°	115.0	4.4
20°-30°	161.6	6.2
30°-40°	176.2	6.8
40°-50°	162.0	6.2
50°-60°	127.2	4.9
60°-70°	82.9	3.2
70°-80°	42.8	1.6
80°-90°	13.5	0.5
90°-100°	38.2	1.5
100°-110°	118.6	4.5
110°-120°	202.7	7.8
120°-130°	266.6	10.2
130°-140°	299.2	11.5
140°-150°	293.4	11.2
150°-160°	246.1	9.4
160°-170°	163.2	6.3
170°-180°	57.0	2.2
0°-30°	318.5	12.2
0°-40°	494.7	19.0
0°-60°	783.8	30.1
0°-90°	923.0	35.4
90°-120°	359.5	13.8
90°-150°	1218.6	46.7
90°-180°	1685.0	64.6
0°-180°	2607.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	448	448	448	448	448	
5°	448	445	440	444	443	42
15°	426	421	408	400	396	120
25°	386	373	347	331	324	178
35°	333	312	277	252	242	208
45°	272	244	202	175	164	210
55°	207	175	132	108	100	185
65°	140	107	70	57	56	138
75°	74	47	32	30	29	79
85°	17	9	8	8	8	21
90°	0	7	18	17	17	2
95°	26	31	32	32	32	30
105°	109	111	112	113	113	115
115°	203	206	206	205	203	201
125°	296	300	299	298	297	264
135°	383	388	390	389	387	296
145°	465	468	471	472	470	290
155°	531	533	534	537	536	244
165°	578	578	578	581	579	163
175°	602	600	599	602	600	57
180°	602	602	602	602	602	



TEST NUMBER: P331625-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	449.2	448.9	448.5	448.2	447.8	447.2	446.4	445.7	444.9	444.1	444.8
5°	447.6	447.2	446.7	446.3	445.9	445.0	443.8	442.6	441.5	440.3	441.1
7.5°	443.0	442.5	441.8	441.3	440.8	439.8	438.5	437.0	435.7	434.4	434.5
10°	439.1	438.5	437.8	437.2	436.6	435.3	433.5	431.8	430.0	428.2	427.9
12.5°	434.3	433.5	432.7	431.9	431.1	429.6	427.3	425.0	422.7	420.4	419.9
15°	425.7	424.7	423.7	422.8	421.8	419.7	416.7	413.7	410.5	407.5	405.8
17.5°	415.3	413.8	412.2	410.7	409.2	406.5	402.6	398.7	394.8	390.8	388.8
20°	407.5	405.7	403.9	402.1	400.3	397.2	392.6	388.2	383.7	379.2	376.9
22.5°	399.1	397.1	395.0	393.1	391.0	387.4	382.4	377.3	372.3	367.2	364.3
25°	386.5	383.5	380.7	377.8	375.0	370.5	364.5	358.6	352.7	346.8	343.0
27.5°	371.2	368.1	365.0	361.9	358.6	353.7	347.1	340.4	333.7	327.0	322.7
30°	360.5	357.1	353.7	350.3	346.9	341.5	334.3	327.2	319.9	312.7	308.2
32.5°	350.2	346.2	342.1	338.1	334.1	328.5	321.2	313.8	306.5	299.1	293.9
35°	333.0	328.4	323.8	319.2	314.6	308.4	300.4	292.5	284.6	276.7	271.0
37.5°	315.8	310.8	305.7	300.7	295.6	288.9	280.4	272.0	263.6	255.1	248.9
40°	303.8	298.5	293.0	287.6	282.2	275.2	266.4	257.7	249.0	240.2	233.8
42.5°	291.5	285.8	280.1	274.5	268.8	261.4	252.4	243.3	234.3	225.3	218.7
45°	272.2	266.2	260.1	254.1	248.1	240.3	230.9	221.4	212.0	202.5	196.2
47.5°	253.4	247.0	240.7	234.3	227.8	219.8	210.0	200.3	190.5	180.7	174.4
50°	239.8	233.4	227.0	220.6	214.3	206.1	196.2	186.3	176.4	166.5	160.2
52.5°	226.5	219.8	213.2	206.5	199.8	191.6	181.9	172.3	162.6	152.8	146.9
55°	207.0	200.0	193.0	185.9	178.9	170.6	160.8	151.1	141.3	131.6	126.3
57.5°	187.0	179.8	172.5	165.4	158.2	149.9	140.5	131.3	121.9	112.5	107.5
60°	173.3	166.2	159.0	151.8	144.5	136.3	127.1	117.8	108.5	99.2	94.6
62.5°	160.1	152.9	145.7	138.5	131.3	123.2	114.4	105.6	96.8	87.9	83.6
65°	139.7	132.4	125.2	117.9	110.6	102.9	94.8	86.7	78.6	70.4	67.4
67.5°	120.1	112.9	105.7	98.4	91.2	83.9	76.6	69.4	62.1	54.8	53.3
70°	106.6	99.5	92.5	85.5	78.5	71.9	65.6	59.4	53.2	47.0	46.1
72.5°	93.5	86.9	80.1	73.4	66.6	60.8	55.8	50.8	45.8	40.8	40.0
75°	74.5	68.2	62.0	55.6	49.3	44.7	41.6	38.5	35.5	32.4	31.7
77.5°	55.8	50.3	44.8	39.2	33.7	30.2	28.7	27.3	25.8	24.3	24.0
80°	44.1	39.6	35.0	30.4	25.8	23.0	22.1	21.2	20.3	19.4	19.1
82.5°	33.4	29.9	26.3	22.7	19.2	17.0	16.4	15.8	15.2	14.6	14.4
85°	17.4	15.5	13.6	11.8	9.9	8.7	8.5	8.2	7.9	7.7	7.7
87.5°	5.3	5.0	4.6	4.4	4.1	4.2	4.6	5.2	5.6	6.2	6.1
90°	0.5	1.9	3.2	4.5	6.0	7.8	10.3	12.8	15.3	17.8	17.6
92.5°	9.1	10.1	11.1	12.0	13.0	13.8	14.4	15.0	15.6	16.1	16.2
95°	26.5	27.6	28.7	29.9	30.9	31.7	31.8	32.1	32.3	32.5	32.5
97.5°	48.3	49.3	50.3	51.3	52.3	53.0	53.4	53.9	54.3	54.8	54.8
100°	64.6	65.5	66.3	67.3	68.2	68.8	69.2	69.5	69.8	70.2	70.2
102.5°	81.7	82.4	83.1	83.8	84.5	85.2	85.6	86.0	86.4	86.9	86.9
105°	109.3	109.7	110.0	110.3	110.7	110.9	111.2	111.4	111.6	111.9	112.1
107.5°	137.2	137.7	138.2	138.7	139.2	139.5	139.5	139.5	139.5	139.5	139.6
110°	155.1	155.8	156.4	157.1	157.8	158.1	158.1	158.1	158.1	158.1	158.1



TEST NUMBER: P331625-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	174.6	175.3	175.9	176.6	177.4	177.6	177.5	177.5	177.4	177.3	177.0
115°	203.4	204.1	204.7	205.5	206.1	206.3	206.1	205.9	205.6	205.5	205.4
117.5°	232.1	233.0	233.9	234.8	235.7	235.9	235.2	234.5	233.9	233.3	233.0
120°	251.2	252.1	253.0	253.9	254.9	254.9	253.9	253.0	252.1	251.2	251.2
122.5°	268.7	269.7	270.9	272.0	273.0	273.2	272.6	272.0	271.3	270.7	270.5
125°	296.0	296.9	298.0	299.0	300.0	300.3	300.0	299.7	299.3	299.0	298.6
127.5°	322.4	323.8	325.0	326.4	327.6	328.1	327.7	327.3	326.9	326.5	326.0
130°	339.2	340.6	342.1	343.6	345.0	345.6	345.4	345.2	345.0	344.7	344.6
132.5°	357.8	359.1	360.3	361.5	362.7	363.3	363.4	363.4	363.5	363.5	363.0
135°	382.9	384.1	385.4	386.6	387.9	388.6	388.8	389.1	389.3	389.5	389.4
137.5°	409.2	410.3	411.3	412.3	413.3	413.9	414.3	414.6	414.8	415.1	415.0
140°	425.1	426.1	427.1	428.1	429.2	430.0	430.5	431.1	431.7	432.2	432.2
142.5°	441.4	442.4	443.4	444.4	445.4	446.1	446.6	446.9	447.3	447.6	447.7
145°	464.8	465.6	466.4	467.2	468.0	468.7	469.3	470.0	470.7	471.4	471.4
147.5°	485.6	486.5	487.5	488.5	489.4	490.1	490.5	491.0	491.4	492.0	492.1
150°	499.9	500.5	501.2	501.9	502.6	503.1	503.5	504.0	504.4	505.0	505.2
152.5°	512.5	513.2	513.8	514.5	515.1	515.8	516.3	516.8	517.4	518.0	518.4
155°	531.4	531.7	532.1	532.4	532.7	533.1	533.4	533.8	534.0	534.4	535.0
157.5°	547.5	547.8	548.0	548.2	548.5	548.7	548.8	549.1	549.3	549.5	550.3
160°	557.3	557.5	557.8	557.9	558.2	558.4	558.5	558.6	558.7	558.8	559.5
162.5°	566.2	566.3	566.3	566.4	566.4	566.5	566.6	566.8	566.9	566.9	567.8
165°	578.2	578.0	577.9	577.8	577.7	577.7	577.7	577.7	577.7	577.7	578.5
167.5°	588.1	587.8	587.5	587.1	586.7	586.6	586.6	586.6	586.5	586.5	587.3
170°	593.4	593.1	592.7	592.4	592.1	591.8	591.7	591.6	591.5	591.4	592.2
172.5°	597.1	596.7	596.4	596.0	595.8	595.5	595.4	595.3	595.1	595.0	595.8
175°	601.5	601.2	600.8	600.6	600.2	599.9	599.7	599.5	599.2	599.0	599.8
177.5°	603.4	603.1	602.8	602.5	602.3	602.1	601.9	601.7	601.5	601.4	601.9
180°	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5



TEST NUMBER: P331625-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	445.5	446.2	446.9	447.2	447.1	446.9	446.7	446.7
5°	441.9	442.7	443.5	443.8	443.5	443.3	443.0	442.7
7.5°	434.8	435.1	435.2	435.2	434.7	434.2	433.7	433.3
10°	427.7	427.4	427.1	426.7	426.1	425.6	425.1	424.5
12.5°	419.5	418.9	418.5	417.8	416.9	416.0	415.1	414.2
15°	404.1	402.3	400.6	399.4	398.5	397.5	396.6	395.7
17.5°	386.7	384.7	382.7	380.9	379.3	377.8	376.2	374.7
20°	374.7	372.4	370.1	368.0	366.0	364.1	362.1	360.2
22.5°	361.4	358.5	355.6	353.4	351.9	350.4	348.9	347.5
25°	339.4	335.6	332.0	329.5	328.1	326.7	325.4	324.0
27.5°	318.3	314.1	309.8	306.6	304.4	302.3	300.1	298.0
30°	303.5	299.0	294.4	290.9	288.4	286.0	283.6	281.2
32.5°	288.6	283.4	278.1	274.4	272.2	269.8	267.5	265.3
35°	265.4	259.7	254.0	250.1	248.2	246.2	244.2	242.3
37.5°	242.6	236.4	230.2	225.9	223.6	221.3	219.1	216.8
40°	227.5	221.1	214.6	210.3	207.9	205.6	203.2	200.9
42.5°	212.0	205.5	198.9	194.5	192.2	189.9	187.6	185.4
45°	189.8	183.3	177.0	172.7	170.6	168.4	166.2	164.1
47.5°	168.0	161.7	155.3	151.1	149.2	147.2	145.3	143.3
50°	154.1	147.8	141.6	137.6	135.7	133.8	131.9	130.0
52.5°	140.9	134.9	128.9	125.0	123.3	121.5	119.8	118.1
55°	120.8	115.5	110.0	106.5	104.8	103.1	101.4	99.7
57.5°	102.6	97.6	92.7	89.5	88.1	86.7	85.2	83.7
60°	90.1	85.5	80.9	77.8	76.4	75.0	73.6	72.1
62.5°	79.2	74.8	70.4	67.8	66.9	66.1	65.2	64.3
65°	64.4	61.3	58.2	56.5	56.3	56.0	55.7	55.5
67.5°	52.0	50.6	49.1	48.3	48.0	47.7	47.4	47.2
70°	45.2	44.3	43.4	42.8	42.4	42.0	41.6	41.3
72.5°	39.3	38.5	37.8	37.4	37.1	36.9	36.6	36.5
75°	31.1	30.5	29.9	29.5	29.4	29.3	29.2	29.2
77.5°	23.5	23.2	22.8	22.6	22.5	22.3	22.2	22.0
80°	18.7	18.4	18.0	17.8	17.8	17.8	17.8	17.8
82.5°	14.2	13.9	13.7	13.6	13.6	13.6	13.6	13.6
85°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	5.9	5.8	5.7	5.6	5.6	5.7	5.7	5.7
90°	17.4	17.1	16.9	16.9	16.9	17.0	17.2	17.3
92.5°	16.2	16.3	16.3	16.4	16.4	16.4	16.5	16.5
95°	32.5	32.5	32.5	32.5	32.2	32.0	31.7	31.6
97.5°	54.8	54.8	54.8	54.7	54.7	54.7	54.7	54.6
100°	70.2	70.2	70.2	70.1	70.0	69.9	69.8	69.6
102.5°	87.0	87.1	87.2	87.2	87.1	86.9	86.9	86.8
105°	112.4	112.5	112.8	112.9	112.9	112.9	112.9	112.9
107.5°	139.6	139.7	139.8	139.6	139.0	138.6	138.0	137.5
110°	158.1	158.1	158.1	158.0	157.7	157.3	156.9	156.6



TEST NUMBER: P331625-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	176.7	176.5	176.2	175.9	175.7	175.4	175.1	175.0
115°	205.2	205.1	205.0	204.7	204.4	204.1	203.8	203.4
117.5°	232.7	232.5	232.2	231.9	231.6	231.2	230.9	230.5
120°	251.2	251.2	251.2	251.0	250.7	250.4	250.0	249.7
122.5°	270.2	269.9	269.7	269.4	269.1	268.9	268.7	268.4
125°	298.3	298.0	297.7	297.4	297.3	297.2	297.0	296.9
127.5°	325.7	325.2	324.9	324.4	324.0	323.7	323.3	323.0
130°	344.3	344.1	343.8	343.5	343.0	342.6	342.1	341.7
132.5°	362.5	361.9	361.5	361.1	360.7	360.3	360.0	359.6
135°	389.3	389.1	389.1	388.8	388.5	388.2	387.8	387.4
137.5°	414.9	414.8	414.7	414.5	414.0	413.6	413.1	412.7
140°	432.2	432.2	432.2	432.0	431.5	431.1	430.6	430.2
142.5°	447.8	447.9	448.0	447.8	447.4	446.9	446.5	446.0
145°	471.6	471.7	471.8	471.6	471.2	470.7	470.3	469.8
147.5°	492.4	492.7	492.9	492.8	492.4	492.0	491.5	491.1
150°	505.6	506.0	506.3	506.3	506.0	505.6	505.2	505.0
152.5°	518.8	519.2	519.7	519.7	519.2	518.8	518.4	518.0
155°	535.6	536.1	536.7	536.8	536.5	536.1	535.7	535.5
157.5°	551.0	551.8	552.6	552.7	552.1	551.6	551.1	550.5
160°	560.2	560.9	561.5	561.7	561.2	560.8	560.3	559.8
162.5°	568.5	569.3	570.1	570.2	569.6	569.1	568.6	568.0
165°	579.3	580.1	580.8	580.9	580.3	579.8	579.3	578.6
167.5°	588.1	588.9	589.7	589.8	589.2	588.6	588.0	587.4
170°	593.0	593.8	594.5	594.6	593.9	593.3	592.5	591.9
172.5°	596.6	597.4	598.2	598.2	597.6	596.9	596.2	595.6
175°	600.6	601.4	602.2	602.3	601.5	600.8	600.2	599.5
177.5°	602.4	603.0	603.5	603.5	603.0	602.4	601.9	601.4
180°	602.5	602.5	602.5	602.5	602.5	602.5	602.5	602.5

(END OF REPORT)