

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331626-940

Luminaire Tested: **SA2XXRDIP-C290D530U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331626-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2763.1 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331626-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331626-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33				
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35	29				
2	86	79	73	68	78	72	67	63	58	54	51	45	42	40	33	31	30	25				
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26	21				
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	23	18				
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18	14				
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13				
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12				
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11				
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7227	7227	7227
5°	7254	7136	7175
10°	7199	7020	6960
15°	7116	6812	6614
20°	7002	6515	6189
25°	6885	6178	5772
30°	6721	5830	5243
35°	6564	5454	4776
40°	6403	5063	4234
45°	6215	4624	3747
50°	6023	4182	3265
55°	5827	3704	2806
60°	5596	3203	2328
65°	5337	2690	2120
70°	5032	2219	1950
75°	4648	2021	1822
80°	4100	1804	1655
85°	3223	1426	1426



TEST NUMBER: P331626-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	1.5
10°-20°	115.0	4.2
20°-30°	161.6	5.8
30°-40°	176.2	6.4
40°-50°	162.0	5.9
50°-60°	127.2	4.6
60°-70°	82.9	3.0
70°-80°	42.8	1.5
80°-90°	13.5	0.5
90°-100°	105.7	3.8
100°-110°	358.8	13.0
110°-120°	381.2	13.8
120°-130°	313.8	11.4
130°-140°	252.0	9.1
140°-150°	190.4	6.9
150°-160°	133.8	4.8
160°-170°	78.8	2.9
170°-180°	25.6	0.9
0°-30°	318.5	11.5
0°-40°	494.7	17.9
0°-60°	783.8	28.4
0°-90°	923.0	33.4
90°-120°	845.7	30.6
90°-150°	1601.9	58.0
90°-180°	1840.0	66.6
0°-180°	2763.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	448	448	448	448	448	
5°	448	445	440	444	443	42
15°	426	421	408	400	396	120
25°	386	373	347	331	324	178
35°	333	312	277	252	242	208
45°	272	244	202	175	164	210
55°	207	175	132	108	100	185
65°	140	107	70	57	56	138
75°	74	47	32	30	29	79
85°	17	9	8	8	8	21
90°	0	7	17	16	17	2
95°	18	44	199	75	58	19
105°	62	94	377	674	573	66
115°	109	138	315	651	754	108
125°	153	180	303	527	612	135
135°	179	214	300	443	507	138
145°	204	235	298	370	405	128
155°	232	251	289	327	340	107
165°	253	261	277	294	298	71
175°	264	264	266	270	269	25
180°	264	264	264	264	264	



TEST NUMBER: P331626-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	449.2	448.9	448.5	448.2	447.8	447.2	446.4	445.7	444.9	444.1	444.8
5°	447.6	447.2	446.7	446.3	445.9	445.0	443.8	442.6	441.5	440.3	441.1
7.5°	443.0	442.5	441.8	441.3	440.8	439.8	438.5	437.0	435.7	434.4	434.5
10°	439.1	438.5	437.8	437.2	436.6	435.3	433.5	431.8	430.0	428.2	427.9
12.5°	434.3	433.5	432.7	431.9	431.1	429.6	427.3	425.0	422.7	420.4	419.9
15°	425.7	424.7	423.7	422.8	421.8	419.7	416.7	413.7	410.5	407.5	405.8
17.5°	415.3	413.8	412.2	410.7	409.2	406.5	402.6	398.7	394.8	390.8	388.8
20°	407.5	405.7	403.9	402.1	400.3	397.2	392.6	388.2	383.7	379.2	376.9
22.5°	399.1	397.1	395.0	393.1	391.0	387.4	382.4	377.3	372.3	367.2	364.3
25°	386.5	383.5	380.7	377.8	375.0	370.5	364.5	358.6	352.7	346.8	343.0
27.5°	371.2	368.1	365.0	361.9	358.6	353.7	347.1	340.4	333.7	327.0	322.7
30°	360.5	357.1	353.7	350.3	346.9	341.5	334.3	327.2	319.9	312.7	308.2
32.5°	350.2	346.2	342.1	338.1	334.1	328.5	321.2	313.8	306.5	299.1	293.9
35°	333.0	328.4	323.8	319.2	314.6	308.4	300.4	292.5	284.6	276.7	271.0
37.5°	315.8	310.8	305.7	300.7	295.6	288.9	280.4	272.0	263.6	255.1	248.9
40°	303.8	298.5	293.0	287.6	282.2	275.2	266.4	257.7	249.0	240.2	233.8
42.5°	291.5	285.8	280.1	274.5	268.8	261.4	252.4	243.3	234.3	225.3	218.7
45°	272.2	266.2	260.1	254.1	248.1	240.3	230.9	221.4	212.0	202.5	196.2
47.5°	253.4	247.0	240.7	234.3	227.8	219.8	210.0	200.3	190.5	180.7	174.4
50°	239.8	233.4	227.0	220.6	214.3	206.1	196.2	186.3	176.4	166.5	160.2
52.5°	226.5	219.8	213.2	206.5	199.8	191.6	181.9	172.3	162.6	152.8	146.9
55°	207.0	200.0	193.0	185.9	178.9	170.6	160.8	151.1	141.3	131.6	126.3
57.5°	187.0	179.8	172.5	165.4	158.2	149.9	140.5	131.3	121.9	112.5	107.5
60°	173.3	166.2	159.0	151.8	144.5	136.3	127.1	117.8	108.5	99.2	94.6
62.5°	160.1	152.9	145.7	138.5	131.3	123.2	114.4	105.6	96.8	87.9	83.6
65°	139.7	132.4	125.2	117.9	110.6	102.9	94.8	86.7	78.6	70.4	67.4
67.5°	120.1	112.9	105.7	98.4	91.2	83.9	76.6	69.4	62.1	54.8	53.3
70°	106.6	99.5	92.5	85.5	78.5	71.9	65.6	59.4	53.2	47.0	46.1
72.5°	93.5	86.9	80.1	73.4	66.6	60.8	55.8	50.8	45.8	40.8	40.0
75°	74.5	68.2	62.0	55.6	49.3	44.7	41.6	38.5	35.5	32.4	31.7
77.5°	55.8	50.3	44.8	39.2	33.7	30.2	28.7	27.3	25.8	24.3	24.0
80°	44.1	39.6	35.0	30.4	25.8	23.0	22.1	21.2	20.3	19.4	19.1
82.5°	33.4	29.9	26.3	22.7	19.2	17.0	16.4	15.8	15.2	14.6	14.4
85°	17.4	15.5	13.6	11.8	9.9	8.7	8.5	8.2	7.9	7.7	7.7
87.5°	5.3	5.0	4.8	4.5	4.1	4.1	4.6	5.4	6.0	6.1	5.9
90°	0.5	2.1	4.1	5.1	6.1	7.7	10.2	13.7	16.8	17.3	16.8
92.5°	6.2	8.9	12.6	14.9	18.3	23.1	34.6	50.7	65.2	66.1	55.8
95°	17.8	19.8	24.9	29.5	37.6	49.8	73.2	117.4	176.5	199.4	174.4
97.5°	29.0	31.7	37.1	44.1	53.4	67.2	96.7	158.3	256.3	340.3	357.0
100°	39.1	40.7	45.3	53.4	63.6	77.8	104.8	166.8	276.6	401.7	474.9
102.5°	48.5	49.7	54.2	62.3	72.9	87.1	112.1	167.2	268.9	403.8	518.9
105°	62.1	64.1	67.6	75.3	86.4	100.7	124.6	169.9	253.8	376.8	512.1
107.5°	76.7	78.3	81.8	88.8	99.9	114.2	137.4	176.8	246.2	347.9	467.4
110°	86.4	88.5	91.6	98.2	108.8	123.6	146.0	182.5	244.6	334.1	439.3



TEST NUMBER: P331626-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	95.4	97.5	100.9	107.1	117.3	132.5	154.1	188.7	245.0	325.1	419.8
115°	109.3	111.9	114.9	121.0	131.2	144.9	166.8	197.8	247.2	315.3	395.7
117.5°	123.8	125.8	128.9	134.3	144.0	158.3	178.5	207.6	250.8	310.5	380.4
120°	132.7	134.7	137.8	142.4	152.6	166.8	186.6	214.1	253.2	307.6	372.3
122.5°	141.2	142.9	146.0	151.0	161.1	175.8	194.4	219.8	256.1	306.0	365.3
125°	152.6	154.1	157.1	163.3	173.4	187.6	206.0	228.8	260.4	303.1	355.4
127.5°	161.5	163.5	167.8	174.5	184.3	198.9	216.8	237.3	264.7	301.4	346.3
130°	166.8	168.8	173.9	181.0	191.2	205.5	223.3	242.5	268.0	300.5	340.2
132.5°	171.7	174.2	179.6	187.2	197.7	212.0	228.9	247.9	271.3	300.1	335.3
135°	179.0	181.0	187.2	194.7	206.4	220.7	237.0	254.8	275.1	299.5	328.5
137.5°	185.9	188.3	194.5	202.6	214.2	227.4	243.5	260.0	278.6	299.4	323.7
140°	191.2	193.2	199.4	207.5	218.6	231.9	247.2	262.9	280.2	299.0	320.9
142.5°	196.5	198.1	203.8	212.0	222.7	235.1	250.0	265.4	281.4	299.0	318.1
145°	204.5	206.4	211.5	219.2	229.3	240.5	254.2	268.5	282.8	298.0	314.2
147.5°	212.9	214.5	219.4	226.4	234.9	244.8	257.7	270.3	283.1	296.1	310.4
150°	218.6	220.2	224.3	230.9	238.5	247.6	259.3	271.1	282.8	295.0	307.2
152.5°	224.4	225.1	229.2	235.0	242.2	250.5	261.0	271.4	282.0	292.9	304.3
155°	232.4	232.9	235.9	241.6	247.2	254.8	263.4	272.1	280.7	289.4	299.0
157.5°	239.1	239.6	242.1	246.9	251.5	257.8	265.1	272.1	278.4	285.7	294.0
160°	243.6	244.1	246.1	250.2	254.2	259.8	266.0	272.1	277.1	283.3	290.3
162.5°	248.1	247.7	249.8	253.1	256.7	261.1	266.4	271.6	275.9	281.2	287.1
165°	253.2	252.7	253.8	256.8	259.3	262.4	267.0	270.5	273.6	277.1	281.7
167.5°	257.5	256.9	257.8	259.8	261.6	263.5	266.9	269.8	271.3	273.6	276.4
170°	260.4	259.3	259.8	261.4	262.4	263.9	266.4	269.0	270.0	271.5	273.6
172.5°	262.0	261.4	261.1	262.6	263.2	264.3	266.1	267.8	268.4	269.1	270.7
175°	263.9	263.4	262.9	263.9	263.9	264.4	265.5	266.4	266.0	266.4	267.0
177.5°	264.8	264.0	263.6	264.4	264.4	264.4	264.8	265.6	264.8	264.4	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331626-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6
2.5°	445.5	446.2	446.9	447.2	447.1	446.9	446.7	446.7
5°	441.9	442.7	443.5	443.8	443.5	443.3	443.0	442.7
7.5°	434.8	435.1	435.2	435.2	434.7	434.2	433.7	433.3
10°	427.7	427.4	427.1	426.7	426.1	425.6	425.1	424.5
12.5°	419.5	418.9	418.5	417.8	416.9	416.0	415.1	414.2
15°	404.1	402.3	400.6	399.4	398.5	397.5	396.6	395.7
17.5°	386.7	384.7	382.7	380.9	379.3	377.8	376.2	374.7
20°	374.7	372.4	370.1	368.0	366.0	364.1	362.1	360.2
22.5°	361.4	358.5	355.6	353.4	351.9	350.4	348.9	347.5
25°	339.4	335.6	332.0	329.5	328.1	326.7	325.4	324.0
27.5°	318.3	314.1	309.8	306.6	304.4	302.3	300.1	298.0
30°	303.5	299.0	294.4	290.9	288.4	286.0	283.6	281.2
32.5°	288.6	283.4	278.1	274.4	272.2	269.8	267.5	265.3
35°	265.4	259.7	254.0	250.1	248.2	246.2	244.2	242.3
37.5°	242.6	236.4	230.2	225.9	223.6	221.3	219.1	216.8
40°	227.5	221.1	214.6	210.3	207.9	205.6	203.2	200.9
42.5°	212.0	205.5	198.9	194.5	192.2	189.9	187.6	185.4
45°	189.8	183.3	177.0	172.7	170.6	168.4	166.2	164.1
47.5°	168.0	161.7	155.3	151.1	149.2	147.2	145.3	143.3
50°	154.1	147.8	141.6	137.6	135.7	133.8	131.9	130.0
52.5°	140.9	134.9	128.9	125.0	123.3	121.5	119.8	118.1
55°	120.8	115.5	110.0	106.5	104.8	103.1	101.4	99.7
57.5°	102.6	97.6	92.7	89.5	88.1	86.7	85.2	83.7
60°	90.1	85.5	80.9	77.8	76.4	75.0	73.6	72.1
62.5°	79.2	74.8	70.4	67.8	66.9	66.1	65.2	64.3
65°	64.4	61.3	58.2	56.5	56.3	56.0	55.7	55.5
67.5°	52.0	50.6	49.1	48.3	48.0	47.7	47.4	47.2
70°	45.2	44.3	43.4	42.8	42.4	42.0	41.6	41.3
72.5°	39.3	38.5	37.8	37.4	37.1	36.9	36.6	36.5
75°	31.1	30.5	29.9	29.5	29.4	29.3	29.2	29.2
77.5°	23.5	23.2	22.8	22.6	22.5	22.3	22.2	22.0
80°	18.7	18.4	18.0	17.8	17.8	17.8	17.8	17.8
82.5°	14.2	13.9	13.7	13.6	13.6	13.6	13.6	13.6
85°	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
87.5°	5.7	5.4	5.5	5.6	5.6	5.6	5.6	5.6
90°	16.2	15.2	16.2	16.8	16.8	16.8	16.8	16.8
92.5°	44.3	38.1	33.8	30.6	30.2	28.6	29.0	28.2
95°	133.2	102.2	80.9	69.6	63.0	59.0	57.4	58.0
97.5°	310.9	254.4	199.4	162.6	138.3	125.8	118.4	114.1
100°	464.3	401.3	331.5	270.0	227.8	206.0	191.2	182.1
102.5°	564.8	550.5	499.6	434.4	388.5	351.2	332.8	320.4
105°	617.9	675.3	682.0	665.1	633.6	602.1	580.2	573.1
107.5°	579.6	666.2	719.1	743.7	747.6	745.9	741.5	732.1
110°	546.7	637.7	702.8	744.5	766.3	776.1	780.6	780.1



TEST NUMBER: P331626-940

CATALOG NUMBER: SA2XXRDIP-C290D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	516.6	604.0	673.5	721.3	751.7	767.9	776.5	779.3
115°	479.6	557.9	624.5	676.9	712.9	736.4	749.6	754.1
117.5°	451.7	520.4	580.9	630.0	666.8	691.5	705.4	709.3
120°	437.8	500.9	554.8	601.1	636.7	660.6	675.3	680.4
122.5°	426.9	484.6	535.7	577.5	609.4	632.9	646.0	650.3
125°	410.9	463.2	508.0	546.2	575.7	594.9	607.7	611.8
127.5°	395.1	442.6	484.7	520.0	545.6	563.7	574.7	578.0
130°	385.0	428.7	468.9	502.4	527.4	544.7	554.8	558.8
132.5°	375.2	415.7	452.6	484.1	508.6	525.9	535.3	539.0
135°	361.6	395.1	428.7	457.2	479.0	495.8	505.0	507.0
137.5°	350.7	378.8	405.4	430.3	450.1	464.6	472.6	475.6
140°	343.8	368.2	391.6	413.9	430.3	443.4	451.0	454.1
142.5°	338.0	358.8	379.0	397.7	413.1	425.2	431.9	432.6
145°	330.0	346.8	362.6	377.4	389.5	398.1	403.2	404.7
147.5°	323.9	337.1	349.4	360.2	370.2	377.1	380.6	381.5
150°	319.3	330.6	341.3	350.4	358.0	364.1	367.1	367.7
152.5°	314.9	325.3	334.3	342.2	348.2	353.6	355.8	355.9
155°	308.7	316.8	324.4	330.0	335.6	339.2	341.3	340.2
157.5°	301.5	308.3	314.7	319.1	323.0	326.0	326.9	326.9
160°	296.9	302.6	308.2	311.7	315.3	317.8	318.3	318.3
162.5°	292.5	297.3	302.1	304.8	308.4	310.1	310.6	310.2
165°	285.8	289.4	292.9	295.0	296.9	299.0	299.0	298.5
167.5°	279.4	282.1	284.5	286.4	287.3	288.5	288.4	287.8
170°	276.2	277.7	279.7	280.7	281.2	282.8	282.2	281.2
172.5°	272.5	273.6	275.2	275.8	276.3	277.1	276.5	275.9
175°	268.5	269.0	269.6	270.0	270.0	270.5	270.0	269.0
177.5°	265.6	265.6	266.1	266.1	266.1	266.1	265.6	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4

(END OF REPORT)