

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332876-930

Luminaire Tested: **SA4XXRDIP-C350D590U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332876-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C350D590U930-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2887.5 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332876-930
CATALOG NUMBER: SA4XXRDIP-C350D590U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332876-930

CATALOG NUMBER: SA4XXRDIP-C350D590U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	80	78	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	27	25	22
5	67	56	48	42	61	51	44	39	43	37	33	34	31	28	27	24	22	19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	28	24	22	22	20	18	15
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	13
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4069	4069	4069
5°	4078	4028	4053
10°	4052	3980	3980
15°	4006	3896	3867
20°	3942	3786	3716
25°	3861	3657	3564
30°	3781	3522	3375
35°	3693	3381	3183
40°	3587	3222	2977
45°	3490	3062	2767
50°	3378	2880	2545
55°	3258	2688	2303
60°	3127	2480	2055
65°	3007	2220	1813
70°	2832	1931	1539
75°	2611	1603	1251
80°	2278	1223	1148
85°	1936	1112	1037



TEST NUMBER: P332876-930

CATALOG NUMBER: SA4XXRDIP-C350D590U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.3	1.6
10°-20°	132.0	4.6
20°-30°	190.6	6.6
30°-40°	216.1	7.5
40°-50°	208.7	7.2
50°-60°	173.5	6.0
60°-70°	119.8	4.1
70°-80°	60.7	2.1
80°-90°	16.9	0.6
90°-100°	171.0	5.9
100°-110°	355.9	12.3
110°-120°	318.7	11.0
120°-130°	268.1	9.3
130°-140°	223.6	7.7
140°-150°	170.8	5.9
150°-160°	120.0	4.2
160°-170°	70.6	2.4
170°-180°	23.0	0.8
0°-30°	370.0	12.8
0°-40°	586.1	20.3
0°-60°	968.3	33.5
0°-90°	1165.8	40.4
90°-120°	845.6	29.3
90°-150°	1508.1	52.2
90°-180°	1722.0	59.6
0°-180°	2887.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	504	504	504	504	504	
5°	503	502	497	501	500	48
15°	479	475	466	465	463	135
25°	433	426	411	404	400	200
35°	375	362	343	330	323	234
45°	306	291	268	250	242	236
55°	232	216	191	172	164	207
65°	157	140	116	100	95	155
75°	84	69	51	43	40	88
85°	21	13	12	11	11	23
90°	0	4	8	9	10	2
95°	15	48	379	188	114	17
105°	54	79	305	657	654	58
115°	96	120	272	523	628	95
125°	134	159	271	445	501	119
135°	159	189	268	395	448	123
145°	183	209	267	333	366	115
155°	208	224	260	294	306	96
165°	226	234	249	263	267	64
175°	236	237	239	242	241	22
180°	237	237	237	237	237	



TEST NUMBER: P332876-930

CATALOG NUMBER: SA4XXRDIP-C350D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	505.2	504.9	504.7	504.4	504.1	503.6	502.9	502.1	501.3	500.6	501.3
5°	503.2	502.9	502.6	502.2	501.8	501.2	500.1	499.1	498.1	497.1	497.9
7.5°	498.6	498.3	498.0	497.6	497.3	496.4	495.0	493.7	492.4	491.1	491.5
10°	494.3	493.9	493.5	493.1	492.6	491.6	490.1	488.5	487.0	485.5	485.8
12.5°	488.8	488.3	487.8	487.3	486.8	485.7	483.8	482.0	480.2	478.3	478.6
15°	479.3	478.5	477.8	477.0	476.2	474.7	472.6	470.4	468.3	466.2	466.0
17.5°	467.8	466.7	465.5	464.5	463.3	461.5	458.9	456.3	453.8	451.2	450.7
20°	458.9	457.7	456.6	455.5	454.4	452.4	449.5	446.5	443.6	440.7	440.0
22.5°	449.0	447.7	446.5	445.2	443.9	441.7	438.6	435.5	432.4	429.3	428.3
25°	433.4	431.9	430.3	428.8	427.2	424.7	421.2	417.7	414.1	410.6	409.1
27.5°	417.0	415.1	413.1	411.2	409.3	406.4	402.7	398.9	395.2	391.4	389.6
30°	405.6	403.4	401.3	399.2	397.1	394.0	389.9	385.9	381.8	377.8	375.7
32.5°	393.5	391.1	388.7	386.3	383.8	380.6	376.4	372.3	368.1	363.9	361.4
35°	374.7	371.9	369.2	366.5	363.7	360.2	356.0	351.6	347.4	343.1	340.1
37.5°	354.6	351.7	348.9	346.1	343.2	339.5	334.7	330.0	325.2	320.5	317.2
40°	340.4	337.5	334.7	331.9	329.1	325.2	320.3	315.4	310.5	305.7	302.1
42.5°	326.8	323.8	320.8	317.9	315.0	310.9	305.8	300.7	295.6	290.5	286.8
45°	305.7	302.5	299.3	296.1	292.9	288.8	283.6	278.5	273.4	268.2	264.0
47.5°	283.8	280.5	277.3	273.9	270.7	266.4	261.1	255.7	250.3	245.0	240.6
50°	269.0	265.6	262.3	258.9	255.6	251.2	245.7	240.2	234.7	229.3	224.9
52.5°	253.9	250.5	247.3	244.0	240.8	236.3	230.6	225.0	219.4	213.8	209.5
55°	231.5	228.1	224.7	221.3	217.8	213.3	207.7	202.2	196.6	191.0	186.5
57.5°	209.5	205.9	202.4	198.8	195.2	190.7	185.2	179.7	174.2	168.7	164.2
60°	193.7	190.3	186.9	183.4	180.0	175.5	170.1	164.5	159.1	153.6	149.1
62.5°	179.5	175.9	172.4	168.8	165.3	160.7	155.1	149.4	143.8	138.2	134.0
65°	157.4	153.8	150.1	146.4	142.7	138.1	132.6	127.1	121.6	116.2	112.5
67.5°	134.5	131.0	127.4	123.9	120.4	116.1	111.0	105.9	100.8	95.7	92.5
70°	120.0	116.4	112.8	109.3	105.6	101.3	96.4	91.6	86.7	81.8	79.0
72.5°	104.6	101.3	98.1	94.8	91.6	87.6	83.0	78.4	73.8	69.1	66.8
75°	83.7	80.6	77.4	74.2	71.0	67.4	63.4	59.4	55.4	51.4	49.3
77.5°	62.6	59.9	57.2	54.5	51.9	48.8	45.6	42.3	39.1	35.8	34.7
80°	49.0	46.6	44.0	41.6	39.1	36.5	34.0	31.4	28.8	26.3	26.0
82.5°	37.3	35.0	32.7	30.4	28.1	26.3	24.8	23.3	21.9	20.4	20.2
85°	20.9	19.2	17.4	15.7	13.9	13.0	12.7	12.5	12.2	12.0	11.8
87.5°	7.2	6.8	6.5	6.1	5.6	5.4	5.9	5.8	5.9	6.0	5.9
90°	0.5	1.4	2.8	3.3	3.8	3.8	6.5	6.5	7.4	8.4	7.9
92.5°	5.3	7.7	12.1	17.8	24.5	34.2	57.9	93.9	129.1	147.5	122.9
95°	15.3	16.7	21.4	27.5	38.6	58.1	98.6	174.9	286.0	379.0	389.7
97.5°	27.6	27.6	31.6	37.1	46.7	63.1	94.2	157.2	267.7	399.3	489.7
100°	35.4	35.4	38.6	44.2	53.0	67.9	95.3	147.9	242.8	373.9	493.0
102.5°	42.8	43.5	46.4	51.6	60.1	74.2	99.1	145.3	226.0	342.3	465.0
105°	54.4	55.8	58.1	63.8	72.1	85.6	107.9	146.5	211.7	305.1	414.4
107.5°	67.3	68.2	70.5	76.5	84.5	97.8	118.2	153.4	209.0	284.3	373.5
110°	75.8	76.7	79.1	84.6	93.0	105.6	126.0	158.6	209.8	277.2	353.0



TEST NUMBER: P332876-930

CATALOG NUMBER: SA4XXRDIP-C350D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.0	85.0	87.6	92.9	101.2	113.7	133.5	164.2	212.0	273.9	341.4
115°	95.8	97.2	100.4	105.1	114.0	126.5	145.1	173.0	216.3	272.1	330.7
117.5°	108.1	109.4	112.3	117.4	125.6	138.7	156.4	182.1	220.8	271.6	325.9
120°	116.3	117.2	120.4	125.6	133.5	146.5	164.2	188.3	224.2	271.6	323.3
122.5°	123.7	124.7	127.9	132.6	141.3	153.9	171.6	194.3	227.6	271.3	320.2
125°	133.5	135.3	138.1	143.2	152.1	165.1	181.8	203.3	232.5	270.7	315.4
127.5°	142.1	143.7	147.0	152.8	162.0	175.1	191.4	211.0	236.5	269.6	308.8
130°	147.0	148.8	152.5	159.6	168.4	181.8	197.6	215.8	239.5	269.3	304.6
132.5°	151.8	153.3	158.2	164.8	174.3	187.0	202.8	220.6	242.1	268.9	300.9
135°	158.6	160.5	165.1	173.0	182.8	194.9	210.2	227.0	246.1	268.3	295.3
137.5°	165.4	167.1	172.3	179.8	190.0	201.5	215.8	231.5	248.3	268.2	290.5
140°	170.2	171.6	176.8	184.7	194.4	205.5	219.6	234.4	250.2	267.9	287.9
142.5°	175.5	176.8	181.6	189.1	198.5	209.3	222.9	236.6	251.7	267.9	285.7
145°	182.8	184.2	188.8	195.3	204.2	214.4	226.5	239.0	252.6	266.9	281.8
147.5°	191.0	191.5	195.6	202.3	209.7	218.9	230.2	241.2	253.0	265.3	278.4
150°	196.2	196.7	200.5	206.0	213.0	221.8	232.1	242.3	253.0	264.2	275.8
152.5°	201.1	201.2	204.9	210.1	216.4	224.5	233.6	243.0	252.3	262.3	272.8
155°	207.9	208.4	211.2	215.8	220.9	227.9	235.8	243.7	251.1	259.5	268.3
157.5°	214.5	214.5	217.1	220.7	225.2	230.6	237.4	243.7	250.0	256.7	263.8
160°	218.6	218.6	220.5	223.7	227.4	232.5	238.1	243.7	248.8	254.4	260.5
162.5°	222.3	221.9	223.4	226.3	229.7	233.7	238.9	243.7	247.7	252.2	257.5
165°	226.5	226.5	227.4	229.8	232.1	234.9	239.0	242.8	245.6	248.8	252.6
167.5°	230.6	230.2	230.6	232.4	233.7	235.9	239.0	241.7	243.4	245.5	248.1
170°	232.5	232.1	232.5	233.9	234.9	236.3	238.6	240.9	241.8	243.2	245.1
172.5°	234.4	233.9	234.0	235.1	235.6	236.6	238.2	240.2	240.4	241.0	242.5
175°	236.3	235.8	235.8	236.3	236.8	236.8	237.7	239.0	238.6	238.6	239.5
177.5°	237.1	236.8	236.4	236.8	236.8	236.8	237.1	237.8	237.1	237.1	237.5
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8



TEST NUMBER: P332876-930

CATALOG NUMBER: SA4XXRDIP-C350D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	502.1	502.9	503.6	503.9	503.9	503.9	503.8	503.7
5°	498.8	499.6	500.5	500.8	500.7	500.5	500.3	500.1
7.5°	492.1	492.7	493.3	493.3	493.1	492.8	492.5	492.3
10°	486.2	486.5	486.8	486.8	486.5	486.2	485.8	485.5
12.5°	478.7	479.0	479.2	479.1	478.6	478.1	477.6	477.1
15°	465.9	465.7	465.5	465.1	464.5	463.9	463.3	462.7
17.5°	450.2	449.8	449.3	448.6	447.7	446.8	445.9	445.0
20°	439.4	438.6	438.0	437.1	435.9	434.8	433.7	432.6
22.5°	427.2	426.2	425.2	424.2	423.3	422.4	421.5	420.5
25°	407.6	406.3	404.8	403.7	402.8	401.9	401.0	400.1
27.5°	387.8	386.0	384.2	382.7	381.4	380.2	379.0	377.7
30°	373.5	371.4	369.2	367.5	366.1	364.8	363.4	362.0
32.5°	359.0	356.4	354.0	352.0	350.7	349.4	348.1	346.8
35°	337.2	334.4	331.4	329.2	327.7	326.1	324.6	323.0
37.5°	314.0	310.7	307.4	305.0	303.5	301.9	300.4	298.8
40°	298.4	294.8	291.2	288.7	287.1	285.6	284.1	282.5
42.5°	283.2	279.5	275.8	273.2	271.6	269.9	268.3	266.8
45°	259.8	255.6	251.4	248.5	247.0	245.4	243.9	242.4
47.5°	236.3	231.9	227.6	224.5	222.8	221.1	219.4	217.8
50°	220.6	216.4	212.1	209.1	207.5	205.9	204.2	202.6
52.5°	205.0	200.7	196.4	193.3	191.7	190.0	188.3	186.5
55°	182.1	177.7	173.2	170.2	168.5	166.9	165.3	163.6
57.5°	159.6	155.2	150.6	147.7	146.5	145.3	144.0	142.8
60°	144.6	140.2	135.7	132.8	131.4	130.1	128.7	127.3
62.5°	130.0	125.8	121.7	119.1	118.0	116.9	115.8	114.7
65°	108.8	105.1	101.4	99.1	98.0	97.0	96.0	94.9
67.5°	89.4	86.2	83.0	80.9	79.7	78.6	77.5	76.3
70°	76.1	73.3	70.5	68.6	67.8	66.9	66.0	65.2
72.5°	64.3	61.9	59.5	57.9	57.1	56.3	55.5	54.7
75°	47.4	45.4	43.5	42.2	41.7	41.2	40.7	40.1
77.5°	33.5	32.4	31.2	30.6	30.4	30.2	30.1	29.9
80°	25.8	25.4	25.2	25.0	24.9	24.9	24.8	24.7
82.5°	20.0	19.8	19.6	19.5	19.4	19.3	19.2	19.2
85°	11.7	11.4	11.3	11.2	11.2	11.2	11.2	11.2
87.5°	5.9	5.9	5.9	5.9	6.0	6.2	6.2	6.3
90°	8.4	8.8	9.3	9.3	9.8	10.2	9.8	9.8
92.5°	91.3	68.7	54.7	45.4	39.9	37.4	35.8	35.8
95°	344.6	272.6	210.2	165.1	142.4	127.9	119.5	113.5
97.5°	509.2	482.4	436.9	388.3	355.0	326.9	313.0	303.3
100°	560.9	570.2	547.4	513.0	472.5	444.2	430.2	426.5
102.5°	558.3	604.5	611.1	596.7	571.9	551.3	536.6	533.6
105°	520.9	601.4	647.4	666.5	667.4	663.7	657.1	654.4
107.5°	467.8	553.4	618.3	659.7	682.7	693.3	698.0	699.2
110°	435.8	516.2	583.7	634.9	667.9	687.4	695.8	699.9



TEST NUMBER: P332876-930

CATALOG NUMBER: SA4XXRDIP-C350D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	412.4	483.5	547.2	598.3	635.9	659.5	671.2	678.0
115°	388.8	446.1	500.4	545.1	581.8	609.8	624.6	628.4
117.5°	377.2	424.6	467.4	505.2	536.6	560.0	575.1	578.0
120°	372.1	415.3	452.5	485.5	512.1	532.6	544.6	549.8
122.5°	367.6	409.4	443.2	472.1	494.6	512.1	522.3	527.4
125°	360.0	400.0	432.0	457.6	476.2	489.8	498.6	501.3
127.5°	350.7	388.9	420.9	445.2	463.9	475.9	483.3	486.1
130°	343.2	380.0	411.6	436.3	455.3	466.9	474.4	477.2
132.5°	335.4	369.9	400.8	425.4	444.2	457.3	464.3	467.2
135°	324.7	354.9	383.2	406.5	425.1	438.1	445.6	448.3
137.5°	314.9	340.5	364.4	385.4	402.8	415.6	421.8	425.1
140°	309.2	331.2	352.0	371.6	387.9	398.1	404.6	408.4
142.5°	304.1	323.3	341.3	358.2	372.6	382.1	387.9	390.4
145°	296.7	312.5	326.5	339.5	351.1	359.1	363.7	366.0
147.5°	290.7	303.2	314.4	324.7	333.2	340.0	343.5	344.4
150°	287.0	297.7	307.0	315.4	322.8	328.8	331.6	332.1
152.5°	282.8	292.0	300.6	307.5	313.8	318.8	320.4	320.9
155°	276.7	284.1	291.1	296.7	301.4	305.1	306.5	306.5
157.5°	270.1	276.4	282.2	286.7	290.2	293.0	293.8	293.8
160°	266.0	271.2	276.2	280.0	282.7	285.6	286.0	286.0
162.5°	262.0	266.3	270.3	273.7	275.7	278.5	279.0	278.6
165°	256.2	259.0	262.3	264.6	266.5	268.3	267.9	267.4
167.5°	250.8	252.9	255.5	256.9	257.9	259.0	258.9	258.6
170°	247.4	248.8	250.7	252.1	253.0	253.5	253.0	253.0
172.5°	244.4	245.5	246.6	247.6	248.2	248.7	248.2	247.4
175°	240.4	240.9	241.8	241.8	241.8	242.8	241.8	240.9
177.5°	237.8	238.2	238.2	238.6	238.2	238.6	237.8	237.1
180°	236.8	236.8	236.8	236.8	236.8	236.8	236.8	236.8

(END OF REPORT)