

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331670-940

Luminaire Tested: **SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331670-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5093.3 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	36	35	35	28
2	86	79	74	69	78	72	67	63	58	54	52	45	42	41	32	31	30	25
3	79	70	63	58	71	64	58	53	51	47	44	40	37	35	29	28	26	22
4	73	63	55	50	65	57	50	46	46	41	38	36	33	30	27	25	23	19
5	67	56	48	43	60	51	44	39	41	37	33	32	29	27	24	22	21	17
6	62	50	43	37	55	46	39	34	37	33	29	30	26	24	22	20	18	15
7	57	45	38	33	51	42	35	30	34	29	26	27	24	21	20	18	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	13
9	49	38	31	26	45	35	28	24	29	24	21	23	20	17	18	15	14	11
10	46	35	28	23	42	32	26	22	26	22	19	21	18	16	16	14	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15474	15474	15474	15474
5°	17280	15571	13807	15571
10°	19174	15462	11968	15462
15°	20117	15234	9429	15234
20°	17438	14899	8158	14899
25°	11437	14439	7285	14439
30°	7700	13882	6594	13882
35°	6236	13180	5947	13180
40°	5545	12416	5503	12416
45°	5019	11520	4912	11520
50°	4567	10630	4549	10630
55°	4293	9647	4236	9647
60°	3591	8741	3549	8741
65°	3030	7939	3435	7939
70°	2799	7091	3238	7091
75°	2620	6170	2994	6170
80°	2408	5077	2659	5077
85°	2205	4020	2353	4020



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.8	1.8
10°-20°	253.1	5.0
20°-30°	326.2	6.4
30°-40°	310.0	6.1
40°-50°	265.6	5.2
50°-60°	202.2	4.0
60°-70°	127.8	2.5
70°-80°	63.8	1.3
80°-90°	21.5	0.4
90°-100°	77.8	1.5
100°-110°	241.6	4.7
110°-120°	412.9	8.1
120°-130°	543.0	10.7
130°-140°	609.4	12.0
140°-150°	597.6	11.7
150°-160°	501.2	9.8
160°-170°	332.4	6.5
170°-180°	116.2	2.3
0°-30°	670.2	13.2
0°-40°	980.2	19.2
0°-60°	1448.0	28.4
0°-90°	1661.2	32.6
90°-120°	732.3	14.4
90°-150°	2482.3	48.7
90°-180°	3432.0	67.4
0°-180°	5093.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	958	958	958	958	958	
5°	1066	961	852	961	1066	105
15°	1204	911	564	911	1204	325
25°	642	810	409	810	642	305
35°	316	669	302	669	316	202
45°	220	504	215	504	220	170
55°	152	343	150	343	152	134
65°	79	208	90	208	79	81
75°	42	99	48	99	42	45
85°	12	22	13	22	12	14
90°	35	1	35	1	35	16
95°	64	54	64	54	64	72
105°	230	223	230	223	230	242
115°	414	414	414	414	414	409
125°	605	603	605	603	605	539
135°	789	780	789	780	789	608
145°	957	947	957	947	957	598
155°	1091	1082	1091	1082	1091	502
165°	1179	1178	1179	1178	1179	332
175°	1221	1225	1221	1225	1221	116
180°	1227	1227	1227	1227	1227	



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	997.3	998.1	998.9	997.0	997.0	995.4	991.9	989.3	981.8	980.7	980.7
5°	1066.2	1065.6	1066.9	1062.6	1056.6	1055.3	1048.9	1040.6	1032.0	1022.3	1020.3
7.5°	1134.9	1133.9	1131.2	1130.4	1125.9	1115.8	1105.6	1094.8	1080.4	1066.3	1059.3
10°	1169.5	1180.4	1173.8	1162.2	1164.5	1148.9	1140.5	1126.2	1114.2	1093.2	1088.6
12.5°	1203.5	1207.9	1205.8	1199.2	1196.2	1185.4	1174.1	1161.6	1139.5	1120.7	1104.3
15°	1203.5	1209.8	1211.5	1209.4	1211.1	1210.4	1204.4	1194.1	1174.8	1154.1	1136.2
17.5°	1114.6	1119.0	1129.9	1137.3	1146.7	1166.4	1176.1	1179.9	1177.0	1165.2	1152.5
20°	1014.9	1007.6	1038.3	1053.9	1067.3	1100.5	1129.2	1140.1	1157.8	1157.5	1154.1
22.5°	873.8	875.5	904.6	923.1	962.1	995.3	1028.0	1069.3	1103.5	1126.1	1139.2
25°	642.0	654.7	683.7	708.9	752.2	814.2	870.5	935.8	997.3	1046.0	1092.3
27.5°	482.1	483.1	506.0	529.5	555.2	605.9	676.8	754.7	842.6	915.0	998.4
30°	413.0	410.9	420.6	434.9	456.9	496.1	549.5	626.1	713.6	822.9	920.1
32.5°	363.9	364.0	371.3	381.9	400.1	426.6	463.2	525.3	608.1	715.5	829.5
35°	316.4	316.0	321.4	329.0	336.6	353.7	378.6	411.3	468.2	568.5	685.0
37.5°	282.2	283.7	286.3	291.1	299.5	309.0	324.0	345.9	386.5	445.8	543.7
40°	263.1	263.8	267.4	271.4	276.4	283.7	296.0	313.7	343.3	390.6	462.2
42.5°	245.5	246.1	248.8	252.4	256.4	263.8	273.9	289.2	313.3	350.1	409.2
45°	219.8	219.8	222.1	223.7	228.1	234.8	243.1	255.7	272.4	299.7	339.0
47.5°	195.6	195.7	197.2	200.1	202.9	208.0	216.2	226.6	238.7	259.8	293.4
50°	181.8	182.2	183.2	185.5	187.2	191.8	198.1	207.1	219.8	236.1	264.0
52.5°	170.6	170.4	171.7	172.7	173.8	177.2	181.9	189.8	201.2	215.3	238.5
55°	152.5	151.1	153.2	154.8	155.9	157.2	159.8	164.9	174.5	186.5	203.8
57.5°	129.8	129.3	130.7	132.2	135.4	139.0	141.2	144.5	149.5	158.0	175.2
60°	111.2	111.2	114.2	115.2	118.9	123.5	128.2	130.9	135.9	141.5	154.2
62.5°	94.7	95.0	96.4	97.4	99.4	105.1	111.7	117.5	122.3	127.7	136.1
65°	79.3	79.9	79.9	80.6	81.9	83.3	85.9	90.6	98.9	106.6	112.9
67.5°	67.2	67.5	67.7	68.3	68.7	70.1	71.2	73.3	75.2	82.5	90.3
70°	59.3	60.3	59.9	60.6	60.9	61.6	63.0	63.9	67.0	68.6	73.3
72.5°	51.8	52.5	52.5	52.9	53.8	53.9	54.9	55.9	57.9	59.3	61.8
75°	42.0	41.6	42.0	42.6	43.0	43.2	43.2	44.6	45.7	47.0	48.6
77.5°	32.4	32.7	32.6	32.7	32.7	33.3	33.3	33.9	34.9	35.6	36.4
80°	25.9	26.3	25.9	26.3	26.7	26.9	26.7	26.9	28.0	28.6	28.6
82.5°	20.2	20.2	20.4	20.4	20.5	20.6	21.0	21.1	21.8	21.7	21.9
85°	11.9	11.7	11.7	11.7	11.9	12.3	11.9	11.9	12.3	12.3	12.3
87.5°	11.3	11.5	11.5	11.4	11.4	11.4	11.5	11.9	11.7	12.0	10.8
90°	35.2	35.0	34.8	34.5	34.3	34.4	34.9	35.3	35.8	36.3	31.2
92.5°	33.5	33.5	33.4	33.4	33.3	33.3	33.2	33.1	33.0	32.9	31.7
95°	64.2	64.6	65.2	65.6	66.1	66.3	66.3	66.3	66.3	66.3	65.8
97.5°	111.3	111.3	111.4	111.4	111.5	111.5	111.5	111.5	111.5	111.5	110.6
100°	141.9	142.1	142.4	142.6	142.9	142.9	142.9	142.9	142.9	142.9	142.2
102.5°	176.7	176.9	177.2	177.4	177.6	177.6	177.5	177.3	177.1	176.9	176.0
105°	230.0	230.0	230.0	230.0	230.0	229.7	229.3	228.8	228.4	227.8	227.4
107.5°	280.1	281.2	282.2	283.3	284.3	284.7	284.5	284.4	284.2	284.0	284.0
110°	319.1	319.7	320.4	321.1	321.8	322.2	322.2	322.2	322.2	322.2	322.2



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.3	356.9	357.3	357.8	358.4	358.9	359.4	360.0	360.5	361.1	361.2
115°	414.3	415.0	415.7	416.4	417.1	417.5	417.8	418.0	418.2	418.5	418.9
117.5°	469.7	470.3	471.0	471.7	472.4	473.1	473.6	474.1	474.7	475.2	476.5
120°	508.5	509.3	510.0	510.7	511.3	511.7	511.7	511.7	511.7	511.7	513.5
122.5°	546.7	547.2	547.7	548.2	548.8	549.2	549.8	550.4	550.9	551.4	552.8
125°	604.9	605.1	605.4	605.6	605.8	606.3	607.0	607.7	608.3	609.0	609.8
127.5°	657.9	658.7	659.4	660.1	660.8	661.6	662.5	663.3	664.1	664.9	665.8
130°	696.1	697.0	697.9	698.8	699.7	700.4	700.9	701.3	701.8	702.3	702.8
132.5°	732.5	733.3	734.0	734.8	735.5	736.4	737.4	738.3	739.4	740.4	740.3
135°	789.3	790.0	790.7	791.3	792.0	792.5	792.7	793.0	793.2	793.4	793.0
137.5°	840.6	841.6	842.5	843.4	844.4	844.9	845.1	845.3	845.4	845.6	845.0
140°	876.3	877.2	878.2	879.0	879.9	880.4	880.4	880.4	880.4	880.4	879.3
142.5°	908.6	909.5	910.4	911.3	912.3	912.7	912.5	912.3	912.1	912.0	911.2
145°	957.1	958.0	958.9	959.8	960.7	961.1	960.9	960.6	960.4	960.2	958.8
147.5°	1000.4	1001.2	1002.1	1003.0	1003.9	1004.1	1003.5	1003.1	1002.6	1002.0	1001.1
150°	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4	1030.6	1029.9	1029.2	1028.6	1027.6
152.5°	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5	1057.7	1056.9	1056.0	1055.1	1054.0
155°	1090.7	1091.4	1092.1	1092.8	1093.4	1093.2	1092.1	1090.9	1089.8	1088.6	1088.0
157.5°	1121.3	1122.5	1123.6	1124.6	1125.8	1125.5	1124.0	1122.4	1120.9	1119.3	1118.8
160°	1140.4	1141.3	1142.3	1143.2	1144.1	1143.9	1142.5	1141.1	1139.7	1138.4	1138.1
162.5°	1157.0	1158.1	1159.2	1160.3	1161.4	1161.2	1159.6	1158.1	1156.5	1154.9	1154.7
165°	1178.8	1179.9	1181.1	1182.2	1183.3	1183.1	1181.5	1179.9	1178.3	1176.7	1176.7
167.5°	1196.6	1197.7	1198.9	1200.2	1201.3	1201.1	1199.5	1197.9	1196.3	1194.7	1194.7
170°	1205.7	1207.0	1208.4	1209.8	1211.2	1211.0	1209.4	1207.8	1206.2	1204.6	1204.9
172.5°	1213.1	1214.5	1215.8	1217.3	1218.6	1218.5	1216.9	1215.3	1213.7	1212.1	1212.3
175°	1221.2	1222.6	1224.0	1225.4	1226.7	1226.6	1225.0	1223.4	1221.8	1220.1	1220.7
177.5°	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3	1228.2	1227.2	1226.0	1224.9	1225.3
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	981.2	979.2	977.3	972.5	970.1	964.7	963.9	963.7	956.8	950.1	948.2
5°	1014.9	1009.7	1001.7	992.3	982.7	972.7	966.0	960.7	947.4	934.7	927.4
7.5°	1048.9	1037.5	1023.7	1006.0	991.3	974.8	962.6	951.5	932.6	914.5	902.3
10°	1074.2	1055.6	1037.3	1013.0	994.0	975.4	958.1	943.1	921.8	897.8	880.7
12.5°	1089.9	1069.4	1044.2	1020.5	995.9	972.1	949.0	929.7	904.7	879.9	859.7
15°	1111.3	1089.2	1058.6	1024.7	993.0	962.1	935.4	911.4	878.8	849.2	824.5
17.5°	1128.6	1098.3	1065.4	1026.2	989.5	950.2	915.9	885.2	848.9	813.2	784.2
20°	1134.2	1104.2	1066.2	1027.0	983.6	937.4	900.4	867.1	828.1	789.2	755.9
22.5°	1130.7	1107.4	1065.1	1018.2	973.8	925.4	883.7	845.0	801.8	762.1	723.4
25°	1107.2	1099.2	1059.3	1008.0	957.3	901.1	852.8	810.5	761.3	718.6	676.6
27.5°	1052.4	1069.7	1044.9	990.2	934.0	873.6	819.4	771.2	720.1	672.1	630.3
30°	999.7	1039.3	1028.6	978.0	915.1	855.8	794.9	744.6	690.0	640.7	599.4
32.5°	927.5	992.9	1003.4	961.0	895.9	830.7	766.9	716.8	659.9	607.9	567.7
35°	812.5	910.4	955.4	928.4	863.1	792.9	726.9	668.7	611.4	560.1	520.1
37.5°	675.4	808.7	883.7	885.6	825.6	752.6	680.8	622.9	564.3	514.0	470.7
40°	586.4	730.9	828.5	850.2	799.5	720.6	648.0	589.1	531.8	482.5	432.9
42.5°	506.5	650.5	770.4	808.1	767.9	689.5	616.6	555.0	499.3	452.6	402.0
45°	409.6	535.5	667.6	734.9	712.7	640.0	563.1	504.5	452.2	411.9	363.3
47.5°	345.5	434.3	562.1	653.2	652.7	586.5	510.9	454.7	406.2	368.5	329.0
50°	309.0	386.3	494.5	597.7	606.4	550.8	478.8	423.2	378.0	338.3	306.7
52.5°	276.3	339.9	437.2	536.2	560.8	512.6	442.9	391.6	347.6	311.1	284.0
55°	233.4	282.7	356.7	449.2	486.5	452.5	390.6	342.7	307.0	276.4	253.1
57.5°	197.4	234.4	293.7	368.3	411.7	390.3	339.3	300.3	269.8	242.1	223.7
60°	174.9	205.1	255.4	317.7	365.6	350.6	307.0	270.7	244.8	220.8	203.5
62.5°	153.6	179.6	222.7	273.2	317.2	310.9	275.4	244.9	222.1	200.3	185.7
65°	123.5	142.5	176.1	215.8	251.1	254.0	228.5	207.8	187.4	170.1	157.2
67.5°	98.4	110.8	134.5	167.8	194.3	203.8	188.1	172.3	156.1	142.8	131.5
70°	82.9	92.9	110.2	137.2	161.5	171.5	162.5	150.2	136.2	125.2	115.6
72.5°	67.2	77.0	89.7	109.5	130.4	141.2	138.0	129.1	117.8	108.7	99.6
75°	50.6	53.6	62.2	75.6	91.9	101.2	103.5	98.9	89.9	82.9	77.6
77.5°	37.5	39.2	43.3	50.4	61.0	69.3	72.8	72.2	66.0	62.0	57.0
80°	30.0	30.9	33.0	35.9	44.0	52.3	54.6	54.6	50.3	48.6	43.6
82.5°	22.7	23.5	24.7	26.4	30.1	37.4	39.9	40.5	37.7	35.6	31.7
85°	13.0	12.7	13.3	14.4	15.0	16.9	21.0	21.7	21.0	18.3	17.3
87.5°	9.7	9.0	8.0	7.0	6.7	6.3	7.1	7.9	7.4	7.1	7.2
90°	26.1	21.0	16.0	12.1	9.4	6.6	3.8	1.1	3.8	6.6	9.4
92.5°	30.6	29.3	28.2	26.6	24.5	22.5	20.4	18.5	20.4	22.5	24.5
95°	65.4	64.9	64.5	63.0	60.7	58.5	56.2	53.9	56.2	58.5	60.7
97.5°	109.7	108.8	108.0	106.5	104.5	102.5	100.4	98.4	100.4	102.5	104.5
100°	141.5	140.9	140.2	138.9	137.1	135.3	133.4	131.5	133.4	135.3	137.1
102.5°	175.1	174.3	173.4	172.3	170.8	169.3	167.8	166.4	167.8	169.3	170.8
105°	226.9	226.5	226.0	225.4	224.8	224.1	223.4	222.7	223.4	224.1	224.8
107.5°	284.0	284.0	284.0	283.5	282.5	281.5	280.4	279.5	280.4	281.5	282.5
110°	322.2	322.2	322.2	321.5	320.0	318.7	317.3	315.9	317.3	318.7	320.0



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	361.4	361.6	361.9	361.2	359.8	358.5	357.0	355.7	357.0	358.5	359.8
115°	419.4	419.8	420.3	419.8	418.5	417.1	415.7	414.3	415.7	417.1	418.5
117.5°	477.8	479.1	480.4	480.1	478.2	476.4	474.6	472.7	474.6	476.4	478.2
120°	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7	513.5	515.4	517.2
122.5°	554.0	555.4	556.6	556.2	553.9	551.7	549.6	547.3	549.6	551.7	553.9
125°	610.5	611.1	611.8	611.1	609.0	607.0	604.9	602.8	604.9	607.0	609.0
127.5°	666.6	667.4	668.3	667.4	664.8	662.2	659.5	656.9	659.5	662.2	664.8
130°	703.2	703.6	704.1	702.8	699.8	696.9	693.8	690.9	693.8	696.9	699.8
132.5°	740.2	740.1	740.0	738.8	736.3	733.9	731.5	729.0	731.5	733.9	736.3
135°	792.5	792.0	791.6	790.1	787.6	785.1	782.5	780.0	782.5	785.1	787.6
137.5°	844.5	843.8	843.2	841.9	839.8	837.8	835.7	833.6	835.7	837.8	839.8
140°	878.2	877.0	875.8	874.2	872.2	870.0	868.0	865.9	868.0	870.0	872.2
142.5°	910.3	909.5	908.7	907.3	905.3	903.2	901.2	899.1	901.2	903.2	905.3
145°	957.4	956.0	954.7	953.1	951.5	949.9	948.3	946.7	948.3	949.9	951.5
147.5°	1000.2	999.3	998.4	996.9	995.0	993.0	991.1	989.2	991.1	993.0	995.0
150°	1026.7	1025.8	1024.8	1023.7	1022.3	1020.9	1019.6	1018.2	1019.6	1020.9	1022.3
152.5°	1052.8	1051.8	1050.6	1049.4	1048.0	1046.6	1045.3	1043.8	1045.3	1046.6	1048.0
155°	1087.3	1086.5	1085.8	1085.2	1084.5	1083.8	1083.1	1082.4	1083.1	1083.8	1084.5
157.5°	1118.5	1118.0	1117.6	1117.2	1116.7	1116.2	1115.8	1115.4	1115.8	1116.2	1116.7
160°	1137.9	1137.6	1137.4	1137.1	1136.6	1136.1	1135.7	1135.2	1135.7	1136.1	1136.6
162.5°	1154.4	1154.2	1154.0	1153.9	1153.7	1153.6	1153.5	1153.4	1153.5	1153.6	1153.7
165°	1176.7	1176.7	1176.7	1176.8	1177.0	1177.2	1177.5	1177.7	1177.5	1177.2	1177.0
167.5°	1194.8	1194.8	1194.9	1195.2	1196.0	1196.6	1197.3	1198.0	1197.3	1196.6	1196.0
170°	1205.1	1205.3	1205.6	1206.0	1206.7	1207.4	1208.1	1208.8	1208.1	1207.4	1206.7
172.5°	1212.5	1212.8	1213.0	1213.4	1214.2	1214.9	1215.6	1216.2	1215.6	1214.9	1214.2
175°	1221.1	1221.6	1222.0	1222.6	1223.2	1224.0	1224.7	1225.4	1224.7	1224.0	1223.2
177.5°	1225.7	1226.0	1226.4	1226.9	1227.4	1228.0	1228.5	1229.0	1228.5	1228.0	1227.4
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	944.8	942.9	939.4	934.2	930.9	925.3	921.6	923.7	924.3	923.7	923.2
5°	919.4	912.4	902.8	893.4	884.8	875.5	870.1	867.8	863.1	860.5	859.2
7.5°	888.7	876.6	863.0	846.8	832.9	818.5	811.1	807.4	797.9	792.7	788.2
10°	865.8	846.8	833.1	811.8	798.9	779.9	766.9	767.2	754.2	746.9	741.5
12.5°	840.5	819.7	796.9	777.8	759.7	744.5	728.8	722.5	708.6	701.6	687.2
15°	798.5	774.2	750.3	724.2	706.0	682.3	659.7	632.0	609.8	590.4	585.1
17.5°	752.7	722.6	698.6	668.1	636.7	596.9	570.7	554.6	541.2	531.0	523.4
20°	721.3	690.6	665.0	619.0	576.8	549.7	530.5	518.2	504.2	493.2	487.1
22.5°	688.2	656.3	621.3	570.0	537.1	515.4	498.2	484.0	474.6	466.0	460.6
25°	641.3	606.4	548.8	513.4	486.9	464.2	452.2	443.5	433.5	421.9	416.6
27.5°	591.8	536.2	494.8	468.6	443.2	428.5	417.7	404.7	395.8	390.6	385.0
30°	554.7	499.2	466.9	438.2	420.3	403.9	391.3	384.0	375.3	366.3	362.7
32.5°	513.4	469.0	438.1	414.3	396.0	382.1	372.1	360.3	354.0	348.5	340.8
35°	462.2	428.6	400.3	380.9	363.6	352.3	340.6	333.7	322.4	317.7	314.7
37.5°	418.7	389.6	368.5	348.1	334.4	321.9	314.8	303.6	298.7	292.2	285.9
40°	394.2	365.6	345.4	328.7	313.3	304.0	295.1	286.1	278.7	275.7	268.0
42.5°	369.3	345.9	325.6	307.4	297.1	287.2	275.9	269.3	261.6	256.8	252.1
45°	334.7	314.1	296.7	281.7	270.4	260.1	252.7	241.7	237.5	227.7	223.7
47.5°	304.3	285.1	268.6	254.3	243.3	236.6	225.9	217.2	210.4	204.4	199.3
50°	282.7	266.7	250.7	238.1	228.1	218.5	207.5	203.1	192.4	189.5	186.5
52.5°	263.0	247.8	233.2	220.8	210.8	201.4	191.7	186.1	178.9	175.8	173.7
55°	235.4	220.8	206.8	195.8	185.8	176.1	170.1	163.2	159.8	157.5	154.8
57.5°	207.7	194.6	183.8	172.7	162.6	155.0	148.0	143.8	140.4	137.3	134.1
60°	190.1	177.5	167.8	157.5	147.2	140.9	135.5	130.5	126.5	121.9	120.6
62.5°	171.5	160.4	151.6	141.5	132.5	126.7	121.7	117.0	112.2	105.4	103.5
65°	145.9	137.2	127.9	119.6	111.6	105.9	98.5	93.3	91.2	90.6	90.2
67.5°	122.7	114.5	106.5	98.0	90.7	85.4	81.7	80.9	79.5	79.1	78.2
70°	107.2	99.6	91.6	83.6	76.6	75.6	74.3	72.9	71.2	70.6	69.9
72.5°	93.4	85.4	77.5	71.1	68.0	66.8	65.5	64.1	63.0	62.3	62.0
75°	71.6	64.3	58.9	56.6	54.9	53.9	52.0	50.9	50.3	49.3	49.0
77.5°	51.5	47.4	44.9	43.5	41.7	40.7	39.6	38.5	37.8	37.6	37.1
80°	39.3	37.3	35.7	33.6	33.0	31.7	31.3	30.3	30.7	29.6	29.6
82.5°	30.5	28.0	26.6	25.7	25.0	23.9	23.5	23.1	23.2	22.5	22.5
85°	15.7	15.0	14.4	13.6	13.6	12.7	13.0	12.7	12.7	11.9	11.7
87.5°	7.5	8.0	8.5	9.5	10.5	11.2	11.1	10.8	10.7	10.6	10.3
90°	12.1	16.0	21.0	26.1	31.2	36.3	35.8	35.3	34.9	34.4	34.3
92.5°	26.6	28.2	29.3	30.6	31.7	32.9	33.0	33.1	33.2	33.3	33.3
95°	63.0	64.5	64.9	65.4	65.8	66.3	66.3	66.3	66.3	66.3	66.1
97.5°	106.5	108.0	108.8	109.7	110.6	111.5	111.5	111.5	111.5	111.5	111.5
100°	138.9	140.2	140.9	141.5	142.2	142.9	142.9	142.9	142.9	142.9	142.9
102.5°	172.3	173.4	174.3	175.1	176.0	176.9	177.1	177.3	177.5	177.6	177.6
105°	225.4	226.0	226.5	226.9	227.4	227.8	228.4	228.8	229.3	229.7	230.0
107.5°	283.5	284.0	284.0	284.0	284.0	284.0	284.2	284.4	284.5	284.7	284.3
110°	321.5	322.2	322.2	322.2	322.2	322.2	322.2	322.2	322.2	322.2	321.8



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	361.2	361.9	361.6	361.4	361.2	361.1	360.5	360.0	359.4	358.9	358.4
115°	419.8	420.3	419.8	419.4	418.9	418.5	418.2	418.0	417.8	417.5	417.1
117.5°	480.1	480.4	479.1	477.8	476.5	475.2	474.7	474.1	473.6	473.1	472.4
120°	519.1	519.1	517.2	515.4	513.5	511.7	511.7	511.7	511.7	511.7	511.3
122.5°	556.2	556.6	555.4	554.0	552.8	551.4	550.9	550.4	549.8	549.2	548.8
125°	611.1	611.8	611.1	610.5	609.8	609.0	608.3	607.7	607.0	606.3	605.8
127.5°	667.4	668.3	667.4	666.6	665.8	664.9	664.1	663.3	662.5	661.6	660.8
130°	702.8	704.1	703.6	703.2	702.8	702.3	701.8	701.3	700.9	700.4	699.7
132.5°	738.8	740.0	740.1	740.2	740.3	740.4	739.4	738.3	737.4	736.4	735.5
135°	790.1	791.6	792.0	792.5	793.0	793.4	793.2	793.0	792.7	792.5	792.0
137.5°	841.9	843.2	843.8	844.5	845.0	845.6	845.4	845.3	845.1	844.9	844.4
140°	874.2	875.8	877.0	878.2	879.3	880.4	880.4	880.4	880.4	880.4	879.9
142.5°	907.3	908.7	909.5	910.3	911.2	912.0	912.1	912.3	912.5	912.7	912.3
145°	953.1	954.7	956.0	957.4	958.8	960.2	960.4	960.6	960.9	961.1	960.7
147.5°	996.9	998.4	999.3	1000.2	1001.1	1002.0	1002.6	1003.1	1003.5	1004.1	1003.9
150°	1023.7	1024.8	1025.8	1026.7	1027.6	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4
152.5°	1049.4	1050.6	1051.8	1052.8	1054.0	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5
155°	1085.2	1085.8	1086.5	1087.3	1088.0	1088.6	1089.8	1090.9	1092.1	1093.2	1093.4
157.5°	1117.2	1117.6	1118.0	1118.5	1118.8	1119.3	1120.9	1122.4	1124.0	1125.5	1125.8
160°	1137.1	1137.4	1137.6	1137.9	1138.1	1138.4	1139.7	1141.1	1142.5	1143.9	1144.1
162.5°	1153.9	1154.0	1154.2	1154.4	1154.7	1154.9	1156.5	1158.1	1159.6	1161.2	1161.4
165°	1176.8	1176.7	1176.7	1176.7	1176.7	1176.7	1178.3	1179.9	1181.5	1183.1	1183.3
167.5°	1195.2	1194.9	1194.8	1194.8	1194.7	1194.7	1196.3	1197.9	1199.5	1201.1	1201.3
170°	1206.0	1205.6	1205.3	1205.1	1204.9	1204.6	1206.2	1207.8	1209.4	1211.0	1211.2
172.5°	1213.4	1213.0	1212.8	1212.5	1212.3	1212.1	1213.7	1215.3	1216.9	1218.5	1218.6
175°	1222.6	1222.0	1221.6	1221.1	1220.7	1220.1	1221.8	1223.4	1225.0	1226.6	1226.7
177.5°	1226.9	1226.4	1226.0	1225.7	1225.3	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	920.2	920.8	920.0	920.5	920.0	920.8	920.2	923.2	923.7	924.3	923.7
5°	857.5	853.5	852.8	851.9	852.8	853.5	857.5	859.2	860.5	863.1	867.8
7.5°	782.5	781.9	780.2	777.8	780.2	781.9	782.5	788.2	792.7	797.9	807.4
10°	734.2	732.6	732.3	730.0	732.3	732.6	734.2	741.5	746.9	754.2	767.2
12.5°	677.8	667.1	665.9	660.1	665.9	667.1	677.8	687.2	701.6	708.6	722.5
15°	577.1	575.1	568.5	564.1	568.5	575.1	577.1	585.1	590.4	609.8	632.0
17.5°	519.5	513.0	511.0	510.1	511.0	513.0	519.5	523.4	531.0	541.2	554.6
20°	482.5	476.5	475.5	474.8	475.5	476.5	482.5	487.1	493.2	504.2	518.2
22.5°	456.9	450.7	448.1	446.1	448.1	450.7	456.9	460.6	466.0	474.6	484.0
25°	413.2	410.9	409.6	408.9	409.6	410.9	413.2	416.6	421.9	433.5	443.5
27.5°	379.1	374.0	372.9	371.2	372.9	374.0	379.1	385.0	390.6	395.8	404.7
30°	359.6	357.9	355.6	353.7	355.6	357.9	359.6	362.7	366.3	375.3	384.0
32.5°	336.7	335.4	333.2	332.3	333.2	335.4	336.7	340.8	348.5	354.0	360.3
35°	311.4	306.7	304.7	301.7	304.7	306.7	311.4	314.7	317.7	322.4	333.7
37.5°	284.5	282.0	279.3	280.3	279.3	282.0	284.5	285.9	292.2	298.7	303.6
40°	263.8	262.1	261.4	261.1	261.4	262.1	263.8	268.0	275.7	278.7	286.1
42.5°	247.2	242.6	240.9	240.9	240.9	242.6	247.2	252.1	256.8	261.6	269.3
45°	222.1	217.8	214.8	215.1	214.8	217.8	222.1	223.7	227.7	237.5	241.7
47.5°	196.4	196.3	194.4	195.0	194.4	196.3	196.4	199.3	204.4	210.4	217.2
50°	184.1	182.2	180.8	181.1	180.8	182.2	184.1	186.5	189.5	192.4	203.1
52.5°	172.5	170.7	169.6	171.0	169.6	170.7	172.5	173.7	175.8	178.9	186.1
55°	153.2	151.1	150.9	150.5	150.9	151.1	153.2	154.8	157.5	159.8	163.2
57.5°	131.7	130.4	128.3	127.5	128.3	130.4	131.7	134.1	137.3	140.4	143.8
60°	116.2	113.5	110.2	109.9	110.2	113.5	116.2	120.6	121.9	126.5	130.5
62.5°	102.1	101.6	100.9	100.9	100.9	101.6	102.1	103.5	105.4	112.2	117.0
65°	89.6	89.3	89.6	89.9	89.6	89.3	89.6	90.2	90.6	91.2	93.3
67.5°	78.0	77.5	76.9	77.1	76.9	77.5	78.0	78.2	79.1	79.5	80.9
70°	69.3	68.9	68.6	68.6	68.6	68.9	69.3	69.9	70.6	71.2	72.9
72.5°	60.7	60.6	60.4	60.1	60.4	60.6	60.7	62.0	62.3	63.0	64.1
75°	48.6	48.0	48.0	48.0	48.0	48.0	48.6	49.0	49.3	50.3	50.9
77.5°	37.0	36.7	36.4	36.1	36.4	36.7	37.0	37.1	37.6	37.8	38.5
80°	29.3	29.0	28.6	28.6	28.6	29.0	29.3	29.6	29.6	30.7	30.3
82.5°	22.4	22.0	21.9	21.7	21.9	22.0	22.4	22.5	22.5	23.2	23.1
85°	11.9	12.3	11.9	12.7	11.9	12.3	11.9	11.7	11.9	12.7	12.7
87.5°	10.3	10.2	10.4	10.3	10.4	10.2	10.3	10.3	10.6	10.7	10.8
90°	34.5	34.8	35.0	35.2	35.0	34.8	34.5	34.3	34.4	34.9	35.3
92.5°	33.4	33.4	33.5	33.5	33.5	33.4	33.4	33.3	33.3	33.2	33.1
95°	65.6	65.2	64.6	64.2	64.6	65.2	65.6	66.1	66.3	66.3	66.3
97.5°	111.4	111.4	111.3	111.3	111.3	111.4	111.4	111.5	111.5	111.5	111.5
100°	142.6	142.4	142.1	141.9	142.1	142.4	142.6	142.9	142.9	142.9	142.9
102.5°	177.4	177.2	176.9	176.7	176.9	177.2	177.4	177.6	177.6	177.5	177.3
105°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	229.7	229.3	228.8
107.5°	283.3	282.2	281.2	280.1	281.2	282.2	283.3	284.3	284.7	284.5	284.4
110°	321.1	320.4	319.7	319.1	319.7	320.4	321.1	321.8	322.2	322.2	322.2



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	357.8	357.3	356.9	356.3	356.9	357.3	357.8	358.4	358.9	359.4	360.0
115°	416.4	415.7	415.0	414.3	415.0	415.7	416.4	417.1	417.5	417.8	418.0
117.5°	471.7	471.0	470.3	469.7	470.3	471.0	471.7	472.4	473.1	473.6	474.1
120°	510.7	510.0	509.3	508.5	509.3	510.0	510.7	511.3	511.7	511.7	511.7
122.5°	548.2	547.7	547.2	546.7	547.2	547.7	548.2	548.8	549.2	549.8	550.4
125°	605.6	605.4	605.1	604.9	605.1	605.4	605.6	605.8	606.3	607.0	607.7
127.5°	660.1	659.4	658.7	657.9	658.7	659.4	660.1	660.8	661.6	662.5	663.3
130°	698.8	697.9	697.0	696.1	697.0	697.9	698.8	699.7	700.4	700.9	701.3
132.5°	734.8	734.0	733.3	732.5	733.3	734.0	734.8	735.5	736.4	737.4	738.3
135°	791.3	790.7	790.0	789.3	790.0	790.7	791.3	792.0	792.5	792.7	793.0
137.5°	843.4	842.5	841.6	840.6	841.6	842.5	843.4	844.4	844.9	845.1	845.3
140°	879.0	878.2	877.2	876.3	877.2	878.2	879.0	879.9	880.4	880.4	880.4
142.5°	911.3	910.4	909.5	908.6	909.5	910.4	911.3	912.3	912.7	912.5	912.3
145°	959.8	958.9	958.0	957.1	958.0	958.9	959.8	960.7	961.1	960.9	960.6
147.5°	1003.0	1002.1	1001.2	1000.4	1001.2	1002.1	1003.0	1003.9	1004.1	1003.5	1003.1
150°	1030.6	1029.9	1029.2	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4	1030.6	1029.9
152.5°	1057.7	1056.9	1056.0	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5	1057.7	1056.9
155°	1092.8	1092.1	1091.4	1090.7	1091.4	1092.1	1092.8	1093.4	1093.2	1092.1	1090.9
157.5°	1124.6	1123.6	1122.5	1121.3	1122.5	1123.6	1124.6	1125.8	1125.5	1124.0	1122.4
160°	1143.2	1142.3	1141.3	1140.4	1141.3	1142.3	1143.2	1144.1	1143.9	1142.5	1141.1
162.5°	1160.3	1159.2	1158.1	1157.0	1158.1	1159.2	1160.3	1161.4	1161.2	1159.6	1158.1
165°	1182.2	1181.1	1179.9	1178.8	1179.9	1181.1	1182.2	1183.3	1183.1	1181.5	1179.9
167.5°	1200.2	1198.9	1197.7	1196.6	1197.7	1198.9	1200.2	1201.3	1201.1	1199.5	1197.9
170°	1209.8	1208.4	1207.0	1205.7	1207.0	1208.4	1209.8	1211.2	1211.0	1209.4	1207.8
172.5°	1217.3	1215.8	1214.5	1213.1	1214.5	1215.8	1217.3	1218.6	1218.5	1216.9	1215.3
175°	1225.4	1224.0	1222.6	1221.2	1222.6	1224.0	1225.4	1226.7	1226.6	1225.0	1223.4
177.5°	1228.2	1227.2	1226.0	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3	1228.2	1227.2
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	921.6	925.3	930.9	934.2	939.4	942.9	944.8	948.2	950.1	956.8	963.7
5°	870.1	875.5	884.8	893.4	902.8	912.4	919.4	927.4	934.7	947.4	960.7
7.5°	811.1	818.5	832.9	846.8	863.0	876.6	888.7	902.3	914.5	932.6	951.5
10°	766.9	779.9	798.9	811.8	833.1	846.8	865.8	880.7	897.8	921.8	943.1
12.5°	728.8	744.5	759.7	777.8	796.9	819.7	840.5	859.7	879.9	904.7	929.7
15°	659.7	682.3	706.0	724.2	750.3	774.2	798.5	824.5	849.2	878.8	911.4
17.5°	570.7	596.9	636.7	668.1	698.6	722.6	752.7	784.2	813.2	848.9	885.2
20°	530.5	549.7	576.8	619.0	665.0	690.6	721.3	755.9	789.2	828.1	867.1
22.5°	498.2	515.4	537.1	570.0	621.3	656.3	688.2	723.4	762.1	801.8	845.0
25°	452.2	464.2	486.9	513.4	548.8	606.4	641.3	676.6	718.6	761.3	810.5
27.5°	417.7	428.5	443.2	468.6	494.8	536.2	591.8	630.3	672.1	720.1	771.2
30°	391.3	403.9	420.3	438.2	466.9	499.2	554.7	599.4	640.7	690.0	744.6
32.5°	372.1	382.1	396.0	414.3	438.1	469.0	513.4	567.7	607.9	659.9	716.8
35°	340.6	352.3	363.6	380.9	400.3	428.6	462.2	520.1	560.1	611.4	668.7
37.5°	314.8	321.9	334.4	348.1	368.5	389.6	418.7	470.7	514.0	564.3	622.9
40°	295.1	304.0	313.3	328.7	345.4	365.6	394.2	432.9	482.5	531.8	589.1
42.5°	275.9	287.2	297.1	307.4	325.6	345.9	369.3	402.0	452.6	499.3	555.0
45°	252.7	260.1	270.4	281.7	296.7	314.1	334.7	363.3	411.9	452.2	504.5
47.5°	225.9	236.6	243.3	254.3	268.6	285.1	304.3	329.0	368.5	406.2	454.7
50°	207.5	218.5	228.1	238.1	250.7	266.7	282.7	306.7	338.3	378.0	423.2
52.5°	191.7	201.4	210.8	220.8	233.2	247.8	263.0	284.0	311.1	347.6	391.6
55°	170.1	176.1	185.8	195.8	206.8	220.8	235.4	253.1	276.4	307.0	342.7
57.5°	148.0	155.0	162.6	172.7	183.8	194.6	207.7	223.7	242.1	269.8	300.3
60°	135.5	140.9	147.2	157.5	167.8	177.5	190.1	203.5	220.8	244.8	270.7
62.5°	121.7	126.7	132.5	141.5	151.6	160.4	171.5	185.7	200.3	222.1	244.9
65°	98.5	105.9	111.6	119.6	127.9	137.2	145.9	157.2	170.1	187.4	207.8
67.5°	81.7	85.4	90.7	98.0	106.5	114.5	122.7	131.5	142.8	156.1	172.3
70°	74.3	75.6	76.6	83.6	91.6	99.6	107.2	115.6	125.2	136.2	150.2
72.5°	65.5	66.8	68.0	71.1	77.5	85.4	93.4	99.6	108.7	117.8	129.1
75°	52.0	53.9	54.9	56.6	58.9	64.3	71.6	77.6	82.9	89.9	98.9
77.5°	39.6	40.7	41.7	43.5	44.9	47.4	51.5	57.0	62.0	66.0	72.2
80°	31.3	31.7	33.0	33.6	35.7	37.3	39.3	43.6	48.6	50.3	54.6
82.5°	23.5	23.9	25.0	25.7	26.6	28.0	30.5	31.7	35.6	37.7	40.5
85°	13.0	12.7	13.6	13.6	14.4	15.0	15.7	17.3	18.3	21.0	21.7
87.5°	11.1	11.2	10.5	9.5	8.5	8.0	7.5	7.2	7.1	7.4	7.9
90°	35.8	36.3	31.2	26.1	21.0	16.0	12.1	9.4	6.6	3.8	1.1
92.5°	33.0	32.9	31.7	30.6	29.3	28.2	26.6	24.5	22.5	20.4	18.5
95°	66.3	66.3	65.8	65.4	64.9	64.5	63.0	60.7	58.5	56.2	53.9
97.5°	111.5	111.5	110.6	109.7	108.8	108.0	106.5	104.5	102.5	100.4	98.4
100°	142.9	142.9	142.2	141.5	140.9	140.2	138.9	137.1	135.3	133.4	131.5
102.5°	177.1	176.9	176.0	175.1	174.3	173.4	172.3	170.8	169.3	167.8	166.4
105°	228.4	227.8	227.4	226.9	226.5	226.0	225.4	224.8	224.1	223.4	222.7
107.5°	284.2	284.0	284.0	284.0	284.0	284.0	283.5	282.5	281.5	280.4	279.5
110°	322.2	322.2	322.2	322.2	322.2	322.2	321.5	320.0	318.7	317.3	315.9



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	360.5	361.1	361.2	361.4	361.6	361.9	361.2	359.8	358.5	357.0	355.7
115°	418.2	418.5	418.9	419.4	419.8	420.3	419.8	418.5	417.1	415.7	414.3
117.5°	474.7	475.2	476.5	477.8	479.1	480.4	480.1	478.2	476.4	474.6	472.7
120°	511.7	511.7	513.5	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7
122.5°	550.9	551.4	552.8	554.0	555.4	556.6	556.2	553.9	551.7	549.6	547.3
125°	608.3	609.0	609.8	610.5	611.1	611.8	611.1	609.0	607.0	604.9	602.8
127.5°	664.1	664.9	665.8	666.6	667.4	668.3	667.4	664.8	662.2	659.5	656.9
130°	701.8	702.3	702.8	703.2	703.6	704.1	702.8	699.8	696.9	693.8	690.9
132.5°	739.4	740.4	740.3	740.2	740.1	740.0	738.8	736.3	733.9	731.5	729.0
135°	793.2	793.4	793.0	792.5	792.0	791.6	790.1	787.6	785.1	782.5	780.0
137.5°	845.4	845.6	845.0	844.5	843.8	843.2	841.9	839.8	837.8	835.7	833.6
140°	880.4	880.4	879.3	878.2	877.0	875.8	874.2	872.2	870.0	868.0	865.9
142.5°	912.1	912.0	911.2	910.3	909.5	908.7	907.3	905.3	903.2	901.2	899.1
145°	960.4	960.2	958.8	957.4	956.0	954.7	953.1	951.5	949.9	948.3	946.7
147.5°	1002.6	1002.0	1001.1	1000.2	999.3	998.4	996.9	995.0	993.0	991.1	989.2
150°	1029.2	1028.6	1027.6	1026.7	1025.8	1024.8	1023.7	1022.3	1020.9	1019.6	1018.2
152.5°	1056.0	1055.1	1054.0	1052.8	1051.8	1050.6	1049.4	1048.0	1046.6	1045.3	1043.8
155°	1089.8	1088.6	1088.0	1087.3	1086.5	1085.8	1085.2	1084.5	1083.8	1083.1	1082.4
157.5°	1120.9	1119.3	1118.8	1118.5	1118.0	1117.6	1117.2	1116.7	1116.2	1115.8	1115.4
160°	1139.7	1138.4	1138.1	1137.9	1137.6	1137.4	1137.1	1136.6	1136.1	1135.7	1135.2
162.5°	1156.5	1154.9	1154.7	1154.4	1154.2	1154.0	1153.9	1153.7	1153.6	1153.5	1153.4
165°	1178.3	1176.7	1176.7	1176.7	1176.7	1176.7	1176.8	1177.0	1177.2	1177.5	1177.7
167.5°	1196.3	1194.7	1194.7	1194.8	1194.8	1194.9	1195.2	1196.0	1196.6	1197.3	1198.0
170°	1206.2	1204.6	1204.9	1205.1	1205.3	1205.6	1206.0	1206.7	1207.4	1208.1	1208.8
172.5°	1213.7	1212.1	1212.3	1212.5	1212.8	1213.0	1213.4	1214.2	1214.9	1215.6	1216.2
175°	1221.8	1220.1	1220.7	1221.1	1221.6	1222.0	1222.6	1223.2	1224.0	1224.7	1225.4
177.5°	1226.0	1224.9	1225.3	1225.7	1226.0	1226.4	1226.9	1227.4	1228.0	1228.5	1229.0
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	963.9	964.7	970.1	972.5	977.3	979.2	981.2	980.7	980.7	981.8	989.3
5°	966.0	972.7	982.7	992.3	1001.7	1009.7	1014.9	1020.3	1022.3	1032.0	1040.6
7.5°	962.6	974.8	991.3	1006.0	1023.7	1037.5	1048.9	1059.3	1066.3	1080.4	1094.8
10°	958.1	975.4	994.0	1013.0	1037.3	1055.6	1074.2	1088.6	1093.2	1114.2	1126.2
12.5°	949.0	972.1	995.9	1020.5	1044.2	1069.4	1089.9	1104.3	1120.7	1139.5	1161.6
15°	935.4	962.1	993.0	1024.7	1058.6	1089.2	1111.3	1136.2	1154.1	1174.8	1194.1
17.5°	915.9	950.2	989.5	1026.2	1065.4	1098.3	1128.6	1152.5	1165.2	1177.0	1179.9
20°	900.4	937.4	983.6	1027.0	1066.2	1104.2	1134.2	1154.1	1157.5	1157.8	1140.1
22.5°	883.7	925.4	973.8	1018.2	1065.1	1107.4	1130.7	1139.2	1126.1	1103.5	1069.3
25°	852.8	901.1	957.3	1008.0	1059.3	1099.2	1107.2	1092.3	1046.0	997.3	935.8
27.5°	819.4	873.6	934.0	990.2	1044.9	1069.7	1052.4	998.4	915.0	842.6	754.7
30°	794.9	855.8	915.1	978.0	1028.6	1039.3	999.7	920.1	822.9	713.6	626.1
32.5°	766.9	830.7	895.9	961.0	1003.4	992.9	927.5	829.5	715.5	608.1	525.3
35°	726.9	792.9	863.1	928.4	955.4	910.4	812.5	685.0	568.5	468.2	411.3
37.5°	680.8	752.6	825.6	885.6	883.7	808.7	675.4	543.7	445.8	386.5	345.9
40°	648.0	720.6	799.5	850.2	828.5	730.9	586.4	462.2	390.6	343.3	313.7
42.5°	616.6	689.5	767.9	808.1	770.4	650.5	506.5	409.2	350.1	313.3	289.2
45°	563.1	640.0	712.7	734.9	667.6	535.5	409.6	339.0	299.7	272.4	255.7
47.5°	510.9	586.5	652.7	653.2	562.1	434.3	345.5	293.4	259.8	238.7	226.6
50°	478.8	550.8	606.4	597.7	494.5	386.3	309.0	264.0	236.1	219.8	207.1
52.5°	442.9	512.6	560.8	536.2	437.2	339.9	276.3	238.5	215.3	201.2	189.8
55°	390.6	452.5	486.5	449.2	356.7	282.7	233.4	203.8	186.5	174.5	164.9
57.5°	339.3	390.3	411.7	368.3	293.7	234.4	197.4	175.2	158.0	149.5	144.5
60°	307.0	350.6	365.6	317.7	255.4	205.1	174.9	154.2	141.5	135.9	130.9
62.5°	275.4	310.9	317.2	273.2	222.7	179.6	153.6	136.1	127.7	122.3	117.5
65°	228.5	254.0	251.1	215.8	176.1	142.5	123.5	112.9	106.6	98.9	90.6
67.5°	188.1	203.8	194.3	167.8	134.5	110.8	98.4	90.3	82.5	75.2	73.3
70°	162.5	171.5	161.5	137.2	110.2	92.9	82.9	73.3	68.6	67.0	63.9
72.5°	138.0	141.2	130.4	109.5	89.7	77.0	67.2	61.8	59.3	57.9	55.9
75°	103.5	101.2	91.9	75.6	62.2	53.6	50.6	48.6	47.0	45.7	44.6
77.5°	72.8	69.3	61.0	50.4	43.3	39.2	37.5	36.4	35.6	34.9	33.9
80°	54.6	52.3	44.0	35.9	33.0	30.9	30.0	28.6	28.6	28.0	26.9
82.5°	39.9	37.4	30.1	26.4	24.7	23.5	22.7	21.9	21.7	21.8	21.1
85°	21.0	16.9	15.0	14.4	13.3	12.7	13.0	12.3	12.3	12.3	11.9
87.5°	7.1	6.3	6.7	7.0	8.0	9.0	9.7	10.8	12.0	11.7	11.9
90°	3.8	6.6	9.4	12.1	16.0	21.0	26.1	31.2	36.3	35.8	35.3
92.5°	20.4	22.5	24.5	26.6	28.2	29.3	30.6	31.7	32.9	33.0	33.1
95°	56.2	58.5	60.7	63.0	64.5	64.9	65.4	65.8	66.3	66.3	66.3
97.5°	100.4	102.5	104.5	106.5	108.0	108.8	109.7	110.6	111.5	111.5	111.5
100°	133.4	135.3	137.1	138.9	140.2	140.9	141.5	142.2	142.9	142.9	142.9
102.5°	167.8	169.3	170.8	172.3	173.4	174.3	175.1	176.0	176.9	177.1	177.3
105°	223.4	224.1	224.8	225.4	226.0	226.5	226.9	227.4	227.8	228.4	228.8
107.5°	280.4	281.5	282.5	283.5	284.0	284.0	284.0	284.0	284.0	284.2	284.4
110°	317.3	318.7	320.0	321.5	322.2	322.2	322.2	322.2	322.2	322.2	322.2



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	357.0	358.5	359.8	361.2	361.9	361.6	361.4	361.2	361.1	360.5	360.0
115°	415.7	417.1	418.5	419.8	420.3	419.8	419.4	418.9	418.5	418.2	418.0
117.5°	474.6	476.4	478.2	480.1	480.4	479.1	477.8	476.5	475.2	474.7	474.1
120°	513.5	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7	511.7	511.7
122.5°	549.6	551.7	553.9	556.2	556.6	555.4	554.0	552.8	551.4	550.9	550.4
125°	604.9	607.0	609.0	611.1	611.8	611.1	610.5	609.8	609.0	608.3	607.7
127.5°	659.5	662.2	664.8	667.4	668.3	667.4	666.6	665.8	664.9	664.1	663.3
130°	693.8	696.9	699.8	702.8	704.1	703.6	703.2	702.8	702.3	701.8	701.3
132.5°	731.5	733.9	736.3	738.8	740.0	740.1	740.2	740.3	740.4	739.4	738.3
135°	782.5	785.1	787.6	790.1	791.6	792.0	792.5	793.0	793.4	793.2	793.0
137.5°	835.7	837.8	839.8	841.9	843.2	843.8	844.5	845.0	845.6	845.4	845.3
140°	868.0	870.0	872.2	874.2	875.8	877.0	878.2	879.3	880.4	880.4	880.4
142.5°	901.2	903.2	905.3	907.3	908.7	909.5	910.3	911.2	912.0	912.1	912.3
145°	948.3	949.9	951.5	953.1	954.7	956.0	957.4	958.8	960.2	960.4	960.6
147.5°	991.1	993.0	995.0	996.9	998.4	999.3	1000.2	1001.1	1002.0	1002.6	1003.1
150°	1019.6	1020.9	1022.3	1023.7	1024.8	1025.8	1026.7	1027.6	1028.6	1029.2	1029.9
152.5°	1045.3	1046.6	1048.0	1049.4	1050.6	1051.8	1052.8	1054.0	1055.1	1056.0	1056.9
155°	1083.1	1083.8	1084.5	1085.2	1085.8	1086.5	1087.3	1088.0	1088.6	1089.8	1090.9
157.5°	1115.8	1116.2	1116.7	1117.2	1117.6	1118.0	1118.5	1118.8	1119.3	1120.9	1122.4
160°	1135.7	1136.1	1136.6	1137.1	1137.4	1137.6	1137.9	1138.1	1138.4	1139.7	1141.1
162.5°	1153.5	1153.6	1153.7	1153.9	1154.0	1154.2	1154.4	1154.7	1154.9	1156.5	1158.1
165°	1177.5	1177.2	1177.0	1176.8	1176.7	1176.7	1176.7	1176.7	1176.7	1178.3	1179.9
167.5°	1197.3	1196.6	1196.0	1195.2	1194.9	1194.8	1194.8	1194.7	1194.7	1196.3	1197.9
170°	1208.1	1207.4	1206.7	1206.0	1205.6	1205.3	1205.1	1204.9	1204.6	1206.2	1207.8
172.5°	1215.6	1214.9	1214.2	1213.4	1213.0	1212.8	1212.5	1212.3	1212.1	1213.7	1215.3
175°	1224.7	1224.0	1223.2	1222.6	1222.0	1221.6	1221.1	1220.7	1220.1	1221.8	1223.4
177.5°	1228.5	1228.0	1227.4	1226.9	1226.4	1226.0	1225.7	1225.3	1224.9	1226.0	1227.2
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	991.9	995.4	997.0	997.0	998.9	998.1	997.3
5°	1048.9	1055.3	1056.6	1062.6	1066.9	1065.6	1066.2
7.5°	1105.6	1115.8	1125.9	1130.4	1131.2	1133.9	1134.9
10°	1140.5	1148.9	1164.5	1162.2	1173.8	1180.4	1169.5
12.5°	1174.1	1185.4	1196.2	1199.2	1205.8	1207.9	1203.5
15°	1204.4	1210.4	1211.1	1209.4	1211.5	1209.8	1203.5
17.5°	1176.1	1166.4	1146.7	1137.3	1129.9	1119.0	1114.6
20°	1129.2	1100.5	1067.3	1053.9	1038.3	1007.6	1014.9
22.5°	1028.0	995.3	962.1	923.1	904.6	875.5	873.8
25°	870.5	814.2	752.2	708.9	683.7	654.7	642.0
27.5°	676.8	605.9	555.2	529.5	506.0	483.1	482.1
30°	549.5	496.1	456.9	434.9	420.6	410.9	413.0
32.5°	463.2	426.6	400.1	381.9	371.3	364.0	363.9
35°	378.6	353.7	336.6	329.0	321.4	316.0	316.4
37.5°	324.0	309.0	299.5	291.1	286.3	283.7	282.2
40°	296.0	283.7	276.4	271.4	267.4	263.8	263.1
42.5°	273.9	263.8	256.4	252.4	248.8	246.1	245.5
45°	243.1	234.8	228.1	223.7	222.1	219.8	219.8
47.5°	216.2	208.0	202.9	200.1	197.2	195.7	195.6
50°	198.1	191.8	187.2	185.5	183.2	182.2	181.8
52.5°	181.9	177.2	173.8	172.7	171.7	170.4	170.6
55°	159.8	157.2	155.9	154.8	153.2	151.1	152.5
57.5°	141.2	139.0	135.4	132.2	130.7	129.3	129.8
60°	128.2	123.5	118.9	115.2	114.2	111.2	111.2
62.5°	111.7	105.1	99.4	97.4	96.4	95.0	94.7
65°	85.9	83.3	81.9	80.6	79.9	79.9	79.3
67.5°	71.2	70.1	68.7	68.3	67.7	67.5	67.2
70°	63.0	61.6	60.9	60.6	59.9	60.3	59.3
72.5°	54.9	53.9	53.8	52.9	52.5	52.5	51.8
75°	43.2	43.2	43.0	42.6	42.0	41.6	42.0
77.5°	33.3	33.3	32.7	32.7	32.6	32.7	32.4
80°	26.7	26.9	26.7	26.3	25.9	26.3	25.9
82.5°	21.0	20.6	20.5	20.4	20.4	20.2	20.2
85°	11.9	12.3	11.9	11.7	11.7	11.7	11.9
87.5°	11.5	11.4	11.4	11.4	11.5	11.5	11.3
90°	34.9	34.4	34.3	34.5	34.8	35.0	35.2
92.5°	33.2	33.3	33.3	33.4	33.4	33.5	33.5
95°	66.3	66.3	66.1	65.6	65.2	64.6	64.2
97.5°	111.5	111.5	111.5	111.4	111.4	111.3	111.3
100°	142.9	142.9	142.9	142.6	142.4	142.1	141.9
102.5°	177.5	177.6	177.6	177.4	177.2	176.9	176.7
105°	229.3	229.7	230.0	230.0	230.0	230.0	230.0
107.5°	284.5	284.7	284.3	283.3	282.2	281.2	280.1
110°	322.2	322.2	321.8	321.1	320.4	319.7	319.1



TEST NUMBER: P331670-940

CATALOG NUMBER: SA2XXRDIP-C485D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	359.4	358.9	358.4	357.8	357.3	356.9	356.3
115°	417.8	417.5	417.1	416.4	415.7	415.0	414.3
117.5°	473.6	473.1	472.4	471.7	471.0	470.3	469.7
120°	511.7	511.7	511.3	510.7	510.0	509.3	508.5
122.5°	549.8	549.2	548.8	548.2	547.7	547.2	546.7
125°	607.0	606.3	605.8	605.6	605.4	605.1	604.9
127.5°	662.5	661.6	660.8	660.1	659.4	658.7	657.9
130°	700.9	700.4	699.7	698.8	697.9	697.0	696.1
132.5°	737.4	736.4	735.5	734.8	734.0	733.3	732.5
135°	792.7	792.5	792.0	791.3	790.7	790.0	789.3
137.5°	845.1	844.9	844.4	843.4	842.5	841.6	840.6
140°	880.4	880.4	879.9	879.0	878.2	877.2	876.3
142.5°	912.5	912.7	912.3	911.3	910.4	909.5	908.6
145°	960.9	961.1	960.7	959.8	958.9	958.0	957.1
147.5°	1003.5	1004.1	1003.9	1003.0	1002.1	1001.2	1000.4
150°	1030.6	1031.4	1031.4	1030.6	1029.9	1029.2	1028.6
152.5°	1057.7	1058.5	1058.5	1057.7	1056.9	1056.0	1055.1
155°	1092.1	1093.2	1093.4	1092.8	1092.1	1091.4	1090.7
157.5°	1124.0	1125.5	1125.8	1124.6	1123.6	1122.5	1121.3
160°	1142.5	1143.9	1144.1	1143.2	1142.3	1141.3	1140.4
162.5°	1159.6	1161.2	1161.4	1160.3	1159.2	1158.1	1157.0
165°	1181.5	1183.1	1183.3	1182.2	1181.1	1179.9	1178.8
167.5°	1199.5	1201.1	1201.3	1200.2	1198.9	1197.7	1196.6
170°	1209.4	1211.0	1211.2	1209.8	1208.4	1207.0	1205.7
172.5°	1216.9	1218.5	1218.6	1217.3	1215.8	1214.5	1213.1
175°	1225.0	1226.6	1226.7	1225.4	1224.0	1222.6	1221.2
177.5°	1228.2	1229.3	1229.3	1228.2	1227.2	1226.0	1224.9
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4

(END OF REPORT)