

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332917-930

Luminaire Tested: **SA4XXRDIP-C575D1035U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332917-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D1035U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4836.8 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332917-930
CATALOG NUMBER: SA4XXRDIP-C575D1035U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332917-930

CATALOG NUMBER: SA4XXRDIP-C575D1035U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40				
1	96	91	88	84	87	83	80	77	68	66	64	54	53	52	41	41	40	34				
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	29				
3	80	71	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29	24				
4	73	62	55	49	66	57	51	45	47	42	38	38	34	32	29	27	25	21				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	27	24	22	18				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16				
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	17	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6689	6689	6689
5°	6704	6622	6663
10°	6662	6542	6542
15°	6586	6405	6358
20°	6480	6225	6110
25°	6347	6013	5860
30°	6216	5790	5547
35°	6071	5558	5233
40°	5896	5296	4894
45°	5737	5034	4548
50°	5554	4732	4182
55°	5358	4421	3786
60°	5142	4077	3381
65°	4946	3647	2980
70°	4657	3175	2530
75°	4295	2633	2059
80°	3747	2004	1888
85°	3168	1815	1704



TEST NUMBER: P332917-930

CATALOG NUMBER: SA4XXRDIP-C575D1035U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.8	1.6
10°-20°	217.0	4.5
20°-30°	313.4	6.5
30°-40°	355.3	7.3
40°-50°	343.1	7.1
50°-60°	285.3	5.9
60°-70°	197.0	4.1
70°-80°	99.8	2.1
80°-90°	28.8	0.6
90°-100°	69.4	1.4
100°-110°	205.6	4.3
110°-120°	348.9	7.2
120°-130°	460.1	9.5
130°-140°	516.7	10.7
140°-150°	507.8	10.5
150°-160°	427.1	8.8
160°-170°	284.1	5.9
170°-180°	99.5	2.1
0°-30°	608.3	12.6
0°-40°	963.6	19.9
0°-60°	1591.9	32.9
0°-90°	1917.5	39.6
90°-120°	623.9	12.9
90°-150°	2108.6	43.6
90°-180°	2919.0	60.4
0°-180°	4836.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	827	824	817	823	822	78
15°	788	782	766	765	761	222
25°	712	700	675	664	658	328
35°	616	595	564	543	531	385
45°	502	478	441	411	398	387
55°	381	354	314	282	269	340
65°	259	231	191	165	156	256
75°	138	114	84	70	66	145
85°	34	22	20	18	18	39
90°	2	11	18	23	24	5
95°	49	56	62	64	64	54
105°	190	191	194	196	198	201
115°	355	355	353	352	352	350
125°	517	517	516	514	513	460
135°	666	671	671	670	667	515
145°	810	813	814	813	810	507
155°	928	928	927	930	927	427
165°	1010	1008	1006	1010	1008	285
175°	1051	1047	1046	1051	1046	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332917-930

CATALOG NUMBER: SA4XXRDIP-C575D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	830.6	830.1	829.7	829.2	828.8	827.9	826.7	825.5	824.2	823.0	824.2
5°	827.3	826.7	826.1	825.6	825.1	823.9	822.2	820.5	818.8	817.2	818.6
7.5°	819.8	819.2	818.6	818.1	817.4	816.0	813.8	811.6	809.4	807.2	808.1
10°	812.7	812.0	811.3	810.6	809.9	808.3	805.8	803.2	800.6	798.1	798.7
12.5°	803.6	802.7	801.9	801.1	800.3	798.4	795.4	792.4	789.5	786.4	786.8
15°	788.0	786.7	785.5	784.2	782.9	780.5	777.0	773.5	769.9	766.4	766.1
17.5°	769.1	767.2	765.4	763.5	761.7	758.7	754.5	750.2	746.0	741.8	741.0
20°	754.3	752.5	750.6	748.9	747.0	743.7	738.9	734.1	729.3	724.6	723.4
22.5°	738.1	736.1	734.0	731.9	729.9	726.3	721.1	716.0	710.9	705.7	704.0
25°	712.5	710.0	707.4	704.8	702.3	698.1	692.4	686.6	680.8	675.1	672.6
27.5°	685.6	682.4	679.2	676.0	672.8	668.1	661.9	655.8	649.6	643.4	640.5
30°	666.8	663.2	659.7	656.2	652.7	647.6	641.0	634.4	627.7	621.1	617.6
32.5°	647.0	643.0	639.0	635.0	631.1	625.7	618.8	612.0	605.1	598.3	594.2
35°	616.0	611.6	607.0	602.5	598.0	592.2	585.1	578.1	571.0	564.0	559.2
37.5°	582.9	578.3	573.6	569.0	564.3	558.1	550.2	542.4	534.7	526.8	521.5
40°	559.5	554.9	550.2	545.6	541.0	534.6	526.6	518.5	510.5	502.5	496.5
42.5°	537.2	532.4	527.5	522.6	517.7	511.1	502.7	494.3	486.0	477.6	471.6
45°	502.5	497.3	492.0	486.8	481.6	474.7	466.3	457.9	449.4	440.9	434.0
47.5°	466.6	461.2	455.8	450.4	445.0	437.9	429.1	420.4	411.6	402.8	395.6
50°	442.2	436.7	431.2	425.7	420.2	412.9	403.9	394.9	385.9	376.8	369.8
52.5°	417.4	412.0	406.6	401.2	395.7	388.5	379.2	370.0	360.7	351.5	344.3
55°	380.7	375.0	369.4	363.7	358.1	350.7	341.5	332.4	323.2	314.1	306.7
57.5°	344.4	338.5	332.6	326.8	320.9	313.5	304.4	295.4	286.4	277.4	269.9
60°	318.5	312.8	307.2	301.6	296.0	288.6	279.6	270.5	261.5	252.5	245.2
62.5°	295.1	289.3	283.4	277.5	271.7	264.2	254.9	245.6	236.4	227.1	220.4
65°	258.9	252.8	246.7	240.7	234.6	227.1	218.0	209.0	200.0	190.9	184.9
67.5°	221.2	215.3	209.5	203.7	198.0	190.9	182.5	174.1	165.8	157.4	152.1
70°	197.3	191.4	185.5	179.5	173.7	166.6	158.6	150.6	142.5	134.5	129.9
72.5°	171.9	166.6	161.2	155.9	150.5	144.1	136.5	128.9	121.2	113.7	109.7
75°	137.7	132.5	127.3	122.1	116.8	110.9	104.3	97.6	91.0	84.4	81.1
77.5°	102.9	98.5	94.1	89.6	85.2	80.3	74.9	69.6	64.2	58.9	57.0
80°	80.6	76.5	72.4	68.3	64.2	60.1	55.8	51.6	47.4	43.1	42.7
82.5°	61.3	57.6	53.8	50.1	46.3	43.2	40.8	38.3	36.0	33.5	33.2
85°	34.2	31.5	28.6	25.8	23.0	21.4	21.0	20.5	20.1	19.6	19.4
87.5°	12.1	11.7	11.2	10.7	10.1	9.9	10.2	10.4	10.5	10.7	10.8
90°	2.4	4.4	6.4	8.4	10.4	12.1	13.5	15.0	16.5	17.9	19.0
92.5°	17.4	19.7	21.9	24.2	26.5	28.2	29.2	30.2	31.2	32.2	32.9
95°	48.8	50.5	52.1	53.7	55.4	56.7	58.0	59.4	60.6	61.9	62.4
97.5°	85.3	86.6	87.9	89.2	90.5	91.9	93.4	94.8	96.4	97.8	98.5
100°	113.9	114.6	115.4	116.1	116.8	118.0	119.6	121.2	122.9	124.5	124.9
102.5°	143.9	144.1	144.5	144.7	145.0	145.9	147.4	148.9	150.3	151.9	152.4
105°	189.6	189.8	190.0	190.1	190.4	190.8	191.5	192.2	193.0	193.7	194.2
107.5°	237.7	237.8	238.1	238.3	238.5	238.6	238.8	238.9	239.0	239.1	239.6
110°	270.2	270.5	270.9	271.3	271.7	271.7	271.5	271.3	271.2	271.0	270.6



TEST NUMBER: P332917-930

CATALOG NUMBER: SA4XXRDIP-C575D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	304.0	304.1	304.2	304.3	304.4	304.2	303.9	303.5	303.2	302.9	302.8
115°	354.8	354.8	354.8	354.8	354.8	354.7	354.2	353.9	353.5	353.2	353.0
117.5°	402.7	402.8	402.9	403.1	403.2	403.2	402.9	402.7	402.4	402.2	401.5
120°	434.6	435.3	436.0	436.8	437.5	437.6	437.0	436.4	435.9	435.4	434.5
122.5°	467.7	468.1	468.3	468.6	468.9	469.0	468.7	468.4	468.1	467.9	467.3
125°	516.7	516.7	516.7	516.7	516.7	516.7	516.5	516.3	516.1	515.9	515.6
127.5°	561.2	561.7	562.2	562.8	563.4	563.5	563.2	562.9	562.6	562.3	562.0
130°	592.4	593.0	593.5	594.0	594.6	594.8	594.8	594.8	594.8	594.8	594.5
132.5°	624.4	624.8	625.1	625.5	625.9	626.1	625.9	625.7	625.6	625.5	625.1
135°	666.5	667.6	668.6	669.8	670.8	671.4	671.4	671.4	671.4	671.4	671.0
137.5°	712.4	712.9	713.4	713.9	714.4	714.8	715.1	715.4	715.7	716.0	715.5
140°	743.0	743.3	743.7	744.0	744.4	744.6	744.6	744.6	744.6	744.6	744.4
142.5°	770.9	771.4	771.7	772.1	772.4	772.5	772.4	772.3	772.1	771.9	771.9
145°	809.7	810.4	811.1	811.9	812.6	813.0	813.3	813.4	813.6	813.8	813.6
147.5°	848.2	849.0	849.9	850.8	851.6	852.0	851.8	851.7	851.5	851.4	851.3
150°	871.6	872.3	873.0	873.8	874.5	874.8	874.8	874.8	874.8	874.8	874.8
152.5°	893.7	894.1	894.5	895.0	895.4	895.7	895.9	896.0	896.2	896.3	896.7
155°	927.7	927.7	927.7	927.7	927.7	927.6	927.4	927.2	927.1	926.9	927.6
157.5°	956.3	956.0	955.7	955.4	955.0	954.9	954.8	954.8	954.8	954.7	955.3
160°	973.3	973.1	972.9	972.7	972.6	972.4	972.2	972.0	971.8	971.7	972.2
162.5°	988.9	988.5	988.0	987.5	987.0	986.7	986.5	986.3	986.2	985.9	986.9
165°	1009.9	1009.3	1008.9	1008.3	1007.7	1007.3	1006.9	1006.6	1006.2	1005.8	1006.9
167.5°	1026.1	1025.2	1024.5	1023.8	1023.0	1022.6	1022.6	1022.7	1022.7	1022.8	1023.9
170°	1035.1	1034.2	1033.3	1032.4	1031.5	1031.1	1031.4	1031.5	1031.7	1031.8	1033.0
172.5°	1041.6	1040.9	1040.2	1039.3	1038.6	1038.2	1038.3	1038.3	1038.4	1038.4	1039.6
175°	1050.6	1049.7	1048.8	1047.9	1047.0	1046.4	1046.3	1046.0	1045.9	1045.7	1047.0
177.5°	1053.5	1052.8	1052.1	1051.3	1050.6	1050.3	1050.3	1050.3	1050.3	1050.3	1051.2
180°	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2



TEST NUMBER: P332917-930

CATALOG NUMBER: SA4XXRDIP-C575D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	825.5	826.7	827.9	828.5	828.4	828.3	828.2	828.1
5°	819.9	821.4	822.8	823.4	823.0	822.8	822.5	822.2
7.5°	809.0	809.9	810.9	811.1	810.7	810.2	809.8	809.3
10°	799.2	799.8	800.4	800.4	799.8	799.2	798.7	798.1
12.5°	787.1	787.4	787.8	787.6	786.8	786.0	785.2	784.4
15°	765.8	765.6	765.2	764.7	763.6	762.6	761.7	760.7
17.5°	740.2	739.4	738.6	737.4	736.0	734.5	733.0	731.5
20°	722.3	721.1	720.0	718.5	716.7	714.9	713.1	711.2
22.5°	702.4	700.7	699.0	697.4	695.9	694.4	692.9	691.4
25°	670.3	667.8	665.4	663.6	662.1	660.7	659.3	657.9
27.5°	637.5	634.5	631.6	629.1	627.0	625.0	623.1	621.0
30°	614.1	610.5	607.0	604.1	601.9	599.6	597.4	595.1
32.5°	590.1	586.0	581.9	578.8	576.7	574.5	572.3	570.2
35°	554.4	549.6	544.9	541.2	538.7	536.1	533.5	531.0
37.5°	516.1	510.8	505.4	501.5	498.9	496.4	493.8	491.3
40°	490.6	484.7	478.7	474.6	472.0	469.4	466.9	464.4
42.5°	465.5	459.5	453.5	449.1	446.5	443.8	441.2	438.5
45°	427.1	420.2	413.3	408.5	406.0	403.5	401.0	398.4
47.5°	388.4	381.2	374.1	369.1	366.3	363.5	360.8	357.9
50°	362.7	355.7	348.6	343.8	341.1	338.4	335.7	333.0
52.5°	337.1	330.0	322.9	317.9	315.0	312.3	309.5	306.7
55°	299.4	292.0	284.7	279.7	277.0	274.3	271.7	269.0
57.5°	262.4	255.0	247.6	242.9	240.8	238.8	236.8	234.7
60°	237.8	230.5	223.1	218.4	216.1	213.9	211.7	209.4
62.5°	213.6	206.8	200.1	195.8	194.0	192.2	190.4	188.6
65°	178.9	172.8	166.7	162.8	161.2	159.5	157.8	156.0
67.5°	146.9	141.7	136.5	133.0	131.1	129.2	127.3	125.5
70°	125.2	120.6	115.9	112.8	111.5	110.1	108.6	107.2
72.5°	105.7	101.7	97.8	95.1	93.8	92.5	91.2	89.9
75°	77.9	74.7	71.4	69.4	68.5	67.7	66.9	66.0
77.5°	55.1	53.2	51.3	50.2	50.0	49.7	49.5	49.2
80°	42.3	41.9	41.4	41.2	41.0	40.8	40.8	40.6
82.5°	32.9	32.5	32.3	32.0	31.9	31.7	31.6	31.5
85°	19.1	18.8	18.5	18.4	18.4	18.4	18.4	18.4
87.5°	10.9	11.0	11.1	11.3	11.4	11.7	11.8	12.0
90°	20.1	21.2	22.3	23.0	23.3	23.7	24.1	24.4
92.5°	33.5	34.2	34.8	35.3	35.5	35.7	36.0	36.1
95°	62.9	63.5	64.0	64.3	64.3	64.3	64.3	64.3
97.5°	99.1	99.8	100.4	100.8	100.8	100.8	100.8	100.8
100°	125.2	125.6	126.0	126.1	126.1	126.1	126.1	126.1
102.5°	152.9	153.4	153.8	154.2	154.3	154.5	154.7	154.7
105°	194.8	195.3	195.8	196.4	196.9	197.5	198.0	198.5
107.5°	240.1	240.6	241.1	241.3	241.3	241.2	241.2	241.2
110°	270.3	269.9	269.5	269.6	270.2	270.7	271.3	271.8



TEST NUMBER: P332917-930

CATALOG NUMBER: SA4XXRDIP-C575D1035U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	302.7	302.6	302.6	302.6	302.7	302.8	303.0	303.0
115°	352.8	352.6	352.5	352.3	352.1	351.9	351.7	351.6
117.5°	401.0	400.3	399.7	399.3	398.8	398.5	398.1	397.8
120°	433.6	432.7	431.8	431.5	431.9	432.2	432.6	432.9
122.5°	466.7	466.1	465.5	464.8	464.1	463.5	462.8	462.2
125°	515.2	514.9	514.5	514.1	513.8	513.4	513.1	512.7
127.5°	561.6	561.3	560.8	560.5	560.3	559.9	559.7	559.4
130°	594.2	593.8	593.5	592.9	592.2	591.4	590.7	590.0
132.5°	624.8	624.4	624.0	623.7	623.4	623.1	622.8	622.6
135°	670.7	670.3	669.9	669.4	669.0	668.4	667.8	667.3
137.5°	715.0	714.5	714.1	713.9	714.0	714.1	714.2	714.4
140°	744.3	744.0	743.9	743.7	743.6	743.3	743.1	743.0
142.5°	771.8	771.8	771.8	771.8	771.8	771.7	771.7	771.6
145°	813.4	813.3	813.0	812.7	812.1	811.6	811.1	810.5
147.5°	851.1	850.9	850.8	850.6	850.4	850.3	850.1	849.9
150°	874.8	874.8	874.8	874.7	874.6	874.3	874.2	874.0
152.5°	897.2	897.6	898.1	898.1	897.6	897.1	896.6	896.1
155°	928.4	929.0	929.8	929.8	929.0	928.4	927.6	926.9
157.5°	955.8	956.3	956.9	956.8	956.3	955.6	955.0	954.4
160°	972.7	973.3	973.8	973.6	972.7	971.8	970.9	970.0
162.5°	987.9	988.9	989.9	989.9	989.0	988.1	987.2	986.3
165°	1008.0	1009.1	1010.2	1010.3	1009.7	1008.9	1008.2	1007.5
167.5°	1024.9	1026.1	1027.1	1027.1	1026.0	1024.8	1023.7	1022.6
170°	1034.0	1035.1	1036.2	1036.1	1034.9	1033.6	1032.3	1031.0
172.5°	1040.8	1042.0	1043.3	1043.3	1042.0	1040.7	1039.5	1038.2
175°	1048.2	1049.5	1050.8	1050.8	1049.5	1048.2	1047.0	1045.7
177.5°	1052.3	1053.3	1054.3	1054.3	1053.1	1051.9	1050.8	1049.6
180°	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2	1052.2

(END OF REPORT)