

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331656-940

Luminaire Tested: **SA2XXRDIP-C485D530U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331656-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D530U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3356.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331656-940
CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331656-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33				
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29				
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25				
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22				
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	22	20				
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17				
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14				
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11880	11880	11880
5°	11925	11733	11797
10°	11835	11540	11442
15°	11699	11198	10877
20°	11510	10710	10172
25°	11318	10156	9492
30°	11050	9587	8617
35°	10789	8966	7849
40°	10526	8323	6962
45°	10218	7604	6158
50°	9902	6875	5368
55°	9579	6092	4611
60°	9203	5270	3827
65°	8779	4424	3484
70°	8266	3644	3205
75°	7642	3319	2994
80°	6750	2966	2724
85°	5298	2353	2353



TEST NUMBER: P331656-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.9	2.1
10°-20°	189.1	5.6
20°-30°	265.6	7.9
30°-40°	289.6	8.6
40°-50°	266.3	7.9
50°-60°	209.1	6.2
60°-70°	136.4	4.1
70°-80°	70.3	2.1
80°-90°	20.6	0.6
90°-100°	105.7	3.2
100°-110°	358.8	10.7
110°-120°	381.2	11.4
120°-130°	313.8	9.3
130°-140°	252.0	7.5
140°-150°	190.4	5.7
150°-160°	133.8	4.0
160°-170°	78.8	2.3
170°-180°	25.6	0.8
0°-30°	523.6	15.6
0°-40°	813.2	24.2
0°-60°	1288.6	38.4
0°-90°	1515.9	45.2
90°-120°	845.7	25.2
90°-150°	1601.9	47.7
90°-180°	1840.0	54.8
0°-180°	3356.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	736	736	736	736	736	
5°	736	732	724	729	728	70
15°	700	692	670	658	651	197
25°	635	613	570	544	533	292
35°	547	512	455	414	398	342
45°	448	402	333	287	270	345
55°	340	287	216	178	164	304
65°	230	176	116	94	91	228
75°	122	77	53	49	48	130
85°	29	15	13	13	13	34
90°	0	7	17	16	17	2
95°	18	44	199	75	58	19
105°	62	94	377	674	573	66
115°	109	138	315	651	754	108
125°	153	180	303	527	612	135
135°	179	214	300	443	507	138
145°	204	235	298	370	405	128
155°	232	251	289	327	340	107
165°	253	261	277	294	298	71
175°	264	264	266	270	269	25
180°	264	264	264	264	264	



TEST NUMBER: P331656-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	738.5	738.0	737.4	736.7	736.2	735.2	734.0	732.6	731.3	730.0	731.2
5°	735.8	735.1	734.4	733.7	732.9	731.6	729.7	727.7	725.9	723.9	725.2
7.5°	728.3	727.4	726.5	725.5	724.6	723.0	720.8	718.5	716.3	714.1	714.4
10°	721.9	720.9	719.8	718.8	717.7	715.8	712.8	709.8	706.9	703.9	703.5
12.5°	713.9	712.7	711.3	710.1	708.8	706.3	702.5	698.7	694.9	691.2	690.4
15°	699.9	698.3	696.7	695.0	693.4	690.1	685.0	680.0	675.0	669.9	667.2
17.5°	682.8	680.3	677.8	675.3	672.8	668.3	661.9	655.4	649.0	642.5	639.2
20°	669.9	667.0	664.1	661.1	658.1	652.9	645.5	638.1	630.7	623.3	619.6
22.5°	656.1	652.8	649.4	646.1	642.8	637.0	628.7	620.3	612.0	603.6	598.9
25°	635.3	630.6	625.9	621.1	616.4	609.1	599.3	589.6	579.8	570.1	564.0
27.5°	610.3	605.1	599.9	594.9	589.7	581.6	570.6	559.5	548.6	537.5	530.5
30°	592.7	587.1	581.5	575.9	570.2	561.5	549.7	537.8	525.9	514.2	506.6
32.5°	575.7	569.1	562.5	556.0	549.4	540.0	528.0	515.9	503.8	491.8	483.1
35°	547.4	539.8	532.4	524.8	517.2	506.9	493.9	480.9	467.9	454.9	445.5
37.5°	519.2	510.9	502.6	494.3	486.1	474.9	461.1	447.2	433.3	419.5	409.1
40°	499.4	490.6	481.7	472.9	464.0	452.4	438.0	423.7	409.3	394.9	384.4
42.5°	479.2	469.8	460.5	451.2	441.8	429.7	414.9	400.0	385.2	370.4	359.5
45°	447.5	437.7	427.7	417.8	407.9	395.1	379.6	364.1	348.5	333.0	322.4
47.5°	416.6	406.1	395.7	385.1	374.6	361.3	345.3	329.2	313.2	297.1	286.7
50°	394.2	383.7	373.3	362.7	352.2	338.9	322.5	306.3	290.0	273.7	263.5
52.5°	372.4	361.4	350.4	339.5	328.5	315.0	299.1	283.2	267.2	251.4	241.5
55°	340.3	328.8	317.2	305.7	294.2	280.4	264.4	248.4	232.4	216.4	207.6
57.5°	307.4	295.6	283.7	271.9	260.0	246.5	231.1	215.7	200.4	185.0	176.8
60°	285.0	273.2	261.4	249.5	237.6	224.2	208.9	193.7	178.4	163.2	155.6
62.5°	263.1	251.4	239.5	227.7	215.8	202.7	188.2	173.6	159.1	144.5	137.3
65°	229.8	217.8	205.8	193.8	181.8	169.2	155.9	142.5	129.2	115.8	110.8
67.5°	197.5	185.7	173.7	161.8	149.9	137.9	126.0	114.0	102.0	90.1	87.7
70°	175.1	163.6	152.0	140.5	128.9	118.1	107.9	97.6	87.5	77.2	75.8
72.5°	153.8	142.8	131.7	120.6	109.6	100.0	91.8	83.6	75.3	67.1	65.9
75°	122.5	112.2	101.8	91.5	81.1	73.4	68.4	63.3	58.3	53.2	52.3
77.5°	91.8	82.7	73.6	64.5	55.5	49.7	47.3	44.9	42.4	39.9	39.3
80°	72.6	65.0	57.5	49.9	42.4	37.9	36.4	35.0	33.4	31.9	31.4
82.5°	55.0	49.1	43.2	37.4	31.5	28.0	27.0	25.9	25.0	24.0	23.6
85°	28.6	25.5	22.4	19.4	16.2	14.4	14.0	13.6	13.1	12.7	12.7
87.5°	8.6	8.0	7.4	6.7	6.0	5.8	6.3	7.0	7.6	7.8	7.5
90°	0.5	2.1	4.1	5.1	6.1	7.7	10.2	13.7	16.8	17.3	16.8
92.5°	6.2	8.9	12.6	14.9	18.3	23.1	34.6	50.7	65.2	66.1	55.8
95°	17.8	19.8	24.9	29.5	37.6	49.8	73.2	117.4	176.5	199.4	174.4
97.5°	29.0	31.7	37.1	44.1	53.4	67.2	96.7	158.3	256.3	340.3	357.0
100°	39.1	40.7	45.3	53.4	63.6	77.8	104.8	166.8	276.6	401.7	474.9
102.5°	48.5	49.7	54.2	62.3	72.9	87.1	112.1	167.2	268.9	403.8	518.9
105°	62.1	64.1	67.6	75.3	86.4	100.7	124.6	169.9	253.8	376.8	512.1
107.5°	76.7	78.3	81.8	88.8	99.9	114.2	137.4	176.8	246.2	347.9	467.4
110°	86.4	88.5	91.6	98.2	108.8	123.6	146.0	182.5	244.6	334.1	439.3



TEST NUMBER: P331656-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	95.4	97.5	100.9	107.1	117.3	132.5	154.1	188.7	245.0	325.1	419.8
115°	109.3	111.9	114.9	121.0	131.2	144.9	166.8	197.8	247.2	315.3	395.7
117.5°	123.8	125.8	128.9	134.3	144.0	158.3	178.5	207.6	250.8	310.5	380.4
120°	132.7	134.7	137.8	142.4	152.6	166.8	186.6	214.1	253.2	307.6	372.3
122.5°	141.2	142.9	146.0	151.0	161.1	175.8	194.4	219.8	256.1	306.0	365.3
125°	152.6	154.1	157.1	163.3	173.4	187.6	206.0	228.8	260.4	303.1	355.4
127.5°	161.5	163.5	167.8	174.5	184.3	198.9	216.8	237.3	264.7	301.4	346.3
130°	166.8	168.8	173.9	181.0	191.2	205.5	223.3	242.5	268.0	300.5	340.2
132.5°	171.7	174.2	179.6	187.2	197.7	212.0	228.9	247.9	271.3	300.1	335.3
135°	179.0	181.0	187.2	194.7	206.4	220.7	237.0	254.8	275.1	299.5	328.5
137.5°	185.9	188.3	194.5	202.6	214.2	227.4	243.5	260.0	278.6	299.4	323.7
140°	191.2	193.2	199.4	207.5	218.6	231.9	247.2	262.9	280.2	299.0	320.9
142.5°	196.5	198.1	203.8	212.0	222.7	235.1	250.0	265.4	281.4	299.0	318.1
145°	204.5	206.4	211.5	219.2	229.3	240.5	254.2	268.5	282.8	298.0	314.2
147.5°	212.9	214.5	219.4	226.4	234.9	244.8	257.7	270.3	283.1	296.1	310.4
150°	218.6	220.2	224.3	230.9	238.5	247.6	259.3	271.1	282.8	295.0	307.2
152.5°	224.4	225.1	229.2	235.0	242.2	250.5	261.0	271.4	282.0	292.9	304.3
155°	232.4	232.9	235.9	241.6	247.2	254.8	263.4	272.1	280.7	289.4	299.0
157.5°	239.1	239.6	242.1	246.9	251.5	257.8	265.1	272.1	278.4	285.7	294.0
160°	243.6	244.1	246.1	250.2	254.2	259.8	266.0	272.1	277.1	283.3	290.3
162.5°	248.1	247.7	249.8	253.1	256.7	261.1	266.4	271.6	275.9	281.2	287.1
165°	253.2	252.7	253.8	256.8	259.3	262.4	267.0	270.5	273.6	277.1	281.7
167.5°	257.5	256.9	257.8	259.8	261.6	263.5	266.9	269.8	271.3	273.6	276.4
170°	260.4	259.3	259.8	261.4	262.4	263.9	266.4	269.0	270.0	271.5	273.6
172.5°	262.0	261.4	261.1	262.6	263.2	264.3	266.1	267.8	268.4	269.1	270.7
175°	263.9	263.4	262.9	263.9	263.9	264.4	265.5	266.4	266.0	266.4	267.0
177.5°	264.8	264.0	263.6	264.4	264.4	264.4	264.8	265.6	264.8	264.4	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4



TEST NUMBER: P331656-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	732.4	733.6	734.8	735.2	735.0	734.8	734.5	734.3
5°	726.6	727.9	729.2	729.7	729.2	728.8	728.3	727.9
7.5°	714.8	715.2	715.6	715.4	714.6	713.8	713.1	712.3
10°	703.0	702.6	702.1	701.5	700.6	699.7	698.8	697.9
12.5°	689.6	688.8	688.0	686.8	685.3	683.9	682.3	680.9
15°	664.3	661.6	658.7	656.6	655.1	653.6	652.1	650.7
17.5°	635.8	632.5	629.1	626.2	623.7	621.1	618.6	616.0
20°	615.9	612.2	608.5	605.0	601.8	598.5	595.3	592.0
22.5°	594.1	589.3	584.6	580.9	578.5	576.1	573.7	571.2
25°	557.9	551.9	545.8	541.6	539.4	537.2	535.0	532.8
27.5°	523.4	516.3	509.3	504.0	500.4	497.0	493.4	489.9
30°	499.0	491.5	483.9	478.1	474.1	470.2	466.2	462.2
32.5°	474.5	465.9	457.3	451.1	447.4	443.6	439.8	436.0
35°	436.2	426.9	417.6	411.3	408.0	404.7	401.5	398.2
37.5°	398.9	388.6	378.4	371.3	367.7	363.9	360.2	356.4
40°	373.9	363.4	352.8	345.7	341.9	338.0	334.1	330.3
42.5°	348.7	337.8	327.0	319.7	315.9	312.2	308.4	304.7
45°	311.9	301.5	291.0	283.9	280.4	276.8	273.2	269.7
47.5°	276.3	265.8	255.4	248.5	245.3	242.1	238.8	235.6
50°	253.2	243.1	232.8	226.2	223.1	220.0	216.9	213.7
52.5°	231.6	221.8	211.9	205.5	202.7	199.8	196.9	194.0
55°	198.7	189.8	180.9	175.0	172.3	169.4	166.7	163.8
57.5°	168.7	160.6	152.5	147.2	144.8	142.5	140.1	137.7
60°	148.0	140.5	133.0	128.0	125.6	123.2	120.9	118.5
62.5°	130.1	123.0	115.7	111.5	110.0	108.6	107.2	105.8
65°	105.8	100.8	95.8	93.0	92.6	92.1	91.7	91.2
67.5°	85.4	83.1	80.8	79.5	78.9	78.5	78.0	77.5
70°	74.3	72.9	71.3	70.3	69.7	69.1	68.5	67.9
72.5°	64.6	63.4	62.2	61.3	61.0	60.6	60.3	59.9
75°	51.2	50.2	49.1	48.5	48.4	48.2	48.1	48.0
77.5°	38.8	38.2	37.6	37.2	36.9	36.7	36.5	36.2
80°	30.8	30.2	29.6	29.3	29.3	29.3	29.3	29.3
82.5°	23.3	22.9	22.6	22.4	22.4	22.4	22.4	22.4
85°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7
87.5°	7.3	7.0	7.0	7.0	7.0	7.0	7.0	7.0
90°	16.2	15.2	16.2	16.8	16.8	16.8	16.8	16.8
92.5°	44.3	38.1	33.8	30.6	30.2	28.6	29.0	28.2
95°	133.2	102.2	80.9	69.6	63.0	59.0	57.4	58.0
97.5°	310.9	254.4	199.4	162.6	138.3	125.8	118.4	114.1
100°	464.3	401.3	331.5	270.0	227.8	206.0	191.2	182.1
102.5°	564.8	550.5	499.6	434.4	388.5	351.2	332.8	320.4
105°	617.9	675.3	682.0	665.1	633.6	602.1	580.2	573.1
107.5°	579.6	666.2	719.1	743.7	747.6	745.9	741.5	732.1
110°	546.7	637.7	702.8	744.5	766.3	776.1	780.6	780.1



TEST NUMBER: P331656-940

CATALOG NUMBER: SA2XXRDIP-C485D530U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	516.6	604.0	673.5	721.3	751.7	767.9	776.5	779.3
115°	479.6	557.9	624.5	676.9	712.9	736.4	749.6	754.1
117.5°	451.7	520.4	580.9	630.0	666.8	691.5	705.4	709.3
120°	437.8	500.9	554.8	601.1	636.7	660.6	675.3	680.4
122.5°	426.9	484.6	535.7	577.5	609.4	632.9	646.0	650.3
125°	410.9	463.2	508.0	546.2	575.7	594.9	607.7	611.8
127.5°	395.1	442.6	484.7	520.0	545.6	563.7	574.7	578.0
130°	385.0	428.7	468.9	502.4	527.4	544.7	554.8	558.8
132.5°	375.2	415.7	452.6	484.1	508.6	525.9	535.3	539.0
135°	361.6	395.1	428.7	457.2	479.0	495.8	505.0	507.0
137.5°	350.7	378.8	405.4	430.3	450.1	464.6	472.6	475.6
140°	343.8	368.2	391.6	413.9	430.3	443.4	451.0	454.1
142.5°	338.0	358.8	379.0	397.7	413.1	425.2	431.9	432.6
145°	330.0	346.8	362.6	377.4	389.5	398.1	403.2	404.7
147.5°	323.9	337.1	349.4	360.2	370.2	377.1	380.6	381.5
150°	319.3	330.6	341.3	350.4	358.0	364.1	367.1	367.7
152.5°	314.9	325.3	334.3	342.2	348.2	353.6	355.8	355.9
155°	308.7	316.8	324.4	330.0	335.6	339.2	341.3	340.2
157.5°	301.5	308.3	314.7	319.1	323.0	326.0	326.9	326.9
160°	296.9	302.6	308.2	311.7	315.3	317.8	318.3	318.3
162.5°	292.5	297.3	302.1	304.8	308.4	310.1	310.6	310.2
165°	285.8	289.4	292.9	295.0	296.9	299.0	299.0	298.5
167.5°	279.4	282.1	284.5	286.4	287.3	288.5	288.4	287.8
170°	276.2	277.7	279.7	280.7	281.2	282.8	282.2	281.2
172.5°	272.5	273.6	275.2	275.8	276.3	277.1	276.5	275.9
175°	268.5	269.0	269.6	270.0	270.0	270.5	270.0	269.0
177.5°	265.6	265.6	266.1	266.1	266.1	266.1	265.6	264.8
180°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4

(END OF REPORT)