

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332904-930

Luminaire Tested: **SA4XXRDIP-C575D590U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332904-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C575D590U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3839.5 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332904-930

CATALOG NUMBER: SA4XXRDIP-C575D590U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332904-930

CATALOG NUMBER: SA4XXRDIP-C575D590U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	87	90	87	83	81	73	71	69	61	60	58	50	49	48	43				
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36				
3	82	72	65	60	75	67	61	56	57	52	49	48	45	42	39	37	35	31				
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27				
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	27	23				
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	21				
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18				
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	24	21	19	16				
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15				
10	47	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6689	6689	6689
5°	6704	6622	6663
10°	6662	6542	6542
15°	6586	6405	6358
20°	6480	6225	6110
25°	6347	6013	5860
30°	6216	5790	5547
35°	6071	5558	5233
40°	5896	5296	4894
45°	5737	5034	4548
50°	5554	4732	4182
55°	5358	4421	3786
60°	5142	4077	3381
65°	4946	3647	2980
70°	4657	3175	2530
75°	4295	2633	2059
80°	3747	2004	1888
85°	3168	1815	1704



TEST NUMBER: P332904-930

CATALOG NUMBER: SA4XXRDIP-C575D590U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.8	2.0
10°-20°	217.0	5.7
20°-30°	313.4	8.2
30°-40°	355.3	9.3
40°-50°	343.1	8.9
50°-60°	285.3	7.4
60°-70°	197.0	5.1
70°-80°	99.8	2.6
80°-90°	27.4	0.7
90°-100°	21.3	0.6
100°-110°	135.6	3.5
110°-120°	259.4	6.8
120°-130°	329.3	8.6
130°-140°	352.3	9.2
140°-150°	329.4	8.6
150°-160°	265.7	6.9
160°-170°	171.4	4.5
170°-180°	59.1	1.5
0°-30°	608.3	15.8
0°-40°	963.6	25.1
0°-60°	1591.9	41.5
0°-90°	1916.1	49.9
90°-120°	416.3	10.8
90°-150°	1427.3	37.2
90°-180°	1923.0	50.1
0°-180°	3839.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	827	824	817	823	822	78
15°	788	782	766	765	761	222
25°	712	700	675	664	658	328
35°	616	595	564	543	531	385
45°	502	478	441	411	398	387
55°	381	354	314	282	269	340
65°	259	231	191	165	156	256
75°	138	114	84	70	66	145
85°	34	22	20	18	18	39
90°	1	6	10	13	14	3
95°	26	11	10	13	14	33
105°	140	143	145	148	133	146
115°	261	263	262	263	263	257
125°	367	369	368	370	370	328
135°	456	455	457	458	459	351
145°	526	527	527	527	528	328
155°	576	577	575	577	576	266
165°	608	606	606	609	605	172
175°	622	619	620	623	618	59
180°	622	622	622	622	622	



TEST NUMBER: P332904-930

CATALOG NUMBER: SA4XXRDIP-C575D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	830.6	830.1	829.7	829.2	828.8	827.9	826.7	825.5	824.2	823.0	824.2
5°	827.3	826.7	826.1	825.6	825.1	823.9	822.2	820.5	818.8	817.2	818.6
7.5°	819.8	819.2	818.6	818.1	817.4	816.0	813.8	811.6	809.4	807.2	808.1
10°	812.7	812.0	811.3	810.6	809.9	808.3	805.8	803.2	800.6	798.1	798.7
12.5°	803.6	802.7	801.9	801.1	800.3	798.4	795.4	792.4	789.5	786.4	786.8
15°	788.0	786.7	785.5	784.2	782.9	780.5	777.0	773.5	769.9	766.4	766.1
17.5°	769.1	767.2	765.4	763.5	761.7	758.7	754.5	750.2	746.0	741.8	741.0
20°	754.3	752.5	750.6	748.9	747.0	743.7	738.9	734.1	729.3	724.6	723.4
22.5°	738.1	736.1	734.0	731.9	729.9	726.3	721.1	716.0	710.9	705.7	704.0
25°	712.5	710.0	707.4	704.8	702.3	698.1	692.4	686.6	680.8	675.1	672.6
27.5°	685.6	682.4	679.2	676.0	672.8	668.1	661.9	655.8	649.6	643.4	640.5
30°	666.8	663.2	659.7	656.2	652.7	647.6	641.0	634.4	627.7	621.1	617.6
32.5°	647.0	643.0	639.0	635.0	631.1	625.7	618.8	612.0	605.1	598.3	594.2
35°	616.0	611.6	607.0	602.5	598.0	592.2	585.1	578.1	571.0	564.0	559.2
37.5°	582.9	578.3	573.6	569.0	564.3	558.1	550.2	542.4	534.7	526.8	521.5
40°	559.5	554.9	550.2	545.6	541.0	534.6	526.6	518.5	510.5	502.5	496.5
42.5°	537.2	532.4	527.5	522.6	517.7	511.1	502.7	494.3	486.0	477.6	471.6
45°	502.5	497.3	492.0	486.8	481.6	474.7	466.3	457.9	449.4	440.9	434.0
47.5°	466.6	461.2	455.8	450.4	445.0	437.9	429.1	420.4	411.6	402.8	395.6
50°	442.2	436.7	431.2	425.7	420.2	412.9	403.9	394.9	385.9	376.8	369.8
52.5°	417.4	412.0	406.6	401.2	395.7	388.5	379.2	370.0	360.7	351.5	344.3
55°	380.7	375.0	369.4	363.7	358.1	350.7	341.5	332.4	323.2	314.1	306.7
57.5°	344.4	338.5	332.6	326.8	320.9	313.5	304.4	295.4	286.4	277.4	269.9
60°	318.5	312.8	307.2	301.6	296.0	288.6	279.6	270.5	261.5	252.5	245.2
62.5°	295.1	289.3	283.4	277.5	271.7	264.2	254.9	245.6	236.4	227.1	220.4
65°	258.9	252.8	246.7	240.7	234.6	227.1	218.0	209.0	200.0	190.9	184.9
67.5°	221.2	215.3	209.5	203.7	198.0	190.9	182.5	174.1	165.8	157.4	152.1
70°	197.3	191.4	185.5	179.5	173.7	166.6	158.6	150.6	142.5	134.5	129.9
72.5°	171.9	166.6	161.2	155.9	150.5	144.1	136.5	128.9	121.2	113.7	109.7
75°	137.7	132.5	127.3	122.1	116.8	110.9	104.3	97.6	91.0	84.4	81.1
77.5°	102.9	98.5	94.1	89.6	85.2	80.3	74.9	69.6	64.2	58.9	57.0
80°	80.6	76.5	72.4	68.3	64.2	60.1	55.8	51.6	47.4	43.1	42.7
82.5°	61.3	57.6	53.8	50.1	46.3	43.2	40.8	38.3	36.0	33.5	33.2
85°	34.2	31.5	28.6	25.8	23.0	21.4	21.0	20.5	20.1	19.6	19.4
87.5°	12.0	11.3	10.6	9.9	9.2	9.0	9.0	9.0	9.1	9.1	9.1
90°	1.4	2.5	3.7	4.8	6.0	6.9	7.7	8.6	9.4	10.2	10.8
92.5°	5.9	6.0	6.0	6.0	6.1	6.5	7.4	8.2	9.0	9.9	10.5
95°	25.6	22.1	18.6	15.0	11.5	9.8	9.9	10.0	10.1	10.2	10.8
97.5°	54.3	56.5	58.7	60.9	63.1	58.4	46.9	35.4	23.8	12.3	12.3
100°	76.2	78.1	80.0	81.9	83.7	77.5	63.3	49.0	34.7	20.5	18.7
102.5°	100.9	102.2	103.5	104.9	106.3	106.1	104.2	102.3	100.4	98.6	79.7
105°	140.0	140.6	141.2	141.9	142.4	143.0	143.6	144.1	144.6	145.1	146.0
107.5°	176.3	176.7	177.0	177.2	177.6	178.1	178.8	179.5	180.2	180.9	181.4
110°	200.9	201.2	201.5	201.9	202.1	202.6	203.3	203.8	204.5	205.1	205.3



TEST NUMBER: P332904-930

CATALOG NUMBER: SA4XXRDIP-C575D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	224.7	225.3	225.8	226.4	227.0	227.4	227.6	228.0	228.3	228.5	228.5
115°	261.4	261.7	262.0	262.3	262.6	262.7	262.6	262.5	262.4	262.3	262.5
117.5°	294.4	294.8	295.2	295.6	296.0	296.4	296.6	296.9	297.0	297.3	297.3
120°	316.7	317.2	317.6	318.0	318.4	318.5	318.5	318.3	318.2	318.1	318.3
122.5°	337.5	337.8	338.0	338.3	338.5	338.8	338.9	339.0	339.2	339.3	339.4
125°	367.4	367.8	368.3	368.7	369.1	369.2	368.9	368.8	368.5	368.4	368.7
127.5°	395.7	395.7	395.9	396.0	396.1	396.4	396.9	397.3	397.8	398.3	398.2
130°	413.9	414.0	414.1	414.3	414.3	414.5	414.8	415.2	415.5	415.8	415.9
132.5°	430.6	430.8	431.0	431.2	431.4	431.7	432.1	432.4	432.8	433.3	433.3
135°	455.8	455.7	455.6	455.4	455.3	455.5	455.9	456.3	456.7	457.1	457.4
137.5°	478.0	478.0	478.1	478.1	478.2	478.4	478.8	479.3	479.8	480.2	480.5
140°	492.5	492.7	492.9	493.1	493.3	493.5	493.7	494.0	494.2	494.4	494.6
142.5°	505.6	505.9	506.3	506.6	507.0	507.3	507.4	507.5	507.6	507.8	508.0
145°	525.5	525.9	526.1	526.4	526.8	526.9	526.9	526.9	526.9	526.9	527.0
147.5°	541.4	542.0	542.6	543.2	543.7	544.0	543.9	543.8	543.6	543.6	543.6
150°	552.9	553.3	553.8	554.2	554.6	554.8	554.6	554.6	554.5	554.3	554.3
152.5°	562.6	563.0	563.3	563.6	563.9	564.0	563.9	563.7	563.5	563.3	563.5
155°	576.3	576.3	576.4	576.5	576.7	576.5	576.3	575.9	575.6	575.3	575.7
157.5°	587.7	587.6	587.5	587.5	587.4	587.2	586.9	586.5	586.1	585.8	586.4
160°	594.4	594.0	593.7	593.5	593.1	592.9	592.8	592.7	592.6	592.5	593.1
162.5°	600.3	599.9	599.5	599.2	598.8	598.5	598.3	598.3	598.2	598.1	598.7
165°	607.8	607.3	606.8	606.3	605.8	605.5	605.5	605.5	605.5	605.5	606.3
167.5°	613.8	613.3	612.7	612.2	611.6	611.3	611.3	611.2	611.1	611.1	612.0
170°	617.2	616.5	615.9	615.3	614.7	614.4	614.5	614.6	614.7	614.8	615.6
172.5°	619.4	618.7	618.2	617.5	616.9	616.6	616.8	616.9	616.9	617.0	617.9
175°	621.8	621.2	620.5	620.0	619.3	619.1	619.1	619.3	619.4	619.5	620.4
177.5°	622.9	622.3	621.7	621.2	620.6	620.4	620.5	620.7	620.9	621.0	621.7
180°	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8



TEST NUMBER: P332904-930

CATALOG NUMBER: SA4XXRDIP-C575D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	825.5	826.7	827.9	828.5	828.4	828.3	828.2	828.1
5°	819.9	821.4	822.8	823.4	823.0	822.8	822.5	822.2
7.5°	809.0	809.9	810.9	811.1	810.7	810.2	809.8	809.3
10°	799.2	799.8	800.4	800.4	799.8	799.2	798.7	798.1
12.5°	787.1	787.4	787.8	787.6	786.8	786.0	785.2	784.4
15°	765.8	765.6	765.2	764.7	763.6	762.6	761.7	760.7
17.5°	740.2	739.4	738.6	737.4	736.0	734.5	733.0	731.5
20°	722.3	721.1	720.0	718.5	716.7	714.9	713.1	711.2
22.5°	702.4	700.7	699.0	697.4	695.9	694.4	692.9	691.4
25°	670.3	667.8	665.4	663.6	662.1	660.7	659.3	657.9
27.5°	637.5	634.5	631.6	629.1	627.0	625.0	623.1	621.0
30°	614.1	610.5	607.0	604.1	601.9	599.6	597.4	595.1
32.5°	590.1	586.0	581.9	578.8	576.7	574.5	572.3	570.2
35°	554.4	549.6	544.9	541.2	538.7	536.1	533.5	531.0
37.5°	516.1	510.8	505.4	501.5	498.9	496.4	493.8	491.3
40°	490.6	484.7	478.7	474.6	472.0	469.4	466.9	464.4
42.5°	465.5	459.5	453.5	449.1	446.5	443.8	441.2	438.5
45°	427.1	420.2	413.3	408.5	406.0	403.5	401.0	398.4
47.5°	388.4	381.2	374.1	369.1	366.3	363.5	360.8	357.9
50°	362.7	355.7	348.6	343.8	341.1	338.4	335.7	333.0
52.5°	337.1	330.0	322.9	317.9	315.0	312.3	309.5	306.7
55°	299.4	292.0	284.7	279.7	277.0	274.3	271.7	269.0
57.5°	262.4	255.0	247.6	242.9	240.8	238.8	236.8	234.7
60°	237.8	230.5	223.1	218.4	216.1	213.9	211.7	209.4
62.5°	213.6	206.8	200.1	195.8	194.0	192.2	190.4	188.6
65°	178.9	172.8	166.7	162.8	161.2	159.5	157.8	156.0
67.5°	146.9	141.7	136.5	133.0	131.1	129.2	127.3	125.5
70°	125.2	120.6	115.9	112.8	111.5	110.1	108.6	107.2
72.5°	105.7	101.7	97.8	95.1	93.8	92.5	91.2	89.9
75°	77.9	74.7	71.4	69.4	68.5	67.7	66.9	66.0
77.5°	55.1	53.2	51.3	50.2	50.0	49.7	49.5	49.2
80°	42.3	41.9	41.4	41.2	41.0	40.8	40.8	40.6
82.5°	32.9	32.5	32.3	32.0	31.9	31.7	31.6	31.5
85°	19.1	18.8	18.5	18.4	18.4	18.4	18.4	18.4
87.5°	9.2	9.2	9.2	9.3	9.5	9.6	9.7	9.9
90°	11.5	12.1	12.7	13.1	13.4	13.5	13.8	13.9
92.5°	11.1	11.7	12.3	12.6	12.7	12.7	12.8	12.8
95°	11.5	12.1	12.7	13.0	13.2	13.3	13.4	13.5
97.5°	12.4	12.5	12.6	12.6	12.7	12.8	12.9	13.0
100°	17.0	15.2	13.5	12.6	12.7	12.8	12.9	13.0
102.5°	60.7	41.7	22.7	13.3	13.4	13.4	13.4	13.4
105°	147.0	147.9	148.8	147.4	143.7	140.0	136.2	132.6
107.5°	181.8	182.3	182.7	183.1	183.5	183.9	184.3	184.7
110°	205.5	205.7	205.9	206.2	206.5	206.8	207.1	207.4



TEST NUMBER: P332904-930

CATALOG NUMBER: SA4XXRDIP-C575D590U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	228.4	228.4	228.4	228.5	228.9	229.3	229.8	230.1
115°	262.7	262.9	263.1	263.3	263.3	263.3	263.3	263.3
117.5°	297.2	297.2	297.1	297.1	297.0	297.0	296.9	296.9
120°	318.5	318.7	318.9	318.9	318.7	318.5	318.3	318.1
122.5°	339.6	339.7	339.8	339.7	339.6	339.3	339.2	338.9
125°	368.9	369.2	369.6	369.8	369.9	370.0	370.1	370.2
127.5°	398.2	398.1	398.0	397.9	397.9	397.8	397.7	397.6
130°	416.0	416.0	416.2	416.2	416.2	416.2	416.2	416.2
132.5°	433.5	433.6	433.7	433.7	433.6	433.5	433.4	433.3
135°	457.5	457.8	458.0	458.2	458.4	458.6	458.9	459.0
137.5°	480.7	480.9	481.1	481.2	481.2	481.1	481.0	480.9
140°	495.0	495.3	495.6	495.8	495.9	496.0	496.1	496.2
142.5°	508.2	508.4	508.7	508.8	508.8	508.8	508.8	508.9
145°	527.1	527.3	527.3	527.5	527.7	527.9	528.2	528.3
147.5°	543.7	543.8	543.9	544.0	544.1	544.2	544.3	544.4
150°	554.3	554.3	554.3	554.4	554.5	554.6	554.7	554.8
152.5°	563.6	563.8	563.9	564.0	563.9	563.9	563.8	563.8
155°	576.1	576.5	576.9	577.0	576.7	576.3	576.1	575.8
157.5°	586.9	587.4	587.9	587.9	587.4	586.9	586.4	585.8
160°	593.7	594.4	595.0	595.0	594.4	593.7	593.1	592.5
162.5°	599.3	599.9	600.5	600.5	599.8	599.1	598.4	597.7
165°	607.2	608.0	608.9	608.8	607.8	606.9	606.0	605.0
167.5°	612.9	613.8	614.7	614.7	613.7	612.6	611.6	610.6
170°	616.4	617.3	618.2	618.0	617.0	616.0	614.9	613.9
172.5°	618.7	619.5	620.4	620.2	619.1	618.0	616.9	615.7
175°	621.3	622.2	623.2	623.1	621.8	620.5	619.3	618.1
177.5°	622.4	623.1	623.7	623.5	622.6	621.6	620.5	619.5
180°	621.8	621.8	621.8	621.8	621.8	621.8	621.8	621.8

(END OF REPORT)