

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331660-940

Luminaire Tested: **SA2XXRDIP-C485D725U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331660-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4099.1 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331660-940
CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331660-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38				32	
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32				27	
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28				23	
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24				20	
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	23	22				18	
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19				16	
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	21	19	17				14	
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15				13	
9	49	38	30	25	45	35	28	24	29	24	20	23	20	17	18	16	14				12	
10	46	34	27	23	42	32	26	21	27	22	18	22	18	16	17	15	13				11	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11880	11880	11880
5°	11925	11733	11797
10°	11835	11540	11442
15°	11699	11198	10877
20°	11510	10710	10172
25°	11318	10156	9492
30°	11050	9587	8617
35°	10789	8966	7849
40°	10526	8323	6962
45°	10218	7604	6158
50°	9902	6875	5368
55°	9579	6092	4611
60°	9203	5270	3827
65°	8779	4424	3484
70°	8266	3644	3205
75°	7642	3319	2994
80°	6750	2966	2724
85°	5298	2353	2353



TEST NUMBER: P331660-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.9	1.7
10°-20°	189.1	4.6
20°-30°	265.6	6.5
30°-40°	289.6	7.1
40°-50°	266.3	6.5
50°-60°	209.1	5.1
60°-70°	136.4	3.3
70°-80°	70.3	1.7
80°-90°	20.4	0.5
90°-100°	29.4	0.7
100°-110°	107.8	2.6
110°-120°	288.3	7.0
120°-130°	475.8	11.6
130°-140°	506.0	12.3
140°-150°	470.3	11.5
150°-160°	378.1	9.2
160°-170°	243.7	5.9
170°-180°	83.9	2.0
0°-30°	523.6	12.8
0°-40°	813.2	19.8
0°-60°	1288.6	31.4
0°-90°	1515.7	37.0
90°-120°	425.5	10.4
90°-150°	1877.7	45.8
90°-180°	2583.0	63.0
0°-180°	4099.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	736	736	736	736	736	
5°	736	732	724	729	728	70
15°	700	692	670	658	651	197
25°	635	613	570	544	533	292
35°	547	512	455	414	398	342
45°	448	402	333	287	270	345
55°	340	287	216	178	164	304
65°	230	176	116	94	91	228
75°	122	77	53	49	48	130
85°	29	15	13	13	13	34
90°	1	8	13	16	17	3
95°	42	22	25	28	28	51
105°	194	202	39	46	48	207
115°	367	378	394	112	52	361
125°	519	527	539	543	545	462
135°	642	652	658	664	663	495
145°	744	744	755	759	756	465
155°	820	815	822	825	820	378
165°	864	860	862	866	862	244
175°	883	879	880	884	878	84
180°	882	882	882	882	882	



TEST NUMBER: P331660-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	738.5	738.0	737.4	736.7	736.2	735.2	734.0	732.6	731.3	730.0	731.2
5°	735.8	735.1	734.4	733.7	732.9	731.6	729.7	727.7	725.9	723.9	725.2
7.5°	728.3	727.4	726.5	725.5	724.6	723.0	720.8	718.5	716.3	714.1	714.4
10°	721.9	720.9	719.8	718.8	717.7	715.8	712.8	709.8	706.9	703.9	703.5
12.5°	713.9	712.7	711.3	710.1	708.8	706.3	702.5	698.7	694.9	691.2	690.4
15°	699.9	698.3	696.7	695.0	693.4	690.1	685.0	680.0	675.0	669.9	667.2
17.5°	682.8	680.3	677.8	675.3	672.8	668.3	661.9	655.4	649.0	642.5	639.2
20°	669.9	667.0	664.1	661.1	658.1	652.9	645.5	638.1	630.7	623.3	619.6
22.5°	656.1	652.8	649.4	646.1	642.8	637.0	628.7	620.3	612.0	603.6	598.9
25°	635.3	630.6	625.9	621.1	616.4	609.1	599.3	589.6	579.8	570.1	564.0
27.5°	610.3	605.1	599.9	594.9	589.7	581.6	570.6	559.5	548.6	537.5	530.5
30°	592.7	587.1	581.5	575.9	570.2	561.5	549.7	537.8	525.9	514.2	506.6
32.5°	575.7	569.1	562.5	556.0	549.4	540.0	528.0	515.9	503.8	491.8	483.1
35°	547.4	539.8	532.4	524.8	517.2	506.9	493.9	480.9	467.9	454.9	445.5
37.5°	519.2	510.9	502.6	494.3	486.1	474.9	461.1	447.2	433.3	419.5	409.1
40°	499.4	490.6	481.7	472.9	464.0	452.4	438.0	423.7	409.3	394.9	384.4
42.5°	479.2	469.8	460.5	451.2	441.8	429.7	414.9	400.0	385.2	370.4	359.5
45°	447.5	437.7	427.7	417.8	407.9	395.1	379.6	364.1	348.5	333.0	322.4
47.5°	416.6	406.1	395.7	385.1	374.6	361.3	345.3	329.2	313.2	297.1	286.7
50°	394.2	383.7	373.3	362.7	352.2	338.9	322.5	306.3	290.0	273.7	263.5
52.5°	372.4	361.4	350.4	339.5	328.5	315.0	299.1	283.2	267.2	251.4	241.5
55°	340.3	328.8	317.2	305.7	294.2	280.4	264.4	248.4	232.4	216.4	207.6
57.5°	307.4	295.6	283.7	271.9	260.0	246.5	231.1	215.7	200.4	185.0	176.8
60°	285.0	273.2	261.4	249.5	237.6	224.2	208.9	193.7	178.4	163.2	155.6
62.5°	263.1	251.4	239.5	227.7	215.8	202.7	188.2	173.6	159.1	144.5	137.3
65°	229.8	217.8	205.8	193.8	181.8	169.2	155.9	142.5	129.2	115.8	110.8
67.5°	197.5	185.7	173.7	161.8	149.9	137.9	126.0	114.0	102.0	90.1	87.7
70°	175.1	163.6	152.0	140.5	128.9	118.1	107.9	97.6	87.5	77.2	75.8
72.5°	153.8	142.8	131.7	120.6	109.6	100.0	91.8	83.6	75.3	67.1	65.9
75°	122.5	112.2	101.8	91.5	81.1	73.4	68.4	63.3	58.3	53.2	52.3
77.5°	91.8	82.7	73.6	64.5	55.5	49.7	47.3	44.9	42.4	39.9	39.3
80°	72.6	65.0	57.5	49.9	42.4	37.9	36.4	35.0	33.4	31.9	31.4
82.5°	55.0	49.1	43.2	37.4	31.5	28.0	27.0	25.9	25.0	24.0	23.6
85°	28.6	25.5	22.4	19.4	16.2	14.4	14.0	13.6	13.1	12.7	12.7
87.5°	8.6	8.0	7.4	6.8	6.2	5.9	6.2	6.3	6.6	6.8	6.9
90°	0.6	2.2	3.7	5.4	6.9	8.2	9.4	10.5	11.6	12.8	13.5
92.5°	12.8	12.8	12.6	12.5	12.3	12.6	13.1	13.6	14.3	14.8	15.2
95°	41.5	36.8	32.1	27.5	22.7	20.9	21.9	22.9	23.9	24.9	25.6
97.5°	82.3	69.1	55.9	42.7	29.5	24.1	26.4	28.7	31.0	33.3	33.9
100°	112.9	93.5	74.1	54.7	35.2	26.8	29.2	31.6	34.0	36.4	37.5
102.5°	146.6	142.5	138.4	134.3	130.1	118.0	97.8	77.7	57.5	37.4	38.9
105°	193.9	198.1	202.4	206.7	210.9	193.7	155.0	116.3	77.6	38.9	40.5
107.5°	247.9	251.3	254.8	258.2	261.6	240.1	193.7	147.3	100.9	54.5	52.9
110°	282.6	285.5	288.6	291.5	294.4	275.4	234.5	193.6	152.6	111.6	97.5



TEST NUMBER: P331660-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	315.2	317.9	320.5	323.2	325.7	322.0	311.9	301.8	291.7	281.5	229.9
115°	366.8	369.2	371.6	374.0	376.4	379.4	382.9	386.5	390.0	393.6	328.0
117.5°	412.9	415.5	418.2	420.9	423.6	426.1	428.6	431.1	433.5	436.0	420.1
120°	446.5	448.6	450.8	452.9	455.0	457.4	459.9	462.4	465.0	467.5	469.2
122.5°	475.1	477.3	479.6	481.8	484.0	486.5	489.4	492.1	494.9	497.7	498.6
125°	518.6	520.4	522.3	524.1	525.9	528.2	530.9	533.6	536.3	539.0	540.0
127.5°	558.0	560.1	562.1	564.1	566.1	568.2	570.2	572.2	574.3	576.2	577.7
130°	583.0	585.3	587.5	589.8	592.1	594.0	595.6	597.1	598.7	600.2	601.8
132.5°	608.5	610.5	612.4	614.3	616.3	618.0	619.6	621.1	622.7	624.2	625.5
135°	641.7	644.0	646.2	648.5	650.8	652.6	653.8	655.1	656.4	657.6	659.1
137.5°	675.3	676.8	678.4	680.0	681.6	683.1	684.6	686.0	687.4	688.9	690.3
140°	697.2	698.3	699.5	700.6	701.7	703.1	704.6	706.2	707.8	709.4	710.6
142.5°	715.6	716.6	717.6	718.6	719.6	721.0	722.8	724.6	726.4	728.2	729.3
145°	744.4	744.2	744.1	744.0	743.9	744.9	747.3	749.8	752.2	754.6	755.6
147.5°	769.5	769.0	768.5	767.9	767.4	768.3	770.7	773.0	775.4	777.8	778.6
150°	785.9	784.9	783.9	782.9	781.9	782.6	784.8	787.0	789.3	791.6	792.5
152.5°	799.6	798.5	797.5	796.3	795.2	795.8	797.9	800.0	802.2	804.3	805.2
155°	819.7	818.4	817.1	815.8	814.6	814.8	816.5	818.1	819.8	821.5	822.4
157.5°	835.4	834.3	833.2	832.1	831.1	831.1	832.3	833.5	834.6	835.9	836.9
160°	844.5	843.6	842.8	842.0	841.2	841.2	842.0	842.8	843.6	844.5	845.4
162.5°	852.7	851.9	851.0	850.2	849.3	849.3	850.0	850.7	851.5	852.2	853.2
165°	863.7	862.8	862.0	861.1	860.2	860.1	860.5	860.9	861.3	861.7	862.7
167.5°	871.8	871.0	870.1	869.3	868.4	868.2	868.6	869.0	869.4	869.8	870.8
170°	876.5	875.6	874.8	873.9	873.1	872.7	873.1	873.3	873.6	873.9	874.9
172.5°	879.5	878.6	877.8	876.9	876.1	875.8	876.1	876.4	876.6	876.9	878.0
175°	883.4	882.4	881.5	880.5	879.5	879.1	879.4	879.7	879.9	880.3	881.3
177.5°	884.1	883.3	882.5	881.7	880.9	880.6	880.7	880.8	880.9	881.0	881.8
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5



TEST NUMBER: P331660-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	732.4	733.6	734.8	735.2	735.0	734.8	734.5	734.3
5°	726.6	727.9	729.2	729.7	729.2	728.8	728.3	727.9
7.5°	714.8	715.2	715.6	715.4	714.6	713.8	713.1	712.3
10°	703.0	702.6	702.1	701.5	700.6	699.7	698.8	697.9
12.5°	689.6	688.8	688.0	686.8	685.3	683.9	682.3	680.9
15°	664.3	661.6	658.7	656.6	655.1	653.6	652.1	650.7
17.5°	635.8	632.5	629.1	626.2	623.7	621.1	618.6	616.0
20°	615.9	612.2	608.5	605.0	601.8	598.5	595.3	592.0
22.5°	594.1	589.3	584.6	580.9	578.5	576.1	573.7	571.2
25°	557.9	551.9	545.8	541.6	539.4	537.2	535.0	532.8
27.5°	523.4	516.3	509.3	504.0	500.4	497.0	493.4	489.9
30°	499.0	491.5	483.9	478.1	474.1	470.2	466.2	462.2
32.5°	474.5	465.9	457.3	451.1	447.4	443.6	439.8	436.0
35°	436.2	426.9	417.6	411.3	408.0	404.7	401.5	398.2
37.5°	398.9	388.6	378.4	371.3	367.7	363.9	360.2	356.4
40°	373.9	363.4	352.8	345.7	341.9	338.0	334.1	330.3
42.5°	348.7	337.8	327.0	319.7	315.9	312.2	308.4	304.7
45°	311.9	301.5	291.0	283.9	280.4	276.8	273.2	269.7
47.5°	276.3	265.8	255.4	248.5	245.3	242.1	238.8	235.6
50°	253.2	243.1	232.8	226.2	223.1	220.0	216.9	213.7
52.5°	231.6	221.8	211.9	205.5	202.7	199.8	196.9	194.0
55°	198.7	189.8	180.9	175.0	172.3	169.4	166.7	163.8
57.5°	168.7	160.6	152.5	147.2	144.8	142.5	140.1	137.7
60°	148.0	140.5	133.0	128.0	125.6	123.2	120.9	118.5
62.5°	130.1	123.0	115.7	111.5	110.0	108.6	107.2	105.8
65°	105.8	100.8	95.8	93.0	92.6	92.1	91.7	91.2
67.5°	85.4	83.1	80.8	79.5	78.9	78.5	78.0	77.5
70°	74.3	72.9	71.3	70.3	69.7	69.1	68.5	67.9
72.5°	64.6	63.4	62.2	61.3	61.0	60.6	60.3	59.9
75°	51.2	50.2	49.1	48.5	48.4	48.2	48.1	48.0
77.5°	38.8	38.2	37.6	37.2	36.9	36.7	36.5	36.2
80°	30.8	30.2	29.6	29.3	29.3	29.3	29.3	29.3
82.5°	23.3	22.9	22.6	22.4	22.4	22.4	22.4	22.4
85°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7
87.5°	6.9	6.9	6.9	7.0	7.0	7.0	7.1	7.1
90°	14.2	14.9	15.6	16.1	16.4	16.7	16.9	17.2
92.5°	15.5	15.9	16.2	16.6	16.7	16.9	17.0	17.2
95°	26.3	27.0	27.7	28.0	27.8	27.7	27.6	27.5
97.5°	34.4	35.0	35.6	35.9	36.1	36.3	36.5	36.6
100°	38.6	39.8	40.9	41.6	41.9	42.2	42.4	42.7
102.5°	40.3	41.8	43.2	44.2	44.6	45.0	45.4	45.8
105°	42.0	43.6	45.1	46.2	46.8	47.3	47.9	48.5
107.5°	51.3	49.7	48.2	47.6	48.2	48.8	49.3	49.8
110°	83.3	69.1	54.9	48.2	48.7	49.2	49.8	50.4



TEST NUMBER: P331660-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	178.2	126.4	74.7	49.0	49.6	50.0	50.5	50.9
115°	262.3	196.7	131.1	93.1	82.9	72.7	62.5	52.3
117.5°	404.2	388.3	372.4	347.7	314.1	280.6	247.1	213.6
120°	471.0	472.7	474.4	465.7	446.5	427.4	408.2	389.1
122.5°	499.7	500.7	501.8	500.4	496.7	492.9	489.3	485.5
125°	541.0	542.0	543.0	543.7	544.1	544.6	544.9	545.4
127.5°	579.2	580.6	582.0	582.8	582.9	583.0	583.1	583.2
130°	603.3	604.9	606.5	607.2	607.1	606.9	606.7	606.6
132.5°	626.9	628.2	629.5	630.2	630.0	629.9	629.7	629.5
135°	660.5	661.9	663.3	663.9	663.6	663.3	663.0	662.7
137.5°	691.7	693.0	694.5	694.9	694.5	693.9	693.5	692.9
140°	711.9	713.1	714.4	714.7	714.0	713.3	712.6	711.9
142.5°	730.5	731.6	732.8	733.1	732.4	731.6	730.9	730.2
145°	756.6	757.6	758.6	758.7	758.0	757.3	756.6	755.9
147.5°	779.3	780.1	780.8	780.9	780.2	779.6	779.1	778.5
150°	793.3	794.2	795.0	795.0	794.3	793.6	792.9	792.2
152.5°	806.0	806.9	807.8	807.7	806.8	805.8	804.9	804.0
155°	823.3	824.1	825.0	824.8	823.7	822.6	821.4	820.3
157.5°	837.8	838.7	839.7	839.6	838.6	837.4	836.3	835.3
160°	846.2	847.1	847.9	847.8	846.9	845.9	844.9	843.9
162.5°	854.1	855.1	856.0	856.0	854.7	853.5	852.3	851.0
165°	863.7	864.8	865.8	865.8	864.8	863.7	862.7	861.7
167.5°	871.8	872.8	873.8	873.6	872.4	871.1	869.8	868.5
170°	875.8	876.8	877.9	877.7	876.5	875.1	873.9	872.6
172.5°	879.0	879.9	880.9	880.7	879.5	878.2	876.9	875.7
175°	882.3	883.2	884.2	884.0	882.6	881.2	879.8	878.3
177.5°	882.6	883.4	884.2	884.1	883.1	882.1	881.0	880.0
180°	881.5	881.5	881.5	881.5	881.5	881.5	881.5	881.5

(END OF REPORT)