

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331662-940

Luminaire Tested: **SA2XXRDIP-C485D725U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331662-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4039.1 lumens  
Efficiency: N/A  
Efficacy: 105.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331662-940  
CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331662-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38	38	38	38	
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32	32	32	32	
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28	28	28	28	
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24	24	24	24	
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21	21	21	21	
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18	18	18	18	
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16	16	16	16	
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15	15	15	15	
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16	13	13	13	13	
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12	12	12	12	
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11	11	11	11	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11880	11880	11880
5°	11925	11733	11797
10°	11835	11540	11442
15°	11699	11198	10877
20°	11510	10710	10172
25°	11318	10156	9492
30°	11050	9587	8617
35°	10789	8966	7849
40°	10526	8323	6962
45°	10218	7604	6158
50°	9902	6875	5368
55°	9579	6092	4611
60°	9203	5270	3827
65°	8779	4424	3484
70°	8266	3644	3205
75°	7642	3319	2994
80°	6750	2966	2724
85°	5298	2353	2353



TEST NUMBER: P331662-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.9	1.7
10°-20°	189.1	4.7
20°-30°	265.6	6.6
30°-40°	289.6	7.2
40°-50°	266.3	6.6
50°-60°	209.1	5.2
60°-70°	136.4	3.4
70°-80°	70.3	1.7
80°-90°	21.5	0.5
90°-100°	144.9	3.6
100°-110°	491.8	12.2
110°-120°	522.5	12.9
120°-130°	430.1	10.6
130°-140°	345.4	8.6
140°-150°	261.0	6.5
150°-160°	183.4	4.5
160°-170°	108.0	2.7
170°-180°	35.1	0.9
0°-30°	523.6	13.0
0°-40°	813.2	20.1
0°-60°	1288.6	31.9
0°-90°	1516.8	37.6
90°-120°	1159.2	28.7
90°-150°	2195.7	54.4
90°-180°	2522.0	62.4
0°-180°	4039.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	736	736	736	736	736	
5°	736	732	724	729	728	70
15°	700	692	670	658	651	197
25°	635	613	570	544	533	292
35°	547	512	455	414	398	342
45°	448	402	333	287	270	345
55°	340	287	216	178	164	304
65°	230	176	116	94	91	228
75°	122	77	53	49	48	130
85°	29	15	13	13	13	34
90°	1	9	24	23	23	3
95°	24	60	273	103	80	26
105°	85	128	516	923	786	90
115°	150	189	432	892	1034	149
125°	209	247	415	722	839	186
135°	245	293	410	607	695	190
145°	280	322	408	507	555	176
155°	318	344	397	449	466	147
165°	347	358	380	403	409	98
175°	362	362	365	370	369	34
180°	362	362	362	362	362	



TEST NUMBER: P331662-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	738.5	738.0	737.4	736.7	736.2	735.2	734.0	732.6	731.3	730.0	731.2
5°	735.8	735.1	734.4	733.7	732.9	731.6	729.7	727.7	725.9	723.9	725.2
7.5°	728.3	727.4	726.5	725.5	724.6	723.0	720.8	718.5	716.3	714.1	714.4
10°	721.9	720.9	719.8	718.8	717.7	715.8	712.8	709.8	706.9	703.9	703.5
12.5°	713.9	712.7	711.3	710.1	708.8	706.3	702.5	698.7	694.9	691.2	690.4
15°	699.9	698.3	696.7	695.0	693.4	690.1	685.0	680.0	675.0	669.9	667.2
17.5°	682.8	680.3	677.8	675.3	672.8	668.3	661.9	655.4	649.0	642.5	639.2
20°	669.9	667.0	664.1	661.1	658.1	652.9	645.5	638.1	630.7	623.3	619.6
22.5°	656.1	652.8	649.4	646.1	642.8	637.0	628.7	620.3	612.0	603.6	598.9
25°	635.3	630.6	625.9	621.1	616.4	609.1	599.3	589.6	579.8	570.1	564.0
27.5°	610.3	605.1	599.9	594.9	589.7	581.6	570.6	559.5	548.6	537.5	530.5
30°	592.7	587.1	581.5	575.9	570.2	561.5	549.7	537.8	525.9	514.2	506.6
32.5°	575.7	569.1	562.5	556.0	549.4	540.0	528.0	515.9	503.8	491.8	483.1
35°	547.4	539.8	532.4	524.8	517.2	506.9	493.9	480.9	467.9	454.9	445.5
37.5°	519.2	510.9	502.6	494.3	486.1	474.9	461.1	447.2	433.3	419.5	409.1
40°	499.4	490.6	481.7	472.9	464.0	452.4	438.0	423.7	409.3	394.9	384.4
42.5°	479.2	469.8	460.5	451.2	441.8	429.7	414.9	400.0	385.2	370.4	359.5
45°	447.5	437.7	427.7	417.8	407.9	395.1	379.6	364.1	348.5	333.0	322.4
47.5°	416.6	406.1	395.7	385.1	374.6	361.3	345.3	329.2	313.2	297.1	286.7
50°	394.2	383.7	373.3	362.7	352.2	338.9	322.5	306.3	290.0	273.7	263.5
52.5°	372.4	361.4	350.4	339.5	328.5	315.0	299.1	283.2	267.2	251.4	241.5
55°	340.3	328.8	317.2	305.7	294.2	280.4	264.4	248.4	232.4	216.4	207.6
57.5°	307.4	295.6	283.7	271.9	260.0	246.5	231.1	215.7	200.4	185.0	176.8
60°	285.0	273.2	261.4	249.5	237.6	224.2	208.9	193.7	178.4	163.2	155.6
62.5°	263.1	251.4	239.5	227.7	215.8	202.7	188.2	173.6	159.1	144.5	137.3
65°	229.8	217.8	205.8	193.8	181.8	169.2	155.9	142.5	129.2	115.8	110.8
67.5°	197.5	185.7	173.7	161.8	149.9	137.9	126.0	114.0	102.0	90.1	87.7
70°	175.1	163.6	152.0	140.5	128.9	118.1	107.9	97.6	87.5	77.2	75.8
72.5°	153.8	142.8	131.7	120.6	109.6	100.0	91.8	83.6	75.3	67.1	65.9
75°	122.5	112.2	101.8	91.5	81.1	73.4	68.4	63.3	58.3	53.2	52.3
77.5°	91.8	82.7	73.6	64.5	55.5	49.7	47.3	44.9	42.4	39.9	39.3
80°	72.6	65.0	57.5	49.9	42.4	37.9	36.4	35.0	33.4	31.9	31.4
82.5°	55.0	49.1	43.2	37.4	31.5	28.0	27.0	25.9	25.0	24.0	23.6
85°	28.6	25.5	22.4	19.4	16.2	14.4	14.0	13.6	13.1	12.7	12.7
87.5°	8.6	8.1	7.8	7.0	6.4	6.3	7.0	8.0	8.8	9.0	8.7
90°	0.7	2.8	5.6	7.0	8.4	10.4	13.9	18.8	23.0	23.7	23.0
92.5°	8.5	12.3	17.3	20.3	25.1	31.7	47.4	69.6	89.3	90.6	76.5
95°	24.4	27.2	34.2	40.4	51.5	68.3	100.4	161.0	241.9	273.2	239.1
97.5°	39.8	43.5	50.9	60.4	73.2	92.1	132.4	217.0	351.3	466.5	489.4
100°	53.7	55.7	62.1	73.2	87.1	106.6	143.6	228.6	379.2	550.6	651.0
102.5°	66.5	68.0	74.3	85.4	100.0	119.5	153.6	229.2	368.6	553.5	711.2
105°	85.1	87.8	92.7	103.2	118.5	138.0	170.8	232.8	347.9	516.5	702.0
107.5°	105.1	107.4	112.1	121.7	136.9	156.6	188.3	242.5	337.5	476.9	640.7
110°	118.5	121.3	125.5	134.6	149.2	169.4	200.0	250.2	335.3	458.0	602.3



TEST NUMBER: P331662-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.7	133.6	138.3	146.8	160.9	181.6	211.2	258.6	335.8	445.7	575.5
115°	149.9	153.4	157.6	165.9	179.9	198.7	228.6	271.2	338.8	432.2	542.3
117.5°	169.7	172.5	176.6	184.0	197.4	217.0	244.7	284.5	343.8	425.6	521.4
120°	181.9	184.8	188.9	195.2	209.1	228.6	255.8	293.5	347.1	421.7	510.2
122.5°	193.7	195.9	200.0	206.9	220.8	240.9	266.4	301.3	351.1	419.5	500.8
125°	209.1	211.2	215.3	223.7	237.7	257.2	282.3	313.7	356.9	415.4	487.2
127.5°	221.4	224.2	230.1	239.2	252.6	272.7	297.1	325.2	362.9	413.0	474.7
130°	228.6	231.4	238.4	248.2	262.1	281.6	306.0	332.5	367.4	412.0	466.4
132.5°	235.3	238.7	246.2	256.5	271.0	290.5	313.8	339.7	371.8	411.4	459.7
135°	245.4	248.2	256.5	267.0	283.0	302.6	324.9	349.2	377.1	410.5	450.3
137.5°	254.9	258.2	266.5	277.7	293.6	311.7	333.8	356.5	381.8	410.5	443.7
140°	262.1	264.8	273.2	284.4	299.7	317.9	338.8	360.3	384.1	409.8	439.9
142.5°	269.3	271.6	279.4	290.5	305.3	322.4	342.7	363.7	385.8	409.8	436.0
145°	280.2	283.0	290.0	300.4	314.3	329.7	348.6	368.0	387.5	408.5	430.8
147.5°	291.9	294.0	300.7	310.3	321.9	335.6	353.3	370.4	388.2	406.0	425.5
150°	299.7	301.8	307.4	316.5	326.9	339.5	355.5	371.5	387.5	404.3	421.0
152.5°	307.6	308.5	314.1	322.0	331.9	343.4	357.8	372.1	386.5	401.5	417.1
155°	318.5	319.2	323.4	331.1	338.8	349.2	361.1	372.9	384.8	396.6	409.8
157.5°	327.8	328.4	331.8	338.5	344.6	353.4	363.5	372.9	381.6	391.6	403.1
160°	333.9	334.6	337.3	343.0	348.6	356.1	364.5	372.9	379.9	388.3	398.1
162.5°	340.0	339.6	342.4	346.9	351.9	357.8	365.2	372.4	378.3	385.5	393.5
165°	347.1	346.4	347.9	352.0	355.5	359.7	366.0	370.9	375.1	379.9	386.2
167.5°	353.0	352.1	353.4	356.1	358.6	361.2	365.8	369.9	371.8	375.1	378.9
170°	356.9	355.5	356.1	358.3	359.7	361.8	365.2	368.7	370.1	372.2	375.1
172.5°	359.1	358.3	357.8	360.0	360.8	362.3	364.7	367.0	367.9	368.9	371.1
175°	361.8	361.1	360.3	361.8	361.8	362.5	363.8	365.2	364.5	365.2	366.0
177.5°	363.0	361.9	361.3	362.5	362.5	362.5	363.0	364.2	363.0	362.5	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5



TEST NUMBER: P331662-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	732.4	733.6	734.8	735.2	735.0	734.8	734.5	734.3
5°	726.6	727.9	729.2	729.7	729.2	728.8	728.3	727.9
7.5°	714.8	715.2	715.6	715.4	714.6	713.8	713.1	712.3
10°	703.0	702.6	702.1	701.5	700.6	699.7	698.8	697.9
12.5°	689.6	688.8	688.0	686.8	685.3	683.9	682.3	680.9
15°	664.3	661.6	658.7	656.6	655.1	653.6	652.1	650.7
17.5°	635.8	632.5	629.1	626.2	623.7	621.1	618.6	616.0
20°	615.9	612.2	608.5	605.0	601.8	598.5	595.3	592.0
22.5°	594.1	589.3	584.6	580.9	578.5	576.1	573.7	571.2
25°	557.9	551.9	545.8	541.6	539.4	537.2	535.0	532.8
27.5°	523.4	516.3	509.3	504.0	500.4	497.0	493.4	489.9
30°	499.0	491.5	483.9	478.1	474.1	470.2	466.2	462.2
32.5°	474.5	465.9	457.3	451.1	447.4	443.6	439.8	436.0
35°	436.2	426.9	417.6	411.3	408.0	404.7	401.5	398.2
37.5°	398.9	388.6	378.4	371.3	367.7	363.9	360.2	356.4
40°	373.9	363.4	352.8	345.7	341.9	338.0	334.1	330.3
42.5°	348.7	337.8	327.0	319.7	315.9	312.2	308.4	304.7
45°	311.9	301.5	291.0	283.9	280.4	276.8	273.2	269.7
47.5°	276.3	265.8	255.4	248.5	245.3	242.1	238.8	235.6
50°	253.2	243.1	232.8	226.2	223.1	220.0	216.9	213.7
52.5°	231.6	221.8	211.9	205.5	202.7	199.8	196.9	194.0
55°	198.7	189.8	180.9	175.0	172.3	169.4	166.7	163.8
57.5°	168.7	160.6	152.5	147.2	144.8	142.5	140.1	137.7
60°	148.0	140.5	133.0	128.0	125.6	123.2	120.9	118.5
62.5°	130.1	123.0	115.7	111.5	110.0	108.6	107.2	105.8
65°	105.8	100.8	95.8	93.0	92.6	92.1	91.7	91.2
67.5°	85.4	83.1	80.8	79.5	78.9	78.5	78.0	77.5
70°	74.3	72.9	71.3	70.3	69.7	69.1	68.5	67.9
72.5°	64.6	63.4	62.2	61.3	61.0	60.6	60.3	59.9
75°	51.2	50.2	49.1	48.5	48.4	48.2	48.1	48.0
77.5°	38.8	38.2	37.6	37.2	36.9	36.7	36.5	36.2
80°	30.8	30.2	29.6	29.3	29.3	29.3	29.3	29.3
82.5°	23.3	22.9	22.6	22.4	22.4	22.4	22.4	22.4
85°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7
87.5°	8.5	8.1	8.3	8.3	8.3	8.3	8.3	8.3
90°	22.3	21.0	22.3	23.0	23.0	23.0	23.0	23.0
92.5°	60.8	52.2	46.3	42.0	41.4	39.1	39.8	38.6
95°	182.6	140.1	110.8	95.5	86.4	80.9	78.7	79.5
97.5°	426.1	348.7	273.2	222.9	189.6	172.5	162.3	156.4
100°	636.4	550.0	454.5	370.1	312.3	282.3	262.1	249.5
102.5°	774.2	754.7	684.7	595.4	532.5	481.3	456.1	439.2
105°	846.9	925.7	934.8	911.8	868.5	825.3	795.3	785.6
107.5°	794.5	913.1	985.6	1019.4	1024.8	1022.4	1016.5	1003.4
110°	749.3	874.1	963.3	1020.5	1050.4	1063.7	1070.0	1069.3





TEST NUMBER: P331662-940

CATALOG NUMBER: SA2XXRDIP-C485D725U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	708.1	827.8	923.2	988.7	1030.4	1052.6	1064.4	1068.2
115°	657.3	764.6	856.0	927.7	977.2	1009.3	1027.4	1033.8
117.5°	619.1	713.4	796.2	863.5	914.0	947.9	967.0	972.2
120°	600.1	686.6	760.5	823.9	872.7	905.4	925.7	932.6
122.5°	585.1	664.3	734.2	791.6	835.4	867.5	885.6	891.4
125°	563.2	635.0	696.3	748.6	789.1	815.6	832.9	838.6
127.5°	541.6	606.5	664.4	712.7	748.0	772.8	787.8	792.3
130°	527.6	587.6	642.7	688.7	722.8	746.5	760.5	766.1
132.5°	514.2	569.8	620.4	663.6	697.2	720.9	733.7	738.7
135°	495.6	541.6	587.6	626.6	656.7	679.7	692.1	695.0
137.5°	480.7	519.2	555.7	589.7	617.1	636.9	647.8	652.0
140°	471.2	504.7	536.7	567.4	589.7	607.8	618.3	622.5
142.5°	463.4	491.9	519.4	545.1	566.3	582.7	592.1	592.9
145°	452.4	475.4	497.0	517.2	534.0	545.8	552.8	554.8
147.5°	443.9	462.0	478.8	493.7	507.5	516.9	521.7	522.9
150°	437.7	453.1	467.7	480.3	490.7	499.1	503.3	504.0
152.5°	431.6	445.9	458.3	469.1	477.3	484.6	487.7	487.8
155°	423.1	434.3	444.7	452.4	460.0	464.9	467.7	466.4
157.5°	413.2	422.6	431.3	437.3	442.7	446.8	448.1	448.1
160°	407.1	414.7	422.4	427.3	432.2	435.7	436.3	436.3
162.5°	400.9	407.5	414.0	417.9	422.7	425.1	425.8	425.2
165°	391.7	396.6	401.5	404.3	407.1	409.8	409.8	409.2
167.5°	383.0	386.7	390.0	392.6	393.9	395.4	395.2	394.4
170°	378.5	380.6	383.3	384.8	385.5	387.5	386.8	385.5
172.5°	373.4	375.1	377.3	378.1	378.8	379.8	379.1	378.3
175°	368.0	368.7	369.4	370.1	370.1	370.9	370.1	368.7
177.5°	364.2	364.2	364.7	364.7	364.7	364.7	364.2	363.0
180°	362.5	362.5	362.5	362.5	362.5	362.5	362.5	362.5

(END OF REPORT)