

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332946-930

Luminaire Tested: **SA4XXRDIP-C795D1035U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332946-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D1035U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5985.9 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332946-930
CATALOG NUMBER: SA4XXRDIP-C795D1035U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332946-930

CATALOG NUMBER: SA4XXRDIP-C795D1035U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50	44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	37	32
3	81	71	64	59	73	66	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	56	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	33	29	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9143	9143	9143
5°	9164	9052	9108
10°	9107	8943	8943
15°	9002	8756	8690
20°	8858	8508	8352
25°	8675	8219	8011
30°	8496	7914	7582
35°	8298	7597	7154
40°	8061	7238	6690
45°	7841	6882	6218
50°	7592	6469	5718
55°	7323	6042	5175
60°	7030	5572	4621
65°	6758	4988	4076
70°	6366	4338	3460
75°	5870	3599	2813
80°	5119	2738	2580
85°	4335	2492	2325



TEST NUMBER: P332946-930

CATALOG NUMBER: SA4XXRDIP-C795D1035U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	1.8
10°-20°	296.7	5.0
20°-30°	428.4	7.2
30°-40°	485.6	8.1
40°-50°	468.9	7.8
50°-60°	389.9	6.5
60°-70°	269.3	4.5
70°-80°	136.5	2.3
80°-90°	38.2	0.6
90°-100°	37.2	0.6
100°-110°	237.3	4.0
110°-120°	453.9	7.6
120°-130°	576.3	9.6
130°-140°	616.6	10.3
140°-150°	576.6	9.6
150°-160°	464.9	7.8
160°-170°	299.9	5.0
170°-180°	103.4	1.7
0°-30°	831.5	13.9
0°-40°	1317.1	22.0
0°-60°	2176.0	36.4
0°-90°	2619.9	43.8
90°-120°	728.5	12.2
90°-150°	2497.9	41.7
90°-180°	3366.0	56.2
0°-180°	5985.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1133	1133	1133	1133	1133	
5°	1131	1127	1117	1125	1124	107
15°	1077	1069	1048	1046	1040	303
25°	974	957	923	908	899	449
35°	842	813	771	742	726	526
45°	687	654	603	562	545	529
55°	520	484	429	386	368	465
65°	354	316	261	225	213	349
75°	188	156	115	96	90	199
85°	47	30	27	25	25	53
90°	2	11	18	23	24	4
95°	45	19	18	23	24	58
105°	245	250	254	259	232	256
115°	457	460	459	461	461	450
125°	643	646	645	647	648	574
135°	798	797	800	802	803	614
145°	920	922	922	923	924	574
155°	1008	1009	1007	1010	1008	465
165°	1064	1060	1060	1065	1059	300
175°	1088	1084	1084	1090	1082	104
180°	1088	1088	1088	1088	1088	



TEST NUMBER: P332946-930

CATALOG NUMBER: SA4XXRDIP-C795D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1135.4	1134.7	1134.1	1133.5	1132.9	1131.7	1130.0	1128.4	1126.7	1124.9	1126.7
5°	1130.8	1130.1	1129.3	1128.5	1127.7	1126.3	1123.9	1121.6	1119.2	1117.0	1118.9
7.5°	1120.6	1119.8	1119.0	1118.2	1117.4	1115.5	1112.5	1109.5	1106.4	1103.4	1104.6
10°	1110.9	1109.9	1109.0	1108.0	1107.0	1104.8	1101.4	1097.9	1094.5	1091.0	1091.7
12.5°	1098.4	1097.3	1096.2	1095.0	1094.0	1091.4	1087.3	1083.1	1079.0	1075.0	1075.5
15°	1077.1	1075.4	1073.6	1071.9	1070.2	1066.9	1062.0	1057.2	1052.4	1047.6	1047.2
17.5°	1051.2	1048.7	1046.2	1043.7	1041.2	1037.1	1031.3	1025.5	1019.7	1013.9	1012.8
20°	1031.1	1028.6	1026.1	1023.6	1021.1	1016.6	1010.0	1003.5	996.9	990.3	988.8
22.5°	1008.9	1006.1	1003.3	1000.5	997.7	992.7	985.7	978.7	971.7	964.7	962.4
25°	973.9	970.4	966.9	963.4	960.0	954.3	946.4	938.5	930.6	922.7	919.4
27.5°	937.1	932.8	928.4	924.1	919.7	913.3	904.8	896.4	887.9	879.5	875.5
30°	911.4	906.6	901.8	897.0	892.2	885.3	876.2	867.2	858.0	849.0	844.2
32.5°	884.4	879.0	873.5	868.0	862.7	855.2	845.9	836.5	827.1	817.7	812.2
35°	842.0	835.9	829.7	823.5	817.4	809.5	799.9	790.2	780.6	770.9	764.4
37.5°	796.8	790.4	784.1	777.7	771.4	762.9	752.2	741.5	730.8	720.2	712.8
40°	764.9	758.6	752.2	745.8	739.5	730.8	719.7	708.8	697.8	686.8	678.7
42.5°	734.3	727.7	721.1	714.4	707.7	698.6	687.2	675.7	664.3	652.8	644.6
45°	686.8	679.7	672.5	665.4	658.3	649.0	637.4	625.8	614.2	602.8	593.3
47.5°	637.7	630.4	623.1	615.6	608.3	598.6	586.6	574.5	562.6	550.5	540.7
50°	604.5	597.0	589.4	581.9	574.4	564.4	552.1	539.8	527.4	515.1	505.5
52.5°	570.5	563.1	555.7	548.4	541.0	531.0	518.4	505.7	493.1	480.5	470.7
55°	520.3	512.6	504.9	497.2	489.5	479.4	466.8	454.3	441.8	429.3	419.2
57.5°	470.8	462.7	454.7	446.7	438.6	428.4	416.1	403.8	391.5	379.1	369.0
60°	435.4	427.6	420.0	412.2	404.5	394.5	382.1	369.8	357.5	345.1	335.1
62.5°	403.4	395.4	387.4	379.4	371.4	361.0	348.4	335.7	323.1	310.5	301.2
65°	353.8	345.5	337.2	329.0	320.7	310.4	298.0	285.7	273.4	261.1	252.7
67.5°	302.3	294.4	286.4	278.5	270.5	260.9	249.4	238.0	226.5	215.1	207.9
70°	269.7	261.6	253.5	245.4	237.3	227.8	216.8	205.8	194.9	183.8	177.5
72.5°	235.1	227.7	220.4	213.0	205.7	196.9	186.5	176.1	165.8	155.4	149.9
75°	188.2	181.1	173.9	166.8	159.6	151.6	142.5	133.5	124.4	115.4	110.9
77.5°	140.6	134.6	128.6	122.5	116.4	109.7	102.5	95.1	87.8	80.5	77.9
80°	110.1	104.5	99.0	93.4	87.8	82.1	76.3	70.5	64.7	58.9	58.4
82.5°	83.8	78.7	73.5	68.4	63.3	59.0	55.8	52.4	49.1	45.8	45.3
85°	46.8	43.0	39.1	35.3	31.4	29.2	28.6	28.0	27.5	26.9	26.5
87.5°	16.5	15.6	14.8	13.9	13.1	12.7	12.9	13.0	13.1	13.3	13.4
90°	2.4	4.4	6.4	8.4	10.4	12.1	13.5	15.0	16.5	17.9	19.0
92.5°	10.3	10.4	10.4	10.6	10.7	11.5	12.9	14.3	15.8	17.3	18.3
95°	44.8	38.6	32.4	26.3	20.1	17.2	17.4	17.5	17.7	17.9	19.0
97.5°	95.1	98.9	102.7	106.6	110.4	102.2	82.0	61.9	41.7	21.5	21.6
100°	133.5	136.7	140.0	143.2	146.5	135.7	110.7	85.8	60.7	35.8	32.8
102.5°	176.4	178.9	181.2	183.6	186.0	185.6	182.3	179.0	175.8	172.5	139.3
105°	245.0	246.1	247.1	248.3	249.3	250.3	251.2	252.1	253.1	254.0	255.6
107.5°	308.6	309.2	309.7	310.2	310.8	311.7	312.9	314.1	315.4	316.6	317.4
110°	351.6	352.1	352.7	353.2	353.8	354.6	355.6	356.8	357.8	358.9	359.3



TEST NUMBER: P332946-930

CATALOG NUMBER: SA4XXRDIP-C795D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.3	394.3	395.3	396.2	397.2	397.9	398.4	398.9	399.4	399.9	399.9
115°	457.4	458.0	458.5	459.0	459.6	459.7	459.6	459.4	459.2	459.0	459.4
117.5°	515.2	515.9	516.7	517.4	518.1	518.6	519.0	519.4	519.8	520.2	520.2
120°	554.2	555.0	555.7	556.4	557.2	557.4	557.3	557.1	556.8	556.7	557.1
122.5°	590.7	591.2	591.6	592.0	592.5	592.8	593.0	593.3	593.5	593.8	594.0
125°	642.9	643.7	644.4	645.1	645.9	646.0	645.7	645.3	645.0	644.6	645.1
127.5°	692.4	692.6	692.8	693.0	693.2	693.7	694.6	695.4	696.2	697.0	696.9
130°	724.4	724.6	724.7	724.9	725.0	725.5	726.0	726.5	727.1	727.7	727.8
132.5°	753.7	754.0	754.3	754.6	755.0	755.5	756.2	756.8	757.5	758.2	758.4
135°	797.6	797.4	797.3	797.0	796.9	797.1	797.9	798.6	799.3	800.1	800.4
137.5°	836.5	836.6	836.7	836.7	836.8	837.2	838.0	838.9	839.6	840.4	840.8
140°	861.9	862.3	862.7	863.0	863.3	863.7	864.1	864.5	864.8	865.2	865.7
142.5°	884.7	885.3	886.0	886.6	887.3	887.7	887.9	888.2	888.4	888.6	889.0
145°	919.7	920.2	920.8	921.3	921.9	922.1	922.1	922.1	922.1	922.1	922.3
147.5°	947.5	948.5	949.6	950.6	951.6	952.0	951.8	951.6	951.5	951.3	951.5
150°	967.7	968.4	969.1	969.9	970.6	970.9	970.7	970.5	970.4	970.1	970.1
152.5°	984.6	985.2	985.8	986.3	986.9	987.1	986.8	986.4	986.1	985.8	986.1
155°	1008.4	1008.6	1008.8	1008.9	1009.1	1008.9	1008.4	1007.9	1007.3	1006.8	1007.5
157.5°	1028.4	1028.3	1028.2	1028.1	1028.0	1027.6	1027.0	1026.4	1025.8	1025.2	1026.1
160°	1040.2	1039.6	1039.1	1038.5	1038.0	1037.6	1037.5	1037.2	1037.1	1036.9	1038.0
162.5°	1050.6	1049.9	1049.2	1048.5	1047.8	1047.4	1047.2	1047.0	1046.8	1046.7	1047.7
165°	1063.7	1062.8	1061.9	1061.0	1060.1	1059.6	1059.6	1059.6	1059.6	1059.6	1061.1
167.5°	1074.2	1073.3	1072.3	1071.4	1070.4	1069.9	1069.8	1069.7	1069.6	1069.4	1071.1
170°	1080.0	1079.0	1077.8	1076.8	1075.7	1075.2	1075.4	1075.6	1075.8	1076.0	1077.4
172.5°	1083.9	1082.9	1081.7	1080.7	1079.6	1079.1	1079.3	1079.5	1079.7	1079.9	1081.3
175°	1088.2	1087.1	1086.0	1084.9	1083.9	1083.4	1083.5	1083.8	1083.9	1084.1	1085.7
177.5°	1090.1	1089.1	1088.1	1087.1	1086.1	1085.7	1086.0	1086.3	1086.5	1086.9	1088.0
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2



TEST NUMBER: P332946-930

CATALOG NUMBER: SA4XXRDIP-C795D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1128.4	1130.0	1131.7	1132.5	1132.4	1132.2	1132.0	1131.9
5°	1120.8	1122.7	1124.7	1125.4	1125.0	1124.7	1124.3	1123.9
7.5°	1105.9	1107.2	1108.4	1108.6	1108.1	1107.4	1106.9	1106.2
10°	1092.5	1093.2	1094.1	1094.1	1093.2	1092.5	1091.7	1091.0
12.5°	1076.0	1076.4	1076.8	1076.5	1075.5	1074.4	1073.3	1072.2
15°	1046.8	1046.4	1046.0	1045.2	1043.8	1042.4	1041.1	1039.8
17.5°	1011.8	1010.7	1009.6	1008.0	1006.0	1004.0	1001.9	999.9
20°	987.2	985.7	984.1	982.2	979.7	977.1	974.6	972.2
22.5°	960.1	957.7	955.4	953.2	951.2	949.2	947.1	945.1
25°	916.2	912.9	909.6	907.0	905.1	903.2	901.2	899.3
27.5°	871.4	867.4	863.3	859.9	857.1	854.4	851.6	848.8
30°	839.4	834.5	829.7	825.7	822.7	819.6	816.5	813.4
32.5°	806.6	801.0	795.4	791.2	788.2	785.3	782.4	779.4
35°	757.8	751.3	744.8	739.7	736.3	732.8	729.3	725.9
37.5°	705.5	698.1	690.8	685.4	682.0	678.5	675.1	671.6
40°	670.7	662.5	654.4	648.7	645.2	641.7	638.3	634.8
42.5°	636.3	628.1	619.9	613.9	610.3	606.7	603.1	599.4
45°	583.8	574.4	564.9	558.5	555.0	551.5	548.0	544.6
47.5°	530.9	521.1	511.4	504.5	500.8	496.9	493.1	489.3
50°	495.9	486.2	476.5	469.9	466.3	462.6	458.9	455.3
52.5°	460.9	451.1	441.2	434.5	430.6	426.8	423.1	419.2
55°	409.2	399.2	389.2	382.4	378.7	375.0	371.4	367.7
57.5°	358.8	348.6	338.4	332.0	329.2	326.4	323.7	320.9
60°	325.1	315.1	305.1	298.5	295.5	292.4	289.3	286.2
62.5°	292.0	282.7	273.5	267.6	265.1	262.7	260.2	257.7
65°	244.4	236.2	227.9	222.6	220.3	217.9	215.6	213.4
67.5°	200.8	193.7	186.5	181.7	179.2	176.6	174.1	171.5
70°	171.1	164.8	158.4	154.3	152.4	150.4	148.5	146.6
72.5°	144.6	139.1	133.6	130.0	128.3	126.5	124.7	122.9
75°	106.5	102.1	97.6	94.8	93.7	92.5	91.3	90.2
77.5°	75.3	72.7	70.1	68.6	68.3	68.0	67.7	67.3
80°	57.8	57.2	56.7	56.3	56.1	55.8	55.7	55.5
82.5°	44.9	44.5	44.1	43.8	43.6	43.4	43.2	43.0
85°	26.1	25.8	25.4	25.1	25.1	25.1	25.1	25.1
87.5°	13.5	13.5	13.5	13.7	13.9	14.1	14.3	14.6
90°	20.1	21.2	22.3	23.0	23.3	23.7	24.1	24.4
92.5°	19.4	20.5	21.6	22.2	22.3	22.3	22.4	22.5
95°	20.1	21.2	22.3	22.9	23.1	23.2	23.4	23.6
97.5°	21.7	21.9	21.9	22.1	22.3	22.4	22.6	22.8
100°	29.7	26.6	23.5	22.1	22.3	22.4	22.6	22.8
102.5°	106.2	73.1	39.9	23.3	23.3	23.4	23.4	23.5
105°	257.2	258.8	260.4	258.0	251.5	245.0	238.5	232.0
107.5°	318.2	319.0	319.8	320.5	321.2	321.9	322.6	323.3
110°	359.6	360.0	360.4	360.9	361.3	361.9	362.5	363.0



TEST NUMBER: P332946-930

CATALOG NUMBER: SA4XXRDIP-C795D1035U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	399.8	399.7	399.7	400.0	400.6	401.4	402.0	402.7
115°	459.7	460.2	460.5	460.6	460.6	460.6	460.6	460.6
117.5°	520.1	520.0	519.9	519.9	519.8	519.8	519.7	519.6
120°	557.4	557.7	558.2	558.2	557.7	557.4	557.1	556.7
122.5°	594.3	594.4	594.7	594.6	594.3	593.9	593.5	593.1
125°	645.7	646.2	646.8	647.1	647.3	647.5	647.7	647.8
127.5°	696.8	696.7	696.6	696.4	696.3	696.2	696.0	695.9
130°	728.0	728.1	728.3	728.5	728.5	728.5	728.5	728.5
132.5°	758.6	758.8	759.0	759.0	758.8	758.6	758.6	758.4
135°	800.8	801.1	801.5	801.8	802.3	802.6	802.9	803.3
137.5°	841.2	841.6	842.0	842.1	842.0	842.0	841.8	841.7
140°	866.3	866.8	867.3	867.7	867.9	868.0	868.2	868.5
142.5°	889.4	889.8	890.2	890.4	890.5	890.5	890.6	890.6
145°	922.5	922.7	922.8	923.2	923.5	923.8	924.2	924.5
147.5°	951.5	951.7	951.9	952.0	952.2	952.4	952.6	952.8
150°	970.1	970.1	970.1	970.2	970.5	970.6	970.8	970.9
152.5°	986.3	986.7	986.9	987.0	986.9	986.8	986.7	986.6
155°	1008.2	1008.9	1009.7	1009.7	1009.3	1008.7	1008.1	1007.6
157.5°	1027.0	1028.0	1028.9	1028.9	1028.0	1027.0	1026.1	1025.2
160°	1039.1	1040.2	1041.2	1041.2	1040.2	1039.1	1038.0	1036.9
162.5°	1048.8	1049.9	1051.0	1050.9	1049.7	1048.5	1047.3	1046.0
165°	1062.6	1064.0	1065.4	1065.4	1063.7	1062.1	1060.5	1058.8
167.5°	1072.6	1074.2	1075.8	1075.7	1073.9	1072.1	1070.2	1068.4
170°	1078.9	1080.3	1081.7	1081.6	1079.8	1078.0	1076.1	1074.3
172.5°	1082.8	1084.2	1085.7	1085.4	1083.5	1081.5	1079.5	1077.6
175°	1087.4	1089.0	1090.6	1090.3	1088.2	1086.0	1083.9	1081.7
177.5°	1089.2	1090.3	1091.5	1091.2	1089.5	1087.8	1086.0	1084.3
180°	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2	1088.2

(END OF REPORT)