

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331668-940

Luminaire Tested: **SA2XXRDIP-C485D925U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331668-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C485D925U940-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4738.0 lumens  
Efficiency: N/A  
Efficacy: 106.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 44.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331668-940  
CATALOG NUMBER: SA2XXRDIP-C485D925U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331668-940

CATALOG NUMBER: SA2XXRDIP-C485D925U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32				
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34	28				
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29	24				
3	78	70	63	57	70	63	57	52	50	46	43	39	36	34	28	27	25	20				
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22	18				
5	66	55	47	42	59	50	43	38	40	35	32	31	28	25	23	21	19	16				
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14				
7	56	44	37	32	51	40	34	29	33	28	24	26	22	20	19	17	15	12				
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11				
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10				
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11880	11880	11880
5°	11925	11733	11797
10°	11835	11540	11442
15°	11699	11198	10877
20°	11510	10710	10172
25°	11318	10156	9492
30°	11050	9587	8617
35°	10789	8966	7849
40°	10526	8323	6962
45°	10218	7604	6158
50°	9902	6875	5368
55°	9579	6092	4611
60°	9203	5270	3827
65°	8779	4424	3484
70°	8266	3644	3205
75°	7642	3319	2994
80°	6750	2966	2724
85°	5298	2353	2353



TEST NUMBER: P331668-940

CATALOG NUMBER: SA2XXRDIP-C485D925U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.9	1.5
10°-20°	189.1	4.0
20°-30°	265.6	5.6
30°-40°	289.6	6.1
40°-50°	266.3	5.6
50°-60°	209.1	4.4
60°-70°	136.4	2.9
70°-80°	70.3	1.5
80°-90°	22.4	0.5
90°-100°	185.0	3.9
100°-110°	627.9	13.3
110°-120°	667.1	14.1
120°-130°	549.1	11.6
130°-140°	441.0	9.3
140°-150°	333.2	7.0
150°-160°	234.2	4.9
160°-170°	137.9	2.9
170°-180°	44.9	0.9
0°-30°	523.6	11.1
0°-40°	813.2	17.2
0°-60°	1288.6	27.2
0°-90°	1517.7	32.0
90°-120°	1480.0	31.2
90°-150°	2803.4	59.2
90°-180°	3220.0	68.0
0°-180°	4738.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	736	736	736	736	736	
5°	736	732	724	729	728	70
15°	700	692	670	658	651	197
25°	635	613	570	544	533	292
35°	547	512	455	414	398	342
45°	448	402	333	287	270	345
55°	340	287	216	178	164	304
65°	230	176	116	94	91	228
75°	122	77	53	49	48	130
85°	29	15	13	13	13	34
90°	1	12	30	29	29	3
95°	31	77	349	132	102	33
105°	109	164	659	1179	1003	115
115°	191	242	552	1139	1320	190
125°	267	316	530	922	1071	237
135°	313	374	524	775	887	242
145°	358	411	522	647	708	224
155°	407	439	506	573	595	187
165°	443	457	485	514	522	125
175°	462	462	466	472	471	44
180°	463	463	463	463	463	



TEST NUMBER: P331668-940

CATALOG NUMBER: SA2XXRDIP-C485D925U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	738.5	738.0	737.4	736.7	736.2	735.2	734.0	732.6	731.3	730.0	731.2
5°	735.8	735.1	734.4	733.7	732.9	731.6	729.7	727.7	725.9	723.9	725.2
7.5°	728.3	727.4	726.5	725.5	724.6	723.0	720.8	718.5	716.3	714.1	714.4
10°	721.9	720.9	719.8	718.8	717.7	715.8	712.8	709.8	706.9	703.9	703.5
12.5°	713.9	712.7	711.3	710.1	708.8	706.3	702.5	698.7	694.9	691.2	690.4
15°	699.9	698.3	696.7	695.0	693.4	690.1	685.0	680.0	675.0	669.9	667.2
17.5°	682.8	680.3	677.8	675.3	672.8	668.3	661.9	655.4	649.0	642.5	639.2
20°	669.9	667.0	664.1	661.1	658.1	652.9	645.5	638.1	630.7	623.3	619.6
22.5°	656.1	652.8	649.4	646.1	642.8	637.0	628.7	620.3	612.0	603.6	598.9
25°	635.3	630.6	625.9	621.1	616.4	609.1	599.3	589.6	579.8	570.1	564.0
27.5°	610.3	605.1	599.9	594.9	589.7	581.6	570.6	559.5	548.6	537.5	530.5
30°	592.7	587.1	581.5	575.9	570.2	561.5	549.7	537.8	525.9	514.2	506.6
32.5°	575.7	569.1	562.5	556.0	549.4	540.0	528.0	515.9	503.8	491.8	483.1
35°	547.4	539.8	532.4	524.8	517.2	506.9	493.9	480.9	467.9	454.9	445.5
37.5°	519.2	510.9	502.6	494.3	486.1	474.9	461.1	447.2	433.3	419.5	409.1
40°	499.4	490.6	481.7	472.9	464.0	452.4	438.0	423.7	409.3	394.9	384.4
42.5°	479.2	469.8	460.5	451.2	441.8	429.7	414.9	400.0	385.2	370.4	359.5
45°	447.5	437.7	427.7	417.8	407.9	395.1	379.6	364.1	348.5	333.0	322.4
47.5°	416.6	406.1	395.7	385.1	374.6	361.3	345.3	329.2	313.2	297.1	286.7
50°	394.2	383.7	373.3	362.7	352.2	338.9	322.5	306.3	290.0	273.7	263.5
52.5°	372.4	361.4	350.4	339.5	328.5	315.0	299.1	283.2	267.2	251.4	241.5
55°	340.3	328.8	317.2	305.7	294.2	280.4	264.4	248.4	232.4	216.4	207.6
57.5°	307.4	295.6	283.7	271.9	260.0	246.5	231.1	215.7	200.4	185.0	176.8
60°	285.0	273.2	261.4	249.5	237.6	224.2	208.9	193.7	178.4	163.2	155.6
62.5°	263.1	251.4	239.5	227.7	215.8	202.7	188.2	173.6	159.1	144.5	137.3
65°	229.8	217.8	205.8	193.8	181.8	169.2	155.9	142.5	129.2	115.8	110.8
67.5°	197.5	185.7	173.7	161.8	149.9	137.9	126.0	114.0	102.0	90.1	87.7
70°	175.1	163.6	152.0	140.5	128.9	118.1	107.9	97.6	87.5	77.2	75.8
72.5°	153.8	142.8	131.7	120.6	109.6	100.0	91.8	83.6	75.3	67.1	65.9
75°	122.5	112.2	101.8	91.5	81.1	73.4	68.4	63.3	58.3	53.2	52.3
77.5°	91.8	82.7	73.6	64.5	55.5	49.7	47.3	44.9	42.4	39.9	39.3
80°	72.6	65.0	57.5	49.9	42.4	37.9	36.4	35.0	33.4	31.9	31.4
82.5°	55.0	49.1	43.2	37.4	31.5	28.0	27.0	25.9	25.0	24.0	23.6
85°	28.6	25.5	22.4	19.4	16.2	14.4	14.0	13.6	13.1	12.7	12.7
87.5°	8.7	8.3	8.0	7.5	6.9	7.0	7.8	9.1	10.2	10.3	10.0
90°	0.9	3.6	7.1	8.9	10.7	13.4	17.8	24.0	29.3	30.2	29.3
92.5°	10.9	15.7	22.1	25.9	32.0	40.4	60.5	88.8	114.0	115.7	97.7
95°	31.1	34.7	43.6	51.6	65.9	87.2	128.1	205.5	308.8	348.8	305.2
97.5°	50.7	55.6	65.0	77.0	93.5	117.6	169.1	277.0	448.5	595.6	624.7
100°	68.5	71.2	79.2	93.5	111.3	136.2	183.3	291.9	484.1	703.0	831.3
102.5°	84.9	86.9	94.9	109.1	127.6	152.6	196.2	292.7	470.6	706.6	908.1
105°	108.6	112.2	118.3	131.7	151.3	176.2	218.0	297.2	444.1	659.4	896.2
107.5°	134.2	137.1	143.1	155.4	174.8	199.9	240.5	309.5	430.9	608.9	818.1
110°	151.3	154.9	160.2	171.7	190.5	216.2	255.4	319.5	428.1	584.7	768.9



TEST NUMBER: P331668-940

CATALOG NUMBER: SA2XXRDIP-C485D925U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	166.9	170.5	176.6	187.4	205.4	231.9	269.7	330.2	428.7	569.0	734.8
115°	191.4	195.8	201.2	211.8	229.6	253.6	291.9	346.2	432.5	551.8	692.4
117.5°	216.6	220.2	225.5	235.0	252.0	277.0	312.4	363.3	438.9	543.4	665.7
120°	232.3	235.9	241.2	249.1	267.0	291.9	326.6	374.7	443.2	538.4	651.5
122.5°	247.3	250.0	255.4	264.1	282.0	307.6	340.1	384.6	448.2	535.6	639.4
125°	267.0	269.7	275.0	285.7	303.4	328.4	360.4	400.5	455.7	530.4	622.1
127.5°	282.7	286.2	293.6	305.4	322.5	348.1	379.3	415.3	463.3	527.4	606.1
130°	291.9	295.4	304.3	316.8	334.7	359.5	390.7	424.5	469.0	525.9	595.4
132.5°	300.4	304.7	314.3	327.5	346.0	371.0	400.6	433.7	474.7	525.2	586.8
135°	313.3	316.8	327.5	340.8	361.3	386.2	414.7	445.9	481.4	524.1	574.9
137.5°	325.4	329.7	340.3	354.5	374.9	398.0	426.1	455.1	487.5	524.0	566.5
140°	334.7	338.2	348.8	363.1	382.7	405.8	432.5	460.1	490.4	523.3	561.6
142.5°	343.8	346.7	356.7	371.0	389.8	411.5	437.5	464.4	492.5	523.3	556.6
145°	357.8	361.3	370.2	383.6	401.4	421.0	445.0	469.9	494.8	521.5	550.0
147.5°	372.7	375.4	383.9	396.2	411.0	428.5	451.0	473.0	495.5	518.4	543.2
150°	382.7	385.3	392.4	404.0	417.4	433.4	453.9	474.3	494.8	516.2	537.5
152.5°	392.6	393.9	401.0	411.2	423.8	438.4	456.7	475.0	493.4	512.6	532.5
155°	406.7	407.6	413.0	422.8	432.5	445.9	461.0	476.1	491.2	506.4	523.3
157.5°	418.5	419.4	423.7	432.1	440.0	451.2	464.0	476.1	487.1	500.0	514.6
160°	426.3	427.2	430.7	437.8	445.0	454.8	465.5	476.1	485.0	495.7	508.2
162.5°	434.1	433.5	437.1	442.8	449.2	456.9	466.2	475.4	482.9	492.1	502.5
165°	443.2	442.3	444.1	449.4	453.9	459.2	467.3	473.5	478.8	485.0	493.0
167.5°	450.7	449.6	451.2	454.6	457.8	461.2	467.1	472.3	474.7	478.8	483.8
170°	455.7	453.9	454.8	457.4	459.2	461.9	466.4	470.8	472.6	475.2	478.8
172.5°	458.5	457.4	456.9	459.6	460.7	462.6	465.7	468.7	469.8	471.0	473.9
175°	461.9	461.0	460.1	461.9	461.9	462.8	464.6	466.4	465.5	466.4	467.3
177.5°	463.5	462.1	461.4	462.8	462.8	462.8	463.5	464.9	463.5	462.8	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331668-940

CATALOG NUMBER: SA2XXRDIP-C485D925U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	735.8	735.8	735.8	735.8	735.8	735.8	735.8	735.8
2.5°	732.4	733.6	734.8	735.2	735.0	734.8	734.5	734.3
5°	726.6	727.9	729.2	729.7	729.2	728.8	728.3	727.9
7.5°	714.8	715.2	715.6	715.4	714.6	713.8	713.1	712.3
10°	703.0	702.6	702.1	701.5	700.6	699.7	698.8	697.9
12.5°	689.6	688.8	688.0	686.8	685.3	683.9	682.3	680.9
15°	664.3	661.6	658.7	656.6	655.1	653.6	652.1	650.7
17.5°	635.8	632.5	629.1	626.2	623.7	621.1	618.6	616.0
20°	615.9	612.2	608.5	605.0	601.8	598.5	595.3	592.0
22.5°	594.1	589.3	584.6	580.9	578.5	576.1	573.7	571.2
25°	557.9	551.9	545.8	541.6	539.4	537.2	535.0	532.8
27.5°	523.4	516.3	509.3	504.0	500.4	497.0	493.4	489.9
30°	499.0	491.5	483.9	478.1	474.1	470.2	466.2	462.2
32.5°	474.5	465.9	457.3	451.1	447.4	443.6	439.8	436.0
35°	436.2	426.9	417.6	411.3	408.0	404.7	401.5	398.2
37.5°	398.9	388.6	378.4	371.3	367.7	363.9	360.2	356.4
40°	373.9	363.4	352.8	345.7	341.9	338.0	334.1	330.3
42.5°	348.7	337.8	327.0	319.7	315.9	312.2	308.4	304.7
45°	311.9	301.5	291.0	283.9	280.4	276.8	273.2	269.7
47.5°	276.3	265.8	255.4	248.5	245.3	242.1	238.8	235.6
50°	253.2	243.1	232.8	226.2	223.1	220.0	216.9	213.7
52.5°	231.6	221.8	211.9	205.5	202.7	199.8	196.9	194.0
55°	198.7	189.8	180.9	175.0	172.3	169.4	166.7	163.8
57.5°	168.7	160.6	152.5	147.2	144.8	142.5	140.1	137.7
60°	148.0	140.5	133.0	128.0	125.6	123.2	120.9	118.5
62.5°	130.1	123.0	115.7	111.5	110.0	108.6	107.2	105.8
65°	105.8	100.8	95.8	93.0	92.6	92.1	91.7	91.2
67.5°	85.4	83.1	80.8	79.5	78.9	78.5	78.0	77.5
70°	74.3	72.9	71.3	70.3	69.7	69.1	68.5	67.9
72.5°	64.6	63.4	62.2	61.3	61.0	60.6	60.3	59.9
75°	51.2	50.2	49.1	48.5	48.4	48.2	48.1	48.0
77.5°	38.8	38.2	37.6	37.2	36.9	36.7	36.5	36.2
80°	30.8	30.2	29.6	29.3	29.3	29.3	29.3	29.3
82.5°	23.3	22.9	22.6	22.4	22.4	22.4	22.4	22.4
85°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7
87.5°	9.7	9.3	9.5	9.6	9.6	9.6	9.6	9.6
90°	28.4	26.7	28.4	29.3	29.3	29.3	29.3	29.3
92.5°	77.6	66.6	59.1	53.6	52.9	50.0	50.7	49.3
95°	233.2	178.9	141.5	121.9	110.4	103.3	100.6	101.5
97.5°	544.1	445.1	348.8	284.6	242.1	220.2	207.1	199.7
100°	812.5	702.1	580.2	472.6	398.7	360.4	334.7	318.6
102.5°	988.4	963.5	874.3	760.2	679.9	614.6	582.4	560.7
105°	1081.3	1181.9	1193.5	1164.0	1108.8	1053.7	1015.4	1003.0
107.5°	1014.4	1165.8	1258.4	1301.5	1308.4	1305.4	1297.7	1281.2
110°	956.7	1116.0	1229.9	1302.9	1341.1	1358.1	1366.1	1365.2





TEST NUMBER: P331668-940

CATALOG NUMBER: SA2XXRDIP-C485D925U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	904.0	1056.9	1178.7	1262.3	1315.5	1343.8	1359.0	1363.8
115°	839.2	976.2	1092.9	1184.5	1247.7	1288.6	1311.8	1319.8
117.5°	790.4	910.8	1016.5	1102.5	1166.9	1210.1	1234.6	1241.3
120°	766.2	876.6	970.9	1052.0	1114.2	1156.0	1181.9	1190.8
122.5°	747.0	848.1	937.5	1010.7	1066.5	1107.6	1130.6	1138.1
125°	719.1	810.7	889.0	955.8	1007.5	1041.3	1063.5	1070.6
127.5°	691.5	774.5	848.3	909.9	954.9	986.6	1005.8	1011.6
130°	673.7	750.2	820.6	879.3	922.9	953.1	970.9	978.0
132.5°	656.6	727.5	792.0	847.2	890.1	920.4	936.7	943.2
135°	632.8	691.5	750.2	800.0	838.3	867.7	883.7	887.3
137.5°	613.7	662.8	709.4	752.9	787.8	813.1	827.2	832.5
140°	601.6	644.4	685.3	724.4	752.9	776.1	789.4	794.7
142.5°	591.7	627.9	663.2	696.0	723.0	744.0	755.9	757.0
145°	577.6	607.0	634.5	660.3	681.7	696.9	705.7	708.4
147.5°	566.7	589.9	611.4	630.3	647.9	660.0	666.0	667.6
150°	558.9	578.5	597.2	613.1	626.5	637.2	642.6	643.5
152.5°	551.1	569.2	585.1	599.0	609.4	618.7	622.6	622.8
155°	540.2	554.5	567.8	577.6	587.4	593.6	597.2	595.4
157.5°	527.5	539.5	550.7	558.4	565.3	570.4	572.0	572.0
160°	519.7	529.5	539.3	545.5	551.8	556.2	557.1	557.1
162.5°	511.9	520.2	528.6	533.4	539.7	542.7	543.6	542.9
165°	500.2	506.4	512.6	516.2	519.7	523.3	523.3	522.4
167.5°	488.9	493.7	498.0	501.2	502.8	504.8	504.6	503.5
170°	483.2	485.9	489.5	491.2	492.1	494.8	493.9	492.1
172.5°	476.8	478.8	481.6	482.7	483.6	484.8	483.9	482.9
175°	469.9	470.8	471.7	472.6	472.6	473.5	472.6	470.8
177.5°	464.9	464.9	465.7	465.7	465.7	465.7	464.9	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8

(END OF REPORT)