

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331700-940

Luminaire Tested: **SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331700-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5701.0 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	24	22	19
7	59	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	40	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21151	21151	21151	21151
5°	23622	21284	18870	21284
10°	26209	21135	16357	21135
15°	27497	20824	12889	20824
20°	23838	20366	11153	20366
25°	15634	19737	9957	19737
30°	10524	18975	9012	18975
35°	8523	18015	8129	18015
40°	7579	16971	7522	16971
45°	6859	15746	6715	15746
50°	6242	14531	6219	14531
55°	5869	13185	5790	13185
60°	4908	11951	4850	11951
65°	4138	10850	4695	10850
70°	3829	9692	4428	9692
75°	3575	8434	4086	8434
80°	3301	6936	3636	6936
85°	3038	5483	3205	5483



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	2.2
10°-20°	346.0	6.1
20°-30°	445.9	7.8
30°-40°	423.7	7.4
40°-50°	363.0	6.4
50°-60°	276.4	4.8
60°-70°	174.7	3.1
70°-80°	87.3	1.5
80°-90°	27.6	0.5
90°-100°	77.8	1.4
100°-110°	241.6	4.2
110°-120°	412.9	7.2
120°-130°	543.0	9.5
130°-140°	609.4	10.7
140°-150°	597.6	10.5
150°-160°	501.2	8.8
160°-170°	332.4	5.8
170°-180°	116.2	2.0
0°-30°	916.1	16.1
0°-40°	1339.8	23.5
0°-60°	1979.2	34.7
0°-90°	2268.9	39.8
90°-120°	732.3	12.8
90°-150°	2482.3	43.5
90°-180°	3432.0	60.2
0°-180°	5701.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1310	1310	1310	1310	1310	
5°	1458	1313	1164	1313	1458	144
15°	1645	1246	771	1246	1645	444
25°	878	1108	559	1108	878	416
35°	432	914	412	914	432	277
45°	300	690	294	690	300	232
55°	208	468	206	468	208	183
65°	108	284	123	284	108	110
75°	57	135	66	135	57	61
85°	16	30	17	30	16	19
90°	35	1	35	1	35	16
95°	64	54	64	54	64	72
105°	230	223	230	223	230	242
115°	414	414	414	414	414	409
125°	605	603	605	603	605	539
135°	789	780	789	780	789	608
145°	957	947	957	947	957	598
155°	1091	1082	1091	1082	1091	502
165°	1179	1178	1179	1178	1179	332
175°	1221	1225	1221	1225	1221	116
180°	1227	1227	1227	1227	1227	



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1363.2	1364.2	1365.4	1362.8	1362.8	1360.6	1355.8	1352.3	1342.0	1340.6	1340.6
5°	1457.5	1456.5	1458.4	1452.5	1444.3	1442.4	1433.8	1422.5	1410.6	1397.4	1394.6
7.5°	1551.2	1549.9	1546.2	1545.2	1538.9	1525.2	1511.3	1496.5	1476.8	1457.6	1448.0
10°	1598.6	1613.6	1604.5	1588.6	1591.8	1570.4	1559.0	1539.4	1523.0	1494.3	1488.0
12.5°	1645.2	1651.1	1648.2	1639.1	1635.0	1620.2	1604.9	1587.9	1557.6	1531.9	1509.5
15°	1645.0	1653.7	1655.9	1653.2	1655.5	1654.6	1646.4	1632.3	1605.9	1577.6	1553.1
17.5°	1523.6	1529.6	1544.5	1554.6	1567.4	1594.3	1607.6	1612.7	1608.8	1592.8	1575.5
20°	1387.4	1377.3	1419.2	1440.6	1458.8	1504.3	1543.5	1558.5	1582.6	1582.2	1577.6
22.5°	1194.4	1196.8	1236.4	1261.9	1315.0	1360.5	1405.2	1461.7	1508.3	1539.2	1557.3
25°	877.6	894.9	934.5	969.1	1028.2	1112.9	1189.8	1279.1	1363.2	1429.7	1493.0
27.5°	659.1	660.4	691.8	723.7	758.8	828.2	925.1	1031.6	1151.6	1250.7	1364.7
30°	564.5	561.7	574.9	594.5	624.5	678.2	751.0	855.8	975.4	1124.7	1257.7
32.5°	497.4	497.6	507.6	522.0	547.0	583.2	633.0	718.1	831.3	978.0	1133.8
35°	432.4	431.9	439.3	449.7	460.2	483.4	517.5	562.1	640.0	776.9	936.3
37.5°	385.8	387.8	391.4	397.9	409.5	422.4	442.9	472.9	528.2	609.3	743.2
40°	359.6	360.5	365.5	371.0	377.8	387.8	404.7	428.7	469.3	534.0	631.8
42.5°	335.6	336.4	340.0	345.1	350.4	360.5	374.4	395.3	428.1	478.6	559.3
45°	300.4	300.4	303.6	305.9	311.8	320.9	332.3	349.6	372.4	409.7	463.3
47.5°	267.4	267.5	269.7	273.6	277.3	284.4	295.6	309.7	326.3	355.2	401.0
50°	248.5	249.0	250.3	253.5	255.8	262.2	270.8	283.1	300.4	322.7	361.0
52.5°	233.3	232.9	234.7	236.0	237.6	242.2	248.6	259.5	274.9	294.4	326.0
55°	208.5	206.6	209.4	211.7	213.0	214.8	218.5	225.3	238.5	254.9	278.6
57.5°	177.5	176.8	178.7	180.8	185.1	190.0	193.1	197.4	204.3	216.1	239.5
60°	152.0	152.0	156.1	157.5	162.5	168.9	175.2	178.9	185.7	193.4	210.7
62.5°	129.5	129.8	131.7	133.1	135.9	143.7	152.7	160.7	167.1	174.5	186.0
65°	108.3	109.2	109.2	110.1	112.0	113.8	117.4	123.8	135.2	145.6	154.3
67.5°	91.9	92.2	92.5	93.4	93.9	95.9	97.3	100.1	102.8	112.7	123.4
70°	81.1	82.4	81.9	82.8	83.3	84.2	86.1	87.4	91.5	93.8	100.1
72.5°	70.8	71.8	71.7	72.3	73.5	73.7	75.1	76.5	79.1	81.1	84.4
75°	57.3	56.9	57.3	58.2	58.7	59.2	59.2	61.0	62.3	64.2	66.4
77.5°	44.2	44.7	44.6	44.7	44.8	45.6	45.5	46.4	47.7	48.6	49.7
80°	35.5	35.9	35.5	35.9	36.4	36.8	36.4	36.8	38.3	39.1	39.1
82.5°	27.5	27.6	27.8	27.9	28.0	28.1	28.8	28.9	29.9	29.7	30.1
85°	16.4	16.0	16.0	16.0	16.4	16.9	16.4	16.4	16.9	16.9	16.9
87.5°	12.8	13.2	13.1	13.1	13.0	13.1	13.2	13.6	13.4	13.8	12.4
90°	35.2	35.0	34.8	34.5	34.3	34.4	34.9	35.3	35.8	36.3	31.2
92.5°	33.5	33.5	33.4	33.4	33.3	33.3	33.2	33.1	33.0	32.9	31.7
95°	64.2	64.6	65.2	65.6	66.1	66.3	66.3	66.3	66.3	66.3	65.8
97.5°	111.3	111.3	111.4	111.4	111.5	111.5	111.5	111.5	111.5	111.5	110.6
100°	141.9	142.1	142.4	142.6	142.9	142.9	142.9	142.9	142.9	142.9	142.2
102.5°	176.7	176.9	177.2	177.4	177.6	177.6	177.5	177.3	177.1	176.9	176.0
105°	230.0	230.0	230.0	230.0	230.0	229.7	229.3	228.8	228.4	227.8	227.4
107.5°	280.1	281.2	282.2	283.3	284.3	284.7	284.5	284.4	284.2	284.0	284.0
110°	319.1	319.7	320.4	321.1	321.8	322.2	322.2	322.2	322.2	322.2	322.2



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.3	356.9	357.3	357.8	358.4	358.9	359.4	360.0	360.5	361.1	361.2
115°	414.3	415.0	415.7	416.4	417.1	417.5	417.8	418.0	418.2	418.5	418.9
117.5°	469.7	470.3	471.0	471.7	472.4	473.1	473.6	474.1	474.7	475.2	476.5
120°	508.5	509.3	510.0	510.7	511.3	511.7	511.7	511.7	511.7	511.7	513.5
122.5°	546.7	547.2	547.7	548.2	548.8	549.2	549.8	550.4	550.9	551.4	552.8
125°	604.9	605.1	605.4	605.6	605.8	606.3	607.0	607.7	608.3	609.0	609.8
127.5°	657.9	658.7	659.4	660.1	660.8	661.6	662.5	663.3	664.1	664.9	665.8
130°	696.1	697.0	697.9	698.8	699.7	700.4	700.9	701.3	701.8	702.3	702.8
132.5°	732.5	733.3	734.0	734.8	735.5	736.4	737.4	738.3	739.4	740.4	740.3
135°	789.3	790.0	790.7	791.3	792.0	792.5	792.7	793.0	793.2	793.4	793.0
137.5°	840.6	841.6	842.5	843.4	844.4	844.9	845.1	845.3	845.4	845.6	845.0
140°	876.3	877.2	878.2	879.0	879.9	880.4	880.4	880.4	880.4	880.4	879.3
142.5°	908.6	909.5	910.4	911.3	912.3	912.7	912.5	912.3	912.1	912.0	911.2
145°	957.1	958.0	958.9	959.8	960.7	961.1	960.9	960.6	960.4	960.2	958.8
147.5°	1000.4	1001.2	1002.1	1003.0	1003.9	1004.1	1003.5	1003.1	1002.6	1002.0	1001.1
150°	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4	1030.6	1029.9	1029.2	1028.6	1027.6
152.5°	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5	1057.7	1056.9	1056.0	1055.1	1054.0
155°	1090.7	1091.4	1092.1	1092.8	1093.4	1093.2	1092.1	1090.9	1089.8	1088.6	1088.0
157.5°	1121.3	1122.5	1123.6	1124.6	1125.8	1125.5	1124.0	1122.4	1120.9	1119.3	1118.8
160°	1140.4	1141.3	1142.3	1143.2	1144.1	1143.9	1142.5	1141.1	1139.7	1138.4	1138.1
162.5°	1157.0	1158.1	1159.2	1160.3	1161.4	1161.2	1159.6	1158.1	1156.5	1154.9	1154.7
165°	1178.8	1179.9	1181.1	1182.2	1183.3	1183.1	1181.5	1179.9	1178.3	1176.7	1176.7
167.5°	1196.6	1197.7	1198.9	1200.2	1201.3	1201.1	1199.5	1197.9	1196.3	1194.7	1194.7
170°	1205.7	1207.0	1208.4	1209.8	1211.2	1211.0	1209.4	1207.8	1206.2	1204.6	1204.9
172.5°	1213.1	1214.5	1215.8	1217.3	1218.6	1218.5	1216.9	1215.3	1213.7	1212.1	1212.3
175°	1221.2	1222.6	1224.0	1225.4	1226.7	1226.6	1225.0	1223.4	1221.8	1220.1	1220.7
177.5°	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3	1228.2	1227.2	1226.0	1224.9	1225.3
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1341.3	1338.4	1335.9	1329.3	1326.1	1318.8	1317.7	1317.3	1307.8	1298.7	1296.2
5°	1387.4	1380.1	1369.1	1356.4	1343.2	1329.5	1320.4	1313.2	1294.9	1277.6	1267.7
7.5°	1433.8	1418.2	1399.3	1375.2	1355.0	1332.5	1315.7	1300.7	1274.9	1250.1	1233.4
10°	1468.4	1442.9	1417.9	1384.6	1358.7	1333.2	1309.6	1289.1	1259.9	1227.2	1203.9
12.5°	1489.9	1461.9	1427.4	1394.8	1361.3	1328.8	1297.2	1270.9	1236.6	1202.7	1175.2
15°	1518.9	1488.9	1447.0	1400.6	1357.4	1315.0	1278.6	1245.8	1201.2	1160.7	1127.0
17.5°	1542.7	1501.4	1456.3	1402.7	1352.6	1298.8	1251.9	1210.1	1160.4	1111.5	1071.8
20°	1550.3	1509.4	1457.5	1403.7	1344.6	1281.3	1230.8	1185.3	1132.0	1078.8	1033.2
22.5°	1545.6	1513.8	1456.0	1391.8	1331.1	1264.9	1207.8	1155.0	1096.0	1041.6	988.8
25°	1513.5	1502.5	1448.0	1377.8	1308.7	1231.7	1165.7	1107.9	1040.5	982.3	924.9
27.5°	1438.5	1462.1	1428.3	1353.6	1276.7	1194.2	1120.0	1054.2	984.3	918.7	861.6
30°	1366.5	1420.6	1406.0	1336.9	1250.8	1169.8	1086.5	1017.8	943.2	875.7	819.3
32.5°	1267.7	1357.3	1371.5	1313.6	1224.6	1135.6	1048.3	979.9	902.0	831.0	776.0
35°	1110.6	1244.5	1305.9	1269.0	1179.8	1083.8	993.6	914.0	835.7	765.6	711.0
37.5°	923.2	1105.5	1207.8	1210.5	1128.5	1028.7	930.6	851.5	771.3	702.5	643.5
40°	801.6	999.1	1132.5	1162.1	1092.9	985.0	885.7	805.2	726.9	659.5	591.7
42.5°	692.3	889.1	1053.1	1104.6	1049.5	942.4	842.8	758.6	682.5	618.8	549.5
45°	559.9	731.9	912.7	1004.6	974.1	874.9	769.7	689.6	618.1	563.0	496.6
47.5°	472.3	593.5	768.4	892.8	892.2	801.6	698.2	621.5	555.3	503.6	449.8
50°	422.4	528.0	675.9	817.1	828.8	752.9	654.5	578.5	516.7	462.4	419.2
52.5°	377.6	464.7	597.6	732.9	766.6	700.8	605.4	535.2	475.1	425.3	388.3
55°	319.1	386.5	487.5	614.0	665.0	618.6	534.0	468.4	419.6	377.8	345.9
57.5°	269.9	320.5	401.5	503.5	562.8	533.6	463.7	410.5	368.8	330.9	305.8
60°	239.0	280.4	349.1	434.3	499.8	479.3	419.6	370.1	334.6	301.8	278.1
62.5°	209.8	245.4	304.3	373.4	433.5	425.1	376.3	334.7	303.6	273.8	253.7
65°	168.9	194.8	240.8	295.0	343.2	347.3	312.3	284.0	256.3	232.6	214.8
67.5°	134.5	151.4	183.8	229.4	265.6	278.5	257.1	235.5	213.5	195.2	179.8
70°	113.3	127.0	150.7	187.5	220.8	234.4	222.1	205.3	186.2	171.1	157.9
72.5°	91.8	105.1	122.6	149.6	178.2	192.9	188.6	176.6	161.0	148.6	136.1
75°	69.2	73.3	85.2	103.3	125.6	138.4	141.6	135.2	122.9	113.3	106.0
77.5°	51.2	53.6	59.3	68.8	83.4	94.8	99.4	98.7	90.2	84.6	77.8
80°	40.9	42.4	45.0	49.1	60.1	71.4	74.6	74.6	68.8	66.4	59.7
82.5°	31.1	32.1	33.8	36.0	41.1	51.1	54.7	55.4	51.6	48.6	43.2
85°	17.7	17.3	18.2	19.5	20.5	23.2	28.7	29.6	28.7	25.1	23.6
87.5°	11.4	10.8	9.7	8.6	8.4	8.2	9.5	10.8	9.9	9.4	9.2
90°	26.1	21.0	16.0	12.1	9.4	6.6	3.8	1.1	3.8	6.6	9.4
92.5°	30.6	29.3	28.2	26.6	24.5	22.5	20.4	18.5	20.4	22.5	24.5
95°	65.4	64.9	64.5	63.0	60.7	58.5	56.2	53.9	56.2	58.5	60.7
97.5°	109.7	108.8	108.0	106.5	104.5	102.5	100.4	98.4	100.4	102.5	104.5
100°	141.5	140.9	140.2	138.9	137.1	135.3	133.4	131.5	133.4	135.3	137.1
102.5°	175.1	174.3	173.4	172.3	170.8	169.3	167.8	166.4	167.8	169.3	170.8
105°	226.9	226.5	226.0	225.4	224.8	224.1	223.4	222.7	223.4	224.1	224.8
107.5°	284.0	284.0	284.0	283.5	282.5	281.5	280.4	279.5	280.4	281.5	282.5
110°	322.2	322.2	322.2	321.5	320.0	318.7	317.3	315.9	317.3	318.7	320.0



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	361.4	361.6	361.9	361.2	359.8	358.5	357.0	355.7	357.0	358.5	359.8
115°	419.4	419.8	420.3	419.8	418.5	417.1	415.7	414.3	415.7	417.1	418.5
117.5°	477.8	479.1	480.4	480.1	478.2	476.4	474.6	472.7	474.6	476.4	478.2
120°	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7	513.5	515.4	517.2
122.5°	554.0	555.4	556.6	556.2	553.9	551.7	549.6	547.3	549.6	551.7	553.9
125°	610.5	611.1	611.8	611.1	609.0	607.0	604.9	602.8	604.9	607.0	609.0
127.5°	666.6	667.4	668.3	667.4	664.8	662.2	659.5	656.9	659.5	662.2	664.8
130°	703.2	703.6	704.1	702.8	699.8	696.9	693.8	690.9	693.8	696.9	699.8
132.5°	740.2	740.1	740.0	738.8	736.3	733.9	731.5	729.0	731.5	733.9	736.3
135°	792.5	792.0	791.6	790.1	787.6	785.1	782.5	780.0	782.5	785.1	787.6
137.5°	844.5	843.8	843.2	841.9	839.8	837.8	835.7	833.6	835.7	837.8	839.8
140°	878.2	877.0	875.8	874.2	872.2	870.0	868.0	865.9	868.0	870.0	872.2
142.5°	910.3	909.5	908.7	907.3	905.3	903.2	901.2	899.1	901.2	903.2	905.3
145°	957.4	956.0	954.7	953.1	951.5	949.9	948.3	946.7	948.3	949.9	951.5
147.5°	1000.2	999.3	998.4	996.9	995.0	993.0	991.1	989.2	991.1	993.0	995.0
150°	1026.7	1025.8	1024.8	1023.7	1022.3	1020.9	1019.6	1018.2	1019.6	1020.9	1022.3
152.5°	1052.8	1051.8	1050.6	1049.4	1048.0	1046.6	1045.3	1043.8	1045.3	1046.6	1048.0
155°	1087.3	1086.5	1085.8	1085.2	1084.5	1083.8	1083.1	1082.4	1083.1	1083.8	1084.5
157.5°	1118.5	1118.0	1117.6	1117.2	1116.7	1116.2	1115.8	1115.4	1115.8	1116.2	1116.7
160°	1137.9	1137.6	1137.4	1137.1	1136.6	1136.1	1135.7	1135.2	1135.7	1136.1	1136.6
162.5°	1154.4	1154.2	1154.0	1153.9	1153.7	1153.6	1153.5	1153.4	1153.5	1153.6	1153.7
165°	1176.7	1176.7	1176.7	1176.8	1177.0	1177.2	1177.5	1177.7	1177.5	1177.2	1177.0
167.5°	1194.8	1194.8	1194.9	1195.2	1196.0	1196.6	1197.3	1198.0	1197.3	1196.6	1196.0
170°	1205.1	1205.3	1205.6	1206.0	1206.7	1207.4	1208.1	1208.8	1208.1	1207.4	1206.7
172.5°	1212.5	1212.8	1213.0	1213.4	1214.2	1214.9	1215.6	1216.2	1215.6	1214.9	1214.2
175°	1221.1	1221.6	1222.0	1222.6	1223.2	1224.0	1224.7	1225.4	1224.7	1224.0	1223.2
177.5°	1225.7	1226.0	1226.4	1226.9	1227.4	1228.0	1228.5	1229.0	1228.5	1228.0	1227.4
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1291.5	1288.9	1284.2	1276.8	1272.5	1264.8	1259.7	1262.7	1263.4	1262.7	1261.9
5°	1256.8	1247.1	1233.9	1221.2	1209.4	1196.7	1189.4	1186.2	1179.8	1176.2	1174.4
7.5°	1214.8	1198.3	1179.6	1157.4	1138.5	1118.8	1108.8	1103.7	1090.7	1083.6	1077.4
10°	1183.5	1157.5	1138.9	1109.7	1092.0	1066.0	1048.3	1048.7	1031.0	1020.9	1013.7
12.5°	1148.9	1120.3	1089.3	1063.1	1038.4	1017.6	996.2	987.6	968.7	959.0	939.4
15°	1091.5	1058.3	1025.6	990.0	965.0	932.6	901.7	863.9	833.4	807.0	799.8
17.5°	1028.9	987.7	954.8	913.2	870.3	815.9	780.1	758.1	739.8	725.9	715.4
20°	985.9	944.1	909.0	846.1	788.4	751.5	725.1	708.3	689.1	674.1	665.9
22.5°	940.8	897.1	849.3	779.2	734.1	704.5	681.0	661.6	648.7	636.9	629.5
25°	876.6	828.8	750.1	701.9	665.5	634.5	618.1	606.3	592.6	576.7	569.4
27.5°	809.0	732.9	676.4	640.5	605.7	585.6	570.9	553.2	541.0	533.9	526.3
30°	758.3	682.3	638.2	599.1	574.4	552.1	534.8	524.9	513.0	500.7	495.7
32.5°	701.9	641.1	598.9	566.2	541.3	522.3	508.6	492.4	483.8	476.3	465.8
35°	631.8	585.9	547.2	520.8	497.0	481.6	465.7	456.1	440.6	434.3	430.2
37.5°	572.4	532.5	503.7	475.8	457.1	440.0	430.3	415.0	408.3	399.5	390.8
40°	539.0	499.8	472.0	449.2	428.3	415.5	403.3	391.0	380.9	376.9	366.4
42.5°	504.7	472.9	445.1	420.1	406.1	392.6	377.1	368.1	357.7	351.1	344.6
45°	457.4	429.3	405.6	385.0	369.6	355.5	345.4	330.5	324.6	311.3	305.9
47.5°	416.0	389.7	367.1	347.7	332.5	323.3	308.7	296.9	287.5	279.4	272.4
50°	386.5	364.6	342.8	325.5	311.8	298.6	283.6	277.7	263.1	259.0	254.9
52.5°	359.5	338.8	318.7	301.8	288.1	275.3	262.1	254.3	244.5	240.4	237.5
55°	321.8	301.8	282.7	267.6	254.0	240.8	232.6	223.0	218.5	215.3	211.7
57.5°	283.9	265.9	251.3	236.0	222.3	211.9	202.3	196.6	191.9	187.7	183.3
60°	259.9	242.6	229.4	215.3	201.2	192.5	185.3	178.4	173.0	166.6	164.8
62.5°	234.4	219.3	207.2	193.4	181.2	173.3	166.3	159.9	153.3	144.0	141.4
65°	199.4	187.5	174.8	163.5	152.5	144.7	134.7	127.4	124.8	123.8	123.3
67.5°	167.7	156.5	145.5	133.9	123.9	116.8	111.7	110.6	108.7	108.2	106.9
70°	146.6	136.1	125.2	114.2	104.7	103.3	101.5	99.7	97.4	96.5	95.6
72.5°	127.6	116.8	105.8	97.1	93.0	91.3	89.5	87.7	86.1	85.2	84.6
75°	97.8	87.8	80.6	77.4	75.1	73.7	71.0	69.6	68.8	67.3	66.9
77.5°	70.4	64.8	61.4	59.5	57.1	55.6	54.0	52.7	51.7	51.5	50.7
80°	53.7	51.0	48.7	46.0	45.0	43.2	42.8	41.5	41.9	40.5	40.5
82.5°	41.7	38.3	36.3	35.0	34.2	32.7	32.2	31.6	31.7	30.7	30.7
85°	21.4	20.5	19.5	18.6	18.6	17.3	17.7	17.3	17.3	16.4	16.0
87.5°	9.4	9.7	10.1	11.1	12.0	12.8	12.7	12.1	12.0	11.9	11.6
90°	12.1	16.0	21.0	26.1	31.2	36.3	35.8	35.3	34.9	34.4	34.3
92.5°	26.6	28.2	29.3	30.6	31.7	32.9	33.0	33.1	33.2	33.3	33.3
95°	63.0	64.5	64.9	65.4	65.8	66.3	66.3	66.3	66.3	66.3	66.1
97.5°	106.5	108.0	108.8	109.7	110.6	111.5	111.5	111.5	111.5	111.5	111.5
100°	138.9	140.2	140.9	141.5	142.2	142.9	142.9	142.9	142.9	142.9	142.9
102.5°	172.3	173.4	174.3	175.1	176.0	176.9	177.1	177.3	177.5	177.6	177.6
105°	225.4	226.0	226.5	226.9	227.4	227.8	228.4	228.8	229.3	229.7	230.0
107.5°	283.5	284.0	284.0	284.0	284.0	284.0	284.2	284.4	284.5	284.7	284.3
110°	321.5	322.2	322.2	322.2	322.2	322.2	322.2	322.2	322.2	322.2	321.8



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	361.2	361.9	361.6	361.4	361.2	361.1	360.5	360.0	359.4	358.9	358.4
115°	419.8	420.3	419.8	419.4	418.9	418.5	418.2	418.0	417.8	417.5	417.1
117.5°	480.1	480.4	479.1	477.8	476.5	475.2	474.7	474.1	473.6	473.1	472.4
120°	519.1	519.1	517.2	515.4	513.5	511.7	511.7	511.7	511.7	511.7	511.3
122.5°	556.2	556.6	555.4	554.0	552.8	551.4	550.9	550.4	549.8	549.2	548.8
125°	611.1	611.8	611.1	610.5	609.8	609.0	608.3	607.7	607.0	606.3	605.8
127.5°	667.4	668.3	667.4	666.6	665.8	664.9	664.1	663.3	662.5	661.6	660.8
130°	702.8	704.1	703.6	703.2	702.8	702.3	701.8	701.3	700.9	700.4	699.7
132.5°	738.8	740.0	740.1	740.2	740.3	740.4	739.4	738.3	737.4	736.4	735.5
135°	790.1	791.6	792.0	792.5	793.0	793.4	793.2	793.0	792.7	792.5	792.0
137.5°	841.9	843.2	843.8	844.5	845.0	845.6	845.4	845.3	845.1	844.9	844.4
140°	874.2	875.8	877.0	878.2	879.3	880.4	880.4	880.4	880.4	880.4	879.9
142.5°	907.3	908.7	909.5	910.3	911.2	912.0	912.1	912.3	912.5	912.7	912.3
145°	953.1	954.7	956.0	957.4	958.8	960.2	960.4	960.6	960.9	961.1	960.7
147.5°	996.9	998.4	999.3	1000.2	1001.1	1002.0	1002.6	1003.1	1003.5	1004.1	1003.9
150°	1023.7	1024.8	1025.8	1026.7	1027.6	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4
152.5°	1049.4	1050.6	1051.8	1052.8	1054.0	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5
155°	1085.2	1085.8	1086.5	1087.3	1088.0	1088.6	1089.8	1090.9	1092.1	1093.2	1093.4
157.5°	1117.2	1117.6	1118.0	1118.5	1118.8	1119.3	1120.9	1122.4	1124.0	1125.5	1125.8
160°	1137.1	1137.4	1137.6	1137.9	1138.1	1138.4	1139.7	1141.1	1142.5	1143.9	1144.1
162.5°	1153.9	1154.0	1154.2	1154.4	1154.7	1154.9	1156.5	1158.1	1159.6	1161.2	1161.4
165°	1176.8	1176.7	1176.7	1176.7	1176.7	1176.7	1178.3	1179.9	1181.5	1183.1	1183.3
167.5°	1195.2	1194.9	1194.8	1194.8	1194.7	1194.7	1196.3	1197.9	1199.5	1201.1	1201.3
170°	1206.0	1205.6	1205.3	1205.1	1204.9	1204.6	1206.2	1207.8	1209.4	1211.0	1211.2
172.5°	1213.4	1213.0	1212.8	1212.5	1212.3	1212.1	1213.7	1215.3	1216.9	1218.5	1218.6
175°	1222.6	1222.0	1221.6	1221.1	1220.7	1220.1	1221.8	1223.4	1225.0	1226.6	1226.7
177.5°	1226.9	1226.4	1226.0	1225.7	1225.3	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1257.9	1258.6	1257.6	1258.3	1257.6	1258.6	1257.9	1261.9	1262.7	1263.4	1262.7
5°	1172.1	1166.6	1165.7	1164.3	1165.7	1166.6	1172.1	1174.4	1176.2	1179.8	1186.2
7.5°	1069.6	1068.7	1066.5	1063.3	1066.5	1068.7	1069.6	1077.4	1083.6	1090.7	1103.7
10°	1003.6	1001.4	1000.9	997.7	1000.9	1001.4	1003.6	1013.7	1020.9	1031.0	1048.7
12.5°	926.5	911.8	910.3	902.3	910.3	911.8	926.5	939.4	959.0	968.7	987.6
15°	788.8	786.1	776.9	771.1	776.9	786.1	788.8	799.8	807.0	833.4	863.9
17.5°	710.2	701.2	698.4	697.1	698.4	701.2	710.2	715.4	725.9	739.8	758.1
20°	659.5	651.4	650.0	649.1	650.0	651.4	659.5	665.9	674.1	689.1	708.3
22.5°	624.6	616.0	612.5	609.8	612.5	616.0	624.6	629.5	636.9	648.7	661.6
25°	564.9	561.7	559.9	558.9	559.9	561.7	564.9	569.4	576.7	592.6	606.3
27.5°	518.2	511.1	509.8	507.5	509.8	511.1	518.2	526.3	533.9	541.0	553.2
30°	491.6	489.3	486.2	483.4	486.2	489.3	491.6	495.7	500.7	513.0	524.9
32.5°	460.3	458.3	455.6	454.2	455.6	458.3	460.3	465.8	476.3	483.8	492.4
35°	425.6	419.2	416.5	412.4	416.5	419.2	425.6	430.2	434.3	440.6	456.1
37.5°	388.9	385.6	381.7	383.1	381.7	385.6	388.9	390.8	399.5	408.3	415.0
40°	360.5	358.2	357.3	356.9	357.3	358.2	360.5	366.4	376.9	380.9	391.0
42.5°	338.0	331.6	329.3	329.2	329.3	331.6	338.0	344.6	351.1	357.7	368.1
45°	303.6	297.7	293.6	294.1	293.6	297.7	303.6	305.9	311.3	324.6	330.5
47.5°	268.5	268.3	265.7	266.5	265.7	268.3	268.5	272.4	279.4	287.5	296.9
50°	251.7	249.0	247.2	247.6	247.2	249.0	251.7	254.9	259.0	263.1	277.7
52.5°	235.7	233.4	231.8	233.8	231.8	233.4	235.7	237.5	240.4	244.5	254.3
55°	209.4	206.6	206.2	205.7	206.2	206.6	209.4	211.7	215.3	218.5	223.0
57.5°	179.9	178.2	175.4	174.2	175.4	178.2	179.9	183.3	187.7	191.9	196.6
60°	158.8	155.2	150.7	150.2	150.7	155.2	158.8	164.8	166.6	173.0	178.4
62.5°	139.6	138.8	137.9	137.9	137.9	138.8	139.6	141.4	144.0	153.3	159.9
65°	122.4	122.0	122.4	122.9	122.4	122.0	122.4	123.3	123.8	124.8	127.4
67.5°	106.7	105.8	105.0	105.4	105.0	105.8	106.7	106.9	108.2	108.7	110.6
70°	94.7	94.3	93.8	93.8	93.8	94.3	94.7	95.6	96.5	97.4	99.7
72.5°	83.0	82.9	82.5	82.1	82.5	82.9	83.0	84.6	85.2	86.1	87.7
75°	66.4	65.5	65.5	65.5	65.5	65.5	66.4	66.9	67.3	68.8	69.6
77.5°	50.6	50.2	49.7	49.3	49.7	50.2	50.6	50.7	51.5	51.7	52.7
80°	40.0	39.6	39.1	39.1	39.1	39.6	40.0	40.5	40.5	41.9	41.5
82.5°	30.6	30.1	30.1	29.7	30.1	30.1	30.6	30.7	30.7	31.7	31.6
85°	16.4	16.9	16.4	17.3	16.4	16.9	16.4	16.0	16.4	17.3	17.3
87.5°	11.7	11.3	11.8	11.4	11.8	11.3	11.7	11.6	11.9	12.0	12.1
90°	34.5	34.8	35.0	35.2	35.0	34.8	34.5	34.3	34.4	34.9	35.3
92.5°	33.4	33.4	33.5	33.5	33.5	33.4	33.4	33.3	33.3	33.2	33.1
95°	65.6	65.2	64.6	64.2	64.6	65.2	65.6	66.1	66.3	66.3	66.3
97.5°	111.4	111.4	111.3	111.3	111.3	111.4	111.4	111.5	111.5	111.5	111.5
100°	142.6	142.4	142.1	141.9	142.1	142.4	142.6	142.9	142.9	142.9	142.9
102.5°	177.4	177.2	176.9	176.7	176.9	177.2	177.4	177.6	177.6	177.5	177.3
105°	230.0	230.0	230.0	230.0	230.0	230.0	230.0	230.0	229.7	229.3	228.8
107.5°	283.3	282.2	281.2	280.1	281.2	282.2	283.3	284.3	284.7	284.5	284.4
110°	321.1	320.4	319.7	319.1	319.7	320.4	321.1	321.8	322.2	322.2	322.2



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	357.8	357.3	356.9	356.3	356.9	357.3	357.8	358.4	358.9	359.4	360.0
115°	416.4	415.7	415.0	414.3	415.0	415.7	416.4	417.1	417.5	417.8	418.0
117.5°	471.7	471.0	470.3	469.7	470.3	471.0	471.7	472.4	473.1	473.6	474.1
120°	510.7	510.0	509.3	508.5	509.3	510.0	510.7	511.3	511.7	511.7	511.7
122.5°	548.2	547.7	547.2	546.7	547.2	547.7	548.2	548.8	549.2	549.8	550.4
125°	605.6	605.4	605.1	604.9	605.1	605.4	605.6	605.8	606.3	607.0	607.7
127.5°	660.1	659.4	658.7	657.9	658.7	659.4	660.1	660.8	661.6	662.5	663.3
130°	698.8	697.9	697.0	696.1	697.0	697.9	698.8	699.7	700.4	700.9	701.3
132.5°	734.8	734.0	733.3	732.5	733.3	734.0	734.8	735.5	736.4	737.4	738.3
135°	791.3	790.7	790.0	789.3	790.0	790.7	791.3	792.0	792.5	792.7	793.0
137.5°	843.4	842.5	841.6	840.6	841.6	842.5	843.4	844.4	844.9	845.1	845.3
140°	879.0	878.2	877.2	876.3	877.2	878.2	879.0	879.9	880.4	880.4	880.4
142.5°	911.3	910.4	909.5	908.6	909.5	910.4	911.3	912.3	912.7	912.5	912.3
145°	959.8	958.9	958.0	957.1	958.0	958.9	959.8	960.7	961.1	960.9	960.6
147.5°	1003.0	1002.1	1001.2	1000.4	1001.2	1002.1	1003.0	1003.9	1004.1	1003.5	1003.1
150°	1030.6	1029.9	1029.2	1028.6	1029.2	1029.9	1030.6	1031.4	1031.4	1030.6	1029.9
152.5°	1057.7	1056.9	1056.0	1055.1	1056.0	1056.9	1057.7	1058.5	1058.5	1057.7	1056.9
155°	1092.8	1092.1	1091.4	1090.7	1091.4	1092.1	1092.8	1093.4	1093.2	1092.1	1090.9
157.5°	1124.6	1123.6	1122.5	1121.3	1122.5	1123.6	1124.6	1125.8	1125.5	1124.0	1122.4
160°	1143.2	1142.3	1141.3	1140.4	1141.3	1142.3	1143.2	1144.1	1143.9	1142.5	1141.1
162.5°	1160.3	1159.2	1158.1	1157.0	1158.1	1159.2	1160.3	1161.4	1161.2	1159.6	1158.1
165°	1182.2	1181.1	1179.9	1178.8	1179.9	1181.1	1182.2	1183.3	1183.1	1181.5	1179.9
167.5°	1200.2	1198.9	1197.7	1196.6	1197.7	1198.9	1200.2	1201.3	1201.1	1199.5	1197.9
170°	1209.8	1208.4	1207.0	1205.7	1207.0	1208.4	1209.8	1211.2	1211.0	1209.4	1207.8
172.5°	1217.3	1215.8	1214.5	1213.1	1214.5	1215.8	1217.3	1218.6	1218.5	1216.9	1215.3
175°	1225.4	1224.0	1222.6	1221.2	1222.6	1224.0	1225.4	1226.7	1226.6	1225.0	1223.4
177.5°	1228.2	1227.2	1226.0	1224.9	1226.0	1227.2	1228.2	1229.3	1229.3	1228.2	1227.2
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1259.7	1264.8	1272.5	1276.8	1284.2	1288.9	1291.5	1296.2	1298.7	1307.8	1317.3
5°	1189.4	1196.7	1209.4	1221.2	1233.9	1247.1	1256.8	1267.7	1277.6	1294.9	1313.2
7.5°	1108.8	1118.8	1138.5	1157.4	1179.6	1198.3	1214.8	1233.4	1250.1	1274.9	1300.7
10°	1048.3	1066.0	1092.0	1109.7	1138.9	1157.5	1183.5	1203.9	1227.2	1259.9	1289.1
12.5°	996.2	1017.6	1038.4	1063.1	1089.3	1120.3	1148.9	1175.2	1202.7	1236.6	1270.9
15°	901.7	932.6	965.0	990.0	1025.6	1058.3	1091.5	1127.0	1160.7	1201.2	1245.8
17.5°	780.1	815.9	870.3	913.2	954.8	987.7	1028.9	1071.8	1111.5	1160.4	1210.1
20°	725.1	751.5	788.4	846.1	909.0	944.1	985.9	1033.2	1078.8	1132.0	1185.3
22.5°	681.0	704.5	734.1	779.2	849.3	897.1	940.8	988.8	1041.6	1096.0	1155.0
25°	618.1	634.5	665.5	701.9	750.1	828.8	876.6	924.9	982.3	1040.5	1107.9
27.5°	570.9	585.6	605.7	640.5	676.4	732.9	809.0	861.6	918.7	984.3	1054.2
30°	534.8	552.1	574.4	599.1	638.2	682.3	758.3	819.3	875.7	943.2	1017.8
32.5°	508.6	522.3	541.3	566.2	598.9	641.1	701.9	776.0	831.0	902.0	979.9
35°	465.7	481.6	497.0	520.8	547.2	585.9	631.8	711.0	765.6	835.7	914.0
37.5°	430.3	440.0	457.1	475.8	503.7	532.5	572.4	643.5	702.5	771.3	851.5
40°	403.3	415.5	428.3	449.2	472.0	499.8	539.0	591.7	659.5	726.9	805.2
42.5°	377.1	392.6	406.1	420.1	445.1	472.9	504.7	549.5	618.8	682.5	758.6
45°	345.4	355.5	369.6	385.0	405.6	429.3	457.4	496.6	563.0	618.1	689.6
47.5°	308.7	323.3	332.5	347.7	367.1	389.7	416.0	449.8	503.6	555.3	621.5
50°	283.6	298.6	311.8	325.5	342.8	364.6	386.5	419.2	462.4	516.7	578.5
52.5°	262.1	275.3	288.1	301.8	318.7	338.8	359.5	388.3	425.3	475.1	535.2
55°	232.6	240.8	254.0	267.6	282.7	301.8	321.8	345.9	377.8	419.6	468.4
57.5°	202.3	211.9	222.3	236.0	251.3	265.9	283.9	305.8	330.9	368.8	410.5
60°	185.3	192.5	201.2	215.3	229.4	242.6	259.9	278.1	301.8	334.6	370.1
62.5°	166.3	173.3	181.2	193.4	207.2	219.3	234.4	253.7	273.8	303.6	334.7
65°	134.7	144.7	152.5	163.5	174.8	187.5	199.4	214.8	232.6	256.3	284.0
67.5°	111.7	116.8	123.9	133.9	145.5	156.5	167.7	179.8	195.2	213.5	235.5
70°	101.5	103.3	104.7	114.2	125.2	136.1	146.6	157.9	171.1	186.2	205.3
72.5°	89.5	91.3	93.0	97.1	105.8	116.8	127.6	136.1	148.6	161.0	176.6
75°	71.0	73.7	75.1	77.4	80.6	87.8	97.8	106.0	113.3	122.9	135.2
77.5°	54.0	55.6	57.1	59.5	61.4	64.8	70.4	77.8	84.6	90.2	98.7
80°	42.8	43.2	45.0	46.0	48.7	51.0	53.7	59.7	66.4	68.8	74.6
82.5°	32.2	32.7	34.2	35.0	36.3	38.3	41.7	43.2	48.6	51.6	55.4
85°	17.7	17.3	18.6	18.6	19.5	20.5	21.4	23.6	25.1	28.7	29.6
87.5°	12.7	12.8	12.0	11.1	10.1	9.7	9.4	9.2	9.4	9.9	10.8
90°	35.8	36.3	31.2	26.1	21.0	16.0	12.1	9.4	6.6	3.8	1.1
92.5°	33.0	32.9	31.7	30.6	29.3	28.2	26.6	24.5	22.5	20.4	18.5
95°	66.3	66.3	65.8	65.4	64.9	64.5	63.0	60.7	58.5	56.2	53.9
97.5°	111.5	111.5	110.6	109.7	108.8	108.0	106.5	104.5	102.5	100.4	98.4
100°	142.9	142.9	142.2	141.5	140.9	140.2	138.9	137.1	135.3	133.4	131.5
102.5°	177.1	176.9	176.0	175.1	174.3	173.4	172.3	170.8	169.3	167.8	166.4
105°	228.4	227.8	227.4	226.9	226.5	226.0	225.4	224.8	224.1	223.4	222.7
107.5°	284.2	284.0	284.0	284.0	284.0	284.0	283.5	282.5	281.5	280.4	279.5
110°	322.2	322.2	322.2	322.2	322.2	322.2	321.5	320.0	318.7	317.3	315.9



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	360.5	361.1	361.2	361.4	361.6	361.9	361.2	359.8	358.5	357.0	355.7
115°	418.2	418.5	418.9	419.4	419.8	420.3	419.8	418.5	417.1	415.7	414.3
117.5°	474.7	475.2	476.5	477.8	479.1	480.4	480.1	478.2	476.4	474.6	472.7
120°	511.7	511.7	513.5	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7
122.5°	550.9	551.4	552.8	554.0	555.4	556.6	556.2	553.9	551.7	549.6	547.3
125°	608.3	609.0	609.8	610.5	611.1	611.8	611.1	609.0	607.0	604.9	602.8
127.5°	664.1	664.9	665.8	666.6	667.4	668.3	667.4	664.8	662.2	659.5	656.9
130°	701.8	702.3	702.8	703.2	703.6	704.1	702.8	699.8	696.9	693.8	690.9
132.5°	739.4	740.4	740.3	740.2	740.1	740.0	738.8	736.3	733.9	731.5	729.0
135°	793.2	793.4	793.0	792.5	792.0	791.6	790.1	787.6	785.1	782.5	780.0
137.5°	845.4	845.6	845.0	844.5	843.8	843.2	841.9	839.8	837.8	835.7	833.6
140°	880.4	880.4	879.3	878.2	877.0	875.8	874.2	872.2	870.0	868.0	865.9
142.5°	912.1	912.0	911.2	910.3	909.5	908.7	907.3	905.3	903.2	901.2	899.1
145°	960.4	960.2	958.8	957.4	956.0	954.7	953.1	951.5	949.9	948.3	946.7
147.5°	1002.6	1002.0	1001.1	1000.2	999.3	998.4	996.9	995.0	993.0	991.1	989.2
150°	1029.2	1028.6	1027.6	1026.7	1025.8	1024.8	1023.7	1022.3	1020.9	1019.6	1018.2
152.5°	1056.0	1055.1	1054.0	1052.8	1051.8	1050.6	1049.4	1048.0	1046.6	1045.3	1043.8
155°	1089.8	1088.6	1088.0	1087.3	1086.5	1085.8	1085.2	1084.5	1083.8	1083.1	1082.4
157.5°	1120.9	1119.3	1118.8	1118.5	1118.0	1117.6	1117.2	1116.7	1116.2	1115.8	1115.4
160°	1139.7	1138.4	1138.1	1137.9	1137.6	1137.4	1137.1	1136.6	1136.1	1135.7	1135.2
162.5°	1156.5	1154.9	1154.7	1154.4	1154.2	1154.0	1153.9	1153.7	1153.6	1153.5	1153.4
165°	1178.3	1176.7	1176.7	1176.7	1176.7	1176.7	1176.8	1177.0	1177.2	1177.5	1177.7
167.5°	1196.3	1194.7	1194.7	1194.8	1194.8	1194.9	1195.2	1196.0	1196.6	1197.3	1198.0
170°	1206.2	1204.6	1204.9	1205.1	1205.3	1205.6	1206.0	1206.7	1207.4	1208.1	1208.8
172.5°	1213.7	1212.1	1212.3	1212.5	1212.8	1213.0	1213.4	1214.2	1214.9	1215.6	1216.2
175°	1221.8	1220.1	1220.7	1221.1	1221.6	1222.0	1222.6	1223.2	1224.0	1224.7	1225.4
177.5°	1226.0	1224.9	1225.3	1225.7	1226.0	1226.4	1226.9	1227.4	1228.0	1228.5	1229.0
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1317.7	1318.8	1326.1	1329.3	1335.9	1338.4	1341.3	1340.6	1340.6	1342.0	1352.3
5°	1320.4	1329.5	1343.2	1356.4	1369.1	1380.1	1387.4	1394.6	1397.4	1410.6	1422.5
7.5°	1315.7	1332.5	1355.0	1375.2	1399.3	1418.2	1433.8	1448.0	1457.6	1476.8	1496.5
10°	1309.6	1333.2	1358.7	1384.6	1417.9	1442.9	1468.4	1488.0	1494.3	1523.0	1539.4
12.5°	1297.2	1328.8	1361.3	1394.8	1427.4	1461.9	1489.9	1509.5	1531.9	1557.6	1587.9
15°	1278.6	1315.0	1357.4	1400.6	1447.0	1488.9	1518.9	1553.1	1577.6	1605.9	1632.3
17.5°	1251.9	1298.8	1352.6	1402.7	1456.3	1501.4	1542.7	1575.5	1592.8	1608.8	1612.7
20°	1230.8	1281.3	1344.6	1403.7	1457.5	1509.4	1550.3	1577.6	1582.2	1582.6	1558.5
22.5°	1207.8	1264.9	1331.1	1391.8	1456.0	1513.8	1545.6	1557.3	1539.2	1508.3	1461.7
25°	1165.7	1231.7	1308.7	1377.8	1448.0	1502.5	1513.5	1493.0	1429.7	1363.2	1279.1
27.5°	1120.0	1194.2	1276.7	1353.6	1428.3	1462.1	1438.5	1364.7	1250.7	1151.6	1031.6
30°	1086.5	1169.8	1250.8	1336.9	1406.0	1420.6	1366.5	1257.7	1124.7	975.4	855.8
32.5°	1048.3	1135.6	1224.6	1313.6	1371.5	1357.3	1267.7	1133.8	978.0	831.3	718.1
35°	993.6	1083.8	1179.8	1269.0	1305.9	1244.5	1110.6	936.3	776.9	640.0	562.1
37.5°	930.6	1028.7	1128.5	1210.5	1207.8	1105.5	923.2	743.2	609.3	528.2	472.9
40°	885.7	985.0	1092.9	1162.1	1132.5	999.1	801.6	631.8	534.0	469.3	428.7
42.5°	842.8	942.4	1049.5	1104.6	1053.1	889.1	692.3	559.3	478.6	428.1	395.3
45°	769.7	874.9	974.1	1004.6	912.7	731.9	559.9	463.3	409.7	372.4	349.6
47.5°	698.2	801.6	892.2	892.8	768.4	593.5	472.3	401.0	355.2	326.3	309.7
50°	654.5	752.9	828.8	817.1	675.9	528.0	422.4	361.0	322.7	300.4	283.1
52.5°	605.4	700.8	766.6	732.9	597.6	464.7	377.6	326.0	294.4	274.9	259.5
55°	534.0	618.6	665.0	614.0	487.5	386.5	319.1	278.6	254.9	238.5	225.3
57.5°	463.7	533.6	562.8	503.5	401.5	320.5	269.9	239.5	216.1	204.3	197.4
60°	419.6	479.3	499.8	434.3	349.1	280.4	239.0	210.7	193.4	185.7	178.9
62.5°	376.3	425.1	433.5	373.4	304.3	245.4	209.8	186.0	174.5	167.1	160.7
65°	312.3	347.3	343.2	295.0	240.8	194.8	168.9	154.3	145.6	135.2	123.8
67.5°	257.1	278.5	265.6	229.4	183.8	151.4	134.5	123.4	112.7	102.8	100.1
70°	222.1	234.4	220.8	187.5	150.7	127.0	113.3	100.1	93.8	91.5	87.4
72.5°	188.6	192.9	178.2	149.6	122.6	105.1	91.8	84.4	81.1	79.1	76.5
75°	141.6	138.4	125.6	103.3	85.2	73.3	69.2	66.4	64.2	62.3	61.0
77.5°	99.4	94.8	83.4	68.8	59.3	53.6	51.2	49.7	48.6	47.7	46.4
80°	74.6	71.4	60.1	49.1	45.0	42.4	40.9	39.1	39.1	38.3	36.8
82.5°	54.7	51.1	41.1	36.0	33.8	32.1	31.1	30.1	29.7	29.9	28.9
85°	28.7	23.2	20.5	19.5	18.2	17.3	17.7	16.9	16.9	16.9	16.4
87.5°	9.5	8.2	8.4	8.6	9.7	10.8	11.4	12.4	13.8	13.4	13.6
90°	3.8	6.6	9.4	12.1	16.0	21.0	26.1	31.2	36.3	35.8	35.3
92.5°	20.4	22.5	24.5	26.6	28.2	29.3	30.6	31.7	32.9	33.0	33.1
95°	56.2	58.5	60.7	63.0	64.5	64.9	65.4	65.8	66.3	66.3	66.3
97.5°	100.4	102.5	104.5	106.5	108.0	108.8	109.7	110.6	111.5	111.5	111.5
100°	133.4	135.3	137.1	138.9	140.2	140.9	141.5	142.2	142.9	142.9	142.9
102.5°	167.8	169.3	170.8	172.3	173.4	174.3	175.1	176.0	176.9	177.1	177.3
105°	223.4	224.1	224.8	225.4	226.0	226.5	226.9	227.4	227.8	228.4	228.8
107.5°	280.4	281.5	282.5	283.5	284.0	284.0	284.0	284.0	284.0	284.2	284.4
110°	317.3	318.7	320.0	321.5	322.2	322.2	322.2	322.2	322.2	322.2	322.2



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	357.0	358.5	359.8	361.2	361.9	361.6	361.4	361.2	361.1	360.5	360.0
115°	415.7	417.1	418.5	419.8	420.3	419.8	419.4	418.9	418.5	418.2	418.0
117.5°	474.6	476.4	478.2	480.1	480.4	479.1	477.8	476.5	475.2	474.7	474.1
120°	513.5	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7	511.7	511.7
122.5°	549.6	551.7	553.9	556.2	556.6	555.4	554.0	552.8	551.4	550.9	550.4
125°	604.9	607.0	609.0	611.1	611.8	611.1	610.5	609.8	609.0	608.3	607.7
127.5°	659.5	662.2	664.8	667.4	668.3	667.4	666.6	665.8	664.9	664.1	663.3
130°	693.8	696.9	699.8	702.8	704.1	703.6	703.2	702.8	702.3	701.8	701.3
132.5°	731.5	733.9	736.3	738.8	740.0	740.1	740.2	740.3	740.4	739.4	738.3
135°	782.5	785.1	787.6	790.1	791.6	792.0	792.5	793.0	793.4	793.2	793.0
137.5°	835.7	837.8	839.8	841.9	843.2	843.8	844.5	845.0	845.6	845.4	845.3
140°	868.0	870.0	872.2	874.2	875.8	877.0	878.2	879.3	880.4	880.4	880.4
142.5°	901.2	903.2	905.3	907.3	908.7	909.5	910.3	911.2	912.0	912.1	912.3
145°	948.3	949.9	951.5	953.1	954.7	956.0	957.4	958.8	960.2	960.4	960.6
147.5°	991.1	993.0	995.0	996.9	998.4	999.3	1000.2	1001.1	1002.0	1002.6	1003.1
150°	1019.6	1020.9	1022.3	1023.7	1024.8	1025.8	1026.7	1027.6	1028.6	1029.2	1029.9
152.5°	1045.3	1046.6	1048.0	1049.4	1050.6	1051.8	1052.8	1054.0	1055.1	1056.0	1056.9
155°	1083.1	1083.8	1084.5	1085.2	1085.8	1086.5	1087.3	1088.0	1088.6	1089.8	1090.9
157.5°	1115.8	1116.2	1116.7	1117.2	1117.6	1118.0	1118.5	1118.8	1119.3	1120.9	1122.4
160°	1135.7	1136.1	1136.6	1137.1	1137.4	1137.6	1137.9	1138.1	1138.4	1139.7	1141.1
162.5°	1153.5	1153.6	1153.7	1153.9	1154.0	1154.2	1154.4	1154.7	1154.9	1156.5	1158.1
165°	1177.5	1177.2	1177.0	1176.8	1176.7	1176.7	1176.7	1176.7	1176.7	1178.3	1179.9
167.5°	1197.3	1196.6	1196.0	1195.2	1194.9	1194.8	1194.8	1194.7	1194.7	1196.3	1197.9
170°	1208.1	1207.4	1206.7	1206.0	1205.6	1205.3	1205.1	1204.9	1204.6	1206.2	1207.8
172.5°	1215.6	1214.9	1214.2	1213.4	1213.0	1212.8	1212.5	1212.3	1212.1	1213.7	1215.3
175°	1224.7	1224.0	1223.2	1222.6	1222.0	1221.6	1221.1	1220.7	1220.1	1221.8	1223.4
177.5°	1228.5	1228.0	1227.4	1226.9	1226.4	1226.0	1225.7	1225.3	1224.9	1226.0	1227.2
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1355.8	1360.6	1362.8	1362.8	1365.4	1364.2	1363.2
5°	1433.8	1442.4	1444.3	1452.5	1458.4	1456.5	1457.5
7.5°	1511.3	1525.2	1538.9	1545.2	1546.2	1549.9	1551.2
10°	1559.0	1570.4	1591.8	1588.6	1604.5	1613.6	1598.6
12.5°	1604.9	1620.2	1635.0	1639.1	1648.2	1651.1	1645.2
15°	1646.4	1654.6	1655.5	1653.2	1655.9	1653.7	1645.0
17.5°	1607.6	1594.3	1567.4	1554.6	1544.5	1529.6	1523.6
20°	1543.5	1504.3	1458.8	1440.6	1419.2	1377.3	1387.4
22.5°	1405.2	1360.5	1315.0	1261.9	1236.4	1196.8	1194.4
25°	1189.8	1112.9	1028.2	969.1	934.5	894.9	877.6
27.5°	925.1	828.2	758.8	723.7	691.8	660.4	659.1
30°	751.0	678.2	624.5	594.5	574.9	561.7	564.5
32.5°	633.0	583.2	547.0	522.0	507.6	497.6	497.4
35°	517.5	483.4	460.2	449.7	439.3	431.9	432.4
37.5°	442.9	422.4	409.5	397.9	391.4	387.8	385.8
40°	404.7	387.8	377.8	371.0	365.5	360.5	359.6
42.5°	374.4	360.5	350.4	345.1	340.0	336.4	335.6
45°	332.3	320.9	311.8	305.9	303.6	300.4	300.4
47.5°	295.6	284.4	277.3	273.6	269.7	267.5	267.4
50°	270.8	262.2	255.8	253.5	250.3	249.0	248.5
52.5°	248.6	242.2	237.6	236.0	234.7	232.9	233.3
55°	218.5	214.8	213.0	211.7	209.4	206.6	208.5
57.5°	193.1	190.0	185.1	180.8	178.7	176.8	177.5
60°	175.2	168.9	162.5	157.5	156.1	152.0	152.0
62.5°	152.7	143.7	135.9	133.1	131.7	129.8	129.5
65°	117.4	113.8	112.0	110.1	109.2	109.2	108.3
67.5°	97.3	95.9	93.9	93.4	92.5	92.2	91.9
70°	86.1	84.2	83.3	82.8	81.9	82.4	81.1
72.5°	75.1	73.7	73.5	72.3	71.7	71.8	70.8
75°	59.2	59.2	58.7	58.2	57.3	56.9	57.3
77.5°	45.5	45.6	44.8	44.7	44.6	44.7	44.2
80°	36.4	36.8	36.4	35.9	35.5	35.9	35.5
82.5°	28.8	28.1	28.0	27.9	27.8	27.6	27.5
85°	16.4	16.9	16.4	16.0	16.0	16.0	16.4
87.5°	13.2	13.1	13.0	13.1	13.1	13.2	12.8
90°	34.9	34.4	34.3	34.5	34.8	35.0	35.2
92.5°	33.2	33.3	33.3	33.4	33.4	33.5	33.5
95°	66.3	66.3	66.1	65.6	65.2	64.6	64.2
97.5°	111.5	111.5	111.5	111.4	111.4	111.3	111.3
100°	142.9	142.9	142.9	142.6	142.4	142.1	141.9
102.5°	177.5	177.6	177.6	177.4	177.2	176.9	176.7
105°	229.3	229.7	230.0	230.0	230.0	230.0	230.0
107.5°	284.5	284.7	284.3	283.3	282.2	281.2	280.1
110°	322.2	322.2	321.8	321.1	320.4	319.7	319.1



TEST NUMBER: P331700-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	359.4	358.9	358.4	357.8	357.3	356.9	356.3
115°	417.8	417.5	417.1	416.4	415.7	415.0	414.3
117.5°	473.6	473.1	472.4	471.7	471.0	470.3	469.7
120°	511.7	511.7	511.3	510.7	510.0	509.3	508.5
122.5°	549.8	549.2	548.8	548.2	547.7	547.2	546.7
125°	607.0	606.3	605.8	605.6	605.4	605.1	604.9
127.5°	662.5	661.6	660.8	660.1	659.4	658.7	657.9
130°	700.9	700.4	699.7	698.8	697.9	697.0	696.1
132.5°	737.4	736.4	735.5	734.8	734.0	733.3	732.5
135°	792.7	792.5	792.0	791.3	790.7	790.0	789.3
137.5°	845.1	844.9	844.4	843.4	842.5	841.6	840.6
140°	880.4	880.4	879.9	879.0	878.2	877.2	876.3
142.5°	912.5	912.7	912.3	911.3	910.4	909.5	908.6
145°	960.9	961.1	960.7	959.8	958.9	958.0	957.1
147.5°	1003.5	1004.1	1003.9	1003.0	1002.1	1001.2	1000.4
150°	1030.6	1031.4	1031.4	1030.6	1029.9	1029.2	1028.6
152.5°	1057.7	1058.5	1058.5	1057.7	1056.9	1056.0	1055.1
155°	1092.1	1093.2	1093.4	1092.8	1092.1	1091.4	1090.7
157.5°	1124.0	1125.5	1125.8	1124.6	1123.6	1122.5	1121.3
160°	1142.5	1143.9	1144.1	1143.2	1142.3	1141.3	1140.4
162.5°	1159.6	1161.2	1161.4	1160.3	1159.2	1158.1	1157.0
165°	1181.5	1183.1	1183.3	1182.2	1181.1	1179.9	1178.8
167.5°	1199.5	1201.1	1201.3	1200.2	1198.9	1197.7	1196.6
170°	1209.4	1211.0	1211.2	1209.8	1208.4	1207.0	1205.7
172.5°	1216.9	1218.5	1218.6	1217.3	1215.8	1214.5	1213.1
175°	1225.0	1226.6	1226.7	1225.4	1224.0	1222.6	1221.2
177.5°	1228.2	1229.3	1229.3	1228.2	1227.2	1226.0	1224.9
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4

(END OF REPORT)