

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331701-940

Luminaire Tested: **SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331701-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6017.1 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	96	92	88	85	87	83	80	78	68	66	64	54	52	51	40	40	39	33				
2	88	81	75	70	79	73	69	65	60	57	54	48	46	44	36	35	34	29				
3	80	71	65	59	73	65	59	55	54	49	46	43	40	38	33	31	29	25				
4	74	64	56	51	67	58	52	47	48	43	40	39	35	33	30	28	26	22				
5	68	57	49	44	62	52	46	41	43	38	35	35	31	29	27	25	23	20				
6	63	51	44	38	57	47	40	36	39	34	31	32	28	26	25	23	21	18				
7	58	46	39	34	53	43	36	32	36	31	27	29	26	23	23	20	19	16				
8	54	42	35	30	49	39	33	28	33	28	24	27	23	21	21	19	17	14				
9	50	39	32	27	46	36	29	25	30	25	22	25	21	19	20	17	15	13				
10	47	36	29	24	43	33	27	23	28	23	20	23	19	17	18	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21151	21151	21151	21151
5°	23622	21284	18870	21284
10°	26209	21135	16357	21135
15°	27497	20824	12889	20824
20°	23838	20366	11153	20366
25°	15634	19737	9957	19737
30°	10524	18975	9012	18975
35°	8523	18015	8129	18015
40°	7579	16971	7522	16971
45°	6859	15746	6715	15746
50°	6242	14531	6219	14531
55°	5869	13185	5790	13185
60°	4908	11951	4850	11951
65°	4138	10850	4695	10850
70°	3829	9692	4428	9692
75°	3575	8434	4086	8434
80°	3301	6936	3636	6936
85°	3038	5483	3205	5483



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	2.1
10°-20°	346.0	5.8
20°-30°	445.9	7.4
30°-40°	423.7	7.0
40°-50°	363.0	6.0
50°-60°	276.4	4.6
60°-70°	174.7	2.9
70°-80°	87.3	1.5
80°-90°	27.6	0.5
90°-100°	215.4	3.6
100°-110°	730.9	12.1
110°-120°	776.4	12.9
120°-130°	639.2	10.6
130°-140°	513.3	8.5
140°-150°	387.9	6.4
150°-160°	272.6	4.5
160°-170°	160.5	2.7
170°-180°	52.2	0.9
0°-30°	916.1	15.2
0°-40°	1339.8	22.3
0°-60°	1979.2	32.9
0°-90°	2268.8	37.7
90°-120°	1722.7	28.6
90°-150°	3263.0	54.2
90°-180°	3748.0	62.3
0°-180°	6017.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1310	1310	1310	1310	1310	
5°	1458	1313	1164	1313	1458	144
15°	1645	1246	771	1246	1645	444
25°	878	1108	559	1108	878	416
35°	432	914	412	914	432	277
45°	300	690	294	690	300	232
55°	208	468	206	468	208	183
65°	108	284	123	284	108	110
75°	57	135	66	135	57	61
85°	16	30	17	30	16	18
90°	34	1	34	1	34	19
95°	118	36	118	36	118	154
105°	1167	126	1167	126	1167	1130
115°	1536	223	1536	223	1536	1504
125°	1246	311	1246	311	1246	1126
135°	1033	365	1033	365	1033	802
145°	825	416	825	416	825	524
155°	693	473	693	473	693	323
165°	608	516	608	516	608	174
175°	548	538	548	538	548	53
180°	539	539	539	539	539	



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1363.2	1364.2	1365.4	1362.8	1362.8	1360.6	1355.8	1352.3	1342.0	1340.6	1340.6
5°	1457.5	1456.5	1458.4	1452.5	1444.3	1442.4	1433.8	1422.5	1410.6	1397.4	1394.6
7.5°	1551.2	1549.9	1546.2	1545.2	1538.9	1525.2	1511.3	1496.5	1476.8	1457.6	1448.0
10°	1598.6	1613.6	1604.5	1588.6	1591.8	1570.4	1559.0	1539.4	1523.0	1494.3	1488.0
12.5°	1645.2	1651.1	1648.2	1639.1	1635.0	1620.2	1604.9	1587.9	1557.6	1531.9	1509.5
15°	1645.0	1653.7	1655.9	1653.2	1655.5	1654.6	1646.4	1632.3	1605.9	1577.6	1553.1
17.5°	1523.6	1529.6	1544.5	1554.6	1567.4	1594.3	1607.6	1612.7	1608.8	1592.8	1575.5
20°	1387.4	1377.3	1419.2	1440.6	1458.8	1504.3	1543.5	1558.5	1582.6	1582.2	1577.6
22.5°	1194.4	1196.8	1236.4	1261.9	1315.0	1360.5	1405.2	1461.7	1508.3	1539.2	1557.3
25°	877.6	894.9	934.5	969.1	1028.2	1112.9	1189.8	1279.1	1363.2	1429.7	1493.0
27.5°	659.1	660.4	691.8	723.7	758.8	828.2	925.1	1031.6	1151.6	1250.7	1364.7
30°	564.5	561.7	574.9	594.5	624.5	678.2	751.0	855.8	975.4	1124.7	1257.7
32.5°	497.4	497.6	507.6	522.0	547.0	583.2	633.0	718.1	831.3	978.0	1133.8
35°	432.4	431.9	439.3	449.7	460.2	483.4	517.5	562.1	640.0	776.9	936.3
37.5°	385.8	387.8	391.4	397.9	409.5	422.4	442.9	472.9	528.2	609.3	743.2
40°	359.6	360.5	365.5	371.0	377.8	387.8	404.7	428.7	469.3	534.0	631.8
42.5°	335.6	336.4	340.0	345.1	350.4	360.5	374.4	395.3	428.1	478.6	559.3
45°	300.4	300.4	303.6	305.9	311.8	320.9	332.3	349.6	372.4	409.7	463.3
47.5°	267.4	267.5	269.7	273.6	277.3	284.4	295.6	309.7	326.3	355.2	401.0
50°	248.5	249.0	250.3	253.5	255.8	262.2	270.8	283.1	300.4	322.7	361.0
52.5°	233.3	232.9	234.7	236.0	237.6	242.2	248.6	259.5	274.9	294.4	326.0
55°	208.5	206.6	209.4	211.7	213.0	214.8	218.5	225.3	238.5	254.9	278.6
57.5°	177.5	176.8	178.7	180.8	185.1	190.0	193.1	197.4	204.3	216.1	239.5
60°	152.0	152.0	156.1	157.5	162.5	168.9	175.2	178.9	185.7	193.4	210.7
62.5°	129.5	129.8	131.7	133.1	135.9	143.7	152.7	160.7	167.1	174.5	186.0
65°	108.3	109.2	109.2	110.1	112.0	113.8	117.4	123.8	135.2	145.6	154.3
67.5°	91.9	92.2	92.5	93.4	93.9	95.9	97.3	100.1	102.8	112.7	123.4
70°	81.1	82.4	81.9	82.8	83.3	84.2	86.1	87.4	91.5	93.8	100.1
72.5°	70.8	71.8	71.7	72.3	73.5	73.7	75.1	76.5	79.1	81.1	84.4
75°	57.3	56.9	57.3	58.2	58.7	59.2	59.2	61.0	62.3	64.2	66.4
77.5°	44.2	44.7	44.6	44.7	44.8	45.6	45.5	46.4	47.7	48.6	49.7
80°	35.5	35.9	35.5	35.9	36.4	36.8	36.4	36.8	38.3	39.1	39.1
82.5°	27.5	27.6	27.8	27.9	28.0	28.1	28.8	28.9	29.9	29.7	30.1
85°	16.4	16.0	16.0	16.0	16.4	16.9	16.4	16.4	16.9	16.9	16.9
87.5°	12.7	13.0	13.0	13.0	13.0	12.8	12.4	13.2	13.0	13.6	13.0
90°	34.2	34.2	34.2	34.2	34.2	33.2	31.1	33.2	34.2	35.2	34.2
92.5°	57.4	59.0	58.2	61.5	62.3	68.8	77.5	90.3	113.8	134.6	132.8
95°	118.1	117.1	120.2	128.4	141.9	164.7	208.2	271.4	355.3	406.1	359.4
97.5°	232.5	241.1	256.3	281.8	331.3	406.1	518.2	633.3	727.2	693.2	522.1
100°	370.9	389.5	419.5	464.0	550.0	675.4	817.3	945.7	967.5	818.3	563.5
102.5°	652.6	677.9	715.4	791.4	884.8	1017.6	1121.4	1150.5	1057.0	822.5	547.8
105°	1167.4	1182.0	1226.5	1290.7	1355.0	1389.1	1375.6	1258.6	1043.1	767.6	516.9
107.5°	1491.2	1510.5	1519.4	1523.0	1514.8	1464.7	1357.0	1180.7	952.2	708.7	501.6
110°	1589.0	1590.1	1580.7	1561.0	1516.5	1431.6	1299.0	1113.6	895.0	680.6	498.3



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1587.3	1581.8	1564.1	1531.2	1469.3	1371.9	1230.2	1052.2	855.2	662.4	499.1
115°	1536.2	1526.9	1499.9	1452.3	1378.8	1272.0	1136.4	976.9	805.9	642.2	503.5
117.5°	1444.8	1437.0	1408.5	1358.3	1283.3	1183.2	1060.2	920.1	774.8	632.5	510.9
120°	1386.0	1375.6	1345.6	1296.9	1224.4	1130.2	1020.3	891.9	758.2	626.7	515.9
122.5°	1324.6	1316.0	1289.2	1241.4	1176.3	1091.2	987.2	869.5	744.1	623.4	521.7
125°	1246.2	1237.9	1212.0	1172.6	1112.5	1034.8	943.7	837.0	724.1	617.4	530.4
127.5°	1177.4	1170.7	1148.3	1111.5	1059.1	987.4	901.4	804.9	705.4	613.9	539.3
130°	1138.4	1130.2	1109.5	1074.2	1023.4	955.1	873.3	784.2	693.0	612.2	545.9
132.5°	1097.8	1090.4	1071.3	1036.1	986.1	921.9	846.8	764.3	683.1	611.4	552.5
135°	1032.8	1028.6	1010.0	975.8	931.2	873.3	804.9	736.5	669.1	610.1	560.4
137.5°	968.9	962.8	946.4	916.9	876.4	825.8	771.5	714.3	659.4	609.9	567.5
140°	925.1	918.8	903.3	876.4	843.2	797.6	750.0	700.3	653.6	609.1	570.8
142.5°	881.1	879.9	866.0	841.5	810.0	772.0	730.9	688.7	647.8	609.1	573.3
145°	824.6	821.4	811.1	793.4	768.7	738.6	706.5	672.3	640.2	607.0	576.0
147.5°	777.1	775.3	768.2	754.1	733.6	711.7	686.6	659.7	632.3	603.3	576.8
150°	748.9	747.9	741.7	729.2	713.7	695.1	673.3	650.5	625.6	600.8	576.0
152.5°	724.9	724.7	720.1	709.4	697.1	681.0	662.5	641.4	619.8	596.6	574.3
155°	693.0	695.1	690.9	683.7	672.3	660.8	645.3	628.7	609.1	589.4	571.8
157.5°	665.8	665.8	664.0	658.0	649.9	641.0	627.9	614.0	599.0	581.9	567.0
160°	648.5	648.5	647.4	642.2	635.0	627.8	616.4	604.9	591.5	577.0	564.5
162.5°	631.9	632.7	631.7	628.1	620.9	615.3	605.6	595.8	584.9	572.8	562.0
165°	608.1	609.1	609.1	604.9	600.8	596.6	589.4	582.2	573.9	564.5	557.3
167.5°	586.1	587.4	587.5	585.2	583.4	579.7	574.7	569.1	563.1	557.3	552.5
170°	572.8	574.9	576.0	572.8	571.8	569.7	565.6	562.5	557.3	553.1	550.0
172.5°	562.0	563.3	564.4	562.9	561.9	560.6	557.3	555.0	551.5	548.2	546.7
175°	548.0	550.0	551.1	550.0	550.0	549.0	548.0	547.0	543.9	542.8	541.8
177.5°	539.5	541.2	542.0	542.0	542.0	542.0	541.2	541.2	539.5	538.7	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1341.3	1338.4	1335.9	1329.3	1326.1	1318.8	1317.7	1317.3	1307.8	1298.7	1296.2
5°	1387.4	1380.1	1369.1	1356.4	1343.2	1329.5	1320.4	1313.2	1294.9	1277.6	1267.7
7.5°	1433.8	1418.2	1399.3	1375.2	1355.0	1332.5	1315.7	1300.7	1274.9	1250.1	1233.4
10°	1468.4	1442.9	1417.9	1384.6	1358.7	1333.2	1309.6	1289.1	1259.9	1227.2	1203.9
12.5°	1489.9	1461.9	1427.4	1394.8	1361.3	1328.8	1297.2	1270.9	1236.6	1202.7	1175.2
15°	1518.9	1488.9	1447.0	1400.6	1357.4	1315.0	1278.6	1245.8	1201.2	1160.7	1127.0
17.5°	1542.7	1501.4	1456.3	1402.7	1352.6	1298.8	1251.9	1210.1	1160.4	1111.5	1071.8
20°	1550.3	1509.4	1457.5	1403.7	1344.6	1281.3	1230.8	1185.3	1132.0	1078.8	1033.2
22.5°	1545.6	1513.8	1456.0	1391.8	1331.1	1264.9	1207.8	1155.0	1096.0	1041.6	988.8
25°	1513.5	1502.5	1448.0	1377.8	1308.7	1231.7	1165.7	1107.9	1040.5	982.3	924.9
27.5°	1438.5	1462.1	1428.3	1353.6	1276.7	1194.2	1120.0	1054.2	984.3	918.7	861.6
30°	1366.5	1420.6	1406.0	1336.9	1250.8	1169.8	1086.5	1017.8	943.2	875.7	819.3
32.5°	1267.7	1357.3	1371.5	1313.6	1224.6	1135.6	1048.3	979.9	902.0	831.0	776.0
35°	1110.6	1244.5	1305.9	1269.0	1179.8	1083.8	993.6	914.0	835.7	765.6	711.0
37.5°	923.2	1105.5	1207.8	1210.5	1128.5	1028.7	930.6	851.5	771.3	702.5	643.5
40°	801.6	999.1	1132.5	1162.1	1092.9	985.0	885.7	805.2	726.9	659.5	591.7
42.5°	692.3	889.1	1053.1	1104.6	1049.5	942.4	842.8	758.6	682.5	618.8	549.5
45°	559.9	731.9	912.7	1004.6	974.1	874.9	769.7	689.6	618.1	563.0	496.6
47.5°	472.3	593.5	768.4	892.8	892.2	801.6	698.2	621.5	555.3	503.6	449.8
50°	422.4	528.0	675.9	817.1	828.8	752.9	654.5	578.5	516.7	462.4	419.2
52.5°	377.6	464.7	597.6	732.9	766.6	700.8	605.4	535.2	475.1	425.3	388.3
55°	319.1	386.5	487.5	614.0	665.0	618.6	534.0	468.4	419.6	377.8	345.9
57.5°	269.9	320.5	401.5	503.5	562.8	533.6	463.7	410.5	368.8	330.9	305.8
60°	239.0	280.4	349.1	434.3	499.8	479.3	419.6	370.1	334.6	301.8	278.1
62.5°	209.8	245.4	304.3	373.4	433.5	425.1	376.3	334.7	303.6	273.8	253.7
65°	168.9	194.8	240.8	295.0	343.2	347.3	312.3	284.0	256.3	232.6	214.8
67.5°	134.5	151.4	183.8	229.4	265.6	278.5	257.1	235.5	213.5	195.2	179.8
70°	113.3	127.0	150.7	187.5	220.8	234.4	222.1	205.3	186.2	171.1	157.9
72.5°	91.8	105.1	122.6	149.6	178.2	192.9	188.6	176.6	161.0	148.6	136.1
75°	69.2	73.3	85.2	103.3	125.6	138.4	141.6	135.2	122.9	113.3	106.0
77.5°	51.2	53.6	59.3	68.8	83.4	94.8	99.4	98.7	90.2	84.6	77.8
80°	40.9	42.4	45.0	49.1	60.1	71.4	74.6	74.6	68.8	66.4	59.7
82.5°	31.1	32.1	33.8	36.0	41.1	51.1	54.7	55.4	51.6	48.6	43.2
85°	17.7	17.3	18.2	19.5	20.5	23.2	28.7	29.6	28.7	25.1	23.6
87.5°	11.8	10.7	9.6	8.6	8.6	8.6	9.5	10.8	9.9	9.6	9.4
90°	28.0	20.7	15.5	12.4	10.3	8.3	4.1	1.1	4.1	8.3	10.3
92.5°	103.3	70.4	47.0	37.3	30.2	25.7	18.2	12.7	18.2	25.7	30.2
95°	239.2	149.2	101.5	76.7	60.1	50.7	40.4	36.3	40.4	50.7	60.1
97.5°	322.4	196.8	137.0	108.8	89.7	75.6	64.6	59.0	64.6	75.6	89.7
100°	339.7	213.4	158.5	129.5	108.8	92.2	82.8	79.7	82.8	92.2	108.8
102.5°	340.6	228.3	177.5	148.6	127.0	110.4	101.1	98.8	101.1	110.4	127.0
105°	346.0	253.8	205.1	176.1	153.3	137.8	130.5	126.4	130.5	137.8	153.3
107.5°	360.3	279.9	232.6	203.5	180.8	166.6	159.5	156.2	159.5	166.6	180.8
110°	371.8	297.3	251.7	221.7	199.9	186.5	180.2	176.1	180.2	186.5	199.9



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	384.3	313.9	269.9	239.1	218.1	205.5	198.5	194.3	198.5	205.5	218.1
115°	403.0	339.7	295.2	267.2	246.6	234.1	227.9	222.7	227.9	234.1	246.6
117.5°	422.8	363.6	322.4	293.4	273.5	262.5	256.3	252.2	256.3	262.5	273.5
120°	436.1	380.1	339.7	310.8	290.1	280.7	274.5	270.4	274.5	280.7	290.1
122.5°	447.7	395.9	358.0	328.1	307.5	297.3	291.1	287.8	291.1	297.3	307.5
125°	466.2	419.5	382.3	353.2	332.5	320.1	313.9	310.8	313.9	320.1	332.5
127.5°	483.3	441.5	405.2	375.4	355.5	341.9	333.1	329.0	333.1	341.9	355.5
130°	494.1	454.8	418.5	389.5	368.8	354.3	343.9	339.7	343.9	354.3	368.8
132.5°	504.9	466.4	431.8	402.8	381.2	365.9	354.7	349.7	354.7	365.9	381.2
135°	519.0	482.7	449.6	420.5	396.7	381.2	368.8	364.6	368.8	381.2	396.7
137.5°	529.8	496.0	463.2	436.3	412.7	396.1	383.7	378.7	383.7	396.1	412.7
140°	535.6	503.5	472.3	445.4	422.7	406.1	393.6	389.5	393.6	406.1	422.7
142.5°	540.6	509.3	479.0	453.7	431.8	415.2	403.6	400.3	403.6	415.2	431.8
145°	547.0	517.9	490.0	467.2	446.5	431.0	420.5	416.4	420.5	431.0	446.5
147.5°	550.5	525.0	498.6	478.4	461.2	446.8	436.9	433.8	436.9	446.8	461.2
150°	552.1	528.3	504.4	485.8	470.3	456.8	448.5	445.4	448.5	456.8	470.3
152.5°	552.9	531.6	510.2	493.3	478.6	466.7	458.5	457.0	458.5	466.7	478.6
155°	554.2	536.5	519.0	503.5	492.0	480.6	474.4	473.4	474.4	480.6	492.0
157.5°	554.2	540.1	525.2	512.1	503.0	493.1	488.1	487.1	488.1	493.1	503.0
160°	554.2	541.8	529.3	517.9	509.6	501.3	497.2	496.1	497.2	501.3	509.6
162.5°	553.4	542.6	531.8	522.9	515.4	508.8	504.7	505.3	504.7	508.8	515.4
165°	551.1	543.9	534.5	528.3	523.1	516.9	514.9	515.9	514.9	516.9	523.1
167.5°	549.7	543.6	536.8	532.9	529.1	525.2	523.3	524.6	523.3	525.2	529.1
170°	548.0	542.8	537.6	534.5	532.4	529.3	528.3	530.4	528.3	529.3	532.4
172.5°	545.5	542.0	538.4	536.2	534.9	531.8	532.4	533.7	532.4	531.8	534.9
175°	542.8	540.7	538.7	537.6	537.6	535.6	536.5	537.6	536.5	535.6	537.6
177.5°	541.2	539.5	538.7	538.7	538.7	537.0	537.8	539.5	537.8	537.0	538.7
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1291.5	1288.9	1284.2	1276.8	1272.5	1264.8	1259.7	1262.7	1263.4	1262.7	1261.9
5°	1256.8	1247.1	1233.9	1221.2	1209.4	1196.7	1189.4	1186.2	1179.8	1176.2	1174.4
7.5°	1214.8	1198.3	1179.6	1157.4	1138.5	1118.8	1108.8	1103.7	1090.7	1083.6	1077.4
10°	1183.5	1157.5	1138.9	1109.7	1092.0	1066.0	1048.3	1048.7	1031.0	1020.9	1013.7
12.5°	1148.9	1120.3	1089.3	1063.1	1038.4	1017.6	996.2	987.6	968.7	959.0	939.4
15°	1091.5	1058.3	1025.6	990.0	965.0	932.6	901.7	863.9	833.4	807.0	799.8
17.5°	1028.9	987.7	954.8	913.2	870.3	815.9	780.1	758.1	739.8	725.9	715.4
20°	985.9	944.1	909.0	846.1	788.4	751.5	725.1	708.3	689.1	674.1	665.9
22.5°	940.8	897.1	849.3	779.2	734.1	704.5	681.0	661.6	648.7	636.9	629.5
25°	876.6	828.8	750.1	701.9	665.5	634.5	618.1	606.3	592.6	576.7	569.4
27.5°	809.0	732.9	676.4	640.5	605.7	585.6	570.9	553.2	541.0	533.9	526.3
30°	758.3	682.3	638.2	599.1	574.4	552.1	534.8	524.9	513.0	500.7	495.7
32.5°	701.9	641.1	598.9	566.2	541.3	522.3	508.6	492.4	483.8	476.3	465.8
35°	631.8	585.9	547.2	520.8	497.0	481.6	465.7	456.1	440.6	434.3	430.2
37.5°	572.4	532.5	503.7	475.8	457.1	440.0	430.3	415.0	408.3	399.5	390.8
40°	539.0	499.8	472.0	449.2	428.3	415.5	403.3	391.0	380.9	376.9	366.4
42.5°	504.7	472.9	445.1	420.1	406.1	392.6	377.1	368.1	357.7	351.1	344.6
45°	457.4	429.3	405.6	385.0	369.6	355.5	345.4	330.5	324.6	311.3	305.9
47.5°	416.0	389.7	367.1	347.7	332.5	323.3	308.7	296.9	287.5	279.4	272.4
50°	386.5	364.6	342.8	325.5	311.8	298.6	283.6	277.7	263.1	259.0	254.9
52.5°	359.5	338.8	318.7	301.8	288.1	275.3	262.1	254.3	244.5	240.4	237.5
55°	321.8	301.8	282.7	267.6	254.0	240.8	232.6	223.0	218.5	215.3	211.7
57.5°	283.9	265.9	251.3	236.0	222.3	211.9	202.3	196.6	191.9	187.7	183.3
60°	259.9	242.6	229.4	215.3	201.2	192.5	185.3	178.4	173.0	166.6	164.8
62.5°	234.4	219.3	207.2	193.4	181.2	173.3	166.3	159.9	153.3	144.0	141.4
65°	199.4	187.5	174.8	163.5	152.5	144.7	134.7	127.4	124.8	123.8	123.3
67.5°	167.7	156.5	145.5	133.9	123.9	116.8	111.7	110.6	108.7	108.2	106.9
70°	146.6	136.1	125.2	114.2	104.7	103.3	101.5	99.7	97.4	96.5	95.6
72.5°	127.6	116.8	105.8	97.1	93.0	91.3	89.5	87.7	86.1	85.2	84.6
75°	97.8	87.8	80.6	77.4	75.1	73.7	71.0	69.6	68.8	67.3	66.9
77.5°	70.4	64.8	61.4	59.5	57.1	55.6	54.0	52.7	51.7	51.5	50.7
80°	53.7	51.0	48.7	46.0	45.0	43.2	42.8	41.5	41.9	40.5	40.5
82.5°	41.7	38.3	36.3	35.0	34.2	32.7	32.2	31.6	31.7	30.7	30.7
85°	21.4	20.5	19.5	18.6	18.6	17.3	17.7	17.3	17.3	16.4	16.0
87.5°	9.4	9.6	10.0	11.4	12.7	12.5	12.3	11.8	11.3	11.8	11.6
90°	12.4	15.5	20.7	28.0	34.2	35.2	34.2	33.2	31.1	33.2	34.2
92.5°	37.3	47.0	70.4	103.3	132.8	134.6	113.8	90.3	77.5	68.8	62.3
95°	76.7	101.5	149.2	239.2	359.4	406.1	355.3	271.4	208.2	164.7	141.9
97.5°	108.8	137.0	196.8	322.4	522.1	693.2	727.2	633.3	518.2	406.1	331.3
100°	129.5	158.5	213.4	339.7	563.5	818.3	967.5	945.7	817.3	675.4	550.0
102.5°	148.6	177.5	228.3	340.6	547.8	822.5	1057.0	1150.5	1121.4	1017.6	884.8
105°	176.1	205.1	253.8	346.0	516.9	767.6	1043.1	1258.6	1375.6	1389.1	1355.0
107.5°	203.5	232.6	279.9	360.3	501.6	708.7	952.2	1180.7	1357.0	1464.7	1514.8
110°	221.7	251.7	297.3	371.8	498.3	680.6	895.0	1113.6	1299.0	1431.6	1516.5



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	239.1	269.9	313.9	384.3	499.1	662.4	855.2	1052.2	1230.2	1371.9	1469.3
115°	267.2	295.2	339.7	403.0	503.5	642.2	805.9	976.9	1136.4	1272.0	1378.8
117.5°	293.4	322.4	363.6	422.8	510.9	632.5	774.8	920.1	1060.2	1183.2	1283.3
120°	310.8	339.7	380.1	436.1	515.9	626.7	758.2	891.9	1020.3	1130.2	1224.4
122.5°	328.1	358.0	395.9	447.7	521.7	623.4	744.1	869.5	987.2	1091.2	1176.3
125°	353.2	382.3	419.5	466.2	530.4	617.4	724.1	837.0	943.7	1034.8	1112.5
127.5°	375.4	405.2	441.5	483.3	539.3	613.9	705.4	804.9	901.4	987.4	1059.1
130°	389.5	418.5	454.8	494.1	545.9	612.2	693.0	784.2	873.3	955.1	1023.4
132.5°	402.8	431.8	466.4	504.9	552.5	611.4	683.1	764.3	846.8	921.9	986.1
135°	420.5	449.6	482.7	519.0	560.4	610.1	669.1	736.5	804.9	873.3	931.2
137.5°	436.3	463.2	496.0	529.8	567.5	609.9	659.4	714.3	771.5	825.8	876.4
140°	445.4	472.3	503.5	535.6	570.8	609.1	653.6	700.3	750.0	797.6	843.2
142.5°	453.7	479.0	509.3	540.6	573.3	609.1	647.8	688.7	730.9	772.0	810.0
145°	467.2	490.0	517.9	547.0	576.0	607.0	640.2	672.3	706.5	738.6	768.7
147.5°	478.4	498.6	525.0	550.5	576.8	603.3	632.3	659.7	686.6	711.7	733.6
150°	485.8	504.4	528.3	552.1	576.0	600.8	625.6	650.5	673.3	695.1	713.7
152.5°	493.3	510.2	531.6	552.9	574.3	596.6	619.8	641.4	662.5	681.0	697.1
155°	503.5	519.0	536.5	554.2	571.8	589.4	609.1	628.7	645.3	660.8	672.3
157.5°	512.1	525.2	540.1	554.2	567.0	581.9	599.0	614.0	627.9	641.0	649.9
160°	517.9	529.3	541.8	554.2	564.5	577.0	591.5	604.9	616.4	627.8	635.0
162.5°	522.9	531.8	542.6	553.4	562.0	572.8	584.9	595.8	605.6	615.3	620.9
165°	528.3	534.5	543.9	551.1	557.3	564.5	573.9	582.2	589.4	596.6	600.8
167.5°	532.9	536.8	543.6	549.7	552.5	557.3	563.1	569.1	574.7	579.7	583.4
170°	534.5	537.6	542.8	548.0	550.0	553.1	557.3	562.5	565.6	569.7	571.8
172.5°	536.2	538.4	542.0	545.5	546.7	548.2	551.5	555.0	557.3	560.6	561.9
175°	537.6	538.7	540.7	542.8	541.8	542.8	543.9	547.0	548.0	549.0	550.0
177.5°	538.7	538.7	539.5	541.2	539.5	538.7	539.5	541.2	541.2	542.0	542.0
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1257.9	1258.6	1257.6	1258.3	1257.6	1258.6	1257.9	1261.9	1262.7	1263.4	1262.7
5°	1172.1	1166.6	1165.7	1164.3	1165.7	1166.6	1172.1	1174.4	1176.2	1179.8	1186.2
7.5°	1069.6	1068.7	1066.5	1063.3	1066.5	1068.7	1069.6	1077.4	1083.6	1090.7	1103.7
10°	1003.6	1001.4	1000.9	997.7	1000.9	1001.4	1003.6	1013.7	1020.9	1031.0	1048.7
12.5°	926.5	911.8	910.3	902.3	910.3	911.8	926.5	939.4	959.0	968.7	987.6
15°	788.8	786.1	776.9	771.1	776.9	786.1	788.8	799.8	807.0	833.4	863.9
17.5°	710.2	701.2	698.4	697.1	698.4	701.2	710.2	715.4	725.9	739.8	758.1
20°	659.5	651.4	650.0	649.1	650.0	651.4	659.5	665.9	674.1	689.1	708.3
22.5°	624.6	616.0	612.5	609.8	612.5	616.0	624.6	629.5	636.9	648.7	661.6
25°	564.9	561.7	559.9	558.9	559.9	561.7	564.9	569.4	576.7	592.6	606.3
27.5°	518.2	511.1	509.8	507.5	509.8	511.1	518.2	526.3	533.9	541.0	553.2
30°	491.6	489.3	486.2	483.4	486.2	489.3	491.6	495.7	500.7	513.0	524.9
32.5°	460.3	458.3	455.6	454.2	455.6	458.3	460.3	465.8	476.3	483.8	492.4
35°	425.6	419.2	416.5	412.4	416.5	419.2	425.6	430.2	434.3	440.6	456.1
37.5°	388.9	385.6	381.7	383.1	381.7	385.6	388.9	390.8	399.5	408.3	415.0
40°	360.5	358.2	357.3	356.9	357.3	358.2	360.5	366.4	376.9	380.9	391.0
42.5°	338.0	331.6	329.3	329.2	329.3	331.6	338.0	344.6	351.1	357.7	368.1
45°	303.6	297.7	293.6	294.1	293.6	297.7	303.6	305.9	311.3	324.6	330.5
47.5°	268.5	268.3	265.7	266.5	265.7	268.3	268.5	272.4	279.4	287.5	296.9
50°	251.7	249.0	247.2	247.6	247.2	249.0	251.7	254.9	259.0	263.1	277.7
52.5°	235.7	233.4	231.8	233.8	231.8	233.4	235.7	237.5	240.4	244.5	254.3
55°	209.4	206.6	206.2	205.7	206.2	206.6	209.4	211.7	215.3	218.5	223.0
57.5°	179.9	178.2	175.4	174.2	175.4	178.2	179.9	183.3	187.7	191.9	196.6
60°	158.8	155.2	150.7	150.2	150.7	155.2	158.8	164.8	166.6	173.0	178.4
62.5°	139.6	138.8	137.9	137.9	137.9	138.8	139.6	141.4	144.0	153.3	159.9
65°	122.4	122.0	122.4	122.9	122.4	122.0	122.4	123.3	123.8	124.8	127.4
67.5°	106.7	105.8	105.0	105.4	105.0	105.8	106.7	106.9	108.2	108.7	110.6
70°	94.7	94.3	93.8	93.8	93.8	94.3	94.7	95.6	96.5	97.4	99.7
72.5°	83.0	82.9	82.5	82.1	82.5	82.9	83.0	84.6	85.2	86.1	87.7
75°	66.4	65.5	65.5	65.5	65.5	65.5	66.4	66.9	67.3	68.8	69.6
77.5°	50.6	50.2	49.7	49.3	49.7	50.2	50.6	50.7	51.5	51.7	52.7
80°	40.0	39.6	39.1	39.1	39.1	39.6	40.0	40.5	40.5	41.9	41.5
82.5°	30.6	30.1	30.1	29.7	30.1	30.1	30.6	30.7	30.7	31.7	31.6
85°	16.4	16.9	16.4	17.3	16.4	16.9	16.4	16.0	16.4	17.3	17.3
87.5°	11.6	11.2	11.6	11.2	11.6	11.2	11.6	11.6	11.8	11.3	11.8
90°	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	33.2	31.1	33.2
92.5°	61.5	58.2	59.0	57.4	59.0	58.2	61.5	62.3	68.8	77.5	90.3
95°	128.4	120.2	117.1	118.1	117.1	120.2	128.4	141.9	164.7	208.2	271.4
97.5°	281.8	256.3	241.1	232.5	241.1	256.3	281.8	331.3	406.1	518.2	633.3
100°	464.0	419.5	389.5	370.9	389.5	419.5	464.0	550.0	675.4	817.3	945.7
102.5°	791.4	715.4	677.9	652.6	677.9	715.4	791.4	884.8	1017.6	1121.4	1150.5
105°	1290.7	1226.5	1182.0	1167.4	1182.0	1226.5	1290.7	1355.0	1389.1	1375.6	1258.6
107.5°	1523.0	1519.4	1510.5	1491.2	1510.5	1519.4	1523.0	1514.8	1464.7	1357.0	1180.7
110°	1561.0	1580.7	1590.1	1589.0	1590.1	1580.7	1561.0	1516.5	1431.6	1299.0	1113.6



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1531.2	1564.1	1581.8	1587.3	1581.8	1564.1	1531.2	1469.3	1371.9	1230.2	1052.2
115°	1452.3	1499.9	1526.9	1536.2	1526.9	1499.9	1452.3	1378.8	1272.0	1136.4	976.9
117.5°	1358.3	1408.5	1437.0	1444.8	1437.0	1408.5	1358.3	1283.3	1183.2	1060.2	920.1
120°	1296.9	1345.6	1375.6	1386.0	1375.6	1345.6	1296.9	1224.4	1130.2	1020.3	891.9
122.5°	1241.4	1289.2	1316.0	1324.6	1316.0	1289.2	1241.4	1176.3	1091.2	987.2	869.5
125°	1172.6	1212.0	1237.9	1246.2	1237.9	1212.0	1172.6	1112.5	1034.8	943.7	837.0
127.5°	1111.5	1148.3	1170.7	1177.4	1170.7	1148.3	1111.5	1059.1	987.4	901.4	804.9
130°	1074.2	1109.5	1130.2	1138.4	1130.2	1109.5	1074.2	1023.4	955.1	873.3	784.2
132.5°	1036.1	1071.3	1090.4	1097.8	1090.4	1071.3	1036.1	986.1	921.9	846.8	764.3
135°	975.8	1010.0	1028.6	1032.8	1028.6	1010.0	975.8	931.2	873.3	804.9	736.5
137.5°	916.9	946.4	962.8	968.9	962.8	946.4	916.9	876.4	825.8	771.5	714.3
140°	876.4	903.3	918.8	925.1	918.8	903.3	876.4	843.2	797.6	750.0	700.3
142.5°	841.5	866.0	879.9	881.1	879.9	866.0	841.5	810.0	772.0	730.9	688.7
145°	793.4	811.1	821.4	824.6	821.4	811.1	793.4	768.7	738.6	706.5	672.3
147.5°	754.1	768.2	775.3	777.1	775.3	768.2	754.1	733.6	711.7	686.6	659.7
150°	729.2	741.7	747.9	748.9	747.9	741.7	729.2	713.7	695.1	673.3	650.5
152.5°	709.4	720.1	724.7	724.9	724.7	720.1	709.4	697.1	681.0	662.5	641.4
155°	683.7	690.9	695.1	693.0	695.1	690.9	683.7	672.3	660.8	645.3	628.7
157.5°	658.0	664.0	665.8	665.8	665.8	664.0	658.0	649.9	641.0	627.9	614.0
160°	642.2	647.4	648.5	648.5	648.5	647.4	642.2	635.0	627.8	616.4	604.9
162.5°	628.1	631.7	632.7	631.9	632.7	631.7	628.1	620.9	615.3	605.6	595.8
165°	604.9	609.1	609.1	608.1	609.1	609.1	604.9	600.8	596.6	589.4	582.2
167.5°	585.2	587.5	587.4	586.1	587.4	587.5	585.2	583.4	579.7	574.7	569.1
170°	572.8	576.0	574.9	572.8	574.9	576.0	572.8	571.8	569.7	565.6	562.5
172.5°	562.9	564.4	563.3	562.0	563.3	564.4	562.9	561.9	560.6	557.3	555.0
175°	550.0	551.1	550.0	548.0	550.0	551.1	550.0	550.0	549.0	548.0	547.0
177.5°	542.0	542.0	541.2	539.5	541.2	542.0	542.0	542.0	542.0	541.2	541.2
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1259.7	1264.8	1272.5	1276.8	1284.2	1288.9	1291.5	1296.2	1298.7	1307.8	1317.3
5°	1189.4	1196.7	1209.4	1221.2	1233.9	1247.1	1256.8	1267.7	1277.6	1294.9	1313.2
7.5°	1108.8	1118.8	1138.5	1157.4	1179.6	1198.3	1214.8	1233.4	1250.1	1274.9	1300.7
10°	1048.3	1066.0	1092.0	1109.7	1138.9	1157.5	1183.5	1203.9	1227.2	1259.9	1289.1
12.5°	996.2	1017.6	1038.4	1063.1	1089.3	1120.3	1148.9	1175.2	1202.7	1236.6	1270.9
15°	901.7	932.6	965.0	990.0	1025.6	1058.3	1091.5	1127.0	1160.7	1201.2	1245.8
17.5°	780.1	815.9	870.3	913.2	954.8	987.7	1028.9	1071.8	1111.5	1160.4	1210.1
20°	725.1	751.5	788.4	846.1	909.0	944.1	985.9	1033.2	1078.8	1132.0	1185.3
22.5°	681.0	704.5	734.1	779.2	849.3	897.1	940.8	988.8	1041.6	1096.0	1155.0
25°	618.1	634.5	665.5	701.9	750.1	828.8	876.6	924.9	982.3	1040.5	1107.9
27.5°	570.9	585.6	605.7	640.5	676.4	732.9	809.0	861.6	918.7	984.3	1054.2
30°	534.8	552.1	574.4	599.1	638.2	682.3	758.3	819.3	875.7	943.2	1017.8
32.5°	508.6	522.3	541.3	566.2	598.9	641.1	701.9	776.0	831.0	902.0	979.9
35°	465.7	481.6	497.0	520.8	547.2	585.9	631.8	711.0	765.6	835.7	914.0
37.5°	430.3	440.0	457.1	475.8	503.7	532.5	572.4	643.5	702.5	771.3	851.5
40°	403.3	415.5	428.3	449.2	472.0	499.8	539.0	591.7	659.5	726.9	805.2
42.5°	377.1	392.6	406.1	420.1	445.1	472.9	504.7	549.5	618.8	682.5	758.6
45°	345.4	355.5	369.6	385.0	405.6	429.3	457.4	496.6	563.0	618.1	689.6
47.5°	308.7	323.3	332.5	347.7	367.1	389.7	416.0	449.8	503.6	555.3	621.5
50°	283.6	298.6	311.8	325.5	342.8	364.6	386.5	419.2	462.4	516.7	578.5
52.5°	262.1	275.3	288.1	301.8	318.7	338.8	359.5	388.3	425.3	475.1	535.2
55°	232.6	240.8	254.0	267.6	282.7	301.8	321.8	345.9	377.8	419.6	468.4
57.5°	202.3	211.9	222.3	236.0	251.3	265.9	283.9	305.8	330.9	368.8	410.5
60°	185.3	192.5	201.2	215.3	229.4	242.6	259.9	278.1	301.8	334.6	370.1
62.5°	166.3	173.3	181.2	193.4	207.2	219.3	234.4	253.7	273.8	303.6	334.7
65°	134.7	144.7	152.5	163.5	174.8	187.5	199.4	214.8	232.6	256.3	284.0
67.5°	111.7	116.8	123.9	133.9	145.5	156.5	167.7	179.8	195.2	213.5	235.5
70°	101.5	103.3	104.7	114.2	125.2	136.1	146.6	157.9	171.1	186.2	205.3
72.5°	89.5	91.3	93.0	97.1	105.8	116.8	127.6	136.1	148.6	161.0	176.6
75°	71.0	73.7	75.1	77.4	80.6	87.8	97.8	106.0	113.3	122.9	135.2
77.5°	54.0	55.6	57.1	59.5	61.4	64.8	70.4	77.8	84.6	90.2	98.7
80°	42.8	43.2	45.0	46.0	48.7	51.0	53.7	59.7	66.4	68.8	74.6
82.5°	32.2	32.7	34.2	35.0	36.3	38.3	41.7	43.2	48.6	51.6	55.4
85°	17.7	17.3	18.6	18.6	19.5	20.5	21.4	23.6	25.1	28.7	29.6
87.5°	12.3	12.5	12.7	11.4	10.0	9.6	9.4	9.4	9.6	9.9	10.8
90°	34.2	35.2	34.2	28.0	20.7	15.5	12.4	10.3	8.3	4.1	1.1
92.5°	113.8	134.6	132.8	103.3	70.4	47.0	37.3	30.2	25.7	18.2	12.7
95°	355.3	406.1	359.4	239.2	149.2	101.5	76.7	60.1	50.7	40.4	36.3
97.5°	727.2	693.2	522.1	322.4	196.8	137.0	108.8	89.7	75.6	64.6	59.0
100°	967.5	818.3	563.5	339.7	213.4	158.5	129.5	108.8	92.2	82.8	79.7
102.5°	1057.0	822.5	547.8	340.6	228.3	177.5	148.6	127.0	110.4	101.1	98.8
105°	1043.1	767.6	516.9	346.0	253.8	205.1	176.1	153.3	137.8	130.5	126.4
107.5°	952.2	708.7	501.6	360.3	279.9	232.6	203.5	180.8	166.6	159.5	156.2
110°	895.0	680.6	498.3	371.8	297.3	251.7	221.7	199.9	186.5	180.2	176.1



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	855.2	662.4	499.1	384.3	313.9	269.9	239.1	218.1	205.5	198.5	194.3
115°	805.9	642.2	503.5	403.0	339.7	295.2	267.2	246.6	234.1	227.9	222.7
117.5°	774.8	632.5	510.9	422.8	363.6	322.4	293.4	273.5	262.5	256.3	252.2
120°	758.2	626.7	515.9	436.1	380.1	339.7	310.8	290.1	280.7	274.5	270.4
122.5°	744.1	623.4	521.7	447.7	395.9	358.0	328.1	307.5	297.3	291.1	287.8
125°	724.1	617.4	530.4	466.2	419.5	382.3	353.2	332.5	320.1	313.9	310.8
127.5°	705.4	613.9	539.3	483.3	441.5	405.2	375.4	355.5	341.9	333.1	329.0
130°	693.0	612.2	545.9	494.1	454.8	418.5	389.5	368.8	354.3	343.9	339.7
132.5°	683.1	611.4	552.5	504.9	466.4	431.8	402.8	381.2	365.9	354.7	349.7
135°	669.1	610.1	560.4	519.0	482.7	449.6	420.5	396.7	381.2	368.8	364.6
137.5°	659.4	609.9	567.5	529.8	496.0	463.2	436.3	412.7	396.1	383.7	378.7
140°	653.6	609.1	570.8	535.6	503.5	472.3	445.4	422.7	406.1	393.6	389.5
142.5°	647.8	609.1	573.3	540.6	509.3	479.0	453.7	431.8	415.2	403.6	400.3
145°	640.2	607.0	576.0	547.0	517.9	490.0	467.2	446.5	431.0	420.5	416.4
147.5°	632.3	603.3	576.8	550.5	525.0	498.6	478.4	461.2	446.8	436.9	433.8
150°	625.6	600.8	576.0	552.1	528.3	504.4	485.8	470.3	456.8	448.5	445.4
152.5°	619.8	596.6	574.3	552.9	531.6	510.2	493.3	478.6	466.7	458.5	457.0
155°	609.1	589.4	571.8	554.2	536.5	519.0	503.5	492.0	480.6	474.4	473.4
157.5°	599.0	581.9	567.0	554.2	540.1	525.2	512.1	503.0	493.1	488.1	487.1
160°	591.5	577.0	564.5	554.2	541.8	529.3	517.9	509.6	501.3	497.2	496.1
162.5°	584.9	572.8	562.0	553.4	542.6	531.8	522.9	515.4	508.8	504.7	505.3
165°	573.9	564.5	557.3	551.1	543.9	534.5	528.3	523.1	516.9	514.9	515.9
167.5°	563.1	557.3	552.5	549.7	543.6	536.8	532.9	529.1	525.2	523.3	524.6
170°	557.3	553.1	550.0	548.0	542.8	537.6	534.5	532.4	529.3	528.3	530.4
172.5°	551.5	548.2	546.7	545.5	542.0	538.4	536.2	534.9	531.8	532.4	533.7
175°	543.9	542.8	541.8	542.8	540.7	538.7	537.6	537.6	535.6	536.5	537.6
177.5°	539.5	538.7	539.5	541.2	539.5	538.7	538.7	538.7	537.0	537.8	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1317.7	1318.8	1326.1	1329.3	1335.9	1338.4	1341.3	1340.6	1340.6	1342.0	1352.3
5°	1320.4	1329.5	1343.2	1356.4	1369.1	1380.1	1387.4	1394.6	1397.4	1410.6	1422.5
7.5°	1315.7	1332.5	1355.0	1375.2	1399.3	1418.2	1433.8	1448.0	1457.6	1476.8	1496.5
10°	1309.6	1333.2	1358.7	1384.6	1417.9	1442.9	1468.4	1488.0	1494.3	1523.0	1539.4
12.5°	1297.2	1328.8	1361.3	1394.8	1427.4	1461.9	1489.9	1509.5	1531.9	1557.6	1587.9
15°	1278.6	1315.0	1357.4	1400.6	1447.0	1488.9	1518.9	1553.1	1577.6	1605.9	1632.3
17.5°	1251.9	1298.8	1352.6	1402.7	1456.3	1501.4	1542.7	1575.5	1592.8	1608.8	1612.7
20°	1230.8	1281.3	1344.6	1403.7	1457.5	1509.4	1550.3	1577.6	1582.2	1582.6	1558.5
22.5°	1207.8	1264.9	1331.1	1391.8	1456.0	1513.8	1545.6	1557.3	1539.2	1508.3	1461.7
25°	1165.7	1231.7	1308.7	1377.8	1448.0	1502.5	1513.5	1493.0	1429.7	1363.2	1279.1
27.5°	1120.0	1194.2	1276.7	1353.6	1428.3	1462.1	1438.5	1364.7	1250.7	1151.6	1031.6
30°	1086.5	1169.8	1250.8	1336.9	1406.0	1420.6	1366.5	1257.7	1124.7	975.4	855.8
32.5°	1048.3	1135.6	1224.6	1313.6	1371.5	1357.3	1267.7	1133.8	978.0	831.3	718.1
35°	993.6	1083.8	1179.8	1269.0	1305.9	1244.5	1110.6	936.3	776.9	640.0	562.1
37.5°	930.6	1028.7	1128.5	1210.5	1207.8	1105.5	923.2	743.2	609.3	528.2	472.9
40°	885.7	985.0	1092.9	1162.1	1132.5	999.1	801.6	631.8	534.0	469.3	428.7
42.5°	842.8	942.4	1049.5	1104.6	1053.1	889.1	692.3	559.3	478.6	428.1	395.3
45°	769.7	874.9	974.1	1004.6	912.7	731.9	559.9	463.3	409.7	372.4	349.6
47.5°	698.2	801.6	892.2	892.8	768.4	593.5	472.3	401.0	355.2	326.3	309.7
50°	654.5	752.9	828.8	817.1	675.9	528.0	422.4	361.0	322.7	300.4	283.1
52.5°	605.4	700.8	766.6	732.9	597.6	464.7	377.6	326.0	294.4	274.9	259.5
55°	534.0	618.6	665.0	614.0	487.5	386.5	319.1	278.6	254.9	238.5	225.3
57.5°	463.7	533.6	562.8	503.5	401.5	320.5	269.9	239.5	216.1	204.3	197.4
60°	419.6	479.3	499.8	434.3	349.1	280.4	239.0	210.7	193.4	185.7	178.9
62.5°	376.3	425.1	433.5	373.4	304.3	245.4	209.8	186.0	174.5	167.1	160.7
65°	312.3	347.3	343.2	295.0	240.8	194.8	168.9	154.3	145.6	135.2	123.8
67.5°	257.1	278.5	265.6	229.4	183.8	151.4	134.5	123.4	112.7	102.8	100.1
70°	222.1	234.4	220.8	187.5	150.7	127.0	113.3	100.1	93.8	91.5	87.4
72.5°	188.6	192.9	178.2	149.6	122.6	105.1	91.8	84.4	81.1	79.1	76.5
75°	141.6	138.4	125.6	103.3	85.2	73.3	69.2	66.4	64.2	62.3	61.0
77.5°	99.4	94.8	83.4	68.8	59.3	53.6	51.2	49.7	48.6	47.7	46.4
80°	74.6	71.4	60.1	49.1	45.0	42.4	40.9	39.1	39.1	38.3	36.8
82.5°	54.7	51.1	41.1	36.0	33.8	32.1	31.1	30.1	29.7	29.9	28.9
85°	28.7	23.2	20.5	19.5	18.2	17.3	17.7	16.9	16.9	16.9	16.4
87.5°	9.5	8.6	8.6	8.6	9.6	10.7	11.8	13.0	13.6	13.0	13.2
90°	4.1	8.3	10.3	12.4	15.5	20.7	28.0	34.2	35.2	34.2	33.2
92.5°	18.2	25.7	30.2	37.3	47.0	70.4	103.3	132.8	134.6	113.8	90.3
95°	40.4	50.7	60.1	76.7	101.5	149.2	239.2	359.4	406.1	355.3	271.4
97.5°	64.6	75.6	89.7	108.8	137.0	196.8	322.4	522.1	693.2	727.2	633.3
100°	82.8	92.2	108.8	129.5	158.5	213.4	339.7	563.5	818.3	967.5	945.7
102.5°	101.1	110.4	127.0	148.6	177.5	228.3	340.6	547.8	822.5	1057.0	1150.5
105°	130.5	137.8	153.3	176.1	205.1	253.8	346.0	516.9	767.6	1043.1	1258.6
107.5°	159.5	166.6	180.8	203.5	232.6	279.9	360.3	501.6	708.7	952.2	1180.7
110°	180.2	186.5	199.9	221.7	251.7	297.3	371.8	498.3	680.6	895.0	1113.6



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	198.5	205.5	218.1	239.1	269.9	313.9	384.3	499.1	662.4	855.2	1052.2
115°	227.9	234.1	246.6	267.2	295.2	339.7	403.0	503.5	642.2	805.9	976.9
117.5°	256.3	262.5	273.5	293.4	322.4	363.6	422.8	510.9	632.5	774.8	920.1
120°	274.5	280.7	290.1	310.8	339.7	380.1	436.1	515.9	626.7	758.2	891.9
122.5°	291.1	297.3	307.5	328.1	358.0	395.9	447.7	521.7	623.4	744.1	869.5
125°	313.9	320.1	332.5	353.2	382.3	419.5	466.2	530.4	617.4	724.1	837.0
127.5°	333.1	341.9	355.5	375.4	405.2	441.5	483.3	539.3	613.9	705.4	804.9
130°	343.9	354.3	368.8	389.5	418.5	454.8	494.1	545.9	612.2	693.0	784.2
132.5°	354.7	365.9	381.2	402.8	431.8	466.4	504.9	552.5	611.4	683.1	764.3
135°	368.8	381.2	396.7	420.5	449.6	482.7	519.0	560.4	610.1	669.1	736.5
137.5°	383.7	396.1	412.7	436.3	463.2	496.0	529.8	567.5	609.9	659.4	714.3
140°	393.6	406.1	422.7	445.4	472.3	503.5	535.6	570.8	609.1	653.6	700.3
142.5°	403.6	415.2	431.8	453.7	479.0	509.3	540.6	573.3	609.1	647.8	688.7
145°	420.5	431.0	446.5	467.2	490.0	517.9	547.0	576.0	607.0	640.2	672.3
147.5°	436.9	446.8	461.2	478.4	498.6	525.0	550.5	576.8	603.3	632.3	659.7
150°	448.5	456.8	470.3	485.8	504.4	528.3	552.1	576.0	600.8	625.6	650.5
152.5°	458.5	466.7	478.6	493.3	510.2	531.6	552.9	574.3	596.6	619.8	641.4
155°	474.4	480.6	492.0	503.5	519.0	536.5	554.2	571.8	589.4	609.1	628.7
157.5°	488.1	493.1	503.0	512.1	525.2	540.1	554.2	567.0	581.9	599.0	614.0
160°	497.2	501.3	509.6	517.9	529.3	541.8	554.2	564.5	577.0	591.5	604.9
162.5°	504.7	508.8	515.4	522.9	531.8	542.6	553.4	562.0	572.8	584.9	595.8
165°	514.9	516.9	523.1	528.3	534.5	543.9	551.1	557.3	564.5	573.9	582.2
167.5°	523.3	525.2	529.1	532.9	536.8	543.6	549.7	552.5	557.3	563.1	569.1
170°	528.3	529.3	532.4	534.5	537.6	542.8	548.0	550.0	553.1	557.3	562.5
172.5°	532.4	531.8	534.9	536.2	538.4	542.0	545.5	546.7	548.2	551.5	555.0
175°	536.5	535.6	537.6	537.6	538.7	540.7	542.8	541.8	542.8	543.9	547.0
177.5°	537.8	537.0	538.7	538.7	538.7	539.5	541.2	539.5	538.7	539.5	541.2
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1355.8	1360.6	1362.8	1362.8	1365.4	1364.2	1363.2
5°	1433.8	1442.4	1444.3	1452.5	1458.4	1456.5	1457.5
7.5°	1511.3	1525.2	1538.9	1545.2	1546.2	1549.9	1551.2
10°	1559.0	1570.4	1591.8	1588.6	1604.5	1613.6	1598.6
12.5°	1604.9	1620.2	1635.0	1639.1	1648.2	1651.1	1645.2
15°	1646.4	1654.6	1655.5	1653.2	1655.9	1653.7	1645.0
17.5°	1607.6	1594.3	1567.4	1554.6	1544.5	1529.6	1523.6
20°	1543.5	1504.3	1458.8	1440.6	1419.2	1377.3	1387.4
22.5°	1405.2	1360.5	1315.0	1261.9	1236.4	1196.8	1194.4
25°	1189.8	1112.9	1028.2	969.1	934.5	894.9	877.6
27.5°	925.1	828.2	758.8	723.7	691.8	660.4	659.1
30°	751.0	678.2	624.5	594.5	574.9	561.7	564.5
32.5°	633.0	583.2	547.0	522.0	507.6	497.6	497.4
35°	517.5	483.4	460.2	449.7	439.3	431.9	432.4
37.5°	442.9	422.4	409.5	397.9	391.4	387.8	385.8
40°	404.7	387.8	377.8	371.0	365.5	360.5	359.6
42.5°	374.4	360.5	350.4	345.1	340.0	336.4	335.6
45°	332.3	320.9	311.8	305.9	303.6	300.4	300.4
47.5°	295.6	284.4	277.3	273.6	269.7	267.5	267.4
50°	270.8	262.2	255.8	253.5	250.3	249.0	248.5
52.5°	248.6	242.2	237.6	236.0	234.7	232.9	233.3
55°	218.5	214.8	213.0	211.7	209.4	206.6	208.5
57.5°	193.1	190.0	185.1	180.8	178.7	176.8	177.5
60°	175.2	168.9	162.5	157.5	156.1	152.0	152.0
62.5°	152.7	143.7	135.9	133.1	131.7	129.8	129.5
65°	117.4	113.8	112.0	110.1	109.2	109.2	108.3
67.5°	97.3	95.9	93.9	93.4	92.5	92.2	91.9
70°	86.1	84.2	83.3	82.8	81.9	82.4	81.1
72.5°	75.1	73.7	73.5	72.3	71.7	71.8	70.8
75°	59.2	59.2	58.7	58.2	57.3	56.9	57.3
77.5°	45.5	45.6	44.8	44.7	44.6	44.7	44.2
80°	36.4	36.8	36.4	35.9	35.5	35.9	35.5
82.5°	28.8	28.1	28.0	27.9	27.8	27.6	27.5
85°	16.4	16.9	16.4	16.0	16.0	16.0	16.4
87.5°	12.4	12.8	13.0	13.0	13.0	13.0	12.7
90°	31.1	33.2	34.2	34.2	34.2	34.2	34.2
92.5°	77.5	68.8	62.3	61.5	58.2	59.0	57.4
95°	208.2	164.7	141.9	128.4	120.2	117.1	118.1
97.5°	518.2	406.1	331.3	281.8	256.3	241.1	232.5
100°	817.3	675.4	550.0	464.0	419.5	389.5	370.9
102.5°	1121.4	1017.6	884.8	791.4	715.4	677.9	652.6
105°	1375.6	1389.1	1355.0	1290.7	1226.5	1182.0	1167.4
107.5°	1357.0	1464.7	1514.8	1523.0	1519.4	1510.5	1491.2
110°	1299.0	1431.6	1516.5	1561.0	1580.7	1590.1	1589.0



TEST NUMBER: P331701-940

CATALOG NUMBER: SA2XXRDIP-C675D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1230.2	1371.9	1469.3	1531.2	1564.1	1581.8	1587.3
115°	1136.4	1272.0	1378.8	1452.3	1499.9	1526.9	1536.2
117.5°	1060.2	1183.2	1283.3	1358.3	1408.5	1437.0	1444.8
120°	1020.3	1130.2	1224.4	1296.9	1345.6	1375.6	1386.0
122.5°	987.2	1091.2	1176.3	1241.4	1289.2	1316.0	1324.6
125°	943.7	1034.8	1112.5	1172.6	1212.0	1237.9	1246.2
127.5°	901.4	987.4	1059.1	1111.5	1148.3	1170.7	1177.4
130°	873.3	955.1	1023.4	1074.2	1109.5	1130.2	1138.4
132.5°	846.8	921.9	986.1	1036.1	1071.3	1090.4	1097.8
135°	804.9	873.3	931.2	975.8	1010.0	1028.6	1032.8
137.5°	771.5	825.8	876.4	916.9	946.4	962.8	968.9
140°	750.0	797.6	843.2	876.4	903.3	918.8	925.1
142.5°	730.9	772.0	810.0	841.5	866.0	879.9	881.1
145°	706.5	738.6	768.7	793.4	811.1	821.4	824.6
147.5°	686.6	711.7	733.6	754.1	768.2	775.3	777.1
150°	673.3	695.1	713.7	729.2	741.7	747.9	748.9
152.5°	662.5	681.0	697.1	709.4	720.1	724.7	724.9
155°	645.3	660.8	672.3	683.7	690.9	695.1	693.0
157.5°	627.9	641.0	649.9	658.0	664.0	665.8	665.8
160°	616.4	627.8	635.0	642.2	647.4	648.5	648.5
162.5°	605.6	615.3	620.9	628.1	631.7	632.7	631.9
165°	589.4	596.6	600.8	604.9	609.1	609.1	608.1
167.5°	574.7	579.7	583.4	585.2	587.5	587.4	586.1
170°	565.6	569.7	571.8	572.8	576.0	574.9	572.8
172.5°	557.3	560.6	561.9	562.9	564.4	563.3	562.0
175°	548.0	549.0	550.0	550.0	551.1	550.0	548.0
177.5°	541.2	542.0	542.0	542.0	542.0	541.2	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7

(END OF REPORT)