

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332949-930

Luminaire Tested: **SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332949-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6642.0 lumens  
Efficiency: N/A  
Efficacy: 116.7 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332949-930  
CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41				
1	96	92	88	85	88	84	81	78	69	67	65	55	54	53	43	42	41	35				
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30				
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26				
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26	23				
5	68	56	49	43	61	52	45	40	43	38	34	35	32	29	28	25	23	20				
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18				
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	16				
8	53	42	34	29	49	38	32	27	32	27	23	27	23	20	21	19	16	14				
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	20	17	15	13				
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8688	8688	8688	8688
5°	10078	8715	7703	8715
10°	11922	8676	6874	8676
15°	13771	8596	5907	8596
20°	15332	8485	5342	8485
25°	15828	8378	4960	8378
30°	13856	8245	4729	8245
35°	10787	8051	4590	8051
40°	8088	7827	4515	7827
45°	6387	7470	4475	7470
50°	5392	7058	4346	7058
55°	4700	6602	4114	6602
60°	4229	6132	3641	6132
65°	3727	5624	3131	5624
70°	3356	5098	2825	5098
75°	2813	4517	2408	4517
80°	2380	3849	2259	3849
85°	2010	3010	2010	3010



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.3	1.6
10°-20°	314.5	4.7
20°-30°	492.0	7.4
30°-40°	546.9	8.2
40°-50°	485.2	7.3
50°-60°	378.1	5.7
60°-70°	247.6	3.7
70°-80°	121.7	1.8
80°-90°	33.7	0.5
90°-100°	43.3	0.7
100°-110°	276.2	4.2
110°-120°	528.4	8.0
120°-130°	670.8	10.1
130°-140°	717.7	10.8
140°-150°	671.1	10.1
150°-160°	541.2	8.1
160°-170°	349.1	5.3
170°-180°	120.3	1.8
0°-30°	910.8	13.7
0°-40°	1457.7	21.9
0°-60°	2321.1	34.9
0°-90°	2724.1	41.0
90°-120°	847.9	12.8
90°-150°	2907.4	43.8
90°-180°	3918.0	59.0
0°-180°	6642.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1076	1076	1076	1076	1076	
5°	1244	1075	950	1075	1244	126
15°	1648	1028	707	1028	1648	469
25°	1777	940	557	940	1777	788
35°	1094	817	466	817	1094	686
45°	559	654	392	654	559	443
55°	334	469	292	469	334	304
65°	195	294	164	294	195	196
75°	90	145	77	145	90	99
85°	22	32	22	32	22	25
90°	28	3	28	3	28	13
95°	28	52	28	52	28	22
105°	270	285	270	285	270	236
115°	536	532	536	532	536	531
125°	754	748	754	748	754	672
135°	935	928	935	928	935	720
145°	1076	1070	1076	1070	1076	673
155°	1173	1174	1173	1174	1173	541
165°	1232	1238	1232	1238	1232	348
175°	1259	1267	1259	1267	1259	120
180°	1267	1267	1267	1267	1267	



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1135.1	1138.3	1135.1	1134.8	1131.4	1130.3	1128.9	1124.5	1116.1	1111.3	1112.3
5°	1243.6	1254.4	1248.4	1247.5	1238.0	1228.4	1222.3	1208.4	1193.7	1183.7	1175.5
7.5°	1369.0	1375.2	1371.4	1365.3	1349.9	1341.2	1327.1	1308.8	1282.4	1262.2	1243.7
10°	1454.3	1459.5	1457.8	1446.5	1435.3	1412.3	1399.2	1373.7	1340.3	1313.9	1289.2
12.5°	1538.2	1543.9	1528.5	1529.1	1507.7	1489.6	1469.0	1436.8	1398.2	1364.2	1333.2
15°	1647.7	1640.8	1640.8	1632.1	1608.3	1583.1	1561.9	1528.0	1479.4	1438.7	1395.8
17.5°	1733.4	1735.8	1732.3	1711.8	1693.1	1667.0	1628.1	1588.6	1543.5	1488.8	1445.0
20°	1784.7	1784.7	1780.9	1766.9	1742.7	1714.9	1672.8	1629.9	1572.7	1517.6	1468.2
22.5°	1805.6	1806.9	1802.3	1790.9	1769.0	1742.0	1706.2	1662.6	1603.5	1541.6	1480.3
25°	1776.9	1785.2	1786.0	1783.0	1776.5	1760.0	1729.2	1684.6	1631.7	1564.5	1498.5
27.5°	1631.4	1641.8	1650.9	1665.9	1685.9	1696.2	1697.6	1675.0	1628.8	1564.1	1497.8
30°	1486.4	1495.1	1523.2	1560.1	1588.8	1614.8	1637.3	1643.4	1617.4	1559.3	1489.5
32.5°	1325.4	1337.3	1365.5	1405.1	1452.8	1496.8	1547.4	1573.3	1572.6	1537.7	1473.2
35°	1094.5	1103.1	1129.1	1170.8	1228.0	1293.5	1373.7	1436.1	1478.6	1475.5	1436.1
37.5°	882.6	892.4	918.8	953.2	1008.8	1089.8	1167.4	1253.4	1332.0	1376.1	1363.0
40°	767.5	767.9	793.5	829.1	881.1	951.8	1036.3	1131.7	1219.3	1290.9	1304.7
42.5°	676.6	676.7	693.6	731.9	769.4	835.9	916.6	1011.4	1113.9	1196.5	1233.3
45°	559.4	563.3	577.2	600.1	629.6	686.0	750.6	838.6	953.5	1051.5	1112.6
47.5°	473.7	479.4	488.2	507.0	530.4	568.0	621.4	700.5	794.0	901.8	988.8
50°	429.3	430.2	441.4	451.8	472.2	502.1	548.9	614.8	700.7	804.4	901.1
52.5°	391.1	390.9	397.7	410.9	427.5	450.8	488.6	548.6	624.8	717.6	817.4
55°	333.9	336.1	341.3	351.6	364.2	380.7	410.6	455.8	515.6	594.9	685.5
57.5°	290.3	291.5	295.5	299.9	311.5	323.5	345.9	377.2	427.7	492.7	577.2
60°	261.9	262.4	263.7	270.1	279.2	290.5	305.7	332.2	374.6	434.1	500.8
62.5°	234.2	234.9	236.9	241.7	248.7	256.5	272.4	293.7	328.8	379.6	439.8
65°	195.1	195.6	198.6	200.3	205.9	212.9	224.6	238.9	263.2	305.7	351.2
67.5°	163.1	163.1	163.2	165.6	169.4	174.1	181.1	192.5	210.8	236.9	277.0
70°	142.2	142.2	143.1	144.4	146.6	150.4	154.3	163.1	176.5	197.7	228.5
72.5°	122.8	123.1	124.0	124.3	125.4	128.6	131.5	137.1	147.0	163.1	187.9
75°	90.2	91.5	93.7	95.4	97.6	97.1	100.2	103.6	106.6	116.2	130.5
77.5°	67.1	66.4	66.7	68.2	68.4	68.9	71.0	73.7	76.0	80.5	85.6
80°	51.2	51.2	52.5	52.9	52.5	52.9	55.0	56.3	57.2	58.9	63.8
82.5°	38.6	39.4	39.0	39.4	39.6	40.0	41.9	42.2	43.0	43.7	45.7
85°	21.7	22.1	22.6	21.7	21.7	21.7	22.6	23.0	23.9	23.4	24.3
87.5°	13.3	12.9	13.1	13.0	13.3	12.8	12.9	13.4	12.4	12.5	12.1
90°	28.5	28.0	27.6	27.1	26.7	25.9	24.6	23.4	22.1	20.9	19.2
92.5°	26.2	26.1	26.0	25.9	25.8	25.1	23.9	22.6	21.4	20.1	18.4
95°	27.5	27.2	27.1	26.8	26.7	25.9	24.6	23.4	22.1	20.9	20.6
97.5°	26.5	26.3	26.1	25.9	25.7	25.5	25.4	25.3	25.1	25.0	48.5
100°	26.5	26.3	26.1	25.9	25.7	27.4	31.0	34.5	38.1	41.7	70.8
102.5°	27.3	27.2	27.2	27.1	27.1	46.4	85.0	123.6	162.2	200.8	204.6
105°	270.0	277.6	285.1	292.7	300.3	303.1	301.3	299.4	297.5	295.5	294.5
107.5°	376.3	375.4	374.7	373.9	373.1	372.2	371.3	370.4	369.4	368.5	367.0
110°	422.5	421.9	421.3	420.6	420.0	419.5	419.1	418.7	418.2	417.8	416.5



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	468.7	468.0	467.2	466.4	465.5	465.2	465.3	465.4	465.5	465.5	465.0
115°	536.2	536.2	536.2	536.2	536.2	536.0	535.6	535.2	534.8	534.3	534.5
117.5°	604.8	604.9	605.0	605.0	605.1	605.2	605.3	605.4	605.4	605.5	605.1
120°	648.0	648.4	648.8	649.2	649.6	649.6	649.2	648.8	648.4	648.0	648.2
122.5°	690.4	690.8	691.3	691.7	692.1	692.2	691.9	691.7	691.5	691.2	690.9
125°	754.1	753.9	753.7	753.4	753.3	752.8	752.2	751.5	750.9	750.3	750.7
127.5°	810.0	810.2	810.3	810.5	810.7	810.8	810.9	811.1	811.1	811.3	810.3
130°	847.8	847.8	847.8	847.8	847.8	847.7	847.6	847.3	847.1	846.9	846.3
132.5°	882.7	882.9	883.1	883.2	883.4	883.4	883.2	883.0	882.7	882.6	881.7
135°	935.0	934.6	934.2	933.8	933.4	932.9	932.5	932.1	931.6	931.2	930.4
137.5°	979.7	979.8	980.0	980.2	980.2	980.1	979.6	979.2	978.7	978.2	977.3
140°	1010.8	1010.6	1010.4	1010.2	1010.0	1009.6	1008.9	1008.3	1007.6	1007.1	1006.6
142.5°	1036.6	1036.6	1036.5	1036.5	1036.4	1036.2	1035.7	1035.3	1034.8	1034.3	1034.0
145°	1076.2	1075.8	1075.3	1074.9	1074.5	1074.2	1074.0	1073.7	1073.6	1073.3	1073.3
147.5°	1109.0	1108.7	1108.6	1108.3	1108.1	1107.9	1107.7	1107.6	1107.4	1107.3	1107.4
150°	1130.2	1130.0	1129.8	1129.5	1129.4	1129.2	1129.2	1129.2	1129.2	1129.2	1129.4
152.5°	1148.3	1148.5	1148.6	1148.8	1148.8	1148.8	1148.4	1148.1	1147.8	1147.5	1147.8
155°	1172.8	1173.5	1174.0	1174.7	1175.3	1175.3	1174.4	1173.5	1172.7	1171.8	1172.5
157.5°	1193.3	1194.3	1195.5	1196.5	1197.7	1197.7	1196.5	1195.5	1194.3	1193.3	1194.0
160°	1206.9	1208.2	1209.4	1210.7	1211.9	1211.9	1210.7	1209.4	1208.2	1206.9	1207.1
162.5°	1217.5	1219.0	1220.4	1221.8	1223.3	1223.4	1222.1	1220.8	1219.5	1218.3	1218.5
165°	1232.5	1234.4	1236.2	1238.2	1240.1	1240.2	1238.5	1236.8	1235.1	1233.5	1233.5
167.5°	1243.7	1245.8	1247.9	1250.0	1252.1	1252.2	1250.3	1248.5	1246.7	1244.8	1245.0
170°	1250.5	1252.6	1254.7	1256.8	1258.9	1259.1	1257.4	1255.7	1254.1	1252.4	1252.1
172.5°	1254.3	1256.5	1258.8	1261.1	1263.4	1263.6	1262.0	1260.3	1258.6	1256.9	1256.7
175°	1259.0	1261.5	1264.0	1266.6	1269.1	1269.4	1267.5	1265.7	1263.7	1261.8	1261.7
177.5°	1262.1	1264.0	1266.1	1268.1	1270.2	1270.5	1269.1	1267.8	1266.4	1265.1	1264.8
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1108.8	1104.0	1101.6	1096.0	1089.4	1085.9	1082.8	1078.3	1072.4	1066.2	1061.6
5°	1165.1	1154.7	1141.7	1126.1	1112.2	1098.8	1087.0	1075.4	1061.9	1048.0	1034.1
7.5°	1222.9	1202.4	1180.3	1154.7	1129.8	1107.2	1086.4	1066.4	1043.8	1023.7	1005.3
10°	1263.1	1235.3	1204.5	1172.1	1139.5	1111.3	1083.6	1058.4	1030.7	1006.0	985.1
12.5°	1295.7	1263.1	1226.0	1185.5	1146.5	1112.4	1080.4	1047.7	1016.1	989.3	961.6
15°	1349.8	1305.1	1255.3	1206.7	1156.0	1109.6	1066.7	1028.5	992.5	954.8	928.4
17.5°	1387.0	1334.0	1273.4	1215.0	1155.1	1100.4	1050.9	1005.4	963.9	925.4	893.9
20°	1409.2	1350.7	1283.4	1217.2	1149.9	1091.4	1038.0	987.7	944.9	903.2	870.7
22.5°	1421.7	1356.9	1283.4	1214.0	1144.4	1081.0	1022.5	970.0	923.3	881.7	845.7
25°	1425.7	1356.3	1281.3	1201.5	1125.2	1058.0	997.3	940.5	888.4	846.9	808.7
27.5°	1420.2	1338.5	1261.6	1179.7	1101.0	1030.1	966.5	906.8	854.7	810.0	770.9
30°	1411.9	1324.2	1241.9	1156.8	1077.1	1009.0	941.8	884.5	830.4	784.0	744.5
32.5°	1393.8	1306.9	1218.2	1131.2	1050.4	980.2	916.5	858.9	805.8	758.3	716.4
35°	1358.0	1270.1	1173.8	1084.4	1005.1	932.2	872.5	816.9	766.2	715.4	671.2
37.5°	1311.0	1221.1	1125.3	1027.4	948.0	879.3	824.3	772.3	722.8	676.5	627.5
40°	1266.6	1184.6	1085.7	988.6	907.1	840.7	790.0	742.7	692.9	646.9	597.9
42.5°	1212.8	1143.0	1043.1	945.6	865.1	801.2	754.0	707.8	662.3	617.8	566.7
45°	1123.1	1070.2	976.5	882.8	801.8	738.4	695.0	654.3	614.4	571.9	523.8
47.5°	1020.2	984.4	903.5	807.6	732.6	675.6	633.7	600.5	566.7	524.2	482.0
50°	948.8	925.8	847.7	760.1	688.6	636.1	593.2	562.0	533.8	493.0	455.3
52.5°	872.5	860.2	794.3	710.5	641.4	590.0	553.3	525.2	496.7	462.8	427.5
55°	756.2	762.7	706.8	634.4	569.3	525.9	492.6	469.1	444.9	416.3	389.0
57.5°	637.4	661.1	623.6	560.0	499.0	459.0	433.9	414.2	393.8	370.1	346.7
60°	566.3	586.2	565.0	509.1	455.8	418.4	395.0	379.8	359.5	337.8	320.0
62.5°	496.9	518.3	505.6	460.5	411.0	378.9	358.2	344.1	329.0	310.1	291.6
65°	409.8	423.6	417.6	386.4	351.2	323.9	304.8	294.4	280.5	266.7	250.2
67.5°	313.8	340.6	337.1	320.5	290.2	268.8	256.3	247.1	234.5	224.2	213.0
70°	258.0	282.7	282.3	268.8	252.3	232.4	223.7	216.0	204.6	194.7	185.6
72.5°	211.2	233.8	237.2	226.9	215.6	200.5	192.2	186.8	175.9	169.0	161.7
75°	147.9	164.4	168.7	168.7	163.5	155.6	148.3	144.8	137.1	130.9	126.6
77.5°	96.9	107.4	114.1	115.7	116.5	113.9	107.8	105.3	99.4	97.2	93.0
80°	68.5	75.4	83.2	85.9	88.1	87.2	84.5	82.8	77.2	75.0	73.3
82.5°	47.4	51.2	57.6	63.3	62.7	65.0	62.7	61.3	57.1	56.3	54.5
85°	24.7	25.1	26.0	29.9	32.1	32.9	33.4	32.5	31.2	31.2	28.2
87.5°	11.8	11.2	11.5	11.1	11.0	11.9	12.5	12.4	11.8	11.2	10.6
90°	17.4	15.8	14.1	12.1	9.8	7.5	5.1	2.9	5.1	7.5	9.8
92.5°	16.7	15.0	13.4	12.5	12.3	12.2	12.1	11.9	12.1	12.2	12.3
95°	20.4	20.2	20.0	23.5	30.7	37.7	44.9	52.1	44.9	37.7	30.7
97.5°	72.0	95.5	119.0	128.5	124.0	119.6	115.1	110.6	115.1	119.6	124.0
100°	99.8	128.8	157.9	170.6	166.7	163.0	159.1	155.4	159.1	163.0	166.7
102.5°	208.4	212.2	216.0	216.5	213.7	210.9	208.1	205.4	208.1	210.9	213.7
105°	293.4	292.4	291.4	290.2	288.9	287.6	286.4	285.1	286.4	287.6	288.9
107.5°	365.7	364.2	362.8	361.7	361.1	360.5	359.9	359.2	359.9	360.5	361.1
110°	415.2	414.0	412.7	411.8	411.2	410.5	409.9	409.3	409.9	410.5	411.2





TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	464.3	463.7	463.2	462.3	461.1	460.0	458.9	457.8	458.9	460.0	461.1
115°	534.8	534.9	535.2	534.9	534.3	533.7	533.0	532.4	533.0	533.7	534.3
117.5°	604.6	604.1	603.6	603.0	602.2	601.4	600.5	599.7	600.5	601.4	602.2
120°	648.4	648.7	648.8	648.5	647.7	646.9	646.0	645.1	646.0	646.9	647.7
122.5°	690.6	690.3	690.0	689.6	689.1	688.6	688.1	687.5	688.1	688.6	689.1
125°	751.1	751.5	752.0	751.8	750.9	750.1	749.3	748.4	749.3	750.1	750.9
127.5°	809.3	808.4	807.4	806.8	806.7	806.4	806.2	806.0	806.2	806.4	806.7
130°	845.6	845.1	844.4	844.0	843.8	843.6	843.3	843.1	843.3	843.6	843.8
132.5°	880.9	880.1	879.4	878.7	878.4	878.0	877.6	877.3	877.6	878.0	878.4
135°	929.5	928.7	927.9	927.6	927.7	928.0	928.2	928.4	928.2	928.0	927.7
137.5°	976.4	975.4	974.5	974.0	974.0	973.9	973.8	973.7	973.8	973.9	974.0
140°	1006.2	1005.8	1005.3	1004.9	1004.5	1004.0	1003.6	1003.2	1003.6	1004.0	1004.5
142.5°	1033.8	1033.6	1033.3	1032.8	1032.0	1031.3	1030.5	1029.7	1030.5	1031.3	1032.0
145°	1073.3	1073.3	1073.3	1073.0	1072.4	1071.8	1071.1	1070.5	1071.1	1071.8	1072.4
147.5°	1107.7	1107.9	1108.1	1107.6	1106.4	1105.2	1104.1	1102.9	1104.1	1105.2	1106.4
150°	1129.7	1129.8	1130.1	1129.8	1128.9	1128.0	1127.2	1126.4	1127.2	1128.0	1128.9
152.5°	1148.2	1148.6	1148.9	1148.8	1148.1	1147.5	1146.8	1146.1	1146.8	1147.5	1148.1
155°	1173.1	1173.8	1174.4	1174.6	1174.4	1174.2	1173.9	1173.8	1173.9	1174.2	1174.4
157.5°	1194.7	1195.4	1196.1	1196.5	1196.7	1196.8	1196.9	1197.0	1196.9	1196.8	1196.7
160°	1207.3	1207.5	1207.8	1208.2	1208.8	1209.4	1210.1	1210.7	1210.1	1209.4	1208.8
162.5°	1218.7	1218.9	1219.1	1219.6	1220.4	1221.2	1222.1	1222.8	1222.1	1221.2	1220.4
165°	1233.5	1233.5	1233.5	1234.0	1235.0	1236.1	1237.1	1238.2	1237.1	1236.1	1235.0
167.5°	1245.0	1245.2	1245.3	1245.9	1247.0	1248.1	1249.2	1250.3	1249.2	1248.1	1247.0
170°	1252.0	1251.7	1251.6	1252.1	1253.4	1254.6	1255.9	1257.1	1255.9	1254.6	1253.4
172.5°	1256.5	1256.3	1256.1	1256.6	1257.8	1259.1	1260.4	1261.7	1260.4	1259.1	1257.8
175°	1261.4	1261.2	1261.0	1261.5	1262.8	1264.0	1265.3	1266.6	1265.3	1264.0	1262.8
177.5°	1264.4	1264.0	1263.7	1264.1	1265.3	1266.5	1267.7	1268.9	1267.7	1266.5	1265.3
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1056.8	1053.3	1048.8	1043.6	1037.4	1031.8	1029.4	1031.4	1032.5	1029.7	1029.4
5°	1024.6	1013.7	1005.1	992.1	981.7	973.0	966.9	964.3	965.2	958.3	956.5
7.5°	988.5	975.6	961.4	946.0	931.6	918.8	912.2	908.5	901.2	898.0	892.7
10°	965.2	947.9	934.0	915.7	899.3	884.1	876.8	870.7	863.3	859.8	852.5
12.5°	941.3	921.1	905.9	887.0	870.2	851.8	844.8	833.6	822.1	814.7	805.3
15°	907.5	883.3	864.6	842.0	822.1	801.3	782.7	761.8	754.1	737.6	728.1
17.5°	868.0	843.4	820.4	790.1	759.4	733.5	713.6	693.7	681.8	671.2	666.3
20°	842.0	819.5	787.4	752.3	718.0	689.4	673.4	660.4	647.3	640.0	634.8
22.5°	817.4	788.6	751.4	713.5	679.2	656.8	643.2	629.8	619.3	612.3	605.3
25°	776.2	738.4	699.0	655.6	632.2	612.7	597.9	587.1	580.6	571.5	568.0
27.5°	733.8	688.0	644.5	615.4	591.0	573.2	560.3	552.1	543.9	538.1	533.6
30°	701.2	654.8	615.7	588.0	563.3	548.5	538.1	528.6	522.0	517.3	513.8
32.5°	668.9	622.5	589.7	559.9	540.4	525.9	514.9	507.8	502.6	496.5	494.4
35°	622.2	581.1	552.4	525.5	505.6	492.6	483.9	476.5	472.2	470.4	469.1
37.5°	577.4	543.6	512.9	490.8	473.0	462.8	452.6	449.0	446.0	442.9	444.3
40°	548.9	517.3	490.0	466.6	452.2	441.0	434.9	430.6	428.0	428.0	428.0
42.5°	524.3	493.3	466.8	445.7	431.5	421.9	415.2	411.5	410.6	410.3	412.4
45°	486.1	457.5	430.6	413.2	401.0	391.5	387.7	384.6	384.6	386.4	386.8
47.5°	448.2	421.3	399.8	380.3	369.2	363.3	359.9	358.3	358.5	360.3	362.2
50°	424.9	398.5	377.2	359.9	349.5	343.8	340.8	340.0	340.8	340.8	343.8
52.5°	399.6	375.9	355.1	340.5	328.6	323.3	321.7	320.5	321.1	322.5	323.8
55°	362.5	341.3	321.3	307.4	298.7	295.3	291.4	291.8	291.0	291.8	291.8
57.5°	325.3	306.2	287.6	276.6	269.0	264.0	259.8	261.0	259.7	259.5	258.8
60°	301.3	280.5	265.8	255.8	247.1	242.8	238.9	239.8	238.5	237.6	235.9
62.5°	275.3	258.0	243.9	234.3	227.4	222.3	218.4	217.6	214.6	211.6	207.8
65°	237.6	223.3	210.8	201.6	195.1	191.2	188.2	185.6	179.0	172.1	168.7
67.5°	201.0	190.6	178.9	171.2	165.9	160.8	155.0	150.6	144.5	140.6	138.5
70°	177.3	167.4	157.4	150.0	144.4	139.7	133.1	130.1	125.7	124.0	121.8
72.5°	154.8	145.5	136.2	129.6	123.6	119.8	114.7	111.7	109.8	109.1	107.0
75°	120.6	113.2	106.2	100.2	95.4	92.8	90.7	88.5	87.6	83.6	81.5
77.5°	88.0	83.1	78.8	74.4	71.0	69.3	65.1	62.6	61.1	59.4	58.9
80°	68.5	65.1	60.7	58.1	53.3	51.6	49.9	49.4	49.0	48.6	48.1
82.5°	51.5	48.0	43.7	42.2	40.8	39.8	38.7	38.3	37.9	38.2	38.1
85°	26.0	24.3	24.3	23.9	23.4	23.0	22.6	22.6	22.1	22.6	22.1
87.5°	11.1	11.2	11.5	11.1	11.8	12.1	12.1	12.3	12.9	12.5	12.6
90°	12.1	14.1	15.8	17.4	19.2	20.9	22.1	23.4	24.6	25.9	26.7
92.5°	12.5	13.4	15.0	16.7	18.4	20.1	21.4	22.6	23.9	25.1	25.8
95°	23.5	20.0	20.2	20.4	20.6	20.9	22.1	23.4	24.6	25.9	26.7
97.5°	128.5	119.0	95.5	72.0	48.5	25.0	25.1	25.3	25.4	25.5	25.7
100°	170.6	157.9	128.8	99.8	70.8	41.7	38.1	34.5	31.0	27.4	25.7
102.5°	216.5	216.0	212.2	208.4	204.6	200.8	162.2	123.6	85.0	46.4	27.1
105°	290.2	291.4	292.4	293.4	294.5	295.5	297.5	299.4	301.3	303.1	300.3
107.5°	361.7	362.8	364.2	365.7	367.0	368.5	369.4	370.4	371.3	372.2	373.1
110°	411.8	412.7	414.0	415.2	416.5	417.8	418.2	418.7	419.1	419.5	420.0



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	462.3	463.2	463.7	464.3	465.0	465.5	465.5	465.4	465.3	465.2	465.5
115°	534.9	535.2	534.9	534.8	534.5	534.3	534.8	535.2	535.6	536.0	536.2
117.5°	603.0	603.6	604.1	604.6	605.1	605.5	605.4	605.4	605.3	605.2	605.1
120°	648.5	648.8	648.7	648.4	648.2	648.0	648.4	648.8	649.2	649.6	649.6
122.5°	689.6	690.0	690.3	690.6	690.9	691.2	691.5	691.7	691.9	692.2	692.1
125°	751.8	752.0	751.5	751.1	750.7	750.3	750.9	751.5	752.2	752.8	753.3
127.5°	806.8	807.4	808.4	809.3	810.3	811.3	811.1	811.1	810.9	810.8	810.7
130°	844.0	844.4	845.1	845.6	846.3	846.9	847.1	847.3	847.6	847.7	847.8
132.5°	878.7	879.4	880.1	880.9	881.7	882.6	882.7	883.0	883.2	883.4	883.4
135°	927.6	927.9	928.7	929.5	930.4	931.2	931.6	932.1	932.5	932.9	933.4
137.5°	974.0	974.5	975.4	976.4	977.3	978.2	978.7	979.2	979.6	980.1	980.2
140°	1004.9	1005.3	1005.8	1006.2	1006.6	1007.1	1007.6	1008.3	1008.9	1009.6	1010.0
142.5°	1032.8	1033.3	1033.6	1033.8	1034.0	1034.3	1034.8	1035.3	1035.7	1036.2	1036.4
145°	1073.0	1073.3	1073.3	1073.3	1073.3	1073.3	1073.6	1073.7	1074.0	1074.2	1074.5
147.5°	1107.6	1108.1	1107.9	1107.7	1107.4	1107.3	1107.4	1107.6	1107.7	1107.9	1108.1
150°	1129.8	1130.1	1129.8	1129.7	1129.4	1129.2	1129.2	1129.2	1129.2	1129.2	1129.4
152.5°	1148.8	1148.9	1148.6	1148.2	1147.8	1147.5	1147.8	1148.1	1148.4	1148.8	1148.8
155°	1174.6	1174.4	1173.8	1173.1	1172.5	1171.8	1172.7	1173.5	1174.4	1175.3	1175.3
157.5°	1196.5	1196.1	1195.4	1194.7	1194.0	1193.3	1194.3	1195.5	1196.5	1197.7	1197.7
160°	1208.2	1207.8	1207.5	1207.3	1207.1	1206.9	1208.2	1209.4	1210.7	1211.9	1211.9
162.5°	1219.6	1219.1	1218.9	1218.7	1218.5	1218.3	1219.5	1220.8	1222.1	1223.4	1223.3
165°	1234.0	1233.5	1233.5	1233.5	1233.5	1233.5	1235.1	1236.8	1238.5	1240.2	1240.1
167.5°	1245.9	1245.3	1245.2	1245.0	1245.0	1244.8	1246.7	1248.5	1250.3	1252.2	1252.1
170°	1252.1	1251.6	1251.7	1252.0	1252.1	1252.4	1254.1	1255.7	1257.4	1259.1	1258.9
172.5°	1256.6	1256.1	1256.3	1256.5	1256.7	1256.9	1258.6	1260.3	1262.0	1263.6	1263.4
175°	1261.5	1261.0	1261.2	1261.4	1261.7	1261.8	1263.7	1265.7	1267.5	1269.4	1269.1
177.5°	1264.1	1263.7	1264.0	1264.4	1264.8	1265.1	1266.4	1267.8	1269.1	1270.5	1270.2
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1027.3	1028.0	1025.6	1024.8	1025.6	1028.0	1027.3	1029.4	1029.7	1032.5	1031.4
5°	953.1	952.2	950.1	950.5	950.1	952.2	953.1	956.5	958.3	965.2	964.3
7.5°	889.6	886.2	887.1	883.7	887.1	886.2	889.6	892.7	898.0	901.2	908.5
10°	850.8	846.0	842.0	838.6	842.0	846.0	850.8	852.5	859.8	863.3	870.7
12.5°	797.7	793.6	788.3	789.4	788.3	793.6	797.7	805.3	814.7	822.1	833.6
15°	722.4	715.9	705.5	706.8	705.5	715.9	722.4	728.1	737.6	754.1	761.8
17.5°	658.7	658.8	654.0	655.1	654.0	658.8	658.7	666.3	671.2	681.8	693.7
20°	625.7	622.6	623.1	621.8	623.1	622.6	625.7	634.8	640.0	647.3	660.4
22.5°	602.8	599.1	596.1	593.4	596.1	599.1	602.8	605.3	612.3	619.3	629.8
25°	564.1	561.5	557.6	556.8	557.6	561.5	564.1	568.0	571.5	580.6	587.1
27.5°	530.1	529.6	528.1	526.0	528.1	529.6	530.1	533.6	538.1	543.9	552.1
30°	510.4	509.5	508.6	507.3	508.6	509.5	510.4	513.8	517.3	522.0	528.6
32.5°	492.7	492.1	491.3	491.4	491.3	492.1	492.7	494.4	496.5	502.6	507.8
35°	467.4	467.0	466.1	465.7	466.1	467.0	467.4	469.1	470.4	472.2	476.5
37.5°	443.8	445.0	444.4	444.3	444.4	445.0	443.8	444.3	442.9	446.0	449.0
40°	427.5	428.0	428.8	428.4	428.8	428.0	427.5	428.0	428.0	428.0	430.6
42.5°	414.0	414.1	415.3	413.8	415.3	414.1	414.0	412.4	410.3	410.6	411.5
45°	389.8	392.4	392.0	392.0	392.0	392.4	389.8	386.8	386.4	384.6	384.6
47.5°	363.4	365.6	366.2	366.2	366.2	365.6	363.4	362.2	360.3	358.5	358.3
50°	346.0	345.1	346.4	346.0	346.4	345.1	346.0	343.8	340.8	340.8	340.0
52.5°	324.9	325.1	325.0	324.5	325.0	325.1	324.9	323.8	322.5	321.1	320.5
55°	292.3	292.7	291.8	292.3	291.8	292.7	292.3	291.8	291.8	291.0	291.8
57.5°	256.9	254.8	255.7	254.6	255.7	254.8	256.9	258.8	259.5	259.7	261.0
60°	231.5	228.0	227.2	225.5	227.2	228.0	231.5	235.9	237.6	238.5	239.8
62.5°	203.1	200.6	197.7	199.1	197.7	200.6	203.1	207.8	211.6	214.6	217.6
65°	165.2	163.5	162.2	163.9	162.2	163.5	165.2	168.7	172.1	179.0	185.6
67.5°	136.7	135.8	135.8	134.9	135.8	135.8	136.7	138.5	140.6	144.5	150.6
70°	121.8	120.6	120.6	119.7	120.6	120.6	121.8	121.8	124.0	125.7	130.1
72.5°	106.6	105.3	105.7	105.1	105.7	105.3	106.6	107.0	109.1	109.8	111.7
75°	78.9	76.7	76.7	77.2	76.7	76.7	78.9	81.5	83.6	87.6	88.5
77.5°	58.9	58.5	59.0	58.3	59.0	58.5	58.9	58.9	59.4	61.1	62.6
80°	48.1	47.7	47.3	48.6	47.3	47.7	48.1	48.1	48.6	49.0	49.4
82.5°	37.3	37.3	37.2	38.9	37.2	37.3	37.3	38.1	38.2	37.9	38.3
85°	22.6	21.7	22.6	21.7	22.6	21.7	22.6	22.1	22.6	22.1	22.6
87.5°	13.4	13.1	12.9	13.3	12.9	13.1	13.4	12.6	12.5	12.9	12.3
90°	27.1	27.6	28.0	28.5	28.0	27.6	27.1	26.7	25.9	24.6	23.4
92.5°	25.9	26.0	26.1	26.2	26.1	26.0	25.9	25.8	25.1	23.9	22.6
95°	26.8	27.1	27.2	27.5	27.2	27.1	26.8	26.7	25.9	24.6	23.4
97.5°	25.9	26.1	26.3	26.5	26.3	26.1	25.9	25.7	25.5	25.4	25.3
100°	25.9	26.1	26.3	26.5	26.3	26.1	25.9	25.7	27.4	31.0	34.5
102.5°	27.1	27.2	27.2	27.3	27.2	27.2	27.1	27.1	46.4	85.0	123.6
105°	292.7	285.1	277.6	270.0	277.6	285.1	292.7	300.3	303.1	301.3	299.4
107.5°	373.9	374.7	375.4	376.3	375.4	374.7	373.9	373.1	372.2	371.3	370.4
110°	420.6	421.3	421.9	422.5	421.9	421.3	420.6	420.0	419.5	419.1	418.7



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	466.4	467.2	468.0	468.7	468.0	467.2	466.4	465.5	465.2	465.3	465.4
115°	536.2	536.2	536.2	536.2	536.2	536.2	536.2	536.2	536.0	535.6	535.2
117.5°	605.0	605.0	604.9	604.8	604.9	605.0	605.0	605.1	605.2	605.3	605.4
120°	649.2	648.8	648.4	648.0	648.4	648.8	649.2	649.6	649.6	649.2	648.8
122.5°	691.7	691.3	690.8	690.4	690.8	691.3	691.7	692.1	692.2	691.9	691.7
125°	753.4	753.7	753.9	754.1	753.9	753.7	753.4	753.3	752.8	752.2	751.5
127.5°	810.5	810.3	810.2	810.0	810.2	810.3	810.5	810.7	810.8	810.9	811.1
130°	847.8	847.8	847.8	847.8	847.8	847.8	847.8	847.8	847.7	847.6	847.3
132.5°	883.2	883.1	882.9	882.7	882.9	883.1	883.2	883.4	883.4	883.2	883.0
135°	933.8	934.2	934.6	935.0	934.6	934.2	933.8	933.4	932.9	932.5	932.1
137.5°	980.2	980.0	979.8	979.7	979.8	980.0	980.2	980.2	980.1	979.6	979.2
140°	1010.2	1010.4	1010.6	1010.8	1010.6	1010.4	1010.2	1010.0	1009.6	1008.9	1008.3
142.5°	1036.5	1036.5	1036.6	1036.6	1036.6	1036.5	1036.5	1036.4	1036.2	1035.7	1035.3
145°	1074.9	1075.3	1075.8	1076.2	1075.8	1075.3	1074.9	1074.5	1074.2	1074.0	1073.7
147.5°	1108.3	1108.6	1108.7	1109.0	1108.7	1108.6	1108.3	1108.1	1107.9	1107.7	1107.6
150°	1129.5	1129.8	1130.0	1130.2	1130.0	1129.8	1129.5	1129.4	1129.2	1129.2	1129.2
152.5°	1148.8	1148.6	1148.5	1148.3	1148.5	1148.6	1148.8	1148.8	1148.8	1148.4	1148.1
155°	1174.7	1174.0	1173.5	1172.8	1173.5	1174.0	1174.7	1175.3	1175.3	1174.4	1173.5
157.5°	1196.5	1195.5	1194.3	1193.3	1194.3	1195.5	1196.5	1197.7	1197.7	1196.5	1195.5
160°	1210.7	1209.4	1208.2	1206.9	1208.2	1209.4	1210.7	1211.9	1211.9	1210.7	1209.4
162.5°	1221.8	1220.4	1219.0	1217.5	1219.0	1220.4	1221.8	1223.3	1223.4	1222.1	1220.8
165°	1238.2	1236.2	1234.4	1232.5	1234.4	1236.2	1238.2	1240.1	1240.2	1238.5	1236.8
167.5°	1250.0	1247.9	1245.8	1243.7	1245.8	1247.9	1250.0	1252.1	1252.2	1250.3	1248.5
170°	1256.8	1254.7	1252.6	1250.5	1252.6	1254.7	1256.8	1258.9	1259.1	1257.4	1255.7
172.5°	1261.1	1258.8	1256.5	1254.3	1256.5	1258.8	1261.1	1263.4	1263.6	1262.0	1260.3
175°	1266.6	1264.0	1261.5	1259.0	1261.5	1264.0	1266.6	1269.1	1269.4	1267.5	1265.7
177.5°	1268.1	1266.1	1264.0	1262.1	1264.0	1266.1	1268.1	1270.2	1270.5	1269.1	1267.8
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332949-930  
 CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1029.4	1031.8	1037.4	1043.6	1048.8	1053.3	1056.8	1061.6	1066.2	1072.4	1078.3
5°	966.9	973.0	981.7	992.1	1005.1	1013.7	1024.6	1034.1	1048.0	1061.9	1075.4
7.5°	912.2	918.8	931.6	946.0	961.4	975.6	988.5	1005.3	1023.7	1043.8	1066.4
10°	876.8	884.1	899.3	915.7	934.0	947.9	965.2	985.1	1006.0	1030.7	1058.4
12.5°	844.8	851.8	870.2	887.0	905.9	921.1	941.3	961.6	989.3	1016.1	1047.7
15°	782.7	801.3	822.1	842.0	864.6	883.3	907.5	928.4	954.8	992.5	1028.5
17.5°	713.6	733.5	759.4	790.1	820.4	843.4	868.0	893.9	925.4	963.9	1005.4
20°	673.4	689.4	718.0	752.3	787.4	819.5	842.0	870.7	903.2	944.9	987.7
22.5°	643.2	656.8	679.2	713.5	751.4	788.6	817.4	845.7	881.7	923.3	970.0
25°	597.9	612.7	632.2	655.6	699.0	738.4	776.2	808.7	846.9	888.4	940.5
27.5°	560.3	573.2	591.0	615.4	644.5	688.0	733.8	770.9	810.0	854.7	906.8
30°	538.1	548.5	563.3	588.0	615.7	654.8	701.2	744.5	784.0	830.4	884.5
32.5°	514.9	525.9	540.4	559.9	589.7	622.5	668.9	716.4	758.3	805.8	858.9
35°	483.9	492.6	505.6	525.5	552.4	581.1	622.2	671.2	715.4	766.2	816.9
37.5°	452.6	462.8	473.0	490.8	512.9	543.6	577.4	627.5	676.5	722.8	772.3
40°	434.9	441.0	452.2	466.6	490.0	517.3	548.9	597.9	646.9	692.9	742.7
42.5°	415.2	421.9	431.5	445.7	466.8	493.3	524.3	566.7	617.8	662.3	707.8
45°	387.7	391.5	401.0	413.2	430.6	457.5	486.1	523.8	571.9	614.4	654.3
47.5°	359.9	363.3	369.2	380.3	399.8	421.3	448.2	482.0	524.2	566.7	600.5
50°	340.8	343.8	349.5	359.9	377.2	398.5	424.9	455.3	493.0	533.8	562.0
52.5°	321.7	323.3	328.6	340.5	355.1	375.9	399.6	427.5	462.8	496.7	525.2
55°	291.4	295.3	298.7	307.4	321.3	341.3	362.5	389.0	416.3	444.9	469.1
57.5°	259.8	264.0	269.0	276.6	287.6	306.2	325.3	346.7	370.1	393.8	414.2
60°	238.9	242.8	247.1	255.8	265.8	280.5	301.3	320.0	337.8	359.5	379.8
62.5°	218.4	222.3	227.4	234.3	243.9	258.0	275.3	291.6	310.1	329.0	344.1
65°	188.2	191.2	195.1	201.6	210.8	223.3	237.6	250.2	266.7	280.5	294.4
67.5°	155.0	160.8	165.9	171.2	178.9	190.6	201.0	213.0	224.2	234.5	247.1
70°	133.1	139.7	144.4	150.0	157.4	167.4	177.3	185.6	194.7	204.6	216.0
72.5°	114.7	119.8	123.6	129.6	136.2	145.5	154.8	161.7	169.0	175.9	186.8
75°	90.7	92.8	95.4	100.2	106.2	113.2	120.6	126.6	130.9	137.1	144.8
77.5°	65.1	69.3	71.0	74.4	78.8	83.1	88.0	93.0	97.2	99.4	105.3
80°	49.9	51.6	53.3	58.1	60.7	65.1	68.5	73.3	75.0	77.2	82.8
82.5°	38.7	39.8	40.8	42.2	43.7	48.0	51.5	54.5	56.3	57.1	61.3
85°	22.6	23.0	23.4	23.9	24.3	24.3	26.0	28.2	31.2	31.2	32.5
87.5°	12.1	12.1	11.8	11.1	11.5	11.2	11.1	10.6	11.2	11.8	12.4
90°	22.1	20.9	19.2	17.4	15.8	14.1	12.1	9.8	7.5	5.1	2.9
92.5°	21.4	20.1	18.4	16.7	15.0	13.4	12.5	12.3	12.2	12.1	11.9
95°	22.1	20.9	20.6	20.4	20.2	20.0	23.5	30.7	37.7	44.9	52.1
97.5°	25.1	25.0	48.5	72.0	95.5	119.0	128.5	124.0	119.6	115.1	110.6
100°	38.1	41.7	70.8	99.8	128.8	157.9	170.6	166.7	163.0	159.1	155.4
102.5°	162.2	200.8	204.6	208.4	212.2	216.0	216.5	213.7	210.9	208.1	205.4
105°	297.5	295.5	294.5	293.4	292.4	291.4	290.2	288.9	287.6	286.4	285.1
107.5°	369.4	368.5	367.0	365.7	364.2	362.8	361.7	361.1	360.5	359.9	359.2
110°	418.2	417.8	416.5	415.2	414.0	412.7	411.8	411.2	410.5	409.9	409.3



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	465.5	465.5	465.0	464.3	463.7	463.2	462.3	461.1	460.0	458.9	457.8
115°	534.8	534.3	534.5	534.8	534.9	535.2	534.9	534.3	533.7	533.0	532.4
117.5°	605.4	605.5	605.1	604.6	604.1	603.6	603.0	602.2	601.4	600.5	599.7
120°	648.4	648.0	648.2	648.4	648.7	648.8	648.5	647.7	646.9	646.0	645.1
122.5°	691.5	691.2	690.9	690.6	690.3	690.0	689.6	689.1	688.6	688.1	687.5
125°	750.9	750.3	750.7	751.1	751.5	752.0	751.8	750.9	750.1	749.3	748.4
127.5°	811.1	811.3	810.3	809.3	808.4	807.4	806.8	806.7	806.4	806.2	806.0
130°	847.1	846.9	846.3	845.6	845.1	844.4	844.0	843.8	843.6	843.3	843.1
132.5°	882.7	882.6	881.7	880.9	880.1	879.4	878.7	878.4	878.0	877.6	877.3
135°	931.6	931.2	930.4	929.5	928.7	927.9	927.6	927.7	928.0	928.2	928.4
137.5°	978.7	978.2	977.3	976.4	975.4	974.5	974.0	974.0	973.9	973.8	973.7
140°	1007.6	1007.1	1006.6	1006.2	1005.8	1005.3	1004.9	1004.5	1004.0	1003.6	1003.2
142.5°	1034.8	1034.3	1034.0	1033.8	1033.6	1033.3	1032.8	1032.0	1031.3	1030.5	1029.7
145°	1073.6	1073.3	1073.3	1073.3	1073.3	1073.3	1073.0	1072.4	1071.8	1071.1	1070.5
147.5°	1107.4	1107.3	1107.4	1107.7	1107.9	1108.1	1107.6	1106.4	1105.2	1104.1	1102.9
150°	1129.2	1129.2	1129.4	1129.7	1129.8	1130.1	1129.8	1128.9	1128.0	1127.2	1126.4
152.5°	1147.8	1147.5	1147.8	1148.2	1148.6	1148.9	1148.8	1148.1	1147.5	1146.8	1146.1
155°	1172.7	1171.8	1172.5	1173.1	1173.8	1174.4	1174.6	1174.4	1174.2	1173.9	1173.8
157.5°	1194.3	1193.3	1194.0	1194.7	1195.4	1196.1	1196.5	1196.7	1196.8	1196.9	1197.0
160°	1208.2	1206.9	1207.1	1207.3	1207.5	1207.8	1208.2	1208.8	1209.4	1210.1	1210.7
162.5°	1219.5	1218.3	1218.5	1218.7	1218.9	1219.1	1219.6	1220.4	1221.2	1222.1	1222.8
165°	1235.1	1233.5	1233.5	1233.5	1233.5	1233.5	1234.0	1235.0	1236.1	1237.1	1238.2
167.5°	1246.7	1244.8	1245.0	1245.0	1245.2	1245.3	1245.9	1247.0	1248.1	1249.2	1250.3
170°	1254.1	1252.4	1252.1	1252.0	1251.7	1251.6	1252.1	1253.4	1254.6	1255.9	1257.1
172.5°	1258.6	1256.9	1256.7	1256.5	1256.3	1256.1	1256.6	1257.8	1259.1	1260.4	1261.7
175°	1263.7	1261.8	1261.7	1261.4	1261.2	1261.0	1261.5	1262.8	1264.0	1265.3	1266.6
177.5°	1266.4	1265.1	1264.8	1264.4	1264.0	1263.7	1264.1	1265.3	1266.5	1267.7	1268.9
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1082.8	1085.9	1089.4	1096.0	1101.6	1104.0	1108.8	1112.3	1111.3	1116.1	1124.5
5°	1087.0	1098.8	1112.2	1126.1	1141.7	1154.7	1165.1	1175.5	1183.7	1193.7	1208.4
7.5°	1086.4	1107.2	1129.8	1154.7	1180.3	1202.4	1222.9	1243.7	1262.2	1282.4	1308.8
10°	1083.6	1111.3	1139.5	1172.1	1204.5	1235.3	1263.1	1289.2	1313.9	1340.3	1373.7
12.5°	1080.4	1112.4	1146.5	1185.5	1226.0	1263.1	1295.7	1333.2	1364.2	1398.2	1436.8
15°	1066.7	1109.6	1156.0	1206.7	1255.3	1305.1	1349.8	1395.8	1438.7	1479.4	1528.0
17.5°	1050.9	1100.4	1155.1	1215.0	1273.4	1334.0	1387.0	1445.0	1488.8	1543.5	1588.6
20°	1038.0	1091.4	1149.9	1217.2	1283.4	1350.7	1409.2	1468.2	1517.6	1572.7	1629.9
22.5°	1022.5	1081.0	1144.4	1214.0	1283.4	1356.9	1421.7	1480.3	1541.6	1603.5	1662.6
25°	997.3	1058.0	1125.2	1201.5	1281.3	1356.3	1425.7	1498.5	1564.5	1631.7	1684.6
27.5°	966.5	1030.1	1101.0	1179.7	1261.6	1338.5	1420.2	1497.8	1564.1	1628.8	1675.0
30°	941.8	1009.0	1077.1	1156.8	1241.9	1324.2	1411.9	1489.5	1559.3	1617.4	1643.4
32.5°	916.5	980.2	1050.4	1131.2	1218.2	1306.9	1393.8	1473.2	1537.7	1572.6	1573.3
35°	872.5	932.2	1005.1	1084.4	1173.8	1270.1	1358.0	1436.1	1475.5	1478.6	1436.1
37.5°	824.3	879.3	948.0	1027.4	1125.3	1221.1	1311.0	1363.0	1376.1	1332.0	1253.4
40°	790.0	840.7	907.1	988.6	1085.7	1184.6	1266.6	1304.7	1290.9	1219.3	1131.7
42.5°	754.0	801.2	865.1	945.6	1043.1	1143.0	1212.8	1233.3	1196.5	1113.9	1011.4
45°	695.0	738.4	801.8	882.8	976.5	1070.2	1123.1	1112.6	1051.5	953.5	838.6
47.5°	633.7	675.6	732.6	807.6	903.5	984.4	1020.2	988.8	901.8	794.0	700.5
50°	593.2	636.1	688.6	760.1	847.7	925.8	948.8	901.1	804.4	700.7	614.8
52.5°	553.3	590.0	641.4	710.5	794.3	860.2	872.5	817.4	717.6	624.8	548.6
55°	492.6	525.9	569.3	634.4	706.8	762.7	756.2	685.5	594.9	515.6	455.8
57.5°	433.9	459.0	499.0	560.0	623.6	661.1	637.4	577.2	492.7	427.7	377.2
60°	395.0	418.4	455.8	509.1	565.0	586.2	566.3	500.8	434.1	374.6	332.2
62.5°	358.2	378.9	411.0	460.5	505.6	518.3	496.9	439.8	379.6	328.8	293.7
65°	304.8	323.9	351.2	386.4	417.6	423.6	409.8	351.2	305.7	263.2	238.9
67.5°	256.3	268.8	290.2	320.5	337.1	340.6	313.8	277.0	236.9	210.8	192.5
70°	223.7	232.4	252.3	268.8	282.3	282.7	258.0	228.5	197.7	176.5	163.1
72.5°	192.2	200.5	215.6	226.9	237.2	233.8	211.2	187.9	163.1	147.0	137.1
75°	148.3	155.6	163.5	168.7	168.7	164.4	147.9	130.5	116.2	106.6	103.6
77.5°	107.8	113.9	116.5	115.7	114.1	107.4	96.9	85.6	80.5	76.0	73.7
80°	84.5	87.2	88.1	85.9	83.2	75.4	68.5	63.8	58.9	57.2	56.3
82.5°	62.7	65.0	62.7	63.3	57.6	51.2	47.4	45.7	43.7	43.0	42.2
85°	33.4	32.9	32.1	29.9	26.0	25.1	24.7	24.3	23.4	23.9	23.0
87.5°	12.5	11.9	11.0	11.1	11.5	11.2	11.8	12.1	12.5	12.4	13.4
90°	5.1	7.5	9.8	12.1	14.1	15.8	17.4	19.2	20.9	22.1	23.4
92.5°	12.1	12.2	12.3	12.5	13.4	15.0	16.7	18.4	20.1	21.4	22.6
95°	44.9	37.7	30.7	23.5	20.0	20.2	20.4	20.6	20.9	22.1	23.4
97.5°	115.1	119.6	124.0	128.5	119.0	95.5	72.0	48.5	25.0	25.1	25.3
100°	159.1	163.0	166.7	170.6	157.9	128.8	99.8	70.8	41.7	38.1	34.5
102.5°	208.1	210.9	213.7	216.5	216.0	212.2	208.4	204.6	200.8	162.2	123.6
105°	286.4	287.6	288.9	290.2	291.4	292.4	293.4	294.5	295.5	297.5	299.4
107.5°	359.9	360.5	361.1	361.7	362.8	364.2	365.7	367.0	368.5	369.4	370.4
110°	409.9	410.5	411.2	411.8	412.7	414.0	415.2	416.5	417.8	418.2	418.7





TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	458.9	460.0	461.1	462.3	463.2	463.7	464.3	465.0	465.5	465.5	465.4
115°	533.0	533.7	534.3	534.9	535.2	534.9	534.8	534.5	534.3	534.8	535.2
117.5°	600.5	601.4	602.2	603.0	603.6	604.1	604.6	605.1	605.5	605.4	605.4
120°	646.0	646.9	647.7	648.5	648.8	648.7	648.4	648.2	648.0	648.4	648.8
122.5°	688.1	688.6	689.1	689.6	690.0	690.3	690.6	690.9	691.2	691.5	691.7
125°	749.3	750.1	750.9	751.8	752.0	751.5	751.1	750.7	750.3	750.9	751.5
127.5°	806.2	806.4	806.7	806.8	807.4	808.4	809.3	810.3	811.3	811.1	811.1
130°	843.3	843.6	843.8	844.0	844.4	845.1	845.6	846.3	846.9	847.1	847.3
132.5°	877.6	878.0	878.4	878.7	879.4	880.1	880.9	881.7	882.6	882.7	883.0
135°	928.2	928.0	927.7	927.6	927.9	928.7	929.5	930.4	931.2	931.6	932.1
137.5°	973.8	973.9	974.0	974.0	974.5	975.4	976.4	977.3	978.2	978.7	979.2
140°	1003.6	1004.0	1004.5	1004.9	1005.3	1005.8	1006.2	1006.6	1007.1	1007.6	1008.3
142.5°	1030.5	1031.3	1032.0	1032.8	1033.3	1033.6	1033.8	1034.0	1034.3	1034.8	1035.3
145°	1071.1	1071.8	1072.4	1073.0	1073.3	1073.3	1073.3	1073.3	1073.3	1073.6	1073.7
147.5°	1104.1	1105.2	1106.4	1107.6	1108.1	1107.9	1107.7	1107.4	1107.3	1107.4	1107.6
150°	1127.2	1128.0	1128.9	1129.8	1130.1	1129.8	1129.7	1129.4	1129.2	1129.2	1129.2
152.5°	1146.8	1147.5	1148.1	1148.8	1148.9	1148.6	1148.2	1147.8	1147.5	1147.8	1148.1
155°	1173.9	1174.2	1174.4	1174.6	1174.4	1173.8	1173.1	1172.5	1171.8	1172.7	1173.5
157.5°	1196.9	1196.8	1196.7	1196.5	1196.1	1195.4	1194.7	1194.0	1193.3	1194.3	1195.5
160°	1210.1	1209.4	1208.8	1208.2	1207.8	1207.5	1207.3	1207.1	1206.9	1208.2	1209.4
162.5°	1222.1	1221.2	1220.4	1219.6	1219.1	1218.9	1218.7	1218.5	1218.3	1219.5	1220.8
165°	1237.1	1236.1	1235.0	1234.0	1233.5	1233.5	1233.5	1233.5	1233.5	1235.1	1236.8
167.5°	1249.2	1248.1	1247.0	1245.9	1245.3	1245.2	1245.0	1245.0	1244.8	1246.7	1248.5
170°	1255.9	1254.6	1253.4	1252.1	1251.6	1251.7	1252.0	1252.1	1252.4	1254.1	1255.7
172.5°	1260.4	1259.1	1257.8	1256.6	1256.1	1256.3	1256.5	1256.7	1256.9	1258.6	1260.3
175°	1265.3	1264.0	1262.8	1261.5	1261.0	1261.2	1261.4	1261.7	1261.8	1263.7	1265.7
177.5°	1267.7	1266.5	1265.3	1264.1	1263.7	1264.0	1264.4	1264.8	1265.1	1266.4	1267.8
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1128.9	1130.3	1131.4	1134.8	1135.1	1138.3	1135.1
5°	1222.3	1228.4	1238.0	1247.5	1248.4	1254.4	1243.6
7.5°	1327.1	1341.2	1349.9	1365.3	1371.4	1375.2	1369.0
10°	1399.2	1412.3	1435.3	1446.5	1457.8	1459.5	1454.3
12.5°	1469.0	1489.6	1507.7	1529.1	1528.5	1543.9	1538.2
15°	1561.9	1583.1	1608.3	1632.1	1640.8	1640.8	1647.7
17.5°	1628.1	1667.0	1693.1	1711.8	1732.3	1735.8	1733.4
20°	1672.8	1714.9	1742.7	1766.9	1780.9	1784.7	1784.7
22.5°	1706.2	1742.0	1769.0	1790.9	1802.3	1806.9	1805.6
25°	1729.2	1760.0	1776.5	1783.0	1786.0	1785.2	1776.9
27.5°	1697.6	1696.2	1685.9	1665.9	1650.9	1641.8	1631.4
30°	1637.3	1614.8	1588.8	1560.1	1523.2	1495.1	1486.4
32.5°	1547.4	1496.8	1452.8	1405.1	1365.5	1337.3	1325.4
35°	1373.7	1293.5	1228.0	1170.8	1129.1	1103.1	1094.5
37.5°	1167.4	1089.8	1008.8	953.2	918.8	892.4	882.6
40°	1036.3	951.8	881.1	829.1	793.5	767.9	767.5
42.5°	916.6	835.9	769.4	731.9	693.6	676.7	676.6
45°	750.6	686.0	629.6	600.1	577.2	563.3	559.4
47.5°	621.4	568.0	530.4	507.0	488.2	479.4	473.7
50°	548.9	502.1	472.2	451.8	441.4	430.2	429.3
52.5°	488.6	450.8	427.5	410.9	397.7	390.9	391.1
55°	410.6	380.7	364.2	351.6	341.3	336.1	333.9
57.5°	345.9	323.5	311.5	299.9	295.5	291.5	290.3
60°	305.7	290.5	279.2	270.1	263.7	262.4	261.9
62.5°	272.4	256.5	248.7	241.7	236.9	234.9	234.2
65°	224.6	212.9	205.9	200.3	198.6	195.6	195.1
67.5°	181.1	174.1	169.4	165.6	163.2	163.1	163.1
70°	154.3	150.4	146.6	144.4	143.1	142.2	142.2
72.5°	131.5	128.6	125.4	124.3	124.0	123.1	122.8
75°	100.2	97.1	97.6	95.4	93.7	91.5	90.2
77.5°	71.0	68.9	68.4	68.2	66.7	66.4	67.1
80°	55.0	52.9	52.5	52.9	52.5	51.2	51.2
82.5°	41.9	40.0	39.6	39.4	39.0	39.4	38.6
85°	22.6	21.7	21.7	21.7	22.6	22.1	21.7
87.5°	12.9	12.8	13.3	13.0	13.1	12.9	13.3
90°	24.6	25.9	26.7	27.1	27.6	28.0	28.5
92.5°	23.9	25.1	25.8	25.9	26.0	26.1	26.2
95°	24.6	25.9	26.7	26.8	27.1	27.2	27.5
97.5°	25.4	25.5	25.7	25.9	26.1	26.3	26.5
100°	31.0	27.4	25.7	25.9	26.1	26.3	26.5
102.5°	85.0	46.4	27.1	27.1	27.2	27.2	27.3
105°	301.3	303.1	300.3	292.7	285.1	277.6	270.0
107.5°	371.3	372.2	373.1	373.9	374.7	375.4	376.3
110°	419.1	419.5	420.0	420.6	421.3	421.9	422.5



TEST NUMBER: P332949-930

CATALOG NUMBER: SA4XXRDIP-C795D1205U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	465.3	465.2	465.5	466.4	467.2	468.0	468.7
115°	535.6	536.0	536.2	536.2	536.2	536.2	536.2
117.5°	605.3	605.2	605.1	605.0	605.0	604.9	604.8
120°	649.2	649.6	649.6	649.2	648.8	648.4	648.0
122.5°	691.9	692.2	692.1	691.7	691.3	690.8	690.4
125°	752.2	752.8	753.3	753.4	753.7	753.9	754.1
127.5°	810.9	810.8	810.7	810.5	810.3	810.2	810.0
130°	847.6	847.7	847.8	847.8	847.8	847.8	847.8
132.5°	883.2	883.4	883.4	883.2	883.1	882.9	882.7
135°	932.5	932.9	933.4	933.8	934.2	934.6	935.0
137.5°	979.6	980.1	980.2	980.2	980.0	979.8	979.7
140°	1008.9	1009.6	1010.0	1010.2	1010.4	1010.6	1010.8
142.5°	1035.7	1036.2	1036.4	1036.5	1036.5	1036.6	1036.6
145°	1074.0	1074.2	1074.5	1074.9	1075.3	1075.8	1076.2
147.5°	1107.7	1107.9	1108.1	1108.3	1108.6	1108.7	1109.0
150°	1129.2	1129.2	1129.4	1129.5	1129.8	1130.0	1130.2
152.5°	1148.4	1148.8	1148.8	1148.8	1148.6	1148.5	1148.3
155°	1174.4	1175.3	1175.3	1174.7	1174.0	1173.5	1172.8
157.5°	1196.5	1197.7	1197.7	1196.5	1195.5	1194.3	1193.3
160°	1210.7	1211.9	1211.9	1210.7	1209.4	1208.2	1206.9
162.5°	1222.1	1223.4	1223.3	1221.8	1220.4	1219.0	1217.5
165°	1238.5	1240.2	1240.1	1238.2	1236.2	1234.4	1232.5
167.5°	1250.3	1252.2	1252.1	1250.0	1247.9	1245.8	1243.7
170°	1257.4	1259.1	1258.9	1256.8	1254.7	1252.6	1250.5
172.5°	1262.0	1263.6	1263.4	1261.1	1258.8	1256.5	1254.3
175°	1267.5	1269.4	1269.1	1266.6	1264.0	1261.5	1259.0
177.5°	1269.1	1270.5	1270.2	1268.1	1266.1	1264.0	1262.1
180°	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6	1266.6

(END OF REPORT)