

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332939-930

Luminaire Tested: **SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332939-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5082.2 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332939-930  
CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54				54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46				46
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	46	44	39				39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34				34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29				29
5	70	59	51	45	65	55	48	42	48	42	38	41	37	33	35	31	29	26				26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23				23
7	60	48	40	34	55	45	38	33	39	34	29	34	29	26	29	26	23	20				20
8	56	43	36	31	52	41	34	29	36	30	26	31	27	23	27	23	21	18				18
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17				17
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	23	19	17	15				15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8688	8688	8688	8688
5°	10078	8715	7703	8715
10°	11922	8676	6874	8676
15°	13771	8596	5907	8596
20°	15332	8485	5342	8485
25°	15828	8378	4960	8378
30°	13856	8245	4729	8245
35°	10787	8051	4590	8051
40°	8088	7827	4515	7827
45°	6387	7470	4475	7470
50°	5392	7058	4346	7058
55°	4700	6602	4114	6602
60°	4229	6132	3641	6132
65°	3727	5624	3131	5624
70°	3356	5098	2825	5098
75°	2813	4517	2408	4517
80°	2380	3849	2259	3849
85°	2010	3010	2010	3010



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.3	2.1
10°-20°	314.5	6.2
20°-30°	492.0	9.7
30°-40°	546.9	10.8
40°-50°	485.2	9.5
50°-60°	378.1	7.4
60°-70°	247.6	4.9
70°-80°	121.7	2.4
80°-90°	31.8	0.6
90°-100°	234.4	4.6
100°-110°	487.8	9.6
110°-120°	436.9	8.6
120°-130°	367.5	7.2
130°-140°	306.4	6.0
140°-150°	234.1	4.6
150°-160°	164.6	3.2
160°-170°	96.8	1.9
170°-180°	31.5	0.6
0°-30°	910.8	17.9
0°-40°	1457.7	28.7
0°-60°	2321.1	45.7
0°-90°	2722.2	53.6
90°-120°	1159.1	22.8
90°-150°	2067.1	40.7
90°-180°	2360.0	46.4
0°-180°	5082.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1076	1076	1076	1076	1076	
5°	1244	1075	950	1075	1244	126
15°	1648	1028	707	1028	1648	469
25°	1777	940	557	940	1777	788
35°	1094	817	466	817	1094	686
45°	559	654	392	654	559	443
55°	334	469	292	469	334	304
65°	195	294	164	294	195	196
75°	90	145	77	145	90	99
85°	22	32	22	32	22	25
90°	13	1	13	1	13	12
95°	156	21	156	21	156	241
105°	897	75	897	75	897	887
115°	861	131	861	131	861	855
125°	687	183	687	183	687	624
135°	615	217	615	217	615	474
145°	502	250	502	250	502	318
155°	420	285	420	285	420	196
165°	367	310	367	310	367	105
175°	330	324	330	324	330	32
180°	324	324	324	324	324	



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1135.1	1138.3	1135.1	1134.8	1131.4	1130.3	1128.9	1124.5	1116.1	1111.3	1112.3
5°	1243.6	1254.4	1248.4	1247.5	1238.0	1228.4	1222.3	1208.4	1193.7	1183.7	1175.5
7.5°	1369.0	1375.2	1371.4	1365.3	1349.9	1341.2	1327.1	1308.8	1282.4	1262.2	1243.7
10°	1454.3	1459.5	1457.8	1446.5	1435.3	1412.3	1399.2	1373.7	1340.3	1313.9	1289.2
12.5°	1538.2	1543.9	1528.5	1529.1	1507.7	1489.6	1469.0	1436.8	1398.2	1364.2	1333.2
15°	1647.7	1640.8	1640.8	1632.1	1608.3	1583.1	1561.9	1528.0	1479.4	1438.7	1395.8
17.5°	1733.4	1735.8	1732.3	1711.8	1693.1	1667.0	1628.1	1588.6	1543.5	1488.8	1445.0
20°	1784.7	1784.7	1780.9	1766.9	1742.7	1714.9	1672.8	1629.9	1572.7	1517.6	1468.2
22.5°	1805.6	1806.9	1802.3	1790.9	1769.0	1742.0	1706.2	1662.6	1603.5	1541.6	1480.3
25°	1776.9	1785.2	1786.0	1783.0	1776.5	1760.0	1729.2	1684.6	1631.7	1564.5	1498.5
27.5°	1631.4	1641.8	1650.9	1665.9	1685.9	1696.2	1697.6	1675.0	1628.8	1564.1	1497.8
30°	1486.4	1495.1	1523.2	1560.1	1588.8	1614.8	1637.3	1643.4	1617.4	1559.3	1489.5
32.5°	1325.4	1337.3	1365.5	1405.1	1452.8	1496.8	1547.4	1573.3	1572.6	1537.7	1473.2
35°	1094.5	1103.1	1129.1	1170.8	1228.0	1293.5	1373.7	1436.1	1478.6	1475.5	1436.1
37.5°	882.6	892.4	918.8	953.2	1008.8	1089.8	1167.4	1253.4	1332.0	1376.1	1363.0
40°	767.5	767.9	793.5	829.1	881.1	951.8	1036.3	1131.7	1219.3	1290.9	1304.7
42.5°	676.6	676.7	693.6	731.9	769.4	835.9	916.6	1011.4	1113.9	1196.5	1233.3
45°	559.4	563.3	577.2	600.1	629.6	686.0	750.6	838.6	953.5	1051.5	1112.6
47.5°	473.7	479.4	488.2	507.0	530.4	568.0	621.4	700.5	794.0	901.8	988.8
50°	429.3	430.2	441.4	451.8	472.2	502.1	548.9	614.8	700.7	804.4	901.1
52.5°	391.1	390.9	397.7	410.9	427.5	450.8	488.6	548.6	624.8	717.6	817.4
55°	333.9	336.1	341.3	351.6	364.2	380.7	410.6	455.8	515.6	594.9	685.5
57.5°	290.3	291.5	295.5	299.9	311.5	323.5	345.9	377.2	427.7	492.7	577.2
60°	261.9	262.4	263.7	270.1	279.2	290.5	305.7	332.2	374.6	434.1	500.8
62.5°	234.2	234.9	236.9	241.7	248.7	256.5	272.4	293.7	328.8	379.6	439.8
65°	195.1	195.6	198.6	200.3	205.9	212.9	224.6	238.9	263.2	305.7	351.2
67.5°	163.1	163.1	163.2	165.6	169.4	174.1	181.1	192.5	210.8	236.9	277.0
70°	142.2	142.2	143.1	144.4	146.6	150.4	154.3	163.1	176.5	197.7	228.5
72.5°	122.8	123.1	124.0	124.3	125.4	128.6	131.5	137.1	147.0	163.1	187.9
75°	90.2	91.5	93.7	95.4	97.6	97.1	100.2	103.6	106.6	116.2	130.5
77.5°	67.1	66.4	66.7	68.2	68.4	68.9	71.0	73.7	76.0	80.5	85.6
80°	51.2	51.2	52.5	52.9	52.5	52.9	55.0	56.3	57.2	58.9	63.8
82.5°	38.6	39.4	39.0	39.4	39.6	40.0	41.9	42.2	43.0	43.7	45.7
85°	21.7	22.1	22.6	21.7	21.7	21.7	22.6	23.0	23.9	23.4	24.3
87.5°	10.3	9.9	10.4	10.3	10.5	10.2	10.4	11.0	10.1	10.6	10.4
90°	13.4	13.4	14.0	13.4	12.7	12.7	12.1	11.5	10.8	11.5	10.2
92.5°	49.1	49.1	51.3	54.7	62.2	75.0	94.2	125.2	168.4	202.2	177.0
95°	155.6	163.9	175.3	195.1	226.3	288.1	373.6	472.4	534.3	519.6	392.1
97.5°	415.8	429.0	448.2	486.6	532.3	598.8	661.2	697.9	671.2	547.2	367.0
100°	584.6	589.7	608.8	647.7	703.2	750.3	781.5	768.8	675.7	512.6	332.8
102.5°	731.5	735.6	755.7	783.9	817.9	837.6	828.5	765.2	637.5	469.2	309.8
105°	897.0	900.8	909.7	914.8	913.5	887.4	824.3	714.0	568.0	418.2	290.1
107.5°	958.4	956.8	950.4	935.9	904.3	847.5	758.6	641.2	511.9	389.6	286.5
110°	959.4	953.7	942.2	915.4	870.2	800.1	707.6	597.4	483.9	379.9	287.5



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	929.4	920.1	904.0	871.6	820.2	750.1	662.8	565.2	468.1	375.4	290.6
115°	861.3	856.1	835.8	797.5	747.1	685.9	611.4	533.0	453.2	372.9	296.4
117.5°	792.3	788.3	767.7	735.6	692.6	640.7	582.0	517.1	446.6	372.3	302.7
120°	753.5	746.5	729.9	701.9	665.5	620.3	569.3	510.0	443.0	372.3	307.3
122.5°	722.9	715.9	701.9	677.9	647.2	607.6	561.1	503.9	439.0	371.8	311.9
125°	687.2	683.4	671.3	652.8	627.3	592.2	548.3	493.4	432.2	371.0	318.8
127.5°	666.3	662.5	652.3	635.9	610.3	576.9	533.0	480.7	423.1	369.7	324.2
130°	654.1	650.3	640.1	624.1	597.9	564.2	520.8	470.5	417.6	369.1	328.3
132.5°	640.3	636.5	626.8	608.8	583.2	549.4	507.0	459.7	412.5	368.6	331.9
135°	614.6	610.7	600.5	582.7	557.2	525.3	486.4	445.0	404.8	367.9	337.2
137.5°	582.7	578.0	569.6	552.0	528.2	499.5	466.7	431.6	398.2	367.7	340.4
140°	559.7	554.6	545.7	531.7	509.4	482.6	453.9	424.0	394.6	367.2	343.0
142.5°	535.2	531.7	523.7	510.8	491.0	467.8	443.2	416.8	391.6	367.2	345.0
145°	501.7	498.6	492.1	481.4	465.4	447.5	428.4	406.8	386.3	365.9	346.2
147.5°	472.0	470.8	466.0	456.7	445.0	431.0	415.6	398.4	381.6	363.6	346.8
150°	455.2	454.5	450.7	442.5	432.2	420.8	408.0	393.3	378.1	362.1	346.8
152.5°	439.9	439.2	436.9	430.2	421.5	412.1	400.3	387.8	374.0	359.5	345.8
155°	420.1	420.1	418.2	413.1	406.8	399.1	389.6	379.3	367.9	355.7	344.2
157.5°	402.8	402.8	401.6	397.8	393.0	386.9	378.8	370.2	361.6	351.8	342.6
160°	392.1	392.1	391.4	387.6	383.8	378.7	371.7	364.7	357.0	348.7	341.0
162.5°	381.9	382.4	381.7	377.9	375.1	370.6	365.0	359.1	352.9	345.7	339.6
165°	366.6	367.2	367.9	365.3	362.7	359.5	355.1	351.2	346.2	341.0	336.6
167.5°	354.4	355.0	355.1	353.4	352.1	350.3	346.7	343.7	340.1	336.5	333.5
170°	346.8	346.8	347.4	346.8	345.5	343.6	341.0	339.2	336.0	333.4	331.5
172.5°	339.2	340.1	340.8	340.1	339.4	338.0	336.5	335.1	332.4	330.4	329.5
175°	330.2	331.5	332.8	331.5	331.5	331.5	330.2	329.6	328.3	327.0	327.0
177.5°	325.0	326.0	327.0	326.5	327.0	326.5	326.5	326.0	325.5	325.0	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1108.8	1104.0	1101.6	1096.0	1089.4	1085.9	1082.8	1078.3	1072.4	1066.2	1061.6
5°	1165.1	1154.7	1141.7	1126.1	1112.2	1098.8	1087.0	1075.4	1061.9	1048.0	1034.1
7.5°	1222.9	1202.4	1180.3	1154.7	1129.8	1107.2	1086.4	1066.4	1043.8	1023.7	1005.3
10°	1263.1	1235.3	1204.5	1172.1	1139.5	1111.3	1083.6	1058.4	1030.7	1006.0	985.1
12.5°	1295.7	1263.1	1226.0	1185.5	1146.5	1112.4	1080.4	1047.7	1016.1	989.3	961.6
15°	1349.8	1305.1	1255.3	1206.7	1156.0	1109.6	1066.7	1028.5	992.5	954.8	928.4
17.5°	1387.0	1334.0	1273.4	1215.0	1155.1	1100.4	1050.9	1005.4	963.9	925.4	893.9
20°	1409.2	1350.7	1283.4	1217.2	1149.9	1091.4	1038.0	987.7	944.9	903.2	870.7
22.5°	1421.7	1356.9	1283.4	1214.0	1144.4	1081.0	1022.5	970.0	923.3	881.7	845.7
25°	1425.7	1356.3	1281.3	1201.5	1125.2	1058.0	997.3	940.5	888.4	846.9	808.7
27.5°	1420.2	1338.5	1261.6	1179.7	1101.0	1030.1	966.5	906.8	854.7	810.0	770.9
30°	1411.9	1324.2	1241.9	1156.8	1077.1	1009.0	941.8	884.5	830.4	784.0	744.5
32.5°	1393.8	1306.9	1218.2	1131.2	1050.4	980.2	916.5	858.9	805.8	758.3	716.4
35°	1358.0	1270.1	1173.8	1084.4	1005.1	932.2	872.5	816.9	766.2	715.4	671.2
37.5°	1311.0	1221.1	1125.3	1027.4	948.0	879.3	824.3	772.3	722.8	676.5	627.5
40°	1266.6	1184.6	1085.7	988.6	907.1	840.7	790.0	742.7	692.9	646.9	597.9
42.5°	1212.8	1143.0	1043.1	945.6	865.1	801.2	754.0	707.8	662.3	617.8	566.7
45°	1123.1	1070.2	976.5	882.8	801.8	738.4	695.0	654.3	614.4	571.9	523.8
47.5°	1020.2	984.4	903.5	807.6	732.6	675.6	633.7	600.5	566.7	524.2	482.0
50°	948.8	925.8	847.7	760.1	688.6	636.1	593.2	562.0	533.8	493.0	455.3
52.5°	872.5	860.2	794.3	710.5	641.4	590.0	553.3	525.2	496.7	462.8	427.5
55°	756.2	762.7	706.8	634.4	569.3	525.9	492.6	469.1	444.9	416.3	389.0
57.5°	637.4	661.1	623.6	560.0	499.0	459.0	433.9	414.2	393.8	370.1	346.7
60°	566.3	586.2	565.0	509.1	455.8	418.4	395.0	379.8	359.5	337.8	320.0
62.5°	496.9	518.3	505.6	460.5	411.0	378.9	358.2	344.1	329.0	310.1	291.6
65°	409.8	423.6	417.6	386.4	351.2	323.9	304.8	294.4	280.5	266.7	250.2
67.5°	313.8	340.6	337.1	320.5	290.2	268.8	256.3	247.1	234.5	224.2	213.0
70°	258.0	282.7	282.3	268.8	252.3	232.4	223.7	216.0	204.6	194.7	185.6
72.5°	211.2	233.8	237.2	226.9	215.6	200.5	192.2	186.8	175.9	169.0	161.7
75°	147.9	164.4	168.7	168.7	163.5	155.6	148.3	144.8	137.1	130.9	126.6
77.5°	96.9	107.4	114.1	115.7	116.5	113.9	107.8	105.3	99.4	97.2	93.0
80°	68.5	75.4	83.2	85.9	88.1	87.2	84.5	82.8	77.2	75.0	73.3
82.5°	47.4	51.2	57.6	63.3	62.7	65.0	62.7	61.3	57.1	56.3	54.5
85°	24.7	25.1	26.0	29.9	32.1	32.9	33.4	32.5	31.2	31.2	28.2
87.5°	10.1	9.8	9.7	9.7	9.9	11.2	11.8	11.9	11.2	10.5	9.5
90°	8.9	8.9	5.1	5.1	4.5	3.8	1.9	0.7	1.9	3.8	4.5
92.5°	128.7	79.3	46.9	33.7	24.4	16.6	10.6	7.3	10.6	16.6	24.4
95°	239.7	135.2	79.7	52.9	37.6	29.4	22.9	21.0	22.9	29.4	37.6
97.5°	215.5	129.1	86.4	64.0	50.9	43.2	37.7	37.7	37.7	43.2	50.9
100°	202.8	130.7	93.1	72.6	60.6	52.9	48.4	48.4	48.4	52.9	60.6
102.5°	199.2	135.7	101.7	82.3	70.8	63.6	59.7	58.6	59.7	63.6	70.8
105°	200.8	147.9	117.3	98.8	87.3	79.7	76.5	74.6	76.5	79.7	87.3
107.5°	210.3	162.1	134.0	115.8	104.8	96.6	93.4	92.2	93.4	96.6	104.8
110°	217.4	172.8	144.7	127.5	116.0	108.4	105.2	104.0	105.2	108.4	116.0





TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	225.0	183.0	156.0	138.7	127.3	120.1	116.4	115.1	116.4	120.1	127.3
115°	237.2	198.9	173.4	156.2	144.1	137.7	133.2	131.3	133.2	137.7	144.1
117.5°	249.5	214.3	190.1	172.3	160.9	153.9	149.9	148.1	149.9	153.9	160.9
120°	258.2	225.0	200.8	183.0	172.1	165.1	160.6	159.4	160.6	165.1	172.1
122.5°	266.4	235.2	211.0	193.6	181.8	175.3	170.9	169.6	170.9	175.3	181.8
125°	278.6	249.2	226.3	208.5	196.3	189.3	185.5	183.0	185.5	189.3	196.3
127.5°	289.2	262.3	240.1	222.1	209.5	201.5	196.9	194.9	196.9	201.5	209.5
130°	295.8	270.9	249.2	230.8	218.7	209.1	204.0	201.5	204.0	209.1	218.7
132.5°	302.4	278.1	256.4	239.0	225.8	216.8	210.1	208.1	210.1	216.8	225.8
135°	311.1	288.1	267.1	250.5	237.2	226.3	220.0	217.4	220.0	226.3	237.2
137.5°	317.2	295.8	276.1	260.3	246.5	236.1	229.1	226.7	229.1	236.1	246.5
140°	321.3	300.9	281.8	266.4	253.1	242.2	235.2	233.3	235.2	242.2	253.1
142.5°	324.3	305.5	286.9	272.1	259.2	248.9	242.4	240.4	242.4	248.9	259.2
145°	327.7	310.5	293.9	279.9	267.7	258.9	252.4	250.5	252.4	258.9	267.7
147.5°	330.6	315.6	300.0	287.4	277.3	268.2	262.5	261.9	262.5	268.2	277.3
150°	332.2	318.1	304.1	292.0	282.4	274.8	269.7	269.0	269.7	274.8	282.4
152.5°	333.1	320.2	307.7	296.6	288.0	280.9	275.8	275.7	275.8	280.9	288.0
155°	334.0	323.2	312.3	302.8	295.8	289.4	285.6	284.9	285.6	289.4	295.8
157.5°	334.0	325.4	316.2	308.7	302.6	297.6	294.0	294.0	294.0	297.6	302.6
160°	334.0	326.4	318.8	311.8	306.6	302.1	299.6	299.6	299.6	302.1	306.6
162.5°	334.0	327.4	320.2	314.8	310.2	306.2	304.2	304.8	304.2	306.2	310.2
165°	332.8	327.7	322.0	318.1	315.0	311.8	310.5	310.5	310.5	311.8	315.0
167.5°	331.3	327.6	323.3	320.4	318.6	316.2	315.6	316.2	315.6	316.2	318.6
170°	330.2	327.0	323.8	322.0	320.7	318.8	318.1	318.8	318.1	318.8	320.7
172.5°	329.2	326.5	324.3	322.9	322.2	320.8	320.7	321.3	320.7	320.8	322.2
175°	327.7	325.8	324.5	324.5	323.8	323.2	323.2	323.8	323.2	323.2	323.8
177.5°	326.0	325.0	324.5	324.5	324.5	324.0	324.5	325.0	324.5	324.0	324.5
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1056.8	1053.3	1048.8	1043.6	1037.4	1031.8	1029.4	1031.4	1032.5	1029.7	1029.4
5°	1024.6	1013.7	1005.1	992.1	981.7	973.0	966.9	964.3	965.2	958.3	956.5
7.5°	988.5	975.6	961.4	946.0	931.6	918.8	912.2	908.5	901.2	898.0	892.7
10°	965.2	947.9	934.0	915.7	899.3	884.1	876.8	870.7	863.3	859.8	852.5
12.5°	941.3	921.1	905.9	887.0	870.2	851.8	844.8	833.6	822.1	814.7	805.3
15°	907.5	883.3	864.6	842.0	822.1	801.3	782.7	761.8	754.1	737.6	728.1
17.5°	868.0	843.4	820.4	790.1	759.4	733.5	713.6	693.7	681.8	671.2	666.3
20°	842.0	819.5	787.4	752.3	718.0	689.4	673.4	660.4	647.3	640.0	634.8
22.5°	817.4	788.6	751.4	713.5	679.2	656.8	643.2	629.8	619.3	612.3	605.3
25°	776.2	738.4	699.0	655.6	632.2	612.7	597.9	587.1	580.6	571.5	568.0
27.5°	733.8	688.0	644.5	615.4	591.0	573.2	560.3	552.1	543.9	538.1	533.6
30°	701.2	654.8	615.7	588.0	563.3	548.5	538.1	528.6	522.0	517.3	513.8
32.5°	668.9	622.5	589.7	559.9	540.4	525.9	514.9	507.8	502.6	496.5	494.4
35°	622.2	581.1	552.4	525.5	505.6	492.6	483.9	476.5	472.2	470.4	469.1
37.5°	577.4	543.6	512.9	490.8	473.0	462.8	452.6	449.0	446.0	442.9	444.3
40°	548.9	517.3	490.0	466.6	452.2	441.0	434.9	430.6	428.0	428.0	428.0
42.5°	524.3	493.3	466.8	445.7	431.5	421.9	415.2	411.5	410.6	410.3	412.4
45°	486.1	457.5	430.6	413.2	401.0	391.5	387.7	384.6	384.6	386.4	386.8
47.5°	448.2	421.3	399.8	380.3	369.2	363.3	359.9	358.3	358.5	360.3	362.2
50°	424.9	398.5	377.2	359.9	349.5	343.8	340.8	340.0	340.8	340.8	343.8
52.5°	399.6	375.9	355.1	340.5	328.6	323.3	321.7	320.5	321.1	322.5	323.8
55°	362.5	341.3	321.3	307.4	298.7	295.3	291.4	291.8	291.0	291.8	291.8
57.5°	325.3	306.2	287.6	276.6	269.0	264.0	259.8	261.0	259.7	259.5	258.8
60°	301.3	280.5	265.8	255.8	247.1	242.8	238.9	239.8	238.5	237.6	235.9
62.5°	275.3	258.0	243.9	234.3	227.4	222.3	218.4	217.6	214.6	211.6	207.8
65°	237.6	223.3	210.8	201.6	195.1	191.2	188.2	185.6	179.0	172.1	168.7
67.5°	201.0	190.6	178.9	171.2	165.9	160.8	155.0	150.6	144.5	140.6	138.5
70°	177.3	167.4	157.4	150.0	144.4	139.7	133.1	130.1	125.7	124.0	121.8
72.5°	154.8	145.5	136.2	129.6	123.6	119.8	114.7	111.7	109.8	109.1	107.0
75°	120.6	113.2	106.2	100.2	95.4	92.8	90.7	88.5	87.6	83.6	81.5
77.5°	88.0	83.1	78.8	74.4	71.0	69.3	65.1	62.6	61.1	59.4	58.9
80°	68.5	65.1	60.7	58.1	53.3	51.6	49.9	49.4	49.0	48.6	48.1
82.5°	51.5	48.0	43.7	42.2	40.8	39.8	38.7	38.3	37.9	38.2	38.1
85°	26.0	24.3	24.3	23.9	23.4	23.0	22.6	22.6	22.1	22.6	22.1
87.5°	9.7	9.4	10.1	9.4	10.0	10.3	9.8	9.9	10.4	9.9	9.9
90°	5.1	5.1	8.9	8.9	10.2	11.5	10.8	11.5	12.1	12.7	12.7
92.5°	33.7	46.9	79.3	128.7	177.0	202.2	168.4	125.2	94.2	75.0	62.2
95°	52.9	79.7	135.2	239.7	392.1	519.6	534.3	472.4	373.6	288.1	226.3
97.5°	64.0	86.4	129.1	215.5	367.0	547.2	671.2	697.9	661.2	598.8	532.3
100°	72.6	93.1	130.7	202.8	332.8	512.6	675.7	768.8	781.5	750.3	703.2
102.5°	82.3	101.7	135.7	199.2	309.8	469.2	637.5	765.2	828.5	837.6	817.9
105°	98.8	117.3	147.9	200.8	290.1	418.2	568.0	714.0	824.3	887.4	913.5
107.5°	115.8	134.0	162.1	210.3	286.5	389.6	511.9	641.2	758.6	847.5	904.3
110°	127.5	144.7	172.8	217.4	287.5	379.9	483.9	597.4	707.6	800.1	870.2



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	138.7	156.0	183.0	225.0	290.6	375.4	468.1	565.2	662.8	750.1	820.2
115°	156.2	173.4	198.9	237.2	296.4	372.9	453.2	533.0	611.4	685.9	747.1
117.5°	172.3	190.1	214.3	249.5	302.7	372.3	446.6	517.1	582.0	640.7	692.6
120°	183.0	200.8	225.0	258.2	307.3	372.3	443.0	510.0	569.3	620.3	665.5
122.5°	193.6	211.0	235.2	266.4	311.9	371.8	439.0	503.9	561.1	607.6	647.2
125°	208.5	226.3	249.2	278.6	318.8	371.0	432.2	493.4	548.3	592.2	627.3
127.5°	222.1	240.1	262.3	289.2	324.2	369.7	423.1	480.7	533.0	576.9	610.3
130°	230.8	249.2	270.9	295.8	328.3	369.1	417.6	470.5	520.8	564.2	597.9
132.5°	239.0	256.4	278.1	302.4	331.9	368.6	412.5	459.7	507.0	549.4	583.2
135°	250.5	267.1	288.1	311.1	337.2	367.9	404.8	445.0	486.4	525.3	557.2
137.5°	260.3	276.1	295.8	317.2	340.4	367.7	398.2	431.6	466.7	499.5	528.2
140°	266.4	281.8	300.9	321.3	343.0	367.2	394.6	424.0	453.9	482.6	509.4
142.5°	272.1	286.9	305.5	324.3	345.0	367.2	391.6	416.8	443.2	467.8	491.0
145°	279.9	293.9	310.5	327.7	346.2	365.9	386.3	406.8	428.4	447.5	465.4
147.5°	287.4	300.0	315.6	330.6	346.8	363.6	381.6	398.4	415.6	431.0	445.0
150°	292.0	304.1	318.1	332.2	346.8	362.1	378.1	393.3	408.0	420.8	432.2
152.5°	296.6	307.7	320.2	333.1	345.8	359.5	374.0	387.8	400.3	412.1	421.5
155°	302.8	312.3	323.2	334.0	344.2	355.7	367.9	379.3	389.6	399.1	406.8
157.5°	308.7	316.2	325.4	334.0	342.6	351.8	361.6	370.2	378.8	386.9	393.0
160°	311.8	318.8	326.4	334.0	341.0	348.7	357.0	364.7	371.7	378.7	383.8
162.5°	314.8	320.2	327.4	334.0	339.6	345.7	352.9	359.1	365.0	370.6	375.1
165°	318.1	322.0	327.7	332.8	336.6	341.0	346.2	351.2	355.1	359.5	362.7
167.5°	320.4	323.3	327.6	331.3	333.5	336.5	340.1	343.7	346.7	350.3	352.1
170°	322.0	323.8	327.0	330.2	331.5	333.4	336.0	339.2	341.0	343.6	345.5
172.5°	322.9	324.3	326.5	329.2	329.5	330.4	332.4	335.1	336.5	338.0	339.4
175°	324.5	324.5	325.8	327.7	327.0	327.0	328.3	329.6	330.2	331.5	331.5
177.5°	324.5	324.5	325.0	326.0	325.0	325.0	325.5	326.0	326.5	326.5	327.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1027.3	1028.0	1025.6	1024.8	1025.6	1028.0	1027.3	1029.4	1029.7	1032.5	1031.4
5°	953.1	952.2	950.1	950.5	950.1	952.2	953.1	956.5	958.3	965.2	964.3
7.5°	889.6	886.2	887.1	883.7	887.1	886.2	889.6	892.7	898.0	901.2	908.5
10°	850.8	846.0	842.0	838.6	842.0	846.0	850.8	852.5	859.8	863.3	870.7
12.5°	797.7	793.6	788.3	789.4	788.3	793.6	797.7	805.3	814.7	822.1	833.6
15°	722.4	715.9	705.5	706.8	705.5	715.9	722.4	728.1	737.6	754.1	761.8
17.5°	658.7	658.8	654.0	655.1	654.0	658.8	658.7	666.3	671.2	681.8	693.7
20°	625.7	622.6	623.1	621.8	623.1	622.6	625.7	634.8	640.0	647.3	660.4
22.5°	602.8	599.1	596.1	593.4	596.1	599.1	602.8	605.3	612.3	619.3	629.8
25°	564.1	561.5	557.6	556.8	557.6	561.5	564.1	568.0	571.5	580.6	587.1
27.5°	530.1	529.6	528.1	526.0	528.1	529.6	530.1	533.6	538.1	543.9	552.1
30°	510.4	509.5	508.6	507.3	508.6	509.5	510.4	513.8	517.3	522.0	528.6
32.5°	492.7	492.1	491.3	491.4	491.3	492.1	492.7	494.4	496.5	502.6	507.8
35°	467.4	467.0	466.1	465.7	466.1	467.0	467.4	469.1	470.4	472.2	476.5
37.5°	443.8	445.0	444.4	444.3	444.4	445.0	443.8	444.3	442.9	446.0	449.0
40°	427.5	428.0	428.8	428.4	428.8	428.0	427.5	428.0	428.0	428.0	430.6
42.5°	414.0	414.1	415.3	413.8	415.3	414.1	414.0	412.4	410.3	410.6	411.5
45°	389.8	392.4	392.0	392.0	392.0	392.4	389.8	386.8	386.4	384.6	384.6
47.5°	363.4	365.6	366.2	366.2	366.2	365.6	363.4	362.2	360.3	358.5	358.3
50°	346.0	345.1	346.4	346.0	346.4	345.1	346.0	343.8	340.8	340.8	340.0
52.5°	324.9	325.1	325.0	324.5	325.0	325.1	324.9	323.8	322.5	321.1	320.5
55°	292.3	292.7	291.8	292.3	291.8	292.7	292.3	291.8	291.8	291.0	291.8
57.5°	256.9	254.8	255.7	254.6	255.7	254.8	256.9	258.8	259.5	259.7	261.0
60°	231.5	228.0	227.2	225.5	227.2	228.0	231.5	235.9	237.6	238.5	239.8
62.5°	203.1	200.6	197.7	199.1	197.7	200.6	203.1	207.8	211.6	214.6	217.6
65°	165.2	163.5	162.2	163.9	162.2	163.5	165.2	168.7	172.1	179.0	185.6
67.5°	136.7	135.8	135.8	134.9	135.8	135.8	136.7	138.5	140.6	144.5	150.6
70°	121.8	120.6	120.6	119.7	120.6	120.6	121.8	121.8	124.0	125.7	130.1
72.5°	106.6	105.3	105.7	105.1	105.7	105.3	106.6	107.0	109.1	109.8	111.7
75°	78.9	76.7	76.7	77.2	76.7	76.7	78.9	81.5	83.6	87.6	88.5
77.5°	58.9	58.5	59.0	58.3	59.0	58.5	58.9	58.9	59.4	61.1	62.6
80°	48.1	47.7	47.3	48.6	47.3	47.7	48.1	48.1	48.6	49.0	49.4
82.5°	37.3	37.3	37.2	38.9	37.2	37.3	37.3	38.1	38.2	37.9	38.3
85°	22.6	21.7	22.6	21.7	22.6	21.7	22.6	22.1	22.6	22.1	22.6
87.5°	10.7	10.4	9.9	10.3	9.9	10.4	10.7	9.9	9.9	10.4	9.9
90°	13.4	14.0	13.4	13.4	13.4	14.0	13.4	12.7	12.7	12.1	11.5
92.5°	54.7	51.3	49.1	49.1	49.1	51.3	54.7	62.2	75.0	94.2	125.2
95°	195.1	175.3	163.9	155.6	163.9	175.3	195.1	226.3	288.1	373.6	472.4
97.5°	486.6	448.2	429.0	415.8	429.0	448.2	486.6	532.3	598.8	661.2	697.9
100°	647.7	608.8	589.7	584.6	589.7	608.8	647.7	703.2	750.3	781.5	768.8
102.5°	783.9	755.7	735.6	731.5	735.6	755.7	783.9	817.9	837.6	828.5	765.2
105°	914.8	909.7	900.8	897.0	900.8	909.7	914.8	913.5	887.4	824.3	714.0
107.5°	935.9	950.4	956.8	958.4	956.8	950.4	935.9	904.3	847.5	758.6	641.2
110°	915.4	942.2	953.7	959.4	953.7	942.2	915.4	870.2	800.1	707.6	597.4



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	871.6	904.0	920.1	929.4	920.1	904.0	871.6	820.2	750.1	662.8	565.2
115°	797.5	835.8	856.1	861.3	856.1	835.8	797.5	747.1	685.9	611.4	533.0
117.5°	735.6	767.7	788.3	792.3	788.3	767.7	735.6	692.6	640.7	582.0	517.1
120°	701.9	729.9	746.5	753.5	746.5	729.9	701.9	665.5	620.3	569.3	510.0
122.5°	677.9	701.9	715.9	722.9	715.9	701.9	677.9	647.2	607.6	561.1	503.9
125°	652.8	671.3	683.4	687.2	683.4	671.3	652.8	627.3	592.2	548.3	493.4
127.5°	635.9	652.3	662.5	666.3	662.5	652.3	635.9	610.3	576.9	533.0	480.7
130°	624.1	640.1	650.3	654.1	650.3	640.1	624.1	597.9	564.2	520.8	470.5
132.5°	608.8	626.8	636.5	640.3	636.5	626.8	608.8	583.2	549.4	507.0	459.7
135°	582.7	600.5	610.7	614.6	610.7	600.5	582.7	557.2	525.3	486.4	445.0
137.5°	552.0	569.6	578.0	582.7	578.0	569.6	552.0	528.2	499.5	466.7	431.6
140°	531.7	545.7	554.6	559.7	554.6	545.7	531.7	509.4	482.6	453.9	424.0
142.5°	510.8	523.7	531.7	535.2	531.7	523.7	510.8	491.0	467.8	443.2	416.8
145°	481.4	492.1	498.6	501.7	498.6	492.1	481.4	465.4	447.5	428.4	406.8
147.5°	456.7	466.0	470.8	472.0	470.8	466.0	456.7	445.0	431.0	415.6	398.4
150°	442.5	450.7	454.5	455.2	454.5	450.7	442.5	432.2	420.8	408.0	393.3
152.5°	430.2	436.9	439.2	439.9	439.2	436.9	430.2	421.5	412.1	400.3	387.8
155°	413.1	418.2	420.1	420.1	420.1	418.2	413.1	406.8	399.1	389.6	379.3
157.5°	397.8	401.6	402.8	402.8	402.8	401.6	397.8	393.0	386.9	378.8	370.2
160°	387.6	391.4	392.1	392.1	392.1	391.4	387.6	383.8	378.7	371.7	364.7
162.5°	377.9	381.7	382.4	381.9	382.4	381.7	377.9	375.1	370.6	365.0	359.1
165°	365.3	367.9	367.2	366.6	367.2	367.9	365.3	362.7	359.5	355.1	351.2
167.5°	353.4	355.1	355.0	354.4	355.0	355.1	353.4	352.1	350.3	346.7	343.7
170°	346.8	347.4	346.8	346.8	346.8	347.4	346.8	345.5	343.6	341.0	339.2
172.5°	340.1	340.8	340.1	339.2	340.1	340.8	340.1	339.4	338.0	336.5	335.1
175°	331.5	332.8	331.5	330.2	331.5	332.8	331.5	331.5	331.5	330.2	329.6
177.5°	326.5	327.0	326.0	325.0	326.0	327.0	326.5	327.0	326.5	326.5	326.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1029.4	1031.8	1037.4	1043.6	1048.8	1053.3	1056.8	1061.6	1066.2	1072.4	1078.3
5°	966.9	973.0	981.7	992.1	1005.1	1013.7	1024.6	1034.1	1048.0	1061.9	1075.4
7.5°	912.2	918.8	931.6	946.0	961.4	975.6	988.5	1005.3	1023.7	1043.8	1066.4
10°	876.8	884.1	899.3	915.7	934.0	947.9	965.2	985.1	1006.0	1030.7	1058.4
12.5°	844.8	851.8	870.2	887.0	905.9	921.1	941.3	961.6	989.3	1016.1	1047.7
15°	782.7	801.3	822.1	842.0	864.6	883.3	907.5	928.4	954.8	992.5	1028.5
17.5°	713.6	733.5	759.4	790.1	820.4	843.4	868.0	893.9	925.4	963.9	1005.4
20°	673.4	689.4	718.0	752.3	787.4	819.5	842.0	870.7	903.2	944.9	987.7
22.5°	643.2	656.8	679.2	713.5	751.4	788.6	817.4	845.7	881.7	923.3	970.0
25°	597.9	612.7	632.2	655.6	699.0	738.4	776.2	808.7	846.9	888.4	940.5
27.5°	560.3	573.2	591.0	615.4	644.5	688.0	733.8	770.9	810.0	854.7	906.8
30°	538.1	548.5	563.3	588.0	615.7	654.8	701.2	744.5	784.0	830.4	884.5
32.5°	514.9	525.9	540.4	559.9	589.7	622.5	668.9	716.4	758.3	805.8	858.9
35°	483.9	492.6	505.6	525.5	552.4	581.1	622.2	671.2	715.4	766.2	816.9
37.5°	452.6	462.8	473.0	490.8	512.9	543.6	577.4	627.5	676.5	722.8	772.3
40°	434.9	441.0	452.2	466.6	490.0	517.3	548.9	597.9	646.9	692.9	742.7
42.5°	415.2	421.9	431.5	445.7	466.8	493.3	524.3	566.7	617.8	662.3	707.8
45°	387.7	391.5	401.0	413.2	430.6	457.5	486.1	523.8	571.9	614.4	654.3
47.5°	359.9	363.3	369.2	380.3	399.8	421.3	448.2	482.0	524.2	566.7	600.5
50°	340.8	343.8	349.5	359.9	377.2	398.5	424.9	455.3	493.0	533.8	562.0
52.5°	321.7	323.3	328.6	340.5	355.1	375.9	399.6	427.5	462.8	496.7	525.2
55°	291.4	295.3	298.7	307.4	321.3	341.3	362.5	389.0	416.3	444.9	469.1
57.5°	259.8	264.0	269.0	276.6	287.6	306.2	325.3	346.7	370.1	393.8	414.2
60°	238.9	242.8	247.1	255.8	265.8	280.5	301.3	320.0	337.8	359.5	379.8
62.5°	218.4	222.3	227.4	234.3	243.9	258.0	275.3	291.6	310.1	329.0	344.1
65°	188.2	191.2	195.1	201.6	210.8	223.3	237.6	250.2	266.7	280.5	294.4
67.5°	155.0	160.8	165.9	171.2	178.9	190.6	201.0	213.0	224.2	234.5	247.1
70°	133.1	139.7	144.4	150.0	157.4	167.4	177.3	185.6	194.7	204.6	216.0
72.5°	114.7	119.8	123.6	129.6	136.2	145.5	154.8	161.7	169.0	175.9	186.8
75°	90.7	92.8	95.4	100.2	106.2	113.2	120.6	126.6	130.9	137.1	144.8
77.5°	65.1	69.3	71.0	74.4	78.8	83.1	88.0	93.0	97.2	99.4	105.3
80°	49.9	51.6	53.3	58.1	60.7	65.1	68.5	73.3	75.0	77.2	82.8
82.5°	38.7	39.8	40.8	42.2	43.7	48.0	51.5	54.5	56.3	57.1	61.3
85°	22.6	23.0	23.4	23.9	24.3	24.3	26.0	28.2	31.2	31.2	32.5
87.5°	9.8	10.3	10.0	9.4	10.1	9.4	9.7	9.5	10.5	11.2	11.9
90°	10.8	11.5	10.2	8.9	8.9	5.1	5.1	4.5	3.8	1.9	0.7
92.5°	168.4	202.2	177.0	128.7	79.3	46.9	33.7	24.4	16.6	10.6	7.3
95°	534.3	519.6	392.1	239.7	135.2	79.7	52.9	37.6	29.4	22.9	21.0
97.5°	671.2	547.2	367.0	215.5	129.1	86.4	64.0	50.9	43.2	37.7	37.7
100°	675.7	512.6	332.8	202.8	130.7	93.1	72.6	60.6	52.9	48.4	48.4
102.5°	637.5	469.2	309.8	199.2	135.7	101.7	82.3	70.8	63.6	59.7	58.6
105°	568.0	418.2	290.1	200.8	147.9	117.3	98.8	87.3	79.7	76.5	74.6
107.5°	511.9	389.6	286.5	210.3	162.1	134.0	115.8	104.8	96.6	93.4	92.2
110°	483.9	379.9	287.5	217.4	172.8	144.7	127.5	116.0	108.4	105.2	104.0



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	468.1	375.4	290.6	225.0	183.0	156.0	138.7	127.3	120.1	116.4	115.1
115°	453.2	372.9	296.4	237.2	198.9	173.4	156.2	144.1	137.7	133.2	131.3
117.5°	446.6	372.3	302.7	249.5	214.3	190.1	172.3	160.9	153.9	149.9	148.1
120°	443.0	372.3	307.3	258.2	225.0	200.8	183.0	172.1	165.1	160.6	159.4
122.5°	439.0	371.8	311.9	266.4	235.2	211.0	193.6	181.8	175.3	170.9	169.6
125°	432.2	371.0	318.8	278.6	249.2	226.3	208.5	196.3	189.3	185.5	183.0
127.5°	423.1	369.7	324.2	289.2	262.3	240.1	222.1	209.5	201.5	196.9	194.9
130°	417.6	369.1	328.3	295.8	270.9	249.2	230.8	218.7	209.1	204.0	201.5
132.5°	412.5	368.6	331.9	302.4	278.1	256.4	239.0	225.8	216.8	210.1	208.1
135°	404.8	367.9	337.2	311.1	288.1	267.1	250.5	237.2	226.3	220.0	217.4
137.5°	398.2	367.7	340.4	317.2	295.8	276.1	260.3	246.5	236.1	229.1	226.7
140°	394.6	367.2	343.0	321.3	300.9	281.8	266.4	253.1	242.2	235.2	233.3
142.5°	391.6	367.2	345.0	324.3	305.5	286.9	272.1	259.2	248.9	242.4	240.4
145°	386.3	365.9	346.2	327.7	310.5	293.9	279.9	267.7	258.9	252.4	250.5
147.5°	381.6	363.6	346.8	330.6	315.6	300.0	287.4	277.3	268.2	262.5	261.9
150°	378.1	362.1	346.8	332.2	318.1	304.1	292.0	282.4	274.8	269.7	269.0
152.5°	374.0	359.5	345.8	333.1	320.2	307.7	296.6	288.0	280.9	275.8	275.7
155°	367.9	355.7	344.2	334.0	323.2	312.3	302.8	295.8	289.4	285.6	284.9
157.5°	361.6	351.8	342.6	334.0	325.4	316.2	308.7	302.6	297.6	294.0	294.0
160°	357.0	348.7	341.0	334.0	326.4	318.8	311.8	306.6	302.1	299.6	299.6
162.5°	352.9	345.7	339.6	334.0	327.4	320.2	314.8	310.2	306.2	304.2	304.8
165°	346.2	341.0	336.6	332.8	327.7	322.0	318.1	315.0	311.8	310.5	310.5
167.5°	340.1	336.5	333.5	331.3	327.6	323.3	320.4	318.6	316.2	315.6	316.2
170°	336.0	333.4	331.5	330.2	327.0	323.8	322.0	320.7	318.8	318.1	318.8
172.5°	332.4	330.4	329.5	329.2	326.5	324.3	322.9	322.2	320.8	320.7	321.3
175°	328.3	327.0	327.0	327.7	325.8	324.5	324.5	323.8	323.2	323.2	323.8
177.5°	325.5	325.0	325.0	326.0	325.0	324.5	324.5	324.5	324.0	324.5	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5





TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1082.8	1085.9	1089.4	1096.0	1101.6	1104.0	1108.8	1112.3	1111.3	1116.1	1124.5
5°	1087.0	1098.8	1112.2	1126.1	1141.7	1154.7	1165.1	1175.5	1183.7	1193.7	1208.4
7.5°	1086.4	1107.2	1129.8	1154.7	1180.3	1202.4	1222.9	1243.7	1262.2	1282.4	1308.8
10°	1083.6	1111.3	1139.5	1172.1	1204.5	1235.3	1263.1	1289.2	1313.9	1340.3	1373.7
12.5°	1080.4	1112.4	1146.5	1185.5	1226.0	1263.1	1295.7	1333.2	1364.2	1398.2	1436.8
15°	1066.7	1109.6	1156.0	1206.7	1255.3	1305.1	1349.8	1395.8	1438.7	1479.4	1528.0
17.5°	1050.9	1100.4	1155.1	1215.0	1273.4	1334.0	1387.0	1445.0	1488.8	1543.5	1588.6
20°	1038.0	1091.4	1149.9	1217.2	1283.4	1350.7	1409.2	1468.2	1517.6	1572.7	1629.9
22.5°	1022.5	1081.0	1144.4	1214.0	1283.4	1356.9	1421.7	1480.3	1541.6	1603.5	1662.6
25°	997.3	1058.0	1125.2	1201.5	1281.3	1356.3	1425.7	1498.5	1564.5	1631.7	1684.6
27.5°	966.5	1030.1	1101.0	1179.7	1261.6	1338.5	1420.2	1497.8	1564.1	1628.8	1675.0
30°	941.8	1009.0	1077.1	1156.8	1241.9	1324.2	1411.9	1489.5	1559.3	1617.4	1643.4
32.5°	916.5	980.2	1050.4	1131.2	1218.2	1306.9	1393.8	1473.2	1537.7	1572.6	1573.3
35°	872.5	932.2	1005.1	1084.4	1173.8	1270.1	1358.0	1436.1	1475.5	1478.6	1436.1
37.5°	824.3	879.3	948.0	1027.4	1125.3	1221.1	1311.0	1363.0	1376.1	1332.0	1253.4
40°	790.0	840.7	907.1	988.6	1085.7	1184.6	1266.6	1304.7	1290.9	1219.3	1131.7
42.5°	754.0	801.2	865.1	945.6	1043.1	1143.0	1212.8	1233.3	1196.5	1113.9	1011.4
45°	695.0	738.4	801.8	882.8	976.5	1070.2	1123.1	1112.6	1051.5	953.5	838.6
47.5°	633.7	675.6	732.6	807.6	903.5	984.4	1020.2	988.8	901.8	794.0	700.5
50°	593.2	636.1	688.6	760.1	847.7	925.8	948.8	901.1	804.4	700.7	614.8
52.5°	553.3	590.0	641.4	710.5	794.3	860.2	872.5	817.4	717.6	624.8	548.6
55°	492.6	525.9	569.3	634.4	706.8	762.7	756.2	685.5	594.9	515.6	455.8
57.5°	433.9	459.0	499.0	560.0	623.6	661.1	637.4	577.2	492.7	427.7	377.2
60°	395.0	418.4	455.8	509.1	565.0	586.2	566.3	500.8	434.1	374.6	332.2
62.5°	358.2	378.9	411.0	460.5	505.6	518.3	496.9	439.8	379.6	328.8	293.7
65°	304.8	323.9	351.2	386.4	417.6	423.6	409.8	351.2	305.7	263.2	238.9
67.5°	256.3	268.8	290.2	320.5	337.1	340.6	313.8	277.0	236.9	210.8	192.5
70°	223.7	232.4	252.3	268.8	282.3	282.7	258.0	228.5	197.7	176.5	163.1
72.5°	192.2	200.5	215.6	226.9	237.2	233.8	211.2	187.9	163.1	147.0	137.1
75°	148.3	155.6	163.5	168.7	168.7	164.4	147.9	130.5	116.2	106.6	103.6
77.5°	107.8	113.9	116.5	115.7	114.1	107.4	96.9	85.6	80.5	76.0	73.7
80°	84.5	87.2	88.1	85.9	83.2	75.4	68.5	63.8	58.9	57.2	56.3
82.5°	62.7	65.0	62.7	63.3	57.6	51.2	47.4	45.7	43.7	43.0	42.2
85°	33.4	32.9	32.1	29.9	26.0	25.1	24.7	24.3	23.4	23.9	23.0
87.5°	11.8	11.2	9.9	9.7	9.7	9.8	10.1	10.4	10.6	10.1	11.0
90°	1.9	3.8	4.5	5.1	5.1	8.9	8.9	10.2	11.5	10.8	11.5
92.5°	10.6	16.6	24.4	33.7	46.9	79.3	128.7	177.0	202.2	168.4	125.2
95°	22.9	29.4	37.6	52.9	79.7	135.2	239.7	392.1	519.6	534.3	472.4
97.5°	37.7	43.2	50.9	64.0	86.4	129.1	215.5	367.0	547.2	671.2	697.9
100°	48.4	52.9	60.6	72.6	93.1	130.7	202.8	332.8	512.6	675.7	768.8
102.5°	59.7	63.6	70.8	82.3	101.7	135.7	199.2	309.8	469.2	637.5	765.2
105°	76.5	79.7	87.3	98.8	117.3	147.9	200.8	290.1	418.2	568.0	714.0
107.5°	93.4	96.6	104.8	115.8	134.0	162.1	210.3	286.5	389.6	511.9	641.2
110°	105.2	108.4	116.0	127.5	144.7	172.8	217.4	287.5	379.9	483.9	597.4





TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	116.4	120.1	127.3	138.7	156.0	183.0	225.0	290.6	375.4	468.1	565.2
115°	133.2	137.7	144.1	156.2	173.4	198.9	237.2	296.4	372.9	453.2	533.0
117.5°	149.9	153.9	160.9	172.3	190.1	214.3	249.5	302.7	372.3	446.6	517.1
120°	160.6	165.1	172.1	183.0	200.8	225.0	258.2	307.3	372.3	443.0	510.0
122.5°	170.9	175.3	181.8	193.6	211.0	235.2	266.4	311.9	371.8	439.0	503.9
125°	185.5	189.3	196.3	208.5	226.3	249.2	278.6	318.8	371.0	432.2	493.4
127.5°	196.9	201.5	209.5	222.1	240.1	262.3	289.2	324.2	369.7	423.1	480.7
130°	204.0	209.1	218.7	230.8	249.2	270.9	295.8	328.3	369.1	417.6	470.5
132.5°	210.1	216.8	225.8	239.0	256.4	278.1	302.4	331.9	368.6	412.5	459.7
135°	220.0	226.3	237.2	250.5	267.1	288.1	311.1	337.2	367.9	404.8	445.0
137.5°	229.1	236.1	246.5	260.3	276.1	295.8	317.2	340.4	367.7	398.2	431.6
140°	235.2	242.2	253.1	266.4	281.8	300.9	321.3	343.0	367.2	394.6	424.0
142.5°	242.4	248.9	259.2	272.1	286.9	305.5	324.3	345.0	367.2	391.6	416.8
145°	252.4	258.9	267.7	279.9	293.9	310.5	327.7	346.2	365.9	386.3	406.8
147.5°	262.5	268.2	277.3	287.4	300.0	315.6	330.6	346.8	363.6	381.6	398.4
150°	269.7	274.8	282.4	292.0	304.1	318.1	332.2	346.8	362.1	378.1	393.3
152.5°	275.8	280.9	288.0	296.6	307.7	320.2	333.1	345.8	359.5	374.0	387.8
155°	285.6	289.4	295.8	302.8	312.3	323.2	334.0	344.2	355.7	367.9	379.3
157.5°	294.0	297.6	302.6	308.7	316.2	325.4	334.0	342.6	351.8	361.6	370.2
160°	299.6	302.1	306.6	311.8	318.8	326.4	334.0	341.0	348.7	357.0	364.7
162.5°	304.2	306.2	310.2	314.8	320.2	327.4	334.0	339.6	345.7	352.9	359.1
165°	310.5	311.8	315.0	318.1	322.0	327.7	332.8	336.6	341.0	346.2	351.2
167.5°	315.6	316.2	318.6	320.4	323.3	327.6	331.3	333.5	336.5	340.1	343.7
170°	318.1	318.8	320.7	322.0	323.8	327.0	330.2	331.5	333.4	336.0	339.2
172.5°	320.7	320.8	322.2	322.9	324.3	326.5	329.2	329.5	330.4	332.4	335.1
175°	323.2	323.2	323.8	324.5	324.5	325.8	327.7	327.0	327.0	328.3	329.6
177.5°	324.5	324.0	324.5	324.5	324.5	325.0	326.0	325.0	325.0	325.5	326.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2	1076.2
2.5°	1128.9	1130.3	1131.4	1134.8	1135.1	1138.3	1135.1
5°	1222.3	1228.4	1238.0	1247.5	1248.4	1254.4	1243.6
7.5°	1327.1	1341.2	1349.9	1365.3	1371.4	1375.2	1369.0
10°	1399.2	1412.3	1435.3	1446.5	1457.8	1459.5	1454.3
12.5°	1469.0	1489.6	1507.7	1529.1	1528.5	1543.9	1538.2
15°	1561.9	1583.1	1608.3	1632.1	1640.8	1640.8	1647.7
17.5°	1628.1	1667.0	1693.1	1711.8	1732.3	1735.8	1733.4
20°	1672.8	1714.9	1742.7	1766.9	1780.9	1784.7	1784.7
22.5°	1706.2	1742.0	1769.0	1790.9	1802.3	1806.9	1805.6
25°	1729.2	1760.0	1776.5	1783.0	1786.0	1785.2	1776.9
27.5°	1697.6	1696.2	1685.9	1665.9	1650.9	1641.8	1631.4
30°	1637.3	1614.8	1588.8	1560.1	1523.2	1495.1	1486.4
32.5°	1547.4	1496.8	1452.8	1405.1	1365.5	1337.3	1325.4
35°	1373.7	1293.5	1228.0	1170.8	1129.1	1103.1	1094.5
37.5°	1167.4	1089.8	1008.8	953.2	918.8	892.4	882.6
40°	1036.3	951.8	881.1	829.1	793.5	767.9	767.5
42.5°	916.6	835.9	769.4	731.9	693.6	676.7	676.6
45°	750.6	686.0	629.6	600.1	577.2	563.3	559.4
47.5°	621.4	568.0	530.4	507.0	488.2	479.4	473.7
50°	548.9	502.1	472.2	451.8	441.4	430.2	429.3
52.5°	488.6	450.8	427.5	410.9	397.7	390.9	391.1
55°	410.6	380.7	364.2	351.6	341.3	336.1	333.9
57.5°	345.9	323.5	311.5	299.9	295.5	291.5	290.3
60°	305.7	290.5	279.2	270.1	263.7	262.4	261.9
62.5°	272.4	256.5	248.7	241.7	236.9	234.9	234.2
65°	224.6	212.9	205.9	200.3	198.6	195.6	195.1
67.5°	181.1	174.1	169.4	165.6	163.2	163.1	163.1
70°	154.3	150.4	146.6	144.4	143.1	142.2	142.2
72.5°	131.5	128.6	125.4	124.3	124.0	123.1	122.8
75°	100.2	97.1	97.6	95.4	93.7	91.5	90.2
77.5°	71.0	68.9	68.4	68.2	66.7	66.4	67.1
80°	55.0	52.9	52.5	52.9	52.5	51.2	51.2
82.5°	41.9	40.0	39.6	39.4	39.0	39.4	38.6
85°	22.6	21.7	21.7	21.7	22.6	22.1	21.7
87.5°	10.4	10.2	10.5	10.3	10.4	9.9	10.3
90°	12.1	12.7	12.7	13.4	14.0	13.4	13.4
92.5°	94.2	75.0	62.2	54.7	51.3	49.1	49.1
95°	373.6	288.1	226.3	195.1	175.3	163.9	155.6
97.5°	661.2	598.8	532.3	486.6	448.2	429.0	415.8
100°	781.5	750.3	703.2	647.7	608.8	589.7	584.6
102.5°	828.5	837.6	817.9	783.9	755.7	735.6	731.5
105°	824.3	887.4	913.5	914.8	909.7	900.8	897.0
107.5°	758.6	847.5	904.3	935.9	950.4	956.8	958.4
110°	707.6	800.1	870.2	915.4	942.2	953.7	959.4



TEST NUMBER: P332939-930

CATALOG NUMBER: SA4XXRDIP-C795D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	662.8	750.1	820.2	871.6	904.0	920.1	929.4
115°	611.4	685.9	747.1	797.5	835.8	856.1	861.3
117.5°	582.0	640.7	692.6	735.6	767.7	788.3	792.3
120°	569.3	620.3	665.5	701.9	729.9	746.5	753.5
122.5°	561.1	607.6	647.2	677.9	701.9	715.9	722.9
125°	548.3	592.2	627.3	652.8	671.3	683.4	687.2
127.5°	533.0	576.9	610.3	635.9	652.3	662.5	666.3
130°	520.8	564.2	597.9	624.1	640.1	650.3	654.1
132.5°	507.0	549.4	583.2	608.8	626.8	636.5	640.3
135°	486.4	525.3	557.2	582.7	600.5	610.7	614.6
137.5°	466.7	499.5	528.2	552.0	569.6	578.0	582.7
140°	453.9	482.6	509.4	531.7	545.7	554.6	559.7
142.5°	443.2	467.8	491.0	510.8	523.7	531.7	535.2
145°	428.4	447.5	465.4	481.4	492.1	498.6	501.7
147.5°	415.6	431.0	445.0	456.7	466.0	470.8	472.0
150°	408.0	420.8	432.2	442.5	450.7	454.5	455.2
152.5°	400.3	412.1	421.5	430.2	436.9	439.2	439.9
155°	389.6	399.1	406.8	413.1	418.2	420.1	420.1
157.5°	378.8	386.9	393.0	397.8	401.6	402.8	402.8
160°	371.7	378.7	383.8	387.6	391.4	392.1	392.1
162.5°	365.0	370.6	375.1	377.9	381.7	382.4	381.9
165°	355.1	359.5	362.7	365.3	367.9	367.2	366.6
167.5°	346.7	350.3	352.1	353.4	355.1	355.0	354.4
170°	341.0	343.6	345.5	346.8	347.4	346.8	346.8
172.5°	336.5	338.0	339.4	340.1	340.8	340.1	339.2
175°	330.2	331.5	331.5	331.5	332.8	331.5	330.2
177.5°	326.5	326.5	327.0	326.5	327.0	326.0	325.0
180°	324.5	324.5	324.5	324.5	324.5	324.5	324.5

(END OF REPORT)