

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331729-940

Luminaire Tested: **SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331729-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6785.1 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	89	85	82	79	71	69	67	57	56	55	45	44	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	82	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	42	38	35	33	31	29	25
5	69	58	50	45	63	54	47	42	45	40	37	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	37	33	38	32	29	32	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	35	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27493	27493	27493	27493
5°	30705	27665	24530	27665
10°	34067	27471	21263	27471
15°	35741	27067	16754	27067
20°	30986	26472	14496	26472
25°	20322	25655	12944	25655
30°	13679	24664	11714	24664
35°	11077	23416	10565	23416
40°	9851	22059	9778	22059
45°	8917	20466	8727	20466
50°	8116	18889	8083	18889
55°	7628	17140	7527	17140
60°	6381	15532	6307	15532
65°	5379	14105	6101	14105
70°	4971	12595	5755	12595
75°	4648	10967	5315	10967
80°	4296	9019	4733	9019
85°	3946	7114	4168	7114



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.4	2.4
10°-20°	449.8	6.6
20°-30°	579.6	8.5
30°-40°	550.8	8.1
40°-50°	471.8	7.0
50°-60°	359.3	5.3
60°-70°	227.1	3.3
70°-80°	113.4	1.7
80°-90°	32.8	0.5
90°-100°	43.7	0.6
100°-110°	160.2	2.4
110°-120°	428.4	6.3
120°-130°	707.1	10.4
130°-140°	752.0	11.1
140°-150°	699.0	10.3
150°-160°	562.0	8.3
160°-170°	362.1	5.3
170°-180°	124.6	1.8
0°-30°	1190.8	17.5
0°-40°	1741.6	25.7
0°-60°	2572.7	37.9
0°-90°	2946.0	43.4
90°-120°	632.3	9.3
90°-150°	2790.4	41.1
90°-180°	3839.0	56.6
0°-180°	6785.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1703	1703	1703	1703	1703	
5°	1894	1707	1514	1707	1894	187
15°	2138	1619	1002	1619	2138	577
25°	1141	1440	727	1440	1141	541
35°	562	1188	536	1188	562	360
45°	390	896	382	896	390	302
55°	271	609	267	609	271	238
65°	141	369	160	369	141	143
75°	74	176	85	176	74	79
85°	21	38	22	38	21	24
90°	26	1	26	1	26	12
95°	41	62	41	62	41	38
105°	72	288	72	288	72	75
115°	78	545	78	545	78	195
125°	810	771	810	771	810	701
135°	985	954	985	954	985	759
145°	1123	1106	1123	1106	1123	702
155°	1219	1218	1219	1218	1219	563
165°	1281	1284	1281	1284	1281	362
175°	1305	1313	1305	1313	1305	124
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1771.9	1773.3	1774.8	1771.4	1771.4	1768.6	1762.5	1757.7	1744.5	1742.6	1742.6
5°	1894.5	1893.3	1895.7	1888.0	1877.3	1875.0	1863.8	1849.0	1833.5	1816.4	1812.8
7.5°	2016.3	2014.6	2009.8	2008.6	2000.4	1982.5	1964.4	1945.2	1919.6	1894.6	1882.0
10°	2077.9	2097.4	2085.6	2064.8	2069.0	2041.2	2026.4	2001.0	1979.7	1942.4	1934.1
12.5°	2138.5	2146.2	2142.4	2130.7	2125.4	2106.0	2086.1	2064.0	2024.6	1991.2	1962.0
15°	2138.2	2149.5	2152.4	2148.9	2151.9	2150.7	2140.0	2121.6	2087.4	2050.7	2018.7
17.5°	1980.4	1988.2	2007.6	2020.7	2037.3	2072.3	2089.6	2096.3	2091.2	2070.3	2047.8
20°	1803.4	1790.4	1844.8	1872.6	1896.2	1955.4	2006.3	2025.9	2057.2	2056.6	2050.7
22.5°	1552.5	1555.6	1607.2	1640.2	1709.3	1768.4	1826.5	1900.0	1960.6	2000.7	2024.2
25°	1140.7	1163.2	1214.7	1259.6	1336.6	1446.6	1546.6	1662.6	1772.0	1858.4	1940.6
27.5°	856.8	858.4	899.2	940.8	986.4	1076.6	1202.5	1341.0	1497.0	1625.8	1773.9
30°	733.7	730.1	747.3	772.7	811.7	881.5	976.2	1112.3	1267.9	1462.0	1634.8
32.5°	646.6	646.8	659.7	678.5	711.0	758.0	822.9	933.4	1080.5	1271.2	1473.8
35°	562.0	561.5	571.0	584.5	598.2	628.3	672.7	730.7	831.9	1010.0	1217.0
37.5°	501.5	504.1	508.7	517.2	532.3	549.0	575.7	614.7	686.7	792.0	966.1
40°	467.4	468.6	475.1	482.2	491.1	504.1	526.0	557.3	610.0	694.0	821.2
42.5°	436.1	437.4	441.9	448.6	455.6	468.6	486.7	513.8	556.5	622.1	727.0
45°	390.5	390.5	394.7	397.6	405.3	417.1	431.9	454.4	483.9	532.5	602.4
47.5°	347.7	347.8	350.5	355.6	360.4	369.7	384.2	402.6	424.1	461.6	521.3
50°	323.1	323.6	325.4	329.6	332.5	340.8	352.0	368.0	390.5	419.5	469.2
52.5°	303.2	302.8	305.1	306.8	308.9	314.8	323.2	337.2	357.4	382.5	423.7
55°	271.0	268.6	272.2	275.1	276.9	279.3	284.0	292.8	310.0	331.4	362.1
57.5°	230.8	229.8	232.3	235.0	240.6	246.9	251.0	256.6	265.6	280.8	311.3
60°	197.6	197.6	203.0	204.7	211.2	219.5	227.8	232.6	241.4	251.5	273.9
62.5°	168.3	168.7	171.2	173.0	176.6	186.8	198.4	208.8	217.2	226.9	241.7
65°	140.8	142.0	142.0	143.2	145.5	147.9	152.7	161.0	175.8	189.3	200.5
67.5°	119.5	119.8	120.2	121.5	122.0	124.6	126.5	130.2	133.6	146.5	160.4
70°	105.3	107.1	106.5	107.7	108.3	109.4	111.8	113.6	119.0	121.9	130.2
72.5°	92.0	93.4	93.3	94.0	95.5	95.8	97.6	99.4	102.8	105.3	109.8
75°	74.5	73.9	74.5	75.7	76.3	77.0	77.0	79.3	81.1	83.5	86.4
77.5°	57.5	58.1	58.0	58.1	58.2	59.3	59.2	60.2	62.0	63.2	64.6
80°	46.2	46.7	46.2	46.7	47.3	47.9	47.3	47.9	49.7	50.9	50.9
82.5°	35.8	35.8	36.2	36.3	36.5	36.6	37.4	37.5	38.8	38.6	39.1
85°	21.3	20.7	20.7	20.7	21.3	21.8	21.3	21.3	21.8	21.8	21.8
87.5°	12.7	13.1	13.0	12.9	12.8	12.7	12.5	12.8	12.0	12.3	11.5
90°	25.6	25.1	24.8	24.3	23.9	23.2	22.1	21.0	20.0	19.0	17.3
92.5°	25.6	25.3	25.1	24.9	24.6	24.2	23.6	23.1	22.6	22.0	21.1
95°	40.8	40.9	41.2	41.4	41.6	41.2	40.1	39.1	38.0	37.0	35.5
97.5°	54.4	54.1	53.9	53.7	53.4	52.9	52.0	51.2	50.3	49.5	46.1
100°	63.5	63.1	62.7	62.2	61.8	60.8	59.1	57.4	55.7	54.0	50.5
102.5°	68.0	67.5	66.9	66.3	65.7	64.3	62.2	59.9	57.8	55.6	85.5
105°	72.1	71.2	70.4	69.6	68.7	67.1	64.7	62.4	60.1	57.8	115.3
107.5°	74.1	73.3	72.4	71.6	70.8	71.5	73.8	76.2	78.6	81.0	149.9
110°	74.9	74.0	73.2	72.3	71.5	81.6	102.7	123.8	144.8	165.9	226.8



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	75.6	75.0	74.3	73.7	72.9	111.0	187.9	264.7	341.6	418.4	433.5
115°	77.8	92.9	108.1	123.2	138.4	194.7	292.3	389.8	487.3	584.9	579.6
117.5°	317.4	367.2	417.1	466.9	516.7	553.5	577.0	600.7	624.2	647.8	644.2
120°	578.3	606.6	635.1	663.5	692.0	705.0	702.4	699.9	697.3	694.8	691.1
122.5°	721.6	727.1	732.6	738.2	743.6	745.6	744.1	742.6	741.1	739.6	735.5
125°	810.5	809.9	809.2	808.6	808.0	806.9	805.4	804.0	802.5	801.0	797.0
127.5°	866.6	866.5	866.4	866.2	866.1	865.0	862.8	860.7	858.5	856.4	853.4
130°	901.5	901.7	901.9	902.1	902.3	901.3	898.9	896.6	894.3	892.0	889.7
132.5°	935.6	935.9	936.0	936.2	936.5	935.6	933.6	931.6	929.6	927.6	925.3
135°	984.9	985.3	985.7	986.1	986.6	985.7	983.6	981.5	979.5	977.3	975.4
137.5°	1029.8	1030.6	1031.3	1032.0	1032.7	1032.0	1029.9	1027.9	1025.8	1023.8	1021.6
140°	1057.9	1058.9	1060.0	1061.0	1062.1	1061.7	1059.8	1057.9	1056.0	1054.1	1051.8
142.5°	1085.2	1086.3	1087.3	1088.3	1089.4	1089.0	1087.4	1085.6	1083.9	1082.2	1079.5
145°	1123.3	1124.4	1125.4	1126.5	1127.5	1127.3	1125.8	1124.4	1122.8	1121.4	1117.8
147.5°	1156.8	1157.7	1158.6	1159.5	1160.4	1160.3	1159.2	1158.1	1157.0	1155.9	1152.4
150°	1177.3	1178.4	1179.5	1180.4	1181.5	1181.4	1180.2	1178.9	1177.7	1176.3	1173.0
152.5°	1194.8	1196.1	1197.6	1198.9	1200.3	1200.4	1199.2	1197.8	1196.6	1195.3	1192.1
155°	1219.1	1220.8	1222.4	1224.1	1225.7	1226.0	1224.8	1223.4	1222.2	1220.9	1218.4
157.5°	1241.2	1242.9	1244.5	1246.2	1247.8	1247.9	1246.4	1245.0	1243.6	1242.2	1240.4
160°	1254.1	1255.6	1257.0	1258.6	1260.0	1260.1	1258.8	1257.6	1256.3	1255.1	1253.8
162.5°	1264.7	1266.5	1268.4	1270.2	1271.9	1272.2	1270.7	1269.3	1267.8	1266.4	1265.3
165°	1280.7	1282.1	1283.6	1285.0	1286.6	1286.6	1285.0	1283.6	1282.1	1280.7	1280.1
167.5°	1290.7	1292.6	1294.5	1296.4	1298.2	1298.5	1297.0	1295.6	1294.1	1292.6	1292.0
170°	1296.7	1298.7	1300.6	1302.4	1304.3	1304.6	1303.1	1301.6	1300.1	1298.7	1298.2
172.5°	1301.3	1303.2	1305.1	1307.0	1308.9	1309.1	1307.6	1306.2	1304.7	1303.2	1302.8
175°	1305.3	1307.4	1309.5	1311.6	1313.8	1314.0	1312.6	1311.1	1309.7	1308.1	1307.7
177.5°	1307.8	1309.3	1310.8	1312.3	1313.8	1314.0	1312.8	1311.6	1310.5	1309.3	1309.1
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1743.5	1739.7	1736.4	1727.9	1723.6	1714.1	1712.7	1712.3	1700.0	1688.1	1684.8
5°	1803.4	1793.9	1779.7	1763.2	1746.0	1728.2	1716.4	1706.9	1683.3	1660.8	1647.8
7.5°	1863.8	1843.3	1818.9	1787.5	1761.4	1732.1	1710.2	1690.7	1657.2	1625.0	1603.3
10°	1908.7	1875.5	1843.0	1799.8	1766.1	1733.0	1702.2	1675.6	1637.7	1595.1	1565.0
12.5°	1936.6	1900.1	1855.3	1813.1	1769.4	1727.2	1686.1	1651.9	1607.4	1563.4	1527.5
15°	1974.3	1935.3	1880.9	1820.5	1764.3	1709.3	1662.0	1619.3	1561.4	1508.7	1464.9
17.5°	2005.3	1951.5	1893.1	1823.3	1758.2	1688.3	1627.3	1572.9	1508.3	1444.8	1393.2
20°	2015.2	1961.9	1894.5	1824.7	1747.8	1665.5	1599.8	1540.7	1471.4	1402.2	1343.1
22.5°	2009.0	1967.6	1892.6	1809.0	1730.3	1644.2	1570.0	1501.4	1424.6	1354.0	1285.3
25°	1967.3	1953.0	1882.0	1790.9	1701.0	1601.1	1515.2	1440.1	1352.5	1276.8	1202.2
27.5°	1869.9	1900.5	1856.5	1759.4	1659.5	1552.3	1455.8	1370.3	1279.4	1194.2	1119.9
30°	1776.2	1846.6	1827.7	1737.7	1625.9	1520.5	1412.3	1322.9	1225.9	1138.4	1065.0
32.5°	1647.9	1764.2	1782.7	1707.4	1591.8	1476.0	1362.6	1273.7	1172.4	1080.1	1008.6
35°	1443.7	1617.6	1697.5	1649.6	1533.6	1408.7	1291.6	1188.0	1086.3	995.1	924.2
37.5°	1200.0	1436.9	1570.0	1573.4	1467.0	1337.1	1209.6	1106.8	1002.6	913.2	836.3
40°	1041.9	1298.7	1472.0	1510.5	1420.6	1280.3	1151.4	1046.6	944.9	857.3	769.2
42.5°	899.9	1155.7	1368.9	1435.7	1364.2	1224.9	1095.6	986.1	887.2	804.3	714.3
45°	727.7	951.4	1186.2	1305.8	1266.1	1137.2	1000.5	896.3	803.4	731.9	645.5
47.5°	613.9	771.5	998.8	1160.5	1159.8	1042.1	907.6	807.9	721.7	654.6	584.7
50°	549.0	686.3	878.6	1062.0	1077.4	978.6	850.8	752.0	671.5	601.1	544.9
52.5°	490.8	604.0	776.9	952.7	996.5	910.9	786.9	695.7	617.6	552.9	504.7
55°	414.7	502.3	633.6	798.2	864.4	804.1	694.0	608.9	545.5	491.1	449.7
57.5°	350.9	416.5	521.9	654.3	731.6	693.6	602.8	533.6	479.4	430.2	397.4
60°	310.6	364.4	453.8	564.5	649.6	623.0	545.5	481.0	434.9	392.3	361.5
62.5°	272.8	319.1	395.6	485.4	563.5	552.5	489.2	435.1	394.7	355.8	329.8
65°	219.5	253.2	313.0	383.4	446.1	451.5	405.9	369.2	333.1	302.4	279.3
67.5°	174.8	196.8	238.9	298.2	345.2	361.9	334.1	306.1	277.5	253.7	233.7
70°	147.3	165.1	195.8	243.8	287.0	304.7	288.7	266.8	242.0	222.5	205.3
72.5°	119.4	136.7	159.3	194.6	231.6	250.7	245.2	229.4	209.3	193.1	176.9
75°	90.0	95.2	110.7	134.3	163.3	179.9	184.0	175.8	159.7	147.3	137.9
77.5°	66.5	69.7	77.0	89.4	108.4	123.1	129.2	128.2	117.3	110.0	101.2
80°	53.2	55.0	58.6	63.9	78.1	92.9	97.0	97.0	89.3	86.4	77.5
82.5°	40.5	41.7	43.9	46.8	53.5	66.3	71.0	72.0	67.1	63.2	56.2
85°	23.1	22.5	23.6	25.4	26.7	30.1	37.3	38.4	37.3	32.5	30.8
87.5°	11.1	11.3	11.0	10.1	10.1	10.1	12.0	13.9	12.5	11.5	11.1
90°	15.6	13.9	12.2	10.3	7.9	5.6	3.3	1.0	3.3	5.6	7.9
92.5°	20.3	19.4	18.6	18.3	18.5	18.7	18.9	19.2	18.9	18.7	18.5
95°	34.1	32.5	31.0	33.8	40.8	47.7	54.7	61.6	54.7	47.7	40.8
97.5°	42.6	39.2	35.8	44.0	63.5	83.1	102.7	122.3	102.7	83.1	63.5
100°	46.9	43.2	39.7	52.3	81.2	110.0	138.9	167.8	138.9	110.0	81.2
102.5°	115.5	145.4	175.4	193.4	199.5	205.6	211.7	217.8	211.7	205.6	199.5
105°	172.8	230.3	287.8	313.4	307.1	300.8	294.5	288.2	294.5	300.8	307.1
107.5°	218.9	287.8	356.9	388.8	383.6	378.5	373.4	368.4	373.4	378.5	383.6
110°	287.7	348.5	409.4	437.7	433.2	428.8	424.4	419.9	424.4	428.8	433.2





TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	448.5	463.5	478.6	484.1	480.2	476.3	472.4	468.5	472.4	476.3	480.2
115°	574.4	569.1	563.8	559.4	555.8	552.2	548.7	545.1	548.7	552.2	555.8
117.5°	640.6	636.9	633.3	629.5	625.5	621.5	617.5	613.5	617.5	621.5	625.5
120°	687.2	683.5	679.7	676.2	673.1	669.9	666.7	663.5	666.7	669.9	673.1
122.5°	731.3	727.2	723.1	719.3	716.0	712.7	709.4	706.1	709.4	712.7	716.0
125°	793.0	789.0	785.0	781.6	778.9	776.1	773.4	770.7	773.4	776.1	778.9
127.5°	850.3	847.4	844.4	841.4	838.4	835.4	832.3	829.3	832.3	835.4	838.4
130°	887.3	885.0	882.7	879.9	876.6	873.2	869.8	866.4	869.8	873.2	876.6
132.5°	923.0	920.7	918.4	915.8	912.9	910.1	907.2	904.3	907.2	910.1	912.9
135°	973.5	971.6	969.7	967.1	963.8	960.4	957.0	953.6	957.0	960.4	963.8
137.5°	1019.5	1017.4	1015.1	1012.9	1010.6	1008.2	1005.8	1003.4	1005.8	1008.2	1010.6
140°	1049.5	1047.1	1044.8	1042.9	1041.2	1039.5	1037.8	1036.1	1037.8	1039.5	1041.2
142.5°	1076.8	1074.2	1071.6	1069.4	1067.9	1066.4	1064.9	1063.4	1064.9	1066.4	1067.9
145°	1114.2	1110.6	1107.1	1105.4	1105.6	1105.8	1106.0	1106.3	1106.0	1105.8	1105.6
147.5°	1148.8	1145.3	1141.7	1140.4	1141.2	1142.0	1142.8	1143.6	1142.8	1142.0	1141.2
150°	1169.7	1166.3	1162.9	1162.0	1163.4	1164.9	1166.4	1167.9	1166.4	1164.9	1163.4
152.5°	1188.9	1185.7	1182.5	1181.8	1183.4	1185.0	1186.7	1188.3	1186.7	1185.0	1183.4
155°	1215.8	1213.4	1210.9	1210.5	1212.4	1214.3	1216.2	1218.1	1216.2	1214.3	1212.4
157.5°	1238.6	1236.9	1235.1	1235.0	1236.6	1238.2	1239.8	1241.4	1239.8	1238.2	1236.6
160°	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1253.8	1252.5	1251.2
162.5°	1264.3	1263.1	1262.0	1262.1	1263.4	1264.6	1266.0	1267.2	1266.0	1264.6	1263.4
165°	1279.4	1278.7	1278.1	1278.4	1279.7	1280.9	1282.2	1283.5	1282.2	1280.9	1279.7
167.5°	1291.4	1290.8	1290.2	1290.6	1291.8	1293.1	1294.4	1295.7	1294.4	1293.1	1291.8
170°	1297.8	1297.4	1297.0	1297.4	1298.7	1299.9	1301.2	1302.4	1301.2	1299.9	1298.7
172.5°	1302.3	1302.0	1301.5	1302.0	1303.2	1304.5	1305.7	1307.0	1305.7	1304.5	1303.2
175°	1307.3	1306.9	1306.4	1307.0	1308.5	1309.9	1311.4	1312.9	1311.4	1309.9	1308.5
177.5°	1308.9	1308.8	1308.6	1309.1	1310.3	1311.4	1312.7	1313.8	1312.7	1311.4	1310.3
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1678.6	1675.3	1669.2	1659.7	1654.0	1644.1	1637.4	1641.3	1642.2	1641.3	1640.3
5°	1633.5	1621.1	1604.0	1587.4	1572.0	1555.5	1546.0	1541.9	1533.6	1528.8	1526.5
7.5°	1579.0	1557.6	1533.3	1504.5	1480.0	1454.3	1441.2	1434.7	1417.7	1408.5	1400.4
10°	1538.3	1504.6	1480.3	1442.4	1419.4	1385.6	1362.6	1363.2	1340.1	1327.0	1317.6
12.5°	1493.3	1456.3	1415.9	1381.9	1349.8	1322.7	1294.9	1283.6	1259.2	1246.6	1221.0
15°	1418.8	1375.6	1333.0	1286.8	1254.3	1212.3	1172.1	1122.9	1083.3	1049.0	1039.6
17.5°	1337.4	1283.9	1241.2	1187.0	1131.2	1060.6	1014.0	985.4	961.5	943.4	930.0
20°	1281.6	1227.1	1181.5	1099.9	1024.8	976.9	942.5	920.6	895.8	876.3	865.6
22.5°	1222.8	1166.0	1103.9	1012.8	954.2	915.8	885.2	860.1	843.2	828.0	818.2
25°	1139.5	1077.4	975.1	912.3	865.0	824.7	803.4	788.1	770.3	749.7	740.1
27.5°	1051.5	952.7	879.2	832.6	787.4	761.3	742.1	719.1	703.2	693.9	684.0
30°	985.7	886.9	829.5	778.6	746.6	717.6	695.2	682.2	666.8	650.9	644.4
32.5°	912.3	833.4	778.4	736.0	703.6	678.9	661.1	640.1	628.9	619.1	605.5
35°	821.2	761.4	711.1	676.9	646.1	626.0	605.3	592.8	572.7	564.5	559.1
37.5°	744.0	692.2	654.7	618.5	594.1	571.9	559.2	539.5	530.7	519.2	508.0
40°	700.5	649.6	613.6	584.0	556.8	540.2	524.2	508.3	495.3	489.9	476.3
42.5°	656.0	614.7	578.5	546.1	527.9	510.3	490.2	478.4	464.9	456.3	447.9
45°	594.6	557.9	527.2	500.5	480.5	462.1	449.1	429.5	421.9	404.7	397.6
47.5°	540.6	506.6	477.2	451.9	432.3	420.4	401.3	386.0	373.7	363.2	354.0
50°	502.3	473.9	445.5	423.0	405.3	388.2	368.6	360.9	342.0	336.6	331.4
52.5°	467.3	440.3	414.3	392.3	374.5	357.8	340.6	330.6	317.8	312.5	308.6
55°	418.3	392.3	367.4	347.9	330.1	313.0	302.4	289.9	284.0	279.8	275.1
57.5°	369.1	345.6	326.6	306.8	289.0	275.4	263.1	255.6	249.4	244.0	238.4
60°	337.9	315.3	298.2	279.8	261.5	250.3	240.8	231.9	224.8	216.5	214.2
62.5°	304.7	285.1	269.3	251.5	235.5	225.2	216.2	207.8	199.3	187.2	183.9
65°	259.1	243.8	227.2	212.4	198.2	188.2	175.1	165.7	162.1	161.0	160.3
67.5°	217.9	203.4	189.2	174.1	161.1	151.9	145.2	143.7	141.2	140.5	138.9
70°	190.5	176.9	162.7	148.5	136.1	134.3	132.0	129.6	126.6	125.5	124.2
72.5°	165.9	151.9	137.6	126.3	120.9	118.7	116.3	114.0	111.9	110.8	110.0
75°	127.2	114.2	104.7	100.6	97.6	95.9	92.3	90.5	89.3	87.6	86.9
77.5°	91.6	84.3	79.9	77.3	74.2	72.3	70.3	68.5	67.2	66.9	65.9
80°	69.8	66.3	63.3	59.7	58.6	56.2	55.6	53.9	54.4	52.7	52.7
82.5°	54.2	49.7	47.2	45.6	44.4	42.4	41.9	41.0	41.2	39.9	39.9
85°	27.8	26.7	25.4	24.3	24.3	22.5	23.1	22.5	22.5	21.3	20.7
87.5°	11.1	11.0	10.3	10.7	11.1	10.9	11.1	10.9	11.1	11.2	11.0
90°	10.3	12.2	13.9	15.6	17.3	19.0	20.0	21.0	22.1	23.2	23.9
92.5°	18.3	18.6	19.4	20.3	21.1	22.0	22.6	23.1	23.6	24.2	24.6
95°	33.8	31.0	32.5	34.1	35.5	37.0	38.0	39.1	40.1	41.2	41.6
97.5°	44.0	35.8	39.2	42.6	46.1	49.5	50.3	51.2	52.0	52.9	53.4
100°	52.3	39.7	43.2	46.9	50.5	54.0	55.7	57.4	59.1	60.8	61.8
102.5°	193.4	175.4	145.4	115.5	85.5	55.6	57.8	59.9	62.2	64.3	65.7
105°	313.4	287.8	230.3	172.8	115.3	57.8	60.1	62.4	64.7	67.1	68.7
107.5°	388.8	356.9	287.8	218.9	149.9	81.0	78.6	76.2	73.8	71.5	70.8
110°	437.7	409.4	348.5	287.7	226.8	165.9	144.8	123.8	102.7	81.6	71.5



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	484.1	478.6	463.5	448.5	433.5	418.4	341.6	264.7	187.9	111.0	72.9
115°	559.4	563.8	569.1	574.4	579.6	584.9	487.3	389.8	292.3	194.7	138.4
117.5°	629.5	633.3	636.9	640.6	644.2	647.8	624.2	600.7	577.0	553.5	516.7
120°	676.2	679.7	683.5	687.2	691.1	694.8	697.3	699.9	702.4	705.0	692.0
122.5°	719.3	723.1	727.2	731.3	735.5	739.6	741.1	742.6	744.1	745.6	743.6
125°	781.6	785.0	789.0	793.0	797.0	801.0	802.5	804.0	805.4	806.9	808.0
127.5°	841.4	844.4	847.4	850.3	853.4	856.4	858.5	860.7	862.8	865.0	866.1
130°	879.9	882.7	885.0	887.3	889.7	892.0	894.3	896.6	898.9	901.3	902.3
132.5°	915.8	918.4	920.7	923.0	925.3	927.6	929.6	931.6	933.6	935.6	936.5
135°	967.1	969.7	971.6	973.5	975.4	977.3	979.5	981.5	983.6	985.7	986.6
137.5°	1012.9	1015.1	1017.4	1019.5	1021.6	1023.8	1025.8	1027.9	1029.9	1032.0	1032.7
140°	1042.9	1044.8	1047.1	1049.5	1051.8	1054.1	1056.0	1057.9	1059.8	1061.7	1062.1
142.5°	1069.4	1071.6	1074.2	1076.8	1079.5	1082.2	1083.9	1085.6	1087.4	1089.0	1089.4
145°	1105.4	1107.1	1110.6	1114.2	1117.8	1121.4	1122.8	1124.4	1125.8	1127.3	1127.5
147.5°	1140.4	1141.7	1145.3	1148.8	1152.4	1155.9	1157.0	1158.1	1159.2	1160.3	1160.4
150°	1162.0	1162.9	1166.3	1169.7	1173.0	1176.3	1177.7	1178.9	1180.2	1181.4	1181.5
152.5°	1181.8	1182.5	1185.7	1188.9	1192.1	1195.3	1196.6	1197.8	1199.2	1200.4	1200.3
155°	1210.5	1210.9	1213.4	1215.8	1218.4	1220.9	1222.2	1223.4	1224.8	1226.0	1225.7
157.5°	1235.0	1235.1	1236.9	1238.6	1240.4	1242.2	1243.6	1245.0	1246.4	1247.9	1247.8
160°	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1256.3	1257.6	1258.8	1260.1	1260.0
162.5°	1262.1	1262.0	1263.1	1264.3	1265.3	1266.4	1267.8	1269.3	1270.7	1272.2	1271.9
165°	1278.4	1278.1	1278.7	1279.4	1280.1	1280.7	1282.1	1283.6	1285.0	1286.6	1286.6
167.5°	1290.6	1290.2	1290.8	1291.4	1292.0	1292.6	1294.1	1295.6	1297.0	1298.5	1298.2
170°	1297.4	1297.0	1297.4	1297.8	1298.2	1298.7	1300.1	1301.6	1303.1	1304.6	1304.3
172.5°	1302.0	1301.5	1302.0	1302.3	1302.8	1303.2	1304.7	1306.2	1307.6	1309.1	1308.9
175°	1307.0	1306.4	1306.9	1307.3	1307.7	1308.1	1309.7	1311.1	1312.6	1314.0	1313.8
177.5°	1309.1	1308.6	1308.8	1308.9	1309.1	1309.3	1310.5	1311.6	1312.8	1314.0	1313.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1635.1	1636.0	1634.6	1635.6	1634.6	1636.0	1635.1	1640.3	1641.3	1642.2	1641.3
5°	1523.5	1516.4	1515.2	1513.5	1515.2	1516.4	1523.5	1526.5	1528.8	1533.6	1541.9
7.5°	1390.3	1389.2	1386.3	1382.2	1386.3	1389.2	1390.3	1400.4	1408.5	1417.7	1434.7
10°	1304.6	1301.6	1301.1	1296.9	1301.1	1301.6	1304.6	1317.6	1327.0	1340.1	1363.2
12.5°	1204.3	1185.2	1183.2	1172.9	1183.2	1185.2	1204.3	1221.0	1246.6	1259.2	1283.6
15°	1025.4	1021.8	1010.0	1002.3	1010.0	1021.8	1025.4	1039.6	1049.0	1083.3	1122.9
17.5°	923.1	911.5	907.9	906.2	907.9	911.5	923.1	930.0	943.4	961.5	985.4
20°	857.3	846.7	844.9	843.7	844.9	846.7	857.3	865.6	876.3	895.8	920.6
22.5°	811.9	800.8	796.1	792.6	796.1	800.8	811.9	818.2	828.0	843.2	860.1
25°	734.2	730.1	727.7	726.6	727.7	730.1	734.2	740.1	749.7	770.3	788.1
27.5°	673.5	664.4	662.6	659.6	662.6	664.4	673.5	684.0	693.9	703.2	719.1
30°	639.0	636.1	631.9	628.3	631.9	636.1	639.0	644.4	650.9	666.8	682.2
32.5°	598.2	595.8	592.1	590.5	592.1	595.8	598.2	605.5	619.1	628.9	640.1
35°	553.2	544.9	541.4	536.0	541.4	544.9	553.2	559.1	564.5	572.7	592.8
37.5°	505.5	501.1	496.1	497.9	496.1	501.1	505.5	508.0	519.2	530.7	539.5
40°	468.6	465.7	464.5	463.9	464.5	465.7	468.6	476.3	489.9	495.3	508.3
42.5°	439.3	431.1	428.0	427.8	428.0	431.1	439.3	447.9	456.3	464.9	478.4
45°	394.7	386.9	381.7	382.2	381.7	386.9	394.7	397.6	404.7	421.9	429.5
47.5°	348.9	348.7	345.4	346.5	345.4	348.7	348.9	354.0	363.2	373.7	386.0
50°	327.2	323.6	321.3	321.8	321.3	323.6	327.2	331.4	336.6	342.0	360.9
52.5°	306.4	303.3	301.4	303.9	301.4	303.3	306.4	308.6	312.5	317.8	330.6
55°	272.2	268.6	268.0	267.4	268.0	268.6	272.2	275.1	279.8	284.0	289.9
57.5°	234.0	231.6	228.0	226.5	228.0	231.6	234.0	238.4	244.0	249.4	255.6
60°	206.5	201.8	195.8	195.3	195.8	201.8	206.5	214.2	216.5	224.8	231.9
62.5°	181.4	180.5	179.2	179.1	179.2	180.5	181.4	183.9	187.2	199.3	207.8
65°	159.2	158.5	159.2	159.7	159.2	158.5	159.2	160.3	161.0	162.1	165.7
67.5°	138.7	137.6	136.5	137.1	136.5	137.6	138.7	138.9	140.5	141.2	143.7
70°	123.1	122.4	121.9	121.9	121.9	122.4	123.1	124.2	125.5	126.6	129.6
72.5°	107.9	107.8	107.2	106.7	107.2	107.8	107.9	110.0	110.8	111.9	114.0
75°	86.4	85.2	85.2	85.2	85.2	85.2	86.4	86.9	87.6	89.3	90.5
77.5°	65.8	65.2	64.6	64.1	64.6	65.2	65.8	65.9	66.9	67.2	68.5
80°	52.1	51.5	50.9	50.9	50.9	51.5	52.1	52.7	52.7	54.4	53.9
82.5°	39.8	39.1	39.1	38.6	39.1	39.1	39.8	39.9	39.9	41.2	41.0
85°	21.3	21.8	21.3	22.5	21.3	21.8	21.3	20.7	21.3	22.5	22.5
87.5°	11.1	10.6	11.1	10.8	11.1	10.6	11.1	11.0	11.2	11.1	10.9
90°	24.3	24.8	25.1	25.6	25.1	24.8	24.3	23.9	23.2	22.1	21.0
92.5°	24.9	25.1	25.3	25.6	25.3	25.1	24.9	24.6	24.2	23.6	23.1
95°	41.4	41.2	40.9	40.8	40.9	41.2	41.4	41.6	41.2	40.1	39.1
97.5°	53.7	53.9	54.1	54.4	54.1	53.9	53.7	53.4	52.9	52.0	51.2
100°	62.2	62.7	63.1	63.5	63.1	62.7	62.2	61.8	60.8	59.1	57.4
102.5°	66.3	66.9	67.5	68.0	67.5	66.9	66.3	65.7	64.3	62.2	59.9
105°	69.6	70.4	71.2	72.1	71.2	70.4	69.6	68.7	67.1	64.7	62.4
107.5°	71.6	72.4	73.3	74.1	73.3	72.4	71.6	70.8	71.5	73.8	76.2
110°	72.3	73.2	74.0	74.9	74.0	73.2	72.3	71.5	81.6	102.7	123.8



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	73.7	74.3	75.0	75.6	75.0	74.3	73.7	72.9	111.0	187.9	264.7
115°	123.2	108.1	92.9	77.8	92.9	108.1	123.2	138.4	194.7	292.3	389.8
117.5°	466.9	417.1	367.2	317.4	367.2	417.1	466.9	516.7	553.5	577.0	600.7
120°	663.5	635.1	606.6	578.3	606.6	635.1	663.5	692.0	705.0	702.4	699.9
122.5°	738.2	732.6	727.1	721.6	727.1	732.6	738.2	743.6	745.6	744.1	742.6
125°	808.6	809.2	809.9	810.5	809.9	809.2	808.6	808.0	806.9	805.4	804.0
127.5°	866.2	866.4	866.5	866.6	866.5	866.4	866.2	866.1	865.0	862.8	860.7
130°	902.1	901.9	901.7	901.5	901.7	901.9	902.1	902.3	901.3	898.9	896.6
132.5°	936.2	936.0	935.9	935.6	935.9	936.0	936.2	936.5	935.6	933.6	931.6
135°	986.1	985.7	985.3	984.9	985.3	985.7	986.1	986.6	985.7	983.6	981.5
137.5°	1032.0	1031.3	1030.6	1029.8	1030.6	1031.3	1032.0	1032.7	1032.0	1029.9	1027.9
140°	1061.0	1060.0	1058.9	1057.9	1058.9	1060.0	1061.0	1062.1	1061.7	1059.8	1057.9
142.5°	1088.3	1087.3	1086.3	1085.2	1086.3	1087.3	1088.3	1089.4	1089.0	1087.4	1085.6
145°	1126.5	1125.4	1124.4	1123.3	1124.4	1125.4	1126.5	1127.5	1127.3	1125.8	1124.4
147.5°	1159.5	1158.6	1157.7	1156.8	1157.7	1158.6	1159.5	1160.4	1160.3	1159.2	1158.1
150°	1180.4	1179.5	1178.4	1177.3	1178.4	1179.5	1180.4	1181.5	1181.4	1180.2	1178.9
152.5°	1198.9	1197.6	1196.1	1194.8	1196.1	1197.6	1198.9	1200.3	1200.4	1199.2	1197.8
155°	1224.1	1222.4	1220.8	1219.1	1220.8	1222.4	1224.1	1225.7	1226.0	1224.8	1223.4
157.5°	1246.2	1244.5	1242.9	1241.2	1242.9	1244.5	1246.2	1247.8	1247.9	1246.4	1245.0
160°	1258.6	1257.0	1255.6	1254.1	1255.6	1257.0	1258.6	1260.0	1260.1	1258.8	1257.6
162.5°	1270.2	1268.4	1266.5	1264.7	1266.5	1268.4	1270.2	1271.9	1272.2	1270.7	1269.3
165°	1285.0	1283.6	1282.1	1280.7	1282.1	1283.6	1285.0	1286.6	1286.6	1285.0	1283.6
167.5°	1296.4	1294.5	1292.6	1290.7	1292.6	1294.5	1296.4	1298.2	1298.5	1297.0	1295.6
170°	1302.4	1300.6	1298.7	1296.7	1298.7	1300.6	1302.4	1304.3	1304.6	1303.1	1301.6
172.5°	1307.0	1305.1	1303.2	1301.3	1303.2	1305.1	1307.0	1308.9	1309.1	1307.6	1306.2
175°	1311.6	1309.5	1307.4	1305.3	1307.4	1309.5	1311.6	1313.8	1314.0	1312.6	1311.1
177.5°	1312.3	1310.8	1309.3	1307.8	1309.3	1310.8	1312.3	1313.8	1314.0	1312.8	1311.6
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1637.4	1644.1	1654.0	1659.7	1669.2	1675.3	1678.6	1684.8	1688.1	1700.0	1712.3
5°	1546.0	1555.5	1572.0	1587.4	1604.0	1621.1	1633.5	1647.8	1660.8	1683.3	1706.9
7.5°	1441.2	1454.3	1480.0	1504.5	1533.3	1557.6	1579.0	1603.3	1625.0	1657.2	1690.7
10°	1362.6	1385.6	1419.4	1442.4	1480.3	1504.6	1538.3	1565.0	1595.1	1637.7	1675.6
12.5°	1294.9	1322.7	1349.8	1381.9	1415.9	1456.3	1493.3	1527.5	1563.4	1607.4	1651.9
15°	1172.1	1212.3	1254.3	1286.8	1333.0	1375.6	1418.8	1464.9	1508.7	1561.4	1619.3
17.5°	1014.0	1060.6	1131.2	1187.0	1241.2	1283.9	1337.4	1393.2	1444.8	1508.3	1572.9
20°	942.5	976.9	1024.8	1099.9	1181.5	1227.1	1281.6	1343.1	1402.2	1471.4	1540.7
22.5°	885.2	915.8	954.2	1012.8	1103.9	1166.0	1222.8	1285.3	1354.0	1424.6	1501.4
25°	803.4	824.7	865.0	912.3	975.1	1077.4	1139.5	1202.2	1276.8	1352.5	1440.1
27.5°	742.1	761.3	787.4	832.6	879.2	952.7	1051.5	1119.9	1194.2	1279.4	1370.3
30°	695.2	717.6	746.6	778.6	829.5	886.9	985.7	1065.0	1138.4	1225.9	1322.9
32.5°	661.1	678.9	703.6	736.0	778.4	833.4	912.3	1008.6	1080.1	1172.4	1273.7
35°	605.3	626.0	646.1	676.9	711.1	761.4	821.2	924.2	995.1	1086.3	1188.0
37.5°	559.2	571.9	594.1	618.5	654.7	692.2	744.0	836.3	913.2	1002.6	1106.8
40°	524.2	540.2	556.8	584.0	613.6	649.6	700.5	769.2	857.3	944.9	1046.6
42.5°	490.2	510.3	527.9	546.1	578.5	614.7	656.0	714.3	804.3	887.2	986.1
45°	449.1	462.1	480.5	500.5	527.2	557.9	594.6	645.5	731.9	803.4	896.3
47.5°	401.3	420.4	432.3	451.9	477.2	506.6	540.6	584.7	654.6	721.7	807.9
50°	368.6	388.2	405.3	423.0	445.5	473.9	502.3	544.9	601.1	671.5	752.0
52.5°	340.6	357.8	374.5	392.3	414.3	440.3	467.3	504.7	552.9	617.6	695.7
55°	302.4	313.0	330.1	347.9	367.4	392.3	418.3	449.7	491.1	545.5	608.9
57.5°	263.1	275.4	289.0	306.8	326.6	345.6	369.1	397.4	430.2	479.4	533.6
60°	240.8	250.3	261.5	279.8	298.2	315.3	337.9	361.5	392.3	434.9	481.0
62.5°	216.2	225.2	235.5	251.5	269.3	285.1	304.7	329.8	355.8	394.7	435.1
65°	175.1	188.2	198.2	212.4	227.2	243.8	259.1	279.3	302.4	333.1	369.2
67.5°	145.2	151.9	161.1	174.1	189.2	203.4	217.9	233.7	253.7	277.5	306.1
70°	132.0	134.3	136.1	148.5	162.7	176.9	190.5	205.3	222.5	242.0	266.8
72.5°	116.3	118.7	120.9	126.3	137.6	151.9	165.9	176.9	193.1	209.3	229.4
75°	92.3	95.9	97.6	100.6	104.7	114.2	127.2	137.9	147.3	159.7	175.8
77.5°	70.3	72.3	74.2	77.3	79.9	84.3	91.6	101.2	110.0	117.3	128.2
80°	55.6	56.2	58.6	59.7	63.3	66.3	69.8	77.5	86.4	89.3	97.0
82.5°	41.9	42.4	44.4	45.6	47.2	49.7	54.2	56.2	63.2	67.1	72.0
85°	23.1	22.5	24.3	24.3	25.4	26.7	27.8	30.8	32.5	37.3	38.4
87.5°	11.1	10.9	11.1	10.7	10.3	11.0	11.1	11.1	11.5	12.5	13.9
90°	20.0	19.0	17.3	15.6	13.9	12.2	10.3	7.9	5.6	3.3	1.0
92.5°	22.6	22.0	21.1	20.3	19.4	18.6	18.3	18.5	18.7	18.9	19.2
95°	38.0	37.0	35.5	34.1	32.5	31.0	33.8	40.8	47.7	54.7	61.6
97.5°	50.3	49.5	46.1	42.6	39.2	35.8	44.0	63.5	83.1	102.7	122.3
100°	55.7	54.0	50.5	46.9	43.2	39.7	52.3	81.2	110.0	138.9	167.8
102.5°	57.8	55.6	85.5	115.5	145.4	175.4	193.4	199.5	205.6	211.7	217.8
105°	60.1	57.8	115.3	172.8	230.3	287.8	313.4	307.1	300.8	294.5	288.2
107.5°	78.6	81.0	149.9	218.9	287.8	356.9	388.8	383.6	378.5	373.4	368.4
110°	144.8	165.9	226.8	287.7	348.5	409.4	437.7	433.2	428.8	424.4	419.9



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	341.6	418.4	433.5	448.5	463.5	478.6	484.1	480.2	476.3	472.4	468.5
115°	487.3	584.9	579.6	574.4	569.1	563.8	559.4	555.8	552.2	548.7	545.1
117.5°	624.2	647.8	644.2	640.6	636.9	633.3	629.5	625.5	621.5	617.5	613.5
120°	697.3	694.8	691.1	687.2	683.5	679.7	676.2	673.1	669.9	666.7	663.5
122.5°	741.1	739.6	735.5	731.3	727.2	723.1	719.3	716.0	712.7	709.4	706.1
125°	802.5	801.0	797.0	793.0	789.0	785.0	781.6	778.9	776.1	773.4	770.7
127.5°	858.5	856.4	853.4	850.3	847.4	844.4	841.4	838.4	835.4	832.3	829.3
130°	894.3	892.0	889.7	887.3	885.0	882.7	879.9	876.6	873.2	869.8	866.4
132.5°	929.6	927.6	925.3	923.0	920.7	918.4	915.8	912.9	910.1	907.2	904.3
135°	979.5	977.3	975.4	973.5	971.6	969.7	967.1	963.8	960.4	957.0	953.6
137.5°	1025.8	1023.8	1021.6	1019.5	1017.4	1015.1	1012.9	1010.6	1008.2	1005.8	1003.4
140°	1056.0	1054.1	1051.8	1049.5	1047.1	1044.8	1042.9	1041.2	1039.5	1037.8	1036.1
142.5°	1083.9	1082.2	1079.5	1076.8	1074.2	1071.6	1069.4	1067.9	1066.4	1064.9	1063.4
145°	1122.8	1121.4	1117.8	1114.2	1110.6	1107.1	1105.4	1105.6	1105.8	1106.0	1106.3
147.5°	1157.0	1155.9	1152.4	1148.8	1145.3	1141.7	1140.4	1141.2	1142.0	1142.8	1143.6
150°	1177.7	1176.3	1173.0	1169.7	1166.3	1162.9	1162.0	1163.4	1164.9	1166.4	1167.9
152.5°	1196.6	1195.3	1192.1	1188.9	1185.7	1182.5	1181.8	1183.4	1185.0	1186.7	1188.3
155°	1222.2	1220.9	1218.4	1215.8	1213.4	1210.9	1210.5	1212.4	1214.3	1216.2	1218.1
157.5°	1243.6	1242.2	1240.4	1238.6	1236.9	1235.1	1235.0	1236.6	1238.2	1239.8	1241.4
160°	1256.3	1255.1	1253.8	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1
162.5°	1267.8	1266.4	1265.3	1264.3	1263.1	1262.0	1262.1	1263.4	1264.6	1266.0	1267.2
165°	1282.1	1280.7	1280.1	1279.4	1278.7	1278.1	1278.4	1279.7	1280.9	1282.2	1283.5
167.5°	1294.1	1292.6	1292.0	1291.4	1290.8	1290.2	1290.6	1291.8	1293.1	1294.4	1295.7
170°	1300.1	1298.7	1298.2	1297.8	1297.4	1297.0	1297.4	1298.7	1299.9	1301.2	1302.4
172.5°	1304.7	1303.2	1302.8	1302.3	1302.0	1301.5	1302.0	1303.2	1304.5	1305.7	1307.0
175°	1309.7	1308.1	1307.7	1307.3	1306.9	1306.4	1307.0	1308.5	1309.9	1311.4	1312.9
177.5°	1310.5	1309.3	1309.1	1308.9	1308.8	1308.6	1309.1	1310.3	1311.4	1312.7	1313.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1712.7	1714.1	1723.6	1727.9	1736.4	1739.7	1743.5	1742.6	1742.6	1744.5	1757.7
5°	1716.4	1728.2	1746.0	1763.2	1779.7	1793.9	1803.4	1812.8	1816.4	1833.5	1849.0
7.5°	1710.2	1732.1	1761.4	1787.5	1818.9	1843.3	1863.8	1882.0	1894.6	1919.6	1945.2
10°	1702.2	1733.0	1766.1	1799.8	1843.0	1875.5	1908.7	1934.1	1942.4	1979.7	2001.0
12.5°	1686.1	1727.2	1769.4	1813.1	1855.3	1900.1	1936.6	1962.0	1991.2	2024.6	2064.0
15°	1662.0	1709.3	1764.3	1820.5	1880.9	1935.3	1974.3	2018.7	2050.7	2087.4	2121.6
17.5°	1627.3	1688.3	1758.2	1823.3	1893.1	1951.5	2005.3	2047.8	2070.3	2091.2	2096.3
20°	1599.8	1665.5	1747.8	1824.7	1894.5	1961.9	2015.2	2050.7	2056.6	2057.2	2025.9
22.5°	1570.0	1644.2	1730.3	1809.0	1892.6	1967.6	2009.0	2024.2	2000.7	1960.6	1900.0
25°	1515.2	1601.1	1701.0	1790.9	1882.0	1953.0	1967.3	1940.6	1858.4	1772.0	1662.6
27.5°	1455.8	1552.3	1659.5	1759.4	1856.5	1900.5	1869.9	1773.9	1625.8	1497.0	1341.0
30°	1412.3	1520.5	1625.9	1737.7	1827.7	1846.6	1776.2	1634.8	1462.0	1267.9	1112.3
32.5°	1362.6	1476.0	1591.8	1707.4	1782.7	1764.2	1647.9	1473.8	1271.2	1080.5	933.4
35°	1291.6	1408.7	1533.6	1649.6	1697.5	1617.6	1443.7	1217.0	1010.0	831.9	730.7
37.5°	1209.6	1337.1	1467.0	1573.4	1570.0	1436.9	1200.0	966.1	792.0	686.7	614.7
40°	1151.4	1280.3	1420.6	1510.5	1472.0	1298.7	1041.9	821.2	694.0	610.0	557.3
42.5°	1095.6	1224.9	1364.2	1435.7	1368.9	1155.7	899.9	727.0	622.1	556.5	513.8
45°	1000.5	1137.2	1266.1	1305.8	1186.2	951.4	727.7	602.4	532.5	483.9	454.4
47.5°	907.6	1042.1	1159.8	1160.5	998.8	771.5	613.9	521.3	461.6	424.1	402.6
50°	850.8	978.6	1077.4	1062.0	878.6	686.3	549.0	469.2	419.5	390.5	368.0
52.5°	786.9	910.9	996.5	952.7	776.9	604.0	490.8	423.7	382.5	357.4	337.2
55°	694.0	804.1	864.4	798.2	633.6	502.3	414.7	362.1	331.4	310.0	292.8
57.5°	602.8	693.6	731.6	654.3	521.9	416.5	350.9	311.3	280.8	265.6	256.6
60°	545.5	623.0	649.6	564.5	453.8	364.4	310.6	273.9	251.5	241.4	232.6
62.5°	489.2	552.5	563.5	485.4	395.6	319.1	272.8	241.7	226.9	217.2	208.8
65°	405.9	451.5	446.1	383.4	313.0	253.2	219.5	200.5	189.3	175.8	161.0
67.5°	334.1	361.9	345.2	298.2	238.9	196.8	174.8	160.4	146.5	133.6	130.2
70°	288.7	304.7	287.0	243.8	195.8	165.1	147.3	130.2	121.9	119.0	113.6
72.5°	245.2	250.7	231.6	194.6	159.3	136.7	119.4	109.8	105.3	102.8	99.4
75°	184.0	179.9	163.3	134.3	110.7	95.2	90.0	86.4	83.5	81.1	79.3
77.5°	129.2	123.1	108.4	89.4	77.0	69.7	66.5	64.6	63.2	62.0	60.2
80°	97.0	92.9	78.1	63.9	58.6	55.0	53.2	50.9	50.9	49.7	47.9
82.5°	71.0	66.3	53.5	46.8	43.9	41.7	40.5	39.1	38.6	38.8	37.5
85°	37.3	30.1	26.7	25.4	23.6	22.5	23.1	21.8	21.8	21.8	21.3
87.5°	12.0	10.1	10.1	10.1	11.0	11.3	11.1	11.5	12.3	12.0	12.8
90°	3.3	5.6	7.9	10.3	12.2	13.9	15.6	17.3	19.0	20.0	21.0
92.5°	18.9	18.7	18.5	18.3	18.6	19.4	20.3	21.1	22.0	22.6	23.1
95°	54.7	47.7	40.8	33.8	31.0	32.5	34.1	35.5	37.0	38.0	39.1
97.5°	102.7	83.1	63.5	44.0	35.8	39.2	42.6	46.1	49.5	50.3	51.2
100°	138.9	110.0	81.2	52.3	39.7	43.2	46.9	50.5	54.0	55.7	57.4
102.5°	211.7	205.6	199.5	193.4	175.4	145.4	115.5	85.5	55.6	57.8	59.9
105°	294.5	300.8	307.1	313.4	287.8	230.3	172.8	115.3	57.8	60.1	62.4
107.5°	373.4	378.5	383.6	388.8	356.9	287.8	218.9	149.9	81.0	78.6	76.2
110°	424.4	428.8	433.2	437.7	409.4	348.5	287.7	226.8	165.9	144.8	123.8





TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	472.4	476.3	480.2	484.1	478.6	463.5	448.5	433.5	418.4	341.6	264.7
115°	548.7	552.2	555.8	559.4	563.8	569.1	574.4	579.6	584.9	487.3	389.8
117.5°	617.5	621.5	625.5	629.5	633.3	636.9	640.6	644.2	647.8	624.2	600.7
120°	666.7	669.9	673.1	676.2	679.7	683.5	687.2	691.1	694.8	697.3	699.9
122.5°	709.4	712.7	716.0	719.3	723.1	727.2	731.3	735.5	739.6	741.1	742.6
125°	773.4	776.1	778.9	781.6	785.0	789.0	793.0	797.0	801.0	802.5	804.0
127.5°	832.3	835.4	838.4	841.4	844.4	847.4	850.3	853.4	856.4	858.5	860.7
130°	869.8	873.2	876.6	879.9	882.7	885.0	887.3	889.7	892.0	894.3	896.6
132.5°	907.2	910.1	912.9	915.8	918.4	920.7	923.0	925.3	927.6	929.6	931.6
135°	957.0	960.4	963.8	967.1	969.7	971.6	973.5	975.4	977.3	979.5	981.5
137.5°	1005.8	1008.2	1010.6	1012.9	1015.1	1017.4	1019.5	1021.6	1023.8	1025.8	1027.9
140°	1037.8	1039.5	1041.2	1042.9	1044.8	1047.1	1049.5	1051.8	1054.1	1056.0	1057.9
142.5°	1064.9	1066.4	1067.9	1069.4	1071.6	1074.2	1076.8	1079.5	1082.2	1083.9	1085.6
145°	1106.0	1105.8	1105.6	1105.4	1107.1	1110.6	1114.2	1117.8	1121.4	1122.8	1124.4
147.5°	1142.8	1142.0	1141.2	1140.4	1141.7	1145.3	1148.8	1152.4	1155.9	1157.0	1158.1
150°	1166.4	1164.9	1163.4	1162.0	1162.9	1166.3	1169.7	1173.0	1176.3	1177.7	1178.9
152.5°	1186.7	1185.0	1183.4	1181.8	1182.5	1185.7	1188.9	1192.1	1195.3	1196.6	1197.8
155°	1216.2	1214.3	1212.4	1210.5	1210.9	1213.4	1215.8	1218.4	1220.9	1222.2	1223.4
157.5°	1239.8	1238.2	1236.6	1235.0	1235.1	1236.9	1238.6	1240.4	1242.2	1243.6	1245.0
160°	1253.8	1252.5	1251.2	1250.0	1250.0	1251.2	1252.5	1253.8	1255.1	1256.3	1257.6
162.5°	1266.0	1264.6	1263.4	1262.1	1262.0	1263.1	1264.3	1265.3	1266.4	1267.8	1269.3
165°	1282.2	1280.9	1279.7	1278.4	1278.1	1278.7	1279.4	1280.1	1280.7	1282.1	1283.6
167.5°	1294.4	1293.1	1291.8	1290.6	1290.2	1290.8	1291.4	1292.0	1292.6	1294.1	1295.6
170°	1301.2	1299.9	1298.7	1297.4	1297.0	1297.4	1297.8	1298.2	1298.7	1300.1	1301.6
172.5°	1305.7	1304.5	1303.2	1302.0	1301.5	1302.0	1302.3	1302.8	1303.2	1304.7	1306.2
175°	1311.4	1309.9	1308.5	1307.0	1306.4	1306.9	1307.3	1307.7	1308.1	1309.7	1311.1
177.5°	1312.7	1311.4	1310.3	1309.1	1308.6	1308.8	1308.9	1309.1	1309.3	1310.5	1311.6
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1762.5	1768.6	1771.4	1771.4	1774.8	1773.3	1771.9
5°	1863.8	1875.0	1877.3	1888.0	1895.7	1893.3	1894.5
7.5°	1964.4	1982.5	2000.4	2008.6	2009.8	2014.6	2016.3
10°	2026.4	2041.2	2069.0	2064.8	2085.6	2097.4	2077.9
12.5°	2086.1	2106.0	2125.4	2130.7	2142.4	2146.2	2138.5
15°	2140.0	2150.7	2151.9	2148.9	2152.4	2149.5	2138.2
17.5°	2089.6	2072.3	2037.3	2020.7	2007.6	1988.2	1980.4
20°	2006.3	1955.4	1896.2	1872.6	1844.8	1790.4	1803.4
22.5°	1826.5	1768.4	1709.3	1640.2	1607.2	1555.6	1552.5
25°	1546.6	1446.6	1336.6	1259.6	1214.7	1163.2	1140.7
27.5°	1202.5	1076.6	986.4	940.8	899.2	858.4	856.8
30°	976.2	881.5	811.7	772.7	747.3	730.1	733.7
32.5°	822.9	758.0	711.0	678.5	659.7	646.8	646.6
35°	672.7	628.3	598.2	584.5	571.0	561.5	562.0
37.5°	575.7	549.0	532.3	517.2	508.7	504.1	501.5
40°	526.0	504.1	491.1	482.2	475.1	468.6	467.4
42.5°	486.7	468.6	455.6	448.6	441.9	437.4	436.1
45°	431.9	417.1	405.3	397.6	394.7	390.5	390.5
47.5°	384.2	369.7	360.4	355.6	350.5	347.8	347.7
50°	352.0	340.8	332.5	329.6	325.4	323.6	323.1
52.5°	323.2	314.8	308.9	306.8	305.1	302.8	303.2
55°	284.0	279.3	276.9	275.1	272.2	268.6	271.0
57.5°	251.0	246.9	240.6	235.0	232.3	229.8	230.8
60°	227.8	219.5	211.2	204.7	203.0	197.6	197.6
62.5°	198.4	186.8	176.6	173.0	171.2	168.7	168.3
65°	152.7	147.9	145.5	143.2	142.0	142.0	140.8
67.5°	126.5	124.6	122.0	121.5	120.2	119.8	119.5
70°	111.8	109.4	108.3	107.7	106.5	107.1	105.3
72.5°	97.6	95.8	95.5	94.0	93.3	93.4	92.0
75°	77.0	77.0	76.3	75.7	74.5	73.9	74.5
77.5°	59.2	59.3	58.2	58.1	58.0	58.1	57.5
80°	47.3	47.9	47.3	46.7	46.2	46.7	46.2
82.5°	37.4	36.6	36.5	36.3	36.2	35.8	35.8
85°	21.3	21.8	21.3	20.7	20.7	20.7	21.3
87.5°	12.5	12.7	12.8	12.9	13.0	13.1	12.7
90°	22.1	23.2	23.9	24.3	24.8	25.1	25.6
92.5°	23.6	24.2	24.6	24.9	25.1	25.3	25.6
95°	40.1	41.2	41.6	41.4	41.2	40.9	40.8
97.5°	52.0	52.9	53.4	53.7	53.9	54.1	54.4
100°	59.1	60.8	61.8	62.2	62.7	63.1	63.5
102.5°	62.2	64.3	65.7	66.3	66.9	67.5	68.0
105°	64.7	67.1	68.7	69.6	70.4	71.2	72.1
107.5°	73.8	71.5	70.8	71.6	72.4	73.3	74.1
110°	102.7	81.6	71.5	72.3	73.2	74.0	74.9



TEST NUMBER: P331729-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	187.9	111.0	72.9	73.7	74.3	75.0	75.6
115°	292.3	194.7	138.4	123.2	108.1	92.9	77.8
117.5°	577.0	553.5	516.7	466.9	417.1	367.2	317.4
120°	702.4	705.0	692.0	663.5	635.1	606.6	578.3
122.5°	744.1	745.6	743.6	738.2	732.6	727.1	721.6
125°	805.4	806.9	808.0	808.6	809.2	809.9	810.5
127.5°	862.8	865.0	866.1	866.2	866.4	866.5	866.6
130°	898.9	901.3	902.3	902.1	901.9	901.7	901.5
132.5°	933.6	935.6	936.5	936.2	936.0	935.9	935.6
135°	983.6	985.7	986.6	986.1	985.7	985.3	984.9
137.5°	1029.9	1032.0	1032.7	1032.0	1031.3	1030.6	1029.8
140°	1059.8	1061.7	1062.1	1061.0	1060.0	1058.9	1057.9
142.5°	1087.4	1089.0	1089.4	1088.3	1087.3	1086.3	1085.2
145°	1125.8	1127.3	1127.5	1126.5	1125.4	1124.4	1123.3
147.5°	1159.2	1160.3	1160.4	1159.5	1158.6	1157.7	1156.8
150°	1180.2	1181.4	1181.5	1180.4	1179.5	1178.4	1177.3
152.5°	1199.2	1200.4	1200.3	1198.9	1197.6	1196.1	1194.8
155°	1224.8	1226.0	1225.7	1224.1	1222.4	1220.8	1219.1
157.5°	1246.4	1247.9	1247.8	1246.2	1244.5	1242.9	1241.2
160°	1258.8	1260.1	1260.0	1258.6	1257.0	1255.6	1254.1
162.5°	1270.7	1272.2	1271.9	1270.2	1268.4	1266.5	1264.7
165°	1285.0	1286.6	1286.6	1285.0	1283.6	1282.1	1280.7
167.5°	1297.0	1298.5	1298.2	1296.4	1294.5	1292.6	1290.7
170°	1303.1	1304.6	1304.3	1302.4	1300.6	1298.7	1296.7
172.5°	1307.6	1309.1	1308.9	1307.0	1305.1	1303.2	1301.3
175°	1312.6	1314.0	1313.8	1311.6	1309.5	1307.4	1305.3
177.5°	1312.8	1314.0	1313.8	1312.3	1310.8	1309.3	1307.8
180°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0

(END OF REPORT)