

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331733-940

Luminaire Tested: **SA2XXRDIP-C865D1080U940-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331733-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6126.2 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331733-940
CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331733-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	86	89	85	82	79	71	68	66	57	56	55	45	44	43	38				
2	88	81	76	71	81	75	70	66	62	59	56	51	48	46	40	39	37	32				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	40	36	34	32	28				
4	74	64	56	50	68	59	52	47	49	45	41	41	37	34	33	30	28	24				
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	30	27	25	21				
6	63	51	44	38	58	47	41	36	40	35	31	33	29	26	27	24	22	19				
7	58	46	39	33	53	43	36	31	37	31	27	30	26	24	25	22	20	17				
8	54	42	35	30	50	39	33	28	33	28	24	28	24	21	23	20	18	15				
9	50	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16	14				
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21111	21111	21111
5°	21191	20846	20960
10°	21028	20505	20330
15°	20787	19896	19323
20°	20452	19029	18076
25°	20110	18045	16864
30°	19634	17031	15310
35°	19170	15930	13947
40°	18704	14790	12370
45°	18155	13511	10942
50°	17595	12215	9540
55°	17022	10826	8194
60°	16353	9361	6801
65°	15595	7866	6193
70°	14691	6477	5693
75°	13587	5908	5315
80°	11985	5281	4844
85°	9429	4168	4168



TEST NUMBER: P331733-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	2.0
10°-20°	336.0	5.5
20°-30°	471.9	7.7
30°-40°	514.6	8.4
40°-50°	473.1	7.7
50°-60°	371.6	6.1
60°-70°	242.3	4.0
70°-80°	124.9	2.0
80°-90°	37.3	0.6
90°-100°	77.8	1.3
100°-110°	241.6	3.9
110°-120°	412.9	6.7
120°-130°	543.0	8.9
130°-140°	609.4	9.9
140°-150°	597.6	9.8
150°-160°	501.2	8.2
160°-170°	332.4	5.4
170°-180°	116.2	1.9
0°-30°	930.3	15.2
0°-40°	1444.9	23.6
0°-60°	2289.6	37.4
0°-90°	2694.1	44.0
90°-120°	732.3	12.0
90°-150°	2482.3	40.5
90°-180°	3432.0	56.0
0°-180°	6126.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1308	1301	1286	1296	1293	124
15°	1244	1229	1190	1168	1156	350
25°	1129	1089	1013	966	947	519
35°	973	910	808	736	708	608
45°	795	713	592	511	479	614
55°	605	510	385	316	291	540
65°	408	312	206	168	162	405
75°	218	137	95	87	85	230
85°	51	27	22	22	22	60
90°	1	14	36	34	35	5
95°	54	64	66	66	64	62
105°	223	226	228	230	230	235
115°	414	420	418	417	414	410
125°	603	611	609	606	605	538
135°	780	791	793	792	789	602
145°	947	954	960	961	957	591
155°	1082	1086	1089	1093	1091	498
165°	1178	1177	1177	1183	1179	332
175°	1225	1222	1220	1227	1221	116
180°	1227	1227	1227	1227	1227	



TEST NUMBER: P331733-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1312.2	1311.2	1310.1	1309.0	1308.1	1306.4	1304.0	1301.7	1299.4	1297.1	1299.2
5°	1307.5	1306.2	1304.8	1303.5	1302.3	1299.8	1296.5	1293.1	1289.6	1286.2	1288.5
7.5°	1294.0	1292.4	1290.8	1289.1	1287.5	1284.7	1280.7	1276.7	1272.6	1268.6	1269.4
10°	1282.6	1280.8	1279.0	1277.1	1275.2	1271.8	1266.5	1261.2	1256.0	1250.7	1249.9
12.5°	1268.5	1266.1	1263.9	1261.7	1259.4	1254.9	1248.1	1241.4	1234.7	1228.0	1226.5
15°	1243.6	1240.7	1237.8	1234.9	1232.0	1226.1	1217.2	1208.3	1199.3	1190.3	1185.4
17.5°	1213.1	1208.6	1204.3	1199.8	1195.4	1187.5	1176.0	1164.5	1153.1	1141.6	1135.7
20°	1190.3	1185.1	1179.8	1174.6	1169.3	1160.1	1146.9	1133.8	1120.7	1107.5	1100.9
22.5°	1165.7	1159.8	1154.0	1148.1	1142.2	1131.8	1117.0	1102.2	1087.4	1072.5	1064.0
25°	1128.8	1120.4	1112.0	1103.6	1095.2	1082.3	1064.9	1047.6	1030.2	1012.9	1002.1
27.5°	1084.3	1075.1	1066.0	1056.9	1047.8	1033.4	1013.8	994.3	974.6	955.1	942.5
30°	1053.1	1043.1	1033.1	1023.1	1013.2	997.6	976.6	955.6	934.5	913.5	900.1
32.5°	1022.8	1011.1	999.4	987.7	976.1	959.6	938.1	916.6	895.2	873.7	858.4
35°	972.6	959.2	945.8	932.4	919.0	900.7	877.5	854.4	831.3	808.2	791.6
37.5°	922.5	907.8	893.0	878.2	863.5	843.8	819.2	794.5	769.9	745.2	726.9
40°	887.4	871.6	855.9	840.1	824.3	803.7	778.2	752.7	727.2	701.7	683.0
42.5°	851.5	834.8	818.2	801.6	785.0	763.5	737.2	710.8	684.5	658.1	638.8
45°	795.1	777.5	759.9	742.3	724.7	702.0	674.5	646.8	619.2	591.7	572.9
47.5°	740.2	721.6	702.9	684.2	665.6	641.9	613.5	585.0	556.4	528.0	509.4
50°	700.5	681.8	663.2	644.4	625.8	602.0	573.1	544.1	515.2	486.3	468.1
52.5°	661.6	642.1	622.7	603.2	583.6	559.7	531.5	503.1	474.8	446.6	429.0
55°	604.7	584.2	563.7	543.1	522.6	498.1	469.8	441.3	413.0	384.6	368.8
57.5°	546.2	525.1	504.1	483.0	462.1	437.9	410.5	383.3	356.0	328.7	314.2
60°	506.4	485.4	464.4	443.4	422.3	398.2	371.1	344.0	317.0	289.9	276.5
62.5°	467.6	446.6	425.5	404.5	383.4	360.1	334.2	308.4	282.6	256.7	244.0
65°	408.2	386.9	365.6	344.3	323.1	300.5	276.9	253.2	229.5	205.9	197.0
67.5°	351.0	329.8	308.7	287.5	266.4	245.1	223.9	202.6	181.3	160.0	155.9
70°	311.2	290.7	270.2	249.7	229.2	209.8	191.7	173.5	155.4	137.2	134.6
72.5°	273.3	253.7	234.0	214.4	194.7	177.5	163.0	148.4	133.8	119.3	117.1
75°	217.8	199.3	180.9	162.5	144.1	130.5	121.5	112.5	103.6	94.7	92.8
77.5°	163.1	146.9	130.7	114.6	98.4	88.3	83.9	79.6	75.3	71.0	69.9
80°	128.9	115.6	102.2	88.7	75.3	67.3	64.6	62.1	59.4	56.8	55.7
82.5°	97.7	87.3	76.8	66.3	55.9	49.8	48.0	46.2	44.4	42.6	42.0
85°	50.9	45.4	39.9	34.3	28.8	25.7	24.9	24.1	23.3	22.5	22.5
87.5°	15.3	14.2	13.1	11.9	10.8	10.8	11.8	12.8	13.8	14.8	14.5
90°	1.1	3.8	6.6	9.4	12.1	16.0	21.0	26.1	31.2	36.3	35.8
92.5°	18.5	20.4	22.5	24.5	26.6	28.2	29.3	30.6	31.7	32.9	33.0
95°	53.9	56.2	58.5	60.7	63.0	64.5	64.9	65.4	65.8	66.3	66.3
97.5°	98.4	100.4	102.5	104.5	106.5	108.0	108.8	109.7	110.6	111.5	111.5
100°	131.5	133.4	135.3	137.1	138.9	140.2	140.9	141.5	142.2	142.9	142.9
102.5°	166.4	167.8	169.3	170.8	172.3	173.4	174.3	175.1	176.0	176.9	177.1
105°	222.7	223.4	224.1	224.8	225.4	226.0	226.5	226.9	227.4	227.8	228.4
107.5°	279.5	280.4	281.5	282.5	283.5	284.0	284.0	284.0	284.0	284.0	284.2
110°	315.9	317.3	318.7	320.0	321.5	322.2	322.2	322.2	322.2	322.2	322.2



TEST NUMBER: P331733-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	355.7	357.0	358.5	359.8	361.2	361.9	361.6	361.4	361.2	361.1	360.5
115°	414.3	415.7	417.1	418.5	419.8	420.3	419.8	419.4	418.9	418.5	418.2
117.5°	472.7	474.6	476.4	478.2	480.1	480.4	479.1	477.8	476.5	475.2	474.7
120°	511.7	513.5	515.4	517.2	519.1	519.1	517.2	515.4	513.5	511.7	511.7
122.5°	547.3	549.6	551.7	553.9	556.2	556.6	555.4	554.0	552.8	551.4	550.9
125°	602.8	604.9	607.0	609.0	611.1	611.8	611.1	610.5	609.8	609.0	608.3
127.5°	656.9	659.5	662.2	664.8	667.4	668.3	667.4	666.6	665.8	664.9	664.1
130°	690.9	693.8	696.9	699.8	702.8	704.1	703.6	703.2	702.8	702.3	701.8
132.5°	729.0	731.5	733.9	736.3	738.8	740.0	740.1	740.2	740.3	740.4	739.4
135°	780.0	782.5	785.1	787.6	790.1	791.6	792.0	792.5	793.0	793.4	793.2
137.5°	833.6	835.7	837.8	839.8	841.9	843.2	843.8	844.5	845.0	845.6	845.4
140°	865.9	868.0	870.0	872.2	874.2	875.8	877.0	878.2	879.3	880.4	880.4
142.5°	899.1	901.2	903.2	905.3	907.3	908.7	909.5	910.3	911.2	912.0	912.1
145°	946.7	948.3	949.9	951.5	953.1	954.7	956.0	957.4	958.8	960.2	960.4
147.5°	989.2	991.1	993.0	995.0	996.9	998.4	999.3	1000.2	1001.1	1002.0	1002.6
150°	1018.2	1019.6	1020.9	1022.3	1023.7	1024.8	1025.8	1026.7	1027.6	1028.6	1029.2
152.5°	1043.8	1045.3	1046.6	1048.0	1049.4	1050.6	1051.8	1052.8	1054.0	1055.1	1056.0
155°	1082.4	1083.1	1083.8	1084.5	1085.2	1085.8	1086.5	1087.3	1088.0	1088.6	1089.8
157.5°	1115.4	1115.8	1116.2	1116.7	1117.2	1117.6	1118.0	1118.5	1118.8	1119.3	1120.9
160°	1135.2	1135.7	1136.1	1136.6	1137.1	1137.4	1137.6	1137.9	1138.1	1138.4	1139.7
162.5°	1153.4	1153.5	1153.6	1153.7	1153.9	1154.0	1154.2	1154.4	1154.7	1154.9	1156.5
165°	1177.7	1177.5	1177.2	1177.0	1176.8	1176.7	1176.7	1176.7	1176.7	1176.7	1178.3
167.5°	1198.0	1197.3	1196.6	1196.0	1195.2	1194.9	1194.8	1194.8	1194.7	1194.7	1196.3
170°	1208.8	1208.1	1207.4	1206.7	1206.0	1205.6	1205.3	1205.1	1204.9	1204.6	1206.2
172.5°	1216.2	1215.6	1214.9	1214.2	1213.4	1213.0	1212.8	1212.5	1212.3	1212.1	1213.7
175°	1225.4	1224.7	1224.0	1223.2	1222.6	1222.0	1221.6	1221.1	1220.7	1220.1	1221.8
177.5°	1229.0	1228.5	1228.0	1227.4	1226.9	1226.4	1226.0	1225.7	1225.3	1224.9	1226.0
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4



TEST NUMBER: P331733-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1301.3	1303.4	1305.5	1306.4	1305.9	1305.5	1305.1	1304.7
5°	1290.9	1293.2	1295.7	1296.5	1295.7	1294.9	1294.1	1293.2
7.5°	1270.1	1270.7	1271.4	1271.0	1269.7	1268.4	1266.9	1265.6
10°	1249.1	1248.3	1247.5	1246.3	1244.7	1243.2	1241.6	1240.0
12.5°	1225.1	1223.7	1222.3	1220.3	1217.6	1215.0	1212.4	1209.8
15°	1180.4	1175.4	1170.4	1166.5	1164.0	1161.3	1158.7	1156.0
17.5°	1129.7	1123.7	1117.8	1112.6	1108.0	1103.6	1099.0	1094.5
20°	1094.4	1087.8	1081.2	1075.0	1069.3	1063.5	1057.7	1052.0
22.5°	1055.6	1047.1	1038.7	1032.2	1028.0	1023.6	1019.3	1015.0
25°	991.3	980.5	969.7	962.3	958.4	954.5	950.6	946.6
27.5°	930.0	917.4	904.8	895.5	889.2	882.9	876.6	870.4
30°	886.6	873.3	859.8	849.5	842.5	835.4	828.3	821.2
32.5°	843.1	827.8	812.5	801.5	794.9	788.2	781.5	774.8
35°	775.0	758.5	741.9	730.8	725.0	719.2	713.4	707.6
37.5°	708.7	690.5	672.3	659.8	653.2	646.5	639.9	633.3
40°	664.3	645.7	627.0	614.2	607.4	600.6	593.7	586.9
42.5°	619.6	600.2	580.9	567.9	561.3	554.7	548.0	541.4
45°	554.3	535.7	516.9	504.4	498.1	491.9	485.5	479.2
47.5°	490.8	472.3	453.7	441.6	435.9	430.1	424.4	418.7
50°	450.0	431.9	413.8	401.9	396.4	390.8	385.3	379.8
52.5°	411.5	394.0	376.5	365.2	360.1	355.0	349.9	344.8
55°	353.0	337.2	321.5	311.0	306.0	301.0	296.0	291.1
57.5°	299.8	285.3	270.9	261.5	257.3	253.1	248.9	244.7
60°	263.1	249.7	236.2	227.5	223.2	219.0	214.8	210.6
62.5°	231.2	218.5	205.6	198.0	195.5	193.0	190.4	187.9
65°	188.0	179.1	170.1	165.2	164.4	163.7	162.9	162.1
67.5°	151.8	147.7	143.6	141.1	140.3	139.4	138.6	137.8
70°	132.0	129.4	126.7	124.9	123.9	122.8	121.7	120.6
72.5°	114.9	112.6	110.4	109.1	108.3	107.7	107.1	106.5
75°	91.0	89.2	87.3	86.2	86.0	85.7	85.4	85.2
77.5°	68.9	67.9	66.8	66.1	65.6	65.2	64.8	64.4
80°	54.7	53.7	52.6	52.1	52.1	52.1	52.1	52.1
82.5°	41.4	40.7	40.0	39.8	39.8	39.8	39.8	39.8
85°	22.5	22.5	22.5	22.5	22.5	22.5	22.5	22.5
87.5°	14.2	13.9	13.6	13.5	13.6	13.6	13.6	13.6
90°	35.3	34.9	34.4	34.3	34.5	34.8	35.0	35.2
92.5°	33.1	33.2	33.3	33.3	33.4	33.4	33.5	33.5
95°	66.3	66.3	66.3	66.1	65.6	65.2	64.6	64.2
97.5°	111.5	111.5	111.5	111.5	111.4	111.4	111.3	111.3
100°	142.9	142.9	142.9	142.9	142.6	142.4	142.1	141.9
102.5°	177.3	177.5	177.6	177.6	177.4	177.2	176.9	176.7
105°	228.8	229.3	229.7	230.0	230.0	230.0	230.0	230.0
107.5°	284.4	284.5	284.7	284.3	283.3	282.2	281.2	280.1
110°	322.2	322.2	322.2	321.8	321.1	320.4	319.7	319.1



TEST NUMBER: P331733-940

CATALOG NUMBER: SA2XXRDIP-C865D1080U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	360.0	359.4	358.9	358.4	357.8	357.3	356.9	356.3
115°	418.0	417.8	417.5	417.1	416.4	415.7	415.0	414.3
117.5°	474.1	473.6	473.1	472.4	471.7	471.0	470.3	469.7
120°	511.7	511.7	511.7	511.3	510.7	510.0	509.3	508.5
122.5°	550.4	549.8	549.2	548.8	548.2	547.7	547.2	546.7
125°	607.7	607.0	606.3	605.8	605.6	605.4	605.1	604.9
127.5°	663.3	662.5	661.6	660.8	660.1	659.4	658.7	657.9
130°	701.3	700.9	700.4	699.7	698.8	697.9	697.0	696.1
132.5°	738.3	737.4	736.4	735.5	734.8	734.0	733.3	732.5
135°	793.0	792.7	792.5	792.0	791.3	790.7	790.0	789.3
137.5°	845.3	845.1	844.9	844.4	843.4	842.5	841.6	840.6
140°	880.4	880.4	880.4	879.9	879.0	878.2	877.2	876.3
142.5°	912.3	912.5	912.7	912.3	911.3	910.4	909.5	908.6
145°	960.6	960.9	961.1	960.7	959.8	958.9	958.0	957.1
147.5°	1003.1	1003.5	1004.1	1003.9	1003.0	1002.1	1001.2	1000.4
150°	1029.9	1030.6	1031.4	1031.4	1030.6	1029.9	1029.2	1028.6
152.5°	1056.9	1057.7	1058.5	1058.5	1057.7	1056.9	1056.0	1055.1
155°	1090.9	1092.1	1093.2	1093.4	1092.8	1092.1	1091.4	1090.7
157.5°	1122.4	1124.0	1125.5	1125.8	1124.6	1123.6	1122.5	1121.3
160°	1141.1	1142.5	1143.9	1144.1	1143.2	1142.3	1141.3	1140.4
162.5°	1158.1	1159.6	1161.2	1161.4	1160.3	1159.2	1158.1	1157.0
165°	1179.9	1181.5	1183.1	1183.3	1182.2	1181.1	1179.9	1178.8
167.5°	1197.9	1199.5	1201.1	1201.3	1200.2	1198.9	1197.7	1196.6
170°	1207.8	1209.4	1211.0	1211.2	1209.8	1208.4	1207.0	1205.7
172.5°	1215.3	1216.9	1218.5	1218.6	1217.3	1215.8	1214.5	1213.1
175°	1223.4	1225.0	1226.6	1226.7	1225.4	1224.0	1222.6	1221.2
177.5°	1227.2	1228.2	1229.3	1229.3	1228.2	1227.2	1226.0	1224.9
180°	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4	1227.4

(END OF REPORT)