

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332662

Luminaire Tested: **SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332662
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8776.6 lumens
Efficiency: N/A
Efficacy: 134.2 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332662
CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	53
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	71	83	77	71	67	66	62	58	55	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	19	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13472	13472	13472	13472
5°	15866	13507	11921	13507
10°	18996	13448	10733	13448
15°	22476	13312	9857	13312
20°	25027	13173	9075	13173
25°	25432	12968	8535	12968
30°	21640	12773	8364	12773
35°	16638	12454	8366	12454
40°	12968	12079	8524	12079
45°	10813	11515	8667	11515
50°	9516	10827	8960	10827
55°	8718	10003	9322	10003
60°	8170	9265	9755	9265
65°	7607	8437	10115	8437
70°	6951	7619	10346	7619
75°	6210	6706	10221	6706
80°	5207	5495	9898	5495
85°	3844	3974	9476	3974



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.6	1.9
10°-20°	501.1	5.7
20°-30°	794.6	9.1
30°-40°	884.3	10.1
40°-50°	805.0	9.2
50°-60°	657.8	7.5
60°-70°	469.6	5.4
70°-80°	258.6	2.9
80°-90°	75.1	0.9
90°-100°	99.1	1.1
100°-110°	293.5	3.3
110°-120°	498.2	5.7
120°-130°	656.9	7.5
130°-140°	737.7	8.4
140°-150°	724.9	8.3
150°-160°	609.7	6.9
160°-170°	405.7	4.6
170°-180°	142.1	1.6
0°-30°	1458.3	16.6
0°-40°	2342.7	26.7
0°-60°	3805.5	43.4
0°-90°	4608.8	52.5
90°-120°	890.8	10.1
90°-150°	3010.3	34.3
90°-180°	4168.0	47.5
0°-180°	8776.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1669	1669	1669	1669	1669	
5°	1958	1667	1471	1667	1958	199
15°	2689	1593	1179	1593	2689	760
25°	2855	1456	958	1456	2855	1259
35°	1688	1264	849	1264	1688	1072
45°	947	1009	759	1009	947	746
55°	619	711	662	711	619	560
65°	398	442	530	442	398	394
75°	199	215	328	215	199	212
85°	42	43	102	43	42	51
90°	35	4	35	4	35	19
95°	92	70	92	70	92	96
105°	284	271	284	271	284	299
115°	502	506	502	506	502	496
125°	732	738	732	738	732	653
135°	953	952	953	952	953	736
145°	1157	1156	1157	1156	1157	724
155°	1323	1324	1323	1324	1323	609
165°	1438	1442	1438	1442	1438	405
175°	1493	1500	1493	1500	1493	142
180°	1502	1502	1502	1502	1502	



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1776.1	1775.6	1770.0	1768.9	1765.0	1760.1	1759.0	1750.1	1732.4	1724.1	1721.9
5°	1957.8	1971.6	1953.6	1950.2	1948.1	1925.3	1913.5	1899.7	1867.9	1849.2	1834.7
7.5°	2174.6	2176.2	2168.4	2162.0	2144.4	2124.5	2094.7	2062.9	2025.0	1985.6	1955.8
10°	2317.3	2322.8	2313.8	2312.4	2277.2	2255.0	2210.8	2173.5	2130.6	2082.9	2039.4
12.5°	2467.7	2459.9	2455.4	2425.8	2419.3	2378.9	2327.5	2289.1	2223.0	2168.1	2110.1
15°	2689.2	2674.0	2664.3	2623.5	2603.5	2547.5	2492.8	2450.7	2364.3	2282.0	2219.8
17.5°	2819.1	2834.4	2812.0	2795.2	2743.4	2704.1	2648.3	2559.8	2492.2	2390.0	2311.5
20°	2913.2	2914.5	2902.1	2884.8	2844.0	2794.3	2733.4	2636.6	2555.8	2454.1	2346.3
22.5°	2938.6	2938.9	2933.6	2917.4	2886.6	2846.2	2784.9	2704.1	2606.1	2495.6	2387.8
25°	2855.1	2852.3	2858.6	2876.5	2864.8	2852.3	2817.1	2756.9	2665.7	2548.8	2432.7
27.5°	2544.8	2563.9	2599.0	2643.3	2685.9	2718.4	2727.5	2715.2	2658.6	2562.5	2440.9
30°	2321.4	2344.9	2371.2	2415.4	2501.1	2550.2	2604.2	2644.9	2622.1	2545.4	2432.0
32.5°	2075.9	2081.7	2120.7	2171.0	2249.5	2343.9	2429.4	2512.2	2539.7	2499.5	2404.9
35°	1688.2	1697.8	1740.0	1789.8	1885.9	2001.3	2129.9	2244.7	2339.4	2377.4	2329.0
37.5°	1377.6	1405.4	1435.2	1488.7	1573.3	1677.2	1810.8	1959.3	2100.5	2195.0	2211.1
40°	1230.5	1247.8	1269.2	1310.0	1381.9	1484.2	1599.0	1769.1	1919.1	2054.6	2098.8
42.5°	1114.4	1124.5	1137.6	1174.5	1229.3	1331.0	1435.8	1585.4	1736.0	1898.0	1972.2
45°	947.1	957.5	979.6	1001.0	1042.5	1113.0	1210.5	1333.5	1484.9	1641.2	1778.0
47.5°	826.2	832.9	846.0	869.0	904.2	950.7	1030.0	1132.8	1273.1	1424.8	1570.6
50°	757.7	763.2	773.6	794.3	821.3	862.7	927.7	1023.8	1133.7	1286.5	1429.6
52.5°	703.5	705.7	713.3	727.4	748.8	783.7	837.0	916.5	1018.7	1154.9	1297.4
55°	619.4	622.2	629.1	639.5	658.1	680.2	721.0	780.5	869.7	987.9	1111.6
57.5°	550.3	552.2	558.0	562.0	577.4	595.4	626.7	669.2	736.8	837.0	947.5
60°	506.0	504.7	511.6	515.0	525.4	540.6	564.8	605.6	664.3	745.2	846.8
62.5°	462.9	461.0	466.8	471.3	477.3	490.3	510.0	542.0	589.7	662.8	750.6
65°	398.2	395.4	398.9	404.4	409.9	416.9	431.4	459.7	497.7	550.3	617.3
67.5°	333.2	336.1	336.7	339.4	342.6	352.0	362.0	382.0	408.8	450.9	507.7
70°	294.5	295.2	298.0	298.0	300.0	308.3	316.6	328.4	354.6	393.4	439.7
72.5°	255.8	258.7	257.6	259.8	261.3	266.8	272.9	284.1	306.5	335.3	374.4
75°	199.1	201.2	201.2	201.9	203.9	206.0	210.8	219.1	235.0	256.5	283.4
77.5°	145.2	145.5	146.4	148.9	148.9	152.2	155.8	162.5	170.3	185.0	201.4
80°	112.0	113.4	112.7	114.1	114.1	116.8	118.2	126.5	130.0	139.6	152.8
82.5°	82.1	83.5	83.4	85.3	86.4	87.0	88.9	92.2	95.7	104.2	109.6
85°	41.5	42.9	41.5	42.9	44.9	45.6	47.7	48.4	51.2	53.2	58.1
87.5°	19.1	20.7	20.6	21.0	22.0	22.4	22.6	21.8	23.7	23.9	25.7
90°	34.9	34.3	33.8	33.3	32.8	31.8	30.2	28.7	27.1	25.6	23.5
92.5°	51.6	51.3	51.0	50.7	50.3	49.7	48.8	47.9	46.9	46.0	44.6
95°	91.8	91.8	91.8	91.8	91.8	91.4	90.6	89.8	89.1	88.3	86.5
97.5°	143.8	143.8	143.8	143.8	143.8	143.4	142.4	141.5	140.6	139.6	137.5
100°	180.1	180.1	180.1	180.1	180.1	179.8	179.3	178.8	178.3	177.8	175.4
102.5°	221.0	220.8	220.6	220.4	220.1	219.7	219.0	218.2	217.5	216.8	214.7
105°	283.5	282.7	281.9	281.2	280.4	279.6	278.8	278.1	277.3	276.5	275.5
107.5°	344.4	344.4	344.5	344.5	344.6	344.2	343.5	342.8	342.1	341.3	341.2
110°	388.0	387.3	386.5	385.7	384.9	384.8	385.3	385.8	386.4	386.9	387.1



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	432.7	432.5	432.3	432.2	432.0	432.0	432.1	432.2	432.3	432.4	432.9
115°	501.9	502.2	502.4	502.7	502.9	503.2	503.4	503.7	504.0	504.2	504.7
117.5°	567.9	568.4	568.9	569.4	570.0	570.6	571.5	572.4	573.3	574.2	574.5
120°	618.1	617.6	617.0	616.5	616.0	616.4	617.7	619.0	620.3	621.6	622.3
122.5°	659.9	660.8	661.8	662.7	663.6	664.5	665.4	666.3	667.2	668.0	668.4
125°	731.9	732.4	733.0	733.5	734.0	734.5	735.0	735.5	736.1	736.6	736.8
127.5°	798.6	799.0	799.4	799.9	800.3	800.7	801.3	801.8	802.3	802.8	803.2
130°	842.3	843.3	844.4	845.4	846.4	847.2	847.7	848.2	848.8	849.3	849.3
132.5°	888.8	889.2	889.6	890.0	890.4	890.9	891.4	891.9	892.4	893.0	893.2
135°	952.7	953.4	954.2	955.0	955.8	956.4	956.9	957.5	958.0	958.5	958.5
137.5°	1019.8	1019.7	1019.5	1019.4	1019.2	1019.5	1020.1	1020.8	1021.5	1022.1	1021.7
140°	1060.7	1061.0	1061.2	1061.5	1061.8	1062.0	1062.3	1062.5	1062.8	1063.0	1063.0
142.5°	1101.6	1101.7	1101.7	1101.8	1101.8	1101.9	1101.9	1102.0	1102.0	1102.1	1102.3
145°	1157.2	1157.9	1158.7	1159.5	1160.2	1160.8	1161.0	1161.3	1161.5	1161.8	1161.5
147.5°	1213.4	1213.6	1213.9	1214.2	1214.4	1214.6	1214.9	1215.1	1215.3	1215.5	1215.7
150°	1247.8	1248.0	1248.3	1248.5	1248.8	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9
152.5°	1279.4	1280.0	1280.7	1281.4	1282.1	1282.1	1281.5	1280.8	1280.2	1279.6	1279.4
155°	1323.3	1324.3	1325.4	1326.4	1327.4	1327.4	1326.4	1325.4	1324.3	1323.3	1323.5
157.5°	1362.6	1363.4	1364.3	1365.2	1366.1	1366.1	1365.3	1364.6	1363.8	1363.0	1363.1
160°	1384.9	1386.2	1387.4	1388.7	1390.0	1390.3	1389.5	1388.7	1388.0	1387.2	1387.4
162.5°	1408.1	1409.4	1410.7	1412.0	1413.3	1413.2	1411.8	1410.4	1409.0	1407.6	1407.9
165°	1438.3	1439.3	1440.4	1441.4	1442.4	1442.2	1440.6	1439.1	1437.5	1436.0	1436.5
167.5°	1459.9	1461.5	1463.1	1464.7	1466.3	1466.3	1464.8	1463.2	1461.7	1460.1	1460.1
170°	1472.0	1473.8	1475.6	1477.4	1479.2	1479.4	1477.8	1476.3	1474.7	1473.2	1472.9
172.5°	1482.2	1484.0	1485.8	1487.6	1489.5	1489.5	1487.7	1486.0	1484.2	1482.5	1482.4
175°	1492.9	1494.7	1496.5	1498.3	1500.1	1500.1	1498.3	1496.5	1494.7	1492.9	1493.2
177.5°	1498.5	1500.1	1501.8	1503.4	1505.1	1505.2	1503.8	1502.3	1500.9	1499.4	1499.4
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1722.5	1714.7	1709.2	1704.8	1692.6	1685.4	1679.9	1672.1	1663.3	1653.9	1642.3
5°	1820.2	1796.7	1779.4	1753.2	1728.3	1707.5	1686.1	1666.7	1643.2	1617.7	1599.0
7.5°	1922.9	1888.0	1843.2	1804.3	1760.6	1722.6	1688.6	1653.7	1617.5	1582.4	1550.2
10°	1988.2	1943.3	1893.5	1834.7	1779.4	1730.3	1684.7	1640.5	1597.6	1554.7	1518.1
12.5°	2058.4	2002.4	1928.9	1860.2	1798.2	1732.6	1677.5	1623.3	1571.6	1526.5	1483.8
15°	2152.7	2071.8	1986.8	1894.9	1813.3	1736.6	1661.2	1592.8	1534.7	1475.2	1433.8
17.5°	2210.7	2110.6	2013.4	1917.3	1818.5	1721.8	1640.5	1561.5	1488.8	1429.8	1377.5
20°	2248.8	2149.3	2028.3	1932.2	1814.7	1715.1	1621.1	1533.3	1457.3	1394.4	1340.4
22.5°	2282.0	2167.0	2046.0	1919.5	1802.5	1696.9	1594.0	1505.7	1428.0	1361.7	1310.0
25°	2300.0	2167.9	2036.6	1910.8	1778.0	1652.9	1559.6	1455.9	1372.9	1303.1	1247.8
27.5°	2301.9	2160.7	2012.1	1872.3	1735.3	1618.8	1501.0	1408.3	1322.2	1248.4	1195.3
30°	2295.8	2148.6	1988.9	1837.5	1699.9	1573.4	1471.1	1370.2	1282.4	1209.1	1153.8
32.5°	2276.5	2123.1	1959.0	1798.8	1656.2	1532.5	1426.9	1330.9	1245.3	1173.1	1115.1
35°	2220.5	2069.1	1894.2	1727.6	1581.7	1456.6	1361.2	1263.7	1178.0	1109.5	1053.6
37.5°	2133.0	1996.1	1818.3	1645.9	1502.6	1376.9	1282.4	1194.3	1117.0	1047.5	990.1
40°	2056.6	1936.3	1758.0	1590.0	1435.2	1315.6	1227.1	1146.2	1069.5	1003.8	949.2
42.5°	1968.7	1863.9	1699.4	1521.4	1372.1	1252.0	1165.7	1093.1	1020.8	960.1	905.5
45°	1811.9	1742.8	1587.9	1423.4	1267.9	1154.5	1072.2	1008.6	947.8	888.3	842.7
47.5°	1631.6	1597.3	1467.0	1310.7	1163.1	1051.3	980.0	921.2	867.9	817.5	777.3
50°	1510.5	1493.9	1381.2	1230.5	1089.5	984.4	912.5	862.1	816.4	772.2	734.2
52.5°	1391.0	1390.5	1288.9	1150.9	1020.4	919.2	847.8	800.7	761.1	725.2	691.0
55°	1208.4	1227.8	1148.3	1025.2	908.4	817.1	752.8	710.7	683.0	653.3	627.7
57.5°	1040.7	1072.8	1007.2	898.8	801.4	717.3	661.3	629.6	600.2	582.2	563.6
60°	931.2	961.6	910.5	819.2	727.3	655.4	602.1	573.8	548.2	535.8	522.6
62.5°	833.9	861.0	823.1	738.5	658.7	589.5	544.6	517.4	500.1	486.5	477.8
65°	694.8	717.6	685.1	623.6	555.1	499.8	463.2	441.7	425.2	419.6	409.9
67.5°	561.6	582.4	564.8	512.5	457.6	415.8	387.1	366.5	356.7	351.9	345.0
70°	482.5	503.3	484.6	439.0	396.8	361.6	334.6	322.8	312.5	310.4	300.7
72.5°	415.6	429.7	411.1	375.4	339.3	309.6	288.7	276.4	271.0	267.3	262.0
75°	311.8	324.2	311.8	284.1	258.5	237.8	219.8	215.0	208.8	206.7	203.2
77.5°	220.7	231.4	221.9	204.6	185.5	169.5	159.8	153.6	152.2	148.6	150.3
80°	168.7	175.6	166.6	154.9	139.6	128.6	121.7	118.2	114.1	112.7	115.4
82.5°	121.1	124.2	119.6	111.7	100.4	93.2	88.5	84.5	83.6	83.9	83.9
85°	62.9	62.2	61.5	54.6	51.2	46.3	43.6	42.9	42.2	43.6	44.9
87.5°	25.3	25.4	24.5	21.8	19.5	17.3	16.2	15.1	16.2	17.3	18.4
90°	21.4	19.4	17.3	14.8	12.0	9.2	6.3	3.5	6.3	9.2	12.0
92.5°	43.1	41.7	40.2	37.9	34.6	31.4	28.1	24.9	28.1	31.4	34.6
95°	84.7	82.9	81.1	79.0	76.7	74.4	72.0	69.7	72.0	74.4	76.7
97.5°	135.4	133.3	131.2	129.2	127.3	125.5	123.6	121.8	123.6	125.5	127.3
100°	173.1	170.8	168.5	166.8	165.7	164.7	163.7	162.7	163.7	164.7	165.7
102.5°	212.6	210.4	208.3	207.1	206.6	206.2	205.8	205.4	205.8	206.2	206.6
105°	274.4	273.4	272.4	271.7	271.5	271.2	271.0	270.7	271.0	271.2	271.5
107.5°	341.0	340.9	340.7	340.5	340.2	339.9	339.6	339.2	339.6	339.9	340.2
110°	387.4	387.7	387.9	387.8	387.3	386.7	386.2	385.7	386.2	386.7	387.3



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	433.4	433.8	434.3	434.5	434.4	434.3	434.2	434.0	434.2	434.3	434.4
115°	505.3	505.8	506.3	506.5	506.5	506.5	506.5	506.5	506.5	506.5	506.5
117.5°	574.9	575.2	575.6	575.7	575.5	575.3	575.1	574.9	575.1	575.3	575.5
120°	623.1	623.9	624.7	624.5	623.5	622.5	621.4	620.4	621.4	622.5	623.5
122.5°	668.8	669.1	669.5	669.5	669.0	668.6	668.2	667.8	668.2	668.6	669.0
125°	737.1	737.4	737.6	737.7	737.7	737.7	737.7	737.7	737.7	737.7	737.7
127.5°	803.6	804.0	804.5	804.3	803.5	802.7	802.0	801.2	802.0	802.7	803.5
130°	849.3	849.3	849.3	848.9	848.1	847.3	846.6	845.8	846.6	847.3	848.1
132.5°	893.4	893.6	893.8	893.6	893.0	892.5	891.9	891.3	891.9	892.5	893.0
135°	958.5	958.5	958.5	957.7	956.2	954.6	953.1	951.5	953.1	954.6	956.2
137.5°	1021.3	1020.9	1020.5	1019.9	1019.2	1018.5	1017.8	1017.0	1017.8	1018.5	1019.2
140°	1063.0	1063.0	1063.0	1062.8	1062.3	1061.8	1061.2	1060.7	1061.2	1061.8	1062.3
142.5°	1102.5	1102.7	1102.9	1102.8	1102.2	1101.7	1101.2	1100.7	1101.2	1101.7	1102.2
145°	1161.3	1161.0	1160.8	1160.1	1159.1	1158.1	1157.0	1156.0	1157.0	1158.1	1159.1
147.5°	1215.9	1216.1	1216.3	1215.8	1214.5	1213.3	1212.1	1210.8	1212.1	1213.3	1214.5
150°	1248.9	1248.9	1248.9	1248.4	1247.4	1246.4	1245.3	1244.3	1245.3	1246.4	1247.4
152.5°	1279.2	1279.0	1278.8	1278.4	1277.7	1277.1	1276.5	1275.9	1276.5	1277.1	1277.7
155°	1323.8	1324.1	1324.3	1324.4	1324.4	1324.4	1324.4	1324.4	1324.4	1324.4	1324.4
157.5°	1363.1	1363.2	1363.2	1363.5	1364.0	1364.4	1364.9	1365.3	1364.9	1364.4	1364.0
160°	1387.7	1388.0	1388.2	1388.5	1388.7	1389.0	1389.3	1389.5	1389.3	1389.0	1388.7
162.5°	1408.2	1408.4	1408.7	1409.1	1409.8	1410.5	1411.1	1411.8	1411.1	1410.5	1409.8
165°	1437.0	1437.5	1438.0	1438.7	1439.5	1440.2	1441.0	1441.8	1441.0	1440.2	1439.5
167.5°	1460.0	1460.0	1459.9	1460.5	1461.5	1462.6	1463.7	1464.8	1463.7	1462.6	1461.5
170°	1472.6	1472.4	1472.1	1472.6	1473.9	1475.2	1476.5	1477.8	1476.5	1475.2	1473.9
172.5°	1482.4	1482.3	1482.2	1482.8	1483.8	1484.9	1486.0	1487.1	1486.0	1484.9	1483.8
175°	1493.4	1493.7	1493.9	1494.7	1496.0	1497.3	1498.6	1499.9	1498.6	1497.3	1496.0
177.5°	1499.4	1499.4	1499.4	1499.9	1501.0	1502.0	1503.0	1504.1	1503.0	1502.0	1501.0
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1636.7	1631.8	1624.6	1614.6	1606.3	1597.5	1595.3	1591.9	1598.6	1593.0	1591.4
5°	1583.1	1568.6	1549.9	1528.5	1516.0	1498.1	1494.6	1487.7	1480.8	1480.1	1473.2
7.5°	1526.3	1505.0	1480.5	1458.7	1438.5	1418.8	1406.0	1403.2	1393.0	1387.0	1380.1
10°	1489.8	1463.5	1435.2	1414.4	1390.9	1370.2	1355.7	1347.4	1340.4	1332.8	1325.9
12.5°	1446.6	1418.7	1395.3	1372.9	1345.0	1329.2	1305.3	1290.9	1289.6	1289.7	1271.7
15°	1396.4	1368.8	1332.8	1301.0	1285.8	1255.4	1242.3	1225.7	1215.3	1204.9	1196.7
17.5°	1339.1	1304.6	1276.6	1240.1	1211.0	1186.8	1169.6	1159.6	1144.0	1129.3	1118.7
20°	1303.1	1266.5	1236.7	1198.0	1166.2	1136.5	1122.0	1108.2	1096.4	1084.0	1072.2
22.5°	1266.6	1228.3	1191.9	1154.3	1124.8	1093.4	1079.4	1060.6	1049.4	1042.5	1030.7
25°	1209.1	1167.6	1126.1	1090.2	1059.8	1032.1	1013.5	998.9	986.5	981.0	973.4
27.5°	1146.6	1105.4	1065.3	1024.5	990.0	969.9	955.0	944.0	936.9	929.5	926.1
30°	1106.8	1063.9	1021.1	983.0	951.2	931.2	917.4	909.8	904.2	900.8	897.3
32.5°	1066.4	1024.1	979.0	944.3	915.8	898.0	887.5	879.9	877.1	875.9	874.6
35°	1001.7	958.8	917.4	886.3	859.3	852.4	843.4	839.2	837.9	842.7	844.8
37.5°	939.1	899.3	861.1	830.9	813.3	803.2	800.1	800.3	805.2	809.5	814.5
40°	898.7	860.0	824.0	797.8	781.2	775.0	773.6	777.0	782.6	787.4	792.9
42.5°	859.4	821.3	788.6	764.0	752.4	746.7	747.6	751.0	758.8	764.7	773.0
45°	798.5	766.7	734.9	714.8	705.1	706.5	706.5	712.7	720.3	729.3	738.3
47.5°	741.1	709.0	682.9	666.0	661.0	659.8	663.7	671.8	682.7	693.8	706.4
50°	702.4	671.9	649.1	633.9	628.4	630.5	636.0	643.6	656.7	670.6	683.7
52.5°	663.1	635.4	614.3	600.2	596.3	600.1	605.6	617.6	629.1	644.0	659.9
55°	602.1	578.6	562.0	551.7	550.3	552.4	558.6	571.7	588.3	607.0	622.2
57.5°	541.4	521.8	506.6	499.4	500.1	502.0	512.3	527.9	545.6	565.5	585.1
60°	500.5	482.5	470.1	464.6	465.2	469.4	481.8	496.4	518.5	537.8	558.6
62.5°	461.8	446.0	434.1	429.2	428.2	437.3	449.2	464.3	486.4	508.0	530.4
65°	399.6	387.1	377.5	374.7	376.8	383.7	398.9	418.9	437.6	460.4	483.9
67.5°	338.7	328.5	321.9	323.1	325.6	335.8	348.6	365.8	387.0	410.6	433.9
70°	300.0	290.3	284.8	285.5	289.7	302.1	313.2	330.4	353.3	377.5	396.8
72.5°	260.2	253.8	248.9	251.8	255.9	264.5	278.3	295.6	315.7	338.2	358.6
75°	199.8	199.8	197.0	199.1	205.3	213.6	224.0	242.0	262.0	280.0	296.6
77.5°	148.2	146.7	148.5	151.0	154.6	164.4	176.3	189.1	204.2	222.2	235.9
80°	113.4	114.1	117.5	121.7	123.1	130.7	143.1	154.9	166.6	181.8	194.9
82.5°	85.2	85.9	87.7	92.9	94.3	102.5	110.5	122.2	132.9	143.1	154.0
85°	46.3	46.3	49.8	51.8	55.3	60.8	65.7	72.6	82.3	89.2	99.5
87.5°	20.7	21.2	23.8	25.3	27.4	30.6	32.0	38.4	40.9	44.0	49.1
90°	14.8	17.3	19.4	21.4	23.5	25.6	27.1	28.7	30.2	31.8	32.8
92.5°	37.9	40.2	41.7	43.1	44.6	46.0	46.9	47.9	48.8	49.7	50.3
95°	79.0	81.1	82.9	84.7	86.5	88.3	89.1	89.8	90.6	91.4	91.8
97.5°	129.2	131.2	133.3	135.4	137.5	139.6	140.6	141.5	142.4	143.4	143.8
100°	166.8	168.5	170.8	173.1	175.4	177.8	178.3	178.8	179.3	179.8	180.1
102.5°	207.1	208.3	210.4	212.6	214.7	216.8	217.5	218.2	219.0	219.7	220.1
105°	271.7	272.4	273.4	274.4	275.5	276.5	277.3	278.1	278.8	279.6	280.4
107.5°	340.5	340.7	340.9	341.0	341.2	341.3	342.1	342.8	343.5	344.2	344.6
110°	387.8	387.9	387.7	387.4	387.1	386.9	386.4	385.8	385.3	384.8	384.9



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	434.5	434.3	433.8	433.4	432.9	432.4	432.3	432.2	432.1	432.0	432.0
115°	506.5	506.3	505.8	505.3	504.7	504.2	504.0	503.7	503.4	503.2	502.9
117.5°	575.7	575.6	575.2	574.9	574.5	574.2	573.3	572.4	571.5	570.6	570.0
120°	624.5	624.7	623.9	623.1	622.3	621.6	620.3	619.0	617.7	616.4	616.0
122.5°	669.5	669.5	669.1	668.8	668.4	668.0	667.2	666.3	665.4	664.5	663.6
125°	737.7	737.6	737.4	737.1	736.8	736.6	736.1	735.5	735.0	734.5	734.0
127.5°	804.3	804.5	804.0	803.6	803.2	802.8	802.3	801.8	801.3	800.7	800.3
130°	848.9	849.3	849.3	849.3	849.3	849.3	848.8	848.2	847.7	847.2	846.4
132.5°	893.6	893.8	893.6	893.4	893.2	893.0	892.4	891.9	891.4	890.9	890.4
135°	957.7	958.5	958.5	958.5	958.5	958.5	958.0	957.5	956.9	956.4	955.8
137.5°	1019.9	1020.5	1020.9	1021.3	1021.7	1022.1	1021.5	1020.8	1020.1	1019.5	1019.2
140°	1062.8	1063.0	1063.0	1063.0	1063.0	1063.0	1062.8	1062.5	1062.3	1062.0	1061.8
142.5°	1102.8	1102.9	1102.7	1102.5	1102.3	1102.1	1102.0	1102.0	1101.9	1101.9	1101.8
145°	1160.1	1160.8	1161.0	1161.3	1161.5	1161.8	1161.5	1161.3	1161.0	1160.8	1160.2
147.5°	1215.8	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3	1215.1	1214.9	1214.6	1214.4
150°	1248.4	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9	1248.8
152.5°	1278.4	1278.8	1279.0	1279.2	1279.4	1279.6	1280.2	1280.8	1281.5	1282.1	1282.1
155°	1324.4	1324.3	1324.1	1323.8	1323.5	1323.3	1324.3	1325.4	1326.4	1327.4	1327.4
157.5°	1363.5	1363.2	1363.2	1363.1	1363.1	1363.0	1363.8	1364.6	1365.3	1366.1	1366.1
160°	1388.5	1388.2	1388.0	1387.7	1387.4	1387.2	1388.0	1388.7	1389.5	1390.3	1390.0
162.5°	1409.1	1408.7	1408.4	1408.2	1407.9	1407.6	1409.0	1410.4	1411.8	1413.2	1413.3
165°	1438.7	1438.0	1437.5	1437.0	1436.5	1436.0	1437.5	1439.1	1440.6	1442.2	1442.4
167.5°	1460.5	1459.9	1460.0	1460.0	1460.1	1460.1	1461.7	1463.2	1464.8	1466.3	1466.3
170°	1472.6	1472.1	1472.4	1472.6	1472.9	1473.2	1474.7	1476.3	1477.8	1479.4	1479.2
172.5°	1482.8	1482.2	1482.3	1482.4	1482.4	1482.5	1484.2	1486.0	1487.7	1489.5	1489.5
175°	1494.7	1493.9	1493.7	1493.4	1493.2	1492.9	1494.7	1496.5	1498.3	1500.1	1500.1
177.5°	1499.9	1499.4	1499.4	1499.4	1499.4	1499.4	1500.9	1502.3	1503.8	1505.2	1505.1
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1590.3	1589.2	1585.3	1584.8	1585.3	1589.2	1590.3	1591.4	1593.0	1598.6	1591.9
5°	1469.0	1465.6	1463.5	1471.1	1463.5	1465.6	1469.0	1473.2	1480.1	1480.8	1487.7
7.5°	1377.6	1374.9	1368.8	1366.9	1368.8	1374.9	1377.6	1380.1	1387.0	1393.0	1403.2
10°	1319.0	1316.2	1310.7	1309.3	1310.7	1316.2	1319.0	1325.9	1332.8	1340.4	1347.4
12.5°	1262.6	1257.1	1256.0	1257.3	1256.0	1257.1	1262.6	1271.7	1289.7	1289.6	1290.9
15°	1187.7	1184.9	1177.3	1179.4	1177.3	1184.9	1187.7	1196.7	1204.9	1215.3	1225.7
17.5°	1113.8	1110.5	1101.3	1109.4	1101.3	1110.5	1113.8	1118.7	1129.3	1144.0	1159.6
20°	1067.4	1061.8	1057.0	1056.3	1057.0	1061.8	1067.4	1072.2	1084.0	1096.4	1108.2
22.5°	1023.1	1018.2	1017.7	1013.2	1017.7	1018.2	1023.1	1030.7	1042.5	1049.4	1060.6
25°	967.8	963.0	961.6	958.2	961.6	963.0	967.8	973.4	981.0	986.5	998.9
27.5°	925.4	923.0	920.5	921.6	920.5	923.0	925.4	926.1	929.5	936.9	944.0
30°	899.4	898.7	897.3	897.3	897.3	898.7	899.4	897.3	900.8	904.2	909.8
32.5°	877.8	877.7	878.5	878.5	878.5	877.7	877.8	874.6	875.9	877.1	879.9
35°	847.5	849.6	851.0	848.9	851.0	849.6	847.5	844.8	842.7	837.9	839.2
37.5°	820.2	822.2	824.2	826.5	824.2	822.2	820.2	814.5	809.5	805.2	800.3
40°	799.1	804.0	805.4	808.8	805.4	804.0	799.1	792.9	787.4	782.6	777.0
42.5°	779.2	784.6	788.2	788.9	788.2	784.6	779.2	773.0	764.7	758.8	751.0
45°	748.7	754.2	759.1	759.1	759.1	754.2	748.7	738.3	729.3	720.3	712.7
47.5°	717.0	725.0	729.9	731.1	729.9	725.0	717.0	706.4	693.8	682.7	671.8
50°	695.5	705.1	710.0	713.4	710.0	705.1	695.5	683.7	670.6	656.7	643.6
52.5°	674.4	684.1	690.6	692.4	690.6	684.1	674.4	659.9	644.0	629.1	617.6
55°	638.1	651.9	659.5	662.3	659.5	651.9	638.1	622.2	607.0	588.3	571.7
57.5°	603.8	616.5	625.4	627.4	625.4	616.5	603.8	585.1	565.5	545.6	527.9
60°	577.2	591.1	602.1	604.2	602.1	591.1	577.2	558.6	537.8	518.5	496.4
62.5°	550.1	564.5	574.5	579.9	574.5	564.5	550.1	530.4	508.0	486.4	464.3
65°	503.3	517.8	527.5	529.5	527.5	517.8	503.3	483.9	460.4	437.6	418.9
67.5°	452.1	466.6	473.0	477.0	473.0	466.6	452.1	433.9	410.6	387.0	365.8
70°	416.2	427.9	434.8	438.3	434.8	427.9	416.2	396.8	377.5	353.3	330.4
72.5°	375.2	387.5	395.6	396.3	395.6	387.5	375.2	358.6	338.2	315.7	295.6
75°	312.5	323.5	327.7	327.7	327.7	323.5	312.5	296.6	280.0	262.0	242.0
77.5°	247.3	253.0	258.3	259.4	258.3	253.0	247.3	235.9	222.2	204.2	189.1
80°	205.3	208.8	212.9	212.9	212.9	208.8	205.3	194.9	181.8	166.6	154.9
82.5°	162.2	165.1	169.2	168.7	169.2	165.1	162.2	154.0	143.1	132.9	122.2
85°	98.2	104.4	103.7	102.3	103.7	104.4	98.2	99.5	89.2	82.3	72.6
87.5°	50.9	51.6	53.3	54.5	53.3	51.6	50.9	49.1	44.0	40.9	38.4
90°	33.3	33.8	34.3	34.9	34.3	33.8	33.3	32.8	31.8	30.2	28.7
92.5°	50.7	51.0	51.3	51.6	51.3	51.0	50.7	50.3	49.7	48.8	47.9
95°	91.8	91.8	91.8	91.8	91.8	91.8	91.8	91.8	91.4	90.6	89.8
97.5°	143.8	143.8	143.8	143.8	143.8	143.8	143.8	143.8	143.4	142.4	141.5
100°	180.1	180.1	180.1	180.1	180.1	180.1	180.1	180.1	179.8	179.3	178.8
102.5°	220.4	220.6	220.8	221.0	220.8	220.6	220.4	220.1	219.7	219.0	218.2
105°	281.2	281.9	282.7	283.5	282.7	281.9	281.2	280.4	279.6	278.8	278.1
107.5°	344.5	344.5	344.4	344.4	344.4	344.5	344.5	344.6	344.2	343.5	342.8
110°	385.7	386.5	387.3	388.0	387.3	386.5	385.7	384.9	384.8	385.3	385.8



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	432.2	432.3	432.5	432.7	432.5	432.3	432.2	432.0	432.0	432.1	432.2
115°	502.7	502.4	502.2	501.9	502.2	502.4	502.7	502.9	503.2	503.4	503.7
117.5°	569.4	568.9	568.4	567.9	568.4	568.9	569.4	570.0	570.6	571.5	572.4
120°	616.5	617.0	617.6	618.1	617.6	617.0	616.5	616.0	616.4	617.7	619.0
122.5°	662.7	661.8	660.8	659.9	660.8	661.8	662.7	663.6	664.5	665.4	666.3
125°	733.5	733.0	732.4	731.9	732.4	733.0	733.5	734.0	734.5	735.0	735.5
127.5°	799.9	799.4	799.0	798.6	799.0	799.4	799.9	800.3	800.7	801.3	801.8
130°	845.4	844.4	843.3	842.3	843.3	844.4	845.4	846.4	847.2	847.7	848.2
132.5°	890.0	889.6	889.2	888.8	889.2	889.6	890.0	890.4	890.9	891.4	891.9
135°	955.0	954.2	953.4	952.7	953.4	954.2	955.0	955.8	956.4	956.9	957.5
137.5°	1019.4	1019.5	1019.7	1019.8	1019.7	1019.5	1019.4	1019.2	1019.5	1020.1	1020.8
140°	1061.5	1061.2	1061.0	1060.7	1061.0	1061.2	1061.5	1061.8	1062.0	1062.3	1062.5
142.5°	1101.8	1101.7	1101.7	1101.6	1101.7	1101.7	1101.8	1101.8	1101.9	1101.9	1102.0
145°	1159.5	1158.7	1157.9	1157.2	1157.9	1158.7	1159.5	1160.2	1160.8	1161.0	1161.3
147.5°	1214.2	1213.9	1213.6	1213.4	1213.6	1213.9	1214.2	1214.4	1214.6	1214.9	1215.1
150°	1248.5	1248.3	1248.0	1247.8	1248.0	1248.3	1248.5	1248.8	1248.9	1248.9	1248.9
152.5°	1281.4	1280.7	1280.0	1279.4	1280.0	1280.7	1281.4	1282.1	1282.1	1281.5	1280.8
155°	1326.4	1325.4	1324.3	1323.3	1324.3	1325.4	1326.4	1327.4	1327.4	1326.4	1325.4
157.5°	1365.2	1364.3	1363.4	1362.6	1363.4	1364.3	1365.2	1366.1	1366.1	1365.3	1364.6
160°	1388.7	1387.4	1386.2	1384.9	1386.2	1387.4	1388.7	1390.0	1390.3	1389.5	1388.7
162.5°	1412.0	1410.7	1409.4	1408.1	1409.4	1410.7	1412.0	1413.3	1413.2	1411.8	1410.4
165°	1441.4	1440.4	1439.3	1438.3	1439.3	1440.4	1441.4	1442.4	1442.2	1440.6	1439.1
167.5°	1464.7	1463.1	1461.5	1459.9	1461.5	1463.1	1464.7	1466.3	1466.3	1464.8	1463.2
170°	1477.4	1475.6	1473.8	1472.0	1473.8	1475.6	1477.4	1479.2	1479.4	1477.8	1476.3
172.5°	1487.6	1485.8	1484.0	1482.2	1484.0	1485.8	1487.6	1489.5	1489.5	1487.7	1486.0
175°	1498.3	1496.5	1494.7	1492.9	1494.7	1496.5	1498.3	1500.1	1500.1	1498.3	1496.5
177.5°	1503.4	1501.8	1500.1	1498.5	1500.1	1501.8	1503.4	1505.1	1505.2	1503.8	1502.3
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1595.3	1597.5	1606.3	1614.6	1624.6	1631.8	1636.7	1642.3	1653.9	1663.3	1672.1
5°	1494.6	1498.1	1516.0	1528.5	1549.9	1568.6	1583.1	1599.0	1617.7	1643.2	1666.7
7.5°	1406.0	1418.8	1438.5	1458.7	1480.5	1505.0	1526.3	1550.2	1582.4	1617.5	1653.7
10°	1355.7	1370.2	1390.9	1414.4	1435.2	1463.5	1489.8	1518.1	1554.7	1597.6	1640.5
12.5°	1305.3	1329.2	1345.0	1372.9	1395.3	1418.7	1446.6	1483.8	1526.5	1571.6	1623.3
15°	1242.3	1255.4	1285.8	1301.0	1332.8	1368.8	1396.4	1433.8	1475.2	1534.7	1592.8
17.5°	1169.6	1186.8	1211.0	1240.1	1276.6	1304.6	1339.1	1377.5	1429.8	1488.8	1561.5
20°	1122.0	1136.5	1166.2	1198.0	1236.7	1266.5	1303.1	1340.4	1394.4	1457.3	1533.3
22.5°	1079.4	1093.4	1124.8	1154.3	1191.9	1228.3	1266.6	1310.0	1361.7	1428.0	1505.7
25°	1013.5	1032.1	1059.8	1090.2	1126.1	1167.6	1209.1	1247.8	1303.1	1372.9	1455.9
27.5°	955.0	969.9	990.0	1024.5	1065.3	1105.4	1146.6	1195.3	1248.4	1322.2	1408.3
30°	917.4	931.2	951.2	983.0	1021.1	1063.9	1106.8	1153.8	1209.1	1282.4	1370.2
32.5°	887.5	898.0	915.8	944.3	979.0	1024.1	1066.4	1115.1	1173.1	1245.3	1330.9
35°	843.4	852.4	859.3	886.3	917.4	958.8	1001.7	1053.6	1109.5	1178.0	1263.7
37.5°	800.1	803.2	813.3	830.9	861.1	899.3	939.1	990.1	1047.5	1117.0	1194.3
40°	773.6	775.0	781.2	797.8	824.0	860.0	898.7	949.2	1003.8	1069.5	1146.2
42.5°	747.6	746.7	752.4	764.0	788.6	821.3	859.4	905.5	960.1	1020.8	1093.1
45°	706.5	706.5	705.1	714.8	734.9	766.7	798.5	842.7	888.3	947.8	1008.6
47.5°	663.7	659.8	661.0	666.0	682.9	709.0	741.1	777.3	817.5	867.9	921.2
50°	636.0	630.5	628.4	633.9	649.1	671.9	702.4	734.2	772.2	816.4	862.1
52.5°	605.6	600.1	596.3	600.2	614.3	635.4	663.1	691.0	725.2	761.1	800.7
55°	558.6	552.4	550.3	551.7	562.0	578.6	602.1	627.7	653.3	683.0	710.7
57.5°	512.3	502.0	500.1	499.4	506.6	521.8	541.4	563.6	582.2	600.2	629.6
60°	481.8	469.4	465.2	464.6	470.1	482.5	500.5	522.6	535.8	548.2	573.8
62.5°	449.2	437.3	428.2	429.2	434.1	446.0	461.8	477.8	486.5	500.1	517.4
65°	398.9	383.7	376.8	374.7	377.5	387.1	399.6	409.9	419.6	425.2	441.7
67.5°	348.6	335.8	325.6	323.1	321.9	328.5	338.7	345.0	351.9	356.7	366.5
70°	313.2	302.1	289.7	285.5	284.8	290.3	300.0	300.7	310.4	312.5	322.8
72.5°	278.3	264.5	255.9	251.8	248.9	253.8	260.2	262.0	267.3	271.0	276.4
75°	224.0	213.6	205.3	199.1	197.0	199.8	199.8	203.2	206.7	208.8	215.0
77.5°	176.3	164.4	154.6	151.0	148.5	146.7	148.2	150.3	148.6	152.2	153.6
80°	143.1	130.7	123.1	121.7	117.5	114.1	113.4	115.4	112.7	114.1	118.2
82.5°	110.5	102.5	94.3	92.9	87.7	85.9	85.2	83.9	83.9	83.6	84.5
85°	65.7	60.8	55.3	51.8	49.8	46.3	46.3	44.9	43.6	42.2	42.9
87.5°	32.0	30.6	27.4	25.3	23.8	21.2	20.7	18.4	17.3	16.2	15.1
90°	27.1	25.6	23.5	21.4	19.4	17.3	14.8	12.0	9.2	6.3	3.5
92.5°	46.9	46.0	44.6	43.1	41.7	40.2	37.9	34.6	31.4	28.1	24.9
95°	89.1	88.3	86.5	84.7	82.9	81.1	79.0	76.7	74.4	72.0	69.7
97.5°	140.6	139.6	137.5	135.4	133.3	131.2	129.2	127.3	125.5	123.6	121.8
100°	178.3	177.8	175.4	173.1	170.8	168.5	166.8	165.7	164.7	163.7	162.7
102.5°	217.5	216.8	214.7	212.6	210.4	208.3	207.1	206.6	206.2	205.8	205.4
105°	277.3	276.5	275.5	274.4	273.4	272.4	271.7	271.5	271.2	271.0	270.7
107.5°	342.1	341.3	341.2	341.0	340.9	340.7	340.5	340.2	339.9	339.6	339.2
110°	386.4	386.9	387.1	387.4	387.7	387.9	387.8	387.3	386.7	386.2	385.7



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	432.3	432.4	432.9	433.4	433.8	434.3	434.5	434.4	434.3	434.2	434.0
115°	504.0	504.2	504.7	505.3	505.8	506.3	506.5	506.5	506.5	506.5	506.5
117.5°	573.3	574.2	574.5	574.9	575.2	575.6	575.7	575.5	575.3	575.1	574.9
120°	620.3	621.6	622.3	623.1	623.9	624.7	624.5	623.5	622.5	621.4	620.4
122.5°	667.2	668.0	668.4	668.8	669.1	669.5	669.5	669.0	668.6	668.2	667.8
125°	736.1	736.6	736.8	737.1	737.4	737.6	737.7	737.7	737.7	737.7	737.7
127.5°	802.3	802.8	803.2	803.6	804.0	804.5	804.3	803.5	802.7	802.0	801.2
130°	848.8	849.3	849.3	849.3	849.3	849.3	848.9	848.1	847.3	846.6	845.8
132.5°	892.4	893.0	893.2	893.4	893.6	893.8	893.6	893.0	892.5	891.9	891.3
135°	958.0	958.5	958.5	958.5	958.5	958.5	957.7	956.2	954.6	953.1	951.5
137.5°	1021.5	1022.1	1021.7	1021.3	1020.9	1020.5	1019.9	1019.2	1018.5	1017.8	1017.0
140°	1062.8	1063.0	1063.0	1063.0	1063.0	1063.0	1062.8	1062.3	1061.8	1061.2	1060.7
142.5°	1102.0	1102.1	1102.3	1102.5	1102.7	1102.9	1102.8	1102.2	1101.7	1101.2	1100.7
145°	1161.5	1161.8	1161.5	1161.3	1161.0	1160.8	1160.1	1159.1	1158.1	1157.0	1156.0
147.5°	1215.3	1215.5	1215.7	1215.9	1216.1	1216.3	1215.8	1214.5	1213.3	1212.1	1210.8
150°	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9	1248.4	1247.4	1246.4	1245.3	1244.3
152.5°	1280.2	1279.6	1279.4	1279.2	1279.0	1278.8	1278.4	1277.7	1277.1	1276.5	1275.9
155°	1324.3	1323.3	1323.5	1323.8	1324.1	1324.3	1324.4	1324.4	1324.4	1324.4	1324.4
157.5°	1363.8	1363.0	1363.1	1363.1	1363.2	1363.2	1363.5	1364.0	1364.4	1364.9	1365.3
160°	1388.0	1387.2	1387.4	1387.7	1388.0	1388.2	1388.5	1388.7	1389.0	1389.3	1389.5
162.5°	1409.0	1407.6	1407.9	1408.2	1408.4	1408.7	1409.1	1409.8	1410.5	1411.1	1411.8
165°	1437.5	1436.0	1436.5	1437.0	1437.5	1438.0	1438.7	1439.5	1440.2	1441.0	1441.8
167.5°	1461.7	1460.1	1460.1	1460.0	1460.0	1459.9	1460.5	1461.5	1462.6	1463.7	1464.8
170°	1474.7	1473.2	1472.9	1472.6	1472.4	1472.1	1472.6	1473.9	1475.2	1476.5	1477.8
172.5°	1484.2	1482.5	1482.4	1482.4	1482.3	1482.2	1482.8	1483.8	1484.9	1486.0	1487.1
175°	1494.7	1492.9	1493.2	1493.4	1493.7	1493.9	1494.7	1496.0	1497.3	1498.6	1499.9
177.5°	1500.9	1499.4	1499.4	1499.4	1499.4	1499.4	1499.9	1501.0	1502.0	1503.0	1504.1
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1679.9	1685.4	1692.6	1704.8	1709.2	1714.7	1722.5	1721.9	1724.1	1732.4	1750.1
5°	1686.1	1707.5	1728.3	1753.2	1779.4	1796.7	1820.2	1834.7	1849.2	1867.9	1899.7
7.5°	1688.6	1722.6	1760.6	1804.3	1843.2	1888.0	1922.9	1955.8	1985.6	2025.0	2062.9
10°	1684.7	1730.3	1779.4	1834.7	1893.5	1943.3	1988.2	2039.4	2082.9	2130.6	2173.5
12.5°	1677.5	1732.6	1798.2	1860.2	1928.9	2002.4	2058.4	2110.1	2168.1	2223.0	2289.1
15°	1661.2	1736.6	1813.3	1894.9	1986.8	2071.8	2152.7	2219.8	2282.0	2364.3	2450.7
17.5°	1640.5	1721.8	1818.5	1917.3	2013.4	2110.6	2210.7	2311.5	2390.0	2492.2	2559.8
20°	1621.1	1715.1	1814.7	1932.2	2028.3	2149.3	2248.8	2346.3	2454.1	2555.8	2636.6
22.5°	1594.0	1696.9	1802.5	1919.5	2046.0	2167.0	2282.0	2387.8	2495.6	2606.1	2704.1
25°	1559.6	1652.9	1778.0	1910.8	2036.6	2167.9	2300.0	2432.7	2548.8	2665.7	2756.9
27.5°	1501.0	1618.8	1735.3	1872.3	2012.1	2160.7	2301.9	2440.9	2562.5	2658.6	2715.2
30°	1471.1	1573.4	1699.9	1837.5	1988.9	2148.6	2295.8	2432.0	2545.4	2622.1	2644.9
32.5°	1426.9	1532.5	1656.2	1798.8	1959.0	2123.1	2276.5	2404.9	2499.5	2539.7	2512.2
35°	1361.2	1456.6	1581.7	1727.6	1894.2	2069.1	2220.5	2329.0	2377.4	2339.4	2244.7
37.5°	1282.4	1376.9	1502.6	1645.9	1818.3	1996.1	2133.0	2211.1	2195.0	2100.5	1959.3
40°	1227.1	1315.6	1435.2	1590.0	1758.0	1936.3	2056.6	2098.8	2054.6	1919.1	1769.1
42.5°	1165.7	1252.0	1372.1	1521.4	1699.4	1863.9	1968.7	1972.2	1898.0	1736.0	1585.4
45°	1072.2	1154.5	1267.9	1423.4	1587.9	1742.8	1811.9	1778.0	1641.2	1484.9	1333.5
47.5°	980.0	1051.3	1163.1	1310.7	1467.0	1597.3	1631.6	1570.6	1424.8	1273.1	1132.8
50°	912.5	984.4	1089.5	1230.5	1381.2	1493.9	1510.5	1429.6	1286.5	1133.7	1023.8
52.5°	847.8	919.2	1020.4	1150.9	1288.9	1390.5	1391.0	1297.4	1154.9	1018.7	916.5
55°	752.8	817.1	908.4	1025.2	1148.3	1227.8	1208.4	1111.6	987.9	869.7	780.5
57.5°	661.3	717.3	801.4	898.8	1007.2	1072.8	1040.7	947.5	837.0	736.8	669.2
60°	602.1	655.4	727.3	819.2	910.5	961.6	931.2	846.8	745.2	664.3	605.6
62.5°	544.6	589.5	658.7	738.5	823.1	861.0	833.9	750.6	662.8	589.7	542.0
65°	463.2	499.8	555.1	623.6	685.1	717.6	694.8	617.3	550.3	497.7	459.7
67.5°	387.1	415.8	457.6	512.5	564.8	582.4	561.6	507.7	450.9	408.8	382.0
70°	334.6	361.6	396.8	439.0	484.6	503.3	482.5	439.7	393.4	354.6	328.4
72.5°	288.7	309.6	339.3	375.4	411.1	429.7	415.6	374.4	335.3	306.5	284.1
75°	219.8	237.8	258.5	284.1	311.8	324.2	311.8	283.4	256.5	235.0	219.1
77.5°	159.8	169.5	185.5	204.6	221.9	231.4	220.7	201.4	185.0	170.3	162.5
80°	121.7	128.6	139.6	154.9	166.6	175.6	168.7	152.8	139.6	130.0	126.5
82.5°	88.5	93.2	100.4	111.7	119.6	124.2	121.1	109.6	104.2	95.7	92.2
85°	43.6	46.3	51.2	54.6	61.5	62.2	62.9	58.1	53.2	51.2	48.4
87.5°	16.2	17.3	19.5	21.8	24.5	25.4	25.3	25.7	23.9	23.7	21.8
90°	6.3	9.2	12.0	14.8	17.3	19.4	21.4	23.5	25.6	27.1	28.7
92.5°	28.1	31.4	34.6	37.9	40.2	41.7	43.1	44.6	46.0	46.9	47.9
95°	72.0	74.4	76.7	79.0	81.1	82.9	84.7	86.5	88.3	89.1	89.8
97.5°	123.6	125.5	127.3	129.2	131.2	133.3	135.4	137.5	139.6	140.6	141.5
100°	163.7	164.7	165.7	166.8	168.5	170.8	173.1	175.4	177.8	178.3	178.8
102.5°	205.8	206.2	206.6	207.1	208.3	210.4	212.6	214.7	216.8	217.5	218.2
105°	271.0	271.2	271.5	271.7	272.4	273.4	274.4	275.5	276.5	277.3	278.1
107.5°	339.6	339.9	340.2	340.5	340.7	340.9	341.0	341.2	341.3	342.1	342.8
110°	386.2	386.7	387.3	387.8	387.9	387.7	387.4	387.1	386.9	386.4	385.8



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	434.2	434.3	434.4	434.5	434.3	433.8	433.4	432.9	432.4	432.3	432.2
115°	506.5	506.5	506.5	506.5	506.3	505.8	505.3	504.7	504.2	504.0	503.7
117.5°	575.1	575.3	575.5	575.7	575.6	575.2	574.9	574.5	574.2	573.3	572.4
120°	621.4	622.5	623.5	624.5	624.7	623.9	623.1	622.3	621.6	620.3	619.0
122.5°	668.2	668.6	669.0	669.5	669.5	669.1	668.8	668.4	668.0	667.2	666.3
125°	737.7	737.7	737.7	737.7	737.6	737.4	737.1	736.8	736.6	736.1	735.5
127.5°	802.0	802.7	803.5	804.3	804.5	804.0	803.6	803.2	802.8	802.3	801.8
130°	846.6	847.3	848.1	848.9	849.3	849.3	849.3	849.3	849.3	848.8	848.2
132.5°	891.9	892.5	893.0	893.6	893.8	893.6	893.4	893.2	893.0	892.4	891.9
135°	953.1	954.6	956.2	957.7	958.5	958.5	958.5	958.5	958.5	958.0	957.5
137.5°	1017.8	1018.5	1019.2	1019.9	1020.5	1020.9	1021.3	1021.7	1022.1	1021.5	1020.8
140°	1061.2	1061.8	1062.3	1062.8	1063.0	1063.0	1063.0	1063.0	1063.0	1062.8	1062.5
142.5°	1101.2	1101.7	1102.2	1102.8	1102.9	1102.7	1102.5	1102.3	1102.1	1102.0	1102.0
145°	1157.0	1158.1	1159.1	1160.1	1160.8	1161.0	1161.3	1161.5	1161.8	1161.5	1161.3
147.5°	1212.1	1213.3	1214.5	1215.8	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3	1215.1
150°	1245.3	1246.4	1247.4	1248.4	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9
152.5°	1276.5	1277.1	1277.7	1278.4	1278.8	1279.0	1279.2	1279.4	1279.6	1280.2	1280.8
155°	1324.4	1324.4	1324.4	1324.4	1324.3	1324.1	1323.8	1323.5	1323.3	1324.3	1325.4
157.5°	1364.9	1364.4	1364.0	1363.5	1363.2	1363.2	1363.1	1363.1	1363.0	1363.8	1364.6
160°	1389.3	1389.0	1388.7	1388.5	1388.2	1388.0	1387.7	1387.4	1387.2	1388.0	1388.7
162.5°	1411.1	1410.5	1409.8	1409.1	1408.7	1408.4	1408.2	1407.9	1407.6	1409.0	1410.4
165°	1441.0	1440.2	1439.5	1438.7	1438.0	1437.5	1437.0	1436.5	1436.0	1437.5	1439.1
167.5°	1463.7	1462.6	1461.5	1460.5	1459.9	1460.0	1460.0	1460.1	1460.1	1461.7	1463.2
170°	1476.5	1475.2	1473.9	1472.6	1472.1	1472.4	1472.6	1472.9	1473.2	1474.7	1476.3
172.5°	1486.0	1484.9	1483.8	1482.8	1482.2	1482.3	1482.4	1482.4	1482.5	1484.2	1486.0
175°	1498.6	1497.3	1496.0	1494.7	1493.9	1493.7	1493.4	1493.2	1492.9	1494.7	1496.5
177.5°	1503.0	1502.0	1501.0	1499.9	1499.4	1499.4	1499.4	1499.4	1499.4	1500.9	1502.3
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1759.0	1760.1	1765.0	1768.9	1770.0	1775.6	1776.1
5°	1913.5	1925.3	1948.1	1950.2	1953.6	1971.6	1957.8
7.5°	2094.7	2124.5	2144.4	2162.0	2168.4	2176.2	2174.6
10°	2210.8	2255.0	2277.2	2312.4	2313.8	2322.8	2317.3
12.5°	2327.5	2378.9	2419.3	2425.8	2455.4	2459.9	2467.7
15°	2492.8	2547.5	2603.5	2623.5	2664.3	2674.0	2689.2
17.5°	2648.3	2704.1	2743.4	2795.2	2812.0	2834.4	2819.1
20°	2733.4	2794.3	2844.0	2884.8	2902.1	2914.5	2913.2
22.5°	2784.9	2846.2	2886.6	2917.4	2933.6	2938.9	2938.6
25°	2817.1	2852.3	2864.8	2876.5	2858.6	2852.3	2855.1
27.5°	2727.5	2718.4	2685.9	2643.3	2599.0	2563.9	2544.8
30°	2604.2	2550.2	2501.1	2415.4	2371.2	2344.9	2321.4
32.5°	2429.4	2343.9	2249.5	2171.0	2120.7	2081.7	2075.9
35°	2129.9	2001.3	1885.9	1789.8	1740.0	1697.8	1688.2
37.5°	1810.8	1677.2	1573.3	1488.7	1435.2	1405.4	1377.6
40°	1599.0	1484.2	1381.9	1310.0	1269.2	1247.8	1230.5
42.5°	1435.8	1331.0	1229.3	1174.5	1137.6	1124.5	1114.4
45°	1210.5	1113.0	1042.5	1001.0	979.6	957.5	947.1
47.5°	1030.0	950.7	904.2	869.0	846.0	832.9	826.2
50°	927.7	862.7	821.3	794.3	773.6	763.2	757.7
52.5°	837.0	783.7	748.8	727.4	713.3	705.7	703.5
55°	721.0	680.2	658.1	639.5	629.1	622.2	619.4
57.5°	626.7	595.4	577.4	562.0	558.0	552.2	550.3
60°	564.8	540.6	525.4	515.0	511.6	504.7	506.0
62.5°	510.0	490.3	477.3	471.3	466.8	461.0	462.9
65°	431.4	416.9	409.9	404.4	398.9	395.4	398.2
67.5°	362.0	352.0	342.6	339.4	336.7	336.1	333.2
70°	316.6	308.3	300.0	298.0	298.0	295.2	294.5
72.5°	272.9	266.8	261.3	259.8	257.6	258.7	255.8
75°	210.8	206.0	203.9	201.9	201.2	201.2	199.1
77.5°	155.8	152.2	148.9	148.9	146.4	145.5	145.2
80°	118.2	116.8	114.1	114.1	112.7	113.4	112.0
82.5°	88.9	87.0	86.4	85.3	83.4	83.5	82.1
85°	47.7	45.6	44.9	42.9	41.5	42.9	41.5
87.5°	22.6	22.4	22.0	21.0	20.6	20.7	19.1
90°	30.2	31.8	32.8	33.3	33.8	34.3	34.9
92.5°	48.8	49.7	50.3	50.7	51.0	51.3	51.6
95°	90.6	91.4	91.8	91.8	91.8	91.8	91.8
97.5°	142.4	143.4	143.8	143.8	143.8	143.8	143.8
100°	179.3	179.8	180.1	180.1	180.1	180.1	180.1
102.5°	219.0	219.7	220.1	220.4	220.6	220.8	221.0
105°	278.8	279.6	280.4	281.2	281.9	282.7	283.5
107.5°	343.5	344.2	344.6	344.5	344.5	344.4	344.4
110°	385.3	384.8	384.9	385.7	386.5	387.3	388.0



TEST NUMBER: P332662

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	432.1	432.0	432.0	432.2	432.3	432.5	432.7
115°	503.4	503.2	502.9	502.7	502.4	502.2	501.9
117.5°	571.5	570.6	570.0	569.4	568.9	568.4	567.9
120°	617.7	616.4	616.0	616.5	617.0	617.6	618.1
122.5°	665.4	664.5	663.6	662.7	661.8	660.8	659.9
125°	735.0	734.5	734.0	733.5	733.0	732.4	731.9
127.5°	801.3	800.7	800.3	799.9	799.4	799.0	798.6
130°	847.7	847.2	846.4	845.4	844.4	843.3	842.3
132.5°	891.4	890.9	890.4	890.0	889.6	889.2	888.8
135°	956.9	956.4	955.8	955.0	954.2	953.4	952.7
137.5°	1020.1	1019.5	1019.2	1019.4	1019.5	1019.7	1019.8
140°	1062.3	1062.0	1061.8	1061.5	1061.2	1061.0	1060.7
142.5°	1101.9	1101.9	1101.8	1101.8	1101.7	1101.7	1101.6
145°	1161.0	1160.8	1160.2	1159.5	1158.7	1157.9	1157.2
147.5°	1214.9	1214.6	1214.4	1214.2	1213.9	1213.6	1213.4
150°	1248.9	1248.9	1248.8	1248.5	1248.3	1248.0	1247.8
152.5°	1281.5	1282.1	1282.1	1281.4	1280.7	1280.0	1279.4
155°	1326.4	1327.4	1327.4	1326.4	1325.4	1324.3	1323.3
157.5°	1365.3	1366.1	1366.1	1365.2	1364.3	1363.4	1362.6
160°	1389.5	1390.3	1390.0	1388.7	1387.4	1386.2	1384.9
162.5°	1411.8	1413.2	1413.3	1412.0	1410.7	1409.4	1408.1
165°	1440.6	1442.2	1442.4	1441.4	1440.4	1439.3	1438.3
167.5°	1464.8	1466.3	1466.3	1464.7	1463.1	1461.5	1459.9
170°	1477.8	1479.4	1479.2	1477.4	1475.6	1473.8	1472.0
172.5°	1487.7	1489.5	1489.5	1487.6	1485.8	1484.0	1482.2
175°	1498.3	1500.1	1500.1	1498.3	1496.5	1494.7	1492.9
177.5°	1503.8	1505.2	1505.1	1503.4	1501.8	1500.1	1498.5
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2

(END OF REPORT)