

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332668

Luminaire Tested: **SA4XXDIP-C1020D1205U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332668  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8600.1 lumens  
Efficiency: N/A  
Efficacy: 131.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332668

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332668

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52				
1	98	94	90	86	91	87	83	80	74	71	69	62	60	58	51	50	48	43				
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36				
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31				
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23				
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20				
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	17	14				
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332668

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.5	1.9
10°-20°	457.8	5.3
20°-30°	673.9	7.8
30°-40°	783.4	9.1
40°-50°	783.4	9.1
50°-60°	685.3	8.0
60°-70°	508.9	5.9
70°-80°	289.1	3.4
80°-90°	87.9	1.0
90°-100°	99.1	1.2
100°-110°	293.5	3.4
110°-120°	498.2	5.8
120°-130°	656.9	7.6
130°-140°	737.7	8.6
140°-150°	724.9	8.4
150°-160°	609.7	7.1
160°-170°	405.7	4.7
170°-180°	142.1	1.7
0°-30°	1294.2	15.0
0°-40°	2077.6	24.2
0°-60°	3546.4	41.2
0°-90°	4432.4	51.5
90°-120°	890.8	10.4
90°-150°	3010.3	35.0
90°-180°	4168.0	48.5
0°-180°	8600.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	4	16	26	32	35	8
95°	70	80	88	92	92	78
105°	271	272	276	280	284	287
115°	506	506	504	503	502	499
125°	738	738	737	734	732	657
135°	952	958	958	956	953	736
145°	1156	1160	1162	1160	1157	723
155°	1324	1324	1323	1327	1323	609
165°	1442	1438	1436	1442	1438	406
175°	1500	1494	1493	1500	1493	142
180°	1502	1502	1502	1502	1502	



TEST NUMBER: P332668

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	29.5	29.8	30.1	30.4	30.7	31.0	31.2	31.3	31.5	31.7	32.0
90°	3.5	6.3	9.2	12.0	14.8	17.3	19.4	21.4	23.5	25.6	27.1
92.5°	24.9	28.1	31.4	34.6	37.9	40.2	41.7	43.1	44.6	46.0	46.9
95°	69.7	72.0	74.4	76.7	79.0	81.1	82.9	84.7	86.5	88.3	89.1
97.5°	121.8	123.6	125.5	127.3	129.2	131.2	133.3	135.4	137.5	139.6	140.6
100°	162.7	163.7	164.7	165.7	166.8	168.5	170.8	173.1	175.4	177.8	178.3
102.5°	205.4	205.8	206.2	206.6	207.1	208.3	210.4	212.6	214.7	216.8	217.5
105°	270.7	271.0	271.2	271.5	271.7	272.4	273.4	274.4	275.5	276.5	277.3
107.5°	339.2	339.6	339.9	340.2	340.5	340.7	340.9	341.0	341.2	341.3	342.1
110°	385.7	386.2	386.7	387.3	387.8	387.9	387.7	387.4	387.1	386.9	386.4



TEST NUMBER: P332668

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	434.0	434.2	434.3	434.4	434.5	434.3	433.8	433.4	432.9	432.4	432.3
115°	506.5	506.5	506.5	506.5	506.5	506.3	505.8	505.3	504.7	504.2	504.0
117.5°	574.9	575.1	575.3	575.5	575.7	575.6	575.2	574.9	574.5	574.2	573.3
120°	620.4	621.4	622.5	623.5	624.5	624.7	623.9	623.1	622.3	621.6	620.3
122.5°	667.8	668.2	668.6	669.0	669.5	669.5	669.1	668.8	668.4	668.0	667.2
125°	737.7	737.7	737.7	737.7	737.7	737.6	737.4	737.1	736.8	736.6	736.1
127.5°	801.2	802.0	802.7	803.5	804.3	804.5	804.0	803.6	803.2	802.8	802.3
130°	845.8	846.6	847.3	848.1	848.9	849.3	849.3	849.3	849.3	849.3	848.8
132.5°	891.3	891.9	892.5	893.0	893.6	893.8	893.6	893.4	893.2	893.0	892.4
135°	951.5	953.1	954.6	956.2	957.7	958.5	958.5	958.5	958.5	958.5	958.0
137.5°	1017.0	1017.8	1018.5	1019.2	1019.9	1020.5	1020.9	1021.3	1021.7	1022.1	1021.5
140°	1060.7	1061.2	1061.8	1062.3	1062.8	1063.0	1063.0	1063.0	1063.0	1063.0	1062.8
142.5°	1100.7	1101.2	1101.7	1102.2	1102.8	1102.9	1102.7	1102.5	1102.3	1102.1	1102.0
145°	1156.0	1157.0	1158.1	1159.1	1160.1	1160.8	1161.0	1161.3	1161.5	1161.8	1161.5
147.5°	1210.8	1212.1	1213.3	1214.5	1215.8	1216.3	1216.1	1215.9	1215.7	1215.5	1215.3
150°	1244.3	1245.3	1246.4	1247.4	1248.4	1248.9	1248.9	1248.9	1248.9	1248.9	1248.9
152.5°	1275.9	1276.5	1277.1	1277.7	1278.4	1278.8	1279.0	1279.2	1279.4	1279.6	1280.2
155°	1324.4	1324.4	1324.4	1324.4	1324.4	1324.3	1324.1	1323.8	1323.5	1323.3	1324.3
157.5°	1365.3	1364.9	1364.4	1364.0	1363.5	1363.2	1363.2	1363.1	1363.1	1363.0	1363.8
160°	1389.5	1389.3	1389.0	1388.7	1388.5	1388.2	1388.0	1387.7	1387.4	1387.2	1388.0
162.5°	1411.8	1411.1	1410.5	1409.8	1409.1	1408.7	1408.4	1408.2	1407.9	1407.6	1409.0
165°	1441.8	1441.0	1440.2	1439.5	1438.7	1438.0	1437.5	1437.0	1436.5	1436.0	1437.5
167.5°	1464.8	1463.7	1462.6	1461.5	1460.5	1459.9	1460.0	1460.0	1460.1	1460.1	1461.7
170°	1477.8	1476.5	1475.2	1473.9	1472.6	1472.1	1472.4	1472.6	1472.9	1473.2	1474.7
172.5°	1487.1	1486.0	1484.9	1483.8	1482.8	1482.2	1482.3	1482.4	1482.4	1482.5	1484.2
175°	1499.9	1498.6	1497.3	1496.0	1494.7	1493.9	1493.7	1493.4	1493.2	1492.9	1494.7
177.5°	1504.1	1503.0	1502.0	1501.0	1499.9	1499.4	1499.4	1499.4	1499.4	1499.4	1500.9
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2



TEST NUMBER: P332668

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	32.3	32.6	32.9	33.1	33.2	33.3	33.4	33.5
90°	28.7	30.2	31.8	32.8	33.3	33.8	34.3	34.9
92.5°	47.9	48.8	49.7	50.3	50.7	51.0	51.3	51.6
95°	89.8	90.6	91.4	91.8	91.8	91.8	91.8	91.8
97.5°	141.5	142.4	143.4	143.8	143.8	143.8	143.8	143.8
100°	178.8	179.3	179.8	180.1	180.1	180.1	180.1	180.1
102.5°	218.2	219.0	219.7	220.1	220.4	220.6	220.8	221.0
105°	278.1	278.8	279.6	280.4	281.2	281.9	282.7	283.5
107.5°	342.8	343.5	344.2	344.6	344.5	344.5	344.4	344.4
110°	385.8	385.3	384.8	384.9	385.7	386.5	387.3	388.0





TEST NUMBER: P332668

CATALOG NUMBER: SA4XXDIP-C1020D1205U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.2	432.1	432.0	432.0	432.2	432.3	432.5	432.7
115°	503.7	503.4	503.2	502.9	502.7	502.4	502.2	501.9
117.5°	572.4	571.5	570.6	570.0	569.4	568.9	568.4	567.9
120°	619.0	617.7	616.4	616.0	616.5	617.0	617.6	618.1
122.5°	666.3	665.4	664.5	663.6	662.7	661.8	660.8	659.9
125°	735.5	735.0	734.5	734.0	733.5	733.0	732.4	731.9
127.5°	801.8	801.3	800.7	800.3	799.9	799.4	799.0	798.6
130°	848.2	847.7	847.2	846.4	845.4	844.4	843.3	842.3
132.5°	891.9	891.4	890.9	890.4	890.0	889.6	889.2	888.8
135°	957.5	956.9	956.4	955.8	955.0	954.2	953.4	952.7
137.5°	1020.8	1020.1	1019.5	1019.2	1019.4	1019.5	1019.7	1019.8
140°	1062.5	1062.3	1062.0	1061.8	1061.5	1061.2	1061.0	1060.7
142.5°	1102.0	1101.9	1101.9	1101.8	1101.8	1101.7	1101.7	1101.6
145°	1161.3	1161.0	1160.8	1160.2	1159.5	1158.7	1157.9	1157.2
147.5°	1215.1	1214.9	1214.6	1214.4	1214.2	1213.9	1213.6	1213.4
150°	1248.9	1248.9	1248.9	1248.8	1248.5	1248.3	1248.0	1247.8
152.5°	1280.8	1281.5	1282.1	1282.1	1281.4	1280.7	1280.0	1279.4
155°	1325.4	1326.4	1327.4	1327.4	1326.4	1325.4	1324.3	1323.3
157.5°	1364.6	1365.3	1366.1	1366.1	1365.2	1364.3	1363.4	1362.6
160°	1388.7	1389.5	1390.3	1390.0	1388.7	1387.4	1386.2	1384.9
162.5°	1410.4	1411.8	1413.2	1413.3	1412.0	1410.7	1409.4	1408.1
165°	1439.1	1440.6	1442.2	1442.4	1441.4	1440.4	1439.3	1438.3
167.5°	1463.2	1464.8	1466.3	1466.3	1464.7	1463.1	1461.5	1459.9
170°	1476.3	1477.8	1479.4	1479.2	1477.4	1475.6	1473.8	1472.0
172.5°	1486.0	1487.7	1489.5	1489.5	1487.6	1485.8	1484.0	1482.2
175°	1496.5	1498.3	1500.1	1500.1	1498.3	1496.5	1494.7	1492.9
177.5°	1502.3	1503.8	1505.2	1505.1	1503.4	1501.8	1500.1	1498.5
180°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2

(END OF REPORT)