

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331714-940

Luminaire Tested: **SA2XXRDIP-C865D530U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331714-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4575.5 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331714-940
CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331714-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	56	55	51
2	92	85	79	74	85	79	74	70	69	65	62	60	57	55	51	49	47	43
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37
4	77	67	59	53	72	63	56	51	55	50	45	48	44	41	42	38	36	33
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32	29
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	34	31	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	23	21	19
10	50	38	31	26	46	36	29	25	32	27	23	28	24	21	25	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21111	21111	21111
5°	21191	20846	20960
10°	21028	20505	20330
15°	20787	19896	19323
20°	20452	19029	18076
25°	20110	18045	16864
30°	19634	17031	15310
35°	19170	15930	13947
40°	18704	14790	12370
45°	18155	13511	10942
50°	17595	12215	9540
55°	17022	10826	8194
60°	16353	9361	6801
65°	15595	7866	6193
70°	14691	6477	5693
75°	13587	5908	5315
80°	11985	5281	4844
85°	9429	4168	4168



TEST NUMBER: P331714-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	2.7
10°-20°	336.0	7.3
20°-30°	471.9	10.3
30°-40°	514.6	11.2
40°-50°	473.1	10.3
50°-60°	371.6	8.1
60°-70°	242.3	5.3
70°-80°	124.9	2.7
80°-90°	34.0	0.7
90°-100°	21.5	0.5
100°-110°	78.7	1.7
110°-120°	210.3	4.6
120°-130°	347.1	7.6
130°-140°	369.2	8.1
140°-150°	343.1	7.5
150°-160°	275.9	6.0
160°-170°	177.8	3.9
170°-180°	61.2	1.3
0°-30°	930.3	20.3
0°-40°	1444.9	31.6
0°-60°	2289.6	50.0
0°-90°	2690.8	58.8
90°-120°	310.4	6.8
90°-150°	1369.9	29.9
90°-180°	1885.0	41.2
0°-180°	4575.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1308	1301	1286	1296	1293	124
15°	1244	1229	1190	1168	1156	350
25°	1129	1089	1013	966	947	519
35°	973	910	808	736	708	608
45°	795	713	592	511	479	614
55°	605	510	385	316	291	540
65°	408	312	206	168	162	405
75°	218	137	95	87	85	230
85°	51	27	22	22	22	60
90°	0	6	9	12	13	3
95°	30	16	18	20	20	37
105°	141	148	28	33	35	151
115°	268	276	287	82	38	263
125°	378	385	393	396	398	337
135°	468	475	480	484	484	361
145°	543	543	550	553	551	340
155°	598	594	599	602	598	275
165°	630	628	629	632	629	178
175°	644	642	642	645	641	61
180°	643	643	643	643	643	



TEST NUMBER: P331714-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1312.2	1311.2	1310.1	1309.0	1308.1	1306.4	1304.0	1301.7	1299.4	1297.1	1299.2
5°	1307.5	1306.2	1304.8	1303.5	1302.3	1299.8	1296.5	1293.1	1289.6	1286.2	1288.5
7.5°	1294.0	1292.4	1290.8	1289.1	1287.5	1284.7	1280.7	1276.7	1272.6	1268.6	1269.4
10°	1282.6	1280.8	1279.0	1277.1	1275.2	1271.8	1266.5	1261.2	1256.0	1250.7	1249.9
12.5°	1268.5	1266.1	1263.9	1261.7	1259.4	1254.9	1248.1	1241.4	1234.7	1228.0	1226.5
15°	1243.6	1240.7	1237.8	1234.9	1232.0	1226.1	1217.2	1208.3	1199.3	1190.3	1185.4
17.5°	1213.1	1208.6	1204.3	1199.8	1195.4	1187.5	1176.0	1164.5	1153.1	1141.6	1135.7
20°	1190.3	1185.1	1179.8	1174.6	1169.3	1160.1	1146.9	1133.8	1120.7	1107.5	1100.9
22.5°	1165.7	1159.8	1154.0	1148.1	1142.2	1131.8	1117.0	1102.2	1087.4	1072.5	1064.0
25°	1128.8	1120.4	1112.0	1103.6	1095.2	1082.3	1064.9	1047.6	1030.2	1012.9	1002.1
27.5°	1084.3	1075.1	1066.0	1056.9	1047.8	1033.4	1013.8	994.3	974.6	955.1	942.5
30°	1053.1	1043.1	1033.1	1023.1	1013.2	997.6	976.6	955.6	934.5	913.5	900.1
32.5°	1022.8	1011.1	999.4	987.7	976.1	959.6	938.1	916.6	895.2	873.7	858.4
35°	972.6	959.2	945.8	932.4	919.0	900.7	877.5	854.4	831.3	808.2	791.6
37.5°	922.5	907.8	893.0	878.2	863.5	843.8	819.2	794.5	769.9	745.2	726.9
40°	887.4	871.6	855.9	840.1	824.3	803.7	778.2	752.7	727.2	701.7	683.0
42.5°	851.5	834.8	818.2	801.6	785.0	763.5	737.2	710.8	684.5	658.1	638.8
45°	795.1	777.5	759.9	742.3	724.7	702.0	674.5	646.8	619.2	591.7	572.9
47.5°	740.2	721.6	702.9	684.2	665.6	641.9	613.5	585.0	556.4	528.0	509.4
50°	700.5	681.8	663.2	644.4	625.8	602.0	573.1	544.1	515.2	486.3	468.1
52.5°	661.6	642.1	622.7	603.2	583.6	559.7	531.5	503.1	474.8	446.6	429.0
55°	604.7	584.2	563.7	543.1	522.6	498.1	469.8	441.3	413.0	384.6	368.8
57.5°	546.2	525.1	504.1	483.0	462.1	437.9	410.5	383.3	356.0	328.7	314.2
60°	506.4	485.4	464.4	443.4	422.3	398.2	371.1	344.0	317.0	289.9	276.5
62.5°	467.6	446.6	425.5	404.5	383.4	360.1	334.2	308.4	282.6	256.7	244.0
65°	408.2	386.9	365.6	344.3	323.1	300.5	276.9	253.2	229.5	205.9	197.0
67.5°	351.0	329.8	308.7	287.5	266.4	245.1	223.9	202.6	181.3	160.0	155.9
70°	311.2	290.7	270.2	249.7	229.2	209.8	191.7	173.5	155.4	137.2	134.6
72.5°	273.3	253.7	234.0	214.4	194.7	177.5	163.0	148.4	133.8	119.3	117.1
75°	217.8	199.3	180.9	162.5	144.1	130.5	121.5	112.5	103.6	94.7	92.8
77.5°	163.1	146.9	130.7	114.6	98.4	88.3	83.9	79.6	75.3	71.0	69.9
80°	128.9	115.6	102.2	88.7	75.3	67.3	64.6	62.1	59.4	56.8	55.7
82.5°	97.7	87.3	76.8	66.3	55.9	49.8	48.0	46.2	44.4	42.6	42.0
85°	50.9	45.4	39.9	34.3	28.8	25.7	24.9	24.1	23.3	22.5	22.5
87.5°	15.2	13.8	12.3	10.9	9.5	8.7	8.9	9.1	9.3	9.5	9.4
90°	0.4	1.6	2.8	3.8	5.0	6.0	6.9	7.7	8.5	9.3	9.8
92.5°	9.4	9.3	9.2	9.1	9.0	9.2	9.5	10.0	10.3	10.8	11.1
95°	30.2	26.8	23.5	20.0	16.6	15.2	16.0	16.7	17.4	18.2	18.6
97.5°	60.0	50.4	40.8	31.2	21.6	17.6	19.3	21.0	22.6	24.3	24.7
100°	82.4	68.2	54.0	39.9	25.7	19.5	21.2	23.0	24.8	26.5	27.4
102.5°	106.9	104.0	100.9	97.9	95.0	86.1	71.4	56.7	42.0	27.3	28.4
105°	141.4	144.5	147.7	150.8	153.9	141.3	113.1	84.9	56.6	28.4	29.5
107.5°	180.8	183.3	185.8	188.3	190.8	175.1	141.3	107.5	73.6	39.8	38.6
110°	206.2	208.3	210.5	212.7	214.8	201.0	171.1	141.2	111.3	81.4	71.1



TEST NUMBER: P331714-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	230.0	231.9	233.8	235.8	237.6	235.0	227.6	220.2	212.8	205.5	167.6
115°	267.6	269.3	271.1	272.9	274.6	276.8	279.4	282.0	284.5	287.1	239.2
117.5°	301.2	303.2	305.1	307.1	309.1	310.9	312.7	314.5	316.3	318.0	306.5
120°	325.7	327.3	328.9	330.4	332.0	333.7	335.6	337.4	339.2	341.1	342.3
122.5°	346.6	348.2	349.9	351.5	353.1	355.0	357.0	359.0	361.1	363.1	363.8
125°	378.4	379.7	381.0	382.4	383.7	385.4	387.4	389.3	391.3	393.2	394.0
127.5°	407.1	408.6	410.1	411.5	413.0	414.6	416.0	417.5	418.9	420.4	421.4
130°	425.3	427.0	428.6	430.3	431.9	433.4	434.5	435.6	436.8	437.9	439.1
132.5°	444.0	445.3	446.7	448.2	449.6	450.8	452.0	453.2	454.2	455.4	456.4
135°	468.1	469.8	471.4	473.1	474.7	476.1	477.0	478.0	478.8	479.7	480.8
137.5°	492.7	493.7	494.9	496.1	497.2	498.4	499.4	500.5	501.5	502.6	503.6
140°	508.6	509.4	510.3	511.1	511.9	512.9	514.1	515.2	516.3	517.5	518.4
142.5°	522.0	522.8	523.5	524.2	525.0	526.0	527.4	528.6	529.9	531.3	532.1
145°	543.1	543.0	542.9	542.8	542.7	543.5	545.3	547.0	548.8	550.5	551.3
147.5°	561.4	561.0	560.6	560.3	559.8	560.5	562.2	564.0	565.7	567.5	568.0
150°	573.3	572.6	571.9	571.1	570.4	570.9	572.6	574.2	575.9	577.5	578.1
152.5°	583.4	582.6	581.8	580.9	580.1	580.5	582.1	583.7	585.2	586.8	587.5
155°	598.0	597.1	596.1	595.2	594.2	594.4	595.7	596.9	598.2	599.4	600.0
157.5°	609.4	608.7	607.9	607.1	606.3	606.4	607.2	608.1	608.9	609.8	610.5
160°	616.2	615.5	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2	616.8
162.5°	622.1	621.4	620.8	620.2	619.6	619.6	620.1	620.6	621.2	621.7	622.4
165°	630.1	629.5	628.8	628.2	627.6	627.5	627.8	628.0	628.4	628.7	629.5
167.5°	636.1	635.4	634.8	634.2	633.6	633.4	633.6	634.0	634.3	634.5	635.3
170°	639.4	638.8	638.2	637.6	636.9	636.7	636.9	637.1	637.3	637.6	638.3
172.5°	641.7	641.1	640.4	639.8	639.2	638.9	639.2	639.4	639.5	639.8	640.5
175°	644.5	643.8	643.1	642.4	641.6	641.4	641.6	641.8	641.9	642.2	642.9
177.5°	645.0	644.4	643.8	643.3	642.7	642.4	642.5	642.6	642.7	642.7	643.4
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331714-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1301.3	1303.4	1305.5	1306.4	1305.9	1305.5	1305.1	1304.7
5°	1290.9	1293.2	1295.7	1296.5	1295.7	1294.9	1294.1	1293.2
7.5°	1270.1	1270.7	1271.4	1271.0	1269.7	1268.4	1266.9	1265.6
10°	1249.1	1248.3	1247.5	1246.3	1244.7	1243.2	1241.6	1240.0
12.5°	1225.1	1223.7	1222.3	1220.3	1217.6	1215.0	1212.4	1209.8
15°	1180.4	1175.4	1170.4	1166.5	1164.0	1161.3	1158.7	1156.0
17.5°	1129.7	1123.7	1117.8	1112.6	1108.0	1103.6	1099.0	1094.5
20°	1094.4	1087.8	1081.2	1075.0	1069.3	1063.5	1057.7	1052.0
22.5°	1055.6	1047.1	1038.7	1032.2	1028.0	1023.6	1019.3	1015.0
25°	991.3	980.5	969.7	962.3	958.4	954.5	950.6	946.6
27.5°	930.0	917.4	904.8	895.5	889.2	882.9	876.6	870.4
30°	886.6	873.3	859.8	849.5	842.5	835.4	828.3	821.2
32.5°	843.1	827.8	812.5	801.5	794.9	788.2	781.5	774.8
35°	775.0	758.5	741.9	730.8	725.0	719.2	713.4	707.6
37.5°	708.7	690.5	672.3	659.8	653.2	646.5	639.9	633.3
40°	664.3	645.7	627.0	614.2	607.4	600.6	593.7	586.9
42.5°	619.6	600.2	580.9	567.9	561.3	554.7	548.0	541.4
45°	554.3	535.7	516.9	504.4	498.1	491.9	485.5	479.2
47.5°	490.8	472.3	453.7	441.6	435.9	430.1	424.4	418.7
50°	450.0	431.9	413.8	401.9	396.4	390.8	385.3	379.8
52.5°	411.5	394.0	376.5	365.2	360.1	355.0	349.9	344.8
55°	353.0	337.2	321.5	311.0	306.0	301.0	296.0	291.1
57.5°	299.8	285.3	270.9	261.5	257.3	253.1	248.9	244.7
60°	263.1	249.7	236.2	227.5	223.2	219.0	214.8	210.6
62.5°	231.2	218.5	205.6	198.0	195.5	193.0	190.4	187.9
65°	188.0	179.1	170.1	165.2	164.4	163.7	162.9	162.1
67.5°	151.8	147.7	143.6	141.1	140.3	139.4	138.6	137.8
70°	132.0	129.4	126.7	124.9	123.9	122.8	121.7	120.6
72.5°	114.9	112.6	110.4	109.1	108.3	107.7	107.1	106.5
75°	91.0	89.2	87.3	86.2	86.0	85.7	85.4	85.2
77.5°	68.9	67.9	66.8	66.1	65.6	65.2	64.8	64.4
80°	54.7	53.7	52.6	52.1	52.1	52.1	52.1	52.1
82.5°	41.4	40.7	40.0	39.8	39.8	39.8	39.8	39.8
85°	22.5	22.5	22.5	22.5	22.5	22.5	22.5	22.5
87.5°	9.2	9.1	9.0	9.0	9.0	9.1	9.1	9.1
90°	10.3	10.9	11.4	11.8	11.9	12.1	12.4	12.6
92.5°	11.3	11.6	11.9	12.0	12.2	12.3	12.5	12.6
95°	19.2	19.7	20.2	20.4	20.3	20.2	20.2	20.0
97.5°	25.1	25.5	25.9	26.2	26.3	26.5	26.6	26.8
100°	28.2	29.0	29.9	30.3	30.6	30.8	30.9	31.2
102.5°	29.4	30.5	31.6	32.3	32.5	32.8	33.1	33.4
105°	30.7	31.8	32.9	33.7	34.2	34.5	35.0	35.4
107.5°	37.5	36.3	35.1	34.8	35.1	35.6	35.9	36.4
110°	60.7	50.4	40.0	35.1	35.5	35.9	36.4	36.7



TEST NUMBER: P331714-940

CATALOG NUMBER: SA2XXRDIP-C865D530U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	129.9	92.2	54.5	35.8	36.1	36.5	36.8	37.1
115°	191.4	143.5	95.6	67.9	60.5	53.1	45.6	38.2
117.5°	294.9	283.3	271.7	253.7	229.2	204.7	180.3	155.8
120°	343.6	344.8	346.1	339.7	325.7	311.8	297.8	283.8
122.5°	364.5	365.3	366.0	365.1	362.4	359.6	357.0	354.2
125°	394.7	395.4	396.1	396.6	397.0	397.3	397.6	397.9
127.5°	422.5	423.6	424.6	425.2	425.3	425.3	425.3	425.4
130°	440.1	441.3	442.5	443.0	442.8	442.7	442.6	442.6
132.5°	457.4	458.3	459.3	459.7	459.6	459.5	459.4	459.3
135°	481.9	482.9	483.9	484.4	484.1	483.9	483.8	483.5
137.5°	504.6	505.6	506.7	506.9	506.6	506.2	506.0	505.6
140°	519.3	520.2	521.2	521.4	520.8	520.4	519.9	519.3
142.5°	533.0	533.8	534.7	534.8	534.3	533.8	533.2	532.7
145°	552.0	552.7	553.4	553.5	553.0	552.5	552.0	551.4
147.5°	568.6	569.1	569.6	569.6	569.3	568.8	568.4	567.9
150°	578.7	579.3	580.0	580.1	579.5	579.0	578.5	578.0
152.5°	588.1	588.7	589.3	589.2	588.6	587.9	587.2	586.6
155°	600.7	601.3	601.9	601.7	600.9	600.1	599.3	598.4
157.5°	611.2	611.9	612.6	612.6	611.7	610.9	610.1	609.3
160°	617.3	618.0	618.6	618.6	617.9	617.2	616.4	615.6
162.5°	623.1	623.8	624.6	624.5	623.6	622.7	621.8	620.9
165°	630.2	630.9	631.6	631.6	630.9	630.2	629.5	628.7
167.5°	636.0	636.8	637.5	637.4	636.4	635.5	634.5	633.6
170°	639.0	639.7	640.4	640.3	639.4	638.5	637.6	636.6
172.5°	641.2	641.9	642.7	642.6	641.7	640.7	639.8	638.8
175°	643.6	644.4	645.1	645.0	643.9	642.8	641.9	640.8
177.5°	643.9	644.5	645.1	645.0	644.3	643.5	642.7	642.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1

(END OF REPORT)