

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332634

Luminaire Tested: **SA4XXDIP-C1020D590U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332634
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6965.6 lumens
Efficiency: N/A
Efficacy: 142.7 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332634
CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66				
1	102	97	93	90	96	92	88	85	81	79	77	72	70	68	63	62	60	56				
2	93	85	79	74	87	81	75	71	72	68	64	64	60	58	56	54	51	48				
3	85	75	68	62	80	71	65	59	64	58	54	56	52	49	50	47	44	41				
4	78	67	59	53	73	63	56	51	57	51	46	51	46	42	45	41	38	35				
5	72	60	52	46	67	57	49	44	51	45	40	46	41	37	40	37	34	31				
6	66	54	46	40	62	51	44	38	46	40	35	41	36	33	37	33	30	27				
7	61	49	41	35	58	46	39	34	42	36	31	38	33	29	34	30	26	24				
8	57	45	37	31	54	42	35	30	38	32	28	35	30	26	31	27	24	22				
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20				
10	50	38	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13472	13472	13472	13472
5°	15866	13507	11921	13507
10°	18996	13448	10733	13448
15°	22476	13312	9857	13312
20°	25027	13173	9075	13173
25°	25432	12968	8535	12968
30°	21640	12773	8364	12773
35°	16638	12454	8366	12454
40°	12968	12079	8524	12079
45°	10813	11515	8667	11515
50°	9516	10827	8960	10827
55°	8718	10003	9322	10003
60°	8170	9265	9755	9265
65°	7607	8437	10115	8437
70°	6951	7619	10346	7619
75°	6210	6706	10221	6706
80°	5207	5495	9898	5495
85°	3844	3974	9476	3974



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.6	2.3
10°-20°	501.1	7.2
20°-30°	794.6	11.4
30°-40°	884.3	12.7
40°-50°	805.0	11.6
50°-60°	657.8	9.4
60°-70°	469.6	6.7
70°-80°	258.6	3.7
80°-90°	72.8	1.0
90°-100°	26.1	0.4
100°-110°	166.3	2.4
110°-120°	318.2	4.6
120°-130°	403.9	5.8
130°-140°	432.1	6.2
140°-150°	404.1	5.8
150°-160°	325.9	4.7
160°-170°	210.2	3.0
170°-180°	72.4	1.0
0°-30°	1458.3	20.9
0°-40°	2342.7	33.6
0°-60°	3805.5	54.6
0°-90°	4606.5	66.1
90°-120°	510.6	7.3
90°-150°	1750.6	25.1
90°-180°	2359.0	33.9
0°-180°	6965.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1669	1669	1669	1669	1669	
5°	1958	1667	1471	1667	1958	199
15°	2689	1593	1179	1593	2689	760
25°	2855	1456	958	1456	2855	1259
35°	1688	1264	849	1264	1688	1072
45°	947	1009	759	1009	947	746
55°	619	711	662	711	619	560
65°	398	442	530	442	398	394
75°	199	215	328	215	199	212
85°	42	43	102	43	42	51
90°	17	2	17	2	17	9
95°	16	31	16	31	16	13
105°	163	172	163	172	163	142
115°	323	321	323	321	323	320
125°	454	451	454	451	454	404
135°	563	559	563	559	563	433
145°	648	645	648	645	648	405
155°	706	707	706	707	706	326
165°	742	746	742	746	742	210
175°	758	763	758	763	758	72
180°	763	763	763	763	763	



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1776.1	1775.6	1770.0	1768.9	1765.0	1760.1	1759.0	1750.1	1732.4	1724.1	1721.9
5°	1957.8	1971.6	1953.6	1950.2	1948.1	1925.3	1913.5	1899.7	1867.9	1849.2	1834.7
7.5°	2174.6	2176.2	2168.4	2162.0	2144.4	2124.5	2094.7	2062.9	2025.0	1985.6	1955.8
10°	2317.3	2322.8	2313.8	2312.4	2277.2	2255.0	2210.8	2173.5	2130.6	2082.9	2039.4
12.5°	2467.7	2459.9	2455.4	2425.8	2419.3	2378.9	2327.5	2289.1	2223.0	2168.1	2110.1
15°	2689.2	2674.0	2664.3	2623.5	2603.5	2547.5	2492.8	2450.7	2364.3	2282.0	2219.8
17.5°	2819.1	2834.4	2812.0	2795.2	2743.4	2704.1	2648.3	2559.8	2492.2	2390.0	2311.5
20°	2913.2	2914.5	2902.1	2884.8	2844.0	2794.3	2733.4	2636.6	2555.8	2454.1	2346.3
22.5°	2938.6	2938.9	2933.6	2917.4	2886.6	2846.2	2784.9	2704.1	2606.1	2495.6	2387.8
25°	2855.1	2852.3	2858.6	2876.5	2864.8	2852.3	2817.1	2756.9	2665.7	2548.8	2432.7
27.5°	2544.8	2563.9	2599.0	2643.3	2685.9	2718.4	2727.5	2715.2	2658.6	2562.5	2440.9
30°	2321.4	2344.9	2371.2	2415.4	2501.1	2550.2	2604.2	2644.9	2622.1	2545.4	2432.0
32.5°	2075.9	2081.7	2120.7	2171.0	2249.5	2343.9	2429.4	2512.2	2539.7	2499.5	2404.9
35°	1688.2	1697.8	1740.0	1789.8	1885.9	2001.3	2129.9	2244.7	2339.4	2377.4	2329.0
37.5°	1377.6	1405.4	1435.2	1488.7	1573.3	1677.2	1810.8	1959.3	2100.5	2195.0	2211.1
40°	1230.5	1247.8	1269.2	1310.0	1381.9	1484.2	1599.0	1769.1	1919.1	2054.6	2098.8
42.5°	1114.4	1124.5	1137.6	1174.5	1229.3	1331.0	1435.8	1585.4	1736.0	1898.0	1972.2
45°	947.1	957.5	979.6	1001.0	1042.5	1113.0	1210.5	1333.5	1484.9	1641.2	1778.0
47.5°	826.2	832.9	846.0	869.0	904.2	950.7	1030.0	1132.8	1273.1	1424.8	1570.6
50°	757.7	763.2	773.6	794.3	821.3	862.7	927.7	1023.8	1133.7	1286.5	1429.6
52.5°	703.5	705.7	713.3	727.4	748.8	783.7	837.0	916.5	1018.7	1154.9	1297.4
55°	619.4	622.2	629.1	639.5	658.1	680.2	721.0	780.5	869.7	987.9	1111.6
57.5°	550.3	552.2	558.0	562.0	577.4	595.4	626.7	669.2	736.8	837.0	947.5
60°	506.0	504.7	511.6	515.0	525.4	540.6	564.8	605.6	664.3	745.2	846.8
62.5°	462.9	461.0	466.8	471.3	477.3	490.3	510.0	542.0	589.7	662.8	750.6
65°	398.2	395.4	398.9	404.4	409.9	416.9	431.4	459.7	497.7	550.3	617.3
67.5°	333.2	336.1	336.7	339.4	342.6	352.0	362.0	382.0	408.8	450.9	507.7
70°	294.5	295.2	298.0	298.0	300.0	308.3	316.6	328.4	354.6	393.4	439.7
72.5°	255.8	258.7	257.6	259.8	261.3	266.8	272.9	284.1	306.5	335.3	374.4
75°	199.1	201.2	201.2	201.9	203.9	206.0	210.8	219.1	235.0	256.5	283.4
77.5°	145.2	145.5	146.4	148.9	148.9	152.2	155.8	162.5	170.3	185.0	201.4
80°	112.0	113.4	112.7	114.1	114.1	116.8	118.2	126.5	130.0	139.6	152.8
82.5°	82.1	83.5	83.4	85.3	86.4	87.0	88.9	92.2	95.7	104.2	109.6
85°	41.5	42.9	41.5	42.9	44.9	45.6	47.7	48.4	51.2	53.2	58.1
87.5°	15.6	17.2	17.1	17.6	18.7	19.2	19.6	18.9	20.9	21.3	23.3
90°	17.1	16.9	16.6	16.4	16.1	15.6	14.8	14.1	13.3	12.5	11.5
92.5°	15.7	15.7	15.6	15.6	15.5	15.1	14.4	13.6	12.9	12.1	11.1
95°	16.5	16.4	16.3	16.2	16.0	15.6	14.8	14.1	13.3	12.5	12.4
97.5°	16.0	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.1	15.1	29.2
100°	16.0	15.8	15.7	15.6	15.5	16.5	18.6	20.8	22.9	25.1	42.6
102.5°	16.4	16.4	16.4	16.4	16.3	27.9	51.2	74.4	97.7	120.9	123.2
105°	162.6	167.1	171.7	176.3	180.8	182.5	181.4	180.3	179.1	178.0	177.3
107.5°	226.6	226.1	225.6	225.1	224.6	224.1	223.6	223.0	222.5	221.9	221.0
110°	254.4	254.0	253.6	253.3	252.9	252.6	252.3	252.1	251.8	251.6	250.8



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	282.2	281.8	281.3	280.8	280.3	280.1	280.2	280.2	280.3	280.3	280.0
115°	322.9	322.9	322.9	322.9	322.9	322.7	322.5	322.2	322.0	321.7	321.8
117.5°	364.2	364.2	364.3	364.3	364.4	364.4	364.5	364.5	364.6	364.6	364.3
120°	390.2	390.4	390.7	390.9	391.2	391.2	390.9	390.7	390.4	390.2	390.3
122.5°	415.7	416.0	416.2	416.5	416.7	416.8	416.6	416.5	416.3	416.2	416.0
125°	454.1	453.9	453.8	453.7	453.6	453.3	452.9	452.5	452.2	451.8	452.0
127.5°	487.7	487.8	487.9	488.0	488.1	488.2	488.3	488.4	488.4	488.5	487.9
130°	510.5	510.5	510.5	510.5	510.5	510.5	510.3	510.2	510.1	510.0	509.6
132.5°	531.5	531.6	531.7	531.8	531.9	531.9	531.8	531.7	531.5	531.4	530.9
135°	563.0	562.8	562.5	562.2	562.0	561.7	561.5	561.2	561.0	560.7	560.2
137.5°	589.9	590.0	590.1	590.2	590.2	590.1	589.9	589.6	589.3	589.0	588.5
140°	608.6	608.5	608.4	608.3	608.1	607.9	607.5	607.1	606.7	606.4	606.1
142.5°	624.2	624.1	624.1	624.1	624.1	623.9	623.6	623.3	623.1	622.8	622.6
145°	648.0	647.8	647.5	647.2	647.0	646.8	646.7	646.5	646.4	646.3	646.3
147.5°	667.7	667.6	667.5	667.4	667.2	667.1	667.0	666.9	666.8	666.7	666.8
150°	680.5	680.4	680.3	680.1	680.0	679.9	679.9	679.9	679.9	679.9	680.1
152.5°	691.5	691.5	691.6	691.7	691.8	691.7	691.5	691.3	691.1	690.9	691.1
155°	706.2	706.6	706.9	707.3	707.7	707.6	707.1	706.6	706.1	705.6	706.0
157.5°	718.5	719.2	719.8	720.5	721.1	721.1	720.5	719.8	719.2	718.5	718.9
160°	726.7	727.5	728.2	729.0	729.8	729.8	729.0	728.2	727.5	726.7	726.8
162.5°	733.1	734.0	734.8	735.7	736.6	736.6	735.8	735.1	734.3	733.6	733.7
165°	742.1	743.3	744.4	745.5	746.7	746.8	745.7	744.7	743.7	742.7	742.7
167.5°	748.9	750.1	751.4	752.7	753.9	754.0	752.9	751.8	750.7	749.5	749.6
170°	753.0	754.2	755.5	756.8	758.0	758.2	757.1	756.1	755.1	754.1	754.0
172.5°	755.2	756.6	758.0	759.4	760.7	760.9	759.9	758.9	757.9	756.8	756.7
175°	758.1	759.6	761.1	762.7	764.2	764.4	763.2	762.1	760.9	759.8	759.7
177.5°	759.9	761.1	762.4	763.6	764.8	765.0	764.2	763.4	762.6	761.7	761.5
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7

TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1722.5	1714.7	1709.2	1704.8	1692.6	1685.4	1679.9	1672.1	1663.3	1653.9	1642.3
5°	1820.2	1796.7	1779.4	1753.2	1728.3	1707.5	1686.1	1666.7	1643.2	1617.7	1599.0
7.5°	1922.9	1888.0	1843.2	1804.3	1760.6	1722.6	1688.6	1653.7	1617.5	1582.4	1550.2
10°	1988.2	1943.3	1893.5	1834.7	1779.4	1730.3	1684.7	1640.5	1597.6	1554.7	1518.1
12.5°	2058.4	2002.4	1928.9	1860.2	1798.2	1732.6	1677.5	1623.3	1571.6	1526.5	1483.8
15°	2152.7	2071.8	1986.8	1894.9	1813.3	1736.6	1661.2	1592.8	1534.7	1475.2	1433.8
17.5°	2210.7	2110.6	2013.4	1917.3	1818.5	1721.8	1640.5	1561.5	1488.8	1429.8	1377.5
20°	2248.8	2149.3	2028.3	1932.2	1814.7	1715.1	1621.1	1533.3	1457.3	1394.4	1340.4
22.5°	2282.0	2167.0	2046.0	1919.5	1802.5	1696.9	1594.0	1505.7	1428.0	1361.7	1310.0
25°	2300.0	2167.9	2036.6	1910.8	1778.0	1652.9	1559.6	1455.9	1372.9	1303.1	1247.8
27.5°	2301.9	2160.7	2012.1	1872.3	1735.3	1618.8	1501.0	1408.3	1322.2	1248.4	1195.3
30°	2295.8	2148.6	1988.9	1837.5	1699.9	1573.4	1471.1	1370.2	1282.4	1209.1	1153.8
32.5°	2276.5	2123.1	1959.0	1798.8	1656.2	1532.5	1426.9	1330.9	1245.3	1173.1	1115.1
35°	2220.5	2069.1	1894.2	1727.6	1581.7	1456.6	1361.2	1263.7	1178.0	1109.5	1053.6
37.5°	2133.0	1996.1	1818.3	1645.9	1502.6	1376.9	1282.4	1194.3	1117.0	1047.5	990.1
40°	2056.6	1936.3	1758.0	1590.0	1435.2	1315.6	1227.1	1146.2	1069.5	1003.8	949.2
42.5°	1968.7	1863.9	1699.4	1521.4	1372.1	1252.0	1165.7	1093.1	1020.8	960.1	905.5
45°	1811.9	1742.8	1587.9	1423.4	1267.9	1154.5	1072.2	1008.6	947.8	888.3	842.7
47.5°	1631.6	1597.3	1467.0	1310.7	1163.1	1051.3	980.0	921.2	867.9	817.5	777.3
50°	1510.5	1493.9	1381.2	1230.5	1089.5	984.4	912.5	862.1	816.4	772.2	734.2
52.5°	1391.0	1390.5	1288.9	1150.9	1020.4	919.2	847.8	800.7	761.1	725.2	691.0
55°	1208.4	1227.8	1148.3	1025.2	908.4	817.1	752.8	710.7	683.0	653.3	627.7
57.5°	1040.7	1072.8	1007.2	898.8	801.4	717.3	661.3	629.6	600.2	582.2	563.6
60°	931.2	961.6	910.5	819.2	727.3	655.4	602.1	573.8	548.2	535.8	522.6
62.5°	833.9	861.0	823.1	738.5	658.7	589.5	544.6	517.4	500.1	486.5	477.8
65°	694.8	717.6	685.1	623.6	555.1	499.8	463.2	441.7	425.2	419.6	409.9
67.5°	561.6	582.4	564.8	512.5	457.6	415.8	387.1	366.5	356.7	351.9	345.0
70°	482.5	503.3	484.6	439.0	396.8	361.6	334.6	322.8	312.5	310.4	300.7
72.5°	415.6	429.7	411.1	375.4	339.3	309.6	288.7	276.4	271.0	267.3	262.0
75°	311.8	324.2	311.8	284.1	258.5	237.8	219.8	215.0	208.8	206.7	203.2
77.5°	220.7	231.4	221.9	204.6	185.5	169.5	159.8	153.6	152.2	148.6	150.3
80°	168.7	175.6	166.6	154.9	139.6	128.6	121.7	118.2	114.1	112.7	115.4
82.5°	121.1	124.2	119.6	111.7	100.4	93.2	88.5	84.5	83.6	83.9	83.9
85°	62.9	62.2	61.5	54.6	51.2	46.3	43.6	42.9	42.2	43.6	44.9
87.5°	23.1	23.5	22.7	20.3	18.3	16.4	15.6	14.7	15.6	16.4	17.2
90°	10.5	9.5	8.5	7.3	5.9	4.5	3.1	1.7	3.1	4.5	5.9
92.5°	10.1	9.1	8.0	7.5	7.4	7.3	7.3	7.2	7.3	7.3	7.4
95°	12.3	12.2	12.0	14.1	18.4	22.8	27.1	31.4	27.1	22.8	18.4
97.5°	43.4	57.5	71.6	77.4	74.7	72.0	69.3	66.6	69.3	72.0	74.7
100°	60.1	77.6	95.1	102.7	100.4	98.1	95.8	93.5	95.8	98.1	100.4
102.5°	125.5	127.8	130.1	130.4	128.7	127.0	125.3	123.7	125.3	127.0	128.7
105°	176.7	176.1	175.4	174.7	174.0	173.2	172.5	171.7	172.5	173.2	174.0
107.5°	220.2	219.3	218.4	217.8	217.4	217.1	216.7	216.3	216.7	217.1	217.4
110°	250.0	249.3	248.5	247.9	247.6	247.2	246.8	246.4	246.8	247.2	247.6



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	279.6	279.2	278.9	278.4	277.7	277.0	276.3	275.6	276.3	277.0	277.7
115°	322.0	322.1	322.2	322.1	321.7	321.3	321.0	320.6	321.0	321.3	321.7
117.5°	364.1	363.8	363.5	363.1	362.6	362.1	361.6	361.1	361.6	362.1	362.6
120°	390.4	390.6	390.7	390.5	390.0	389.5	389.0	388.5	389.0	389.5	390.0
122.5°	415.8	415.7	415.5	415.2	414.9	414.6	414.3	414.0	414.3	414.6	414.9
125°	452.3	452.5	452.8	452.7	452.2	451.7	451.1	450.6	451.1	451.7	452.2
127.5°	487.3	486.8	486.2	485.8	485.7	485.6	485.4	485.3	485.4	485.6	485.7
130°	509.2	508.8	508.4	508.2	508.1	507.9	507.8	507.7	507.8	507.9	508.1
132.5°	530.4	530.0	529.5	529.1	528.9	528.7	528.4	528.2	528.4	528.7	528.9
135°	559.7	559.2	558.7	558.5	558.6	558.8	558.9	559.0	558.9	558.8	558.6
137.5°	587.9	587.3	586.8	586.5	586.4	586.4	586.3	586.3	586.3	586.4	586.4
140°	605.9	605.6	605.3	605.1	604.8	604.6	604.3	604.1	604.3	604.6	604.8
142.5°	622.5	622.3	622.2	621.9	621.4	621.0	620.5	620.1	620.5	621.0	621.4
145°	646.3	646.3	646.3	646.1	645.7	645.3	645.0	644.6	645.0	645.3	645.7
147.5°	667.0	667.1	667.2	666.9	666.2	665.5	664.8	664.1	664.8	665.5	666.2
150°	680.2	680.3	680.5	680.3	679.8	679.3	678.7	678.2	678.7	679.3	679.8
152.5°	691.4	691.6	691.8	691.7	691.3	690.9	690.5	690.1	690.5	690.9	691.3
155°	706.4	706.8	707.1	707.3	707.1	707.0	706.9	706.8	706.9	707.0	707.1
157.5°	719.4	719.8	720.2	720.5	720.6	720.6	720.7	720.8	720.7	720.6	720.6
160°	727.0	727.1	727.2	727.5	727.9	728.2	728.6	729.0	728.6	728.2	727.9
162.5°	733.8	733.9	734.1	734.4	734.9	735.3	735.8	736.3	735.8	735.3	734.9
165°	742.7	742.7	742.7	743.0	743.6	744.3	744.9	745.5	744.9	744.3	743.6
167.5°	749.7	749.8	749.8	750.2	750.9	751.5	752.2	752.8	752.2	751.5	750.9
170°	753.8	753.7	753.6	753.9	754.7	755.4	756.2	757.0	756.2	755.4	754.7
172.5°	756.6	756.5	756.3	756.7	757.4	758.2	758.9	759.7	758.9	758.2	757.4
175°	759.6	759.4	759.3	759.6	760.4	761.1	761.9	762.7	761.9	761.1	760.4
177.5°	761.3	761.1	760.9	761.2	761.9	762.6	763.3	764.0	763.3	762.6	761.9
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1636.7	1631.8	1624.6	1614.6	1606.3	1597.5	1595.3	1591.9	1598.6	1593.0	1591.4
5°	1583.1	1568.6	1549.9	1528.5	1516.0	1498.1	1494.6	1487.7	1480.8	1480.1	1473.2
7.5°	1526.3	1505.0	1480.5	1458.7	1438.5	1418.8	1406.0	1403.2	1393.0	1387.0	1380.1
10°	1489.8	1463.5	1435.2	1414.4	1390.9	1370.2	1355.7	1347.4	1340.4	1332.8	1325.9
12.5°	1446.6	1418.7	1395.3	1372.9	1345.0	1329.2	1305.3	1290.9	1289.6	1289.7	1271.7
15°	1396.4	1368.8	1332.8	1301.0	1285.8	1255.4	1242.3	1225.7	1215.3	1204.9	1196.7
17.5°	1339.1	1304.6	1276.6	1240.1	1211.0	1186.8	1169.6	1159.6	1144.0	1129.3	1118.7
20°	1303.1	1266.5	1236.7	1198.0	1166.2	1136.5	1122.0	1108.2	1096.4	1084.0	1072.2
22.5°	1266.6	1228.3	1191.9	1154.3	1124.8	1093.4	1079.4	1060.6	1049.4	1042.5	1030.7
25°	1209.1	1167.6	1126.1	1090.2	1059.8	1032.1	1013.5	998.9	986.5	981.0	973.4
27.5°	1146.6	1105.4	1065.3	1024.5	990.0	969.9	955.0	944.0	936.9	929.5	926.1
30°	1106.8	1063.9	1021.1	983.0	951.2	931.2	917.4	909.8	904.2	900.8	897.3
32.5°	1066.4	1024.1	979.0	944.3	915.8	898.0	887.5	879.9	877.1	875.9	874.6
35°	1001.7	958.8	917.4	886.3	859.3	852.4	843.4	839.2	837.9	842.7	844.8
37.5°	939.1	899.3	861.1	830.9	813.3	803.2	800.1	800.3	805.2	809.5	814.5
40°	898.7	860.0	824.0	797.8	781.2	775.0	773.6	777.0	782.6	787.4	792.9
42.5°	859.4	821.3	788.6	764.0	752.4	746.7	747.6	751.0	758.8	764.7	773.0
45°	798.5	766.7	734.9	714.8	705.1	706.5	706.5	712.7	720.3	729.3	738.3
47.5°	741.1	709.0	682.9	666.0	661.0	659.8	663.7	671.8	682.7	693.8	706.4
50°	702.4	671.9	649.1	633.9	628.4	630.5	636.0	643.6	656.7	670.6	683.7
52.5°	663.1	635.4	614.3	600.2	596.3	600.1	605.6	617.6	629.1	644.0	659.9
55°	602.1	578.6	562.0	551.7	550.3	552.4	558.6	571.7	588.3	607.0	622.2
57.5°	541.4	521.8	506.6	499.4	500.1	502.0	512.3	527.9	545.6	565.5	585.1
60°	500.5	482.5	470.1	464.6	465.2	469.4	481.8	496.4	518.5	537.8	558.6
62.5°	461.8	446.0	434.1	429.2	428.2	437.3	449.2	464.3	486.4	508.0	530.4
65°	399.6	387.1	377.5	374.7	376.8	383.7	398.9	418.9	437.6	460.4	483.9
67.5°	338.7	328.5	321.9	323.1	325.6	335.8	348.6	365.8	387.0	410.6	433.9
70°	300.0	290.3	284.8	285.5	289.7	302.1	313.2	330.4	353.3	377.5	396.8
72.5°	260.2	253.8	248.9	251.8	255.9	264.5	278.3	295.6	315.7	338.2	358.6
75°	199.8	199.8	197.0	199.1	205.3	213.6	224.0	242.0	262.0	280.0	296.6
77.5°	148.2	146.7	148.5	151.0	154.6	164.4	176.3	189.1	204.2	222.2	235.9
80°	113.4	114.1	117.5	121.7	123.1	130.7	143.1	154.9	166.6	181.8	194.9
82.5°	85.2	85.9	87.7	92.9	94.3	102.5	110.5	122.2	132.9	143.1	154.0
85°	46.3	46.3	49.8	51.8	55.3	60.8	65.7	72.6	82.3	89.2	99.5
87.5°	19.2	19.4	21.8	23.1	25.0	27.9	29.2	35.4	37.8	40.7	45.8
90°	7.3	8.5	9.5	10.5	11.5	12.5	13.3	14.1	14.8	15.6	16.1
92.5°	7.5	8.0	9.1	10.1	11.1	12.1	12.9	13.6	14.4	15.1	15.5
95°	14.1	12.0	12.2	12.3	12.4	12.5	13.3	14.1	14.8	15.6	16.0
97.5°	77.4	71.6	57.5	43.4	29.2	15.1	15.1	15.2	15.3	15.4	15.5
100°	102.7	95.1	77.6	60.1	42.6	25.1	22.9	20.8	18.6	16.5	15.5
102.5°	130.4	130.1	127.8	125.5	123.2	120.9	97.7	74.4	51.2	27.9	16.3
105°	174.7	175.4	176.1	176.7	177.3	178.0	179.1	180.3	181.4	182.5	180.8
107.5°	217.8	218.4	219.3	220.2	221.0	221.9	222.5	223.0	223.6	224.1	224.6
110°	247.9	248.5	249.3	250.0	250.8	251.6	251.8	252.1	252.3	252.6	252.9



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	278.4	278.9	279.2	279.6	280.0	280.3	280.3	280.2	280.2	280.1	280.3
115°	322.1	322.2	322.1	322.0	321.8	321.7	322.0	322.2	322.5	322.7	322.9
117.5°	363.1	363.5	363.8	364.1	364.3	364.6	364.6	364.5	364.5	364.4	364.4
120°	390.5	390.7	390.6	390.4	390.3	390.2	390.4	390.7	390.9	391.2	391.2
122.5°	415.2	415.5	415.7	415.8	416.0	416.2	416.3	416.5	416.6	416.8	416.7
125°	452.7	452.8	452.5	452.3	452.0	451.8	452.2	452.5	452.9	453.3	453.6
127.5°	485.8	486.2	486.8	487.3	487.9	488.5	488.4	488.4	488.3	488.2	488.1
130°	508.2	508.4	508.8	509.2	509.6	510.0	510.1	510.2	510.3	510.5	510.5
132.5°	529.1	529.5	530.0	530.4	530.9	531.4	531.5	531.7	531.8	531.9	531.9
135°	558.5	558.7	559.2	559.7	560.2	560.7	561.0	561.2	561.5	561.7	562.0
137.5°	586.5	586.8	587.3	587.9	588.5	589.0	589.3	589.6	589.9	590.1	590.2
140°	605.1	605.3	605.6	605.9	606.1	606.4	606.7	607.1	607.5	607.9	608.1
142.5°	621.9	622.2	622.3	622.5	622.6	622.8	623.1	623.3	623.6	623.9	624.1
145°	646.1	646.3	646.3	646.3	646.3	646.3	646.4	646.5	646.7	646.8	647.0
147.5°	666.9	667.2	667.1	667.0	666.8	666.7	666.8	666.9	667.0	667.1	667.2
150°	680.3	680.5	680.3	680.2	680.1	679.9	679.9	679.9	679.9	679.9	680.0
152.5°	691.7	691.8	691.6	691.4	691.1	690.9	691.1	691.3	691.5	691.7	691.8
155°	707.3	707.1	706.8	706.4	706.0	705.6	706.1	706.6	707.1	707.6	707.7
157.5°	720.5	720.2	719.8	719.4	718.9	718.5	719.2	719.8	720.5	721.1	721.1
160°	727.5	727.2	727.1	727.0	726.8	726.7	727.5	728.2	729.0	729.8	729.8
162.5°	734.4	734.1	733.9	733.8	733.7	733.6	734.3	735.1	735.8	736.6	736.6
165°	743.0	742.7	742.7	742.7	742.7	742.7	743.7	744.7	745.7	746.8	746.7
167.5°	750.2	749.8	749.8	749.7	749.6	749.5	750.7	751.8	752.9	754.0	753.9
170°	753.9	753.6	753.7	753.8	754.0	754.1	755.1	756.1	757.1	758.2	758.0
172.5°	756.7	756.3	756.5	756.6	756.7	756.8	757.9	758.9	759.9	760.9	760.7
175°	759.6	759.3	759.4	759.6	759.7	759.8	760.9	762.1	763.2	764.4	764.2
177.5°	761.2	760.9	761.1	761.3	761.5	761.7	762.6	763.4	764.2	765.0	764.8
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1590.3	1589.2	1585.3	1584.8	1585.3	1589.2	1590.3	1591.4	1593.0	1598.6	1591.9
5°	1469.0	1465.6	1463.5	1471.1	1463.5	1465.6	1469.0	1473.2	1480.1	1480.8	1487.7
7.5°	1377.6	1374.9	1368.8	1366.9	1368.8	1374.9	1377.6	1380.1	1387.0	1393.0	1403.2
10°	1319.0	1316.2	1310.7	1309.3	1310.7	1316.2	1319.0	1325.9	1332.8	1340.4	1347.4
12.5°	1262.6	1257.1	1256.0	1257.3	1256.0	1257.1	1262.6	1271.7	1289.7	1289.6	1290.9
15°	1187.7	1184.9	1177.3	1179.4	1177.3	1184.9	1187.7	1196.7	1204.9	1215.3	1225.7
17.5°	1113.8	1110.5	1101.3	1109.4	1101.3	1110.5	1113.8	1118.7	1129.3	1144.0	1159.6
20°	1067.4	1061.8	1057.0	1056.3	1057.0	1061.8	1067.4	1072.2	1084.0	1096.4	1108.2
22.5°	1023.1	1018.2	1017.7	1013.2	1017.7	1018.2	1023.1	1030.7	1042.5	1049.4	1060.6
25°	967.8	963.0	961.6	958.2	961.6	963.0	967.8	973.4	981.0	986.5	998.9
27.5°	925.4	923.0	920.5	921.6	920.5	923.0	925.4	926.1	929.5	936.9	944.0
30°	899.4	898.7	897.3	897.3	897.3	898.7	899.4	897.3	900.8	904.2	909.8
32.5°	877.8	877.7	878.5	878.5	878.5	877.7	877.8	874.6	875.9	877.1	879.9
35°	847.5	849.6	851.0	848.9	851.0	849.6	847.5	844.8	842.7	837.9	839.2
37.5°	820.2	822.2	824.2	826.5	824.2	822.2	820.2	814.5	809.5	805.2	800.3
40°	799.1	804.0	805.4	808.8	805.4	804.0	799.1	792.9	787.4	782.6	777.0
42.5°	779.2	784.6	788.2	788.9	788.2	784.6	779.2	773.0	764.7	758.8	751.0
45°	748.7	754.2	759.1	759.1	759.1	754.2	748.7	738.3	729.3	720.3	712.7
47.5°	717.0	725.0	729.9	731.1	729.9	725.0	717.0	706.4	693.8	682.7	671.8
50°	695.5	705.1	710.0	713.4	710.0	705.1	695.5	683.7	670.6	656.7	643.6
52.5°	674.4	684.1	690.6	692.4	690.6	684.1	674.4	659.9	644.0	629.1	617.6
55°	638.1	651.9	659.5	662.3	659.5	651.9	638.1	622.2	607.0	588.3	571.7
57.5°	603.8	616.5	625.4	627.4	625.4	616.5	603.8	585.1	565.5	545.6	527.9
60°	577.2	591.1	602.1	604.2	602.1	591.1	577.2	558.6	537.8	518.5	496.4
62.5°	550.1	564.5	574.5	579.9	574.5	564.5	550.1	530.4	508.0	486.4	464.3
65°	503.3	517.8	527.5	529.5	527.5	517.8	503.3	483.9	460.4	437.6	418.9
67.5°	452.1	466.6	473.0	477.0	473.0	466.6	452.1	433.9	410.6	387.0	365.8
70°	416.2	427.9	434.8	438.3	434.8	427.9	416.2	396.8	377.5	353.3	330.4
72.5°	375.2	387.5	395.6	396.3	395.6	387.5	375.2	358.6	338.2	315.7	295.6
75°	312.5	323.5	327.7	327.7	327.7	323.5	312.5	296.6	280.0	262.0	242.0
77.5°	247.3	253.0	258.3	259.4	258.3	253.0	247.3	235.9	222.2	204.2	189.1
80°	205.3	208.8	212.9	212.9	212.9	208.8	205.3	194.9	181.8	166.6	154.9
82.5°	162.2	165.1	169.2	168.7	169.2	165.1	162.2	154.0	143.1	132.9	122.2
85°	98.2	104.4	103.7	102.3	103.7	104.4	98.2	99.5	89.2	82.3	72.6
87.5°	47.5	48.1	49.8	51.0	49.8	48.1	47.5	45.8	40.7	37.8	35.4
90°	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	15.6	14.8	14.1
92.5°	15.6	15.6	15.7	15.7	15.7	15.6	15.6	15.5	15.1	14.4	13.6
95°	16.2	16.3	16.4	16.5	16.4	16.3	16.2	16.0	15.6	14.8	14.1
97.5°	15.6	15.7	15.8	16.0	15.8	15.7	15.6	15.5	15.4	15.3	15.2
100°	15.6	15.7	15.8	16.0	15.8	15.7	15.6	15.5	16.5	18.6	20.8
102.5°	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.3	27.9	51.2	74.4
105°	176.3	171.7	167.1	162.6	167.1	171.7	176.3	180.8	182.5	181.4	180.3
107.5°	225.1	225.6	226.1	226.6	226.1	225.6	225.1	224.6	224.1	223.6	223.0
110°	253.3	253.6	254.0	254.4	254.0	253.6	253.3	252.9	252.6	252.3	252.1



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	280.8	281.3	281.8	282.2	281.8	281.3	280.8	280.3	280.1	280.2	280.2
115°	322.9	322.9	322.9	322.9	322.9	322.9	322.9	322.9	322.7	322.5	322.2
117.5°	364.3	364.3	364.2	364.2	364.2	364.3	364.3	364.4	364.4	364.5	364.5
120°	390.9	390.7	390.4	390.2	390.4	390.7	390.9	391.2	391.2	390.9	390.7
122.5°	416.5	416.2	416.0	415.7	416.0	416.2	416.5	416.7	416.8	416.6	416.5
125°	453.7	453.8	453.9	454.1	453.9	453.8	453.7	453.6	453.3	452.9	452.5
127.5°	488.0	487.9	487.8	487.7	487.8	487.9	488.0	488.1	488.2	488.3	488.4
130°	510.5	510.5	510.5	510.5	510.5	510.5	510.5	510.5	510.5	510.3	510.2
132.5°	531.8	531.7	531.6	531.5	531.6	531.7	531.8	531.9	531.9	531.8	531.7
135°	562.2	562.5	562.8	563.0	562.8	562.5	562.2	562.0	561.7	561.5	561.2
137.5°	590.2	590.1	590.0	589.9	590.0	590.1	590.2	590.2	590.1	589.9	589.6
140°	608.3	608.4	608.5	608.6	608.5	608.4	608.3	608.1	607.9	607.5	607.1
142.5°	624.1	624.1	624.1	624.2	624.1	624.1	624.1	624.1	623.9	623.6	623.3
145°	647.2	647.5	647.8	648.0	647.8	647.5	647.2	647.0	646.8	646.7	646.5
147.5°	667.4	667.5	667.6	667.7	667.6	667.5	667.4	667.2	667.1	667.0	666.9
150°	680.1	680.3	680.4	680.5	680.4	680.3	680.1	680.0	679.9	679.9	679.9
152.5°	691.7	691.6	691.5	691.5	691.5	691.6	691.7	691.8	691.7	691.5	691.3
155°	707.3	706.9	706.6	706.2	706.6	706.9	707.3	707.7	707.6	707.1	706.6
157.5°	720.5	719.8	719.2	718.5	719.2	719.8	720.5	721.1	721.1	720.5	719.8
160°	729.0	728.2	727.5	726.7	727.5	728.2	729.0	729.8	729.8	729.0	728.2
162.5°	735.7	734.8	734.0	733.1	734.0	734.8	735.7	736.6	736.6	735.8	735.1
165°	745.5	744.4	743.3	742.1	743.3	744.4	745.5	746.7	746.8	745.7	744.7
167.5°	752.7	751.4	750.1	748.9	750.1	751.4	752.7	753.9	754.0	752.9	751.8
170°	756.8	755.5	754.2	753.0	754.2	755.5	756.8	758.0	758.2	757.1	756.1
172.5°	759.4	758.0	756.6	755.2	756.6	758.0	759.4	760.7	760.9	759.9	758.9
175°	762.7	761.1	759.6	758.1	759.6	761.1	762.7	764.2	764.4	763.2	762.1
177.5°	763.6	762.4	761.1	759.9	761.1	762.4	763.6	764.8	765.0	764.2	763.4
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1595.3	1597.5	1606.3	1614.6	1624.6	1631.8	1636.7	1642.3	1653.9	1663.3	1672.1
5°	1494.6	1498.1	1516.0	1528.5	1549.9	1568.6	1583.1	1599.0	1617.7	1643.2	1666.7
7.5°	1406.0	1418.8	1438.5	1458.7	1480.5	1505.0	1526.3	1550.2	1582.4	1617.5	1653.7
10°	1355.7	1370.2	1390.9	1414.4	1435.2	1463.5	1489.8	1518.1	1554.7	1597.6	1640.5
12.5°	1305.3	1329.2	1345.0	1372.9	1395.3	1418.7	1446.6	1483.8	1526.5	1571.6	1623.3
15°	1242.3	1255.4	1285.8	1301.0	1332.8	1368.8	1396.4	1433.8	1475.2	1534.7	1592.8
17.5°	1169.6	1186.8	1211.0	1240.1	1276.6	1304.6	1339.1	1377.5	1429.8	1488.8	1561.5
20°	1122.0	1136.5	1166.2	1198.0	1236.7	1266.5	1303.1	1340.4	1394.4	1457.3	1533.3
22.5°	1079.4	1093.4	1124.8	1154.3	1191.9	1228.3	1266.6	1310.0	1361.7	1428.0	1505.7
25°	1013.5	1032.1	1059.8	1090.2	1126.1	1167.6	1209.1	1247.8	1303.1	1372.9	1455.9
27.5°	955.0	969.9	990.0	1024.5	1065.3	1105.4	1146.6	1195.3	1248.4	1322.2	1408.3
30°	917.4	931.2	951.2	983.0	1021.1	1063.9	1106.8	1153.8	1209.1	1282.4	1370.2
32.5°	887.5	898.0	915.8	944.3	979.0	1024.1	1066.4	1115.1	1173.1	1245.3	1330.9
35°	843.4	852.4	859.3	886.3	917.4	958.8	1001.7	1053.6	1109.5	1178.0	1263.7
37.5°	800.1	803.2	813.3	830.9	861.1	899.3	939.1	990.1	1047.5	1117.0	1194.3
40°	773.6	775.0	781.2	797.8	824.0	860.0	898.7	949.2	1003.8	1069.5	1146.2
42.5°	747.6	746.7	752.4	764.0	788.6	821.3	859.4	905.5	960.1	1020.8	1093.1
45°	706.5	706.5	705.1	714.8	734.9	766.7	798.5	842.7	888.3	947.8	1008.6
47.5°	663.7	659.8	661.0	666.0	682.9	709.0	741.1	777.3	817.5	867.9	921.2
50°	636.0	630.5	628.4	633.9	649.1	671.9	702.4	734.2	772.2	816.4	862.1
52.5°	605.6	600.1	596.3	600.2	614.3	635.4	663.1	691.0	725.2	761.1	800.7
55°	558.6	552.4	550.3	551.7	562.0	578.6	602.1	627.7	653.3	683.0	710.7
57.5°	512.3	502.0	500.1	499.4	506.6	521.8	541.4	563.6	582.2	600.2	629.6
60°	481.8	469.4	465.2	464.6	470.1	482.5	500.5	522.6	535.8	548.2	573.8
62.5°	449.2	437.3	428.2	429.2	434.1	446.0	461.8	477.8	486.5	500.1	517.4
65°	398.9	383.7	376.8	374.7	377.5	387.1	399.6	409.9	419.6	425.2	441.7
67.5°	348.6	335.8	325.6	323.1	321.9	328.5	338.7	345.0	351.9	356.7	366.5
70°	313.2	302.1	289.7	285.5	284.8	290.3	300.0	300.7	310.4	312.5	322.8
72.5°	278.3	264.5	255.9	251.8	248.9	253.8	260.2	262.0	267.3	271.0	276.4
75°	224.0	213.6	205.3	199.1	197.0	199.8	199.8	203.2	206.7	208.8	215.0
77.5°	176.3	164.4	154.6	151.0	148.5	146.7	148.2	150.3	148.6	152.2	153.6
80°	143.1	130.7	123.1	121.7	117.5	114.1	113.4	115.4	112.7	114.1	118.2
82.5°	110.5	102.5	94.3	92.9	87.7	85.9	85.2	83.9	83.9	83.6	84.5
85°	65.7	60.8	55.3	51.8	49.8	46.3	46.3	44.9	43.6	42.2	42.9
87.5°	29.2	27.9	25.0	23.1	21.8	19.4	19.2	17.2	16.4	15.6	14.7
90°	13.3	12.5	11.5	10.5	9.5	8.5	7.3	5.9	4.5	3.1	1.7
92.5°	12.9	12.1	11.1	10.1	9.1	8.0	7.5	7.4	7.3	7.3	7.2
95°	13.3	12.5	12.4	12.3	12.2	12.0	14.1	18.4	22.8	27.1	31.4
97.5°	15.1	15.1	29.2	43.4	57.5	71.6	77.4	74.7	72.0	69.3	66.6
100°	22.9	25.1	42.6	60.1	77.6	95.1	102.7	100.4	98.1	95.8	93.5
102.5°	97.7	120.9	123.2	125.5	127.8	130.1	130.4	128.7	127.0	125.3	123.7
105°	179.1	178.0	177.3	176.7	176.1	175.4	174.7	174.0	173.2	172.5	171.7
107.5°	222.5	221.9	221.0	220.2	219.3	218.4	217.8	217.4	217.1	216.7	216.3
110°	251.8	251.6	250.8	250.0	249.3	248.5	247.9	247.6	247.2	246.8	246.4



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.3	280.3	280.0	279.6	279.2	278.9	278.4	277.7	277.0	276.3	275.6
115°	322.0	321.7	321.8	322.0	322.1	322.2	322.1	321.7	321.3	321.0	320.6
117.5°	364.6	364.6	364.3	364.1	363.8	363.5	363.1	362.6	362.1	361.6	361.1
120°	390.4	390.2	390.3	390.4	390.6	390.7	390.5	390.0	389.5	389.0	388.5
122.5°	416.3	416.2	416.0	415.8	415.7	415.5	415.2	414.9	414.6	414.3	414.0
125°	452.2	451.8	452.0	452.3	452.5	452.8	452.7	452.2	451.7	451.1	450.6
127.5°	488.4	488.5	487.9	487.3	486.8	486.2	485.8	485.7	485.6	485.4	485.3
130°	510.1	510.0	509.6	509.2	508.8	508.4	508.2	508.1	507.9	507.8	507.7
132.5°	531.5	531.4	530.9	530.4	530.0	529.5	529.1	528.9	528.7	528.4	528.2
135°	561.0	560.7	560.2	559.7	559.2	558.7	558.5	558.6	558.8	558.9	559.0
137.5°	589.3	589.0	588.5	587.9	587.3	586.8	586.5	586.4	586.4	586.3	586.3
140°	606.7	606.4	606.1	605.9	605.6	605.3	605.1	604.8	604.6	604.3	604.1
142.5°	623.1	622.8	622.6	622.5	622.3	622.2	621.9	621.4	621.0	620.5	620.1
145°	646.4	646.3	646.3	646.3	646.3	646.3	646.1	645.7	645.3	645.0	644.6
147.5°	666.8	666.7	666.8	667.0	667.1	667.2	666.9	666.2	665.5	664.8	664.1
150°	679.9	679.9	680.1	680.2	680.3	680.5	680.3	679.8	679.3	678.7	678.2
152.5°	691.1	690.9	691.1	691.4	691.6	691.8	691.7	691.3	690.9	690.5	690.1
155°	706.1	705.6	706.0	706.4	706.8	707.1	707.3	707.1	707.0	706.9	706.8
157.5°	719.2	718.5	718.9	719.4	719.8	720.2	720.5	720.6	720.6	720.7	720.8
160°	727.5	726.7	726.8	727.0	727.1	727.2	727.5	727.9	728.2	728.6	729.0
162.5°	734.3	733.6	733.7	733.8	733.9	734.1	734.4	734.9	735.3	735.8	736.3
165°	743.7	742.7	742.7	742.7	742.7	742.7	743.0	743.6	744.3	744.9	745.5
167.5°	750.7	749.5	749.6	749.7	749.8	749.8	750.2	750.9	751.5	752.2	752.8
170°	755.1	754.1	754.0	753.8	753.7	753.6	753.9	754.7	755.4	756.2	757.0
172.5°	757.9	756.8	756.7	756.6	756.5	756.3	756.7	757.4	758.2	758.9	759.7
175°	760.9	759.8	759.7	759.6	759.4	759.3	759.6	760.4	761.1	761.9	762.7
177.5°	762.6	761.7	761.5	761.3	761.1	760.9	761.2	761.9	762.6	763.3	764.0
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1679.9	1685.4	1692.6	1704.8	1709.2	1714.7	1722.5	1721.9	1724.1	1732.4	1750.1
5°	1686.1	1707.5	1728.3	1753.2	1779.4	1796.7	1820.2	1834.7	1849.2	1867.9	1899.7
7.5°	1688.6	1722.6	1760.6	1804.3	1843.2	1888.0	1922.9	1955.8	1985.6	2025.0	2062.9
10°	1684.7	1730.3	1779.4	1834.7	1893.5	1943.3	1988.2	2039.4	2082.9	2130.6	2173.5
12.5°	1677.5	1732.6	1798.2	1860.2	1928.9	2002.4	2058.4	2110.1	2168.1	2223.0	2289.1
15°	1661.2	1736.6	1813.3	1894.9	1986.8	2071.8	2152.7	2219.8	2282.0	2364.3	2450.7
17.5°	1640.5	1721.8	1818.5	1917.3	2013.4	2110.6	2210.7	2311.5	2390.0	2492.2	2559.8
20°	1621.1	1715.1	1814.7	1932.2	2028.3	2149.3	2248.8	2346.3	2454.1	2555.8	2636.6
22.5°	1594.0	1696.9	1802.5	1919.5	2046.0	2167.0	2282.0	2387.8	2495.6	2606.1	2704.1
25°	1559.6	1652.9	1778.0	1910.8	2036.6	2167.9	2300.0	2432.7	2548.8	2665.7	2756.9
27.5°	1501.0	1618.8	1735.3	1872.3	2012.1	2160.7	2301.9	2440.9	2562.5	2658.6	2715.2
30°	1471.1	1573.4	1699.9	1837.5	1988.9	2148.6	2295.8	2432.0	2545.4	2622.1	2644.9
32.5°	1426.9	1532.5	1656.2	1798.8	1959.0	2123.1	2276.5	2404.9	2499.5	2539.7	2512.2
35°	1361.2	1456.6	1581.7	1727.6	1894.2	2069.1	2220.5	2329.0	2377.4	2339.4	2244.7
37.5°	1282.4	1376.9	1502.6	1645.9	1818.3	1996.1	2133.0	2211.1	2195.0	2100.5	1959.3
40°	1227.1	1315.6	1435.2	1590.0	1758.0	1936.3	2056.6	2098.8	2054.6	1919.1	1769.1
42.5°	1165.7	1252.0	1372.1	1521.4	1699.4	1863.9	1968.7	1972.2	1898.0	1736.0	1585.4
45°	1072.2	1154.5	1267.9	1423.4	1587.9	1742.8	1811.9	1778.0	1641.2	1484.9	1333.5
47.5°	980.0	1051.3	1163.1	1310.7	1467.0	1597.3	1631.6	1570.6	1424.8	1273.1	1132.8
50°	912.5	984.4	1089.5	1230.5	1381.2	1493.9	1510.5	1429.6	1286.5	1133.7	1023.8
52.5°	847.8	919.2	1020.4	1150.9	1288.9	1390.5	1391.0	1297.4	1154.9	1018.7	916.5
55°	752.8	817.1	908.4	1025.2	1148.3	1227.8	1208.4	1111.6	987.9	869.7	780.5
57.5°	661.3	717.3	801.4	898.8	1007.2	1072.8	1040.7	947.5	837.0	736.8	669.2
60°	602.1	655.4	727.3	819.2	910.5	961.6	931.2	846.8	745.2	664.3	605.6
62.5°	544.6	589.5	658.7	738.5	823.1	861.0	833.9	750.6	662.8	589.7	542.0
65°	463.2	499.8	555.1	623.6	685.1	717.6	694.8	617.3	550.3	497.7	459.7
67.5°	387.1	415.8	457.6	512.5	564.8	582.4	561.6	507.7	450.9	408.8	382.0
70°	334.6	361.6	396.8	439.0	484.6	503.3	482.5	439.7	393.4	354.6	328.4
72.5°	288.7	309.6	339.3	375.4	411.1	429.7	415.6	374.4	335.3	306.5	284.1
75°	219.8	237.8	258.5	284.1	311.8	324.2	311.8	283.4	256.5	235.0	219.1
77.5°	159.8	169.5	185.5	204.6	221.9	231.4	220.7	201.4	185.0	170.3	162.5
80°	121.7	128.6	139.6	154.9	166.6	175.6	168.7	152.8	139.6	130.0	126.5
82.5°	88.5	93.2	100.4	111.7	119.6	124.2	121.1	109.6	104.2	95.7	92.2
85°	43.6	46.3	51.2	54.6	61.5	62.2	62.9	58.1	53.2	51.2	48.4
87.5°	15.6	16.4	18.3	20.3	22.7	23.5	23.1	23.3	21.3	20.9	18.9
90°	3.1	4.5	5.9	7.3	8.5	9.5	10.5	11.5	12.5	13.3	14.1
92.5°	7.3	7.3	7.4	7.5	8.0	9.1	10.1	11.1	12.1	12.9	13.6
95°	27.1	22.8	18.4	14.1	12.0	12.2	12.3	12.4	12.5	13.3	14.1
97.5°	69.3	72.0	74.7	77.4	71.6	57.5	43.4	29.2	15.1	15.1	15.2
100°	95.8	98.1	100.4	102.7	95.1	77.6	60.1	42.6	25.1	22.9	20.8
102.5°	125.3	127.0	128.7	130.4	130.1	127.8	125.5	123.2	120.9	97.7	74.4
105°	172.5	173.2	174.0	174.7	175.4	176.1	176.7	177.3	178.0	179.1	180.3
107.5°	216.7	217.1	217.4	217.8	218.4	219.3	220.2	221.0	221.9	222.5	223.0
110°	246.8	247.2	247.6	247.9	248.5	249.3	250.0	250.8	251.6	251.8	252.1



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.3	277.0	277.7	278.4	278.9	279.2	279.6	280.0	280.3	280.3	280.2
115°	321.0	321.3	321.7	322.1	322.2	322.1	322.0	321.8	321.7	322.0	322.2
117.5°	361.6	362.1	362.6	363.1	363.5	363.8	364.1	364.3	364.6	364.6	364.5
120°	389.0	389.5	390.0	390.5	390.7	390.6	390.4	390.3	390.2	390.4	390.7
122.5°	414.3	414.6	414.9	415.2	415.5	415.7	415.8	416.0	416.2	416.3	416.5
125°	451.1	451.7	452.2	452.7	452.8	452.5	452.3	452.0	451.8	452.2	452.5
127.5°	485.4	485.6	485.7	485.8	486.2	486.8	487.3	487.9	488.5	488.4	488.4
130°	507.8	507.9	508.1	508.2	508.4	508.8	509.2	509.6	510.0	510.1	510.2
132.5°	528.4	528.7	528.9	529.1	529.5	530.0	530.4	530.9	531.4	531.5	531.7
135°	558.9	558.8	558.6	558.5	558.7	559.2	559.7	560.2	560.7	561.0	561.2
137.5°	586.3	586.4	586.4	586.5	586.8	587.3	587.9	588.5	589.0	589.3	589.6
140°	604.3	604.6	604.8	605.1	605.3	605.6	605.9	606.1	606.4	606.7	607.1
142.5°	620.5	621.0	621.4	621.9	622.2	622.3	622.5	622.6	622.8	623.1	623.3
145°	645.0	645.3	645.7	646.1	646.3	646.3	646.3	646.3	646.3	646.4	646.5
147.5°	664.8	665.5	666.2	666.9	667.2	667.1	667.0	666.8	666.7	666.8	666.9
150°	678.7	679.3	679.8	680.3	680.5	680.3	680.2	680.1	679.9	679.9	679.9
152.5°	690.5	690.9	691.3	691.7	691.8	691.6	691.4	691.1	690.9	691.1	691.3
155°	706.9	707.0	707.1	707.3	707.1	706.8	706.4	706.0	705.6	706.1	706.6
157.5°	720.7	720.6	720.6	720.5	720.2	719.8	719.4	718.9	718.5	719.2	719.8
160°	728.6	728.2	727.9	727.5	727.2	727.1	727.0	726.8	726.7	727.5	728.2
162.5°	735.8	735.3	734.9	734.4	734.1	733.9	733.8	733.7	733.6	734.3	735.1
165°	744.9	744.3	743.6	743.0	742.7	742.7	742.7	742.7	742.7	743.7	744.7
167.5°	752.2	751.5	750.9	750.2	749.8	749.8	749.7	749.6	749.5	750.7	751.8
170°	756.2	755.4	754.7	753.9	753.6	753.7	753.8	754.0	754.1	755.1	756.1
172.5°	758.9	758.2	757.4	756.7	756.3	756.5	756.6	756.7	756.8	757.9	758.9
175°	761.9	761.1	760.4	759.6	759.3	759.4	759.6	759.7	759.8	760.9	762.1
177.5°	763.3	762.6	761.9	761.2	760.9	761.1	761.3	761.5	761.7	762.6	763.4
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1759.0	1760.1	1765.0	1768.9	1770.0	1775.6	1776.1
5°	1913.5	1925.3	1948.1	1950.2	1953.6	1971.6	1957.8
7.5°	2094.7	2124.5	2144.4	2162.0	2168.4	2176.2	2174.6
10°	2210.8	2255.0	2277.2	2312.4	2313.8	2322.8	2317.3
12.5°	2327.5	2378.9	2419.3	2425.8	2455.4	2459.9	2467.7
15°	2492.8	2547.5	2603.5	2623.5	2664.3	2674.0	2689.2
17.5°	2648.3	2704.1	2743.4	2795.2	2812.0	2834.4	2819.1
20°	2733.4	2794.3	2844.0	2884.8	2902.1	2914.5	2913.2
22.5°	2784.9	2846.2	2886.6	2917.4	2933.6	2938.9	2938.6
25°	2817.1	2852.3	2864.8	2876.5	2858.6	2852.3	2855.1
27.5°	2727.5	2718.4	2685.9	2643.3	2599.0	2563.9	2544.8
30°	2604.2	2550.2	2501.1	2415.4	2371.2	2344.9	2321.4
32.5°	2429.4	2343.9	2249.5	2171.0	2120.7	2081.7	2075.9
35°	2129.9	2001.3	1885.9	1789.8	1740.0	1697.8	1688.2
37.5°	1810.8	1677.2	1573.3	1488.7	1435.2	1405.4	1377.6
40°	1599.0	1484.2	1381.9	1310.0	1269.2	1247.8	1230.5
42.5°	1435.8	1331.0	1229.3	1174.5	1137.6	1124.5	1114.4
45°	1210.5	1113.0	1042.5	1001.0	979.6	957.5	947.1
47.5°	1030.0	950.7	904.2	869.0	846.0	832.9	826.2
50°	927.7	862.7	821.3	794.3	773.6	763.2	757.7
52.5°	837.0	783.7	748.8	727.4	713.3	705.7	703.5
55°	721.0	680.2	658.1	639.5	629.1	622.2	619.4
57.5°	626.7	595.4	577.4	562.0	558.0	552.2	550.3
60°	564.8	540.6	525.4	515.0	511.6	504.7	506.0
62.5°	510.0	490.3	477.3	471.3	466.8	461.0	462.9
65°	431.4	416.9	409.9	404.4	398.9	395.4	398.2
67.5°	362.0	352.0	342.6	339.4	336.7	336.1	333.2
70°	316.6	308.3	300.0	298.0	298.0	295.2	294.5
72.5°	272.9	266.8	261.3	259.8	257.6	258.7	255.8
75°	210.8	206.0	203.9	201.9	201.2	201.2	199.1
77.5°	155.8	152.2	148.9	148.9	146.4	145.5	145.2
80°	118.2	116.8	114.1	114.1	112.7	113.4	112.0
82.5°	88.9	87.0	86.4	85.3	83.4	83.5	82.1
85°	47.7	45.6	44.9	42.9	41.5	42.9	41.5
87.5°	19.6	19.2	18.7	17.6	17.1	17.2	15.6
90°	14.8	15.6	16.1	16.4	16.6	16.9	17.1
92.5°	14.4	15.1	15.5	15.6	15.6	15.7	15.7
95°	14.8	15.6	16.0	16.2	16.3	16.4	16.5
97.5°	15.3	15.4	15.5	15.6	15.7	15.8	16.0
100°	18.6	16.5	15.5	15.6	15.7	15.8	16.0
102.5°	51.2	27.9	16.3	16.4	16.4	16.4	16.4
105°	181.4	182.5	180.8	176.3	171.7	167.1	162.6
107.5°	223.6	224.1	224.6	225.1	225.6	226.1	226.6
110°	252.3	252.6	252.9	253.3	253.6	254.0	254.4



TEST NUMBER: P332634

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	280.2	280.1	280.3	280.8	281.3	281.8	282.2
115°	322.5	322.7	322.9	322.9	322.9	322.9	322.9
117.5°	364.5	364.4	364.4	364.3	364.3	364.2	364.2
120°	390.9	391.2	391.2	390.9	390.7	390.4	390.2
122.5°	416.6	416.8	416.7	416.5	416.2	416.0	415.7
125°	452.9	453.3	453.6	453.7	453.8	453.9	454.1
127.5°	488.3	488.2	488.1	488.0	487.9	487.8	487.7
130°	510.3	510.5	510.5	510.5	510.5	510.5	510.5
132.5°	531.8	531.9	531.9	531.8	531.7	531.6	531.5
135°	561.5	561.7	562.0	562.2	562.5	562.8	563.0
137.5°	589.9	590.1	590.2	590.2	590.1	590.0	589.9
140°	607.5	607.9	608.1	608.3	608.4	608.5	608.6
142.5°	623.6	623.9	624.1	624.1	624.1	624.1	624.2
145°	646.7	646.8	647.0	647.2	647.5	647.8	648.0
147.5°	667.0	667.1	667.2	667.4	667.5	667.6	667.7
150°	679.9	679.9	680.0	680.1	680.3	680.4	680.5
152.5°	691.5	691.7	691.8	691.7	691.6	691.5	691.5
155°	707.1	707.6	707.7	707.3	706.9	706.6	706.2
157.5°	720.5	721.1	721.1	720.5	719.8	719.2	718.5
160°	729.0	729.8	729.8	729.0	728.2	727.5	726.7
162.5°	735.8	736.6	736.6	735.7	734.8	734.0	733.1
165°	745.7	746.8	746.7	745.5	744.4	743.3	742.1
167.5°	752.9	754.0	753.9	752.7	751.4	750.1	748.9
170°	757.1	758.2	758.0	756.8	755.5	754.2	753.0
172.5°	759.9	760.9	760.7	759.4	758.0	756.6	755.2
175°	763.2	764.4	764.2	762.7	761.1	759.6	758.1
177.5°	764.2	765.0	764.8	763.6	762.4	761.1	759.9
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7

(END OF REPORT)