

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331726-940

Luminaire Tested: **SA2XXRDIP-C865D925U940-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331726-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5990.2 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331726-940
CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331726-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	39	38	33				
3	81	72	65	60	74	66	60	55	56	51	48	46	43	40	37	35	33	29				
4	74	64	56	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25				
5	68	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22				
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	27	25	22	19				
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17				
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				
9	51	39	31	27	47	36	30	25	31	26	22	26	22	19	22	19	16	14				
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21111	21111	21111
5°	21191	20846	20960
10°	21028	20505	20330
15°	20787	19896	19323
20°	20452	19029	18076
25°	20110	18045	16864
30°	19634	17031	15310
35°	19170	15930	13947
40°	18704	14790	12370
45°	18155	13511	10942
50°	17595	12215	9540
55°	17022	10826	8194
60°	16353	9361	6801
65°	15595	7866	6193
70°	14691	6477	5693
75°	13587	5908	5315
80°	11985	5281	4844
85°	9429	4168	4168



TEST NUMBER: P331726-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	2.0
10°-20°	336.0	5.6
20°-30°	471.9	7.9
30°-40°	514.6	8.6
40°-50°	473.1	7.9
50°-60°	371.6	6.2
60°-70°	242.3	4.0
70°-80°	124.9	2.1
80°-90°	35.2	0.6
90°-100°	37.5	0.6
100°-110°	137.7	2.3
110°-120°	368.0	6.1
120°-130°	607.5	10.1
130°-140°	646.1	10.8
140°-150°	600.5	10.0
150°-160°	482.8	8.1
160°-170°	311.1	5.2
170°-180°	107.1	1.8
0°-30°	930.3	15.5
0°-40°	1444.9	24.1
0°-60°	2289.6	38.2
0°-90°	2692.0	44.9
90°-120°	543.2	9.1
90°-150°	2397.3	40.0
90°-180°	3298.0	55.1
0°-180°	5990.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1308	1301	1286	1296	1293	124
15°	1244	1229	1190	1168	1156	350
25°	1129	1089	1013	966	947	519
35°	973	910	808	736	708	608
45°	795	713	592	511	479	614
55°	605	510	385	316	291	540
65°	408	312	206	168	162	405
75°	218	137	95	87	85	230
85°	51	27	22	22	22	60
90°	1	10	16	20	22	5
95°	53	28	32	36	35	65
105°	248	258	50	58	62	265
115°	468	482	502	143	67	461
125°	662	673	688	694	696	590
135°	819	832	840	847	846	633
145°	950	950	963	969	965	594
155°	1046	1040	1049	1053	1047	482
165°	1103	1098	1100	1105	1100	311
175°	1128	1123	1124	1129	1121	107
180°	1126	1126	1126	1126	1126	



TEST NUMBER: P331726-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1312.2	1311.2	1310.1	1309.0	1308.1	1306.4	1304.0	1301.7	1299.4	1297.1	1299.2
5°	1307.5	1306.2	1304.8	1303.5	1302.3	1299.8	1296.5	1293.1	1289.6	1286.2	1288.5
7.5°	1294.0	1292.4	1290.8	1289.1	1287.5	1284.7	1280.7	1276.7	1272.6	1268.6	1269.4
10°	1282.6	1280.8	1279.0	1277.1	1275.2	1271.8	1266.5	1261.2	1256.0	1250.7	1249.9
12.5°	1268.5	1266.1	1263.9	1261.7	1259.4	1254.9	1248.1	1241.4	1234.7	1228.0	1226.5
15°	1243.6	1240.7	1237.8	1234.9	1232.0	1226.1	1217.2	1208.3	1199.3	1190.3	1185.4
17.5°	1213.1	1208.6	1204.3	1199.8	1195.4	1187.5	1176.0	1164.5	1153.1	1141.6	1135.7
20°	1190.3	1185.1	1179.8	1174.6	1169.3	1160.1	1146.9	1133.8	1120.7	1107.5	1100.9
22.5°	1165.7	1159.8	1154.0	1148.1	1142.2	1131.8	1117.0	1102.2	1087.4	1072.5	1064.0
25°	1128.8	1120.4	1112.0	1103.6	1095.2	1082.3	1064.9	1047.6	1030.2	1012.9	1002.1
27.5°	1084.3	1075.1	1066.0	1056.9	1047.8	1033.4	1013.8	994.3	974.6	955.1	942.5
30°	1053.1	1043.1	1033.1	1023.1	1013.2	997.6	976.6	955.6	934.5	913.5	900.1
32.5°	1022.8	1011.1	999.4	987.7	976.1	959.6	938.1	916.6	895.2	873.7	858.4
35°	972.6	959.2	945.8	932.4	919.0	900.7	877.5	854.4	831.3	808.2	791.6
37.5°	922.5	907.8	893.0	878.2	863.5	843.8	819.2	794.5	769.9	745.2	726.9
40°	887.4	871.6	855.9	840.1	824.3	803.7	778.2	752.7	727.2	701.7	683.0
42.5°	851.5	834.8	818.2	801.6	785.0	763.5	737.2	710.8	684.5	658.1	638.8
45°	795.1	777.5	759.9	742.3	724.7	702.0	674.5	646.8	619.2	591.7	572.9
47.5°	740.2	721.6	702.9	684.2	665.6	641.9	613.5	585.0	556.4	528.0	509.4
50°	700.5	681.8	663.2	644.4	625.8	602.0	573.1	544.1	515.2	486.3	468.1
52.5°	661.6	642.1	622.7	603.2	583.6	559.7	531.5	503.1	474.8	446.6	429.0
55°	604.7	584.2	563.7	543.1	522.6	498.1	469.8	441.3	413.0	384.6	368.8
57.5°	546.2	525.1	504.1	483.0	462.1	437.9	410.5	383.3	356.0	328.7	314.2
60°	506.4	485.4	464.4	443.4	422.3	398.2	371.1	344.0	317.0	289.9	276.5
62.5°	467.6	446.6	425.5	404.5	383.4	360.1	334.2	308.4	282.6	256.7	244.0
65°	408.2	386.9	365.6	344.3	323.1	300.5	276.9	253.2	229.5	205.9	197.0
67.5°	351.0	329.8	308.7	287.5	266.4	245.1	223.9	202.6	181.3	160.0	155.9
70°	311.2	290.7	270.2	249.7	229.2	209.8	191.7	173.5	155.4	137.2	134.6
72.5°	273.3	253.7	234.0	214.4	194.7	177.5	163.0	148.4	133.8	119.3	117.1
75°	217.8	199.3	180.9	162.5	144.1	130.5	121.5	112.5	103.6	94.7	92.8
77.5°	163.1	146.9	130.7	114.6	98.4	88.3	83.9	79.6	75.3	71.0	69.9
80°	128.9	115.6	102.2	88.7	75.3	67.3	64.6	62.1	59.4	56.8	55.7
82.5°	97.7	87.3	76.8	66.3	55.9	49.8	48.0	46.2	44.4	42.6	42.0
85°	50.9	45.4	39.9	34.3	28.8	25.7	24.9	24.1	23.3	22.5	22.5
87.5°	15.3	14.0	12.8	11.4	10.2	9.6	10.0	10.3	10.5	10.8	10.8
90°	0.8	2.8	4.8	6.8	8.7	10.5	11.9	13.4	14.8	16.3	17.2
92.5°	16.4	16.2	16.1	15.9	15.7	16.0	16.8	17.5	18.2	18.9	19.4
95°	53.0	47.0	41.0	35.0	29.1	26.7	28.0	29.2	30.5	31.7	32.6
97.5°	105.0	88.2	71.4	54.6	37.7	30.8	33.7	36.6	39.6	42.5	43.2
100°	144.2	119.3	94.5	69.7	44.9	34.2	37.2	40.3	43.3	46.5	47.9
102.5°	187.2	181.9	176.6	171.4	166.1	150.7	124.9	99.2	73.5	47.7	49.6
105°	247.5	253.0	258.4	263.9	269.3	247.3	197.9	148.5	99.1	49.7	51.6
107.5°	316.5	320.8	325.2	329.6	334.0	306.6	247.3	188.1	128.8	69.6	67.5
110°	360.8	364.6	368.4	372.2	375.9	351.7	299.4	247.1	194.8	142.5	124.4



TEST NUMBER: P331726-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	402.4	405.8	409.2	412.6	415.9	411.2	398.2	385.3	372.4	359.4	293.5
115°	468.2	471.4	474.4	477.5	480.5	484.4	488.9	493.5	497.9	502.5	418.7
117.5°	527.1	530.5	534.0	537.4	540.8	544.1	547.2	550.4	553.5	556.5	536.3
120°	570.1	572.7	575.5	578.2	580.9	583.9	587.2	590.4	593.7	596.9	599.1
122.5°	606.5	609.4	612.2	615.1	618.0	621.2	624.7	628.3	631.9	635.4	636.7
125°	662.1	664.4	666.8	669.1	671.5	674.4	677.9	681.3	684.7	688.1	689.5
127.5°	712.4	715.1	717.6	720.2	722.8	725.4	728.0	730.6	733.2	735.8	737.5
130°	744.4	747.3	750.1	753.0	755.9	758.4	760.4	762.3	764.4	766.3	768.3
132.5°	776.9	779.4	781.9	784.3	786.8	789.0	791.0	793.0	795.0	796.9	798.7
135°	819.3	822.2	825.1	828.0	830.9	833.1	834.7	836.4	838.0	839.6	841.4
137.5°	862.1	864.2	866.2	868.2	870.2	872.2	874.0	875.8	877.7	879.6	881.3
140°	890.1	891.6	893.0	894.5	895.9	897.7	899.6	901.6	903.7	905.6	907.2
142.5°	913.6	914.9	916.2	917.5	918.8	920.6	922.8	925.1	927.5	929.7	931.2
145°	950.4	950.2	950.0	949.9	949.7	951.1	954.2	957.3	960.4	963.4	964.7
147.5°	982.5	981.8	981.1	980.4	979.7	980.9	983.9	987.0	990.1	993.1	994.0
150°	1003.4	1002.1	1000.8	999.5	998.3	999.1	1002.0	1004.9	1007.8	1010.7	1011.7
152.5°	1020.9	1019.5	1018.1	1016.7	1015.3	1015.9	1018.7	1021.5	1024.2	1027.0	1028.1
155°	1046.5	1044.9	1043.2	1041.6	1040.0	1040.3	1042.4	1044.6	1046.8	1048.9	1050.0
157.5°	1066.5	1065.1	1063.8	1062.4	1061.0	1061.1	1062.7	1064.2	1065.7	1067.2	1068.4
160°	1078.3	1077.2	1076.1	1075.0	1073.9	1073.9	1075.0	1076.1	1077.2	1078.3	1079.3
162.5°	1088.7	1087.6	1086.5	1085.4	1084.3	1084.2	1085.2	1086.1	1087.1	1088.1	1089.2
165°	1102.7	1101.6	1100.5	1099.4	1098.3	1098.1	1098.6	1099.1	1099.7	1100.3	1101.5
167.5°	1113.1	1112.1	1111.0	1109.8	1108.8	1108.5	1109.0	1109.5	1110.0	1110.5	1111.8
170°	1119.0	1117.8	1116.8	1115.7	1114.6	1114.3	1114.6	1115.0	1115.4	1115.7	1117.0
172.5°	1122.8	1121.8	1120.7	1119.6	1118.6	1118.2	1118.6	1118.9	1119.3	1119.6	1120.9
175°	1127.9	1126.7	1125.4	1124.1	1122.8	1122.4	1122.8	1123.1	1123.5	1123.8	1125.2
177.5°	1128.7	1127.7	1126.8	1125.7	1124.7	1124.3	1124.4	1124.5	1124.7	1124.8	1125.9
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5



TEST NUMBER: P331726-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1301.3	1303.4	1305.5	1306.4	1305.9	1305.5	1305.1	1304.7
5°	1290.9	1293.2	1295.7	1296.5	1295.7	1294.9	1294.1	1293.2
7.5°	1270.1	1270.7	1271.4	1271.0	1269.7	1268.4	1266.9	1265.6
10°	1249.1	1248.3	1247.5	1246.3	1244.7	1243.2	1241.6	1240.0
12.5°	1225.1	1223.7	1222.3	1220.3	1217.6	1215.0	1212.4	1209.8
15°	1180.4	1175.4	1170.4	1166.5	1164.0	1161.3	1158.7	1156.0
17.5°	1129.7	1123.7	1117.8	1112.6	1108.0	1103.6	1099.0	1094.5
20°	1094.4	1087.8	1081.2	1075.0	1069.3	1063.5	1057.7	1052.0
22.5°	1055.6	1047.1	1038.7	1032.2	1028.0	1023.6	1019.3	1015.0
25°	991.3	980.5	969.7	962.3	958.4	954.5	950.6	946.6
27.5°	930.0	917.4	904.8	895.5	889.2	882.9	876.6	870.4
30°	886.6	873.3	859.8	849.5	842.5	835.4	828.3	821.2
32.5°	843.1	827.8	812.5	801.5	794.9	788.2	781.5	774.8
35°	775.0	758.5	741.9	730.8	725.0	719.2	713.4	707.6
37.5°	708.7	690.5	672.3	659.8	653.2	646.5	639.9	633.3
40°	664.3	645.7	627.0	614.2	607.4	600.6	593.7	586.9
42.5°	619.6	600.2	580.9	567.9	561.3	554.7	548.0	541.4
45°	554.3	535.7	516.9	504.4	498.1	491.9	485.5	479.2
47.5°	490.8	472.3	453.7	441.6	435.9	430.1	424.4	418.7
50°	450.0	431.9	413.8	401.9	396.4	390.8	385.3	379.8
52.5°	411.5	394.0	376.5	365.2	360.1	355.0	349.9	344.8
55°	353.0	337.2	321.5	311.0	306.0	301.0	296.0	291.1
57.5°	299.8	285.3	270.9	261.5	257.3	253.1	248.9	244.7
60°	263.1	249.7	236.2	227.5	223.2	219.0	214.8	210.6
62.5°	231.2	218.5	205.6	198.0	195.5	193.0	190.4	187.9
65°	188.0	179.1	170.1	165.2	164.4	163.7	162.9	162.1
67.5°	151.8	147.7	143.6	141.1	140.3	139.4	138.6	137.8
70°	132.0	129.4	126.7	124.9	123.9	122.8	121.7	120.6
72.5°	114.9	112.6	110.4	109.1	108.3	107.7	107.1	106.5
75°	91.0	89.2	87.3	86.2	86.0	85.7	85.4	85.2
77.5°	68.9	67.9	66.8	66.1	65.6	65.2	64.8	64.4
80°	54.7	53.7	52.6	52.1	52.1	52.1	52.1	52.1
82.5°	41.4	40.7	40.0	39.8	39.8	39.8	39.8	39.8
85°	22.5	22.5	22.5	22.5	22.5	22.5	22.5	22.5
87.5°	10.8	10.7	10.7	10.7	10.8	10.9	11.0	11.1
90°	18.1	19.0	19.9	20.5	20.9	21.2	21.7	22.0
92.5°	19.8	20.3	20.8	21.1	21.3	21.6	21.8	22.0
95°	33.5	34.5	35.4	35.8	35.6	35.4	35.2	35.0
97.5°	44.0	44.7	45.4	45.8	46.1	46.3	46.5	46.7
100°	49.3	50.7	52.3	53.1	53.5	53.9	54.2	54.6
102.5°	51.5	53.4	55.3	56.4	57.0	57.4	58.0	58.5
105°	53.7	55.6	57.6	59.0	59.7	60.5	61.2	61.9
107.5°	65.5	63.5	61.4	60.8	61.5	62.2	63.0	63.7
110°	106.3	88.2	70.1	61.4	62.2	62.9	63.6	64.4



TEST NUMBER: P331726-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	227.5	161.4	95.4	62.7	63.2	63.8	64.4	65.0
115°	334.9	251.1	167.3	118.9	105.8	92.8	79.8	66.8
117.5°	516.0	495.8	475.5	443.9	401.1	358.3	315.5	272.7
120°	601.3	603.5	605.6	594.5	570.1	545.6	521.2	496.8
122.5°	638.0	639.3	640.6	638.9	634.2	629.4	624.6	619.9
125°	690.7	692.0	693.2	694.1	694.6	695.2	695.8	696.3
127.5°	739.4	741.3	743.2	744.0	744.2	744.3	744.4	744.5
130°	770.3	772.3	774.3	775.3	775.1	774.8	774.6	774.5
132.5°	800.4	802.1	803.8	804.5	804.3	804.1	804.0	803.8
135°	843.3	845.1	846.9	847.6	847.2	846.9	846.5	846.1
137.5°	883.1	884.8	886.6	887.3	886.6	886.0	885.4	884.8
140°	908.8	910.5	912.1	912.5	911.6	910.7	909.8	908.8
142.5°	932.6	934.2	935.7	935.9	935.0	934.2	933.3	932.3
145°	966.0	967.2	968.5	968.7	967.8	966.9	966.0	965.1
147.5°	995.0	995.9	996.8	996.9	996.1	995.4	994.6	993.9
150°	1012.8	1014.0	1015.0	1015.1	1014.2	1013.3	1012.4	1011.5
152.5°	1029.1	1030.2	1031.3	1031.3	1030.0	1028.9	1027.7	1026.4
155°	1051.1	1052.2	1053.3	1053.1	1051.7	1050.2	1048.7	1047.3
157.5°	1069.6	1070.9	1072.1	1072.0	1070.6	1069.2	1067.7	1066.4
160°	1080.4	1081.6	1082.6	1082.5	1081.2	1080.0	1078.7	1077.5
162.5°	1090.5	1091.7	1093.0	1092.8	1091.3	1089.7	1088.2	1086.5
165°	1102.8	1104.0	1105.3	1105.3	1104.0	1102.8	1101.5	1100.3
167.5°	1113.0	1114.3	1115.6	1115.4	1113.7	1112.1	1110.5	1108.8
170°	1118.3	1119.5	1120.8	1120.6	1119.0	1117.3	1115.7	1114.1
172.5°	1122.1	1123.5	1124.7	1124.5	1122.8	1121.2	1119.6	1118.0
175°	1126.4	1127.7	1128.9	1128.6	1126.9	1125.1	1123.2	1121.4
177.5°	1126.9	1127.9	1128.9	1128.7	1127.5	1126.1	1124.8	1123.6
180°	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5	1125.5

(END OF REPORT)