

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332639

Luminaire Tested: **SA4XXDIP-C1020D590U835-4F0-1E-UDD-D4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332639  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D590U835-4F0-1E-UDD-D4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6322.1 lumens  
Efficiency: N/A  
Efficacy: 129.6 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39  
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')  
CIE Type: Semi-Direct

Input Watts (W): 48.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332639  
CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-D4

### Luminous Intensity Polar Plot





TEST NUMBER: P332639

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-D4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67	62	
1	99	94	90	86	92	88	84	81	77	74	71	67	64	62	57	55	54	54	54	54	49	
2	90	82	75	69	84	76	70	65	67	62	58	58	54	51	49	47	44	44	44	44	40	
3	82	71	63	57	76	67	60	54	58	53	48	51	46	43	43	40	37	37	37	37	33	
4	74	63	54	48	69	59	51	45	52	46	41	45	40	36	39	35	32	32	32	32	28	
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	35	31	27	27	27	27	24	
6	63	50	41	35	58	47	39	34	41	35	30	36	31	27	31	27	24	24	24	24	21	
7	58	45	37	31	54	42	35	29	38	31	27	33	28	24	28	24	21	21	21	21	19	
8	54	41	33	27	50	39	31	26	34	28	24	30	25	21	26	22	19	19	19	19	17	
9	50	37	30	24	47	35	28	23	31	25	21	28	23	19	24	20	17	17	17	17	15	
10	47	34	27	22	44	32	25	21	29	23	19	26	21	17	22	18	15	15	15	15	13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9968	9968	9968
5°	9998	9741	9769
10°	9937	9582	9575
15°	9848	9397	9346
20°	9714	9194	9123
25°	9563	8966	8879
30°	9399	8739	8627
35°	9213	8507	8407
40°	9065	8285	8178
45°	8844	8081	7981
50°	8658	7846	7773
55°	8466	7625	7529
60°	8166	7342	7306
65°	7837	7040	7032
70°	7439	6694	6714
75°	6882	6312	6425
80°	6266	5946	6141
85°	5484	5623	5977



TEST NUMBER: P332639

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-D4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.9	1.8
10°-20°	335.0	5.3
20°-30°	506.5	8.0
30°-40°	612.9	9.7
40°-50°	647.9	10.2
50°-60°	609.8	9.6
60°-70°	505.9	8.0
70°-80°	355.4	5.6
80°-90°	202.5	3.2
90°-100°	329.0	5.2
100°-110°	524.8	8.3
110°-120°	450.2	7.1
120°-130°	362.3	5.7
130°-140°	288.7	4.6
140°-150°	212.4	3.4
150°-160°	147.3	2.3
160°-170°	86.6	1.4
170°-180°	28.2	0.4
0°-30°	958.4	15.2
0°-40°	1571.3	24.9
0°-60°	2829.0	44.7
0°-90°	3892.8	61.6
90°-120°	1304.0	20.6
90°-150°	2167.4	34.3
90°-180°	2429.0	38.4
0°-180°	6322.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1235	1235	1235	1235	1235	
5°	1236	1232	1222	1233	1232	117
15°	1185	1186	1182	1194	1193	334
25°	1084	1092	1096	1111	1113	499
35°	948	965	979	997	1002	594
45°	791	817	843	866	874	611
55°	619	649	690	716	726	552
65°	429	473	520	553	566	425
75°	238	289	347	384	398	253
85°	73	132	194	234	249	78
90°	23	82	147	187	200	16
95°	37	124	585	386	309	35
105°	79	138	466	930	940	85
115°	126	170	399	735	876	125
125°	169	201	371	610	688	151
135°	197	235	342	518	593	153
145°	226	257	327	417	463	142
155°	255	275	318	360	376	118
165°	278	286	305	323	328	78
175°	290	290	293	297	296	27
180°	290	290	290	290	290	



TEST NUMBER: P332639

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-D4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7
2.5°	1239.1	1238.4	1237.6	1236.9	1236.1	1234.8	1232.8	1230.9	1228.9	1226.9	1228.6
5°	1236.0	1235.1	1234.2	1233.3	1232.4	1230.8	1228.7	1226.5	1224.4	1222.2	1224.7
7.5°	1225.5	1225.0	1224.4	1223.9	1223.3	1222.2	1220.4	1218.6	1216.8	1215.0	1217.8
10°	1216.7	1216.4	1216.1	1215.8	1215.5	1214.5	1213.0	1211.5	1209.9	1208.4	1211.2
12.5°	1204.5	1204.5	1204.4	1204.3	1204.3	1203.7	1202.7	1201.6	1200.6	1199.5	1202.1
15°	1184.9	1185.2	1185.5	1185.8	1186.1	1185.8	1184.9	1184.0	1183.0	1182.1	1184.9
17.5°	1158.1	1159.0	1159.9	1160.8	1161.8	1162.1	1161.9	1161.8	1161.6	1161.4	1164.2
20°	1139.3	1140.2	1141.1	1142.0	1143.0	1143.6	1143.9	1144.2	1144.5	1144.8	1147.9
22.5°	1118.2	1119.4	1120.6	1121.8	1122.9	1123.8	1124.3	1124.9	1125.4	1126.0	1129.1
25°	1084.0	1085.8	1087.6	1089.5	1091.3	1092.7	1093.6	1094.6	1095.5	1096.4	1099.8
27.5°	1045.8	1048.5	1051.2	1053.9	1056.6	1058.7	1060.1	1061.5	1062.9	1064.3	1067.5
30°	1020.4	1022.8	1025.3	1027.7	1030.2	1032.5	1034.6	1036.8	1038.9	1041.1	1044.5
32.5°	992.7	995.7	998.6	1001.6	1004.5	1007.2	1009.6	1012.0	1014.4	1016.8	1020.6
35°	948.5	952.2	955.8	959.5	963.2	966.6	969.7	972.7	975.8	978.9	983.2
37.5°	903.9	908.2	912.4	916.7	920.9	924.9	928.7	932.5	936.4	940.2	944.5
40°	875.2	879.2	883.2	887.2	891.2	895.3	899.6	903.9	908.2	912.5	917.1
42.5°	842.0	846.5	851.0	855.5	859.9	864.7	869.7	874.8	879.8	884.9	890.0
45°	790.8	796.7	802.5	808.4	814.2	820.0	825.9	831.7	837.5	843.4	848.6
47.5°	741.9	747.9	753.9	760.0	766.0	772.4	779.1	785.9	792.7	799.4	804.8
50°	706.5	713.3	720.0	726.8	733.5	740.3	747.1	753.8	760.6	767.3	773.5
52.5°	671.1	677.9	684.6	691.4	698.2	705.4	713.1	720.9	728.6	736.4	742.5
55°	619.4	625.9	632.3	638.8	645.2	653.0	662.3	671.5	680.7	689.9	696.1
57.5°	561.6	569.6	577.6	585.6	593.6	602.1	611.3	620.5	629.6	638.8	646.1
60°	524.0	532.0	540.0	548.0	556.0	565.0	575.2	585.3	595.4	605.6	612.6
62.5°	487.5	496.2	505.0	513.7	522.4	531.8	542.0	552.1	562.3	572.4	579.5
65°	428.6	438.4	448.3	458.1	467.9	478.1	488.5	499.0	509.4	519.9	527.5
67.5°	371.9	382.4	392.8	403.3	413.7	424.5	435.7	446.9	458.1	469.3	477.1
70°	333.2	343.7	354.1	364.5	375.0	386.1	397.7	409.4	421.1	432.8	441.1
72.5°	295.6	306.3	317.0	327.7	338.4	349.9	362.3	374.7	387.2	399.6	407.6
75°	237.8	249.2	260.5	271.9	283.3	295.4	308.3	321.2	334.1	347.0	355.6
77.5°	183.9	195.9	208.0	220.0	232.1	244.8	258.4	271.9	285.4	298.9	307.6
80°	150.7	163.0	175.3	187.6	199.9	212.8	226.3	239.8	253.3	266.8	276.1
82.5°	117.5	130.3	143.1	155.9	168.6	181.8	195.3	208.8	222.4	235.9	245.3
85°	73.3	86.2	99.1	112.0	124.9	138.3	152.1	165.9	179.7	193.6	202.8
87.5°	41.0	53.8	66.7	79.3	92.0	105.0	119.1	132.6	146.3	159.9	168.7
90°	22.7	36.1	50.1	63.0	75.8	88.6	105.2	118.4	132.8	147.1	155.5
92.5°	27.5	41.5	58.0	76.0	95.4	119.4	161.6	219.0	275.4	311.2	289.6
95°	36.8	48.6	64.5	82.0	105.9	141.2	203.4	309.6	458.5	585.2	606.6
97.5°	50.1	58.8	72.4	88.0	108.5	139.2	189.9	279.6	427.6	601.4	720.3
100°	58.6	66.6	78.5	93.4	112.2	140.4	186.1	262.5	390.9	563.7	718.0
102.5°	67.7	75.6	86.1	99.5	116.9	143.6	185.8	254.3	365.0	519.4	678.0
105°	79.2	87.0	96.0	109.0	125.4	150.7	189.5	248.2	339.4	465.5	607.2
107.5°	94.7	100.8	108.7	121.1	135.9	160.1	196.0	249.9	328.8	431.9	548.9
110°	104.0	109.5	116.6	127.8	142.4	165.3	201.1	251.8	325.3	418.8	518.8



TEST NUMBER: P332639

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-D4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	113.0	117.9	125.0	135.2	149.3	171.8	206.2	254.1	323.0	409.2	498.9
115°	125.8	130.3	137.0	145.5	159.1	180.8	213.5	257.5	320.4	398.7	477.3
117.5°	140.6	143.8	149.0	157.0	168.8	190.2	221.0	261.6	318.4	389.8	462.7
120°	149.5	151.6	156.5	163.7	174.3	195.2	225.8	264.4	317.2	384.3	453.8
122.5°	158.7	160.0	164.2	170.2	181.0	200.8	230.9	267.1	316.3	378.3	444.6
125°	169.2	171.2	174.3	180.3	190.8	210.5	238.7	272.6	316.3	370.7	431.3
127.5°	179.6	181.1	184.9	191.8	202.8	221.7	247.4	277.4	314.6	361.2	414.6
130°	184.4	186.4	190.6	198.9	209.4	228.3	252.6	279.7	313.8	355.2	404.1
132.5°	190.3	191.9	197.5	205.3	216.7	234.2	257.5	283.2	313.5	350.3	394.8
135°	197.3	199.6	205.3	215.0	227.0	242.9	263.8	286.5	312.1	341.6	379.6
137.5°	205.6	207.5	213.4	222.4	234.5	249.0	267.6	287.8	309.7	335.1	366.9
140°	211.5	213.0	218.9	228.3	240.0	253.7	271.1	289.7	309.4	331.3	359.9
142.5°	216.8	218.5	224.2	233.4	244.9	258.0	274.5	291.2	309.5	329.1	354.4
145°	225.6	227.0	232.4	240.0	250.6	263.0	277.8	293.2	309.8	327.4	347.5
147.5°	235.7	236.0	240.7	248.6	257.3	268.5	282.4	295.8	310.3	325.4	341.7
150°	242.1	242.4	246.6	253.2	261.4	272.1	284.7	297.2	310.3	324.0	338.3
152.5°	246.9	247.0	251.5	257.8	265.4	275.3	286.5	298.1	309.4	321.7	334.6
155°	255.0	255.6	259.0	264.7	271.0	279.5	289.2	298.9	308.0	318.3	329.1
157.5°	263.1	263.1	266.3	270.7	276.2	282.9	291.2	298.9	306.6	314.8	323.6
160°	268.1	268.1	270.4	274.4	278.9	285.2	292.1	298.9	305.2	312.0	319.5
162.5°	272.7	272.2	274.0	277.6	281.7	286.6	293.0	298.9	303.8	309.3	315.8
165°	277.8	277.8	278.9	281.8	284.7	288.1	293.2	297.8	301.2	305.2	309.8
167.5°	282.9	282.4	282.9	285.1	286.7	289.3	293.1	296.4	298.5	301.1	304.3
170°	285.2	284.7	285.2	286.9	288.1	289.8	292.6	295.5	296.6	298.3	300.6
172.5°	287.5	286.9	287.0	288.3	289.0	290.2	292.2	294.6	294.8	295.6	297.4
175°	289.8	289.2	289.2	289.8	290.4	290.4	291.5	293.2	292.6	292.6	293.8
177.5°	290.8	290.4	289.9	290.4	290.4	290.4	290.8	291.7	290.8	290.8	291.3
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P332639

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-D4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7
2.5°	1230.4	1232.1	1233.8	1234.5	1234.3	1234.0	1233.8	1233.6
5°	1227.1	1229.6	1232.1	1233.1	1232.8	1232.5	1232.2	1231.9
7.5°	1220.6	1223.3	1226.1	1227.3	1227.0	1226.7	1226.4	1226.1
10°	1213.9	1216.7	1219.5	1220.7	1220.4	1220.1	1219.8	1219.5
12.5°	1204.6	1207.1	1209.6	1210.9	1210.8	1210.7	1210.7	1210.6
15°	1187.7	1190.4	1193.2	1194.4	1194.1	1193.8	1193.5	1193.2
17.5°	1167.0	1169.9	1172.7	1174.0	1173.7	1173.5	1173.2	1173.0
20°	1150.9	1154.0	1157.1	1158.6	1158.6	1158.6	1158.6	1158.6
22.5°	1132.1	1135.2	1138.3	1140.1	1140.6	1141.0	1141.5	1142.0
25°	1103.2	1106.5	1109.9	1111.8	1112.1	1112.4	1112.7	1113.0
27.5°	1070.6	1073.7	1076.9	1078.6	1079.0	1079.4	1079.7	1080.1
30°	1047.9	1051.2	1054.6	1056.6	1057.2	1057.8	1058.5	1059.1
32.5°	1024.5	1028.4	1032.3	1034.5	1035.1	1035.7	1036.3	1037.0
35°	987.5	991.8	996.1	998.7	999.6	1000.5	1001.5	1002.4
37.5°	948.9	953.3	957.6	960.3	961.3	962.3	963.2	964.2
40°	921.7	926.3	931.0	933.9	935.1	936.3	937.6	938.8
42.5°	895.1	900.2	905.3	908.3	909.3	910.3	911.3	912.2
45°	853.8	859.1	864.3	867.7	869.2	870.7	872.3	873.8
47.5°	810.2	815.6	821.1	824.7	826.5	828.4	830.2	832.1
50°	779.6	785.8	791.9	795.9	797.8	799.6	801.4	803.3
52.5°	748.7	754.8	761.0	764.9	766.8	768.6	770.5	772.3
55°	702.2	708.4	714.5	718.5	720.3	722.2	724.0	725.9
57.5°	653.4	660.7	668.0	672.5	674.2	676.0	677.7	679.4
60°	619.7	626.8	633.8	638.6	641.1	643.5	646.0	648.4
62.5°	586.5	593.6	600.7	605.4	607.9	610.3	612.8	615.3
65°	535.2	542.9	550.6	555.7	558.1	560.6	563.0	565.5
67.5°	484.9	492.7	500.5	505.6	508.0	510.4	512.8	515.2
70°	449.3	457.6	465.9	471.2	473.3	475.5	477.6	479.8
72.5°	415.7	423.7	431.8	437.0	439.4	441.8	444.2	446.6
75°	364.2	372.8	381.4	387.1	389.9	392.7	395.4	398.2
77.5°	316.4	325.1	333.8	339.7	342.6	345.6	348.5	351.5
80°	285.3	294.5	303.7	309.5	312.0	314.5	316.9	319.4
82.5°	254.8	264.3	273.7	279.8	282.5	285.2	287.9	290.6
85°	212.0	221.2	230.4	236.6	239.7	242.7	245.8	248.9
87.5°	177.8	186.8	195.8	201.6	204.4	207.3	209.8	212.6
90°	165.0	174.4	183.9	189.6	192.6	195.7	197.6	200.0
92.5°	259.6	240.5	232.0	226.1	221.9	221.2	221.8	224.2
95°	559.6	479.5	411.3	361.5	336.3	321.4	313.9	309.2
97.5°	752.3	727.5	679.8	625.6	587.3	555.6	541.1	531.9
100°	809.6	829.3	809.7	772.7	725.2	692.6	677.6	675.2
102.5°	800.4	865.1	881.2	868.9	840.8	818.0	802.3	801.1
105°	745.5	851.9	916.0	944.5	948.1	946.0	940.5	939.5
107.5°	672.1	784.7	871.8	927.6	958.0	973.2	981.1	984.8
110°	627.5	733.2	823.0	890.5	933.5	959.9	972.6	980.2





TEST NUMBER: P332639

CATALOG NUMBER: SA4XXDIP-C1020D590U835-4F0-1E-UDD-D4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	592.7	686.8	771.8	839.1	887.6	919.0	935.8	946.6
115°	555.4	632.3	705.8	765.0	812.3	848.6	869.0	875.8
117.5°	532.2	596.7	655.6	706.4	747.3	778.5	799.5	805.5
120°	519.8	579.0	630.8	675.6	710.6	738.1	755.4	764.1
122.5°	508.8	566.2	613.8	653.5	683.2	706.9	721.6	730.1
125°	491.9	546.8	592.0	627.2	651.9	670.3	683.0	688.2
127.5°	471.6	524.0	568.8	602.4	627.4	644.2	655.4	660.9
130°	456.9	507.5	551.9	585.8	611.0	627.1	638.1	643.3
132.5°	442.4	490.1	533.2	567.0	591.8	609.7	620.2	625.5
135°	420.4	462.4	502.2	534.1	558.7	576.5	587.5	592.8
137.5°	401.2	437.1	470.9	499.7	522.6	539.9	548.9	554.6
140°	390.1	420.9	450.6	477.3	498.8	512.9	522.4	528.5
142.5°	380.5	407.6	433.2	456.3	475.3	488.2	496.6	501.1
145°	367.6	388.9	407.8	425.3	440.8	451.8	458.7	462.8
147.5°	357.0	372.7	386.6	399.8	411.3	420.6	425.9	427.9
150°	352.0	365.1	376.5	386.8	395.9	403.3	406.7	407.3
152.5°	346.9	358.2	368.7	377.2	384.9	391.0	393.0	393.6
155°	339.4	348.5	357.1	363.9	369.7	374.2	375.9	375.9
157.5°	331.3	339.0	346.1	351.6	356.0	359.4	360.4	360.4
160°	326.3	332.6	338.8	343.4	346.8	350.3	350.8	350.8
162.5°	321.3	326.6	331.5	335.7	338.2	341.6	342.2	341.7
165°	314.3	317.7	321.7	324.6	326.9	329.1	328.6	328.0
167.5°	307.6	310.2	313.4	315.1	316.3	317.7	317.6	317.2
170°	303.5	305.2	307.5	309.2	310.3	310.9	310.3	310.3
172.5°	299.8	301.1	302.5	303.7	304.4	305.0	304.4	303.5
175°	294.9	295.5	296.6	296.6	296.6	297.8	296.6	295.5
177.5°	291.7	292.2	292.2	292.6	292.2	292.6	291.7	290.8
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4

(END OF REPORT)