

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331728-940

Luminaire Tested: **SA2XXRDIP-C865D925U940-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331728-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5913.6 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331728-940
CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331728-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	93	89	86	89	86	82	80	71	69	67	59	57	56	47	46	45	39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	42	40	38	34
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25
5	69	57	50	44	63	53	46	41	45	40	36	37	34	31	30	28	25	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	25	23	20	18
8	54	42	35	30	50	40	33	28	34	29	25	28	24	22	23	21	18	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21111	21111	21111
5°	21191	20846	20960
10°	21028	20505	20330
15°	20787	19896	19323
20°	20452	19029	18076
25°	20110	18045	16864
30°	19634	17031	15310
35°	19170	15930	13947
40°	18704	14790	12370
45°	18155	13511	10942
50°	17595	12215	9540
55°	17022	10826	8194
60°	16353	9361	6801
65°	15595	7866	6193
70°	14691	6477	5693
75°	13587	5908	5315
80°	11985	5281	4844
85°	9429	4168	4168



TEST NUMBER: P331728-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	2.1
10°-20°	336.0	5.7
20°-30°	471.9	8.0
30°-40°	514.6	8.7
40°-50°	473.1	8.0
50°-60°	371.6	6.3
60°-70°	242.3	4.1
70°-80°	124.9	2.1
80°-90°	36.6	0.6
90°-100°	185.0	3.1
100°-110°	627.9	10.6
110°-120°	667.1	11.3
120°-130°	549.1	9.3
130°-140°	441.0	7.5
140°-150°	333.2	5.6
150°-160°	234.2	4.0
160°-170°	137.9	2.3
170°-180°	44.9	0.8
0°-30°	930.3	15.7
0°-40°	1444.9	24.4
0°-60°	2289.6	38.7
0°-90°	2693.3	45.5
90°-120°	1480.0	25.0
90°-150°	2803.4	47.4
90°-180°	3220.0	54.5
0°-180°	5913.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1308	1301	1286	1296	1293	124
15°	1244	1229	1190	1168	1156	350
25°	1129	1089	1013	966	947	519
35°	973	910	808	736	708	608
45°	795	713	592	511	479	614
55°	605	510	385	316	291	540
65°	408	312	206	168	162	405
75°	218	137	95	87	85	230
85°	51	27	22	22	22	60
90°	1	12	30	29	29	4
95°	31	77	349	132	102	33
105°	109	164	659	1179	1003	115
115°	191	242	552	1139	1320	190
125°	267	316	530	922	1071	237
135°	313	374	524	775	887	242
145°	358	411	522	647	708	224
155°	407	439	506	573	595	187
165°	443	457	485	514	522	125
175°	462	462	466	472	471	44
180°	463	463	463	463	463	



TEST NUMBER: P331728-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1312.2	1311.2	1310.1	1309.0	1308.1	1306.4	1304.0	1301.7	1299.4	1297.1	1299.2
5°	1307.5	1306.2	1304.8	1303.5	1302.3	1299.8	1296.5	1293.1	1289.6	1286.2	1288.5
7.5°	1294.0	1292.4	1290.8	1289.1	1287.5	1284.7	1280.7	1276.7	1272.6	1268.6	1269.4
10°	1282.6	1280.8	1279.0	1277.1	1275.2	1271.8	1266.5	1261.2	1256.0	1250.7	1249.9
12.5°	1268.5	1266.1	1263.9	1261.7	1259.4	1254.9	1248.1	1241.4	1234.7	1228.0	1226.5
15°	1243.6	1240.7	1237.8	1234.9	1232.0	1226.1	1217.2	1208.3	1199.3	1190.3	1185.4
17.5°	1213.1	1208.6	1204.3	1199.8	1195.4	1187.5	1176.0	1164.5	1153.1	1141.6	1135.7
20°	1190.3	1185.1	1179.8	1174.6	1169.3	1160.1	1146.9	1133.8	1120.7	1107.5	1100.9
22.5°	1165.7	1159.8	1154.0	1148.1	1142.2	1131.8	1117.0	1102.2	1087.4	1072.5	1064.0
25°	1128.8	1120.4	1112.0	1103.6	1095.2	1082.3	1064.9	1047.6	1030.2	1012.9	1002.1
27.5°	1084.3	1075.1	1066.0	1056.9	1047.8	1033.4	1013.8	994.3	974.6	955.1	942.5
30°	1053.1	1043.1	1033.1	1023.1	1013.2	997.6	976.6	955.6	934.5	913.5	900.1
32.5°	1022.8	1011.1	999.4	987.7	976.1	959.6	938.1	916.6	895.2	873.7	858.4
35°	972.6	959.2	945.8	932.4	919.0	900.7	877.5	854.4	831.3	808.2	791.6
37.5°	922.5	907.8	893.0	878.2	863.5	843.8	819.2	794.5	769.9	745.2	726.9
40°	887.4	871.6	855.9	840.1	824.3	803.7	778.2	752.7	727.2	701.7	683.0
42.5°	851.5	834.8	818.2	801.6	785.0	763.5	737.2	710.8	684.5	658.1	638.8
45°	795.1	777.5	759.9	742.3	724.7	702.0	674.5	646.8	619.2	591.7	572.9
47.5°	740.2	721.6	702.9	684.2	665.6	641.9	613.5	585.0	556.4	528.0	509.4
50°	700.5	681.8	663.2	644.4	625.8	602.0	573.1	544.1	515.2	486.3	468.1
52.5°	661.6	642.1	622.7	603.2	583.6	559.7	531.5	503.1	474.8	446.6	429.0
55°	604.7	584.2	563.7	543.1	522.6	498.1	469.8	441.3	413.0	384.6	368.8
57.5°	546.2	525.1	504.1	483.0	462.1	437.9	410.5	383.3	356.0	328.7	314.2
60°	506.4	485.4	464.4	443.4	422.3	398.2	371.1	344.0	317.0	289.9	276.5
62.5°	467.6	446.6	425.5	404.5	383.4	360.1	334.2	308.4	282.6	256.7	244.0
65°	408.2	386.9	365.6	344.3	323.1	300.5	276.9	253.2	229.5	205.9	197.0
67.5°	351.0	329.8	308.7	287.5	266.4	245.1	223.9	202.6	181.3	160.0	155.9
70°	311.2	290.7	270.2	249.7	229.2	209.8	191.7	173.5	155.4	137.2	134.6
72.5°	273.3	253.7	234.0	214.4	194.7	177.5	163.0	148.4	133.8	119.3	117.1
75°	217.8	199.3	180.9	162.5	144.1	130.5	121.5	112.5	103.6	94.7	92.8
77.5°	163.1	146.9	130.7	114.6	98.4	88.3	83.9	79.6	75.3	71.0	69.9
80°	128.9	115.6	102.2	88.7	75.3	67.3	64.6	62.1	59.4	56.8	55.7
82.5°	97.7	87.3	76.8	66.3	55.9	49.8	48.0	46.2	44.4	42.6	42.0
85°	50.9	45.4	39.9	34.3	28.8	25.7	24.9	24.1	23.3	22.5	22.5
87.5°	15.3	14.2	13.2	11.9	10.5	10.3	11.1	12.4	13.5	13.6	13.2
90°	0.9	3.6	7.1	8.9	10.7	13.4	17.8	24.0	29.3	30.2	29.3
92.5°	10.9	15.7	22.1	25.9	32.0	40.4	60.5	88.8	114.0	115.7	97.7
95°	31.1	34.7	43.6	51.6	65.9	87.2	128.1	205.5	308.8	348.8	305.2
97.5°	50.7	55.6	65.0	77.0	93.5	117.6	169.1	277.0	448.5	595.6	624.7
100°	68.5	71.2	79.2	93.5	111.3	136.2	183.3	291.9	484.1	703.0	831.3
102.5°	84.9	86.9	94.9	109.1	127.6	152.6	196.2	292.7	470.6	706.6	908.1
105°	108.6	112.2	118.3	131.7	151.3	176.2	218.0	297.2	444.1	659.4	896.2
107.5°	134.2	137.1	143.1	155.4	174.8	199.9	240.5	309.5	430.9	608.9	818.1
110°	151.3	154.9	160.2	171.7	190.5	216.2	255.4	319.5	428.1	584.7	768.9



TEST NUMBER: P331728-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	166.9	170.5	176.6	187.4	205.4	231.9	269.7	330.2	428.7	569.0	734.8
115°	191.4	195.8	201.2	211.8	229.6	253.6	291.9	346.2	432.5	551.8	692.4
117.5°	216.6	220.2	225.5	235.0	252.0	277.0	312.4	363.3	438.9	543.4	665.7
120°	232.3	235.9	241.2	249.1	267.0	291.9	326.6	374.7	443.2	538.4	651.5
122.5°	247.3	250.0	255.4	264.1	282.0	307.6	340.1	384.6	448.2	535.6	639.4
125°	267.0	269.7	275.0	285.7	303.4	328.4	360.4	400.5	455.7	530.4	622.1
127.5°	282.7	286.2	293.6	305.4	322.5	348.1	379.3	415.3	463.3	527.4	606.1
130°	291.9	295.4	304.3	316.8	334.7	359.5	390.7	424.5	469.0	525.9	595.4
132.5°	300.4	304.7	314.3	327.5	346.0	371.0	400.6	433.7	474.7	525.2	586.8
135°	313.3	316.8	327.5	340.8	361.3	386.2	414.7	445.9	481.4	524.1	574.9
137.5°	325.4	329.7	340.3	354.5	374.9	398.0	426.1	455.1	487.5	524.0	566.5
140°	334.7	338.2	348.8	363.1	382.7	405.8	432.5	460.1	490.4	523.3	561.6
142.5°	343.8	346.7	356.7	371.0	389.8	411.5	437.5	464.4	492.5	523.3	556.6
145°	357.8	361.3	370.2	383.6	401.4	421.0	445.0	469.9	494.8	521.5	550.0
147.5°	372.7	375.4	383.9	396.2	411.0	428.5	451.0	473.0	495.5	518.4	543.2
150°	382.7	385.3	392.4	404.0	417.4	433.4	453.9	474.3	494.8	516.2	537.5
152.5°	392.6	393.9	401.0	411.2	423.8	438.4	456.7	475.0	493.4	512.6	532.5
155°	406.7	407.6	413.0	422.8	432.5	445.9	461.0	476.1	491.2	506.4	523.3
157.5°	418.5	419.4	423.7	432.1	440.0	451.2	464.0	476.1	487.1	500.0	514.6
160°	426.3	427.2	430.7	437.8	445.0	454.8	465.5	476.1	485.0	495.7	508.2
162.5°	434.1	433.5	437.1	442.8	449.2	456.9	466.2	475.4	482.9	492.1	502.5
165°	443.2	442.3	444.1	449.4	453.9	459.2	467.3	473.5	478.8	485.0	493.0
167.5°	450.7	449.6	451.2	454.6	457.8	461.2	467.1	472.3	474.7	478.8	483.8
170°	455.7	453.9	454.8	457.4	459.2	461.9	466.4	470.8	472.6	475.2	478.8
172.5°	458.5	457.4	456.9	459.6	460.7	462.6	465.7	468.7	469.8	471.0	473.9
175°	461.9	461.0	460.1	461.9	461.9	462.8	464.6	466.4	465.5	466.4	467.3
177.5°	463.5	462.1	461.4	462.8	462.8	462.8	463.5	464.9	463.5	462.8	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8



TEST NUMBER: P331728-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1301.3	1303.4	1305.5	1306.4	1305.9	1305.5	1305.1	1304.7
5°	1290.9	1293.2	1295.7	1296.5	1295.7	1294.9	1294.1	1293.2
7.5°	1270.1	1270.7	1271.4	1271.0	1269.7	1268.4	1266.9	1265.6
10°	1249.1	1248.3	1247.5	1246.3	1244.7	1243.2	1241.6	1240.0
12.5°	1225.1	1223.7	1222.3	1220.3	1217.6	1215.0	1212.4	1209.8
15°	1180.4	1175.4	1170.4	1166.5	1164.0	1161.3	1158.7	1156.0
17.5°	1129.7	1123.7	1117.8	1112.6	1108.0	1103.6	1099.0	1094.5
20°	1094.4	1087.8	1081.2	1075.0	1069.3	1063.5	1057.7	1052.0
22.5°	1055.6	1047.1	1038.7	1032.2	1028.0	1023.6	1019.3	1015.0
25°	991.3	980.5	969.7	962.3	958.4	954.5	950.6	946.6
27.5°	930.0	917.4	904.8	895.5	889.2	882.9	876.6	870.4
30°	886.6	873.3	859.8	849.5	842.5	835.4	828.3	821.2
32.5°	843.1	827.8	812.5	801.5	794.9	788.2	781.5	774.8
35°	775.0	758.5	741.9	730.8	725.0	719.2	713.4	707.6
37.5°	708.7	690.5	672.3	659.8	653.2	646.5	639.9	633.3
40°	664.3	645.7	627.0	614.2	607.4	600.6	593.7	586.9
42.5°	619.6	600.2	580.9	567.9	561.3	554.7	548.0	541.4
45°	554.3	535.7	516.9	504.4	498.1	491.9	485.5	479.2
47.5°	490.8	472.3	453.7	441.6	435.9	430.1	424.4	418.7
50°	450.0	431.9	413.8	401.9	396.4	390.8	385.3	379.8
52.5°	411.5	394.0	376.5	365.2	360.1	355.0	349.9	344.8
55°	353.0	337.2	321.5	311.0	306.0	301.0	296.0	291.1
57.5°	299.8	285.3	270.9	261.5	257.3	253.1	248.9	244.7
60°	263.1	249.7	236.2	227.5	223.2	219.0	214.8	210.6
62.5°	231.2	218.5	205.6	198.0	195.5	193.0	190.4	187.9
65°	188.0	179.1	170.1	165.2	164.4	163.7	162.9	162.1
67.5°	151.8	147.7	143.6	141.1	140.3	139.4	138.6	137.8
70°	132.0	129.4	126.7	124.9	123.9	122.8	121.7	120.6
72.5°	114.9	112.6	110.4	109.1	108.3	107.7	107.1	106.5
75°	91.0	89.2	87.3	86.2	86.0	85.7	85.4	85.2
77.5°	68.9	67.9	66.8	66.1	65.6	65.2	64.8	64.4
80°	54.7	53.7	52.6	52.1	52.1	52.1	52.1	52.1
82.5°	41.4	40.7	40.0	39.8	39.8	39.8	39.8	39.8
85°	22.5	22.5	22.5	22.5	22.5	22.5	22.5	22.5
87.5°	12.8	12.3	12.4	12.5	12.5	12.5	12.5	12.5
90°	28.4	26.7	28.4	29.3	29.3	29.3	29.3	29.3
92.5°	77.6	66.6	59.1	53.6	52.9	50.0	50.7	49.3
95°	233.2	178.9	141.5	121.9	110.4	103.3	100.6	101.5
97.5°	544.1	445.1	348.8	284.6	242.1	220.2	207.1	199.7
100°	812.5	702.1	580.2	472.6	398.7	360.4	334.7	318.6
102.5°	988.4	963.5	874.3	760.2	679.9	614.6	582.4	560.7
105°	1081.3	1181.9	1193.5	1164.0	1108.8	1053.7	1015.4	1003.0
107.5°	1014.4	1165.8	1258.4	1301.5	1308.4	1305.4	1297.7	1281.2
110°	956.7	1116.0	1229.9	1302.9	1341.1	1358.1	1366.1	1365.2



TEST NUMBER: P331728-940

CATALOG NUMBER: SA2XXRDIP-C865D925U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	904.0	1056.9	1178.7	1262.3	1315.5	1343.8	1359.0	1363.8
115°	839.2	976.2	1092.9	1184.5	1247.7	1288.6	1311.8	1319.8
117.5°	790.4	910.8	1016.5	1102.5	1166.9	1210.1	1234.6	1241.3
120°	766.2	876.6	970.9	1052.0	1114.2	1156.0	1181.9	1190.8
122.5°	747.0	848.1	937.5	1010.7	1066.5	1107.6	1130.6	1138.1
125°	719.1	810.7	889.0	955.8	1007.5	1041.3	1063.5	1070.6
127.5°	691.5	774.5	848.3	909.9	954.9	986.6	1005.8	1011.6
130°	673.7	750.2	820.6	879.3	922.9	953.1	970.9	978.0
132.5°	656.6	727.5	792.0	847.2	890.1	920.4	936.7	943.2
135°	632.8	691.5	750.2	800.0	838.3	867.7	883.7	887.3
137.5°	613.7	662.8	709.4	752.9	787.8	813.1	827.2	832.5
140°	601.6	644.4	685.3	724.4	752.9	776.1	789.4	794.7
142.5°	591.7	627.9	663.2	696.0	723.0	744.0	755.9	757.0
145°	577.6	607.0	634.5	660.3	681.7	696.9	705.7	708.4
147.5°	566.7	589.9	611.4	630.3	647.9	660.0	666.0	667.6
150°	558.9	578.5	597.2	613.1	626.5	637.2	642.6	643.5
152.5°	551.1	569.2	585.1	599.0	609.4	618.7	622.6	622.8
155°	540.2	554.5	567.8	577.6	587.4	593.6	597.2	595.4
157.5°	527.5	539.5	550.7	558.4	565.3	570.4	572.0	572.0
160°	519.7	529.5	539.3	545.5	551.8	556.2	557.1	557.1
162.5°	511.9	520.2	528.6	533.4	539.7	542.7	543.6	542.9
165°	500.2	506.4	512.6	516.2	519.7	523.3	523.3	522.4
167.5°	488.9	493.7	498.0	501.2	502.8	504.8	504.6	503.5
170°	483.2	485.9	489.5	491.2	492.1	494.8	493.9	492.1
172.5°	476.8	478.8	481.6	482.7	483.6	484.8	483.9	482.9
175°	469.9	470.8	471.7	472.6	472.6	473.5	472.6	470.8
177.5°	464.9	464.9	465.7	465.7	465.7	465.7	464.9	463.5
180°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8

(END OF REPORT)