

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332648

Luminaire Tested: **SA4XXDIP-C1020D810U835-4F0-1E-UDD-D4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332648  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D810U835-4F0-1E-UDD-D4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7105.6 lumens  
Efficiency: N/A  
Efficacy: 130.6 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39  
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.08')  
CIE Type: General Diffuse

Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332648  
CATALOG NUMBER: SA4XXDIP-C1020D810U835-4F0-1E-UDD-D4

### Luminous Intensity Polar Plot





TEST NUMBER: P332648

CATALOG NUMBER: SA4XXDIP-C1020D810U835-4F0-1E-UDD-D4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	98	93	89	85	90	86	82	79	74	71	68	62	60	58	52	50	49	44				
2	89	80	74	68	82	75	69	64	64	60	56	54	51	48	45	42	40	36				
3	80	70	63	56	74	65	58	53	56	51	46	47	43	40	39	36	34	30				
4	73	62	54	47	68	58	50	45	50	44	39	42	38	34	35	32	29	25				
5	67	55	47	40	62	51	44	38	44	38	34	38	33	29	31	28	25	22				
6	62	49	41	35	57	46	38	33	40	34	29	34	29	25	28	25	22	19				
7	57	44	36	30	53	42	34	29	36	30	26	31	26	22	26	22	19	17				
8	53	40	32	27	49	38	30	25	33	27	23	28	23	20	24	20	17	15				
9	49	37	29	24	46	34	27	23	30	24	20	26	21	18	22	18	15	13				
10	46	34	26	21	43	32	25	20	28	22	18	24	19	16	20	17	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9968	9968	9968
5°	9998	9741	9769
10°	9937	9582	9575
15°	9848	9397	9346
20°	9714	9194	9123
25°	9563	8966	8879
30°	9399	8739	8627
35°	9213	8507	8407
40°	9065	8285	8178
45°	8844	8081	7981
50°	8658	7846	7773
55°	8466	7625	7529
60°	8166	7342	7306
65°	7837	7040	7032
70°	7439	6694	6714
75°	6882	6312	6425
80°	6266	5946	6141
85°	5484	5623	5977



TEST NUMBER: P332648

CATALOG NUMBER: SA4XXDIP-C1020D810U835-4F0-1E-UDD-D4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.9	1.6
10°-20°	335.0	4.7
20°-30°	506.5	7.1
30°-40°	612.9	8.6
40°-50°	647.9	9.1
50°-60°	609.8	8.6
60°-70°	505.9	7.1
70°-80°	355.4	5.0
80°-90°	203.1	2.9
90°-100°	406.8	5.7
100°-110°	686.6	9.7
110°-120°	595.2	8.4
120°-130°	484.2	6.8
130°-140°	390.3	5.5
140°-150°	290.1	4.1
150°-160°	201.8	2.8
160°-170°	118.7	1.7
170°-180°	38.6	0.5
0°-30°	958.4	13.5
0°-40°	1571.3	22.1
0°-60°	2829.0	39.8
0°-90°	3893.3	54.8
90°-120°	1688.5	23.8
90°-150°	2853.1	40.2
90°-180°	3212.0	45.2
0°-180°	7105.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1235	1235	1235	1235	1235	
5°	1236	1232	1222	1233	1232	117
15°	1185	1186	1182	1194	1193	334
25°	1084	1092	1096	1111	1113	499
35°	948	965	979	997	1002	594
45°	791	817	843	866	874	611
55°	619	649	690	716	726	552
65°	429	473	520	553	566	425
75°	238	289	347	384	398	253
85°	73	132	194	234	249	78
90°	23	84	151	191	204	16
95°	44	146	758	472	361	43
105°	104	174	604	1229	1237	112
115°	169	225	522	973	1162	168
125°	230	273	494	812	916	205
135°	269	321	464	698	797	209
145°	309	352	449	568	629	194
155°	350	377	436	494	515	161
165°	381	393	418	443	450	107
175°	397	398	401	407	405	38
180°	398	398	398	398	398	



TEST NUMBER: P332648

CATALOG NUMBER: SA4XXDIP-C1020D810U835-4F0-1E-UDD-D4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7
2.5°	1239.1	1238.4	1237.6	1236.9	1236.1	1234.8	1232.8	1230.9	1228.9	1226.9	1228.6
5°	1236.0	1235.1	1234.2	1233.3	1232.4	1230.8	1228.7	1226.5	1224.4	1222.2	1224.7
7.5°	1225.5	1225.0	1224.4	1223.9	1223.3	1222.2	1220.4	1218.6	1216.8	1215.0	1217.8
10°	1216.7	1216.4	1216.1	1215.8	1215.5	1214.5	1213.0	1211.5	1209.9	1208.4	1211.2
12.5°	1204.5	1204.5	1204.4	1204.3	1204.3	1203.7	1202.7	1201.6	1200.6	1199.5	1202.1
15°	1184.9	1185.2	1185.5	1185.8	1186.1	1185.8	1184.9	1184.0	1183.0	1182.1	1184.9
17.5°	1158.1	1159.0	1159.9	1160.8	1161.8	1162.1	1161.9	1161.8	1161.6	1161.4	1164.2
20°	1139.3	1140.2	1141.1	1142.0	1143.0	1143.6	1143.9	1144.2	1144.5	1144.8	1147.9
22.5°	1118.2	1119.4	1120.6	1121.8	1122.9	1123.8	1124.3	1124.9	1125.4	1126.0	1129.1
25°	1084.0	1085.8	1087.6	1089.5	1091.3	1092.7	1093.6	1094.6	1095.5	1096.4	1099.8
27.5°	1045.8	1048.5	1051.2	1053.9	1056.6	1058.7	1060.1	1061.5	1062.9	1064.3	1067.5
30°	1020.4	1022.8	1025.3	1027.7	1030.2	1032.5	1034.6	1036.8	1038.9	1041.1	1044.5
32.5°	992.7	995.7	998.6	1001.6	1004.5	1007.2	1009.6	1012.0	1014.4	1016.8	1020.6
35°	948.5	952.2	955.8	959.5	963.2	966.6	969.7	972.7	975.8	978.9	983.2
37.5°	903.9	908.2	912.4	916.7	920.9	924.9	928.7	932.5	936.4	940.2	944.5
40°	875.2	879.2	883.2	887.2	891.2	895.3	899.6	903.9	908.2	912.5	917.1
42.5°	842.0	846.5	851.0	855.5	859.9	864.7	869.7	874.8	879.8	884.9	890.0
45°	790.8	796.7	802.5	808.4	814.2	820.0	825.9	831.7	837.5	843.4	848.6
47.5°	741.9	747.9	753.9	760.0	766.0	772.4	779.1	785.9	792.7	799.4	804.8
50°	706.5	713.3	720.0	726.8	733.5	740.3	747.1	753.8	760.6	767.3	773.5
52.5°	671.1	677.9	684.6	691.4	698.2	705.4	713.1	720.9	728.6	736.4	742.5
55°	619.4	625.9	632.3	638.8	645.2	653.0	662.3	671.5	680.7	689.9	696.1
57.5°	561.6	569.6	577.6	585.6	593.6	602.1	611.3	620.5	629.6	638.8	646.1
60°	524.0	532.0	540.0	548.0	556.0	565.0	575.2	585.3	595.4	605.6	612.6
62.5°	487.5	496.2	505.0	513.7	522.4	531.8	542.0	552.1	562.3	572.4	579.5
65°	428.6	438.4	448.3	458.1	467.9	478.1	488.5	499.0	509.4	519.9	527.5
67.5°	371.9	382.4	392.8	403.3	413.7	424.5	435.7	446.9	458.1	469.3	477.1
70°	333.2	343.7	354.1	364.5	375.0	386.1	397.7	409.4	421.1	432.8	441.1
72.5°	295.6	306.3	317.0	327.7	338.4	349.9	362.3	374.7	387.2	399.6	407.6
75°	237.8	249.2	260.5	271.9	283.3	295.4	308.3	321.2	334.1	347.0	355.6
77.5°	183.9	195.9	208.0	220.0	232.1	244.8	258.4	271.9	285.4	298.9	307.6
80°	150.7	163.0	175.3	187.6	199.9	212.8	226.3	239.8	253.3	266.8	276.1
82.5°	117.5	130.3	143.1	155.9	168.6	181.8	195.3	208.8	222.4	235.9	245.3
85°	73.3	86.2	99.1	112.0	124.9	138.3	152.1	165.9	179.7	193.6	202.8
87.5°	41.1	53.9	66.9	79.6	92.3	105.3	119.7	133.2	146.9	160.7	169.5
90°	22.9	36.8	51.4	64.5	77.5	90.3	108.2	121.4	136.2	151.0	159.1
92.5°	29.9	45.1	63.5	84.1	106.5	134.9	187.9	261.8	334.1	378.3	345.5
95°	43.8	56.3	74.2	94.5	123.4	167.6	248.3	389.1	588.6	757.6	783.8
97.5°	62.6	71.3	86.8	104.9	129.7	167.8	232.7	351.1	549.3	782.9	943.0
100°	74.6	82.6	96.1	113.5	136.3	171.3	229.4	329.8	501.3	733.7	942.2
102.5°	87.1	95.4	107.3	123.0	144.3	177.4	230.9	320.3	467.8	675.0	889.5
105°	103.9	112.4	122.5	138.0	158.2	189.7	238.6	314.8	435.7	604.2	795.6
107.5°	125.2	131.8	140.8	155.8	174.3	204.6	249.7	319.6	423.9	561.1	718.7
110°	138.5	144.4	152.6	166.3	184.7	213.3	258.4	323.9	420.7	544.8	679.4



TEST NUMBER: P332648

CATALOG NUMBER: SA4XXDIP-C1020D810U835-4F0-1E-UDD-D4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	151.2	156.5	164.9	177.5	195.3	223.5	266.9	328.8	419.4	533.7	654.2
115°	169.4	174.5	182.7	193.3	210.9	238.3	279.4	336.2	418.7	522.4	627.7
117.5°	189.7	193.6	200.1	210.4	225.9	253.2	292.1	344.4	418.8	513.3	610.9
120°	202.4	204.9	211.3	220.8	235.0	261.8	300.4	350.0	419.1	507.8	600.7
122.5°	214.9	216.7	222.3	230.5	245.2	270.8	308.9	355.5	419.7	501.6	590.2
125°	229.9	232.8	237.1	245.4	260.0	285.6	321.4	365.1	422.0	493.8	574.7
127.5°	244.2	246.4	251.7	261.3	276.4	301.3	334.4	373.3	422.2	483.8	555.0
130°	251.2	254.1	260.0	271.4	286.0	311.0	342.5	377.9	422.7	477.6	542.6
132.5°	259.4	261.6	269.4	280.2	296.0	319.2	349.7	383.5	423.6	472.6	531.7
135°	269.4	272.5	280.3	293.6	310.1	331.5	359.4	389.7	423.9	463.6	513.9
137.5°	280.8	283.5	291.8	304.1	320.9	340.6	365.8	393.1	422.6	457.1	499.0
140°	288.9	291.0	299.3	312.3	328.4	347.1	370.9	396.2	423.1	453.2	490.8
142.5°	296.6	298.9	306.8	319.4	335.1	353.2	375.8	398.8	423.9	450.9	484.3
145°	308.7	310.7	318.2	328.9	343.4	360.5	380.8	401.9	424.6	448.8	475.7
147.5°	322.6	323.1	329.6	340.6	352.6	368.0	387.1	405.5	425.4	446.0	468.3
150°	331.4	331.8	337.8	346.9	358.3	373.0	390.2	407.4	425.4	444.1	463.7
152.5°	338.4	338.5	344.7	353.4	363.8	377.4	392.7	408.6	424.1	441.0	458.7
155°	349.5	350.3	355.0	362.8	371.4	383.1	396.4	409.7	422.2	436.3	451.2
157.5°	360.6	360.6	365.0	371.1	378.6	387.8	399.1	409.7	420.2	431.5	443.5
160°	367.5	367.5	370.6	376.1	382.4	391.0	400.3	409.7	418.3	427.7	437.9
162.5°	373.8	373.1	375.6	380.5	386.1	392.8	401.6	409.7	416.5	424.0	432.9
165°	380.8	380.8	382.4	386.3	390.2	394.9	401.9	408.2	412.9	418.3	424.6
167.5°	387.8	387.1	387.8	390.8	393.0	396.6	401.8	406.3	409.1	412.7	417.1
170°	391.0	390.2	391.0	393.3	394.9	397.2	401.1	405.0	406.6	408.9	412.1
172.5°	394.1	393.3	393.5	395.2	396.1	397.8	400.5	403.8	404.1	405.2	407.7
175°	397.2	396.4	396.4	397.2	398.0	398.0	399.6	401.9	401.1	401.1	402.7
177.5°	398.6	398.0	397.4	398.0	398.0	398.0	398.6	399.9	398.6	398.6	399.2
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332648

CATALOG NUMBER: SA4XXDIP-C1020D810U835-4F0-1E-UDD-D4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7	1234.7
2.5°	1230.4	1232.1	1233.8	1234.5	1234.3	1234.0	1233.8	1233.6
5°	1227.1	1229.6	1232.1	1233.1	1232.8	1232.5	1232.2	1231.9
7.5°	1220.6	1223.3	1226.1	1227.3	1227.0	1226.7	1226.4	1226.1
10°	1213.9	1216.7	1219.5	1220.7	1220.4	1220.1	1219.8	1219.5
12.5°	1204.6	1207.1	1209.6	1210.9	1210.8	1210.7	1210.7	1210.6
15°	1187.7	1190.4	1193.2	1194.4	1194.1	1193.8	1193.5	1193.2
17.5°	1167.0	1169.9	1172.7	1174.0	1173.7	1173.5	1173.2	1173.0
20°	1150.9	1154.0	1157.1	1158.6	1158.6	1158.6	1158.6	1158.6
22.5°	1132.1	1135.2	1138.3	1140.1	1140.6	1141.0	1141.5	1142.0
25°	1103.2	1106.5	1109.9	1111.8	1112.1	1112.4	1112.7	1113.0
27.5°	1070.6	1073.7	1076.9	1078.6	1079.0	1079.4	1079.7	1080.1
30°	1047.9	1051.2	1054.6	1056.6	1057.2	1057.8	1058.5	1059.1
32.5°	1024.5	1028.4	1032.3	1034.5	1035.1	1035.7	1036.3	1037.0
35°	987.5	991.8	996.1	998.7	999.6	1000.5	1001.5	1002.4
37.5°	948.9	953.3	957.6	960.3	961.3	962.3	963.2	964.2
40°	921.7	926.3	931.0	933.9	935.1	936.3	937.6	938.8
42.5°	895.1	900.2	905.3	908.3	909.3	910.3	911.3	912.2
45°	853.8	859.1	864.3	867.7	869.2	870.7	872.3	873.8
47.5°	810.2	815.6	821.1	824.7	826.5	828.4	830.2	832.1
50°	779.6	785.8	791.9	795.9	797.8	799.6	801.4	803.3
52.5°	748.7	754.8	761.0	764.9	766.8	768.6	770.5	772.3
55°	702.2	708.4	714.5	718.5	720.3	722.2	724.0	725.9
57.5°	653.4	660.7	668.0	672.5	674.2	676.0	677.7	679.4
60°	619.7	626.8	633.8	638.6	641.1	643.5	646.0	648.4
62.5°	586.5	593.6	600.7	605.4	607.9	610.3	612.8	615.3
65°	535.2	542.9	550.6	555.7	558.1	560.6	563.0	565.5
67.5°	484.9	492.7	500.5	505.6	508.0	510.4	512.8	515.2
70°	449.3	457.6	465.9	471.2	473.3	475.5	477.6	479.8
72.5°	415.7	423.7	431.8	437.0	439.4	441.8	444.2	446.6
75°	364.2	372.8	381.4	387.1	389.9	392.7	395.4	398.2
77.5°	316.4	325.1	333.8	339.7	342.6	345.6	348.5	351.5
80°	285.3	294.5	303.7	309.5	312.0	314.5	316.9	319.4
82.5°	254.8	264.3	273.7	279.8	282.5	285.2	287.9	290.6
85°	212.0	221.2	230.4	236.6	239.7	242.7	245.8	248.9
87.5°	178.5	187.6	196.7	202.5	205.3	208.2	210.7	213.4
90°	168.8	178.5	188.2	193.8	197.1	200.3	202.0	204.5
92.5°	301.1	271.8	256.9	246.8	240.0	238.2	238.0	240.5
95°	716.3	603.4	506.9	436.6	401.0	379.6	368.2	360.8
97.5°	983.9	946.9	878.5	802.2	748.7	704.2	683.4	669.8
100°	1064.7	1088.6	1058.6	1005.9	940.1	894.5	873.2	869.1
102.5°	1054.3	1139.9	1159.0	1140.2	1100.8	1068.7	1046.3	1043.7
105°	982.4	1125.3	1210.4	1247.5	1251.6	1247.8	1239.3	1237.0
107.5°	884.8	1036.4	1153.0	1227.6	1268.4	1288.5	1298.5	1302.7
110°	825.6	967.9	1088.4	1179.2	1237.1	1272.4	1289.0	1298.5





TEST NUMBER: P332648

CATALOG NUMBER: SA4XXDIP-C1020D810U835-4F0-1E-UDD-D4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	780.2	906.6	1020.6	1111.2	1176.7	1218.9	1241.0	1254.9
115°	732.2	835.1	933.4	1012.9	1076.8	1125.9	1153.0	1161.5
117.5°	703.8	789.8	868.1	936.2	991.3	1033.2	1061.0	1068.3
120°	689.0	767.8	836.5	896.4	943.4	980.3	1003.0	1014.1
122.5°	675.9	752.3	815.4	868.2	908.1	939.7	959.1	969.9
125°	655.6	728.7	788.5	835.3	868.4	893.0	909.7	916.2
127.5°	631.0	700.9	760.2	804.8	838.3	860.6	875.2	882.0
130°	613.0	680.3	739.0	784.1	818.0	839.4	853.8	860.3
132.5°	595.0	658.3	715.5	760.5	793.7	817.6	831.4	837.9
135°	568.1	623.8	676.4	718.9	752.0	775.7	790.1	796.6
137.5°	544.4	591.9	636.6	674.9	705.7	728.8	740.7	747.9
140°	530.7	571.5	610.7	646.3	675.2	693.9	706.4	714.2
142.5°	518.8	554.7	588.3	619.2	644.7	662.0	673.0	678.6
145°	502.6	531.0	556.3	579.7	600.5	615.0	624.1	629.2
147.5°	489.2	510.6	529.6	547.4	562.8	575.1	582.1	584.5
150°	482.4	500.4	516.1	530.1	542.7	552.8	557.5	558.3
152.5°	475.6	491.0	505.4	517.0	527.6	535.9	538.7	539.5
155°	465.2	477.8	489.5	498.9	506.7	512.9	515.3	515.3
157.5°	454.1	464.6	474.5	482.0	487.9	492.6	494.0	494.0
160°	447.3	455.9	464.5	470.7	475.4	480.1	480.9	480.9
162.5°	440.4	447.7	454.5	460.1	463.5	468.2	469.0	468.4
165°	430.8	435.5	441.0	444.9	448.0	451.2	450.4	449.6
167.5°	421.6	425.2	429.6	431.9	433.5	435.5	435.4	434.7
170°	416.0	418.3	421.5	423.8	425.4	426.1	425.4	425.4
172.5°	411.0	412.7	414.6	416.3	417.2	418.0	417.2	416.0
175°	404.3	405.0	406.6	406.6	406.6	408.2	406.6	405.0
177.5°	399.9	400.5	400.5	401.1	400.5	401.1	399.9	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0

(END OF REPORT)