

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332677

Luminaire Tested: **SA4XXDIP-C1195D365U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332677  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D365U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6382.9 lumens  
Efficiency: N/A  
Efficacy: 128.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332677  
CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332677

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	92	92	92	84	84	84	80
1	104	100	96	92	100	96	92	89	88	85	82	81	78	76	74	72	71	67
2	95	87	81	75	91	84	78	73	77	72	68	71	67	64	65	62	60	56
3	87	77	69	63	83	74	67	61	68	62	57	63	58	54	58	54	51	48
4	80	68	60	53	76	66	58	52	61	54	49	56	51	46	52	47	44	41
5	73	61	52	46	70	59	51	45	54	48	43	50	45	40	47	42	38	36
6	68	55	46	40	64	53	45	39	49	42	37	46	40	35	42	37	34	31
7	63	50	41	35	60	48	40	35	45	38	33	42	36	31	39	34	30	28
8	58	45	37	32	56	44	36	31	41	34	30	38	32	28	36	31	27	25
9	54	42	34	28	52	40	33	28	38	31	27	35	30	25	33	28	24	22
10	51	38	31	26	49	37	30	25	35	28	24	33	27	23	31	26	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16088	16088	16088
5°	16136	15943	16058
10°	16035	15813	15891
15°	15841	15588	15628
20°	15584	15309	15323
25°	15291	14991	14949
30°	14930	14618	14483
35°	14557	14226	14038
40°	14169	13782	13529
45°	13764	13345	13089
50°	13317	12955	12554
55°	12833	12451	12047
60°	12350	11885	11525
65°	11805	11347	10890
70°	11195	10629	10213
75°	10259	9763	9513
80°	9131	8759	8536
85°	7984	7688	7540



TEST NUMBER: P332677

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.7	2.9
10°-20°	528.8	8.3
20°-30°	778.3	12.2
30°-40°	904.8	14.2
40°-50°	904.8	14.2
50°-60°	791.5	12.4
60°-70°	587.8	9.2
70°-80°	333.9	5.2
80°-90°	97.7	1.5
90°-100°	30.1	0.5
100°-110°	89.3	1.4
110°-120°	151.5	2.4
120°-130°	199.8	3.1
130°-140°	224.4	3.5
140°-150°	220.5	3.5
150°-160°	185.4	2.9
160°-170°	123.4	1.9
170°-180°	43.2	0.7
0°-30°	1494.7	23.4
0°-40°	2399.5	37.6
0°-60°	4095.8	64.2
0°-90°	5115.3	80.1
90°-120°	270.9	4.2
90°-150°	915.6	14.3
90°-180°	1268.0	19.9
0°-180°	6382.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1993	1993	1993	1993	1993	
5°	1991	1984	1967	1984	1982	189
15°	1895	1888	1865	1874	1870	534
25°	1717	1705	1683	1684	1678	789
35°	1477	1465	1444	1433	1424	923
45°	1206	1194	1169	1152	1146	929
55°	912	906	885	866	856	816
65°	618	610	594	578	570	612
75°	329	321	313	307	305	350
85°	86	86	83	83	81	95
90°	1	5	8	10	11	6
95°	21	24	27	28	28	24
105°	82	83	84	85	86	87
115°	154	154	153	153	153	152
125°	224	224	224	223	223	200
135°	289	291	292	291	290	224
145°	352	353	353	353	352	220
155°	403	403	402	404	402	185
165°	438	438	437	439	438	124
175°	456	454	454	456	454	43
180°	457	457	457	457	457	



TEST NUMBER: P332677

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1997.9	1997.1	1996.2	1995.4	1994.5	1992.5	1989.4	1986.3	1983.2	1980.1	1982.9
5°	1991.2	1989.8	1988.4	1987.0	1985.6	1982.9	1979.0	1975.1	1971.2	1967.3	1971.2
7.5°	1972.7	1971.3	1969.9	1968.4	1967.0	1964.2	1959.8	1955.5	1951.2	1946.8	1950.0
10°	1956.1	1954.7	1953.3	1951.8	1950.4	1947.4	1942.8	1938.2	1933.6	1929.0	1931.8
12.5°	1934.4	1933.0	1931.5	1930.1	1928.7	1925.5	1920.7	1915.8	1910.9	1906.0	1909.1
15°	1895.4	1894.0	1892.6	1891.2	1889.7	1886.4	1881.0	1875.7	1870.4	1865.1	1867.2
17.5°	1848.5	1846.7	1844.9	1843.2	1841.4	1838.0	1832.9	1827.9	1822.9	1817.8	1819.2
20°	1814.0	1812.2	1810.4	1808.7	1806.9	1803.3	1798.0	1792.7	1787.4	1782.0	1783.1
22.5°	1776.9	1774.6	1772.3	1769.9	1767.6	1763.7	1758.4	1753.1	1747.8	1742.4	1744.4
25°	1716.6	1714.1	1711.6	1709.1	1706.6	1702.9	1697.9	1693.0	1688.0	1683.0	1683.4
27.5°	1647.6	1645.0	1642.5	1639.9	1637.4	1633.8	1629.2	1624.6	1620.0	1615.3	1614.5
30°	1601.6	1598.8	1595.9	1593.1	1590.3	1586.5	1581.9	1577.3	1572.7	1568.1	1566.7
32.5°	1553.1	1550.5	1548.0	1545.4	1542.8	1539.1	1534.2	1529.3	1524.4	1519.5	1517.8
35°	1477.1	1474.6	1472.1	1469.6	1467.1	1463.4	1458.4	1453.5	1448.5	1443.5	1441.0
37.5°	1396.9	1394.6	1392.4	1390.1	1387.8	1384.0	1378.7	1373.4	1368.0	1362.7	1360.0
40°	1344.5	1341.7	1338.8	1336.0	1333.2	1329.1	1323.8	1318.4	1313.1	1307.8	1304.2
42.5°	1288.3	1286.6	1284.9	1283.2	1281.5	1277.7	1271.8	1265.9	1260.0	1254.1	1250.0
45°	1205.6	1203.1	1200.6	1198.1	1195.7	1191.6	1185.9	1180.2	1174.5	1168.9	1165.0
47.5°	1119.0	1117.3	1115.6	1113.9	1112.2	1108.8	1103.5	1098.3	1093.0	1087.8	1083.4
50°	1060.3	1058.9	1057.4	1056.0	1054.6	1051.4	1046.4	1041.5	1036.5	1031.5	1026.6
52.5°	1002.8	1001.1	999.4	997.7	996.0	992.5	987.3	982.0	976.8	971.5	967.1
55°	911.8	910.7	909.7	908.6	907.5	904.5	899.5	894.6	889.6	884.6	880.4
57.5°	824.9	823.7	822.5	821.3	820.1	817.0	812.1	807.2	802.3	797.4	793.4
60°	764.9	763.1	761.3	759.6	757.8	754.6	750.0	745.4	740.7	736.1	732.9
62.5°	706.1	704.6	703.1	701.6	700.2	697.0	692.1	687.2	682.3	677.4	674.5
65°	618.0	616.2	614.4	612.6	610.9	608.2	604.7	601.1	597.6	594.0	590.5
67.5°	529.2	527.6	525.9	524.3	522.7	520.1	516.7	513.3	509.9	506.5	503.1
70°	474.3	471.8	469.3	466.8	464.3	461.7	458.8	456.0	453.1	450.3	447.5
72.5°	415.5	413.0	410.5	408.0	405.6	403.2	400.9	398.6	396.4	394.1	391.8
75°	328.9	327.2	325.4	323.6	321.8	320.1	318.3	316.5	314.8	313.0	311.6
77.5°	246.2	245.4	244.7	243.9	243.1	241.9	240.4	238.8	237.3	235.7	235.3
80°	196.4	195.3	194.3	193.2	192.2	191.3	190.6	189.8	189.1	188.4	187.7
82.5°	147.9	147.4	146.9	146.4	145.9	145.6	145.4	145.3	145.1	145.0	144.6
85°	86.2	86.2	86.2	86.2	86.2	85.9	85.2	84.5	83.7	83.0	83.0
87.5°	33.4	33.3	33.2	33.1	33.0	32.8	32.7	32.5	32.4	32.2	32.3
90°	1.1	1.9	2.8	3.7	4.5	5.3	5.9	6.5	7.1	7.8	8.2
92.5°	7.6	8.6	9.5	10.5	11.5	12.2	12.7	13.1	13.6	14.0	14.3
95°	21.2	21.9	22.6	23.3	24.0	24.7	25.2	25.8	26.3	26.9	27.1
97.5°	37.0	37.6	38.2	38.7	39.3	39.9	40.5	41.2	41.8	42.5	42.8
100°	49.5	49.8	50.1	50.4	50.7	51.2	51.9	52.7	53.4	54.1	54.2
102.5°	62.5	62.6	62.7	62.9	63.0	63.4	64.0	64.7	65.3	65.9	66.2
105°	82.3	82.4	82.5	82.6	82.6	82.8	83.2	83.5	83.8	84.1	84.3
107.5°	103.2	103.3	103.4	103.5	103.6	103.6	103.7	103.7	103.8	103.8	104.0
110°	117.3	117.5	117.6	117.8	117.9	118.0	117.9	117.8	117.7	117.7	117.5



TEST NUMBER: P332677

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	132.0	132.0	132.1	132.1	132.1	132.1	131.9	131.8	131.7	131.5	131.5
115°	154.1	154.1	154.1	154.1	154.1	154.0	153.8	153.7	153.5	153.4	153.3
117.5°	174.8	174.9	175.0	175.0	175.1	175.1	175.0	174.9	174.7	174.6	174.4
120°	188.7	189.0	189.3	189.6	190.0	190.0	189.8	189.5	189.3	189.1	188.7
122.5°	203.1	203.2	203.4	203.5	203.6	203.6	203.5	203.4	203.3	203.2	202.9
125°	224.4	224.4	224.4	224.4	224.4	224.3	224.3	224.2	224.1	224.0	223.9
127.5°	243.7	243.9	244.2	244.4	244.6	244.7	244.6	244.4	244.3	244.2	244.0
130°	257.3	257.5	257.7	258.0	258.2	258.3	258.3	258.3	258.3	258.3	258.2
132.5°	271.1	271.3	271.4	271.6	271.8	271.8	271.8	271.7	271.7	271.6	271.4
135°	289.4	289.9	290.3	290.8	291.3	291.5	291.5	291.5	291.5	291.5	291.4
137.5°	309.3	309.6	309.8	310.0	310.2	310.4	310.5	310.6	310.8	310.9	310.7
140°	322.6	322.8	322.9	323.1	323.3	323.3	323.3	323.3	323.3	323.3	323.3
142.5°	334.8	334.9	335.1	335.2	335.4	335.5	335.4	335.3	335.3	335.2	335.2
145°	351.6	351.9	352.2	352.5	352.9	353.1	353.1	353.2	353.3	353.4	353.3
147.5°	368.3	368.7	369.0	369.4	369.8	369.9	369.9	369.8	369.8	369.7	369.6
150°	378.5	378.8	379.1	379.4	379.7	379.9	379.9	379.9	379.9	379.9	379.9
152.5°	388.1	388.3	388.4	388.6	388.8	388.9	389.0	389.1	389.1	389.2	389.4
155°	402.8	402.8	402.8	402.8	402.8	402.8	402.7	402.6	402.6	402.5	402.8
157.5°	415.3	415.1	415.0	414.9	414.7	414.6	414.6	414.6	414.6	414.6	414.8
160°	422.6	422.5	422.5	422.4	422.3	422.2	422.2	422.1	422.0	421.9	422.2
162.5°	429.4	429.2	429.0	428.8	428.6	428.5	428.4	428.3	428.2	428.1	428.6
165°	438.5	438.3	438.1	437.8	437.6	437.4	437.2	437.1	436.9	436.8	437.2
167.5°	445.5	445.2	444.9	444.5	444.2	444.0	444.1	444.1	444.1	444.1	444.6
170°	449.5	449.1	448.7	448.3	447.9	447.8	447.8	447.9	448.0	448.1	448.5
172.5°	452.3	452.0	451.6	451.3	451.0	450.8	450.8	450.9	450.9	450.9	451.4
175°	456.2	455.8	455.4	455.0	454.6	454.4	454.3	454.2	454.2	454.1	454.6
177.5°	457.5	457.2	456.8	456.5	456.2	456.1	456.1	456.1	456.1	456.1	456.5
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9



TEST NUMBER: P332677

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8	1992.8
2.5°	1985.7	1988.6	1991.4	1992.7	1992.4	1992.1	1991.8	1991.5
5°	1975.1	1979.0	1982.9	1984.5	1983.8	1983.1	1982.4	1981.6
7.5°	1953.1	1956.2	1959.3	1960.7	1960.3	1959.8	1959.4	1959.0
10°	1934.6	1937.5	1940.3	1941.4	1940.7	1940.0	1939.2	1938.5
12.5°	1912.2	1915.3	1918.5	1919.5	1918.5	1917.5	1916.5	1915.5
15°	1869.3	1871.5	1873.6	1874.1	1873.1	1872.0	1870.9	1869.9
17.5°	1820.5	1821.9	1823.2	1823.5	1822.8	1822.1	1821.4	1820.7
20°	1784.2	1785.2	1786.3	1786.5	1785.8	1785.1	1784.4	1783.6
22.5°	1746.3	1748.2	1750.1	1750.4	1749.2	1747.9	1746.6	1745.3
25°	1683.8	1684.1	1684.5	1683.9	1682.5	1681.1	1679.7	1678.3
27.5°	1613.6	1612.8	1611.9	1610.6	1608.8	1607.1	1605.3	1603.5
30°	1565.2	1563.8	1562.4	1560.8	1559.0	1557.3	1555.5	1553.7
32.5°	1516.1	1514.4	1512.7	1511.0	1509.2	1507.4	1505.7	1503.9
35°	1438.6	1436.1	1433.6	1431.5	1429.7	1427.9	1426.1	1424.4
37.5°	1357.3	1354.6	1351.9	1349.4	1347.1	1344.7	1342.4	1340.0
40°	1300.7	1297.1	1293.6	1290.9	1289.2	1287.4	1285.6	1283.8
42.5°	1245.9	1241.8	1237.7	1235.0	1233.8	1232.6	1231.4	1230.2
45°	1161.1	1157.2	1153.3	1150.8	1149.7	1148.6	1147.6	1146.5
47.5°	1079.0	1074.6	1070.2	1066.6	1063.9	1061.2	1058.5	1055.8
50°	1021.6	1016.6	1011.7	1008.1	1006.0	1003.9	1001.7	999.6
52.5°	962.7	958.3	953.9	950.4	947.7	945.0	942.3	939.6
55°	876.1	871.9	867.6	864.4	862.3	860.2	858.0	855.9
57.5°	789.4	785.3	781.3	778.2	776.2	774.1	772.0	770.0
60°	729.7	726.6	723.4	720.9	719.1	717.3	715.6	713.8
62.5°	671.5	668.6	665.7	663.4	661.6	659.8	658.1	656.3
65°	586.9	583.4	579.8	577.2	575.4	573.6	571.8	570.1
67.5°	499.7	496.3	492.9	490.9	490.4	489.9	489.4	488.9
70°	444.6	441.8	438.9	437.0	435.9	434.9	433.8	432.7
72.5°	389.6	387.3	385.0	383.3	382.3	381.2	380.1	379.1
75°	310.1	308.7	307.3	306.4	306.1	305.7	305.3	305.0
77.5°	234.8	234.4	234.0	233.3	232.4	231.5	230.5	229.6
80°	187.0	186.3	185.6	185.1	184.7	184.3	184.0	183.6
82.5°	144.1	143.7	143.3	142.9	142.5	142.2	141.8	141.5
85°	83.0	83.0	83.0	82.9	82.5	82.1	81.8	81.4
87.5°	32.4	32.5	32.6	32.7	32.7	32.7	32.7	32.8
90°	8.7	9.2	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	14.6	14.8	15.1	15.3	15.4	15.5	15.6	15.7
95°	27.3	27.6	27.8	27.9	27.9	27.9	27.9	27.9
97.5°	43.0	43.3	43.6	43.7	43.7	43.7	43.7	43.7
100°	54.4	54.5	54.7	54.8	54.8	54.8	54.8	54.8
102.5°	66.4	66.6	66.8	67.0	67.0	67.1	67.1	67.2
105°	84.6	84.8	85.0	85.3	85.5	85.8	86.0	86.2
107.5°	104.3	104.5	104.7	104.8	104.8	104.8	104.8	104.7
110°	117.4	117.2	117.0	117.1	117.3	117.6	117.8	118.0





TEST NUMBER: P332677

CATALOG NUMBER: SA4XXDIP-C1195D365U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	131.5	131.4	131.4	131.4	131.5	131.5	131.5	131.6
115°	153.2	153.1	153.0	153.0	152.9	152.8	152.7	152.7
117.5°	174.1	173.8	173.6	173.4	173.2	173.0	172.9	172.7
120°	188.3	187.9	187.5	187.4	187.5	187.7	187.8	188.0
122.5°	202.7	202.4	202.1	201.8	201.6	201.3	201.0	200.7
125°	223.7	223.6	223.4	223.2	223.1	222.9	222.8	222.6
127.5°	243.9	243.7	243.5	243.4	243.3	243.2	243.0	242.9
130°	258.0	257.8	257.7	257.4	257.1	256.8	256.5	256.2
132.5°	271.3	271.1	271.0	270.8	270.7	270.6	270.5	270.3
135°	291.2	291.1	290.9	290.7	290.5	290.2	290.0	289.8
137.5°	310.5	310.3	310.1	310.0	310.0	310.1	310.1	310.2
140°	323.2	323.1	323.0	322.9	322.9	322.8	322.7	322.6
142.5°	335.2	335.2	335.1	335.1	335.1	335.1	335.1	335.1
145°	353.2	353.1	353.1	352.9	352.7	352.4	352.2	352.0
147.5°	369.6	369.5	369.4	369.4	369.3	369.2	369.1	369.1
150°	379.9	379.9	379.9	379.8	379.8	379.7	379.6	379.5
152.5°	389.6	389.8	390.0	389.9	389.7	389.5	389.3	389.1
155°	403.1	403.4	403.7	403.7	403.4	403.1	402.8	402.5
157.5°	415.0	415.3	415.5	415.5	415.2	415.0	414.7	414.4
160°	422.4	422.6	422.9	422.8	422.4	422.0	421.6	421.2
162.5°	429.0	429.4	429.8	429.8	429.5	429.1	428.7	428.3
165°	437.7	438.2	438.6	438.7	438.4	438.1	437.8	437.5
167.5°	445.1	445.5	446.0	446.0	445.5	445.0	444.5	444.0
170°	449.0	449.5	450.0	449.9	449.4	448.8	448.3	447.7
172.5°	452.0	452.5	453.0	453.0	452.5	451.9	451.4	450.8
175°	455.2	455.7	456.3	456.3	455.7	455.2	454.6	454.1
177.5°	456.9	457.4	457.8	457.8	457.3	456.8	456.3	455.8
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9

(END OF REPORT)