

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332679

Luminaire Tested: **SA4XXDIP-C1195D590U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332679  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7679.0 lumens  
Efficiency: N/A  
Efficacy: 139.4 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332679  
CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	69		
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	66	64	63	59		
2	94	86	80	75	88	82	76	71	73	69	65	65	62	59	58	56	54	50		
3	86	76	69	63	81	72	65	60	65	60	55	58	54	50	52	49	46	43		
4	78	68	59	53	74	64	57	51	58	52	47	52	47	44	47	43	40	37		
5	72	60	52	46	68	58	50	44	52	46	41	47	42	38	42	38	35	32		
6	67	54	46	40	63	52	44	39	47	41	36	43	37	34	38	34	31	28		
7	62	49	41	36	58	47	40	34	43	37	32	39	34	30	35	31	28	25		
8	58	45	37	32	54	43	36	31	39	33	29	36	30	27	32	28	25	23		
9	54	41	34	28	51	39	32	28	36	30	26	33	28	24	30	26	22	20		
10	50	38	31	26	48	36	29	25	33	27	23	30	25	22	28	24	20	19		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15560	15560	15560	15560
5°	18323	15600	13768	15600
10°	21939	15531	12396	15531
15°	25957	15374	11384	15374
20°	28905	15214	10481	15214
25°	29372	14978	9857	14978
30°	24993	14752	9660	14752
35°	19215	14384	9662	14384
40°	14977	13951	9844	13951
45°	12488	13300	10009	13300
50°	10991	12504	10349	12504
55°	10069	11553	10766	11553
60°	9436	10700	11267	10700
65°	8785	9746	11683	9746
70°	8028	8802	11948	8802
75°	7171	7745	11803	7745
80°	6011	6346	11432	6346
85°	4437	4585	10948	4585



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	187.8	2.4
10°-20°	578.8	7.5
20°-30°	917.8	12.0
30°-40°	1021.3	13.3
40°-50°	929.7	12.1
50°-60°	759.7	9.9
60°-70°	542.4	7.1
70°-80°	298.7	3.9
80°-90°	83.7	1.1
90°-100°	26.1	0.3
100°-110°	166.3	2.2
110°-120°	318.2	4.1
120°-130°	403.9	5.3
130°-140°	432.1	5.6
140°-150°	404.1	5.3
150°-160°	325.9	4.2
160°-170°	210.2	2.7
170°-180°	72.4	0.9
0°-30°	1684.3	21.9
0°-40°	2705.6	35.2
0°-60°	4395.1	57.2
0°-90°	5319.9	69.3
90°-120°	510.6	6.6
90°-150°	1750.6	22.8
90°-180°	2359.0	30.7
0°-180°	7679.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1927	1927	1927	1927	1927	
5°	2261	1925	1699	1925	2261	230
15°	3106	1840	1362	1840	3106	878
25°	3297	1682	1107	1682	3297	1454
35°	1950	1460	980	1460	1950	1238
45°	1094	1165	877	1165	1094	862
55°	715	821	765	821	715	646
65°	460	510	612	510	460	455
75°	230	248	378	248	230	244
85°	48	50	118	50	48	59
90°	17	2	17	2	17	9
95°	16	31	16	31	16	13
105°	163	172	163	172	163	142
115°	323	321	323	321	323	320
125°	454	451	454	451	454	404
135°	563	559	563	559	563	433
145°	648	645	648	645	648	405
155°	706	707	706	707	706	326
165°	742	746	742	746	742	210
175°	758	763	758	763	758	72
180°	763	763	763	763	763	



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	2051.3	2050.6	2044.3	2043.0	2038.5	2032.8	2031.5	2021.3	2000.8	1991.2	1988.7
5°	2261.1	2277.1	2256.3	2252.3	2249.9	2223.6	2210.0	2194.0	2157.3	2135.8	2119.0
7.5°	2511.5	2513.4	2504.3	2497.0	2476.7	2453.7	2419.2	2382.5	2338.7	2293.2	2258.9
10°	2676.3	2682.7	2672.3	2670.7	2630.0	2604.4	2553.3	2510.2	2460.7	2405.6	2355.3
12.5°	2850.0	2841.1	2835.8	2801.6	2794.1	2747.5	2688.1	2643.7	2567.4	2504.0	2437.1
15°	3105.8	3088.3	3077.1	3030.0	3006.8	2942.1	2879.1	2830.4	2730.6	2635.6	2563.7
17.5°	3255.9	3273.5	3247.6	3228.3	3168.4	3123.1	3058.6	2956.4	2878.3	2760.3	2669.6
20°	3364.5	3366.1	3351.7	3331.8	3284.7	3227.2	3156.9	3045.1	2951.7	2834.4	2709.8
22.5°	3393.9	3394.2	3388.1	3369.5	3333.8	3287.2	3216.3	3123.1	3009.9	2882.3	2757.7
25°	3297.4	3294.2	3301.4	3322.2	3308.6	3294.2	3253.5	3184.1	3078.7	2943.7	2809.6
27.5°	2939.1	2961.1	3001.7	3052.8	3102.0	3139.5	3150.1	3135.8	3070.5	2959.6	2819.0
30°	2681.1	2708.2	2738.6	2789.6	2888.7	2945.3	3007.6	3054.7	3028.4	2939.8	2808.8
32.5°	2397.5	2404.2	2449.2	2507.3	2598.0	2707.1	2805.8	2901.4	2933.2	2886.7	2777.5
35°	1949.7	1960.9	2009.6	2067.1	2178.1	2311.4	2459.9	2592.4	2701.8	2745.7	2689.8
37.5°	1591.1	1623.2	1657.5	1719.3	1817.0	1937.1	2091.4	2262.9	2425.9	2535.1	2553.6
40°	1421.2	1441.1	1465.9	1513.0	1596.0	1714.2	1846.7	2043.1	2216.4	2372.9	2424.0
42.5°	1287.0	1298.7	1313.9	1356.5	1419.7	1537.3	1658.3	1831.1	2005.0	2192.1	2277.7
45°	1093.8	1105.8	1131.3	1156.1	1204.0	1285.4	1398.0	1540.1	1715.0	1895.4	2053.5
47.5°	954.3	961.9	977.1	1003.6	1044.3	1098.0	1189.6	1308.3	1470.4	1645.5	1814.0
50°	875.1	881.4	893.4	917.4	948.5	996.4	1071.5	1182.4	1309.4	1485.8	1651.1
52.5°	812.5	815.0	823.8	840.1	864.8	905.1	966.7	1058.5	1176.5	1333.8	1498.5
55°	715.4	718.6	726.6	738.5	760.1	785.6	832.7	901.4	1004.4	1140.9	1283.8
57.5°	635.5	637.8	644.5	649.1	666.8	687.6	723.8	772.9	850.9	966.7	1094.3
60°	584.4	582.8	590.8	594.8	606.8	624.4	652.3	699.4	767.3	860.7	978.1
62.5°	534.6	532.4	539.1	544.4	551.2	566.2	589.1	626.0	681.0	765.5	866.9
65°	459.9	456.7	460.7	467.1	473.5	481.4	498.2	530.9	574.9	635.5	713.0
67.5°	384.8	388.2	388.8	392.0	395.7	406.6	418.0	441.2	472.2	520.7	586.4
70°	340.1	340.9	344.1	344.1	346.5	356.1	365.7	379.2	409.6	454.3	507.8
72.5°	295.4	298.8	297.5	300.0	301.8	308.2	315.2	328.1	354.0	387.2	432.4
75°	229.9	232.3	232.3	233.1	235.5	237.9	243.5	253.1	271.5	296.2	327.3
77.5°	167.7	168.0	169.1	172.0	172.0	175.8	180.0	187.6	196.7	213.7	232.7
80°	129.3	130.9	130.1	131.7	131.7	134.9	136.5	146.1	150.1	161.3	176.4
82.5°	94.9	96.4	96.3	98.5	99.8	100.4	102.7	106.5	110.5	120.4	126.6
85°	47.9	49.5	47.9	49.5	51.9	52.7	55.1	55.9	59.1	61.5	67.1
87.5°	17.5	19.3	19.3	19.9	21.1	21.6	22.1	21.3	23.7	24.2	26.6
90°	17.1	16.9	16.6	16.4	16.1	15.6	14.8	14.1	13.3	12.5	11.5
92.5°	15.7	15.7	15.6	15.6	15.5	15.1	14.4	13.6	12.9	12.1	11.1
95°	16.5	16.4	16.3	16.2	16.0	15.6	14.8	14.1	13.3	12.5	12.4
97.5°	16.0	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.1	15.1	29.2
100°	16.0	15.8	15.7	15.6	15.5	16.5	18.6	20.8	22.9	25.1	42.6
102.5°	16.4	16.4	16.4	16.4	16.3	27.9	51.2	74.4	97.7	120.9	123.2
105°	162.6	167.1	171.7	176.3	180.8	182.5	181.4	180.3	179.1	178.0	177.3
107.5°	226.6	226.1	225.6	225.1	224.6	224.1	223.6	223.0	222.5	221.9	221.0
110°	254.4	254.0	253.6	253.3	252.9	252.6	252.3	252.1	251.8	251.6	250.8



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	282.2	281.8	281.3	280.8	280.3	280.1	280.2	280.2	280.3	280.3	280.0
115°	322.9	322.9	322.9	322.9	322.9	322.7	322.5	322.2	322.0	321.7	321.8
117.5°	364.2	364.2	364.3	364.3	364.4	364.4	364.5	364.5	364.6	364.6	364.3
120°	390.2	390.4	390.7	390.9	391.2	391.2	390.9	390.7	390.4	390.2	390.3
122.5°	415.7	416.0	416.2	416.5	416.7	416.8	416.6	416.5	416.3	416.2	416.0
125°	454.1	453.9	453.8	453.7	453.6	453.3	452.9	452.5	452.2	451.8	452.0
127.5°	487.7	487.8	487.9	488.0	488.1	488.2	488.3	488.4	488.4	488.5	487.9
130°	510.5	510.5	510.5	510.5	510.5	510.5	510.3	510.2	510.1	510.0	509.6
132.5°	531.5	531.6	531.7	531.8	531.9	531.9	531.8	531.7	531.5	531.4	530.9
135°	563.0	562.8	562.5	562.2	562.0	561.7	561.5	561.2	561.0	560.7	560.2
137.5°	589.9	590.0	590.1	590.2	590.2	590.1	589.9	589.6	589.3	589.0	588.5
140°	608.6	608.5	608.4	608.3	608.1	607.9	607.5	607.1	606.7	606.4	606.1
142.5°	624.2	624.1	624.1	624.1	624.1	623.9	623.6	623.3	623.1	622.8	622.6
145°	648.0	647.8	647.5	647.2	647.0	646.8	646.7	646.5	646.4	646.3	646.3
147.5°	667.7	667.6	667.5	667.4	667.2	667.1	667.0	666.9	666.8	666.7	666.8
150°	680.5	680.4	680.3	680.1	680.0	679.9	679.9	679.9	679.9	679.9	680.1
152.5°	691.5	691.5	691.6	691.7	691.8	691.7	691.5	691.3	691.1	690.9	691.1
155°	706.2	706.6	706.9	707.3	707.7	707.6	707.1	706.6	706.1	705.6	706.0
157.5°	718.5	719.2	719.8	720.5	721.1	721.1	720.5	719.8	719.2	718.5	718.9
160°	726.7	727.5	728.2	729.0	729.8	729.8	729.0	728.2	727.5	726.7	726.8
162.5°	733.1	734.0	734.8	735.7	736.6	736.6	735.8	735.1	734.3	733.6	733.7
165°	742.1	743.3	744.4	745.5	746.7	746.8	745.7	744.7	743.7	742.7	742.7
167.5°	748.9	750.1	751.4	752.7	753.9	754.0	752.9	751.8	750.7	749.5	749.6
170°	753.0	754.2	755.5	756.8	758.0	758.2	757.1	756.1	755.1	754.1	754.0
172.5°	755.2	756.6	758.0	759.4	760.7	760.9	759.9	758.9	757.9	756.8	756.7
175°	758.1	759.6	761.1	762.7	764.2	764.4	763.2	762.1	760.9	759.8	759.7
177.5°	759.9	761.1	762.4	763.6	764.8	765.0	764.2	763.4	762.6	761.7	761.5
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1989.3	1980.4	1974.0	1968.9	1954.8	1946.5	1940.1	1931.2	1921.0	1910.1	1896.7
5°	2102.2	2075.1	2055.1	2024.8	1996.0	1972.1	1947.3	1925.0	1897.8	1868.3	1846.7
7.5°	2220.9	2180.5	2128.7	2083.9	2033.4	1989.5	1950.2	1910.0	1868.1	1827.6	1790.4
10°	2296.2	2244.3	2186.8	2119.0	2055.1	1998.4	1945.7	1894.6	1845.1	1795.6	1753.3
12.5°	2377.4	2312.7	2227.7	2148.4	2076.8	2001.0	1937.4	1874.8	1815.1	1763.1	1713.7
15°	2486.3	2392.8	2294.6	2188.4	2094.2	2005.6	1918.6	1839.5	1772.5	1703.8	1655.9
17.5°	2553.2	2437.6	2325.3	2214.3	2100.3	1988.5	1894.6	1803.5	1719.5	1651.3	1590.9
20°	2597.2	2482.3	2342.5	2231.6	2095.8	1980.9	1872.3	1770.9	1683.1	1610.4	1548.1
22.5°	2635.6	2502.7	2363.0	2216.9	2081.8	1959.8	1841.0	1738.9	1649.2	1572.7	1513.0
25°	2656.3	2503.8	2352.1	2206.8	2053.5	1909.0	1801.2	1681.5	1585.6	1505.0	1441.1
27.5°	2658.6	2495.5	2323.9	2162.4	2004.2	1869.6	1733.5	1626.5	1527.0	1441.8	1380.5
30°	2651.5	2481.5	2297.0	2122.2	1963.3	1817.2	1699.0	1582.5	1481.1	1396.4	1332.5
32.5°	2629.2	2452.1	2262.5	2077.5	1912.8	1769.9	1647.9	1537.1	1438.3	1354.9	1287.8
35°	2564.5	2389.6	2187.6	1995.2	1826.8	1682.3	1572.1	1459.5	1360.5	1281.5	1216.8
37.5°	2463.4	2305.3	2100.0	1900.9	1735.4	1590.3	1481.1	1379.3	1290.1	1209.8	1143.5
40°	2375.3	2236.4	2030.4	1836.3	1657.5	1519.4	1417.2	1323.8	1235.1	1159.3	1096.2
42.5°	2273.7	2152.7	1962.7	1757.1	1584.7	1445.9	1346.3	1262.4	1178.9	1108.8	1045.8
45°	2092.6	2012.8	1834.0	1643.9	1464.3	1333.3	1238.3	1164.9	1094.6	1026.0	973.3
47.5°	1884.4	1844.8	1694.2	1513.8	1343.2	1214.2	1131.8	1064.0	1002.3	944.2	897.7
50°	1744.5	1725.4	1595.2	1421.2	1258.3	1136.9	1053.9	995.6	942.9	891.8	847.9
52.5°	1606.6	1605.9	1488.6	1329.2	1178.5	1061.6	979.2	924.7	879.1	837.5	798.1
55°	1395.6	1418.0	1326.2	1184.0	1049.1	943.7	869.5	820.8	788.8	754.5	725.0
57.5°	1201.9	1239.0	1163.3	1038.1	925.5	828.4	763.8	727.2	693.2	672.4	650.9
60°	1075.5	1110.6	1051.5	946.1	839.9	756.9	695.4	662.7	633.1	618.8	603.6
62.5°	963.0	994.3	950.6	852.9	760.7	680.9	629.0	597.5	577.6	561.9	551.9
65°	802.4	828.8	791.2	720.2	641.1	577.3	534.9	510.2	491.0	484.6	473.5
67.5°	648.6	672.6	652.3	591.9	528.5	480.2	447.1	423.3	412.0	406.4	398.4
70°	557.3	581.2	559.7	507.0	458.3	417.6	386.4	372.9	360.9	358.5	347.3
72.5°	480.0	496.3	474.7	433.5	391.9	357.5	333.4	319.2	313.0	308.7	302.6
75°	360.1	374.5	360.1	328.1	298.6	274.7	253.9	248.3	241.1	238.7	234.7
77.5°	254.9	267.3	256.3	236.3	214.3	195.8	184.6	177.4	175.8	171.7	173.6
80°	194.8	202.8	192.4	178.8	161.3	148.5	140.5	136.5	131.7	130.1	133.3
82.5°	139.9	143.4	138.1	129.0	115.9	107.6	102.2	97.6	96.6	96.9	96.9
85°	72.7	71.9	71.1	63.1	59.1	53.5	50.3	49.5	48.7	50.3	51.9
87.5°	26.4	26.8	26.0	23.2	21.0	18.8	17.9	16.9	17.9	18.8	19.7
90°	10.5	9.5	8.5	7.3	5.9	4.5	3.1	1.7	3.1	4.5	5.9
92.5°	10.1	9.1	8.0	7.5	7.4	7.3	7.3	7.2	7.3	7.3	7.4
95°	12.3	12.2	12.0	14.1	18.4	22.8	27.1	31.4	27.1	22.8	18.4
97.5°	43.4	57.5	71.6	77.4	74.7	72.0	69.3	66.6	69.3	72.0	74.7
100°	60.1	77.6	95.1	102.7	100.4	98.1	95.8	93.5	95.8	98.1	100.4
102.5°	125.5	127.8	130.1	130.4	128.7	127.0	125.3	123.7	125.3	127.0	128.7
105°	176.7	176.1	175.4	174.7	174.0	173.2	172.5	171.7	172.5	173.2	174.0
107.5°	220.2	219.3	218.4	217.8	217.4	217.1	216.7	216.3	216.7	217.1	217.4
110°	250.0	249.3	248.5	247.9	247.6	247.2	246.8	246.4	246.8	247.2	247.6





TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	279.6	279.2	278.9	278.4	277.7	277.0	276.3	275.6	276.3	277.0	277.7
115°	322.0	322.1	322.2	322.1	321.7	321.3	321.0	320.6	321.0	321.3	321.7
117.5°	364.1	363.8	363.5	363.1	362.6	362.1	361.6	361.1	361.6	362.1	362.6
120°	390.4	390.6	390.7	390.5	390.0	389.5	389.0	388.5	389.0	389.5	390.0
122.5°	415.8	415.7	415.5	415.2	414.9	414.6	414.3	414.0	414.3	414.6	414.9
125°	452.3	452.5	452.8	452.7	452.2	451.7	451.1	450.6	451.1	451.7	452.2
127.5°	487.3	486.8	486.2	485.8	485.7	485.6	485.4	485.3	485.4	485.6	485.7
130°	509.2	508.8	508.4	508.2	508.1	507.9	507.8	507.7	507.8	507.9	508.1
132.5°	530.4	530.0	529.5	529.1	528.9	528.7	528.4	528.2	528.4	528.7	528.9
135°	559.7	559.2	558.7	558.5	558.6	558.8	558.9	559.0	558.9	558.8	558.6
137.5°	587.9	587.3	586.8	586.5	586.4	586.4	586.3	586.3	586.3	586.4	586.4
140°	605.9	605.6	605.3	605.1	604.8	604.6	604.3	604.1	604.3	604.6	604.8
142.5°	622.5	622.3	622.2	621.9	621.4	621.0	620.5	620.1	620.5	621.0	621.4
145°	646.3	646.3	646.3	646.1	645.7	645.3	645.0	644.6	645.0	645.3	645.7
147.5°	667.0	667.1	667.2	666.9	666.2	665.5	664.8	664.1	664.8	665.5	666.2
150°	680.2	680.3	680.5	680.3	679.8	679.3	678.7	678.2	678.7	679.3	679.8
152.5°	691.4	691.6	691.8	691.7	691.3	690.9	690.5	690.1	690.5	690.9	691.3
155°	706.4	706.8	707.1	707.3	707.1	707.0	706.9	706.8	706.9	707.0	707.1
157.5°	719.4	719.8	720.2	720.5	720.6	720.6	720.7	720.8	720.7	720.6	720.6
160°	727.0	727.1	727.2	727.5	727.9	728.2	728.6	729.0	728.6	728.2	727.9
162.5°	733.8	733.9	734.1	734.4	734.9	735.3	735.8	736.3	735.8	735.3	734.9
165°	742.7	742.7	742.7	743.0	743.6	744.3	744.9	745.5	744.9	744.3	743.6
167.5°	749.7	749.8	749.8	750.2	750.9	751.5	752.2	752.8	752.2	751.5	750.9
170°	753.8	753.7	753.6	753.9	754.7	755.4	756.2	757.0	756.2	755.4	754.7
172.5°	756.6	756.5	756.3	756.7	757.4	758.2	758.9	759.7	758.9	758.2	757.4
175°	759.6	759.4	759.3	759.6	760.4	761.1	761.9	762.7	761.9	761.1	760.4
177.5°	761.3	761.1	760.9	761.2	761.9	762.6	763.3	764.0	763.3	762.6	761.9
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1890.3	1884.6	1876.3	1864.8	1855.2	1845.0	1842.4	1838.6	1846.2	1839.9	1837.9
5°	1828.4	1811.6	1790.0	1765.3	1750.9	1730.2	1726.2	1718.2	1710.2	1709.4	1701.4
7.5°	1762.7	1738.1	1709.9	1684.6	1661.3	1638.7	1623.8	1620.6	1608.8	1601.9	1593.9
10°	1720.6	1690.2	1657.5	1633.6	1606.4	1582.5	1565.7	1556.1	1548.1	1539.3	1531.4
12.5°	1670.8	1638.5	1611.5	1585.6	1553.4	1535.2	1507.6	1491.0	1489.4	1489.5	1468.8
15°	1612.8	1580.9	1539.3	1502.6	1485.0	1449.9	1434.7	1415.6	1403.6	1391.6	1382.1
17.5°	1546.5	1506.8	1474.3	1432.2	1398.7	1370.7	1350.8	1339.3	1321.2	1304.3	1292.0
20°	1505.0	1462.7	1428.4	1383.6	1346.9	1312.6	1295.8	1279.9	1266.3	1251.9	1238.3
22.5°	1462.8	1418.6	1376.6	1333.2	1299.0	1262.8	1246.6	1224.9	1212.0	1204.0	1190.4
25°	1396.4	1348.5	1300.6	1259.1	1224.0	1192.0	1170.5	1153.7	1139.3	1132.9	1124.2
27.5°	1324.2	1276.7	1230.4	1183.2	1143.3	1120.2	1102.9	1090.3	1082.0	1073.5	1069.6
30°	1278.3	1228.8	1179.3	1135.3	1098.6	1075.5	1059.5	1050.7	1044.3	1040.3	1036.3
32.5°	1231.6	1182.8	1130.7	1090.6	1057.7	1037.1	1025.0	1016.2	1013.0	1011.6	1010.2
35°	1156.9	1107.4	1059.5	1023.6	992.4	984.4	974.1	969.3	967.7	973.3	975.7
37.5°	1084.6	1038.6	994.5	959.7	939.3	927.6	924.1	924.2	930.0	934.9	940.7
40°	1037.9	993.2	951.7	921.4	902.2	895.0	893.4	897.4	903.8	909.4	915.8
42.5°	992.6	948.5	910.8	882.4	869.0	862.4	863.4	867.4	876.3	883.2	892.8
45°	922.2	885.4	848.7	825.6	814.4	816.0	816.0	823.2	831.9	842.3	852.7
47.5°	855.9	818.9	788.7	769.2	763.4	762.0	766.5	775.9	788.5	801.3	815.8
50°	811.2	776.1	749.7	732.1	725.8	728.2	734.5	743.3	758.5	774.5	789.6
52.5°	765.8	733.9	709.5	693.2	688.7	693.0	699.4	713.3	726.6	743.8	762.2
55°	695.4	668.3	649.1	637.1	635.5	637.9	645.1	660.3	679.4	701.0	718.6
57.5°	625.3	602.6	585.1	576.8	577.6	579.8	591.6	609.7	630.1	653.1	675.8
60°	578.0	557.3	542.9	536.5	537.3	542.1	556.5	573.3	598.8	621.2	645.1
62.5°	533.3	515.1	501.4	495.7	494.5	505.1	518.8	536.2	561.8	586.7	612.5
65°	461.5	447.1	435.9	432.7	435.1	443.1	460.7	483.8	505.4	531.7	558.9
67.5°	391.2	379.4	371.7	373.2	376.1	387.9	402.6	422.5	447.0	474.3	501.1
70°	346.5	335.3	328.9	329.7	334.5	348.9	361.7	381.6	408.0	435.9	458.3
72.5°	300.5	293.2	287.4	290.8	295.6	305.5	321.4	341.4	364.6	390.6	414.2
75°	230.7	230.7	227.5	229.9	237.1	246.7	258.7	279.4	302.6	323.4	342.5
77.5°	171.2	169.4	171.5	174.4	178.5	189.9	203.6	218.4	235.9	256.6	272.4
80°	130.9	131.7	135.7	140.5	142.1	150.9	165.3	178.8	192.4	210.0	225.2
82.5°	98.4	99.2	101.2	107.3	108.9	118.3	127.6	141.2	153.5	165.3	177.9
85°	53.5	53.5	57.5	59.9	63.9	70.3	75.8	83.8	95.0	103.0	115.0
87.5°	21.9	22.1	24.9	26.4	28.5	31.9	33.3	40.5	43.2	46.6	52.4
90°	7.3	8.5	9.5	10.5	11.5	12.5	13.3	14.1	14.8	15.6	16.1
92.5°	7.5	8.0	9.1	10.1	11.1	12.1	12.9	13.6	14.4	15.1	15.5
95°	14.1	12.0	12.2	12.3	12.4	12.5	13.3	14.1	14.8	15.6	16.0
97.5°	77.4	71.6	57.5	43.4	29.2	15.1	15.1	15.2	15.3	15.4	15.5
100°	102.7	95.1	77.6	60.1	42.6	25.1	22.9	20.8	18.6	16.5	15.5
102.5°	130.4	130.1	127.8	125.5	123.2	120.9	97.7	74.4	51.2	27.9	16.3
105°	174.7	175.4	176.1	176.7	177.3	178.0	179.1	180.3	181.4	182.5	180.8
107.5°	217.8	218.4	219.3	220.2	221.0	221.9	222.5	223.0	223.6	224.1	224.6
110°	247.9	248.5	249.3	250.0	250.8	251.6	251.8	252.1	252.3	252.6	252.9



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	278.4	278.9	279.2	279.6	280.0	280.3	280.3	280.2	280.2	280.1	280.3
115°	322.1	322.2	322.1	322.0	321.8	321.7	322.0	322.2	322.5	322.7	322.9
117.5°	363.1	363.5	363.8	364.1	364.3	364.6	364.6	364.5	364.5	364.4	364.4
120°	390.5	390.7	390.6	390.4	390.3	390.2	390.4	390.7	390.9	391.2	391.2
122.5°	415.2	415.5	415.7	415.8	416.0	416.2	416.3	416.5	416.6	416.8	416.7
125°	452.7	452.8	452.5	452.3	452.0	451.8	452.2	452.5	452.9	453.3	453.6
127.5°	485.8	486.2	486.8	487.3	487.9	488.5	488.4	488.4	488.3	488.2	488.1
130°	508.2	508.4	508.8	509.2	509.6	510.0	510.1	510.2	510.3	510.5	510.5
132.5°	529.1	529.5	530.0	530.4	530.9	531.4	531.5	531.7	531.8	531.9	531.9
135°	558.5	558.7	559.2	559.7	560.2	560.7	561.0	561.2	561.5	561.7	562.0
137.5°	586.5	586.8	587.3	587.9	588.5	589.0	589.3	589.6	589.9	590.1	590.2
140°	605.1	605.3	605.6	605.9	606.1	606.4	606.7	607.1	607.5	607.9	608.1
142.5°	621.9	622.2	622.3	622.5	622.6	622.8	623.1	623.3	623.6	623.9	624.1
145°	646.1	646.3	646.3	646.3	646.3	646.3	646.4	646.5	646.7	646.8	647.0
147.5°	666.9	667.2	667.1	667.0	666.8	666.7	666.8	666.9	667.0	667.1	667.2
150°	680.3	680.5	680.3	680.2	680.1	679.9	679.9	679.9	679.9	679.9	680.0
152.5°	691.7	691.8	691.6	691.4	691.1	690.9	691.1	691.3	691.5	691.7	691.8
155°	707.3	707.1	706.8	706.4	706.0	705.6	706.1	706.6	707.1	707.6	707.7
157.5°	720.5	720.2	719.8	719.4	718.9	718.5	719.2	719.8	720.5	721.1	721.1
160°	727.5	727.2	727.1	727.0	726.8	726.7	727.5	728.2	729.0	729.8	729.8
162.5°	734.4	734.1	733.9	733.8	733.7	733.6	734.3	735.1	735.8	736.6	736.6
165°	743.0	742.7	742.7	742.7	742.7	742.7	743.7	744.7	745.7	746.8	746.7
167.5°	750.2	749.8	749.8	749.7	749.6	749.5	750.7	751.8	752.9	754.0	753.9
170°	753.9	753.6	753.7	753.8	754.0	754.1	755.1	756.1	757.1	758.2	758.0
172.5°	756.7	756.3	756.5	756.6	756.7	756.8	757.9	758.9	759.9	760.9	760.7
175°	759.6	759.3	759.4	759.6	759.7	759.8	760.9	762.1	763.2	764.4	764.2
177.5°	761.2	760.9	761.1	761.3	761.5	761.7	762.6	763.4	764.2	765.0	764.8
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1836.7	1835.4	1830.9	1830.3	1830.9	1835.4	1836.7	1837.9	1839.9	1846.2	1838.6
5°	1696.6	1692.6	1690.2	1699.0	1690.2	1692.6	1696.6	1701.4	1709.4	1710.2	1718.2
7.5°	1591.1	1587.9	1580.9	1578.6	1580.9	1587.9	1591.1	1593.9	1601.9	1608.8	1620.6
10°	1523.4	1520.2	1513.8	1512.2	1513.8	1520.2	1523.4	1531.4	1539.3	1548.1	1556.1
12.5°	1458.2	1451.8	1450.6	1452.2	1450.6	1451.8	1458.2	1468.8	1489.5	1489.4	1491.0
15°	1371.7	1368.5	1359.7	1362.1	1359.7	1368.5	1371.7	1382.1	1391.6	1403.6	1415.6
17.5°	1286.4	1282.6	1271.9	1281.3	1271.9	1282.6	1286.4	1292.0	1304.3	1321.2	1339.3
20°	1232.7	1226.4	1220.8	1220.0	1220.8	1226.4	1232.7	1238.3	1251.9	1266.3	1279.9
22.5°	1181.6	1175.9	1175.4	1170.2	1175.4	1175.9	1181.6	1190.4	1204.0	1212.0	1224.9
25°	1117.8	1112.2	1110.6	1106.6	1110.6	1112.2	1117.8	1124.2	1132.9	1139.3	1153.7
27.5°	1068.8	1066.0	1063.2	1064.4	1063.2	1066.0	1068.8	1069.6	1073.5	1082.0	1090.3
30°	1038.7	1037.9	1036.3	1036.3	1036.3	1037.9	1038.7	1036.3	1040.3	1044.3	1050.7
32.5°	1013.8	1013.7	1014.6	1014.6	1014.6	1013.7	1013.8	1010.2	1011.6	1013.0	1016.2
35°	978.9	981.2	982.8	980.4	982.8	981.2	978.9	975.7	973.3	967.7	969.3
37.5°	947.2	949.6	951.9	954.6	951.9	949.6	947.2	940.7	934.9	930.0	924.2
40°	923.0	928.6	930.1	934.1	930.1	928.6	923.0	915.8	909.4	903.8	897.4
42.5°	900.0	906.2	910.3	911.1	910.3	906.2	900.0	892.8	883.2	876.3	867.4
45°	864.7	871.1	876.7	876.7	876.7	871.1	864.7	852.7	842.3	831.9	823.2
47.5°	828.1	837.4	843.0	844.4	843.0	837.4	828.1	815.8	801.3	788.5	775.9
50°	803.2	814.4	820.0	824.0	820.0	814.4	803.2	789.6	774.5	758.5	743.3
52.5°	778.9	790.1	797.6	799.7	797.6	790.1	778.9	762.2	743.8	726.6	713.3
55°	736.9	752.9	761.7	764.9	761.7	752.9	736.9	718.6	701.0	679.4	660.3
57.5°	697.3	712.0	722.2	724.6	722.2	712.0	697.3	675.8	653.1	630.1	609.7
60°	666.7	682.6	695.4	697.8	695.4	682.6	666.7	645.1	621.2	598.8	573.3
62.5°	635.4	652.0	663.5	669.7	663.5	652.0	635.4	612.5	586.7	561.8	536.2
65°	581.2	598.0	609.2	611.6	609.2	598.0	581.2	558.9	531.7	505.4	483.8
67.5°	522.2	538.9	546.3	550.9	546.3	538.9	522.2	501.1	474.3	447.0	422.5
70°	480.6	494.2	502.2	506.2	502.2	494.2	480.6	458.3	435.9	408.0	381.6
72.5°	433.4	447.6	456.9	457.6	456.9	447.6	433.4	414.2	390.6	364.6	341.4
75°	360.9	373.7	378.4	378.4	378.4	373.7	360.9	342.5	323.4	302.6	279.4
77.5°	285.7	292.2	298.3	299.6	298.3	292.2	285.7	272.4	256.6	235.9	218.4
80°	237.1	241.1	245.9	245.9	245.9	241.1	237.1	225.2	210.0	192.4	178.8
82.5°	187.3	190.7	195.5	194.8	195.5	190.7	187.3	177.9	165.3	153.5	141.2
85°	113.4	120.6	119.8	118.2	119.8	120.6	113.4	115.0	103.0	95.0	83.8
87.5°	54.4	55.1	57.0	58.4	57.0	55.1	54.4	52.4	46.6	43.2	40.5
90°	16.4	16.6	16.9	17.1	16.9	16.6	16.4	16.1	15.6	14.8	14.1
92.5°	15.6	15.6	15.7	15.7	15.7	15.6	15.6	15.5	15.1	14.4	13.6
95°	16.2	16.3	16.4	16.5	16.4	16.3	16.2	16.0	15.6	14.8	14.1
97.5°	15.6	15.7	15.8	16.0	15.8	15.7	15.6	15.5	15.4	15.3	15.2
100°	15.6	15.7	15.8	16.0	15.8	15.7	15.6	15.5	16.5	18.6	20.8
102.5°	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.3	27.9	51.2	74.4
105°	176.3	171.7	167.1	162.6	167.1	171.7	176.3	180.8	182.5	181.4	180.3
107.5°	225.1	225.6	226.1	226.6	226.1	225.6	225.1	224.6	224.1	223.6	223.0
110°	253.3	253.6	254.0	254.4	254.0	253.6	253.3	252.9	252.6	252.3	252.1



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	280.8	281.3	281.8	282.2	281.8	281.3	280.8	280.3	280.1	280.2	280.2
115°	322.9	322.9	322.9	322.9	322.9	322.9	322.9	322.9	322.7	322.5	322.2
117.5°	364.3	364.3	364.2	364.2	364.2	364.3	364.3	364.4	364.4	364.5	364.5
120°	390.9	390.7	390.4	390.2	390.4	390.7	390.9	391.2	391.2	390.9	390.7
122.5°	416.5	416.2	416.0	415.7	416.0	416.2	416.5	416.7	416.8	416.6	416.5
125°	453.7	453.8	453.9	454.1	453.9	453.8	453.7	453.6	453.3	452.9	452.5
127.5°	488.0	487.9	487.8	487.7	487.8	487.9	488.0	488.1	488.2	488.3	488.4
130°	510.5	510.5	510.5	510.5	510.5	510.5	510.5	510.5	510.5	510.3	510.2
132.5°	531.8	531.7	531.6	531.5	531.6	531.7	531.8	531.9	531.9	531.8	531.7
135°	562.2	562.5	562.8	563.0	562.8	562.5	562.2	562.0	561.7	561.5	561.2
137.5°	590.2	590.1	590.0	589.9	590.0	590.1	590.2	590.2	590.1	589.9	589.6
140°	608.3	608.4	608.5	608.6	608.5	608.4	608.3	608.1	607.9	607.5	607.1
142.5°	624.1	624.1	624.1	624.2	624.1	624.1	624.1	624.1	623.9	623.6	623.3
145°	647.2	647.5	647.8	648.0	647.8	647.5	647.2	647.0	646.8	646.7	646.5
147.5°	667.4	667.5	667.6	667.7	667.6	667.5	667.4	667.2	667.1	667.0	666.9
150°	680.1	680.3	680.4	680.5	680.4	680.3	680.1	680.0	679.9	679.9	679.9
152.5°	691.7	691.6	691.5	691.5	691.5	691.6	691.7	691.8	691.7	691.5	691.3
155°	707.3	706.9	706.6	706.2	706.6	706.9	707.3	707.7	707.6	707.1	706.6
157.5°	720.5	719.8	719.2	718.5	719.2	719.8	720.5	721.1	721.1	720.5	719.8
160°	729.0	728.2	727.5	726.7	727.5	728.2	729.0	729.8	729.8	729.0	728.2
162.5°	735.7	734.8	734.0	733.1	734.0	734.8	735.7	736.6	736.6	735.8	735.1
165°	745.5	744.4	743.3	742.1	743.3	744.4	745.5	746.7	746.8	745.7	744.7
167.5°	752.7	751.4	750.1	748.9	750.1	751.4	752.7	753.9	754.0	752.9	751.8
170°	756.8	755.5	754.2	753.0	754.2	755.5	756.8	758.0	758.2	757.1	756.1
172.5°	759.4	758.0	756.6	755.2	756.6	758.0	759.4	760.7	760.9	759.9	758.9
175°	762.7	761.1	759.6	758.1	759.6	761.1	762.7	764.2	764.4	763.2	762.1
177.5°	763.6	762.4	761.1	759.9	761.1	762.4	763.6	764.8	765.0	764.2	763.4
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1842.4	1845.0	1855.2	1864.8	1876.3	1884.6	1890.3	1896.7	1910.1	1921.0	1931.2
5°	1726.2	1730.2	1750.9	1765.3	1790.0	1811.6	1828.4	1846.7	1868.3	1897.8	1925.0
7.5°	1623.8	1638.7	1661.3	1684.6	1709.9	1738.1	1762.7	1790.4	1827.6	1868.1	1910.0
10°	1565.7	1582.5	1606.4	1633.6	1657.5	1690.2	1720.6	1753.3	1795.6	1845.1	1894.6
12.5°	1507.6	1535.2	1553.4	1585.6	1611.5	1638.5	1670.8	1713.7	1763.1	1815.1	1874.8
15°	1434.7	1449.9	1485.0	1502.6	1539.3	1580.9	1612.8	1655.9	1703.8	1772.5	1839.5
17.5°	1350.8	1370.7	1398.7	1432.2	1474.3	1506.8	1546.5	1590.9	1651.3	1719.5	1803.5
20°	1295.8	1312.6	1346.9	1383.6	1428.4	1462.7	1505.0	1548.1	1610.4	1683.1	1770.9
22.5°	1246.6	1262.8	1299.0	1333.2	1376.6	1418.6	1462.8	1513.0	1572.7	1649.2	1738.9
25°	1170.5	1192.0	1224.0	1259.1	1300.6	1348.5	1396.4	1441.1	1505.0	1585.6	1681.5
27.5°	1102.9	1120.2	1143.3	1183.2	1230.4	1276.7	1324.2	1380.5	1441.8	1527.0	1626.5
30°	1059.5	1075.5	1098.6	1135.3	1179.3	1228.8	1278.3	1332.5	1396.4	1481.1	1582.5
32.5°	1025.0	1037.1	1057.7	1090.6	1130.7	1182.8	1231.6	1287.8	1354.9	1438.3	1537.1
35°	974.1	984.4	992.4	1023.6	1059.5	1107.4	1156.9	1216.8	1281.5	1360.5	1459.5
37.5°	924.1	927.6	939.3	959.7	994.5	1038.6	1084.6	1143.5	1209.8	1290.1	1379.3
40°	893.4	895.0	902.2	921.4	951.7	993.2	1037.9	1096.2	1159.3	1235.1	1323.8
42.5°	863.4	862.4	869.0	882.4	910.8	948.5	992.6	1045.8	1108.8	1178.9	1262.4
45°	816.0	816.0	814.4	825.6	848.7	885.4	922.2	973.3	1026.0	1094.6	1164.9
47.5°	766.5	762.0	763.4	769.2	788.7	818.9	855.9	897.7	944.2	1002.3	1064.0
50°	734.5	728.2	725.8	732.1	749.7	776.1	811.2	847.9	891.8	942.9	995.6
52.5°	699.4	693.0	688.7	693.2	709.5	733.9	765.8	798.1	837.5	879.1	924.7
55°	645.1	637.9	635.5	637.1	649.1	668.3	695.4	725.0	754.5	788.8	820.8
57.5°	591.6	579.8	577.6	576.8	585.1	602.6	625.3	650.9	672.4	693.2	727.2
60°	556.5	542.1	537.3	536.5	542.9	557.3	578.0	603.6	618.8	633.1	662.7
62.5°	518.8	505.1	494.5	495.7	501.4	515.1	533.3	551.9	561.9	577.6	597.5
65°	460.7	443.1	435.1	432.7	435.9	447.1	461.5	473.5	484.6	491.0	510.2
67.5°	402.6	387.9	376.1	373.2	371.7	379.4	391.2	398.4	406.4	412.0	423.3
70°	361.7	348.9	334.5	329.7	328.9	335.3	346.5	347.3	358.5	360.9	372.9
72.5°	321.4	305.5	295.6	290.8	287.4	293.2	300.5	302.6	308.7	313.0	319.2
75°	258.7	246.7	237.1	229.9	227.5	230.7	230.7	234.7	238.7	241.1	248.3
77.5°	203.6	189.9	178.5	174.4	171.5	169.4	171.2	173.6	171.7	175.8	177.4
80°	165.3	150.9	142.1	140.5	135.7	131.7	130.9	133.3	130.1	131.7	136.5
82.5°	127.6	118.3	108.9	107.3	101.2	99.2	98.4	96.9	96.9	96.6	97.6
85°	75.8	70.3	63.9	59.9	57.5	53.5	53.5	51.9	50.3	48.7	49.5
87.5°	33.3	31.9	28.5	26.4	24.9	22.1	21.9	19.7	18.8	17.9	16.9
90°	13.3	12.5	11.5	10.5	9.5	8.5	7.3	5.9	4.5	3.1	1.7
92.5°	12.9	12.1	11.1	10.1	9.1	8.0	7.5	7.4	7.3	7.3	7.2
95°	13.3	12.5	12.4	12.3	12.2	12.0	14.1	18.4	22.8	27.1	31.4
97.5°	15.1	15.1	29.2	43.4	57.5	71.6	77.4	74.7	72.0	69.3	66.6
100°	22.9	25.1	42.6	60.1	77.6	95.1	102.7	100.4	98.1	95.8	93.5
102.5°	97.7	120.9	123.2	125.5	127.8	130.1	130.4	128.7	127.0	125.3	123.7
105°	179.1	178.0	177.3	176.7	176.1	175.4	174.7	174.0	173.2	172.5	171.7
107.5°	222.5	221.9	221.0	220.2	219.3	218.4	217.8	217.4	217.1	216.7	216.3
110°	251.8	251.6	250.8	250.0	249.3	248.5	247.9	247.6	247.2	246.8	246.4



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.3	280.3	280.0	279.6	279.2	278.9	278.4	277.7	277.0	276.3	275.6
115°	322.0	321.7	321.8	322.0	322.1	322.2	322.1	321.7	321.3	321.0	320.6
117.5°	364.6	364.6	364.3	364.1	363.8	363.5	363.1	362.6	362.1	361.6	361.1
120°	390.4	390.2	390.3	390.4	390.6	390.7	390.5	390.0	389.5	389.0	388.5
122.5°	416.3	416.2	416.0	415.8	415.7	415.5	415.2	414.9	414.6	414.3	414.0
125°	452.2	451.8	452.0	452.3	452.5	452.8	452.7	452.2	451.7	451.1	450.6
127.5°	488.4	488.5	487.9	487.3	486.8	486.2	485.8	485.7	485.6	485.4	485.3
130°	510.1	510.0	509.6	509.2	508.8	508.4	508.2	508.1	507.9	507.8	507.7
132.5°	531.5	531.4	530.9	530.4	530.0	529.5	529.1	528.9	528.7	528.4	528.2
135°	561.0	560.7	560.2	559.7	559.2	558.7	558.5	558.6	558.8	558.9	559.0
137.5°	589.3	589.0	588.5	587.9	587.3	586.8	586.5	586.4	586.4	586.3	586.3
140°	606.7	606.4	606.1	605.9	605.6	605.3	605.1	604.8	604.6	604.3	604.1
142.5°	623.1	622.8	622.6	622.5	622.3	622.2	621.9	621.4	621.0	620.5	620.1
145°	646.4	646.3	646.3	646.3	646.3	646.3	646.1	645.7	645.3	645.0	644.6
147.5°	666.8	666.7	666.8	667.0	667.1	667.2	666.9	666.2	665.5	664.8	664.1
150°	679.9	679.9	680.1	680.2	680.3	680.5	680.3	679.8	679.3	678.7	678.2
152.5°	691.1	690.9	691.1	691.4	691.6	691.8	691.7	691.3	690.9	690.5	690.1
155°	706.1	705.6	706.0	706.4	706.8	707.1	707.3	707.1	707.0	706.9	706.8
157.5°	719.2	718.5	718.9	719.4	719.8	720.2	720.5	720.6	720.6	720.7	720.8
160°	727.5	726.7	726.8	727.0	727.1	727.2	727.5	727.9	728.2	728.6	729.0
162.5°	734.3	733.6	733.7	733.8	733.9	734.1	734.4	734.9	735.3	735.8	736.3
165°	743.7	742.7	742.7	742.7	742.7	742.7	743.0	743.6	744.3	744.9	745.5
167.5°	750.7	749.5	749.6	749.7	749.8	749.8	750.2	750.9	751.5	752.2	752.8
170°	755.1	754.1	754.0	753.8	753.7	753.6	753.9	754.7	755.4	756.2	757.0
172.5°	757.9	756.8	756.7	756.6	756.5	756.3	756.7	757.4	758.2	758.9	759.7
175°	760.9	759.8	759.7	759.6	759.4	759.3	759.6	760.4	761.1	761.9	762.7
177.5°	762.6	761.7	761.5	761.3	761.1	760.9	761.2	761.9	762.6	763.3	764.0
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	1940.1	1946.5	1954.8	1968.9	1974.0	1980.4	1989.3	1988.7	1991.2	2000.8	2021.3
5°	1947.3	1972.1	1996.0	2024.8	2055.1	2075.1	2102.2	2119.0	2135.8	2157.3	2194.0
7.5°	1950.2	1989.5	2033.4	2083.9	2128.7	2180.5	2220.9	2258.9	2293.2	2338.7	2382.5
10°	1945.7	1998.4	2055.1	2119.0	2186.8	2244.3	2296.2	2355.3	2405.6	2460.7	2510.2
12.5°	1937.4	2001.0	2076.8	2148.4	2227.7	2312.7	2377.4	2437.1	2504.0	2567.4	2643.7
15°	1918.6	2005.6	2094.2	2188.4	2294.6	2392.8	2486.3	2563.7	2635.6	2730.6	2830.4
17.5°	1894.6	1988.5	2100.3	2214.3	2325.3	2437.6	2553.2	2669.6	2760.3	2878.3	2956.4
20°	1872.3	1980.9	2095.8	2231.6	2342.5	2482.3	2597.2	2709.8	2834.4	2951.7	3045.1
22.5°	1841.0	1959.8	2081.8	2216.9	2363.0	2502.7	2635.6	2757.7	2882.3	3009.9	3123.1
25°	1801.2	1909.0	2053.5	2206.8	2352.1	2503.8	2656.3	2809.6	2943.7	3078.7	3184.1
27.5°	1733.5	1869.6	2004.2	2162.4	2323.9	2495.5	2658.6	2819.0	2959.6	3070.5	3135.8
30°	1699.0	1817.2	1963.3	2122.2	2297.0	2481.5	2651.5	2808.8	2939.8	3028.4	3054.7
32.5°	1647.9	1769.9	1912.8	2077.5	2262.5	2452.1	2629.2	2777.5	2886.7	2933.2	2901.4
35°	1572.1	1682.3	1826.8	1995.2	2187.6	2389.6	2564.5	2689.8	2745.7	2701.8	2592.4
37.5°	1481.1	1590.3	1735.4	1900.9	2100.0	2305.3	2463.4	2553.6	2535.1	2425.9	2262.9
40°	1417.2	1519.4	1657.5	1836.3	2030.4	2236.4	2375.3	2424.0	2372.9	2216.4	2043.1
42.5°	1346.3	1445.9	1584.7	1757.1	1962.7	2152.7	2273.7	2277.7	2192.1	2005.0	1831.1
45°	1238.3	1333.3	1464.3	1643.9	1834.0	2012.8	2092.6	2053.5	1895.4	1715.0	1540.1
47.5°	1131.8	1214.2	1343.2	1513.8	1694.2	1844.8	1884.4	1814.0	1645.5	1470.4	1308.3
50°	1053.9	1136.9	1258.3	1421.2	1595.2	1725.4	1744.5	1651.1	1485.8	1309.4	1182.4
52.5°	979.2	1061.6	1178.5	1329.2	1488.6	1605.9	1606.6	1498.5	1333.8	1176.5	1058.5
55°	869.5	943.7	1049.1	1184.0	1326.2	1418.0	1395.6	1283.8	1140.9	1004.4	901.4
57.5°	763.8	828.4	925.5	1038.1	1163.3	1239.0	1201.9	1094.3	966.7	850.9	772.9
60°	695.4	756.9	839.9	946.1	1051.5	1110.6	1075.5	978.1	860.7	767.3	699.4
62.5°	629.0	680.9	760.7	852.9	950.6	994.3	963.0	866.9	765.5	681.0	626.0
65°	534.9	577.3	641.1	720.2	791.2	828.8	802.4	713.0	635.5	574.9	530.9
67.5°	447.1	480.2	528.5	591.9	652.3	672.6	648.6	586.4	520.7	472.2	441.2
70°	386.4	417.6	458.3	507.0	559.7	581.2	557.3	507.8	454.3	409.6	379.2
72.5°	333.4	357.5	391.9	433.5	474.7	496.3	480.0	432.4	387.2	354.0	328.1
75°	253.9	274.7	298.6	328.1	360.1	374.5	360.1	327.3	296.2	271.5	253.1
77.5°	184.6	195.8	214.3	236.3	256.3	267.3	254.9	232.7	213.7	196.7	187.6
80°	140.5	148.5	161.3	178.8	192.4	202.8	194.8	176.4	161.3	150.1	146.1
82.5°	102.2	107.6	115.9	129.0	138.1	143.4	139.9	126.6	120.4	110.5	106.5
85°	50.3	53.5	59.1	63.1	71.1	71.9	72.7	67.1	61.5	59.1	55.9
87.5°	17.9	18.8	21.0	23.2	26.0	26.8	26.4	26.6	24.2	23.7	21.3
90°	3.1	4.5	5.9	7.3	8.5	9.5	10.5	11.5	12.5	13.3	14.1
92.5°	7.3	7.3	7.4	7.5	8.0	9.1	10.1	11.1	12.1	12.9	13.6
95°	27.1	22.8	18.4	14.1	12.0	12.2	12.3	12.4	12.5	13.3	14.1
97.5°	69.3	72.0	74.7	77.4	71.6	57.5	43.4	29.2	15.1	15.1	15.2
100°	95.8	98.1	100.4	102.7	95.1	77.6	60.1	42.6	25.1	22.9	20.8
102.5°	125.3	127.0	128.7	130.4	130.1	127.8	125.5	123.2	120.9	97.7	74.4
105°	172.5	173.2	174.0	174.7	175.4	176.1	176.7	177.3	178.0	179.1	180.3
107.5°	216.7	217.1	217.4	217.8	218.4	219.3	220.2	221.0	221.9	222.5	223.0
110°	246.8	247.2	247.6	247.9	248.5	249.3	250.0	250.8	251.6	251.8	252.1





TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.3	277.0	277.7	278.4	278.9	279.2	279.6	280.0	280.3	280.3	280.2
115°	321.0	321.3	321.7	322.1	322.2	322.1	322.0	321.8	321.7	322.0	322.2
117.5°	361.6	362.1	362.6	363.1	363.5	363.8	364.1	364.3	364.6	364.6	364.5
120°	389.0	389.5	390.0	390.5	390.7	390.6	390.4	390.3	390.2	390.4	390.7
122.5°	414.3	414.6	414.9	415.2	415.5	415.7	415.8	416.0	416.2	416.3	416.5
125°	451.1	451.7	452.2	452.7	452.8	452.5	452.3	452.0	451.8	452.2	452.5
127.5°	485.4	485.6	485.7	485.8	486.2	486.8	487.3	487.9	488.5	488.4	488.4
130°	507.8	507.9	508.1	508.2	508.4	508.8	509.2	509.6	510.0	510.1	510.2
132.5°	528.4	528.7	528.9	529.1	529.5	530.0	530.4	530.9	531.4	531.5	531.7
135°	558.9	558.8	558.6	558.5	558.7	559.2	559.7	560.2	560.7	561.0	561.2
137.5°	586.3	586.4	586.4	586.5	586.8	587.3	587.9	588.5	589.0	589.3	589.6
140°	604.3	604.6	604.8	605.1	605.3	605.6	605.9	606.1	606.4	606.7	607.1
142.5°	620.5	621.0	621.4	621.9	622.2	622.3	622.5	622.6	622.8	623.1	623.3
145°	645.0	645.3	645.7	646.1	646.3	646.3	646.3	646.3	646.3	646.4	646.5
147.5°	664.8	665.5	666.2	666.9	667.2	667.1	667.0	666.8	666.7	666.8	666.9
150°	678.7	679.3	679.8	680.3	680.5	680.3	680.2	680.1	679.9	679.9	679.9
152.5°	690.5	690.9	691.3	691.7	691.8	691.6	691.4	691.1	690.9	691.1	691.3
155°	706.9	707.0	707.1	707.3	707.1	706.8	706.4	706.0	705.6	706.1	706.6
157.5°	720.7	720.6	720.6	720.5	720.2	719.8	719.4	718.9	718.5	719.2	719.8
160°	728.6	728.2	727.9	727.5	727.2	727.1	727.0	726.8	726.7	727.5	728.2
162.5°	735.8	735.3	734.9	734.4	734.1	733.9	733.8	733.7	733.6	734.3	735.1
165°	744.9	744.3	743.6	743.0	742.7	742.7	742.7	742.7	742.7	743.7	744.7
167.5°	752.2	751.5	750.9	750.2	749.8	749.8	749.7	749.6	749.5	750.7	751.8
170°	756.2	755.4	754.7	753.9	753.6	753.7	753.8	754.0	754.1	755.1	756.1
172.5°	758.9	758.2	757.4	756.7	756.3	756.5	756.6	756.7	756.8	757.9	758.9
175°	761.9	761.1	760.4	759.6	759.3	759.4	759.6	759.7	759.8	760.9	762.1
177.5°	763.3	762.6	761.9	761.2	760.9	761.1	761.3	761.5	761.7	762.6	763.4
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4	1927.4
2.5°	2031.5	2032.8	2038.5	2043.0	2044.3	2050.6	2051.3
5°	2210.0	2223.6	2249.9	2252.3	2256.3	2277.1	2261.1
7.5°	2419.2	2453.7	2476.7	2497.0	2504.3	2513.4	2511.5
10°	2553.3	2604.4	2630.0	2670.7	2672.3	2682.7	2676.3
12.5°	2688.1	2747.5	2794.1	2801.6	2835.8	2841.1	2850.0
15°	2879.1	2942.1	3006.8	3030.0	3077.1	3088.3	3105.8
17.5°	3058.6	3123.1	3168.4	3228.3	3247.6	3273.5	3255.9
20°	3156.9	3227.2	3284.7	3331.8	3351.7	3366.1	3364.5
22.5°	3216.3	3287.2	3333.8	3369.5	3388.1	3394.2	3393.9
25°	3253.5	3294.2	3308.6	3322.2	3301.4	3294.2	3297.4
27.5°	3150.1	3139.5	3102.0	3052.8	3001.7	2961.1	2939.1
30°	3007.6	2945.3	2888.7	2789.6	2738.6	2708.2	2681.1
32.5°	2805.8	2707.1	2598.0	2507.3	2449.2	2404.2	2397.5
35°	2459.9	2311.4	2178.1	2067.1	2009.6	1960.9	1949.7
37.5°	2091.4	1937.1	1817.0	1719.3	1657.5	1623.2	1591.1
40°	1846.7	1714.2	1596.0	1513.0	1465.9	1441.1	1421.2
42.5°	1658.3	1537.3	1419.7	1356.5	1313.9	1298.7	1287.0
45°	1398.0	1285.4	1204.0	1156.1	1131.3	1105.8	1093.8
47.5°	1189.6	1098.0	1044.3	1003.6	977.1	961.9	954.3
50°	1071.5	996.4	948.5	917.4	893.4	881.4	875.1
52.5°	966.7	905.1	864.8	840.1	823.8	815.0	812.5
55°	832.7	785.6	760.1	738.5	726.6	718.6	715.4
57.5°	723.8	687.6	666.8	649.1	644.5	637.8	635.5
60°	652.3	624.4	606.8	594.8	590.8	582.8	584.4
62.5°	589.1	566.2	551.2	544.4	539.1	532.4	534.6
65°	498.2	481.4	473.5	467.1	460.7	456.7	459.9
67.5°	418.0	406.6	395.7	392.0	388.8	388.2	384.8
70°	365.7	356.1	346.5	344.1	344.1	340.9	340.1
72.5°	315.2	308.2	301.8	300.0	297.5	298.8	295.4
75°	243.5	237.9	235.5	233.1	232.3	232.3	229.9
77.5°	180.0	175.8	172.0	172.0	169.1	168.0	167.7
80°	136.5	134.9	131.7	131.7	130.1	130.9	129.3
82.5°	102.7	100.4	99.8	98.5	96.3	96.4	94.9
85°	55.1	52.7	51.9	49.5	47.9	49.5	47.9
87.5°	22.1	21.6	21.1	19.9	19.3	19.3	17.5
90°	14.8	15.6	16.1	16.4	16.6	16.9	17.1
92.5°	14.4	15.1	15.5	15.6	15.6	15.7	15.7
95°	14.8	15.6	16.0	16.2	16.3	16.4	16.5
97.5°	15.3	15.4	15.5	15.6	15.7	15.8	16.0
100°	18.6	16.5	15.5	15.6	15.7	15.8	16.0
102.5°	51.2	27.9	16.3	16.4	16.4	16.4	16.4
105°	181.4	182.5	180.8	176.3	171.7	167.1	162.6
107.5°	223.6	224.1	224.6	225.1	225.6	226.1	226.6
110°	252.3	252.6	252.9	253.3	253.6	254.0	254.4



TEST NUMBER: P332679

CATALOG NUMBER: SA4XXDIP-C1195D590U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	280.2	280.1	280.3	280.8	281.3	281.8	282.2
115°	322.5	322.7	322.9	322.9	322.9	322.9	322.9
117.5°	364.5	364.4	364.4	364.3	364.3	364.2	364.2
120°	390.9	391.2	391.2	390.9	390.7	390.4	390.2
122.5°	416.6	416.8	416.7	416.5	416.2	416.0	415.7
125°	452.9	453.3	453.6	453.7	453.8	453.9	454.1
127.5°	488.3	488.2	488.1	488.0	487.9	487.8	487.7
130°	510.3	510.5	510.5	510.5	510.5	510.5	510.5
132.5°	531.8	531.9	531.9	531.8	531.7	531.6	531.5
135°	561.5	561.7	562.0	562.2	562.5	562.8	563.0
137.5°	589.9	590.1	590.2	590.2	590.1	590.0	589.9
140°	607.5	607.9	608.1	608.3	608.4	608.5	608.6
142.5°	623.6	623.9	624.1	624.1	624.1	624.1	624.2
145°	646.7	646.8	647.0	647.2	647.5	647.8	648.0
147.5°	667.0	667.1	667.2	667.4	667.5	667.6	667.7
150°	679.9	679.9	680.0	680.1	680.3	680.4	680.5
152.5°	691.5	691.7	691.8	691.7	691.6	691.5	691.5
155°	707.1	707.6	707.7	707.3	706.9	706.6	706.2
157.5°	720.5	721.1	721.1	720.5	719.8	719.2	718.5
160°	729.0	729.8	729.8	729.0	728.2	727.5	726.7
162.5°	735.8	736.6	736.6	735.7	734.8	734.0	733.1
165°	745.7	746.8	746.7	745.5	744.4	743.3	742.1
167.5°	752.9	754.0	753.9	752.7	751.4	750.1	748.9
170°	757.1	758.2	758.0	756.8	755.5	754.2	753.0
172.5°	759.9	760.9	760.7	759.4	758.0	756.6	755.2
175°	763.2	764.4	764.2	762.7	761.1	759.6	758.1
177.5°	764.2	765.0	764.8	763.6	762.4	761.1	759.9
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7

(END OF REPORT)