

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332496

Luminaire Tested: **SA4XXDIP-C350D365U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332496  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C350D365U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2978.9 lumens  
Efficiency: N/A  
Efficacy: 146.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332496  
CATALOG NUMBER: SA4XXDIP-C350D365U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332496

CATALOG NUMBER: SA4XXDIP-C350D365U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	43				
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36				
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	30				
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	26				
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	32	28	26	23				
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20				
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	25	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4769	4769	4769
5°	4783	4725	4760
10°	4753	4687	4710
15°	4695	4621	4633
20°	4619	4538	4542
25°	4532	4444	4431
30°	4426	4333	4294
35°	4315	4217	4161
40°	4200	4086	4011
45°	4080	3956	3881
50°	3947	3841	3721
55°	3804	3690	3571
60°	3660	3523	3416
65°	3500	3364	3228
70°	3319	3151	3028
75°	3041	2895	2820
80°	2706	2599	2529
85°	2371	2279	2232



TEST NUMBER: P332496

CATALOG NUMBER: SA4XXDIP-C350D365U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.6	1.9
10°-20°	156.7	5.3
20°-30°	230.7	7.7
30°-40°	268.2	9.0
40°-50°	268.2	9.0
50°-60°	234.6	7.9
60°-70°	174.2	5.8
70°-80°	99.0	3.3
80°-90°	29.9	1.0
90°-100°	16.2	0.5
100°-110°	103.0	3.5
110°-120°	197.1	6.6
120°-130°	250.2	8.4
130°-140°	267.7	9.0
140°-150°	250.4	8.4
150°-160°	201.9	6.8
160°-170°	130.2	4.4
170°-180°	44.9	1.5
0°-30°	443.1	14.9
0°-40°	711.3	23.9
0°-60°	1214.1	40.8
0°-90°	1517.2	50.9
90°-120°	316.3	10.6
90°-150°	1084.6	36.4
90°-180°	1462.0	49.1
0°-180°	2978.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	591	591	591	591	591	
5°	590	588	583	588	587	56
15°	562	560	553	555	554	158
25°	509	505	499	499	498	234
35°	438	434	428	425	422	274
45°	357	354	346	342	340	275
55°	270	269	262	257	254	242
65°	183	181	176	172	169	181
75°	98	95	93	91	90	104
85°	26	26	25	25	24	28
90°	1	5	8	10	11	2
95°	19	8	8	10	10	25
105°	106	108	110	113	101	111
115°	199	200	199	200	200	195
125°	279	280	280	281	281	249
135°	346	346	347	348	349	267
145°	399	400	400	401	402	249
155°	438	438	437	438	438	202
165°	462	460	460	463	460	130
175°	472	470	471	474	470	45
180°	472	472	472	472	472	



TEST NUMBER: P332496

CATALOG NUMBER: SA4XXDIP-C350D365U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	592.2	592.0	591.7	591.5	591.2	590.6	589.7	588.8	587.9	586.9	587.8
5°	590.2	589.8	589.4	589.0	588.6	587.8	586.6	585.5	584.3	583.1	584.3
7.5°	584.8	584.3	583.9	583.5	583.1	582.2	580.9	579.7	578.4	577.1	578.0
10°	579.8	579.4	579.0	578.6	578.2	577.3	575.9	574.5	573.2	571.8	572.6
12.5°	573.4	573.0	572.6	572.1	571.7	570.8	569.3	567.9	566.4	565.0	565.9
15°	561.8	561.4	561.0	560.6	560.2	559.2	557.6	556.0	554.4	552.9	553.5
17.5°	547.9	547.4	546.9	546.4	545.8	544.8	543.3	541.8	540.3	538.8	539.2
20°	537.7	537.2	536.7	536.1	535.6	534.6	533.0	531.4	529.8	528.2	528.6
22.5°	526.7	526.0	525.3	524.6	523.9	522.8	521.2	519.7	518.1	516.5	517.1
25°	508.8	508.1	507.4	506.6	505.9	504.8	503.3	501.8	500.4	498.9	499.0
27.5°	488.4	487.6	486.9	486.1	485.4	484.3	482.9	481.6	480.2	478.8	478.6
30°	474.8	473.9	473.1	472.2	471.4	470.3	468.9	467.5	466.2	464.8	464.4
32.5°	460.4	459.6	458.8	458.1	457.3	456.2	454.8	453.3	451.9	450.4	449.9
35°	437.8	437.1	436.4	435.6	434.9	433.8	432.3	430.8	429.4	427.9	427.2
37.5°	414.1	413.4	412.7	412.1	411.4	410.3	408.7	407.1	405.5	403.9	403.1
40°	398.5	397.7	396.9	396.0	395.2	394.0	392.4	390.8	389.2	387.7	386.6
42.5°	381.9	381.4	380.9	380.4	379.9	378.7	377.0	375.2	373.5	371.8	370.5
45°	357.4	356.6	355.9	355.2	354.4	353.2	351.5	349.8	348.2	346.5	345.3
47.5°	331.7	331.2	330.7	330.2	329.7	328.7	327.1	325.5	324.0	322.4	321.1
50°	314.3	313.9	313.5	313.0	312.6	311.7	310.2	308.7	307.2	305.8	304.3
52.5°	297.3	296.7	296.2	295.7	295.2	294.2	292.6	291.1	289.5	288.0	286.7
55°	270.3	270.0	269.6	269.3	269.0	268.1	266.6	265.2	263.7	262.2	261.0
57.5°	244.5	244.2	243.8	243.5	243.1	242.2	240.7	239.3	237.8	236.4	235.2
60°	226.7	226.2	225.7	225.1	224.6	223.7	222.3	220.9	219.6	218.2	217.3
62.5°	209.3	208.9	208.4	208.0	207.5	206.6	205.1	203.7	202.2	200.8	199.9
65°	183.2	182.7	182.1	181.6	181.1	180.3	179.2	178.2	177.1	176.1	175.0
67.5°	156.9	156.4	155.9	155.4	154.9	154.2	153.2	152.2	151.2	150.1	149.1
70°	140.6	139.8	139.1	138.4	137.6	136.8	136.0	135.2	134.3	133.5	132.6
72.5°	123.2	122.4	121.7	121.0	120.2	119.5	118.8	118.2	117.5	116.8	116.1
75°	97.5	97.0	96.5	95.9	95.4	94.9	94.4	93.8	93.3	92.8	92.4
77.5°	73.0	72.8	72.5	72.3	72.1	71.7	71.3	70.8	70.3	69.9	69.7
80°	58.2	57.9	57.6	57.3	57.0	56.7	56.5	56.3	56.1	55.9	55.6
82.5°	43.8	43.7	43.5	43.4	43.2	43.1	43.1	43.1	43.0	43.0	42.9
85°	25.6	25.6	25.6	25.6	25.6	25.5	25.2	25.0	24.8	24.6	24.6
87.5°	10.1	10.1	10.2	10.3	10.4	10.5	10.5	10.6	10.6	10.6	10.7
90°	1.1	1.9	2.8	3.7	4.5	5.3	5.9	6.5	7.1	7.8	8.2
92.5°	4.5	4.5	4.5	4.6	4.6	5.0	5.6	6.2	6.9	7.5	8.0
95°	19.4	16.8	14.1	11.4	8.8	7.5	7.5	7.6	7.7	7.8	8.2
97.5°	41.3	42.9	44.6	46.3	47.9	44.4	35.6	26.9	18.1	9.3	9.4
100°	58.0	59.4	60.8	62.2	63.6	58.9	48.1	37.2	26.4	15.6	14.2
102.5°	76.6	77.7	78.7	79.7	80.8	80.6	79.2	77.8	76.3	74.9	60.5
105°	106.4	106.8	107.3	107.8	108.3	108.7	109.1	109.5	109.9	110.3	111.0
107.5°	134.0	134.2	134.5	134.7	135.0	135.3	135.9	136.4	136.9	137.5	137.8
110°	152.7	152.9	153.1	153.4	153.6	154.0	154.4	154.9	155.4	155.9	156.0



TEST NUMBER: P332496

CATALOG NUMBER: SA4XXDIP-C350D365U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.8	171.2	171.6	172.0	172.5	172.8	173.0	173.2	173.4	173.7	173.6
115°	198.6	198.9	199.1	199.3	199.6	199.6	199.6	199.5	199.4	199.3	199.5
117.5°	223.7	224.0	224.3	224.7	225.0	225.2	225.4	225.6	225.7	225.9	225.9
120°	240.7	241.0	241.3	241.6	241.9	242.0	242.0	241.9	241.8	241.7	241.9
122.5°	256.5	256.7	256.9	257.1	257.3	257.4	257.5	257.6	257.7	257.9	257.9
125°	279.2	279.5	279.8	280.1	280.5	280.5	280.4	280.2	280.1	279.9	280.1
127.5°	300.7	300.8	300.8	300.9	301.0	301.2	301.6	301.9	302.3	302.7	302.6
130°	314.5	314.6	314.7	314.8	314.9	315.0	315.2	315.5	315.7	316.0	316.0
132.5°	327.3	327.4	327.5	327.7	327.8	328.0	328.3	328.6	328.9	329.2	329.3
135°	346.3	346.3	346.2	346.1	346.0	346.1	346.5	346.8	347.1	347.4	347.6
137.5°	363.2	363.3	363.3	363.3	363.4	363.6	363.9	364.2	364.6	364.9	365.1
140°	374.3	374.4	374.6	374.7	374.9	375.0	375.2	375.4	375.5	375.7	375.9
142.5°	384.2	384.4	384.7	385.0	385.3	385.5	385.6	385.7	385.8	385.9	386.0
145°	399.4	399.6	399.8	400.1	400.3	400.4	400.4	400.4	400.4	400.4	400.5
147.5°	411.4	411.9	412.3	412.8	413.2	413.4	413.3	413.2	413.1	413.1	413.1
150°	420.2	420.5	420.8	421.2	421.5	421.6	421.5	421.4	421.3	421.3	421.3
152.5°	427.6	427.8	428.1	428.3	428.6	428.6	428.5	428.3	428.2	428.1	428.2
155°	437.9	438.0	438.0	438.1	438.2	438.1	437.9	437.6	437.4	437.2	437.5
157.5°	446.6	446.5	446.5	446.4	446.4	446.2	446.0	445.7	445.4	445.2	445.6
160°	451.7	451.4	451.2	451.0	450.7	450.6	450.5	450.4	450.3	450.2	450.7
162.5°	456.2	455.9	455.6	455.3	455.0	454.8	454.7	454.6	454.6	454.5	455.0
165°	461.9	461.5	461.1	460.7	460.3	460.1	460.1	460.1	460.1	460.1	460.8
167.5°	466.4	466.0	465.6	465.2	464.8	464.6	464.5	464.5	464.4	464.4	465.1
170°	469.0	468.5	468.0	467.6	467.1	466.9	467.0	467.1	467.1	467.2	467.8
172.5°	470.7	470.2	469.7	469.3	468.8	468.6	468.7	468.8	468.8	468.9	469.5
175°	472.5	472.0	471.6	471.1	470.6	470.4	470.5	470.6	470.7	470.7	471.5
177.5°	473.4	472.9	472.5	472.0	471.6	471.4	471.6	471.7	471.8	471.9	472.5
180°	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5



TEST NUMBER: P332496

CATALOG NUMBER: SA4XXDIP-C350D365U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	588.6	589.5	590.3	590.7	590.6	590.5	590.4	590.3
5°	585.5	586.6	587.8	588.2	588.0	587.8	587.6	587.4
7.5°	578.9	579.9	580.8	581.2	581.1	580.9	580.8	580.7
10°	573.5	574.3	575.2	575.5	575.3	575.0	574.8	574.6
12.5°	566.8	567.7	568.7	569.0	568.7	568.4	568.1	567.8
15°	554.1	554.7	555.4	555.5	555.2	554.9	554.6	554.3
17.5°	539.6	540.0	540.4	540.5	540.3	540.1	539.9	539.7
20°	528.9	529.2	529.5	529.6	529.3	529.1	528.9	528.7
22.5°	517.6	518.2	518.8	518.9	518.5	518.1	517.7	517.4
25°	499.1	499.2	499.3	499.2	498.7	498.3	497.9	497.5
27.5°	478.3	478.1	477.8	477.4	476.9	476.4	475.8	475.3
30°	464.0	463.6	463.1	462.7	462.1	461.6	461.1	460.6
32.5°	449.4	448.9	448.4	447.9	447.4	446.8	446.3	445.8
35°	426.4	425.7	424.9	424.3	423.8	423.3	422.7	422.2
37.5°	402.3	401.5	400.7	400.0	399.3	398.6	397.9	397.2
40°	385.6	384.5	383.5	382.7	382.1	381.6	381.1	380.6
42.5°	369.3	368.1	366.9	366.1	365.7	365.4	365.0	364.7
45°	344.2	343.0	341.9	341.1	340.8	340.5	340.2	339.9
47.5°	319.8	318.5	317.2	316.2	315.4	314.6	313.8	313.0
50°	302.8	301.4	299.9	298.8	298.2	297.6	296.9	296.3
52.5°	285.4	284.1	282.8	281.7	280.9	280.1	279.3	278.5
55°	259.7	258.4	257.2	256.2	255.6	255.0	254.3	253.7
57.5°	234.0	232.8	231.6	230.7	230.1	229.5	228.9	228.2
60°	216.3	215.4	214.4	213.7	213.2	212.6	212.1	211.6
62.5°	199.1	198.2	197.3	196.6	196.1	195.6	195.1	194.5
65°	174.0	172.9	171.9	171.1	170.6	170.0	169.5	169.0
67.5°	148.1	147.1	146.1	145.5	145.4	145.2	145.1	144.9
70°	131.8	131.0	130.1	129.5	129.2	128.9	128.6	128.3
72.5°	115.5	114.8	114.1	113.6	113.3	113.0	112.7	112.4
75°	91.9	91.5	91.1	90.8	90.7	90.6	90.5	90.4
77.5°	69.6	69.5	69.4	69.2	68.9	68.6	68.3	68.1
80°	55.4	55.2	55.0	54.9	54.7	54.6	54.5	54.4
82.5°	42.7	42.6	42.5	42.4	42.3	42.1	42.0	41.9
85°	24.6	24.6	24.6	24.6	24.5	24.4	24.2	24.1
87.5°	10.8	10.9	11.0	11.1	11.1	11.1	11.2	11.2
90°	8.7	9.2	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	8.4	8.9	9.4	9.6	9.7	9.7	9.7	9.8
95°	8.7	9.2	9.7	9.9	10.0	10.1	10.2	10.2
97.5°	9.4	9.5	9.5	9.6	9.7	9.7	9.8	9.9
100°	12.9	11.5	10.2	9.6	9.7	9.7	9.8	9.9
102.5°	46.1	31.7	17.3	10.1	10.1	10.1	10.2	10.2
105°	111.7	112.4	113.1	112.0	109.2	106.4	103.5	100.7
107.5°	138.2	138.5	138.9	139.2	139.5	139.8	140.1	140.4
110°	156.2	156.3	156.5	156.7	156.9	157.2	157.4	157.6





TEST NUMBER: P332496

CATALOG NUMBER: SA4XXDIP-C350D365U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	173.6	173.6	173.5	173.7	174.0	174.3	174.6	174.9
115°	199.6	199.8	200.0	200.0	200.0	200.0	200.0	200.0
117.5°	225.8	225.8	225.8	225.7	225.7	225.7	225.7	225.6
120°	242.0	242.2	242.4	242.4	242.2	242.0	241.9	241.7
122.5°	258.0	258.1	258.2	258.2	258.0	257.9	257.7	257.6
125°	280.4	280.6	280.8	281.0	281.1	281.2	281.2	281.3
127.5°	302.6	302.5	302.5	302.4	302.4	302.3	302.2	302.2
130°	316.1	316.2	316.3	316.3	316.3	316.3	316.3	316.3
132.5°	329.4	329.5	329.6	329.6	329.5	329.4	329.4	329.3
135°	347.7	347.9	348.0	348.2	348.3	348.5	348.7	348.8
137.5°	365.3	365.5	365.6	365.7	365.6	365.6	365.5	365.5
140°	376.1	376.4	376.6	376.8	376.9	376.9	377.0	377.1
142.5°	386.2	386.4	386.5	386.6	386.7	386.7	386.7	386.7
145°	400.6	400.7	400.7	400.8	401.0	401.2	401.3	401.5
147.5°	413.2	413.3	413.3	413.4	413.5	413.5	413.6	413.7
150°	421.3	421.3	421.3	421.3	421.4	421.5	421.5	421.6
152.5°	428.3	428.4	428.6	428.6	428.5	428.5	428.5	428.4
155°	437.8	438.1	438.4	438.5	438.2	438.0	437.8	437.5
157.5°	446.0	446.4	446.8	446.8	446.4	446.0	445.6	445.2
160°	451.2	451.7	452.1	452.1	451.7	451.2	450.7	450.2
162.5°	455.4	455.9	456.4	456.3	455.8	455.3	454.7	454.2
165°	461.4	462.0	462.7	462.6	461.9	461.2	460.5	459.8
167.5°	465.8	466.5	467.1	467.1	466.3	465.5	464.7	464.0
170°	468.5	469.1	469.7	469.6	468.9	468.1	467.3	466.5
172.5°	470.2	470.8	471.4	471.3	470.5	469.6	468.8	467.9
175°	472.2	472.9	473.6	473.5	472.5	471.6	470.6	469.7
177.5°	473.0	473.5	474.0	473.8	473.1	472.3	471.6	470.8
180°	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5

(END OF REPORT)