

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332516

Luminaire Tested: **SA4XXDIP-C350D810U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332516
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C350D810U835-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4412.7 lumens
Efficiency: N/A
Efficacy: 141.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332516

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332516

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	34				
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29				
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24				
3	78	69	62	56	70	63	56	52	50	46	42	39	36	34	29	27	25	20				
4	71	61	53	47	64	55	49	44	45	40	36	35	31	29	26	23	22	18				
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15				
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	18	17	13				
7	56	44	36	31	50	40	33	28	32	27	24	26	22	19	19	17	15	12				
8	52	40	32	27	46	36	29	25	30	24	21	23	20	17	18	15	13	11				
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12	10				
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4769	4769	4769
5°	4783	4725	4760
10°	4753	4687	4710
15°	4695	4621	4633
20°	4619	4538	4542
25°	4532	4444	4431
30°	4426	4333	4294
35°	4315	4217	4161
40°	4200	4086	4011
45°	4080	3956	3881
50°	3947	3841	3721
55°	3804	3690	3571
60°	3660	3523	3416
65°	3500	3364	3228
70°	3319	3151	3028
75°	3041	2895	2820
80°	2706	2599	2529
85°	2371	2279	2232



TEST NUMBER: P332516

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	1.3
10°-20°	156.7	3.6
20°-30°	230.7	5.2
30°-40°	268.2	6.1
40°-50°	268.2	6.1
50°-60°	234.6	5.3
60°-70°	174.2	3.9
70°-80°	99.0	2.2
80°-90°	30.8	0.7
90°-100°	287.5	6.5
100°-110°	598.3	13.6
110°-120°	535.9	12.1
120°-130°	450.8	10.2
130°-140°	375.9	8.5
140°-150°	287.1	6.5
150°-160°	201.8	4.6
160°-170°	118.7	2.7
170°-180°	38.6	0.9
0°-30°	443.1	10.0
0°-40°	711.3	16.1
0°-60°	1214.1	27.5
0°-90°	1518.1	34.4
90°-120°	1421.6	32.2
90°-150°	2535.4	57.5
90°-180°	2895.0	65.6
0°-180°	4412.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	591	591	591	591	591	
5°	590	588	583	588	587	56
15°	562	560	553	555	554	158
25°	509	505	499	499	498	234
35°	438	434	428	425	422	274
45°	357	354	346	342	340	275
55°	270	269	262	257	254	242
65°	183	181	176	172	169	181
75°	98	95	93	91	90	104
85°	26	26	25	25	24	28
90°	1	6	14	16	16	3
95°	26	81	637	316	191	29
105°	92	133	513	1104	1100	98
115°	161	202	457	879	1056	160
125°	224	267	455	748	843	200
135°	267	317	451	664	754	206
145°	307	352	449	560	615	193
155°	350	377	436	494	515	161
165°	381	393	418	443	450	107
175°	397	398	401	407	405	38
180°	398	398	398	398	398	



TEST NUMBER: P332516

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	592.2	592.0	591.7	591.5	591.2	590.6	589.7	588.8	587.9	586.9	587.8
5°	590.2	589.8	589.4	589.0	588.6	587.8	586.6	585.5	584.3	583.1	584.3
7.5°	584.8	584.3	583.9	583.5	583.1	582.2	580.9	579.7	578.4	577.1	578.0
10°	579.8	579.4	579.0	578.6	578.2	577.3	575.9	574.5	573.2	571.8	572.6
12.5°	573.4	573.0	572.6	572.1	571.7	570.8	569.3	567.9	566.4	565.0	565.9
15°	561.8	561.4	561.0	560.6	560.2	559.2	557.6	556.0	554.4	552.9	553.5
17.5°	547.9	547.4	546.9	546.4	545.8	544.8	543.3	541.8	540.3	538.8	539.2
20°	537.7	537.2	536.7	536.1	535.6	534.6	533.0	531.4	529.8	528.2	528.6
22.5°	526.7	526.0	525.3	524.6	523.9	522.8	521.2	519.7	518.1	516.5	517.1
25°	508.8	508.1	507.4	506.6	505.9	504.8	503.3	501.8	500.4	498.9	499.0
27.5°	488.4	487.6	486.9	486.1	485.4	484.3	482.9	481.6	480.2	478.8	478.6
30°	474.8	473.9	473.1	472.2	471.4	470.3	468.9	467.5	466.2	464.8	464.4
32.5°	460.4	459.6	458.8	458.1	457.3	456.2	454.8	453.3	451.9	450.4	449.9
35°	437.8	437.1	436.4	435.6	434.9	433.8	432.3	430.8	429.4	427.9	427.2
37.5°	414.1	413.4	412.7	412.1	411.4	410.3	408.7	407.1	405.5	403.9	403.1
40°	398.5	397.7	396.9	396.0	395.2	394.0	392.4	390.8	389.2	387.7	386.6
42.5°	381.9	381.4	380.9	380.4	379.9	378.7	377.0	375.2	373.5	371.8	370.5
45°	357.4	356.6	355.9	355.2	354.4	353.2	351.5	349.8	348.2	346.5	345.3
47.5°	331.7	331.2	330.7	330.2	329.7	328.7	327.1	325.5	324.0	322.4	321.1
50°	314.3	313.9	313.5	313.0	312.6	311.7	310.2	308.7	307.2	305.8	304.3
52.5°	297.3	296.7	296.2	295.7	295.2	294.2	292.6	291.1	289.5	288.0	286.7
55°	270.3	270.0	269.6	269.3	269.0	268.1	266.6	265.2	263.7	262.2	261.0
57.5°	244.5	244.2	243.8	243.5	243.1	242.2	240.7	239.3	237.8	236.4	235.2
60°	226.7	226.2	225.7	225.1	224.6	223.7	222.3	220.9	219.6	218.2	217.3
62.5°	209.3	208.9	208.4	208.0	207.5	206.6	205.1	203.7	202.2	200.8	199.9
65°	183.2	182.7	182.1	181.6	181.1	180.3	179.2	178.2	177.1	176.1	175.0
67.5°	156.9	156.4	155.9	155.4	154.9	154.2	153.2	152.2	151.2	150.1	149.1
70°	140.6	139.8	139.1	138.4	137.6	136.8	136.0	135.2	134.3	133.5	132.6
72.5°	123.2	122.4	121.7	121.0	120.2	119.5	118.8	118.2	117.5	116.8	116.1
75°	97.5	97.0	96.5	95.9	95.4	94.9	94.4	93.8	93.3	92.8	92.4
77.5°	73.0	72.8	72.5	72.3	72.1	71.7	71.3	70.8	70.3	69.9	69.7
80°	58.2	57.9	57.6	57.3	57.0	56.7	56.5	56.3	56.1	55.9	55.6
82.5°	43.8	43.7	43.5	43.4	43.2	43.1	43.1	43.1	43.0	43.0	42.9
85°	25.6	25.6	25.6	25.6	25.6	25.5	25.2	25.0	24.8	24.6	24.6
87.5°	10.0	10.2	10.6	10.7	10.8	10.7	11.5	11.4	11.7	11.9	11.7
90°	0.8	2.3	4.7	5.5	6.3	6.3	10.9	10.9	12.5	14.1	13.3
92.5°	8.9	13.0	20.3	29.9	41.3	57.5	97.3	157.9	217.1	248.0	206.6
95°	25.8	28.1	36.0	46.1	64.9	97.7	165.8	294.0	480.9	637.3	655.3
97.5°	46.3	46.3	53.0	62.4	78.5	106.0	158.4	264.3	450.1	671.2	823.2
100°	59.4	59.4	64.9	74.3	89.1	114.2	160.3	248.7	408.2	628.7	828.8
102.5°	71.9	73.2	78.0	86.8	101.0	124.8	166.5	244.3	380.0	575.5	781.9
105°	91.5	93.8	97.7	107.1	121.2	143.9	181.4	246.3	355.8	512.9	696.7
107.5°	113.1	114.6	118.5	128.5	142.0	164.4	198.8	257.9	351.4	477.9	627.9
110°	127.5	129.0	132.9	142.3	156.4	177.5	211.9	266.6	352.6	466.0	593.5



TEST NUMBER: P332516

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	141.2	142.8	147.3	156.1	170.1	191.3	224.4	276.0	356.4	460.4	574.1
115°	161.1	163.4	168.9	176.7	191.6	212.7	244.0	290.9	363.6	457.4	555.9
117.5°	181.7	183.9	188.8	197.4	211.3	233.2	262.9	306.0	371.3	456.6	547.8
120°	195.5	197.0	202.5	211.1	224.4	246.3	276.0	316.7	376.9	456.6	543.4
122.5°	208.0	209.6	215.0	223.0	237.5	258.8	288.5	326.7	382.5	456.0	538.4
125°	224.4	227.5	232.2	240.8	255.7	277.6	305.7	341.7	391.0	455.1	530.1
127.5°	239.0	241.5	247.1	256.9	272.4	294.5	321.7	354.7	397.7	453.4	519.0
130°	247.1	250.2	256.5	268.2	283.1	305.7	332.3	362.8	402.7	452.7	512.2
132.5°	255.2	257.7	265.9	277.0	293.1	314.5	341.1	370.9	407.1	452.1	505.9
135°	266.6	269.8	277.6	290.9	307.3	327.6	353.4	381.6	413.6	451.2	496.5
137.5°	278.1	281.0	289.6	302.3	319.3	338.7	362.8	389.1	417.5	451.0	488.4
140°	286.2	288.5	297.1	310.4	326.8	345.6	369.1	394.1	420.7	450.4	484.0
142.5°	294.9	297.3	305.3	317.9	333.7	351.9	374.7	397.8	423.2	450.4	480.3
145°	307.3	309.6	317.5	328.4	343.3	360.5	380.8	401.9	424.6	448.8	473.8
147.5°	321.2	322.0	328.9	340.1	352.5	368.0	387.1	405.5	425.4	446.0	468.1
150°	330.0	330.8	337.0	346.4	358.1	373.0	390.2	407.4	425.4	444.1	463.7
152.5°	338.1	338.3	344.5	353.3	363.8	377.4	392.7	408.6	424.1	441.0	458.7
155°	349.5	350.3	355.0	362.8	371.4	383.1	396.4	409.7	422.2	436.3	451.2
157.5°	360.6	360.6	365.0	371.1	378.6	387.8	399.1	409.7	420.2	431.5	443.5
160°	367.5	367.5	370.6	376.1	382.4	391.0	400.3	409.7	418.3	427.7	437.9
162.5°	373.8	373.1	375.6	380.5	386.1	392.8	401.6	409.7	416.5	424.0	432.9
165°	380.8	380.8	382.4	386.3	390.2	394.9	401.9	408.2	412.9	418.3	424.6
167.5°	387.8	387.1	387.8	390.8	393.0	396.6	401.8	406.3	409.1	412.7	417.1
170°	391.0	390.2	391.0	393.3	394.9	397.2	401.1	405.0	406.6	408.9	412.1
172.5°	394.1	393.3	393.5	395.2	396.1	397.8	400.5	403.8	404.1	405.2	407.7
175°	397.2	396.4	396.4	397.2	398.0	398.0	399.6	401.9	401.1	401.1	402.7
177.5°	398.6	398.0	397.4	398.0	398.0	398.0	398.6	399.9	398.6	398.6	399.2
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0



TEST NUMBER: P332516

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	590.7	590.7	590.7	590.7	590.7	590.7	590.7	590.7
2.5°	588.6	589.5	590.3	590.7	590.6	590.5	590.4	590.3
5°	585.5	586.6	587.8	588.2	588.0	587.8	587.6	587.4
7.5°	578.9	579.9	580.8	581.2	581.1	580.9	580.8	580.7
10°	573.5	574.3	575.2	575.5	575.3	575.0	574.8	574.6
12.5°	566.8	567.7	568.7	569.0	568.7	568.4	568.1	567.8
15°	554.1	554.7	555.4	555.5	555.2	554.9	554.6	554.3
17.5°	539.6	540.0	540.4	540.5	540.3	540.1	539.9	539.7
20°	528.9	529.2	529.5	529.6	529.3	529.1	528.9	528.7
22.5°	517.6	518.2	518.8	518.9	518.5	518.1	517.7	517.4
25°	499.1	499.2	499.3	499.2	498.7	498.3	497.9	497.5
27.5°	478.3	478.1	477.8	477.4	476.9	476.4	475.8	475.3
30°	464.0	463.6	463.1	462.7	462.1	461.6	461.1	460.6
32.5°	449.4	448.9	448.4	447.9	447.4	446.8	446.3	445.8
35°	426.4	425.7	424.9	424.3	423.8	423.3	422.7	422.2
37.5°	402.3	401.5	400.7	400.0	399.3	398.6	397.9	397.2
40°	385.6	384.5	383.5	382.7	382.1	381.6	381.1	380.6
42.5°	369.3	368.1	366.9	366.1	365.7	365.4	365.0	364.7
45°	344.2	343.0	341.9	341.1	340.8	340.5	340.2	339.9
47.5°	319.8	318.5	317.2	316.2	315.4	314.6	313.8	313.0
50°	302.8	301.4	299.9	298.8	298.2	297.6	296.9	296.3
52.5°	285.4	284.1	282.8	281.7	280.9	280.1	279.3	278.5
55°	259.7	258.4	257.2	256.2	255.6	255.0	254.3	253.7
57.5°	234.0	232.8	231.6	230.7	230.1	229.5	228.9	228.2
60°	216.3	215.4	214.4	213.7	213.2	212.6	212.1	211.6
62.5°	199.1	198.2	197.3	196.6	196.1	195.6	195.1	194.5
65°	174.0	172.9	171.9	171.1	170.6	170.0	169.5	169.0
67.5°	148.1	147.1	146.1	145.5	145.4	145.2	145.1	144.9
70°	131.8	131.0	130.1	129.5	129.2	128.9	128.6	128.3
72.5°	115.5	114.8	114.1	113.6	113.3	113.0	112.7	112.4
75°	91.9	91.5	91.1	90.8	90.7	90.6	90.5	90.4
77.5°	69.6	69.5	69.4	69.2	68.9	68.6	68.3	68.1
80°	55.4	55.2	55.0	54.9	54.7	54.6	54.5	54.4
82.5°	42.7	42.6	42.5	42.4	42.3	42.1	42.0	41.9
85°	24.6	24.6	24.6	24.6	24.5	24.4	24.2	24.1
87.5°	11.9	12.1	12.2	12.2	12.4	12.5	12.4	12.4
90°	14.1	14.9	15.6	15.6	16.4	17.2	16.4	16.4
92.5°	153.6	115.6	92.0	76.3	67.1	62.9	60.2	60.2
95°	579.4	458.2	353.4	277.6	239.3	215.0	201.0	190.8
97.5°	856.0	811.0	734.5	652.9	596.8	549.7	526.2	510.0
100°	943.0	958.6	920.3	862.5	794.4	746.7	723.3	717.0
102.5°	938.6	1016.2	1027.3	1003.2	961.5	926.9	902.2	897.2
105°	875.8	1011.0	1088.4	1120.5	1122.1	1115.8	1104.9	1100.2
107.5°	786.5	930.5	1039.5	1109.2	1147.9	1165.7	1173.5	1175.5
110°	732.7	867.9	981.3	1067.3	1122.8	1155.7	1169.8	1176.8



TEST NUMBER: P332516

CATALOG NUMBER: SA4XXDIP-C350D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	693.3	812.9	920.0	1006.0	1069.0	1108.8	1128.5	1139.9
115°	653.7	749.9	841.3	916.4	978.2	1025.1	1050.1	1056.4
117.5°	634.3	713.9	785.8	849.5	902.2	941.6	966.9	971.8
120°	625.5	698.3	760.8	816.3	860.9	895.3	915.6	924.2
122.5°	618.0	688.2	745.2	793.8	831.5	860.9	878.1	886.7
125°	605.2	672.5	726.4	769.4	800.7	823.4	838.2	842.9
127.5°	589.6	653.8	707.6	748.5	779.9	800.1	812.6	817.3
130°	577.1	638.8	692.0	733.4	765.5	785.1	797.6	802.3
132.5°	563.9	621.9	673.9	715.3	746.7	768.8	780.7	785.4
135°	545.8	596.6	644.3	683.4	714.7	736.6	749.1	753.8
137.5°	529.4	572.4	612.6	647.9	677.1	698.7	709.0	714.7
140°	520.0	556.7	591.9	624.8	652.1	669.3	680.3	686.5
142.5°	511.2	543.6	573.8	602.2	626.5	642.4	652.1	656.5
145°	498.9	525.5	548.9	570.8	590.4	603.6	611.5	615.4
147.5°	488.7	509.8	528.6	545.8	560.2	571.6	577.5	578.9
150°	482.4	500.4	516.1	530.1	542.7	552.8	557.5	558.3
152.5°	475.6	491.0	505.4	517.0	527.6	535.9	538.7	539.5
155°	465.2	477.8	489.5	498.9	506.7	512.9	515.3	515.3
157.5°	454.1	464.6	474.5	482.0	487.9	492.6	494.0	494.0
160°	447.3	455.9	464.5	470.7	475.4	480.1	480.9	480.9
162.5°	440.4	447.7	454.5	460.1	463.5	468.2	469.0	468.4
165°	430.8	435.5	441.0	444.9	448.0	451.2	450.4	449.6
167.5°	421.6	425.2	429.6	431.9	433.5	435.5	435.4	434.7
170°	416.0	418.3	421.5	423.8	425.4	426.1	425.4	425.4
172.5°	411.0	412.7	414.6	416.3	417.2	418.0	417.2	416.0
175°	404.3	405.0	406.6	406.6	406.6	408.2	406.6	405.0
177.5°	399.9	400.5	400.5	401.1	400.5	401.1	399.9	398.6
180°	398.0	398.0	398.0	398.0	398.0	398.0	398.0	398.0

(END OF REPORT)