

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332541

Luminaire Tested: **SA4XXDIP-C575D365U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332541
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C575D365U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3955.1 lumens
Efficiency: N/A
Efficacy: 143.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332541
CATALOG NUMBER: SA4XXDIP-C575D365U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332541

CATALOG NUMBER: SA4XXDIP-C575D365U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	51	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	38
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25
7	60	47	39	34	56	45	37	32	40	34	30	36	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7840	7840	7840
5°	7864	7769	7826
10°	7814	7706	7744
15°	7720	7596	7616
20°	7594	7460	7467
25°	7451	7306	7285
30°	7276	7124	7058
35°	7094	6933	6841
40°	6905	6716	6593
45°	6707	6503	6379
50°	6489	6314	6118
55°	6253	6068	5871
60°	6018	5792	5616
65°	5752	5530	5307
70°	5455	5179	4978
75°	5000	4757	4635
80°	4449	4268	4161
85°	3890	3751	3677



TEST NUMBER: P332541

CATALOG NUMBER: SA4XXDIP-C575D365U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	2.3
10°-20°	257.7	6.5
20°-30°	379.3	9.6
30°-40°	440.9	11.1
40°-50°	440.9	11.1
50°-60°	385.7	9.8
60°-70°	286.4	7.2
70°-80°	162.7	4.1
80°-90°	48.3	1.2
90°-100°	16.2	0.4
100°-110°	103.0	2.6
110°-120°	197.1	5.0
120°-130°	250.2	6.3
130°-140°	267.7	6.8
140°-150°	250.4	6.3
150°-160°	201.9	5.1
160°-170°	130.2	3.3
170°-180°	44.9	1.1
0°-30°	728.4	18.4
0°-40°	1169.3	29.6
0°-60°	1996.0	50.5
0°-90°	2493.5	63.0
90°-120°	316.3	8.0
90°-150°	1084.6	27.4
90°-180°	1462.0	37.0
0°-180°	3955.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	920	909	913	911	260
25°	836	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	150	149	170
85°	42	42	40	40	40	46
90°	1	5	8	10	11	3
95°	19	8	8	10	10	25
105°	106	108	110	113	101	111
115°	199	200	199	200	200	195
125°	279	280	280	281	281	249
135°	346	346	347	348	349	267
145°	399	400	400	401	402	249
155°	438	438	437	438	438	202
165°	462	460	460	463	460	130
175°	472	470	471	474	470	45
180°	472	472	472	472	472	



TEST NUMBER: P332541

CATALOG NUMBER: SA4XXDIP-C575D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	973.6	973.2	972.8	972.4	972.0	971.0	969.5	968.0	966.4	964.9	966.3
5°	970.4	969.7	969.0	968.3	967.6	966.3	964.4	962.5	960.6	958.7	960.6
7.5°	961.3	960.6	960.0	959.3	958.6	957.2	955.1	953.0	950.8	948.7	950.3
10°	953.2	952.6	951.9	951.2	950.5	949.0	946.8	944.5	942.3	940.0	941.4
12.5°	942.7	942.0	941.3	940.6	939.9	938.4	936.0	933.6	931.2	928.8	930.3
15°	923.7	923.0	922.3	921.6	920.9	919.3	916.7	914.1	911.5	908.9	909.9
17.5°	900.8	899.9	899.1	898.2	897.3	895.7	893.2	890.8	888.3	885.9	886.5
20°	884.0	883.1	882.3	881.4	880.5	878.8	876.2	873.6	871.0	868.4	868.9
22.5°	865.9	864.8	863.7	862.5	861.4	859.5	856.9	854.3	851.7	849.1	850.1
25°	836.5	835.3	834.1	832.9	831.7	829.9	827.4	825.0	822.6	820.2	820.4
27.5°	802.9	801.7	800.4	799.2	797.9	796.2	793.9	791.7	789.4	787.2	786.8
30°	780.5	779.1	777.7	776.3	775.0	773.1	770.9	768.6	766.4	764.2	763.5
32.5°	756.8	755.6	754.3	753.1	751.9	750.0	747.7	745.3	742.9	740.5	739.7
35°	719.8	718.6	717.4	716.2	715.0	713.1	710.7	708.3	705.9	703.5	702.2
37.5°	680.7	679.6	678.5	677.4	676.3	674.5	671.9	669.3	666.7	664.1	662.8
40°	655.2	653.8	652.4	651.1	649.7	647.7	645.1	642.5	639.9	637.3	635.6
42.5°	627.8	627.0	626.2	625.3	624.5	622.6	619.8	616.9	614.0	611.2	609.2
45°	587.5	586.3	585.1	583.9	582.7	580.7	577.9	575.1	572.4	569.6	567.7
47.5°	545.3	544.5	543.7	542.8	542.0	540.3	537.8	535.2	532.6	530.1	527.9
50°	516.7	516.0	515.3	514.6	513.9	512.4	510.0	507.5	505.1	502.7	500.3
52.5°	488.7	487.9	487.0	486.2	485.4	483.7	481.1	478.6	476.0	473.4	471.3
55°	444.3	443.8	443.3	442.8	442.3	440.8	438.4	435.9	433.5	431.1	429.0
57.5°	402.0	401.4	400.8	400.2	399.6	398.2	395.8	393.4	391.0	388.6	386.6
60°	372.7	371.9	371.0	370.1	369.3	367.7	365.5	363.2	361.0	358.7	357.2
62.5°	344.1	343.4	342.6	341.9	341.2	339.6	337.3	334.9	332.5	330.1	328.7
65°	301.1	300.3	299.4	298.6	297.7	296.4	294.7	292.9	291.2	289.5	287.7
67.5°	257.9	257.1	256.3	255.5	254.7	253.5	251.8	250.2	248.5	246.8	245.2
70°	231.1	229.9	228.7	227.5	226.3	225.0	223.6	222.2	220.8	219.4	218.1
72.5°	202.5	201.3	200.1	198.8	197.6	196.5	195.4	194.3	193.2	192.0	190.9
75°	160.3	159.4	158.6	157.7	156.8	156.0	155.1	154.2	153.4	152.5	151.8
77.5°	120.0	119.6	119.2	118.9	118.5	117.9	117.1	116.4	115.6	114.9	114.6
80°	95.7	95.2	94.7	94.2	93.6	93.2	92.9	92.5	92.2	91.8	91.5
82.5°	72.1	71.8	71.6	71.3	71.1	70.9	70.9	70.8	70.7	70.7	70.4
85°	42.0	42.0	42.0	42.0	42.0	41.8	41.5	41.2	40.8	40.5	40.5
87.5°	16.4	16.4	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.6
90°	1.1	1.9	2.8	3.7	4.5	5.3	5.9	6.5	7.1	7.8	8.2
92.5°	4.5	4.5	4.5	4.6	4.6	5.0	5.6	6.2	6.9	7.5	8.0
95°	19.4	16.8	14.1	11.4	8.8	7.5	7.5	7.6	7.7	7.8	8.2
97.5°	41.3	42.9	44.6	46.3	47.9	44.4	35.6	26.9	18.1	9.3	9.4
100°	58.0	59.4	60.8	62.2	63.6	58.9	48.1	37.2	26.4	15.6	14.2
102.5°	76.6	77.7	78.7	79.7	80.8	80.6	79.2	77.8	76.3	74.9	60.5
105°	106.4	106.8	107.3	107.8	108.3	108.7	109.1	109.5	109.9	110.3	111.0
107.5°	134.0	134.2	134.5	134.7	135.0	135.3	135.9	136.4	136.9	137.5	137.8
110°	152.7	152.9	153.1	153.4	153.6	154.0	154.4	154.9	155.4	155.9	156.0



TEST NUMBER: P332541

CATALOG NUMBER: SA4XXDIP-C575D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.8	171.2	171.6	172.0	172.5	172.8	173.0	173.2	173.4	173.7	173.6
115°	198.6	198.9	199.1	199.3	199.6	199.6	199.6	199.5	199.4	199.3	199.5
117.5°	223.7	224.0	224.3	224.7	225.0	225.2	225.4	225.6	225.7	225.9	225.9
120°	240.7	241.0	241.3	241.6	241.9	242.0	242.0	241.9	241.8	241.7	241.9
122.5°	256.5	256.7	256.9	257.1	257.3	257.4	257.5	257.6	257.7	257.9	257.9
125°	279.2	279.5	279.8	280.1	280.5	280.5	280.4	280.2	280.1	279.9	280.1
127.5°	300.7	300.8	300.8	300.9	301.0	301.2	301.6	301.9	302.3	302.7	302.6
130°	314.5	314.6	314.7	314.8	314.9	315.0	315.2	315.5	315.7	316.0	316.0
132.5°	327.3	327.4	327.5	327.7	327.8	328.0	328.3	328.6	328.9	329.2	329.3
135°	346.3	346.3	346.2	346.1	346.0	346.1	346.5	346.8	347.1	347.4	347.6
137.5°	363.2	363.3	363.3	363.3	363.4	363.6	363.9	364.2	364.6	364.9	365.1
140°	374.3	374.4	374.6	374.7	374.9	375.0	375.2	375.4	375.5	375.7	375.9
142.5°	384.2	384.4	384.7	385.0	385.3	385.5	385.6	385.7	385.8	385.9	386.0
145°	399.4	399.6	399.8	400.1	400.3	400.4	400.4	400.4	400.4	400.4	400.5
147.5°	411.4	411.9	412.3	412.8	413.2	413.4	413.3	413.2	413.1	413.1	413.1
150°	420.2	420.5	420.8	421.2	421.5	421.6	421.5	421.4	421.3	421.3	421.3
152.5°	427.6	427.8	428.1	428.3	428.6	428.6	428.5	428.3	428.2	428.1	428.2
155°	437.9	438.0	438.0	438.1	438.2	438.1	437.9	437.6	437.4	437.2	437.5
157.5°	446.6	446.5	446.5	446.4	446.4	446.2	446.0	445.7	445.4	445.2	445.6
160°	451.7	451.4	451.2	451.0	450.7	450.6	450.5	450.4	450.3	450.2	450.7
162.5°	456.2	455.9	455.6	455.3	455.0	454.8	454.7	454.6	454.6	454.5	455.0
165°	461.9	461.5	461.1	460.7	460.3	460.1	460.1	460.1	460.1	460.1	460.8
167.5°	466.4	466.0	465.6	465.2	464.8	464.6	464.5	464.5	464.4	464.4	465.1
170°	469.0	468.5	468.0	467.6	467.1	466.9	467.0	467.1	467.1	467.2	467.8
172.5°	470.7	470.2	469.7	469.3	468.8	468.6	468.7	468.8	468.8	468.9	469.5
175°	472.5	472.0	471.6	471.1	470.6	470.4	470.5	470.6	470.7	470.7	471.5
177.5°	473.4	472.9	472.5	472.0	471.6	471.4	471.6	471.7	471.8	471.9	472.5
180°	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5



TEST NUMBER: P332541

CATALOG NUMBER: SA4XXDIP-C575D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	971.1	971.1	971.1	971.1	971.1	971.1	971.1	971.1
2.5°	967.7	969.1	970.5	971.1	970.9	970.8	970.7	970.5
5°	962.5	964.4	966.3	967.1	966.7	966.4	966.0	965.7
7.5°	951.8	953.3	954.8	955.5	955.3	955.1	954.9	954.6
10°	942.8	944.2	945.6	946.1	945.7	945.4	945.0	944.7
12.5°	931.9	933.4	934.9	935.4	934.9	934.4	934.0	933.5
15°	911.0	912.0	913.0	913.3	912.8	912.3	911.7	911.2
17.5°	887.2	887.8	888.5	888.6	888.3	887.9	887.6	887.3
20°	869.5	870.0	870.5	870.6	870.2	869.9	869.6	869.2
22.5°	851.0	851.9	852.9	853.0	852.4	851.8	851.2	850.5
25°	820.5	820.7	820.9	820.6	819.9	819.2	818.5	817.8
27.5°	786.4	785.9	785.5	784.9	784.0	783.2	782.3	781.4
30°	762.8	762.1	761.4	760.6	759.7	758.9	758.0	757.1
32.5°	738.8	738.0	737.2	736.3	735.5	734.6	733.7	732.9
35°	701.0	699.8	698.6	697.6	696.7	695.8	695.0	694.1
37.5°	661.5	660.1	658.8	657.6	656.5	655.3	654.2	653.0
40°	633.9	632.1	630.4	629.1	628.2	627.4	626.5	625.6
42.5°	607.2	605.1	603.1	601.8	601.3	600.7	600.1	599.5
45°	565.8	563.9	562.0	560.8	560.3	559.8	559.2	558.7
47.5°	525.8	523.6	521.5	519.8	518.5	517.1	515.8	514.5
50°	497.8	495.4	493.0	491.3	490.2	489.2	488.2	487.1
52.5°	469.1	467.0	464.9	463.1	461.8	460.5	459.2	457.9
55°	427.0	424.9	422.8	421.2	420.2	419.2	418.1	417.1
57.5°	384.7	382.7	380.7	379.2	378.2	377.2	376.2	375.2
60°	355.6	354.1	352.5	351.3	350.4	349.6	348.7	347.8
62.5°	327.3	325.8	324.4	323.3	322.4	321.6	320.7	319.8
65°	286.0	284.3	282.6	281.3	280.4	279.5	278.7	277.8
67.5°	243.5	241.9	240.2	239.2	239.0	238.8	238.5	238.3
70°	216.7	215.3	213.9	213.0	212.4	211.9	211.4	210.9
72.5°	189.8	188.7	187.6	186.8	186.3	185.8	185.3	184.7
75°	151.1	150.4	149.8	149.3	149.1	149.0	148.8	148.6
77.5°	114.4	114.2	114.0	113.7	113.2	112.8	112.3	111.9
80°	91.1	90.8	90.4	90.2	90.0	89.8	89.7	89.5
82.5°	70.2	70.0	69.8	69.6	69.5	69.3	69.1	68.9
85°	40.5	40.5	40.5	40.4	40.2	40.0	39.9	39.7
87.5°	16.7	16.8	16.9	16.9	17.0	17.0	17.0	17.1
90°	8.7	9.2	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	8.4	8.9	9.4	9.6	9.7	9.7	9.7	9.8
95°	8.7	9.2	9.7	9.9	10.0	10.1	10.2	10.2
97.5°	9.4	9.5	9.5	9.6	9.7	9.7	9.8	9.9
100°	12.9	11.5	10.2	9.6	9.7	9.7	9.8	9.9
102.5°	46.1	31.7	17.3	10.1	10.1	10.1	10.2	10.2
105°	111.7	112.4	113.1	112.0	109.2	106.4	103.5	100.7
107.5°	138.2	138.5	138.9	139.2	139.5	139.8	140.1	140.4
110°	156.2	156.3	156.5	156.7	156.9	157.2	157.4	157.6



TEST NUMBER: P332541

CATALOG NUMBER: SA4XXDIP-C575D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	173.6	173.6	173.5	173.7	174.0	174.3	174.6	174.9
115°	199.6	199.8	200.0	200.0	200.0	200.0	200.0	200.0
117.5°	225.8	225.8	225.8	225.7	225.7	225.7	225.7	225.6
120°	242.0	242.2	242.4	242.4	242.2	242.0	241.9	241.7
122.5°	258.0	258.1	258.2	258.2	258.0	257.9	257.7	257.6
125°	280.4	280.6	280.8	281.0	281.1	281.2	281.2	281.3
127.5°	302.6	302.5	302.5	302.4	302.4	302.3	302.2	302.2
130°	316.1	316.2	316.3	316.3	316.3	316.3	316.3	316.3
132.5°	329.4	329.5	329.6	329.6	329.5	329.4	329.4	329.3
135°	347.7	347.9	348.0	348.2	348.3	348.5	348.7	348.8
137.5°	365.3	365.5	365.6	365.7	365.6	365.6	365.5	365.5
140°	376.1	376.4	376.6	376.8	376.9	376.9	377.0	377.1
142.5°	386.2	386.4	386.5	386.6	386.7	386.7	386.7	386.7
145°	400.6	400.7	400.7	400.8	401.0	401.2	401.3	401.5
147.5°	413.2	413.3	413.3	413.4	413.5	413.5	413.6	413.7
150°	421.3	421.3	421.3	421.3	421.4	421.5	421.5	421.6
152.5°	428.3	428.4	428.6	428.6	428.5	428.5	428.5	428.4
155°	437.8	438.1	438.4	438.5	438.2	438.0	437.8	437.5
157.5°	446.0	446.4	446.8	446.8	446.4	446.0	445.6	445.2
160°	451.2	451.7	452.1	452.1	451.7	451.2	450.7	450.2
162.5°	455.4	455.9	456.4	456.3	455.8	455.3	454.7	454.2
165°	461.4	462.0	462.7	462.6	461.9	461.2	460.5	459.8
167.5°	465.8	466.5	467.1	467.1	466.3	465.5	464.7	464.0
170°	468.5	469.1	469.7	469.6	468.9	468.1	467.3	466.5
172.5°	470.2	470.8	471.4	471.3	470.5	469.6	468.8	467.9
175°	472.2	472.9	473.6	473.5	472.5	471.6	470.6	469.7
177.5°	473.0	473.5	474.0	473.8	473.1	472.3	471.6	470.8
180°	472.5	472.5	472.5	472.5	472.5	472.5	472.5	472.5

(END OF REPORT)