

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332582

Luminaire Tested: **SA4XXDIP-C795D365U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332582  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4851.5 lumens  
Efficiency: N/A  
Efficacy: 138.6 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332582  
CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	73	
1	103	99	95	91	98	94	91	87	85	82	80	77	75	73	69	67	66	66	66	66	62	
2	94	87	81	75	89	83	77	72	75	70	67	68	64	61	61	58	56	56	56	56	53	
3	86	77	69	63	82	73	66	61	66	61	57	60	56	52	54	51	48	48	48	48	45	
4	79	68	60	54	75	65	58	52	59	53	49	54	49	45	49	45	42	42	42	42	39	
5	73	61	53	47	69	58	51	45	53	47	42	49	43	39	44	40	37	37	37	37	34	
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	32	32	32	32	30	
7	62	50	42	36	59	48	40	35	44	38	33	40	35	31	37	32	29	29	29	29	27	
8	58	45	38	32	55	44	36	31	40	34	29	37	32	28	34	29	26	26	26	26	24	
9	54	42	34	29	52	40	33	28	37	31	27	34	29	25	31	27	24	24	24	24	22	
10	51	38	31	26	48	37	30	25	34	28	24	32	26	23	29	25	21	21	21	21	20	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10365	10365	10365	10365
5°	12206	10391	9172	10391
10°	14614	10346	8257	10346
15°	17291	10242	7583	10242
20°	19254	10134	6981	10134
25°	19565	9977	6566	9977
30°	16648	9826	6435	9826
35°	12799	9581	6436	9581
40°	9977	9293	6558	9293
45°	8318	8859	6667	8859
50°	7321	8329	6894	8329
55°	6707	7695	7171	7695
60°	6286	7127	7505	7127
65°	5851	6491	7782	6491
70°	5349	5863	7959	5863
75°	4779	5159	7863	5159
80°	4007	4226	7615	4226
85°	2955	3057	7290	3057



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.1	2.6
10°-20°	385.5	7.9
20°-30°	611.3	12.6
30°-40°	680.3	14.0
40°-50°	619.3	12.8
50°-60°	506.1	10.4
60°-70°	361.3	7.4
70°-80°	198.9	4.1
80°-90°	55.3	1.1
90°-100°	129.9	2.7
100°-110°	270.4	5.6
110°-120°	242.2	5.0
120°-130°	203.7	4.2
130°-140°	169.9	3.5
140°-150°	129.8	2.7
150°-160°	91.2	1.9
160°-170°	53.7	1.1
170°-180°	17.5	0.4
0°-30°	1121.9	23.1
0°-40°	1802.3	37.1
0°-60°	2927.7	60.3
0°-90°	3543.2	73.0
90°-120°	642.6	13.2
90°-150°	1146.0	23.6
90°-180°	1308.0	27.0
0°-180°	4851.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1506	1282	1132	1282	1506	153
15°	2069	1225	907	1225	2069	585
25°	2196	1120	737	1120	2196	968
35°	1299	972	653	972	1299	824
45°	729	776	584	776	729	574
55°	476	547	510	547	476	430
65°	306	340	407	340	306	303
75°	153	165	252	165	153	163
85°	32	33	79	33	32	39
90°	7	0	7	0	7	7
95°	86	12	86	12	86	134
105°	497	41	497	41	497	492
115°	478	73	478	73	478	474
125°	381	101	381	101	381	346
135°	341	120	341	120	341	263
145°	278	139	278	139	278	176
155°	233	158	233	158	233	109
165°	203	172	203	172	203	58
175°	183	180	183	180	183	18
180°	180	180	180	180	180	



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1366.4	1366.0	1361.7	1360.9	1357.9	1354.1	1353.2	1346.4	1332.8	1326.4	1324.7
5°	1506.2	1516.8	1503.0	1500.3	1498.7	1481.2	1472.1	1461.5	1437.0	1422.7	1411.5
7.5°	1673.0	1674.2	1668.2	1663.3	1649.8	1634.4	1611.5	1587.0	1557.9	1527.5	1504.7
10°	1782.7	1787.0	1780.1	1779.0	1751.9	1734.9	1700.8	1672.1	1639.1	1602.4	1568.9
12.5°	1898.5	1892.5	1889.0	1866.2	1861.2	1830.2	1790.6	1761.0	1710.2	1668.0	1623.4
15°	2068.9	2057.2	2049.7	2018.3	2002.9	1959.8	1917.8	1885.4	1818.9	1755.6	1707.7
17.5°	2168.8	2180.5	2163.3	2150.4	2110.5	2080.3	2037.4	1969.3	1917.3	1838.7	1778.3
20°	2241.2	2242.2	2232.7	2219.4	2188.0	2149.7	2102.9	2028.4	1966.2	1888.0	1805.1
22.5°	2260.7	2261.0	2256.9	2244.5	2220.7	2189.7	2142.5	2080.3	2004.9	1919.9	1837.0
25°	2196.5	2194.4	2199.2	2213.0	2203.9	2194.4	2167.2	2121.0	2050.8	1960.9	1871.5
27.5°	1957.8	1972.5	1999.5	2033.5	2066.3	2091.3	2098.3	2088.8	2045.3	1971.4	1877.8
30°	1785.9	1804.0	1824.2	1858.2	1924.2	1962.0	2003.4	2034.8	2017.3	1958.2	1871.0
32.5°	1597.0	1601.5	1631.5	1670.2	1730.6	1803.3	1869.0	1932.7	1953.9	1922.9	1850.2
35°	1298.7	1306.2	1338.6	1376.9	1450.9	1539.7	1638.6	1726.9	1799.7	1829.0	1791.8
37.5°	1059.8	1081.2	1104.1	1145.3	1210.4	1290.3	1393.1	1507.3	1615.9	1688.7	1701.0
40°	946.7	960.0	976.5	1007.8	1063.1	1141.9	1230.1	1361.0	1476.4	1580.6	1614.7
42.5°	857.3	865.1	875.2	903.6	945.7	1024.0	1104.6	1219.7	1335.6	1460.2	1517.2
45°	728.6	736.6	753.6	770.1	802.0	856.3	931.2	1025.9	1142.4	1262.6	1367.9
47.5°	635.7	640.8	650.9	668.5	695.6	731.4	792.4	871.5	979.4	1096.1	1208.3
50°	582.9	587.1	595.1	611.1	631.8	663.7	713.7	787.7	872.2	989.8	1099.8
52.5°	541.2	542.9	548.8	559.6	576.1	602.9	643.9	705.1	783.7	888.5	998.2
55°	476.5	478.7	484.0	492.0	506.3	523.3	554.7	600.4	669.1	760.0	855.2
57.5°	423.3	424.8	429.3	432.4	444.2	458.0	482.2	514.8	566.8	643.9	728.9
60°	389.3	388.2	393.6	396.2	404.2	415.9	434.5	465.9	511.1	573.3	651.5
62.5°	356.1	354.6	359.1	362.6	367.2	377.2	392.4	417.0	453.7	509.9	577.5
65°	306.3	304.2	306.9	311.1	315.4	320.7	331.9	353.7	382.9	423.3	474.9
67.5°	256.3	258.6	259.0	261.1	263.6	270.8	278.5	293.9	314.5	346.9	390.6
70°	226.6	227.1	229.2	229.2	230.8	237.2	243.6	252.6	272.8	302.6	338.2
72.5°	196.8	199.0	198.2	199.9	201.0	205.3	210.0	218.6	235.8	257.9	288.0
75°	153.2	154.8	154.8	155.3	156.9	158.5	162.2	168.6	180.8	197.3	218.1
77.5°	111.7	111.9	112.6	114.6	114.6	117.1	119.9	125.0	131.0	142.3	155.0
80°	86.2	87.2	86.7	87.8	87.8	89.9	90.9	97.3	100.0	107.4	117.5
82.5°	63.2	64.2	64.1	65.6	66.5	66.9	68.4	70.9	73.6	80.2	84.3
85°	31.9	33.0	31.9	33.0	34.6	35.1	36.7	37.2	39.4	41.0	44.7
87.5°	10.8	12.1	12.2	12.5	13.3	13.8	14.1	13.6	15.2	15.7	17.3
90°	7.4	7.4	7.8	7.4	7.1	7.1	6.7	6.4	6.0	6.4	5.7
92.5°	27.2	27.2	28.4	30.3	34.5	41.6	52.2	69.4	93.4	112.1	98.1
95°	86.2	90.8	97.2	108.1	125.5	159.7	207.1	261.9	296.2	288.0	217.4
97.5°	230.5	237.9	248.5	269.7	295.1	332.0	366.6	386.9	372.1	303.4	203.4
100°	324.1	326.9	337.5	359.1	389.8	416.0	433.3	426.2	374.6	284.2	184.5
102.5°	405.5	407.8	419.0	434.6	453.4	464.3	459.3	424.3	353.4	260.1	171.8
105°	497.3	499.4	504.3	507.2	506.5	492.0	457.0	395.8	314.9	231.8	160.8
107.5°	531.3	530.4	526.9	518.8	501.4	469.8	420.6	355.5	283.8	216.0	158.8
110°	531.9	528.7	522.4	507.5	482.4	443.6	392.3	331.2	268.3	210.6	159.4



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	515.2	510.1	501.2	483.2	454.7	415.8	367.4	313.3	259.5	208.1	161.1
115°	477.5	474.7	463.3	442.1	414.2	380.3	338.9	295.5	251.3	206.8	164.3
117.5°	439.2	437.0	425.6	407.8	384.0	355.2	322.7	286.7	247.6	206.4	167.8
120°	417.8	413.9	404.7	389.1	369.0	343.9	315.6	282.7	245.6	206.4	170.4
122.5°	400.8	396.9	389.1	375.8	358.8	336.8	311.1	279.3	243.4	206.1	172.9
125°	381.0	378.9	372.2	361.9	347.8	328.3	303.9	273.6	239.6	205.7	176.7
127.5°	369.4	367.3	361.6	352.5	338.3	319.9	295.5	266.5	234.6	204.9	179.8
130°	362.6	360.5	354.8	346.0	331.5	312.8	288.8	260.8	231.5	204.6	182.0
132.5°	355.0	352.9	347.5	337.5	323.3	304.6	281.1	254.9	228.7	204.4	184.0
135°	340.7	338.6	332.9	323.0	308.9	291.2	269.7	246.7	224.4	203.9	187.0
137.5°	323.0	320.5	315.8	306.1	292.8	276.9	258.7	239.3	220.8	203.9	188.7
140°	310.3	307.5	302.5	294.8	282.4	267.5	251.6	235.0	218.8	203.6	190.1
142.5°	296.7	294.8	290.4	283.2	272.2	259.3	245.7	231.1	217.1	203.6	191.3
145°	278.1	276.4	272.8	266.8	258.0	248.1	237.5	225.5	214.2	202.9	191.9
147.5°	261.7	261.0	258.4	253.2	246.7	238.9	230.4	220.9	211.6	201.6	192.3
150°	252.3	252.0	249.9	245.3	239.6	233.3	226.2	218.1	209.6	200.7	192.3
152.5°	243.9	243.5	242.2	238.5	233.7	228.5	222.0	215.0	207.3	199.3	191.7
155°	232.9	232.9	231.8	229.0	225.5	221.2	215.9	210.3	203.9	197.2	190.9
157.5°	223.3	223.3	222.7	220.5	217.9	214.5	210.0	205.3	200.5	195.0	189.9
160°	217.4	217.4	217.0	214.9	212.8	209.9	206.0	202.2	197.9	193.3	189.1
162.5°	211.7	212.0	211.6	209.5	208.0	205.4	202.4	199.1	195.7	191.6	188.2
165°	203.2	203.6	203.9	202.5	201.1	199.3	196.9	194.7	191.9	189.1	186.6
167.5°	196.5	196.8	196.9	195.9	195.2	194.2	192.2	190.6	188.5	186.5	184.9
170°	192.3	192.3	192.6	192.3	191.6	190.5	189.1	188.0	186.3	184.8	183.8
172.5°	188.0	188.6	188.9	188.6	188.2	187.4	186.5	185.8	184.3	183.1	182.7
175°	183.1	183.8	184.5	183.8	183.8	183.8	183.1	182.7	182.0	181.3	181.3
177.5°	180.2	180.7	181.3	181.0	181.3	181.0	181.0	180.7	180.5	180.2	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1325.1	1319.2	1314.9	1311.5	1302.2	1296.6	1292.4	1286.4	1279.6	1272.4	1263.4
5°	1400.3	1382.2	1369.0	1348.7	1329.6	1313.6	1297.2	1282.3	1264.2	1244.5	1230.1
7.5°	1479.4	1452.5	1418.0	1388.1	1354.5	1325.2	1299.1	1272.3	1244.4	1217.4	1192.6
10°	1529.6	1495.0	1456.7	1411.5	1369.0	1331.2	1296.1	1262.1	1229.1	1196.1	1167.9
12.5°	1583.6	1540.5	1483.9	1431.1	1383.4	1332.9	1290.6	1248.9	1209.1	1174.4	1141.5
15°	1656.1	1593.9	1528.5	1457.8	1395.0	1336.0	1278.0	1225.4	1180.7	1134.9	1103.0
17.5°	1700.7	1623.7	1548.9	1475.0	1399.1	1324.6	1262.1	1201.3	1145.4	1099.9	1059.7
20°	1730.1	1653.5	1560.4	1486.5	1396.1	1319.5	1247.2	1179.6	1121.1	1072.7	1031.2
22.5°	1755.6	1667.1	1574.0	1476.7	1386.7	1305.5	1226.3	1158.3	1098.6	1047.6	1007.8
25°	1769.4	1667.8	1566.8	1470.0	1367.9	1271.6	1199.8	1120.1	1056.2	1002.5	960.0
27.5°	1770.9	1662.3	1548.0	1440.4	1335.0	1245.4	1154.7	1083.5	1017.2	960.4	919.5
30°	1766.2	1653.0	1530.1	1413.6	1307.8	1210.5	1131.8	1054.1	986.6	930.2	887.6
32.5°	1751.3	1633.4	1507.1	1383.8	1274.2	1179.0	1097.7	1023.9	958.1	902.5	857.9
35°	1708.3	1591.8	1457.2	1329.1	1216.8	1120.6	1047.2	972.2	906.3	853.6	810.5
37.5°	1640.9	1535.6	1398.8	1266.2	1156.0	1059.3	986.6	918.8	859.3	805.8	761.7
40°	1582.2	1489.7	1352.5	1223.2	1104.1	1012.1	944.0	881.8	822.8	772.2	730.2
42.5°	1514.6	1433.9	1307.4	1170.5	1055.6	963.2	896.8	840.9	785.3	738.6	696.6
45°	1393.9	1340.8	1221.6	1095.1	975.4	888.2	824.9	776.0	729.2	683.4	648.3
47.5°	1255.2	1228.9	1128.6	1008.4	894.8	808.8	753.9	708.7	667.7	629.0	598.0
50°	1162.1	1149.3	1062.6	946.7	838.2	757.3	702.0	663.2	628.1	594.1	564.8
52.5°	1070.2	1069.7	991.6	885.4	785.0	707.1	652.2	616.0	585.6	557.9	531.6
55°	929.7	944.5	883.4	788.7	698.8	628.6	579.2	546.7	525.5	502.6	482.9
57.5°	800.6	825.3	774.9	691.5	616.5	551.8	508.8	484.4	461.7	447.9	433.6
60°	716.4	739.8	700.4	630.2	559.5	504.2	463.2	441.4	421.7	412.2	402.1
62.5°	641.5	662.4	633.2	568.1	506.7	453.6	419.0	398.0	384.7	374.3	367.6
65°	534.5	552.0	527.1	479.7	427.1	384.5	356.3	339.8	327.1	322.8	315.4
67.5°	432.1	448.0	434.5	394.3	352.1	319.8	297.8	282.0	274.4	270.7	265.4
70°	371.2	387.2	372.8	337.7	305.3	278.2	257.4	248.4	240.4	238.8	231.3
72.5°	319.7	330.6	316.2	288.8	261.0	238.2	222.1	212.6	208.5	205.6	201.6
75°	239.9	249.4	239.9	218.6	198.9	183.0	169.1	165.4	160.6	159.0	156.4
77.5°	169.8	178.1	170.7	157.4	142.7	130.4	123.0	118.2	117.1	114.3	115.6
80°	129.8	135.1	128.2	119.1	107.4	98.9	93.6	90.9	87.8	86.7	88.8
82.5°	93.2	95.5	92.0	85.9	77.2	71.7	68.1	65.0	64.4	64.6	64.6
85°	48.4	47.9	47.3	42.0	39.4	35.6	33.5	33.0	32.4	33.5	34.6
87.5°	17.2	17.6	16.7	15.0	13.7	12.3	11.7	11.1	11.7	12.3	12.8
90°	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4	1.1	2.1	2.5
92.5°	71.4	44.0	26.0	18.7	13.5	9.2	5.9	4.0	5.9	9.2	13.5
95°	132.9	74.9	44.2	29.3	20.9	16.3	12.7	11.7	12.7	16.3	20.9
97.5°	119.5	71.6	47.9	35.5	28.2	24.0	20.9	20.9	20.9	24.0	28.2
100°	112.4	72.5	51.6	40.3	33.6	29.3	26.9	26.9	26.9	29.3	33.6
102.5°	110.4	75.3	56.4	45.7	39.2	35.3	33.1	32.5	33.1	35.3	39.2
105°	111.3	82.0	65.0	54.8	48.4	44.2	42.4	41.4	42.4	44.2	48.4
107.5°	116.6	89.8	74.3	64.2	58.1	53.6	51.8	51.1	51.8	53.6	58.1
110°	120.5	95.8	80.2	70.7	64.3	60.1	58.3	57.6	58.3	60.1	64.3





TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	124.8	101.4	86.4	76.9	70.5	66.6	64.5	63.8	64.5	66.6	70.5
115°	131.5	110.3	96.1	86.6	79.9	76.3	73.9	72.8	73.9	76.3	79.9
117.5°	138.3	118.8	105.4	95.5	89.2	85.3	83.1	82.1	83.1	85.3	89.2
120°	143.1	124.8	111.3	101.4	95.4	91.5	89.1	88.4	89.1	91.5	95.4
122.5°	147.7	130.4	117.0	107.4	100.8	97.2	94.7	94.0	94.7	97.2	100.8
125°	154.4	138.2	125.5	115.6	108.9	105.0	102.8	101.4	102.8	105.0	108.9
127.5°	160.3	145.4	133.1	123.1	116.1	111.7	109.1	108.0	109.1	111.7	116.1
130°	164.0	150.2	138.2	127.9	121.2	115.9	113.1	111.7	113.1	115.9	121.2
132.5°	167.7	154.2	142.1	132.5	125.2	120.2	116.5	115.4	116.5	120.2	125.2
135°	172.5	159.7	148.1	138.9	131.5	125.5	121.9	120.5	121.9	125.5	131.5
137.5°	175.9	164.0	153.1	144.3	136.6	130.9	127.0	125.7	127.0	130.9	136.6
140°	178.1	166.8	156.2	147.7	140.3	134.3	130.4	129.4	130.4	134.3	140.3
142.5°	179.8	169.4	159.0	150.8	143.7	138.0	134.4	133.3	134.4	138.0	143.7
145°	181.7	172.1	162.9	155.2	148.4	143.5	140.0	138.9	140.0	143.5	148.4
147.5°	183.3	174.9	166.3	159.3	153.7	148.7	145.5	145.2	145.5	148.7	153.7
150°	184.1	176.4	168.6	161.9	156.6	152.3	149.5	149.1	149.5	152.3	156.6
152.5°	184.7	177.5	170.6	164.4	159.7	155.7	152.9	152.8	152.9	155.7	159.7
155°	185.2	179.2	173.2	167.9	164.0	160.5	158.3	158.0	158.3	160.5	164.0
157.5°	185.2	180.4	175.3	171.1	167.7	165.0	163.0	163.0	163.0	165.0	167.7
160°	185.2	181.0	176.7	172.8	170.0	167.5	166.1	166.1	166.1	167.5	170.0
162.5°	185.2	181.5	177.6	174.5	172.0	169.8	168.7	168.9	168.7	169.8	172.0
165°	184.5	181.7	178.5	176.4	174.6	172.8	172.1	172.1	172.1	172.8	174.6
167.5°	183.6	181.6	179.3	177.6	176.6	175.3	174.9	175.3	174.9	175.3	176.6
170°	183.1	181.3	179.5	178.5	177.8	176.7	176.4	176.7	176.4	176.7	177.8
172.5°	182.5	181.0	179.8	179.0	178.6	177.8	177.8	178.1	177.8	177.8	178.6
175°	181.7	180.6	179.9	179.9	179.5	179.2	179.2	179.5	179.2	179.2	179.5
177.5°	180.7	180.2	179.9	179.9	179.9	179.6	179.9	180.2	179.9	179.6	179.9
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1259.2	1255.4	1249.8	1242.2	1235.8	1229.0	1227.3	1224.7	1229.8	1225.6	1224.3
5°	1217.9	1206.7	1192.4	1175.9	1166.3	1152.5	1149.8	1144.5	1139.2	1138.7	1133.3
7.5°	1174.2	1157.8	1139.0	1122.2	1106.6	1091.5	1081.7	1079.5	1071.7	1067.1	1061.8
10°	1146.1	1125.9	1104.1	1088.1	1070.1	1054.1	1042.9	1036.6	1031.2	1025.4	1020.1
12.5°	1112.9	1091.4	1073.5	1056.2	1034.7	1022.6	1004.2	993.2	992.1	992.2	978.4
15°	1074.3	1053.0	1025.4	1000.9	989.2	965.8	955.7	942.9	935.0	927.0	920.6
17.5°	1030.2	1003.7	982.1	954.0	931.7	913.1	899.8	892.1	880.1	868.8	860.6
20°	1002.5	974.3	951.5	921.7	897.2	874.3	863.2	852.5	843.5	833.9	824.9
22.5°	974.4	945.0	917.0	888.1	865.3	841.2	830.4	815.9	807.3	802.0	793.0
25°	930.2	898.3	866.4	838.7	815.3	794.0	779.7	768.5	758.9	754.7	748.8
27.5°	882.1	850.4	819.6	788.2	761.6	746.2	734.7	726.3	720.7	715.1	712.5
30°	851.5	818.5	785.5	756.3	731.8	716.4	705.7	699.9	695.6	693.0	690.3
32.5°	820.4	787.9	753.2	726.5	704.6	690.9	682.8	676.9	674.8	673.8	672.9
35°	770.6	737.7	705.7	681.8	661.1	655.8	648.8	645.7	644.6	648.3	649.9
37.5°	722.4	691.8	662.5	639.3	625.7	617.9	615.5	615.7	619.5	622.8	626.6
40°	691.4	661.6	634.0	613.7	601.0	596.2	595.1	597.8	602.0	605.8	610.0
42.5°	661.2	631.8	606.7	587.8	578.9	574.5	575.1	577.8	583.7	588.3	594.7
45°	614.3	589.8	565.3	549.9	542.5	543.5	543.5	548.3	554.2	561.1	568.0
47.5°	570.1	545.5	525.3	512.4	508.5	507.6	510.6	516.8	525.2	533.8	543.4
50°	540.3	516.9	499.4	487.7	483.4	485.0	489.3	495.1	505.2	515.9	526.0
52.5°	510.1	488.9	472.6	461.7	458.8	461.6	465.9	475.1	484.0	495.5	507.7
55°	463.2	445.1	432.4	424.4	423.3	424.9	429.7	439.8	452.6	467.0	478.7
57.5°	416.5	401.4	389.7	384.2	384.7	386.2	394.1	406.1	419.7	435.0	450.1
60°	385.1	371.2	361.7	357.4	357.9	361.1	370.7	381.9	398.9	413.8	429.7
62.5°	355.3	343.1	334.0	330.2	329.4	336.4	345.6	357.2	374.2	390.8	408.0
65°	307.4	297.8	290.4	288.3	289.9	295.2	306.9	322.3	336.7	354.2	372.3
67.5°	260.6	252.7	247.6	248.6	250.5	258.4	268.2	281.4	297.7	315.9	333.8
70°	230.8	223.4	219.1	219.6	222.8	232.4	240.9	254.2	271.8	290.4	305.3
72.5°	200.2	195.3	191.5	193.7	196.9	203.5	214.1	227.4	242.8	260.2	275.9
75°	153.7	153.7	151.6	153.2	158.0	164.3	172.3	186.1	201.6	215.4	228.2
77.5°	114.0	112.9	114.2	116.2	118.9	126.5	135.6	145.5	157.1	170.9	181.5
80°	87.2	87.8	90.4	93.6	94.7	100.5	110.1	119.1	128.2	139.9	150.0
82.5°	65.5	66.1	67.4	71.5	72.5	78.8	85.0	94.0	102.2	110.1	118.5
85°	35.6	35.6	38.3	39.9	42.5	46.8	50.5	55.8	63.3	68.6	76.6
87.5°	14.2	14.2	16.3	17.2	18.6	20.8	21.6	26.4	28.1	30.3	34.2
90°	2.8	2.8	4.9	4.9	5.7	6.4	6.0	6.4	6.7	7.1	7.1
92.5°	18.7	26.0	44.0	71.4	98.1	112.1	93.4	69.4	52.2	41.6	34.5
95°	29.3	44.2	74.9	132.9	217.4	288.0	296.2	261.9	207.1	159.7	125.5
97.5°	35.5	47.9	71.6	119.5	203.4	303.4	372.1	386.9	366.6	332.0	295.1
100°	40.3	51.6	72.5	112.4	184.5	284.2	374.6	426.2	433.3	416.0	389.8
102.5°	45.7	56.4	75.3	110.4	171.8	260.1	353.4	424.3	459.3	464.3	453.4
105°	54.8	65.0	82.0	111.3	160.8	231.8	314.9	395.8	457.0	492.0	506.5
107.5°	64.2	74.3	89.8	116.6	158.8	216.0	283.8	355.5	420.6	469.8	501.4
110°	70.7	80.2	95.8	120.5	159.4	210.6	268.3	331.2	392.3	443.6	482.4



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	76.9	86.4	101.4	124.8	161.1	208.1	259.5	313.3	367.4	415.8	454.7
115°	86.6	96.1	110.3	131.5	164.3	206.8	251.3	295.5	338.9	380.3	414.2
117.5°	95.5	105.4	118.8	138.3	167.8	206.4	247.6	286.7	322.7	355.2	384.0
120°	101.4	111.3	124.8	143.1	170.4	206.4	245.6	282.7	315.6	343.9	369.0
122.5°	107.4	117.0	130.4	147.7	172.9	206.1	243.4	279.3	311.1	336.8	358.8
125°	115.6	125.5	138.2	154.4	176.7	205.7	239.6	273.6	303.9	328.3	347.8
127.5°	123.1	133.1	145.4	160.3	179.8	204.9	234.6	266.5	295.5	319.9	338.3
130°	127.9	138.2	150.2	164.0	182.0	204.6	231.5	260.8	288.8	312.8	331.5
132.5°	132.5	142.1	154.2	167.7	184.0	204.4	228.7	254.9	281.1	304.6	323.3
135°	138.9	148.1	159.7	172.5	187.0	203.9	224.4	246.7	269.7	291.2	308.9
137.5°	144.3	153.1	164.0	175.9	188.7	203.9	220.8	239.3	258.7	276.9	292.8
140°	147.7	156.2	166.8	178.1	190.1	203.6	218.8	235.0	251.6	267.5	282.4
142.5°	150.8	159.0	169.4	179.8	191.3	203.6	217.1	231.1	245.7	259.3	272.2
145°	155.2	162.9	172.1	181.7	191.9	202.9	214.2	225.5	237.5	248.1	258.0
147.5°	159.3	166.3	174.9	183.3	192.3	201.6	211.6	220.9	230.4	238.9	246.7
150°	161.9	168.6	176.4	184.1	192.3	200.7	209.6	218.1	226.2	233.3	239.6
152.5°	164.4	170.6	177.5	184.7	191.7	199.3	207.3	215.0	222.0	228.5	233.7
155°	167.9	173.2	179.2	185.2	190.9	197.2	203.9	210.3	215.9	221.2	225.5
157.5°	171.1	175.3	180.4	185.2	189.9	195.0	200.5	205.3	210.0	214.5	217.9
160°	172.8	176.7	181.0	185.2	189.1	193.3	197.9	202.2	206.0	209.9	212.8
162.5°	174.5	177.6	181.5	185.2	188.2	191.6	195.7	199.1	202.4	205.4	208.0
165°	176.4	178.5	181.7	184.5	186.6	189.1	191.9	194.7	196.9	199.3	201.1
167.5°	177.6	179.3	181.6	183.6	184.9	186.5	188.5	190.6	192.2	194.2	195.2
170°	178.5	179.5	181.3	183.1	183.8	184.8	186.3	188.0	189.1	190.5	191.6
172.5°	179.0	179.8	181.0	182.5	182.7	183.1	184.3	185.8	186.5	187.4	188.2
175°	179.9	179.9	180.6	181.7	181.3	181.3	182.0	182.7	183.1	183.8	183.8
177.5°	179.9	179.9	180.2	180.7	180.2	180.2	180.5	180.7	181.0	181.0	181.3
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1223.4	1222.6	1219.6	1219.2	1219.6	1222.6	1223.4	1224.3	1225.6	1229.8	1224.7
5°	1130.2	1127.5	1125.9	1131.8	1125.9	1127.5	1130.2	1133.3	1138.7	1139.2	1144.5
7.5°	1059.8	1057.7	1053.0	1051.6	1053.0	1057.7	1059.8	1061.8	1067.1	1071.7	1079.5
10°	1014.7	1012.6	1008.4	1007.3	1008.4	1012.6	1014.7	1020.1	1025.4	1031.2	1036.6
12.5°	971.3	967.1	966.2	967.3	966.2	967.1	971.3	978.4	992.2	992.1	993.2
15°	913.7	911.6	905.7	907.3	905.7	911.6	913.7	920.6	927.0	935.0	942.9
17.5°	856.9	854.3	847.2	853.5	847.2	854.3	856.9	860.6	868.8	880.1	892.1
20°	821.2	816.9	813.2	812.6	813.2	816.9	821.2	824.9	833.9	843.5	852.5
22.5°	787.1	783.3	783.0	779.5	783.0	783.3	787.1	793.0	802.0	807.3	815.9
25°	744.6	740.9	739.8	737.1	739.8	740.9	744.6	748.8	754.7	758.9	768.5
27.5°	711.9	710.1	708.2	709.0	708.2	710.1	711.9	712.5	715.1	720.7	726.3
30°	691.9	691.4	690.3	690.3	690.3	691.4	691.9	690.3	693.0	695.6	699.9
32.5°	675.3	675.2	675.9	675.9	675.9	675.2	675.3	672.9	673.8	674.8	676.9
35°	652.0	653.6	654.7	653.1	654.7	653.6	652.0	649.9	648.3	644.6	645.7
37.5°	631.0	632.6	634.1	635.9	634.1	632.6	631.0	626.6	622.8	619.5	615.7
40°	614.8	618.5	619.6	622.3	619.6	618.5	614.8	610.0	605.8	602.0	597.8
42.5°	599.5	603.6	606.4	606.9	606.4	603.6	599.5	594.7	588.3	583.7	577.8
45°	576.0	580.2	584.0	584.0	584.0	580.2	576.0	568.0	561.1	554.2	548.3
47.5°	551.6	557.8	561.5	562.5	561.5	557.8	551.6	543.4	533.8	525.2	516.8
50°	535.0	542.5	546.2	548.9	546.2	542.5	535.0	526.0	515.9	505.2	495.1
52.5°	518.9	526.3	531.3	532.7	531.3	526.3	518.9	507.7	495.5	484.0	475.1
55°	490.9	501.5	507.4	509.5	507.4	501.5	490.9	478.7	467.0	452.6	439.8
57.5°	464.5	474.3	481.1	482.7	481.1	474.3	464.5	450.1	435.0	419.7	406.1
60°	444.1	454.7	463.2	464.8	463.2	454.7	444.1	429.7	413.8	398.9	381.9
62.5°	423.2	434.3	442.0	446.1	442.0	434.3	423.2	408.0	390.8	374.2	357.2
65°	387.2	398.3	405.8	407.4	405.8	398.3	387.2	372.3	354.2	336.7	322.3
67.5°	347.8	359.0	363.9	367.0	363.9	359.0	347.8	333.8	315.9	297.7	281.4
70°	320.2	329.2	334.5	337.2	334.5	329.2	320.2	305.3	290.4	271.8	254.2
72.5°	288.7	298.1	304.3	304.8	304.3	298.1	288.7	275.9	260.2	242.8	227.4
75°	240.4	248.9	252.1	252.1	252.1	248.9	240.4	228.2	215.4	201.6	186.1
77.5°	190.3	194.7	198.7	199.5	198.7	194.7	190.3	181.5	170.9	157.1	145.5
80°	158.0	160.6	163.8	163.8	163.8	160.6	158.0	150.0	139.9	128.2	119.1
82.5°	124.8	127.0	130.2	129.8	130.2	127.0	124.8	118.5	110.1	102.2	94.0
85°	75.5	80.3	79.8	78.7	79.8	80.3	75.5	76.6	68.6	63.3	55.8
87.5°	35.5	36.0	37.2	38.1	37.2	36.0	35.5	34.2	30.3	28.1	26.4
90°	7.4	7.8	7.4	7.4	7.4	7.8	7.4	7.1	7.1	6.7	6.4
92.5°	30.3	28.4	27.2	27.2	27.2	28.4	30.3	34.5	41.6	52.2	69.4
95°	108.1	97.2	90.8	86.2	90.8	97.2	108.1	125.5	159.7	207.1	261.9
97.5°	269.7	248.5	237.9	230.5	237.9	248.5	269.7	295.1	332.0	366.6	386.9
100°	359.1	337.5	326.9	324.1	326.9	337.5	359.1	389.8	416.0	433.3	426.2
102.5°	434.6	419.0	407.8	405.5	407.8	419.0	434.6	453.4	464.3	459.3	424.3
105°	507.2	504.3	499.4	497.3	499.4	504.3	507.2	506.5	492.0	457.0	395.8
107.5°	518.8	526.9	530.4	531.3	530.4	526.9	518.8	501.4	469.8	420.6	355.5
110°	507.5	522.4	528.7	531.9	528.7	522.4	507.5	482.4	443.6	392.3	331.2



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	483.2	501.2	510.1	515.2	510.1	501.2	483.2	454.7	415.8	367.4	313.3
115°	442.1	463.3	474.7	477.5	474.7	463.3	442.1	414.2	380.3	338.9	295.5
117.5°	407.8	425.6	437.0	439.2	437.0	425.6	407.8	384.0	355.2	322.7	286.7
120°	389.1	404.7	413.9	417.8	413.9	404.7	389.1	369.0	343.9	315.6	282.7
122.5°	375.8	389.1	396.9	400.8	396.9	389.1	375.8	358.8	336.8	311.1	279.3
125°	361.9	372.2	378.9	381.0	378.9	372.2	361.9	347.8	328.3	303.9	273.6
127.5°	352.5	361.6	367.3	369.4	367.3	361.6	352.5	338.3	319.9	295.5	266.5
130°	346.0	354.8	360.5	362.6	360.5	354.8	346.0	331.5	312.8	288.8	260.8
132.5°	337.5	347.5	352.9	355.0	352.9	347.5	337.5	323.3	304.6	281.1	254.9
135°	323.0	332.9	338.6	340.7	338.6	332.9	323.0	308.9	291.2	269.7	246.7
137.5°	306.1	315.8	320.5	323.0	320.5	315.8	306.1	292.8	276.9	258.7	239.3
140°	294.8	302.5	307.5	310.3	307.5	302.5	294.8	282.4	267.5	251.6	235.0
142.5°	283.2	290.4	294.8	296.7	294.8	290.4	283.2	272.2	259.3	245.7	231.1
145°	266.8	272.8	276.4	278.1	276.4	272.8	266.8	258.0	248.1	237.5	225.5
147.5°	253.2	258.4	261.0	261.7	261.0	258.4	253.2	246.7	238.9	230.4	220.9
150°	245.3	249.9	252.0	252.3	252.0	249.9	245.3	239.6	233.3	226.2	218.1
152.5°	238.5	242.2	243.5	243.9	243.5	242.2	238.5	233.7	228.5	222.0	215.0
155°	229.0	231.8	232.9	232.9	232.9	231.8	229.0	225.5	221.2	215.9	210.3
157.5°	220.5	222.7	223.3	223.3	223.3	222.7	220.5	217.9	214.5	210.0	205.3
160°	214.9	217.0	217.4	217.4	217.4	217.0	214.9	212.8	209.9	206.0	202.2
162.5°	209.5	211.6	212.0	211.7	212.0	211.6	209.5	208.0	205.4	202.4	199.1
165°	202.5	203.9	203.6	203.2	203.6	203.9	202.5	201.1	199.3	196.9	194.7
167.5°	195.9	196.9	196.8	196.5	196.8	196.9	195.9	195.2	194.2	192.2	190.6
170°	192.3	192.6	192.3	192.3	192.3	192.6	192.3	191.6	190.5	189.1	188.0
172.5°	188.6	188.9	188.6	188.0	188.6	188.9	188.6	188.2	187.4	186.5	185.8
175°	183.8	184.5	183.8	183.1	183.8	184.5	183.8	183.8	183.8	183.1	182.7
177.5°	181.0	181.3	180.7	180.2	180.7	181.3	181.0	181.3	181.0	181.0	180.7
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1227.3	1229.0	1235.8	1242.2	1249.8	1255.4	1259.2	1263.4	1272.4	1279.6	1286.4
5°	1149.8	1152.5	1166.3	1175.9	1192.4	1206.7	1217.9	1230.1	1244.5	1264.2	1282.3
7.5°	1081.7	1091.5	1106.6	1122.2	1139.0	1157.8	1174.2	1192.6	1217.4	1244.4	1272.3
10°	1042.9	1054.1	1070.1	1088.1	1104.1	1125.9	1146.1	1167.9	1196.1	1229.1	1262.1
12.5°	1004.2	1022.6	1034.7	1056.2	1073.5	1091.4	1112.9	1141.5	1174.4	1209.1	1248.9
15°	955.7	965.8	989.2	1000.9	1025.4	1053.0	1074.3	1103.0	1134.9	1180.7	1225.4
17.5°	899.8	913.1	931.7	954.0	982.1	1003.7	1030.2	1059.7	1099.9	1145.4	1201.3
20°	863.2	874.3	897.2	921.7	951.5	974.3	1002.5	1031.2	1072.7	1121.1	1179.6
22.5°	830.4	841.2	865.3	888.1	917.0	945.0	974.4	1007.8	1047.6	1098.6	1158.3
25°	779.7	794.0	815.3	838.7	866.4	898.3	930.2	960.0	1002.5	1056.2	1120.1
27.5°	734.7	746.2	761.6	788.2	819.6	850.4	882.1	919.5	960.4	1017.2	1083.5
30°	705.7	716.4	731.8	756.3	785.5	818.5	851.5	887.6	930.2	986.6	1054.1
32.5°	682.8	690.9	704.6	726.5	753.2	787.9	820.4	857.9	902.5	958.1	1023.9
35°	648.8	655.8	661.1	681.8	705.7	737.7	770.6	810.5	853.6	906.3	972.2
37.5°	615.5	617.9	625.7	639.3	662.5	691.8	722.4	761.7	805.8	859.3	918.8
40°	595.1	596.2	601.0	613.7	634.0	661.6	691.4	730.2	772.2	822.8	881.8
42.5°	575.1	574.5	578.9	587.8	606.7	631.8	661.2	696.6	738.6	785.3	840.9
45°	543.5	543.5	542.5	549.9	565.3	589.8	614.3	648.3	683.4	729.2	776.0
47.5°	510.6	507.6	508.5	512.4	525.3	545.5	570.1	598.0	629.0	667.7	708.7
50°	489.3	485.0	483.4	487.7	499.4	516.9	540.3	564.8	594.1	628.1	663.2
52.5°	465.9	461.6	458.8	461.7	472.6	488.9	510.1	531.6	557.9	585.6	616.0
55°	429.7	424.9	423.3	424.4	432.4	445.1	463.2	482.9	502.6	525.5	546.7
57.5°	394.1	386.2	384.7	384.2	389.7	401.4	416.5	433.6	447.9	461.7	484.4
60°	370.7	361.1	357.9	357.4	361.7	371.2	385.1	402.1	412.2	421.7	441.4
62.5°	345.6	336.4	329.4	330.2	334.0	343.1	355.3	367.6	374.3	384.7	398.0
65°	306.9	295.2	289.9	288.3	290.4	297.8	307.4	315.4	322.8	327.1	339.8
67.5°	268.2	258.4	250.5	248.6	247.6	252.7	260.6	265.4	270.7	274.4	282.0
70°	240.9	232.4	222.8	219.6	219.1	223.4	230.8	231.3	238.8	240.4	248.4
72.5°	214.1	203.5	196.9	193.7	191.5	195.3	200.2	201.6	205.6	208.5	212.6
75°	172.3	164.3	158.0	153.2	151.6	153.7	153.7	156.4	159.0	160.6	165.4
77.5°	135.6	126.5	118.9	116.2	114.2	112.9	114.0	115.6	114.3	117.1	118.2
80°	110.1	100.5	94.7	93.6	90.4	87.8	87.2	88.8	86.7	87.8	90.9
82.5°	85.0	78.8	72.5	71.5	67.4	66.1	65.5	64.6	64.6	64.4	65.0
85°	50.5	46.8	42.5	39.9	38.3	35.6	35.6	34.6	33.5	32.4	33.0
87.5°	21.6	20.8	18.6	17.2	16.3	14.2	14.2	12.8	12.3	11.7	11.1
90°	6.0	6.4	5.7	4.9	4.9	2.8	2.8	2.5	2.1	1.1	0.4
92.5°	93.4	112.1	98.1	71.4	44.0	26.0	18.7	13.5	9.2	5.9	4.0
95°	296.2	288.0	217.4	132.9	74.9	44.2	29.3	20.9	16.3	12.7	11.7
97.5°	372.1	303.4	203.4	119.5	71.6	47.9	35.5	28.2	24.0	20.9	20.9
100°	374.6	284.2	184.5	112.4	72.5	51.6	40.3	33.6	29.3	26.9	26.9
102.5°	353.4	260.1	171.8	110.4	75.3	56.4	45.7	39.2	35.3	33.1	32.5
105°	314.9	231.8	160.8	111.3	82.0	65.0	54.8	48.4	44.2	42.4	41.4
107.5°	283.8	216.0	158.8	116.6	89.8	74.3	64.2	58.1	53.6	51.8	51.1
110°	268.3	210.6	159.4	120.5	95.8	80.2	70.7	64.3	60.1	58.3	57.6



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	259.5	208.1	161.1	124.8	101.4	86.4	76.9	70.5	66.6	64.5	63.8
115°	251.3	206.8	164.3	131.5	110.3	96.1	86.6	79.9	76.3	73.9	72.8
117.5°	247.6	206.4	167.8	138.3	118.8	105.4	95.5	89.2	85.3	83.1	82.1
120°	245.6	206.4	170.4	143.1	124.8	111.3	101.4	95.4	91.5	89.1	88.4
122.5°	243.4	206.1	172.9	147.7	130.4	117.0	107.4	100.8	97.2	94.7	94.0
125°	239.6	205.7	176.7	154.4	138.2	125.5	115.6	108.9	105.0	102.8	101.4
127.5°	234.6	204.9	179.8	160.3	145.4	133.1	123.1	116.1	111.7	109.1	108.0
130°	231.5	204.6	182.0	164.0	150.2	138.2	127.9	121.2	115.9	113.1	111.7
132.5°	228.7	204.4	184.0	167.7	154.2	142.1	132.5	125.2	120.2	116.5	115.4
135°	224.4	203.9	187.0	172.5	159.7	148.1	138.9	131.5	125.5	121.9	120.5
137.5°	220.8	203.9	188.7	175.9	164.0	153.1	144.3	136.6	130.9	127.0	125.7
140°	218.8	203.6	190.1	178.1	166.8	156.2	147.7	140.3	134.3	130.4	129.4
142.5°	217.1	203.6	191.3	179.8	169.4	159.0	150.8	143.7	138.0	134.4	133.3
145°	214.2	202.9	191.9	181.7	172.1	162.9	155.2	148.4	143.5	140.0	138.9
147.5°	211.6	201.6	192.3	183.3	174.9	166.3	159.3	153.7	148.7	145.5	145.2
150°	209.6	200.7	192.3	184.1	176.4	168.6	161.9	156.6	152.3	149.5	149.1
152.5°	207.3	199.3	191.7	184.7	177.5	170.6	164.4	159.7	155.7	152.9	152.8
155°	203.9	197.2	190.9	185.2	179.2	173.2	167.9	164.0	160.5	158.3	158.0
157.5°	200.5	195.0	189.9	185.2	180.4	175.3	171.1	167.7	165.0	163.0	163.0
160°	197.9	193.3	189.1	185.2	181.0	176.7	172.8	170.0	167.5	166.1	166.1
162.5°	195.7	191.6	188.2	185.2	181.5	177.6	174.5	172.0	169.8	168.7	168.9
165°	191.9	189.1	186.6	184.5	181.7	178.5	176.4	174.6	172.8	172.1	172.1
167.5°	188.5	186.5	184.9	183.6	181.6	179.3	177.6	176.6	175.3	174.9	175.3
170°	186.3	184.8	183.8	183.1	181.3	179.5	178.5	177.8	176.7	176.4	176.7
172.5°	184.3	183.1	182.7	182.5	181.0	179.8	179.0	178.6	177.8	177.8	178.1
175°	182.0	181.3	181.3	181.7	180.6	179.9	179.9	179.5	179.2	179.2	179.5
177.5°	180.5	180.2	180.2	180.7	180.2	179.9	179.9	179.9	179.6	179.9	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9





TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1292.4	1296.6	1302.2	1311.5	1314.9	1319.2	1325.1	1324.7	1326.4	1332.8	1346.4
5°	1297.2	1313.6	1329.6	1348.7	1369.0	1382.2	1400.3	1411.5	1422.7	1437.0	1461.5
7.5°	1299.1	1325.2	1354.5	1388.1	1418.0	1452.5	1479.4	1504.7	1527.5	1557.9	1587.0
10°	1296.1	1331.2	1369.0	1411.5	1456.7	1495.0	1529.6	1568.9	1602.4	1639.1	1672.1
12.5°	1290.6	1332.9	1383.4	1431.1	1483.9	1540.5	1583.6	1623.4	1668.0	1710.2	1761.0
15°	1278.0	1336.0	1395.0	1457.8	1528.5	1593.9	1656.1	1707.7	1755.6	1818.9	1885.4
17.5°	1262.1	1324.6	1399.1	1475.0	1548.9	1623.7	1700.7	1778.3	1838.7	1917.3	1969.3
20°	1247.2	1319.5	1396.1	1486.5	1560.4	1653.5	1730.1	1805.1	1888.0	1966.2	2028.4
22.5°	1226.3	1305.5	1386.7	1476.7	1574.0	1667.1	1755.6	1837.0	1919.9	2004.9	2080.3
25°	1199.8	1271.6	1367.9	1470.0	1566.8	1667.8	1769.4	1871.5	1960.9	2050.8	2121.0
27.5°	1154.7	1245.4	1335.0	1440.4	1548.0	1662.3	1770.9	1877.8	1971.4	2045.3	2088.8
30°	1131.8	1210.5	1307.8	1413.6	1530.1	1653.0	1766.2	1871.0	1958.2	2017.3	2034.8
32.5°	1097.7	1179.0	1274.2	1383.8	1507.1	1633.4	1751.3	1850.2	1922.9	1953.9	1932.7
35°	1047.2	1120.6	1216.8	1329.1	1457.2	1591.8	1708.3	1791.8	1829.0	1799.7	1726.9
37.5°	986.6	1059.3	1156.0	1266.2	1398.8	1535.6	1640.9	1701.0	1688.7	1615.9	1507.3
40°	944.0	1012.1	1104.1	1223.2	1352.5	1489.7	1582.2	1614.7	1580.6	1476.4	1361.0
42.5°	896.8	963.2	1055.6	1170.5	1307.4	1433.9	1514.6	1517.2	1460.2	1335.6	1219.7
45°	824.9	888.2	975.4	1095.1	1221.6	1340.8	1393.9	1367.9	1262.6	1142.4	1025.9
47.5°	753.9	808.8	894.8	1008.4	1128.6	1228.9	1255.2	1208.3	1096.1	979.4	871.5
50°	702.0	757.3	838.2	946.7	1062.6	1149.3	1162.1	1099.8	989.8	872.2	787.7
52.5°	652.2	707.1	785.0	885.4	991.6	1069.7	1070.2	998.2	888.5	783.7	705.1
55°	579.2	628.6	698.8	788.7	883.4	944.5	929.7	855.2	760.0	669.1	600.4
57.5°	508.8	551.8	616.5	691.5	774.9	825.3	800.6	728.9	643.9	566.8	514.8
60°	463.2	504.2	559.5	630.2	700.4	739.8	716.4	651.5	573.3	511.1	465.9
62.5°	419.0	453.6	506.7	568.1	633.2	662.4	641.5	577.5	509.9	453.7	417.0
65°	356.3	384.5	427.1	479.7	527.1	552.0	534.5	474.9	423.3	382.9	353.7
67.5°	297.8	319.8	352.1	394.3	434.5	448.0	432.1	390.6	346.9	314.5	293.9
70°	257.4	278.2	305.3	337.7	372.8	387.2	371.2	338.2	302.6	272.8	252.6
72.5°	222.1	238.2	261.0	288.8	316.2	330.6	319.7	288.0	257.9	235.8	218.6
75°	169.1	183.0	198.9	218.6	239.9	249.4	239.9	218.1	197.3	180.8	168.6
77.5°	123.0	130.4	142.7	157.4	170.7	178.1	169.8	155.0	142.3	131.0	125.0
80°	93.6	98.9	107.4	119.1	128.2	135.1	129.8	117.5	107.4	100.0	97.3
82.5°	68.1	71.7	77.2	85.9	92.0	95.5	93.2	84.3	80.2	73.6	70.9
85°	33.5	35.6	39.4	42.0	47.3	47.9	48.4	44.7	41.0	39.4	37.2
87.5°	11.7	12.3	13.7	15.0	16.7	17.6	17.2	17.3	15.7	15.2	13.6
90°	1.1	2.1	2.5	2.8	2.8	4.9	4.9	5.7	6.4	6.0	6.4
92.5°	5.9	9.2	13.5	18.7	26.0	44.0	71.4	98.1	112.1	93.4	69.4
95°	12.7	16.3	20.9	29.3	44.2	74.9	132.9	217.4	288.0	296.2	261.9
97.5°	20.9	24.0	28.2	35.5	47.9	71.6	119.5	203.4	303.4	372.1	386.9
100°	26.9	29.3	33.6	40.3	51.6	72.5	112.4	184.5	284.2	374.6	426.2
102.5°	33.1	35.3	39.2	45.7	56.4	75.3	110.4	171.8	260.1	353.4	424.3
105°	42.4	44.2	48.4	54.8	65.0	82.0	111.3	160.8	231.8	314.9	395.8
107.5°	51.8	53.6	58.1	64.2	74.3	89.8	116.6	158.8	216.0	283.8	355.5
110°	58.3	60.1	64.3	70.7	80.2	95.8	120.5	159.4	210.6	268.3	331.2





TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	64.5	66.6	70.5	76.9	86.4	101.4	124.8	161.1	208.1	259.5	313.3
115°	73.9	76.3	79.9	86.6	96.1	110.3	131.5	164.3	206.8	251.3	295.5
117.5°	83.1	85.3	89.2	95.5	105.4	118.8	138.3	167.8	206.4	247.6	286.7
120°	89.1	91.5	95.4	101.4	111.3	124.8	143.1	170.4	206.4	245.6	282.7
122.5°	94.7	97.2	100.8	107.4	117.0	130.4	147.7	172.9	206.1	243.4	279.3
125°	102.8	105.0	108.9	115.6	125.5	138.2	154.4	176.7	205.7	239.6	273.6
127.5°	109.1	111.7	116.1	123.1	133.1	145.4	160.3	179.8	204.9	234.6	266.5
130°	113.1	115.9	121.2	127.9	138.2	150.2	164.0	182.0	204.6	231.5	260.8
132.5°	116.5	120.2	125.2	132.5	142.1	154.2	167.7	184.0	204.4	228.7	254.9
135°	121.9	125.5	131.5	138.9	148.1	159.7	172.5	187.0	203.9	224.4	246.7
137.5°	127.0	130.9	136.6	144.3	153.1	164.0	175.9	188.7	203.9	220.8	239.3
140°	130.4	134.3	140.3	147.7	156.2	166.8	178.1	190.1	203.6	218.8	235.0
142.5°	134.4	138.0	143.7	150.8	159.0	169.4	179.8	191.3	203.6	217.1	231.1
145°	140.0	143.5	148.4	155.2	162.9	172.1	181.7	191.9	202.9	214.2	225.5
147.5°	145.5	148.7	153.7	159.3	166.3	174.9	183.3	192.3	201.6	211.6	220.9
150°	149.5	152.3	156.6	161.9	168.6	176.4	184.1	192.3	200.7	209.6	218.1
152.5°	152.9	155.7	159.7	164.4	170.6	177.5	184.7	191.7	199.3	207.3	215.0
155°	158.3	160.5	164.0	167.9	173.2	179.2	185.2	190.9	197.2	203.9	210.3
157.5°	163.0	165.0	167.7	171.1	175.3	180.4	185.2	189.9	195.0	200.5	205.3
160°	166.1	167.5	170.0	172.8	176.7	181.0	185.2	189.1	193.3	197.9	202.2
162.5°	168.7	169.8	172.0	174.5	177.6	181.5	185.2	188.2	191.6	195.7	199.1
165°	172.1	172.8	174.6	176.4	178.5	181.7	184.5	186.6	189.1	191.9	194.7
167.5°	174.9	175.3	176.6	177.6	179.3	181.6	183.6	184.9	186.5	188.5	190.6
170°	176.4	176.7	177.8	178.5	179.5	181.3	183.1	183.8	184.8	186.3	188.0
172.5°	177.8	177.8	178.6	179.0	179.8	181.0	182.5	182.7	183.1	184.3	185.8
175°	179.2	179.2	179.5	179.9	179.9	180.6	181.7	181.3	181.3	182.0	182.7
177.5°	179.9	179.6	179.9	179.9	179.9	180.2	180.7	180.2	180.2	180.5	180.7
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9	179.9



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9	1283.9
2.5°	1353.2	1354.1	1357.9	1360.9	1361.7	1366.0	1366.4
5°	1472.1	1481.2	1498.7	1500.3	1503.0	1516.8	1506.2
7.5°	1611.5	1634.4	1649.8	1663.3	1668.2	1674.2	1673.0
10°	1700.8	1734.9	1751.9	1779.0	1780.1	1787.0	1782.7
12.5°	1790.6	1830.2	1861.2	1866.2	1889.0	1892.5	1898.5
15°	1917.8	1959.8	2002.9	2018.3	2049.7	2057.2	2068.9
17.5°	2037.4	2080.3	2110.5	2150.4	2163.3	2180.5	2168.8
20°	2102.9	2149.7	2188.0	2219.4	2232.7	2242.2	2241.2
22.5°	2142.5	2189.7	2220.7	2244.5	2256.9	2261.0	2260.7
25°	2167.2	2194.4	2203.9	2213.0	2199.2	2194.4	2196.5
27.5°	2098.3	2091.3	2066.3	2033.5	1999.5	1972.5	1957.8
30°	2003.4	1962.0	1924.2	1858.2	1824.2	1804.0	1785.9
32.5°	1869.0	1803.3	1730.6	1670.2	1631.5	1601.5	1597.0
35°	1638.6	1539.7	1450.9	1376.9	1338.6	1306.2	1298.7
37.5°	1393.1	1290.3	1210.4	1145.3	1104.1	1081.2	1059.8
40°	1230.1	1141.9	1063.1	1007.8	976.5	960.0	946.7
42.5°	1104.6	1024.0	945.7	903.6	875.2	865.1	857.3
45°	931.2	856.3	802.0	770.1	753.6	736.6	728.6
47.5°	792.4	731.4	695.6	668.5	650.9	640.8	635.7
50°	713.7	663.7	631.8	611.1	595.1	587.1	582.9
52.5°	643.9	602.9	576.1	559.6	548.8	542.9	541.2
55°	554.7	523.3	506.3	492.0	484.0	478.7	476.5
57.5°	482.2	458.0	444.2	432.4	429.3	424.8	423.3
60°	434.5	415.9	404.2	396.2	393.6	388.2	389.3
62.5°	392.4	377.2	367.2	362.6	359.1	354.6	356.1
65°	331.9	320.7	315.4	311.1	306.9	304.2	306.3
67.5°	278.5	270.8	263.6	261.1	259.0	258.6	256.3
70°	243.6	237.2	230.8	229.2	229.2	227.1	226.6
72.5°	210.0	205.3	201.0	199.9	198.2	199.0	196.8
75°	162.2	158.5	156.9	155.3	154.8	154.8	153.2
77.5°	119.9	117.1	114.6	114.6	112.6	111.9	111.7
80°	90.9	89.9	87.8	87.8	86.7	87.2	86.2
82.5°	68.4	66.9	66.5	65.6	64.1	64.2	63.2
85°	36.7	35.1	34.6	33.0	31.9	33.0	31.9
87.5°	14.1	13.8	13.3	12.5	12.2	12.1	10.8
90°	6.7	7.1	7.1	7.4	7.8	7.4	7.4
92.5°	52.2	41.6	34.5	30.3	28.4	27.2	27.2
95°	207.1	159.7	125.5	108.1	97.2	90.8	86.2
97.5°	366.6	332.0	295.1	269.7	248.5	237.9	230.5
100°	433.3	416.0	389.8	359.1	337.5	326.9	324.1
102.5°	459.3	464.3	453.4	434.6	419.0	407.8	405.5
105°	457.0	492.0	506.5	507.2	504.3	499.4	497.3
107.5°	420.6	469.8	501.4	518.8	526.9	530.4	531.3
110°	392.3	443.6	482.4	507.5	522.4	528.7	531.9



TEST NUMBER: P332582

CATALOG NUMBER: SA4XXDIP-C795D365U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	367.4	415.8	454.7	483.2	501.2	510.1	515.2
115°	338.9	380.3	414.2	442.1	463.3	474.7	477.5
117.5°	322.7	355.2	384.0	407.8	425.6	437.0	439.2
120°	315.6	343.9	369.0	389.1	404.7	413.9	417.8
122.5°	311.1	336.8	358.8	375.8	389.1	396.9	400.8
125°	303.9	328.3	347.8	361.9	372.2	378.9	381.0
127.5°	295.5	319.9	338.3	352.5	361.6	367.3	369.4
130°	288.8	312.8	331.5	346.0	354.8	360.5	362.6
132.5°	281.1	304.6	323.3	337.5	347.5	352.9	355.0
135°	269.7	291.2	308.9	323.0	332.9	338.6	340.7
137.5°	258.7	276.9	292.8	306.1	315.8	320.5	323.0
140°	251.6	267.5	282.4	294.8	302.5	307.5	310.3
142.5°	245.7	259.3	272.2	283.2	290.4	294.8	296.7
145°	237.5	248.1	258.0	266.8	272.8	276.4	278.1
147.5°	230.4	238.9	246.7	253.2	258.4	261.0	261.7
150°	226.2	233.3	239.6	245.3	249.9	252.0	252.3
152.5°	222.0	228.5	233.7	238.5	242.2	243.5	243.9
155°	215.9	221.2	225.5	229.0	231.8	232.9	232.9
157.5°	210.0	214.5	217.9	220.5	222.7	223.3	223.3
160°	206.0	209.9	212.8	214.9	217.0	217.4	217.4
162.5°	202.4	205.4	208.0	209.5	211.6	212.0	211.7
165°	196.9	199.3	201.1	202.5	203.9	203.6	203.2
167.5°	192.2	194.2	195.2	195.9	196.9	196.8	196.5
170°	189.1	190.5	191.6	192.3	192.6	192.3	192.3
172.5°	186.5	187.4	188.2	188.6	188.9	188.6	188.0
175°	183.1	183.8	183.8	183.8	184.5	183.8	183.1
177.5°	181.0	181.0	181.3	181.0	181.3	180.7	180.2
180°	179.9	179.9	179.9	179.9	179.9	179.9	179.9

(END OF REPORT)