

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332595

Luminaire Tested: **SA4XXDIP-C795D590U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332595  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C795D590U835-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5767.8 lumens  
Efficiency: N/A  
Efficacy: 143.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332595  
CATALOG NUMBER: SA4XXDIP-C795D590U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332595

CATALOG NUMBER: SA4XXDIP-C795D590U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59	59	59	59	59	59	59	59	59	59	59	59																
	1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50	50	50	50	50	50	50	50	50	50	50	50																
	2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46	42	42	42	42	42	42	42	42	42	42	42	42																
	3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35	35	35	35	35	35	35	35	35	35	35	35																
	4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30	30	30	30	30	30	30	30	30	30	30	30																
	5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26	26	26	26	26	26	26	26	26	26	26	26																
	6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23	23	23	23	23	23	23	23	23	23	23	23																
	7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20	20	20	20	20	20	20	20	20	20	20	20																
	8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18	18	18	18	18	18	18	18	18	18	18	18																
	9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17	17	17	17	17	17	17	17	17	17	17	17																
	10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15	15	15	15	15	15	15	15	15	15	15	15																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10717	10717	10717
5°	10749	10619	10697
10°	10681	10533	10585
15°	10552	10384	10410
20°	10381	10198	10207
25°	10185	9986	9958
30°	9945	9737	9648
35°	9697	9477	9351
40°	9438	9180	9013
45°	9169	8889	8719
50°	8871	8629	8363
55°	8549	8294	8024
60°	8226	7918	7677
65°	7862	7559	7253
70°	7456	7081	6805
75°	6834	6503	6338
80°	6081	5835	5686
85°	5317	5122	5020



TEST NUMBER: P332595

CATALOG NUMBER: SA4XXDIP-C795D590U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.0	2.2
10°-20°	352.2	6.1
20°-30°	518.4	9.0
30°-40°	602.7	10.4
40°-50°	602.7	10.4
50°-60°	527.2	9.1
60°-70°	391.5	6.8
70°-80°	222.4	3.9
80°-90°	66.4	1.2
90°-100°	26.1	0.5
100°-110°	166.3	2.9
110°-120°	318.2	5.5
120°-130°	403.9	7.0
130°-140°	432.1	7.5
140°-150°	404.1	7.0
150°-160°	325.9	5.6
160°-170°	210.2	3.6
170°-180°	72.4	1.3
0°-30°	995.7	17.3
0°-40°	1598.4	27.7
0°-60°	2728.3	47.3
0°-90°	3408.7	59.1
90°-120°	510.6	8.9
90°-150°	1750.6	30.4
90°-180°	2359.0	40.9
0°-180°	5767.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1328	1328	1328	1328	1328	
5°	1326	1322	1310	1321	1320	126
15°	1263	1258	1242	1248	1246	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	962	954	949	615
45°	803	795	779	767	764	619
55°	607	604	589	577	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	233
85°	57	57	55	55	54	63
90°	2	8	12	16	17	5
95°	31	13	12	16	16	40
105°	172	175	178	182	163	180
115°	321	322	322	323	323	315
125°	451	453	452	453	454	402
135°	559	559	561	562	563	431
145°	645	646	646	647	648	403
155°	707	707	706	708	706	326
165°	746	743	743	747	742	211
175°	763	759	760	764	758	73
180°	763	763	763	763	763	



TEST NUMBER: P332595

CATALOG NUMBER: SA4XXDIP-C795D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1330.9	1330.3	1329.7	1329.2	1328.6	1327.3	1325.2	1323.1	1321.0	1319.0	1320.8
5°	1326.4	1325.5	1324.5	1323.6	1322.6	1320.8	1318.2	1315.6	1313.0	1310.4	1313.0
7.5°	1314.1	1313.1	1312.2	1311.2	1310.3	1308.4	1305.5	1302.6	1299.7	1296.8	1298.9
10°	1303.0	1302.1	1301.1	1300.2	1299.2	1297.2	1294.1	1291.1	1288.0	1284.9	1286.8
12.5°	1288.5	1287.6	1286.6	1285.7	1284.8	1282.6	1279.4	1276.1	1272.9	1269.6	1271.7
15°	1262.6	1261.6	1260.7	1259.7	1258.8	1256.6	1253.0	1249.5	1245.9	1242.4	1243.8
17.5°	1231.3	1230.1	1228.9	1227.8	1226.6	1224.3	1221.0	1217.6	1214.2	1210.9	1211.8
20°	1208.3	1207.1	1206.0	1204.8	1203.6	1201.2	1197.7	1194.1	1190.6	1187.1	1187.8
22.5°	1183.7	1182.1	1180.5	1179.0	1177.4	1174.9	1171.3	1167.8	1164.2	1160.7	1162.0
25°	1143.4	1141.8	1140.1	1138.5	1136.8	1134.3	1131.0	1127.7	1124.4	1121.1	1121.3
27.5°	1097.5	1095.8	1094.1	1092.4	1090.7	1088.3	1085.2	1082.2	1079.1	1076.0	1075.4
30°	1066.9	1065.0	1063.1	1061.2	1059.3	1056.8	1053.7	1050.7	1047.6	1044.5	1043.6
32.5°	1034.5	1032.8	1031.1	1029.4	1027.7	1025.2	1022.0	1018.7	1015.5	1012.2	1011.1
35°	983.9	982.2	980.6	978.9	977.3	974.8	971.5	968.2	964.9	961.6	959.9
37.5°	930.5	929.0	927.5	926.0	924.4	921.9	918.4	914.8	911.3	907.7	905.9
40°	895.6	893.7	891.8	889.9	888.0	885.3	881.8	878.2	874.7	871.1	868.8
42.5°	858.2	857.0	855.9	854.8	853.6	851.1	847.2	843.3	839.3	835.4	832.7
45°	803.1	801.4	799.8	798.1	796.5	793.7	790.0	786.2	782.4	778.6	776.0
47.5°	745.4	744.3	743.2	742.0	740.9	738.6	735.1	731.6	728.1	724.6	721.6
50°	706.3	705.3	704.4	703.4	702.5	700.4	697.1	693.8	690.4	687.1	683.8
52.5°	668.0	666.9	665.7	664.6	663.4	661.1	657.6	654.1	650.6	647.1	644.2
55°	607.4	606.6	605.9	605.2	604.5	602.5	599.2	595.9	592.6	589.3	586.4
57.5°	549.5	548.7	547.9	547.1	546.3	544.2	541.0	537.7	534.5	531.2	528.5
60°	509.5	508.3	507.1	506.0	504.8	502.6	499.6	496.5	493.4	490.4	488.2
62.5°	470.4	469.4	468.4	467.4	466.4	464.3	461.0	457.7	454.5	451.2	449.3
65°	411.6	410.5	409.3	408.1	406.9	405.1	402.8	400.4	398.0	395.7	393.3
67.5°	352.5	351.4	350.3	349.2	348.2	346.5	344.2	341.9	339.7	337.4	335.1
70°	315.9	314.3	312.6	310.9	309.3	307.5	305.6	303.7	301.8	300.0	298.1
72.5°	276.8	275.1	273.5	271.8	270.1	268.6	267.1	265.5	264.0	262.5	261.0
75°	219.1	217.9	216.8	215.6	214.4	213.2	212.0	210.8	209.7	208.5	207.5
77.5°	164.0	163.5	163.0	162.5	161.9	161.2	160.1	159.1	158.0	157.0	156.7
80°	130.8	130.1	129.4	128.7	128.0	127.4	126.9	126.5	126.0	125.5	125.0
82.5°	98.5	98.2	97.8	97.5	97.2	97.0	96.9	96.8	96.7	96.6	96.3
85°	57.4	57.4	57.4	57.4	57.4	57.2	56.7	56.3	55.8	55.3	55.3
87.5°	22.5	22.6	22.6	22.7	22.8	22.9	22.9	22.9	22.9	22.9	23.1
90°	1.7	3.1	4.5	5.9	7.3	8.5	9.5	10.5	11.5	12.5	13.3
92.5°	7.2	7.3	7.3	7.4	7.5	8.0	9.1	10.1	11.1	12.1	12.9
95°	31.4	27.1	22.8	18.4	14.1	12.0	12.2	12.3	12.4	12.5	13.3
97.5°	66.6	69.3	72.0	74.7	77.4	71.6	57.5	43.4	29.2	15.1	15.1
100°	93.5	95.8	98.1	100.4	102.7	95.1	77.6	60.1	42.6	25.1	22.9
102.5°	123.7	125.3	127.0	128.7	130.4	130.1	127.8	125.5	123.2	120.9	97.7
105°	171.7	172.5	173.2	174.0	174.7	175.4	176.1	176.7	177.3	178.0	179.1
107.5°	216.3	216.7	217.1	217.4	217.8	218.4	219.3	220.2	221.0	221.9	222.5
110°	246.4	246.8	247.2	247.6	247.9	248.5	249.3	250.0	250.8	251.6	251.8



TEST NUMBER: P332595

CATALOG NUMBER: SA4XXDIP-C795D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.6	276.3	277.0	277.7	278.4	278.9	279.2	279.6	280.0	280.3	280.3
115°	320.6	321.0	321.3	321.7	322.1	322.2	322.1	322.0	321.8	321.7	322.0
117.5°	361.1	361.6	362.1	362.6	363.1	363.5	363.8	364.1	364.3	364.6	364.6
120°	388.5	389.0	389.5	390.0	390.5	390.7	390.6	390.4	390.3	390.2	390.4
122.5°	414.0	414.3	414.6	414.9	415.2	415.5	415.7	415.8	416.0	416.2	416.3
125°	450.6	451.1	451.7	452.2	452.7	452.8	452.5	452.3	452.0	451.8	452.2
127.5°	485.3	485.4	485.6	485.7	485.8	486.2	486.8	487.3	487.9	488.5	488.4
130°	507.7	507.8	507.9	508.1	508.2	508.4	508.8	509.2	509.6	510.0	510.1
132.5°	528.2	528.4	528.7	528.9	529.1	529.5	530.0	530.4	530.9	531.4	531.5
135°	559.0	558.9	558.8	558.6	558.5	558.7	559.2	559.7	560.2	560.7	561.0
137.5°	586.3	586.3	586.4	586.4	586.5	586.8	587.3	587.9	588.5	589.0	589.3
140°	604.1	604.3	604.6	604.8	605.1	605.3	605.6	605.9	606.1	606.4	606.7
142.5°	620.1	620.5	621.0	621.4	621.9	622.2	622.3	622.5	622.6	622.8	623.1
145°	644.6	645.0	645.3	645.7	646.1	646.3	646.3	646.3	646.3	646.3	646.4
147.5°	664.1	664.8	665.5	666.2	666.9	667.2	667.1	667.0	666.8	666.7	666.8
150°	678.2	678.7	679.3	679.8	680.3	680.5	680.3	680.2	680.1	679.9	679.9
152.5°	690.1	690.5	690.9	691.3	691.7	691.8	691.6	691.4	691.1	690.9	691.1
155°	706.8	706.9	707.0	707.1	707.3	707.1	706.8	706.4	706.0	705.6	706.1
157.5°	720.8	720.7	720.6	720.6	720.5	720.2	719.8	719.4	718.9	718.5	719.2
160°	729.0	728.6	728.2	727.9	727.5	727.2	727.1	727.0	726.8	726.7	727.5
162.5°	736.3	735.8	735.3	734.9	734.4	734.1	733.9	733.8	733.7	733.6	734.3
165°	745.5	744.9	744.3	743.6	743.0	742.7	742.7	742.7	742.7	742.7	743.7
167.5°	752.8	752.2	751.5	750.9	750.2	749.8	749.8	749.7	749.6	749.5	750.7
170°	757.0	756.2	755.4	754.7	753.9	753.6	753.7	753.8	754.0	754.1	755.1
172.5°	759.7	758.9	758.2	757.4	756.7	756.3	756.5	756.6	756.7	756.8	757.9
175°	762.7	761.9	761.1	760.4	759.6	759.3	759.4	759.6	759.7	759.8	760.9
177.5°	764.0	763.3	762.6	761.9	761.2	760.9	761.1	761.3	761.5	761.7	762.6
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7



TEST NUMBER: P332595

CATALOG NUMBER: SA4XXDIP-C795D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5	1327.5
2.5°	1322.7	1324.6	1326.5	1327.4	1327.2	1327.0	1326.8	1326.6
5°	1315.6	1318.2	1320.8	1321.9	1321.4	1321.0	1320.5	1320.0
7.5°	1301.0	1303.1	1305.1	1306.0	1305.8	1305.5	1305.2	1304.9
10°	1288.7	1290.6	1292.5	1293.2	1292.7	1292.2	1291.8	1291.3
12.5°	1273.8	1275.8	1277.9	1278.6	1278.0	1277.3	1276.6	1276.0
15°	1245.2	1246.6	1248.0	1248.4	1247.7	1247.0	1246.3	1245.6
17.5°	1212.7	1213.6	1214.5	1214.7	1214.2	1213.7	1213.3	1212.8
20°	1188.5	1189.2	1189.9	1190.0	1189.5	1189.1	1188.6	1188.1
22.5°	1163.2	1164.5	1165.8	1166.0	1165.1	1164.3	1163.4	1162.6
25°	1121.6	1121.8	1122.1	1121.7	1120.8	1119.8	1118.9	1117.9
27.5°	1074.9	1074.3	1073.7	1072.9	1071.7	1070.5	1069.3	1068.1
30°	1042.6	1041.7	1040.7	1039.7	1038.5	1037.3	1036.1	1035.0
32.5°	1009.9	1008.8	1007.7	1006.5	1005.3	1004.1	1002.9	1001.8
35°	958.3	956.6	954.9	953.5	952.3	951.2	950.0	948.8
37.5°	904.1	902.3	900.6	898.9	897.3	895.8	894.2	892.6
40°	866.4	864.1	861.7	859.9	858.7	857.6	856.4	855.2
42.5°	829.9	827.2	824.4	822.7	821.9	821.1	820.3	819.5
45°	773.4	770.8	768.2	766.6	765.8	765.1	764.4	763.7
47.5°	718.7	715.8	712.8	710.5	708.7	706.9	705.1	703.3
50°	680.5	677.2	673.9	671.5	670.1	668.7	667.3	665.9
52.5°	641.3	638.3	635.4	633.1	631.3	629.5	627.7	625.9
55°	583.6	580.8	577.9	575.8	574.4	573.0	571.5	570.1
57.5°	525.8	523.1	520.4	518.4	517.0	515.6	514.3	512.9
60°	486.1	484.0	481.8	480.2	479.0	477.8	476.6	475.5
62.5°	447.3	445.4	443.5	441.9	440.7	439.5	438.4	437.2
65°	391.0	388.6	386.2	384.5	383.3	382.1	380.9	379.7
67.5°	332.9	330.6	328.3	327.0	326.7	326.4	326.0	325.7
70°	296.2	294.3	292.4	291.1	290.4	289.7	289.0	288.3
72.5°	259.5	258.0	256.5	255.4	254.6	253.9	253.2	252.5
75°	206.6	205.6	204.7	204.1	203.9	203.6	203.4	203.2
77.5°	156.4	156.1	155.9	155.4	154.8	154.2	153.6	153.0
80°	124.6	124.1	123.6	123.3	123.0	122.8	122.6	122.3
82.5°	96.0	95.7	95.4	95.2	95.0	94.7	94.5	94.2
85°	55.3	55.3	55.3	55.2	55.0	54.7	54.5	54.2
87.5°	23.2	23.4	23.5	23.6	23.7	23.7	23.8	23.8
90°	14.1	14.8	15.6	16.1	16.4	16.6	16.9	17.1
92.5°	13.6	14.4	15.1	15.5	15.6	15.6	15.7	15.7
95°	14.1	14.8	15.6	16.0	16.2	16.3	16.4	16.5
97.5°	15.2	15.3	15.4	15.5	15.6	15.7	15.8	16.0
100°	20.8	18.6	16.5	15.5	15.6	15.7	15.8	16.0
102.5°	74.4	51.2	27.9	16.3	16.4	16.4	16.4	16.4
105°	180.3	181.4	182.5	180.8	176.3	171.7	167.1	162.6
107.5°	223.0	223.6	224.1	224.6	225.1	225.6	226.1	226.6
110°	252.1	252.3	252.6	252.9	253.3	253.6	254.0	254.4





TEST NUMBER: P332595

CATALOG NUMBER: SA4XXDIP-C795D590U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	280.2	280.2	280.1	280.3	280.8	281.3	281.8	282.2
115°	322.2	322.5	322.7	322.9	322.9	322.9	322.9	322.9
117.5°	364.5	364.5	364.4	364.4	364.3	364.3	364.2	364.2
120°	390.7	390.9	391.2	391.2	390.9	390.7	390.4	390.2
122.5°	416.5	416.6	416.8	416.7	416.5	416.2	416.0	415.7
125°	452.5	452.9	453.3	453.6	453.7	453.8	453.9	454.1
127.5°	488.4	488.3	488.2	488.1	488.0	487.9	487.8	487.7
130°	510.2	510.3	510.5	510.5	510.5	510.5	510.5	510.5
132.5°	531.7	531.8	531.9	531.9	531.8	531.7	531.6	531.5
135°	561.2	561.5	561.7	562.0	562.2	562.5	562.8	563.0
137.5°	589.6	589.9	590.1	590.2	590.2	590.1	590.0	589.9
140°	607.1	607.5	607.9	608.1	608.3	608.4	608.5	608.6
142.5°	623.3	623.6	623.9	624.1	624.1	624.1	624.1	624.2
145°	646.5	646.7	646.8	647.0	647.2	647.5	647.8	648.0
147.5°	666.9	667.0	667.1	667.2	667.4	667.5	667.6	667.7
150°	679.9	679.9	679.9	680.0	680.1	680.3	680.4	680.5
152.5°	691.3	691.5	691.7	691.8	691.7	691.6	691.5	691.5
155°	706.6	707.1	707.6	707.7	707.3	706.9	706.6	706.2
157.5°	719.8	720.5	721.1	721.1	720.5	719.8	719.2	718.5
160°	728.2	729.0	729.8	729.8	729.0	728.2	727.5	726.7
162.5°	735.1	735.8	736.6	736.6	735.7	734.8	734.0	733.1
165°	744.7	745.7	746.8	746.7	745.5	744.4	743.3	742.1
167.5°	751.8	752.9	754.0	753.9	752.7	751.4	750.1	748.9
170°	756.1	757.1	758.2	758.0	756.8	755.5	754.2	753.0
172.5°	758.9	759.9	760.9	760.7	759.4	758.0	756.6	755.2
175°	762.1	763.2	764.4	764.2	762.7	761.1	759.6	758.1
177.5°	763.4	764.2	765.0	764.8	763.6	762.4	761.1	759.9
180°	762.7	762.7	762.7	762.7	762.7	762.7	762.7	762.7

(END OF REPORT)