

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332652-927

Luminaire Tested: **SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332652-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6921.1 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332652-927  
CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	58	56	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10672	10672	10672	10672
5°	12568	10699	9444	10699
10°	15048	10653	8502	10653
15°	17804	10546	7809	10546
20°	19826	10436	7189	10436
25°	20147	10273	6762	10273
30°	17143	10118	6626	10118
35°	13180	9866	6628	9866
40°	10273	9569	6752	9569
45°	8566	9122	6865	9122
50°	7538	8577	7097	8577
55°	6906	7924	7385	7924
60°	6471	7340	7727	7340
65°	6025	6684	8013	6684
70°	5507	6035	8195	6035
75°	4919	5312	8097	5312
80°	4124	4351	7843	4351
85°	3047	3149	7503	3149



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.8	1.9
10°-20°	397.0	5.7
20°-30°	629.5	9.1
30°-40°	700.6	10.1
40°-50°	637.7	9.2
50°-60°	521.1	7.5
60°-70°	372.0	5.4
70°-80°	204.9	3.0
80°-90°	59.0	0.9
90°-100°	36.2	0.5
100°-110°	230.6	3.3
110°-120°	441.1	6.4
120°-130°	559.9	8.1
130°-140°	599.1	8.7
140°-150°	560.2	8.1
150°-160°	451.8	6.5
160°-170°	291.4	4.2
170°-180°	100.4	1.5
0°-30°	1155.3	16.7
0°-40°	1855.8	26.8
0°-60°	3014.6	43.6
0°-90°	3650.5	52.7
90°-120°	707.8	10.2
90°-150°	2427.0	35.1
90°-180°	3271.0	47.3
0°-180°	6921.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1322	1322	1322	1322	1322	
5°	1551	1320	1165	1320	1551	158
15°	2130	1262	934	1262	2130	602
25°	2262	1153	759	1153	2262	997
35°	1337	1001	672	1001	1337	849
45°	750	799	601	799	750	591
55°	491	563	525	563	491	443
65°	315	350	420	350	315	312
75°	158	170	260	170	158	168
85°	33	34	81	34	33	41
90°	24	2	24	2	24	11
95°	23	44	23	44	23	18
105°	225	238	225	238	225	197
115°	448	444	448	444	448	443
125°	630	625	630	625	630	561
135°	780	775	780	775	780	601
145°	898	894	898	894	898	561
155°	979	980	979	980	979	451
165°	1029	1034	1029	1034	1029	291
175°	1051	1057	1051	1057	1051	100
180°	1057	1057	1057	1057	1057	



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1407.0	1406.6	1402.2	1401.3	1398.2	1394.3	1393.4	1386.4	1372.4	1365.8	1364.1
5°	1550.9	1561.9	1547.6	1544.9	1543.3	1525.2	1515.8	1504.9	1479.7	1464.9	1453.4
7.5°	1722.7	1723.9	1717.8	1712.7	1698.8	1683.0	1659.4	1634.2	1604.2	1573.0	1549.4
10°	1835.7	1840.1	1833.0	1831.8	1804.0	1786.4	1751.4	1721.8	1687.8	1650.0	1615.6
12.5°	1954.9	1948.7	1945.1	1921.7	1916.5	1884.5	1843.8	1813.4	1761.0	1717.5	1671.6
15°	2130.3	2118.3	2110.6	2078.3	2062.4	2018.1	1974.8	1941.4	1873.0	1807.8	1758.5
17.5°	2233.2	2245.4	2227.6	2214.3	2173.3	2142.1	2097.9	2027.8	1974.3	1893.3	1831.1
20°	2307.8	2308.8	2299.0	2285.3	2253.0	2213.6	2165.4	2088.7	2024.7	1944.1	1858.7
22.5°	2327.9	2328.1	2323.9	2311.1	2286.7	2254.7	2206.1	2142.1	2064.5	1977.0	1891.6
25°	2261.8	2259.5	2264.5	2278.7	2269.4	2259.5	2231.7	2184.0	2111.7	2019.1	1927.1
27.5°	2015.9	2031.1	2058.9	2094.0	2127.7	2153.5	2160.7	2150.9	2106.1	2030.0	1933.6
30°	1839.0	1857.6	1878.4	1913.4	1981.3	2020.2	2063.0	2095.2	2077.2	2016.4	1926.6
32.5°	1644.5	1649.1	1680.0	1719.8	1782.0	1856.8	1924.5	1990.1	2011.9	1980.1	1905.1
35°	1337.4	1345.0	1378.4	1417.8	1494.0	1585.4	1687.3	1778.2	1853.2	1883.3	1845.0
37.5°	1091.3	1113.3	1136.9	1179.3	1246.3	1328.6	1434.5	1552.1	1664.0	1738.8	1751.6
40°	974.8	988.5	1005.4	1037.8	1094.7	1175.8	1266.7	1401.4	1520.3	1627.6	1662.6
42.5°	882.8	890.8	901.2	930.4	973.8	1054.4	1137.4	1255.9	1375.2	1503.6	1562.3
45°	750.3	758.5	776.0	793.0	825.9	881.7	958.9	1056.4	1176.3	1300.1	1408.5
47.5°	654.5	659.8	670.2	688.4	716.3	753.1	815.9	897.4	1008.5	1128.7	1244.2
50°	600.2	604.6	612.8	629.2	650.6	683.4	734.9	811.0	898.1	1019.1	1132.5
52.5°	557.3	559.0	565.1	576.2	593.2	620.8	663.1	726.0	807.0	914.9	1027.8
55°	490.7	492.9	498.4	506.6	521.3	538.8	571.2	618.3	689.0	782.6	880.6
57.5°	435.9	437.4	442.0	445.2	457.4	471.7	496.5	530.1	583.7	663.1	750.6
60°	400.8	399.8	405.3	408.0	416.2	428.3	447.4	479.7	526.2	590.3	670.8
62.5°	366.7	365.2	369.8	373.4	378.1	388.4	404.0	429.4	467.1	525.1	594.6
65°	315.4	313.2	316.0	320.4	324.7	330.3	341.7	364.2	394.3	435.9	489.0
67.5°	264.0	266.3	266.7	268.9	271.4	278.8	286.8	302.6	323.8	357.2	402.2
70°	233.3	233.9	236.1	236.1	237.7	244.2	250.8	260.2	280.9	311.6	348.3
72.5°	202.6	204.9	204.1	205.8	207.0	211.4	216.2	225.1	242.8	265.6	296.6
75°	157.7	159.4	159.4	159.9	161.5	163.2	167.0	173.6	186.2	203.2	224.5
77.5°	115.0	115.3	116.0	118.0	118.0	120.6	123.4	128.7	134.9	146.6	159.5
80°	88.7	89.8	89.3	90.4	90.4	92.5	93.6	100.2	103.0	110.6	121.0
82.5°	65.0	66.1	66.1	67.6	68.4	68.9	70.4	73.0	75.8	82.5	86.8
85°	32.9	34.0	32.9	34.0	35.6	36.1	37.8	38.3	40.6	42.1	46.0
87.5°	14.4	15.6	15.5	15.9	16.7	17.0	17.3	16.6	18.1	18.4	19.9
90°	23.7	23.4	23.1	22.7	22.3	21.6	20.6	19.5	18.5	17.4	16.0
92.5°	21.9	21.8	21.7	21.6	21.5	21.0	20.0	18.9	17.8	16.8	15.4
95°	22.9	22.7	22.6	22.4	22.3	21.6	20.6	19.5	18.5	17.4	17.2
97.5°	22.2	21.9	21.8	21.6	21.5	21.3	21.2	21.1	21.0	20.9	40.5
100°	22.2	21.9	21.8	21.6	21.5	22.8	25.8	28.8	31.8	34.8	59.0
102.5°	22.8	22.7	22.7	22.7	22.7	38.7	71.0	103.2	135.4	167.6	170.8
105°	225.4	231.7	238.1	244.4	250.7	253.0	251.4	249.9	248.3	246.8	245.9
107.5°	314.1	313.5	312.8	312.1	311.4	310.7	310.0	309.2	308.4	307.6	306.4
110°	352.7	352.2	351.6	351.1	350.6	350.1	349.8	349.4	349.1	348.7	347.7



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	391.3	390.6	390.0	389.3	388.6	388.3	388.4	388.5	388.6	388.6	388.1
115°	447.6	447.6	447.6	447.6	447.6	447.4	447.1	446.7	446.4	446.0	446.2
117.5°	504.9	504.9	505.0	505.1	505.2	505.2	505.3	505.3	505.4	505.5	505.1
120°	540.9	541.3	541.6	541.9	542.3	542.3	541.9	541.6	541.3	540.9	541.1
122.5°	576.3	576.7	577.0	577.4	577.7	577.8	577.6	577.4	577.2	576.9	576.7
125°	629.5	629.3	629.2	629.0	628.8	628.4	627.9	627.4	626.9	626.3	626.7
127.5°	676.1	676.3	676.4	676.6	676.7	676.8	676.9	677.1	677.2	677.2	676.4
130°	707.8	707.8	707.8	707.8	707.8	707.7	707.5	707.3	707.2	707.0	706.5
132.5°	736.9	737.0	737.1	737.3	737.4	737.4	737.3	737.0	736.9	736.7	736.0
135°	780.5	780.1	779.8	779.5	779.1	778.8	778.4	778.1	777.7	777.4	776.7
137.5°	817.8	817.9	818.1	818.2	818.2	818.2	817.8	817.4	817.0	816.6	815.8
140°	843.8	843.6	843.4	843.3	843.1	842.7	842.2	841.7	841.1	840.7	840.3
142.5°	865.3	865.3	865.2	865.2	865.1	865.0	864.6	864.2	863.8	863.4	863.2
145°	898.3	898.0	897.6	897.3	897.0	896.7	896.5	896.4	896.2	896.0	896.0
147.5°	925.7	925.6	925.3	925.2	925.0	924.9	924.7	924.6	924.5	924.3	924.5
150°	943.4	943.3	943.1	942.9	942.7	942.6	942.6	942.6	942.6	942.6	942.9
152.5°	958.6	958.7	958.9	958.9	959.0	958.9	958.7	958.4	958.1	957.8	958.1
155°	979.1	979.5	980.1	980.6	981.1	981.0	980.3	979.6	978.9	978.3	978.7
157.5°	996.1	997.0	997.9	998.9	999.7	999.7	998.9	997.9	997.0	996.1	996.7
160°	1007.5	1008.5	1009.6	1010.7	1011.7	1011.7	1010.7	1009.6	1008.5	1007.5	1007.7
162.5°	1016.4	1017.6	1018.7	1019.9	1021.1	1021.2	1020.2	1019.1	1018.0	1017.0	1017.2
165°	1028.8	1030.4	1032.0	1033.6	1035.1	1035.2	1033.9	1032.5	1031.0	1029.6	1029.6
167.5°	1038.2	1039.9	1041.7	1043.5	1045.2	1045.3	1043.8	1042.2	1040.7	1039.1	1039.3
170°	1043.9	1045.6	1047.4	1049.2	1050.9	1051.1	1049.6	1048.3	1046.9	1045.4	1045.3
172.5°	1047.0	1048.9	1050.8	1052.7	1054.6	1054.9	1053.4	1052.1	1050.7	1049.2	1049.1
175°	1051.0	1053.1	1055.2	1057.3	1059.4	1059.7	1058.1	1056.5	1054.9	1053.4	1053.2
177.5°	1053.5	1055.2	1056.9	1058.6	1060.3	1060.6	1059.4	1058.3	1057.2	1056.1	1055.7
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1364.5	1358.4	1354.0	1350.5	1340.8	1335.1	1330.8	1324.6	1317.6	1310.2	1301.0
5°	1441.9	1423.3	1409.6	1388.9	1369.1	1352.7	1335.7	1320.3	1301.7	1281.5	1266.7
7.5°	1523.3	1495.6	1460.2	1429.3	1394.7	1364.6	1337.7	1310.0	1281.4	1253.5	1228.0
10°	1575.0	1539.4	1500.0	1453.4	1409.6	1370.7	1334.6	1299.6	1265.6	1231.6	1202.6
12.5°	1630.6	1586.3	1528.0	1473.6	1424.5	1372.5	1328.9	1285.9	1245.0	1209.3	1175.4
15°	1705.3	1641.2	1573.9	1501.1	1436.5	1375.7	1316.0	1261.8	1215.8	1168.6	1135.8
17.5°	1751.3	1672.0	1595.0	1518.9	1440.6	1364.0	1299.6	1237.0	1179.4	1132.7	1091.2
20°	1781.5	1702.6	1606.8	1530.7	1437.6	1358.7	1284.2	1214.7	1154.4	1104.6	1061.8
22.5°	1807.8	1716.7	1620.8	1520.6	1427.9	1344.3	1262.7	1192.8	1131.2	1078.7	1037.8
25°	1822.0	1717.4	1613.4	1513.7	1408.5	1309.4	1235.5	1153.3	1087.6	1032.3	988.5
27.5°	1823.5	1711.7	1593.9	1483.2	1374.7	1282.4	1189.1	1115.6	1047.4	989.0	946.9
30°	1818.7	1702.1	1575.6	1455.6	1346.6	1246.4	1165.4	1085.4	1015.9	957.8	914.0
32.5°	1803.4	1681.9	1551.9	1425.0	1312.0	1214.0	1130.4	1054.3	986.5	929.3	883.4
35°	1759.0	1639.1	1500.6	1368.6	1253.0	1153.9	1078.3	1001.1	933.2	878.9	834.6
37.5°	1689.7	1581.3	1440.4	1303.9	1190.3	1090.8	1015.9	946.1	884.9	829.8	784.3
40°	1629.2	1533.9	1392.7	1259.6	1136.9	1042.2	972.1	908.0	847.2	795.2	751.9
42.5°	1559.6	1476.5	1346.2	1205.2	1087.0	991.8	923.4	865.9	808.7	760.6	717.3
45°	1435.4	1380.6	1257.9	1127.6	1004.4	914.6	849.4	799.0	750.8	703.7	667.6
47.5°	1292.5	1265.4	1162.1	1038.3	921.4	832.8	776.3	729.8	687.5	647.6	615.8
50°	1196.6	1183.4	1094.2	974.8	863.1	779.8	722.9	682.9	646.7	611.7	581.6
52.5°	1101.9	1101.5	1021.0	911.7	808.3	728.2	671.6	634.3	602.9	574.5	547.4
55°	957.3	972.6	909.7	812.1	719.6	647.3	596.4	563.0	541.1	517.5	497.3
57.5°	824.4	849.9	797.9	712.0	634.9	568.2	523.9	498.8	475.5	461.2	446.5
60°	737.7	761.8	721.3	649.0	576.2	519.2	477.0	454.6	434.3	424.5	414.0
62.5°	660.6	682.1	652.0	585.0	521.8	467.0	431.4	409.9	396.2	385.4	378.5
65°	550.4	568.5	542.7	494.0	439.7	395.9	366.9	349.9	336.8	332.4	324.7
67.5°	444.9	461.4	447.4	406.0	362.5	329.4	306.7	290.3	282.6	278.8	273.3
70°	382.2	398.7	383.9	347.8	314.3	286.5	265.1	255.7	247.6	245.9	238.2
72.5°	329.2	340.4	325.7	297.4	268.8	245.3	228.7	219.0	214.7	211.8	207.6
75°	247.0	256.8	247.0	225.1	204.8	188.4	174.1	170.3	165.4	163.7	161.0
77.5°	174.8	183.3	175.8	162.1	146.9	134.3	126.6	121.7	120.6	117.7	119.1
80°	133.6	139.1	132.0	122.7	110.6	101.9	96.4	93.6	90.4	89.3	91.4
82.5°	95.9	98.4	94.7	88.5	79.5	73.8	70.1	66.9	66.2	66.5	66.5
85°	49.8	49.3	48.7	43.3	40.6	36.7	34.5	34.0	33.4	34.5	35.6
87.5°	19.6	19.7	19.0	17.0	15.2	13.5	12.7	11.9	12.7	13.5	14.3
90°	14.6	13.2	11.8	10.1	8.2	6.3	4.3	2.4	4.3	6.3	8.2
92.5°	13.9	12.5	11.2	10.4	10.3	10.1	10.1	10.0	10.1	10.1	10.3
95°	17.0	16.9	16.7	19.6	25.6	31.5	37.5	43.5	37.5	31.5	25.6
97.5°	60.1	79.7	99.3	107.3	103.5	99.8	96.1	92.4	96.1	99.8	103.5
100°	83.3	107.6	131.8	142.4	139.2	136.0	132.8	129.7	132.8	136.0	139.2
102.5°	174.0	177.1	180.3	180.7	178.4	176.1	173.8	171.4	173.8	176.1	178.4
105°	244.9	244.1	243.2	242.2	241.2	240.1	239.1	238.1	239.1	240.1	241.2
107.5°	305.2	304.0	302.9	302.0	301.4	301.0	300.4	299.8	300.4	301.0	301.4
110°	346.7	345.5	344.5	343.7	343.2	342.7	342.1	341.7	342.1	342.7	343.2





TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	387.6	387.1	386.7	386.0	385.0	384.0	383.1	382.1	383.1	384.0	385.0
115°	446.4	446.6	446.7	446.6	446.0	445.5	445.0	444.4	445.0	445.5	446.0
117.5°	504.7	504.3	503.9	503.4	502.7	502.0	501.3	500.6	501.3	502.0	502.7
120°	541.3	541.5	541.6	541.4	540.7	540.0	539.2	538.5	539.2	540.0	540.7
122.5°	576.5	576.2	576.0	575.7	575.2	574.8	574.4	573.9	574.4	574.8	575.2
125°	627.0	627.4	627.7	627.6	626.9	626.1	625.4	624.7	625.4	626.1	626.9
127.5°	675.7	674.9	674.0	673.5	673.4	673.2	673.0	672.8	673.0	673.2	673.4
130°	705.9	705.4	704.9	704.5	704.3	704.2	704.0	703.9	704.0	704.2	704.3
132.5°	735.4	734.7	734.0	733.6	733.2	732.9	732.6	732.3	732.6	732.9	733.2
135°	775.9	775.2	774.5	774.3	774.4	774.7	774.8	775.0	774.8	774.7	774.4
137.5°	815.1	814.3	813.5	813.1	813.0	812.9	812.9	812.8	812.9	812.9	813.0
140°	840.0	839.6	839.2	838.8	838.5	838.2	837.8	837.5	837.8	838.2	838.5
142.5°	863.0	862.8	862.5	862.1	861.5	860.9	860.2	859.6	860.2	860.9	861.5
145°	896.0	896.0	896.0	895.7	895.2	894.7	894.1	893.6	894.1	894.7	895.2
147.5°	924.6	924.8	925.0	924.6	923.6	922.7	921.6	920.7	921.6	922.7	923.6
150°	943.0	943.2	943.3	943.1	942.4	941.7	941.0	940.2	941.0	941.7	942.4
152.5°	958.5	958.8	959.1	958.9	958.4	957.8	957.3	956.7	957.3	957.8	958.4
155°	979.3	979.9	980.3	980.5	980.3	980.2	980.0	979.9	980.0	980.2	980.3
157.5°	997.3	997.9	998.5	998.9	998.9	999.0	999.2	999.3	999.2	999.0	998.9
160°	1007.8	1008.1	1008.2	1008.5	1009.1	1009.6	1010.1	1010.7	1010.1	1009.6	1009.1
162.5°	1017.3	1017.5	1017.7	1018.1	1018.7	1019.5	1020.1	1020.8	1020.1	1019.5	1018.7
165°	1029.6	1029.6	1029.6	1030.1	1030.9	1031.8	1032.7	1033.6	1032.7	1031.8	1030.9
167.5°	1039.3	1039.4	1039.6	1040.1	1041.0	1041.9	1042.8	1043.7	1042.8	1041.9	1041.0
170°	1045.1	1044.9	1044.7	1045.2	1046.2	1047.3	1048.4	1049.4	1048.4	1047.3	1046.2
172.5°	1048.9	1048.7	1048.5	1049.0	1050.0	1051.1	1052.2	1053.2	1052.2	1051.1	1050.0
175°	1053.0	1052.8	1052.7	1053.1	1054.2	1055.2	1056.3	1057.3	1056.3	1055.2	1054.2
177.5°	1055.5	1055.2	1054.9	1055.3	1056.3	1057.2	1058.2	1059.2	1058.2	1057.2	1056.3
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1296.6	1292.7	1287.0	1279.1	1272.5	1265.5	1263.8	1261.1	1266.4	1261.9	1260.7
5°	1254.1	1242.6	1227.8	1210.9	1200.9	1186.8	1184.0	1178.5	1173.1	1172.5	1167.0
7.5°	1209.1	1192.2	1172.8	1155.6	1139.6	1123.9	1113.8	1111.6	1103.5	1098.8	1093.3
10°	1180.2	1159.4	1136.9	1120.5	1101.8	1085.4	1074.0	1067.4	1061.8	1055.8	1050.4
12.5°	1146.0	1123.9	1105.3	1087.6	1065.5	1053.0	1034.0	1022.6	1021.6	1021.7	1007.4
15°	1106.2	1084.3	1055.8	1030.6	1018.6	994.5	984.1	971.0	962.7	954.5	948.0
17.5°	1060.8	1033.5	1011.3	982.4	959.3	940.2	926.5	918.6	906.3	894.6	886.2
20°	1032.3	1003.3	979.7	949.0	923.8	900.3	888.8	877.9	868.5	858.7	849.4
22.5°	1003.4	973.0	944.2	914.4	891.0	866.2	855.1	840.2	831.3	825.9	816.5
25°	957.8	925.0	892.1	863.6	839.6	817.6	802.9	791.3	781.5	777.1	771.1
27.5°	908.3	875.7	843.9	811.6	784.3	768.3	756.5	747.8	742.2	736.3	733.6
30°	876.8	842.8	808.9	778.7	753.5	737.7	726.7	720.7	716.3	713.6	710.8
32.5°	844.8	811.3	775.5	748.1	725.5	711.4	703.1	697.0	694.8	693.9	692.8
35°	793.5	759.5	726.7	702.1	680.7	675.3	668.1	664.8	663.8	667.6	669.2
37.5°	743.9	712.4	682.1	658.2	644.3	636.3	633.8	634.0	637.9	641.3	645.2
40°	711.9	681.3	652.8	632.0	618.9	613.9	612.8	615.5	620.0	623.8	628.1
42.5°	680.8	650.6	624.7	605.2	596.0	591.5	592.2	594.9	601.1	605.8	612.4
45°	632.6	607.4	582.2	566.3	558.6	559.7	559.7	564.6	570.6	577.7	584.9
47.5°	587.1	561.7	541.0	527.6	523.6	522.7	525.8	532.2	540.8	549.6	559.6
50°	556.4	532.3	514.2	502.2	497.8	499.5	503.8	509.8	520.2	531.2	541.6
52.5°	525.3	503.4	486.6	475.5	472.4	475.4	479.7	489.3	498.4	510.2	522.8
55°	477.0	458.4	445.2	437.0	435.9	437.6	442.5	452.9	466.0	480.9	492.9
57.5°	428.9	413.4	401.3	395.6	396.2	397.7	405.8	418.2	432.2	448.0	463.5
60°	396.5	382.2	372.4	368.0	368.5	371.9	381.7	393.2	410.7	426.0	442.5
62.5°	365.8	353.3	343.9	340.0	339.2	346.4	355.8	367.8	385.3	402.4	420.2
65°	316.6	306.7	299.0	296.8	298.5	304.0	316.0	331.8	346.7	364.7	383.3
67.5°	268.3	260.2	255.0	256.0	257.9	266.0	276.2	289.8	306.6	325.3	343.7
70°	237.7	230.0	225.6	226.2	229.5	239.3	248.1	261.7	279.9	299.0	314.3
72.5°	206.1	201.1	197.2	199.5	202.7	209.5	220.5	234.2	250.1	267.9	284.1
75°	158.3	158.3	156.1	157.7	162.6	169.2	177.4	191.7	207.6	221.8	235.0
77.5°	117.4	116.2	117.6	119.6	122.5	130.2	139.7	149.8	161.8	176.0	186.9
80°	89.8	90.4	93.1	96.4	97.5	103.5	113.4	122.7	132.0	144.0	154.4
82.5°	67.5	68.0	69.5	73.6	74.7	81.2	87.5	96.8	105.3	113.4	122.0
85°	36.7	36.7	39.5	41.0	43.8	48.2	52.0	57.5	65.2	70.7	78.8
87.5°	16.0	16.4	18.4	19.6	21.2	23.6	24.7	29.8	31.7	34.1	38.2
90°	10.1	11.8	13.2	14.6	16.0	17.4	18.5	19.5	20.6	21.6	22.3
92.5°	10.4	11.2	12.5	13.9	15.4	16.8	17.8	18.9	20.0	21.0	21.5
95°	19.6	16.7	16.9	17.0	17.2	17.4	18.5	19.5	20.6	21.6	22.3
97.5°	107.3	99.3	79.7	60.1	40.5	20.9	21.0	21.1	21.2	21.3	21.5
100°	142.4	131.8	107.6	83.3	59.0	34.8	31.8	28.8	25.8	22.8	21.5
102.5°	180.7	180.3	177.1	174.0	170.8	167.6	135.4	103.2	71.0	38.7	22.7
105°	242.2	243.2	244.1	244.9	245.9	246.8	248.3	249.9	251.4	253.0	250.7
107.5°	302.0	302.9	304.0	305.2	306.4	307.6	308.4	309.2	310.0	310.7	311.4
110°	343.7	344.5	345.5	346.7	347.7	348.7	349.1	349.4	349.8	350.1	350.6



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	386.0	386.7	387.1	387.6	388.1	388.6	388.6	388.5	388.4	388.3	388.6
115°	446.6	446.7	446.6	446.4	446.2	446.0	446.4	446.7	447.1	447.4	447.6
117.5°	503.4	503.9	504.3	504.7	505.1	505.5	505.4	505.3	505.3	505.2	505.2
120°	541.4	541.6	541.5	541.3	541.1	540.9	541.3	541.6	541.9	542.3	542.3
122.5°	575.7	576.0	576.2	576.5	576.7	576.9	577.2	577.4	577.6	577.8	577.7
125°	627.6	627.7	627.4	627.0	626.7	626.3	626.9	627.4	627.9	628.4	628.8
127.5°	673.5	674.0	674.9	675.7	676.4	677.2	677.2	677.1	676.9	676.8	676.7
130°	704.5	704.9	705.4	705.9	706.5	707.0	707.2	707.3	707.5	707.7	707.8
132.5°	733.6	734.0	734.7	735.4	736.0	736.7	736.9	737.0	737.3	737.4	737.4
135°	774.3	774.5	775.2	775.9	776.7	777.4	777.7	778.1	778.4	778.8	779.1
137.5°	813.1	813.5	814.3	815.1	815.8	816.6	817.0	817.4	817.8	818.2	818.2
140°	838.8	839.2	839.6	840.0	840.3	840.7	841.1	841.7	842.2	842.7	843.1
142.5°	862.1	862.5	862.8	863.0	863.2	863.4	863.8	864.2	864.6	865.0	865.1
145°	895.7	896.0	896.0	896.0	896.0	896.0	896.2	896.4	896.5	896.7	897.0
147.5°	924.6	925.0	924.8	924.6	924.5	924.3	924.5	924.6	924.7	924.9	925.0
150°	943.1	943.3	943.2	943.0	942.9	942.6	942.6	942.6	942.6	942.6	942.7
152.5°	958.9	959.1	958.8	958.5	958.1	957.8	958.1	958.4	958.7	958.9	959.0
155°	980.5	980.3	979.9	979.3	978.7	978.3	978.9	979.6	980.3	981.0	981.1
157.5°	998.9	998.5	997.9	997.3	996.7	996.1	997.0	997.9	998.9	999.7	999.7
160°	1008.5	1008.2	1008.1	1007.8	1007.7	1007.5	1008.5	1009.6	1010.7	1011.7	1011.7
162.5°	1018.1	1017.7	1017.5	1017.3	1017.2	1017.0	1018.0	1019.1	1020.2	1021.2	1021.1
165°	1030.1	1029.6	1029.6	1029.6	1029.6	1029.6	1031.0	1032.5	1033.9	1035.2	1035.1
167.5°	1040.1	1039.6	1039.4	1039.3	1039.3	1039.1	1040.7	1042.2	1043.8	1045.3	1045.2
170°	1045.2	1044.7	1044.9	1045.1	1045.3	1045.4	1046.9	1048.3	1049.6	1051.1	1050.9
172.5°	1049.0	1048.5	1048.7	1048.9	1049.1	1049.2	1050.7	1052.1	1053.4	1054.9	1054.6
175°	1053.1	1052.7	1052.8	1053.0	1053.2	1053.4	1054.9	1056.5	1058.1	1059.7	1059.4
177.5°	1055.3	1054.9	1055.2	1055.5	1055.7	1056.1	1057.2	1058.3	1059.4	1060.6	1060.3
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1259.8	1258.9	1255.8	1255.5	1255.8	1258.9	1259.8	1260.7	1261.9	1266.4	1261.1
5°	1163.7	1161.0	1159.4	1165.4	1159.4	1161.0	1163.7	1167.0	1172.5	1173.1	1178.5
7.5°	1091.3	1089.2	1084.3	1082.8	1084.3	1089.2	1091.3	1093.3	1098.8	1103.5	1111.6
10°	1044.9	1042.7	1038.3	1037.2	1038.3	1042.7	1044.9	1050.4	1055.8	1061.8	1067.4
12.5°	1000.2	995.9	995.0	996.0	995.0	995.9	1000.2	1007.4	1021.7	1021.6	1022.6
15°	940.9	938.7	932.6	934.3	932.6	938.7	940.9	948.0	954.5	962.7	971.0
17.5°	882.3	879.7	872.4	878.8	872.4	879.7	882.3	886.2	894.6	906.3	918.6
20°	845.6	841.1	837.3	836.8	837.3	841.1	845.6	849.4	858.7	868.5	877.9
22.5°	810.5	806.6	806.2	802.6	806.2	806.6	810.5	816.5	825.9	831.3	840.2
25°	766.7	762.9	761.8	759.1	761.8	762.9	766.7	771.1	777.1	781.5	791.3
27.5°	733.1	731.2	729.2	730.1	729.2	731.2	733.1	733.6	736.3	742.2	747.8
30°	712.5	711.9	710.8	710.8	710.8	711.9	712.5	710.8	713.6	716.3	720.7
32.5°	695.4	695.3	695.9	695.9	695.9	695.3	695.4	692.8	693.9	694.8	697.0
35°	671.4	673.0	674.1	672.5	674.1	673.0	671.4	669.2	667.6	663.8	664.8
37.5°	649.7	651.3	652.9	654.7	652.9	651.3	649.7	645.2	641.3	637.9	634.0
40°	633.0	636.9	638.0	640.7	638.0	636.9	633.0	628.1	623.8	620.0	615.5
42.5°	617.3	621.5	624.4	625.0	624.4	621.5	617.3	612.4	605.8	601.1	594.9
45°	593.1	597.5	601.3	601.3	601.3	597.5	593.1	584.9	577.7	570.6	564.6
47.5°	568.0	574.3	578.2	579.2	578.2	574.3	568.0	559.6	549.6	540.8	532.2
50°	551.0	558.6	562.4	565.1	562.4	558.6	551.0	541.6	531.2	520.2	509.8
52.5°	534.2	541.9	547.1	548.5	547.1	541.9	534.2	522.8	510.2	498.4	489.3
55°	505.5	516.4	522.4	524.7	522.4	516.4	505.5	492.9	480.9	466.0	452.9
57.5°	478.3	488.4	495.4	497.0	495.4	488.4	478.3	463.5	448.0	432.2	418.2
60°	457.2	468.3	477.0	478.6	477.0	468.3	457.2	442.5	426.0	410.7	393.2
62.5°	435.8	447.2	455.1	459.4	455.1	447.2	435.8	420.2	402.4	385.3	367.8
65°	398.7	410.2	417.9	419.5	417.9	410.2	398.7	383.3	364.7	346.7	331.8
67.5°	358.1	369.6	374.7	377.9	374.7	369.6	358.1	343.7	325.3	306.6	289.8
70°	329.7	339.0	344.4	347.2	344.4	339.0	329.7	314.3	299.0	279.9	261.7
72.5°	297.2	307.0	313.4	313.9	313.4	307.0	297.2	284.1	267.9	250.1	234.2
75°	247.6	256.3	259.6	259.6	259.6	256.3	247.6	235.0	221.8	207.6	191.7
77.5°	195.9	200.4	204.6	205.5	204.6	200.4	195.9	186.9	176.0	161.8	149.8
80°	162.6	165.4	168.7	168.7	168.7	165.4	162.6	154.4	144.0	132.0	122.7
82.5°	128.5	130.8	134.0	133.6	134.0	130.8	128.5	122.0	113.4	105.3	96.8
85°	77.8	82.7	82.1	81.0	82.1	82.7	77.8	78.8	70.7	65.2	57.5
87.5°	39.6	40.1	41.5	42.5	41.5	40.1	39.6	38.2	34.1	31.7	29.8
90°	22.7	23.1	23.4	23.7	23.4	23.1	22.7	22.3	21.6	20.6	19.5
92.5°	21.6	21.7	21.8	21.9	21.8	21.7	21.6	21.5	21.0	20.0	18.9
95°	22.4	22.6	22.7	22.9	22.7	22.6	22.4	22.3	21.6	20.6	19.5
97.5°	21.6	21.8	21.9	22.2	21.9	21.8	21.6	21.5	21.3	21.2	21.1
100°	21.6	21.8	21.9	22.2	21.9	21.8	21.6	21.5	22.8	25.8	28.8
102.5°	22.7	22.7	22.7	22.8	22.7	22.7	22.7	22.7	38.7	71.0	103.2
105°	244.4	238.1	231.7	225.4	231.7	238.1	244.4	250.7	253.0	251.4	249.9
107.5°	312.1	312.8	313.5	314.1	313.5	312.8	312.1	311.4	310.7	310.0	309.2
110°	351.1	351.6	352.2	352.7	352.2	351.6	351.1	350.6	350.1	349.8	349.4



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	389.3	390.0	390.6	391.3	390.6	390.0	389.3	388.6	388.3	388.4	388.5
115°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.4	447.1	446.7
117.5°	505.1	505.0	504.9	504.9	504.9	505.0	505.1	505.2	505.2	505.3	505.3
120°	541.9	541.6	541.3	540.9	541.3	541.6	541.9	542.3	542.3	541.9	541.6
122.5°	577.4	577.0	576.7	576.3	576.7	577.0	577.4	577.7	577.8	577.6	577.4
125°	629.0	629.2	629.3	629.5	629.3	629.2	629.0	628.8	628.4	627.9	627.4
127.5°	676.6	676.4	676.3	676.1	676.3	676.4	676.6	676.7	676.8	676.9	677.1
130°	707.8	707.8	707.8	707.8	707.8	707.8	707.8	707.8	707.7	707.5	707.3
132.5°	737.3	737.1	737.0	736.9	737.0	737.1	737.3	737.4	737.4	737.3	737.0
135°	779.5	779.8	780.1	780.5	780.1	779.8	779.5	779.1	778.8	778.4	778.1
137.5°	818.2	818.1	817.9	817.8	817.9	818.1	818.2	818.2	818.2	817.8	817.4
140°	843.3	843.4	843.6	843.8	843.6	843.4	843.3	843.1	842.7	842.2	841.7
142.5°	865.2	865.2	865.3	865.3	865.3	865.2	865.2	865.1	865.0	864.6	864.2
145°	897.3	897.6	898.0	898.3	898.0	897.6	897.3	897.0	896.7	896.5	896.4
147.5°	925.2	925.3	925.6	925.7	925.6	925.3	925.2	925.0	924.9	924.7	924.6
150°	942.9	943.1	943.3	943.4	943.3	943.1	942.9	942.7	942.6	942.6	942.6
152.5°	958.9	958.9	958.7	958.6	958.7	958.9	958.9	959.0	958.9	958.7	958.4
155°	980.6	980.1	979.5	979.1	979.5	980.1	980.6	981.1	981.0	980.3	979.6
157.5°	998.9	997.9	997.0	996.1	997.0	997.9	998.9	999.7	999.7	998.9	997.9
160°	1010.7	1009.6	1008.5	1007.5	1008.5	1009.6	1010.7	1011.7	1011.7	1010.7	1009.6
162.5°	1019.9	1018.7	1017.6	1016.4	1017.6	1018.7	1019.9	1021.1	1021.2	1020.2	1019.1
165°	1033.6	1032.0	1030.4	1028.8	1030.4	1032.0	1033.6	1035.1	1035.2	1033.9	1032.5
167.5°	1043.5	1041.7	1039.9	1038.2	1039.9	1041.7	1043.5	1045.2	1045.3	1043.8	1042.2
170°	1049.2	1047.4	1045.6	1043.9	1045.6	1047.4	1049.2	1050.9	1051.1	1049.6	1048.3
172.5°	1052.7	1050.8	1048.9	1047.0	1048.9	1050.8	1052.7	1054.6	1054.9	1053.4	1052.1
175°	1057.3	1055.2	1053.1	1051.0	1053.1	1055.2	1057.3	1059.4	1059.7	1058.1	1056.5
177.5°	1058.6	1056.9	1055.2	1053.5	1055.2	1056.9	1058.6	1060.3	1060.6	1059.4	1058.3
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1263.8	1265.5	1272.5	1279.1	1287.0	1292.7	1296.6	1301.0	1310.2	1317.6	1324.6
5°	1184.0	1186.8	1200.9	1210.9	1227.8	1242.6	1254.1	1266.7	1281.5	1301.7	1320.3
7.5°	1113.8	1123.9	1139.6	1155.6	1172.8	1192.2	1209.1	1228.0	1253.5	1281.4	1310.0
10°	1074.0	1085.4	1101.8	1120.5	1136.9	1159.4	1180.2	1202.6	1231.6	1265.6	1299.6
12.5°	1034.0	1053.0	1065.5	1087.6	1105.3	1123.9	1146.0	1175.4	1209.3	1245.0	1285.9
15°	984.1	994.5	1018.6	1030.6	1055.8	1084.3	1106.2	1135.8	1168.6	1215.8	1261.8
17.5°	926.5	940.2	959.3	982.4	1011.3	1033.5	1060.8	1091.2	1132.7	1179.4	1237.0
20°	888.8	900.3	923.8	949.0	979.7	1003.3	1032.3	1061.8	1104.6	1154.4	1214.7
22.5°	855.1	866.2	891.0	914.4	944.2	973.0	1003.4	1037.8	1078.7	1131.2	1192.8
25°	802.9	817.6	839.6	863.6	892.1	925.0	957.8	988.5	1032.3	1087.6	1153.3
27.5°	756.5	768.3	784.3	811.6	843.9	875.7	908.3	946.9	989.0	1047.4	1115.6
30°	726.7	737.7	753.5	778.7	808.9	842.8	876.8	914.0	957.8	1015.9	1085.4
32.5°	703.1	711.4	725.5	748.1	775.5	811.3	844.8	883.4	929.3	986.5	1054.3
35°	668.1	675.3	680.7	702.1	726.7	759.5	793.5	834.6	878.9	933.2	1001.1
37.5°	633.8	636.3	644.3	658.2	682.1	712.4	743.9	784.3	829.8	884.9	946.1
40°	612.8	613.9	618.9	632.0	652.8	681.3	711.9	751.9	795.2	847.2	908.0
42.5°	592.2	591.5	596.0	605.2	624.7	650.6	680.8	717.3	760.6	808.7	865.9
45°	559.7	559.7	558.6	566.3	582.2	607.4	632.6	667.6	703.7	750.8	799.0
47.5°	525.8	522.7	523.6	527.6	541.0	561.7	587.1	615.8	647.6	687.5	729.8
50°	503.8	499.5	497.8	502.2	514.2	532.3	556.4	581.6	611.7	646.7	682.9
52.5°	479.7	475.4	472.4	475.5	486.6	503.4	525.3	547.4	574.5	602.9	634.3
55°	442.5	437.6	435.9	437.0	445.2	458.4	477.0	497.3	517.5	541.1	563.0
57.5°	405.8	397.7	396.2	395.6	401.3	413.4	428.9	446.5	461.2	475.5	498.8
60°	381.7	371.9	368.5	368.0	372.4	382.2	396.5	414.0	424.5	434.3	454.6
62.5°	355.8	346.4	339.2	340.0	343.9	353.3	365.8	378.5	385.4	396.2	409.9
65°	316.0	304.0	298.5	296.8	299.0	306.7	316.6	324.7	332.4	336.8	349.9
67.5°	276.2	266.0	257.9	256.0	255.0	260.2	268.3	273.3	278.8	282.6	290.3
70°	248.1	239.3	229.5	226.2	225.6	230.0	237.7	238.2	245.9	247.6	255.7
72.5°	220.5	209.5	202.7	199.5	197.2	201.1	206.1	207.6	211.8	214.7	219.0
75°	177.4	169.2	162.6	157.7	156.1	158.3	158.3	161.0	163.7	165.4	170.3
77.5°	139.7	130.2	122.5	119.6	117.6	116.2	117.4	119.1	117.7	120.6	121.7
80°	113.4	103.5	97.5	96.4	93.1	90.4	89.8	91.4	89.3	90.4	93.6
82.5°	87.5	81.2	74.7	73.6	69.5	68.0	67.5	66.5	66.5	66.2	66.9
85°	52.0	48.2	43.8	41.0	39.5	36.7	36.7	35.6	34.5	33.4	34.0
87.5°	24.7	23.6	21.2	19.6	18.4	16.4	16.0	14.3	13.5	12.7	11.9
90°	18.5	17.4	16.0	14.6	13.2	11.8	10.1	8.2	6.3	4.3	2.4
92.5°	17.8	16.8	15.4	13.9	12.5	11.2	10.4	10.3	10.1	10.1	10.0
95°	18.5	17.4	17.2	17.0	16.9	16.7	19.6	25.6	31.5	37.5	43.5
97.5°	21.0	20.9	40.5	60.1	79.7	99.3	107.3	103.5	99.8	96.1	92.4
100°	31.8	34.8	59.0	83.3	107.6	131.8	142.4	139.2	136.0	132.8	129.7
102.5°	135.4	167.6	170.8	174.0	177.1	180.3	180.7	178.4	176.1	173.8	171.4
105°	248.3	246.8	245.9	244.9	244.1	243.2	242.2	241.2	240.1	239.1	238.1
107.5°	308.4	307.6	306.4	305.2	304.0	302.9	302.0	301.4	301.0	300.4	299.8
110°	349.1	348.7	347.7	346.7	345.5	344.5	343.7	343.2	342.7	342.1	341.7



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	388.6	388.6	388.1	387.6	387.1	386.7	386.0	385.0	384.0	383.1	382.1
115°	446.4	446.0	446.2	446.4	446.6	446.7	446.6	446.0	445.5	445.0	444.4
117.5°	505.4	505.5	505.1	504.7	504.3	503.9	503.4	502.7	502.0	501.3	500.6
120°	541.3	540.9	541.1	541.3	541.5	541.6	541.4	540.7	540.0	539.2	538.5
122.5°	577.2	576.9	576.7	576.5	576.2	576.0	575.7	575.2	574.8	574.4	573.9
125°	626.9	626.3	626.7	627.0	627.4	627.7	627.6	626.9	626.1	625.4	624.7
127.5°	677.2	677.2	676.4	675.7	674.9	674.0	673.5	673.4	673.2	673.0	672.8
130°	707.2	707.0	706.5	705.9	705.4	704.9	704.5	704.3	704.2	704.0	703.9
132.5°	736.9	736.7	736.0	735.4	734.7	734.0	733.6	733.2	732.9	732.6	732.3
135°	777.7	777.4	776.7	775.9	775.2	774.5	774.3	774.4	774.7	774.8	775.0
137.5°	817.0	816.6	815.8	815.1	814.3	813.5	813.1	813.0	812.9	812.9	812.8
140°	841.1	840.7	840.3	840.0	839.6	839.2	838.8	838.5	838.2	837.8	837.5
142.5°	863.8	863.4	863.2	863.0	862.8	862.5	862.1	861.5	860.9	860.2	859.6
145°	896.2	896.0	896.0	896.0	896.0	896.0	895.7	895.2	894.7	894.1	893.6
147.5°	924.5	924.3	924.5	924.6	924.8	925.0	924.6	923.6	922.7	921.6	920.7
150°	942.6	942.6	942.9	943.0	943.2	943.3	943.1	942.4	941.7	941.0	940.2
152.5°	958.1	957.8	958.1	958.5	958.8	959.1	958.9	958.4	957.8	957.3	956.7
155°	978.9	978.3	978.7	979.3	979.9	980.3	980.5	980.3	980.2	980.0	979.9
157.5°	997.0	996.1	996.7	997.3	997.9	998.5	998.9	998.9	999.0	999.2	999.3
160°	1008.5	1007.5	1007.7	1007.8	1008.1	1008.2	1008.5	1009.1	1009.6	1010.1	1010.7
162.5°	1018.0	1017.0	1017.2	1017.3	1017.5	1017.7	1018.1	1018.7	1019.5	1020.1	1020.8
165°	1031.0	1029.6	1029.6	1029.6	1029.6	1029.6	1030.1	1030.9	1031.8	1032.7	1033.6
167.5°	1040.7	1039.1	1039.3	1039.3	1039.4	1039.6	1040.1	1041.0	1041.9	1042.8	1043.7
170°	1046.9	1045.4	1045.3	1045.1	1044.9	1044.7	1045.2	1046.2	1047.3	1048.4	1049.4
172.5°	1050.7	1049.2	1049.1	1048.9	1048.7	1048.5	1049.0	1050.0	1051.1	1052.2	1053.2
175°	1054.9	1053.4	1053.2	1053.0	1052.8	1052.7	1053.1	1054.2	1055.2	1056.3	1057.3
177.5°	1057.2	1056.1	1055.7	1055.5	1055.2	1054.9	1055.3	1056.3	1057.2	1058.2	1059.2
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1330.8	1335.1	1340.8	1350.5	1354.0	1358.4	1364.5	1364.1	1365.8	1372.4	1386.4
5°	1335.7	1352.7	1369.1	1388.9	1409.6	1423.3	1441.9	1453.4	1464.9	1479.7	1504.9
7.5°	1337.7	1364.6	1394.7	1429.3	1460.2	1495.6	1523.3	1549.4	1573.0	1604.2	1634.2
10°	1334.6	1370.7	1409.6	1453.4	1500.0	1539.4	1575.0	1615.6	1650.0	1687.8	1721.8
12.5°	1328.9	1372.5	1424.5	1473.6	1528.0	1586.3	1630.6	1671.6	1717.5	1761.0	1813.4
15°	1316.0	1375.7	1436.5	1501.1	1573.9	1641.2	1705.3	1758.5	1807.8	1873.0	1941.4
17.5°	1299.6	1364.0	1440.6	1518.9	1595.0	1672.0	1751.3	1831.1	1893.3	1974.3	2027.8
20°	1284.2	1358.7	1437.6	1530.7	1606.8	1702.6	1781.5	1858.7	1944.1	2024.7	2088.7
22.5°	1262.7	1344.3	1427.9	1520.6	1620.8	1716.7	1807.8	1891.6	1977.0	2064.5	2142.1
25°	1235.5	1309.4	1408.5	1513.7	1613.4	1717.4	1822.0	1927.1	2019.1	2111.7	2184.0
27.5°	1189.1	1282.4	1374.7	1483.2	1593.9	1711.7	1823.5	1933.6	2030.0	2106.1	2150.9
30°	1165.4	1246.4	1346.6	1455.6	1575.6	1702.1	1818.7	1926.6	2016.4	2077.2	2095.2
32.5°	1130.4	1214.0	1312.0	1425.0	1551.9	1681.9	1803.4	1905.1	1980.1	2011.9	1990.1
35°	1078.3	1153.9	1253.0	1368.6	1500.6	1639.1	1759.0	1845.0	1883.3	1853.2	1778.2
37.5°	1015.9	1090.8	1190.3	1303.9	1440.4	1581.3	1689.7	1751.6	1738.8	1664.0	1552.1
40°	972.1	1042.2	1136.9	1259.6	1392.7	1533.9	1629.2	1662.6	1627.6	1520.3	1401.4
42.5°	923.4	991.8	1087.0	1205.2	1346.2	1476.5	1559.6	1562.3	1503.6	1375.2	1255.9
45°	849.4	914.6	1004.4	1127.6	1257.9	1380.6	1435.4	1408.5	1300.1	1176.3	1056.4
47.5°	776.3	832.8	921.4	1038.3	1162.1	1265.4	1292.5	1244.2	1128.7	1008.5	897.4
50°	722.9	779.8	863.1	974.8	1094.2	1183.4	1196.6	1132.5	1019.1	898.1	811.0
52.5°	671.6	728.2	808.3	911.7	1021.0	1101.5	1101.9	1027.8	914.9	807.0	726.0
55°	596.4	647.3	719.6	812.1	909.7	972.6	957.3	880.6	782.6	689.0	618.3
57.5°	523.9	568.2	634.9	712.0	797.9	849.9	824.4	750.6	663.1	583.7	530.1
60°	477.0	519.2	576.2	649.0	721.3	761.8	737.7	670.8	590.3	526.2	479.7
62.5°	431.4	467.0	521.8	585.0	652.0	682.1	660.6	594.6	525.1	467.1	429.4
65°	366.9	395.9	439.7	494.0	542.7	568.5	550.4	489.0	435.9	394.3	364.2
67.5°	306.7	329.4	362.5	406.0	447.4	461.4	444.9	402.2	357.2	323.8	302.6
70°	265.1	286.5	314.3	347.8	383.9	398.7	382.2	348.3	311.6	280.9	260.2
72.5°	228.7	245.3	268.8	297.4	325.7	340.4	329.2	296.6	265.6	242.8	225.1
75°	174.1	188.4	204.8	225.1	247.0	256.8	247.0	224.5	203.2	186.2	173.6
77.5°	126.6	134.3	146.9	162.1	175.8	183.3	174.8	159.5	146.6	134.9	128.7
80°	96.4	101.9	110.6	122.7	132.0	139.1	133.6	121.0	110.6	103.0	100.2
82.5°	70.1	73.8	79.5	88.5	94.7	98.4	95.9	86.8	82.5	75.8	73.0
85°	34.5	36.7	40.6	43.3	48.7	49.3	49.8	46.0	42.1	40.6	38.3
87.5°	12.7	13.5	15.2	17.0	19.0	19.7	19.6	19.9	18.4	18.1	16.6
90°	4.3	6.3	8.2	10.1	11.8	13.2	14.6	16.0	17.4	18.5	19.5
92.5°	10.1	10.1	10.3	10.4	11.2	12.5	13.9	15.4	16.8	17.8	18.9
95°	37.5	31.5	25.6	19.6	16.7	16.9	17.0	17.2	17.4	18.5	19.5
97.5°	96.1	99.8	103.5	107.3	99.3	79.7	60.1	40.5	20.9	21.0	21.1
100°	132.8	136.0	139.2	142.4	131.8	107.6	83.3	59.0	34.8	31.8	28.8
102.5°	173.8	176.1	178.4	180.7	180.3	177.1	174.0	170.8	167.6	135.4	103.2
105°	239.1	240.1	241.2	242.2	243.2	244.1	244.9	245.9	246.8	248.3	249.9
107.5°	300.4	301.0	301.4	302.0	302.9	304.0	305.2	306.4	307.6	308.4	309.2
110°	342.1	342.7	343.2	343.7	344.5	345.5	346.7	347.7	348.7	349.1	349.4





TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	383.1	384.0	385.0	386.0	386.7	387.1	387.6	388.1	388.6	388.6	388.5
115°	445.0	445.5	446.0	446.6	446.7	446.6	446.4	446.2	446.0	446.4	446.7
117.5°	501.3	502.0	502.7	503.4	503.9	504.3	504.7	505.1	505.5	505.4	505.3
120°	539.2	540.0	540.7	541.4	541.6	541.5	541.3	541.1	540.9	541.3	541.6
122.5°	574.4	574.8	575.2	575.7	576.0	576.2	576.5	576.7	576.9	577.2	577.4
125°	625.4	626.1	626.9	627.6	627.7	627.4	627.0	626.7	626.3	626.9	627.4
127.5°	673.0	673.2	673.4	673.5	674.0	674.9	675.7	676.4	677.2	677.2	677.1
130°	704.0	704.2	704.3	704.5	704.9	705.4	705.9	706.5	707.0	707.2	707.3
132.5°	732.6	732.9	733.2	733.6	734.0	734.7	735.4	736.0	736.7	736.9	737.0
135°	774.8	774.7	774.4	774.3	774.5	775.2	775.9	776.7	777.4	777.7	778.1
137.5°	812.9	812.9	813.0	813.1	813.5	814.3	815.1	815.8	816.6	817.0	817.4
140°	837.8	838.2	838.5	838.8	839.2	839.6	840.0	840.3	840.7	841.1	841.7
142.5°	860.2	860.9	861.5	862.1	862.5	862.8	863.0	863.2	863.4	863.8	864.2
145°	894.1	894.7	895.2	895.7	896.0	896.0	896.0	896.0	896.0	896.2	896.4
147.5°	921.6	922.7	923.6	924.6	925.0	924.8	924.6	924.5	924.3	924.5	924.6
150°	941.0	941.7	942.4	943.1	943.3	943.2	943.0	942.9	942.6	942.6	942.6
152.5°	957.3	957.8	958.4	958.9	959.1	958.8	958.5	958.1	957.8	958.1	958.4
155°	980.0	980.2	980.3	980.5	980.3	979.9	979.3	978.7	978.3	978.9	979.6
157.5°	999.2	999.0	998.9	998.9	998.5	997.9	997.3	996.7	996.1	997.0	997.9
160°	1010.1	1009.6	1009.1	1008.5	1008.2	1008.1	1007.8	1007.7	1007.5	1008.5	1009.6
162.5°	1020.1	1019.5	1018.7	1018.1	1017.7	1017.5	1017.3	1017.2	1017.0	1018.0	1019.1
165°	1032.7	1031.8	1030.9	1030.1	1029.6	1029.6	1029.6	1029.6	1029.6	1031.0	1032.5
167.5°	1042.8	1041.9	1041.0	1040.1	1039.6	1039.4	1039.3	1039.3	1039.1	1040.7	1042.2
170°	1048.4	1047.3	1046.2	1045.2	1044.7	1044.9	1045.1	1045.3	1045.4	1046.9	1048.3
172.5°	1052.2	1051.1	1050.0	1049.0	1048.5	1048.7	1048.9	1049.1	1049.2	1050.7	1052.1
175°	1056.3	1055.2	1054.2	1053.1	1052.7	1052.8	1053.0	1053.2	1053.4	1054.9	1056.5
177.5°	1058.2	1057.2	1056.3	1055.3	1054.9	1055.2	1055.5	1055.7	1056.1	1057.2	1058.3
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0
2.5°	1393.4	1394.3	1398.2	1401.3	1402.2	1406.6	1407.0
5°	1515.8	1525.2	1543.3	1544.9	1547.6	1561.9	1550.9
7.5°	1659.4	1683.0	1698.8	1712.7	1717.8	1723.9	1722.7
10°	1751.4	1786.4	1804.0	1831.8	1833.0	1840.1	1835.7
12.5°	1843.8	1884.5	1916.5	1921.7	1945.1	1948.7	1954.9
15°	1974.8	2018.1	2062.4	2078.3	2110.6	2118.3	2130.3
17.5°	2097.9	2142.1	2173.3	2214.3	2227.6	2245.4	2233.2
20°	2165.4	2213.6	2253.0	2285.3	2299.0	2308.8	2307.8
22.5°	2206.1	2254.7	2286.7	2311.1	2323.9	2328.1	2327.9
25°	2231.7	2259.5	2269.4	2278.7	2264.5	2259.5	2261.8
27.5°	2160.7	2153.5	2127.7	2094.0	2058.9	2031.1	2015.9
30°	2063.0	2020.2	1981.3	1913.4	1878.4	1857.6	1839.0
32.5°	1924.5	1856.8	1782.0	1719.8	1680.0	1649.1	1644.5
35°	1687.3	1585.4	1494.0	1417.8	1378.4	1345.0	1337.4
37.5°	1434.5	1328.6	1246.3	1179.3	1136.9	1113.3	1091.3
40°	1266.7	1175.8	1094.7	1037.8	1005.4	988.5	974.8
42.5°	1137.4	1054.4	973.8	930.4	901.2	890.8	882.8
45°	958.9	881.7	825.9	793.0	776.0	758.5	750.3
47.5°	815.9	753.1	716.3	688.4	670.2	659.8	654.5
50°	734.9	683.4	650.6	629.2	612.8	604.6	600.2
52.5°	663.1	620.8	593.2	576.2	565.1	559.0	557.3
55°	571.2	538.8	521.3	506.6	498.4	492.9	490.7
57.5°	496.5	471.7	457.4	445.2	442.0	437.4	435.9
60°	447.4	428.3	416.2	408.0	405.3	399.8	400.8
62.5°	404.0	388.4	378.1	373.4	369.8	365.2	366.7
65°	341.7	330.3	324.7	320.4	316.0	313.2	315.4
67.5°	286.8	278.8	271.4	268.9	266.7	266.3	264.0
70°	250.8	244.2	237.7	236.1	236.1	233.9	233.3
72.5°	216.2	211.4	207.0	205.8	204.1	204.9	202.6
75°	167.0	163.2	161.5	159.9	159.4	159.4	157.7
77.5°	123.4	120.6	118.0	118.0	116.0	115.3	115.0
80°	93.6	92.5	90.4	90.4	89.3	89.8	88.7
82.5°	70.4	68.9	68.4	67.6	66.1	66.1	65.0
85°	37.8	36.1	35.6	34.0	32.9	34.0	32.9
87.5°	17.3	17.0	16.7	15.9	15.5	15.6	14.4
90°	20.6	21.6	22.3	22.7	23.1	23.4	23.7
92.5°	20.0	21.0	21.5	21.6	21.7	21.8	21.9
95°	20.6	21.6	22.3	22.4	22.6	22.7	22.9
97.5°	21.2	21.3	21.5	21.6	21.8	21.9	22.2
100°	25.8	22.8	21.5	21.6	21.8	21.9	22.2
102.5°	71.0	38.7	22.7	22.7	22.7	22.7	22.8
105°	251.4	253.0	250.7	244.4	238.1	231.7	225.4
107.5°	310.0	310.7	311.4	312.1	312.8	313.5	314.1
110°	349.8	350.1	350.6	351.1	351.6	352.2	352.7



TEST NUMBER: P332652-927

CATALOG NUMBER: SA4XXDIP-C1020D1035U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	388.4	388.3	388.6	389.3	390.0	390.6	391.3
115°	447.1	447.4	447.6	447.6	447.6	447.6	447.6
117.5°	505.3	505.2	505.2	505.1	505.0	504.9	504.9
120°	541.9	542.3	542.3	541.9	541.6	541.3	540.9
122.5°	577.6	577.8	577.7	577.4	577.0	576.7	576.3
125°	627.9	628.4	628.8	629.0	629.2	629.3	629.5
127.5°	676.9	676.8	676.7	676.6	676.4	676.3	676.1
130°	707.5	707.7	707.8	707.8	707.8	707.8	707.8
132.5°	737.3	737.4	737.4	737.3	737.1	737.0	736.9
135°	778.4	778.8	779.1	779.5	779.8	780.1	780.5
137.5°	817.8	818.2	818.2	818.2	818.1	817.9	817.8
140°	842.2	842.7	843.1	843.3	843.4	843.6	843.8
142.5°	864.6	865.0	865.1	865.2	865.2	865.3	865.3
145°	896.5	896.7	897.0	897.3	897.6	898.0	898.3
147.5°	924.7	924.9	925.0	925.2	925.3	925.6	925.7
150°	942.6	942.6	942.7	942.9	943.1	943.3	943.4
152.5°	958.7	958.9	959.0	958.9	958.9	958.7	958.6
155°	980.3	981.0	981.1	980.6	980.1	979.5	979.1
157.5°	998.9	999.7	999.7	998.9	997.9	997.0	996.1
160°	1010.7	1011.7	1011.7	1010.7	1009.6	1008.5	1007.5
162.5°	1020.2	1021.2	1021.1	1019.9	1018.7	1017.6	1016.4
165°	1033.9	1035.2	1035.1	1033.6	1032.0	1030.4	1028.8
167.5°	1043.8	1045.3	1045.2	1043.5	1041.7	1039.9	1038.2
170°	1049.6	1051.1	1050.9	1049.2	1047.4	1045.6	1043.9
172.5°	1053.4	1054.9	1054.6	1052.7	1050.8	1048.9	1047.0
175°	1058.1	1059.7	1059.4	1057.3	1055.2	1053.1	1051.0
177.5°	1059.4	1060.6	1060.3	1058.6	1056.9	1055.2	1053.5
180°	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3	1057.3

(END OF REPORT)