

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332978

Luminaire Tested: **SA4XXRDIP-C1020D1035U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332978
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D1035U835-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7870.3 lumens
Efficiency: N/A
Efficacy: 130.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332978
CATALOG NUMBER: SA4XXRDIP-C1020D1035U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332978

CATALOG NUMBER: SA4XXRDIP-C1020D1035U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	87	91	88	84	82	75	73	70	63	62	60	53	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	76	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14577	14577	14577
5°	14610	14431	14521
10°	14519	14258	14258
15°	14352	13959	13855
20°	14123	13564	13315
25°	13831	13104	12772
30°	13546	12618	12089
35°	13231	12113	11404
40°	12852	11540	10666
45°	12501	10970	9913
50°	12103	10315	9117
55°	11676	9633	8251
60°	11207	8885	7367
65°	10776	7950	6497
70°	10150	6918	5516
75°	9357	5736	4485
80°	8164	4370	4114
85°	6919	3974	3714



TEST NUMBER: P332978

CATALOG NUMBER: SA4XXRDIP-C1020D1035U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.6	2.2
10°-20°	473.0	6.0
20°-30°	683.0	8.7
30°-40°	774.2	9.8
40°-50°	747.6	9.5
50°-60°	621.7	7.9
60°-70°	429.3	5.5
70°-80°	217.6	2.8
80°-90°	58.6	0.7
90°-100°	367.0	4.7
100°-110°	763.9	9.7
110°-120°	684.2	8.7
120°-130°	575.5	7.3
130°-140°	479.9	6.1
140°-150°	366.6	4.7
150°-160°	257.7	3.3
160°-170°	151.6	1.9
170°-180°	49.3	0.6
0°-30°	1325.6	16.8
0°-40°	2099.9	26.7
0°-60°	3469.2	44.1
0°-90°	4174.7	53.0
90°-120°	1815.1	23.1
90°-150°	3237.1	41.1
90°-180°	3696.0	47.0
0°-180°	7870.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1806	1806	1806	1806	1806	
5°	1803	1797	1781	1794	1792	171
15°	1717	1704	1670	1667	1658	484
25°	1553	1526	1471	1448	1434	715
35°	1342	1297	1229	1183	1157	839
45°	1095	1042	961	896	868	844
55°	830	772	684	615	586	742
65°	564	503	416	359	340	557
75°	300	248	184	153	144	317
85°	75	48	43	40	40	84
90°	1	8	18	20	21	5
95°	33	104	814	403	244	37
105°	117	169	655	1410	1405	125
115°	206	258	584	1122	1349	204
125°	286	340	581	955	1076	255
135°	340	405	576	848	962	263
145°	392	449	573	715	786	246
155°	446	482	557	631	658	206
165°	486	501	534	566	574	137
175°	507	508	512	519	517	48
180°	508	508	508	508	508	



TEST NUMBER: P332978

CATALOG NUMBER: SA4XXRDIP-C1020D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1810.1	1809.1	1808.1	1807.2	1806.2	1804.3	1801.6	1798.9	1796.2	1793.5	1796.2
5°	1802.9	1801.7	1800.5	1799.2	1798.0	1795.5	1791.9	1788.2	1784.5	1780.8	1783.9
7.5°	1786.6	1785.3	1784.0	1782.7	1781.4	1778.4	1773.6	1768.8	1764.0	1759.2	1761.2
10°	1771.1	1769.6	1768.0	1766.5	1765.0	1761.4	1755.9	1750.4	1744.8	1739.3	1740.5
12.5°	1751.2	1749.4	1747.6	1745.9	1744.1	1739.9	1733.4	1726.9	1720.4	1713.9	1714.6
15°	1717.2	1714.4	1711.7	1708.9	1706.1	1700.9	1693.2	1685.5	1677.9	1670.2	1669.6
17.5°	1676.0	1672.0	1668.0	1664.0	1660.0	1653.4	1644.2	1635.0	1625.8	1616.5	1614.8
20°	1643.9	1639.9	1635.9	1631.9	1627.9	1620.7	1610.3	1599.8	1589.4	1578.9	1576.5
22.5°	1608.5	1604.0	1599.5	1595.1	1590.6	1582.7	1571.6	1560.4	1549.2	1538.0	1534.3
25°	1552.7	1547.1	1541.6	1536.1	1530.5	1521.5	1508.9	1496.3	1483.7	1471.1	1465.9
27.5°	1494.0	1487.1	1480.2	1473.2	1466.3	1456.1	1442.6	1429.2	1415.7	1402.2	1395.8
30°	1453.1	1445.4	1437.8	1430.1	1422.4	1411.3	1396.9	1382.4	1368.0	1353.6	1345.9
32.5°	1410.0	1401.3	1392.6	1384.0	1375.3	1363.5	1348.6	1333.7	1318.7	1303.8	1294.9
35°	1342.5	1332.7	1322.8	1313.0	1303.2	1290.6	1275.2	1259.9	1244.5	1229.1	1218.7
37.5°	1270.3	1260.2	1250.1	1239.9	1229.8	1216.2	1199.2	1182.2	1165.1	1148.1	1136.4
40°	1219.5	1209.3	1199.2	1189.0	1178.9	1165.1	1147.6	1130.0	1112.5	1095.0	1082.1
42.5°	1170.8	1160.2	1149.5	1138.9	1128.3	1113.8	1095.6	1077.3	1059.1	1040.8	1027.7
45°	1095.0	1083.7	1072.3	1060.9	1049.5	1034.6	1016.2	997.8	979.3	960.9	945.9
47.5°	1016.8	1005.0	993.3	981.6	969.8	954.4	935.2	916.0	896.8	877.7	862.1
50°	963.7	951.7	939.7	927.7	915.7	899.9	880.3	860.6	840.9	821.3	805.9
52.5°	909.5	897.7	886.0	874.3	862.5	846.6	826.4	806.3	786.1	766.0	750.4
55°	829.6	817.3	805.0	792.7	780.4	764.3	744.3	724.3	704.4	684.4	668.4
57.5°	750.5	737.7	724.9	712.1	699.4	683.1	663.5	643.8	624.1	604.5	588.3
60°	694.1	681.8	669.5	657.2	644.9	628.9	609.3	589.6	569.9	550.3	534.3
62.5°	643.2	630.4	617.6	604.8	592.1	575.6	555.4	535.3	515.1	495.0	480.2
65°	564.1	550.9	537.7	524.5	511.3	494.8	475.2	455.5	435.8	416.2	403.0
67.5°	482.0	469.3	456.7	444.0	431.3	415.9	397.6	379.4	361.1	342.9	331.5
70°	430.0	417.1	404.2	391.3	378.4	363.2	345.7	328.1	310.6	293.1	283.0
72.5°	374.7	363.0	351.3	339.7	328.0	313.9	297.4	280.8	264.3	247.8	239.1
75°	300.0	288.7	277.3	265.9	254.6	241.6	227.2	212.8	198.3	183.9	176.8
77.5°	224.3	214.6	205.0	195.3	185.7	175.0	163.3	151.7	140.0	128.3	124.2
80°	175.6	166.7	157.8	148.9	140.0	130.9	121.7	112.5	103.2	94.0	93.1
82.5°	133.6	125.4	117.2	109.0	100.9	94.1	88.9	83.6	78.3	73.0	72.3
85°	74.7	68.5	62.4	56.2	50.1	46.5	45.6	44.7	43.8	42.9	42.2
87.5°	25.6	24.1	22.7	20.9	19.2	18.1	19.0	18.8	18.9	19.1	18.6
90°	1.0	3.0	6.0	7.0	8.0	8.0	14.0	14.0	16.0	18.0	17.0
92.5°	11.4	16.6	26.0	38.1	52.7	73.5	124.2	201.7	277.1	316.7	263.8
95°	32.9	35.9	45.9	58.9	82.9	124.8	211.6	375.4	614.0	813.6	836.6
97.5°	59.1	59.1	67.7	79.7	100.2	135.4	202.3	337.4	574.6	856.9	1051.0
100°	75.9	75.9	82.9	94.8	113.8	145.8	204.7	317.5	521.1	802.6	1058.2
102.5°	91.8	93.4	99.6	110.8	129.0	159.3	212.6	311.9	485.2	734.8	998.3
105°	116.8	119.8	124.8	136.8	154.7	183.7	231.6	314.5	454.2	654.9	889.5
107.5°	144.4	146.4	151.3	164.1	181.3	209.8	253.8	329.2	448.6	610.2	801.6
110°	162.7	164.7	169.7	181.7	199.7	226.6	270.5	340.4	450.2	595.0	757.7



TEST NUMBER: P332978

CATALOG NUMBER: SA4XXRDIP-C1020D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	180.3	182.3	188.1	199.3	217.2	244.2	286.5	352.4	455.0	587.8	733.0
115°	205.7	208.6	215.6	225.6	244.6	271.5	311.5	371.4	464.2	584.0	709.8
117.5°	232.0	234.8	241.0	252.0	269.7	297.7	335.6	390.7	474.0	583.0	699.4
120°	249.6	251.6	258.6	269.5	286.5	314.5	352.4	404.3	481.2	583.0	693.8
122.5°	265.6	267.5	274.5	284.7	303.3	330.4	368.4	417.1	488.4	582.2	687.4
125°	286.5	290.5	296.5	307.5	326.4	354.4	390.3	436.3	499.2	581.0	676.9
127.5°	305.1	308.3	315.5	328.0	347.8	376.0	410.7	452.8	507.7	578.8	662.7
130°	315.5	319.5	327.4	342.4	361.4	390.3	424.3	463.2	514.1	578.0	653.9
132.5°	325.8	329.0	339.4	353.6	374.2	401.5	435.5	473.6	519.7	577.2	645.9
135°	340.4	344.4	354.4	371.4	392.3	418.3	451.2	487.2	528.1	576.0	633.9
137.5°	355.0	358.8	369.8	385.9	407.7	432.5	463.2	496.8	533.1	575.8	623.5
140°	365.4	368.4	379.4	396.3	417.3	441.3	471.2	503.1	537.1	575.0	618.0
142.5°	376.6	379.6	389.7	405.9	426.1	449.2	478.4	507.9	540.3	575.0	613.2
145°	392.3	395.3	405.3	419.3	438.3	460.2	486.2	513.1	542.1	573.0	605.0
147.5°	410.1	411.1	419.9	434.3	450.0	469.8	494.2	517.7	543.1	569.4	597.6
150°	421.3	422.3	430.3	442.3	457.2	476.2	498.2	520.1	543.1	567.0	592.0
152.5°	431.7	431.9	439.9	451.0	464.4	481.8	501.4	521.7	541.5	563.0	585.6
155°	446.2	447.2	453.2	463.2	474.2	489.2	506.1	523.1	539.1	557.1	576.0
157.5°	460.4	460.4	466.0	473.8	483.4	495.2	509.5	523.1	536.5	550.9	566.2
160°	469.2	469.2	473.2	480.2	488.2	499.2	511.1	523.1	534.1	546.1	559.1
162.5°	477.2	476.4	479.6	485.8	493.0	501.6	512.7	523.1	531.7	541.3	552.7
165°	486.2	486.2	488.2	493.2	498.2	504.1	513.1	521.1	527.1	534.1	542.1
167.5°	495.2	494.2	495.2	499.0	501.8	506.3	512.9	518.7	522.3	526.9	532.5
170°	499.2	498.2	499.2	502.2	504.1	507.1	512.1	517.1	519.1	522.1	526.1
172.5°	503.1	502.2	502.3	504.5	505.7	507.9	511.3	515.5	515.9	517.3	520.5
175°	507.1	506.1	506.1	507.1	508.1	508.1	510.1	513.1	512.1	512.1	514.1
177.5°	508.9	508.1	507.3	508.1	508.1	508.1	508.9	510.5	508.9	508.9	509.7
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1



TEST NUMBER: P332978

CATALOG NUMBER: SA4XXRDIP-C1020D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1798.9	1801.6	1804.3	1805.6	1805.3	1805.1	1804.8	1804.6
5°	1786.9	1790.0	1793.1	1794.3	1793.7	1793.1	1792.5	1791.9
7.5°	1763.2	1765.1	1767.1	1767.6	1766.6	1765.6	1764.6	1763.6
10°	1741.8	1743.0	1744.2	1744.2	1743.0	1741.8	1740.5	1739.3
12.5°	1715.3	1716.1	1716.8	1716.3	1714.6	1712.9	1711.2	1709.5
15°	1669.0	1668.3	1667.7	1666.3	1664.2	1662.0	1659.9	1657.7
17.5°	1613.1	1611.4	1609.7	1607.2	1603.9	1600.7	1597.4	1594.1
20°	1574.0	1571.6	1569.1	1565.9	1561.9	1557.9	1553.9	1549.9
22.5°	1530.6	1526.9	1523.3	1519.8	1516.5	1513.3	1510.0	1506.8
25°	1460.6	1455.4	1450.2	1446.0	1443.0	1439.9	1436.8	1433.8
27.5°	1389.3	1382.9	1376.4	1371.0	1366.6	1362.1	1357.7	1353.3
30°	1338.2	1330.5	1322.8	1316.5	1311.6	1306.7	1301.8	1296.9
32.5°	1286.0	1277.1	1268.2	1261.4	1256.7	1252.0	1247.4	1242.7
35°	1208.2	1197.8	1187.3	1179.4	1173.8	1168.3	1162.8	1157.2
37.5°	1124.8	1113.1	1101.4	1092.8	1087.3	1081.7	1076.2	1070.7
40°	1069.2	1056.3	1043.4	1034.2	1028.7	1023.1	1017.6	1012.1
42.5°	1014.5	1001.4	988.2	978.8	973.0	967.2	961.4	955.7
45°	930.8	915.7	900.7	890.4	884.9	879.3	873.8	868.3
47.5°	846.5	830.9	815.2	804.4	798.3	792.2	786.1	780.1
50°	790.5	775.2	759.8	749.2	743.4	737.5	731.7	725.9
52.5°	734.7	719.1	703.5	692.7	686.6	680.5	674.4	668.4
55°	652.4	636.5	620.5	609.6	603.7	597.9	592.1	586.2
57.5°	572.0	555.8	539.6	529.3	524.8	520.4	516.0	511.6
60°	518.3	502.3	486.4	475.9	471.0	466.1	461.2	456.3
62.5°	465.5	450.7	436.0	426.6	422.7	418.8	414.8	410.9
65°	389.7	376.5	363.3	354.9	351.2	347.5	343.8	340.1
67.5°	320.1	308.8	297.4	289.7	285.6	281.6	277.5	273.5
70°	272.8	262.7	252.6	245.9	242.9	239.8	236.7	233.7
72.5°	230.4	221.8	213.1	207.4	204.5	201.7	198.9	196.1
75°	169.8	162.7	155.6	151.2	149.3	147.5	145.6	143.8
77.5°	120.1	116.0	111.8	109.5	108.9	108.4	107.8	107.3
80°	92.2	91.3	90.3	89.7	89.4	89.1	88.8	88.5
82.5°	71.6	71.0	70.3	69.8	69.5	69.2	68.9	68.6
85°	41.6	41.0	40.4	40.1	40.1	40.1	40.1	40.1
87.5°	18.6	18.5	18.5	18.5	18.9	19.4	19.4	19.7
90°	18.0	19.0	20.0	20.0	21.0	22.0	21.0	21.0
92.5°	196.1	147.6	117.4	97.4	85.7	80.3	76.9	76.9
95°	739.7	585.0	451.2	354.4	305.5	274.5	256.6	243.6
97.5°	1093.0	1035.4	937.8	833.6	761.9	701.8	671.9	651.1
100°	1204.0	1223.9	1175.0	1101.1	1014.3	953.4	923.4	915.5
102.5°	1198.4	1297.4	1311.6	1280.8	1227.5	1183.4	1151.9	1145.5
105°	1118.1	1290.8	1389.6	1430.6	1432.6	1424.6	1410.6	1404.6
107.5°	1004.1	1188.0	1327.2	1416.2	1465.5	1488.3	1498.3	1500.9
110°	935.4	1108.1	1252.9	1362.7	1433.6	1475.5	1493.5	1502.5



TEST NUMBER: P332978

CATALOG NUMBER: SA4XXRDIP-C1020D1035U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	885.1	1037.8	1174.6	1284.4	1364.9	1415.6	1440.8	1455.3
115°	834.6	957.4	1074.2	1170.0	1248.9	1308.8	1340.7	1348.7
117.5°	809.8	911.5	1003.3	1084.6	1151.9	1202.2	1234.5	1240.7
120°	798.6	891.5	971.4	1042.2	1099.1	1143.1	1169.0	1180.0
122.5°	789.1	878.7	951.4	1013.5	1061.6	1099.1	1121.1	1132.1
125°	772.7	858.5	927.4	982.3	1022.3	1051.2	1070.2	1076.2
127.5°	752.7	834.8	903.5	955.6	995.7	1021.5	1037.4	1043.4
130°	736.8	815.6	883.5	936.4	977.3	1002.3	1018.3	1024.3
132.5°	720.0	794.1	860.3	913.3	953.4	981.5	996.7	1002.7
135°	696.8	761.7	822.6	872.5	912.5	940.4	956.4	962.4
137.5°	675.9	730.8	782.1	827.2	864.5	892.1	905.3	912.5
140°	663.9	710.8	755.7	797.6	832.6	854.6	868.5	876.5
142.5°	652.7	694.0	732.6	768.9	799.8	820.2	832.6	838.2
145°	636.9	670.9	700.8	728.8	753.7	770.7	780.7	785.7
147.5°	623.9	650.9	674.9	696.8	715.2	729.8	737.4	739.1
150°	616.0	638.9	658.9	676.9	692.8	705.8	711.8	712.8
152.5°	607.2	626.9	645.3	660.1	673.7	684.2	687.8	688.8
155°	594.0	610.0	624.9	636.9	646.9	654.9	657.9	657.9
157.5°	579.8	593.2	605.8	615.4	622.9	628.9	630.7	630.7
160°	571.0	582.0	593.0	601.0	607.0	613.0	614.0	614.0
162.5°	562.2	571.6	580.2	587.4	591.8	597.8	598.8	598.0
165°	550.1	556.1	563.0	568.0	572.0	576.0	575.0	574.0
167.5°	538.3	542.9	548.5	551.5	553.5	556.1	555.9	555.1
170°	531.1	534.1	538.1	541.1	543.1	544.1	543.1	543.1
172.5°	524.7	526.9	529.3	531.5	532.7	533.7	532.7	531.1
175°	516.1	517.1	519.1	519.1	519.1	521.1	519.1	517.1
177.5°	510.5	511.3	511.3	512.1	511.3	512.1	510.5	508.9
180°	508.1	508.1	508.1	508.1	508.1	508.1	508.1	508.1

(END OF REPORT)