

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332633-927

Luminaire Tested: **SA4XXDIP-C1020D365U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332633-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-C1020D365U927-4F0-1E-UDD-F4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4544.9 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332633-927

CATALOG NUMBER: SA4XXDIP-C1020D365U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332633-927

CATALOG NUMBER: SA4XXDIP-C1020D365U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77				77
1	104	99	95	92	99	95	91	88	86	84	81	79	77	75	72	70	68				65	
2	95	87	80	75	90	83	77	72	76	71	67	69	65	62	63	60	58				54	
3	86	76	69	62	82	73	66	60	67	61	56	61	57	53	56	52	49				46	
4	79	68	59	53	75	65	57	51	60	53	48	55	49	45	50	46	42				39	
5	73	60	52	46	69	58	50	44	53	47	42	49	44	39	45	41	37				34	
6	67	54	46	40	64	52	44	39	48	42	37	44	39	35	41	36	33				30	
7	62	49	41	35	59	47	40	34	44	37	32	41	35	31	37	33	29				27	
8	58	45	37	31	55	43	36	30	40	34	29	37	32	27	34	30	26				24	
9	54	41	33	28	51	40	32	27	37	31	26	34	29	25	32	27	24				22	
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	21				20	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11035	11035	11035
5°	11068	10935	11015
10°	10999	10846	10900
15°	10866	10692	10719
20°	10689	10501	10510
25°	10488	10283	10253
30°	10241	10026	9934
35°	9984	9758	9629
40°	9720	9454	9280
45°	9442	9154	8978
50°	9134	8887	8611
55°	8802	8541	8263
60°	8472	8152	7905
65°	8097	7782	7469
70°	7678	7291	7006
75°	7037	6697	6525
80°	6267	6007	5858
85°	5483	5280	5169



TEST NUMBER: P332633-927

CATALOG NUMBER: SA4XXDIP-C1020D365U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.7	2.8
10°-20°	362.7	8.0
20°-30°	533.8	11.7
30°-40°	620.6	13.7
40°-50°	620.6	13.7
50°-60°	542.9	11.9
60°-70°	403.2	8.9
70°-80°	229.1	5.0
80°-90°	66.9	1.5
90°-100°	102.9	2.3
100°-110°	214.2	4.7
110°-120°	191.9	4.2
120°-130°	161.4	3.6
130°-140°	134.6	3.0
140°-150°	102.8	2.3
150°-160°	72.3	1.6
160°-170°	42.5	0.9
170°-180°	13.8	0.3
0°-30°	1025.2	22.6
0°-40°	1645.9	36.2
0°-60°	2809.4	61.8
0°-90°	3508.5	77.2
90°-120°	509.0	11.2
90°-150°	907.8	20.0
90°-180°	1036.0	22.8
0°-180°	4544.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1367	1367	1367	1367	1367	
5°	1366	1361	1349	1361	1359	129
15°	1300	1295	1279	1285	1282	366
25°	1177	1169	1154	1155	1151	541
35°	1013	1005	990	983	977	633
45°	827	819	802	790	786	637
55°	625	621	607	594	587	560
65°	424	418	407	397	391	420
75°	226	220	215	210	209	240
85°	59	59	57	57	56	65
90°	0	2	5	6	6	4
95°	9	29	228	113	68	10
105°	33	47	184	396	394	35
115°	58	72	164	315	378	57
125°	80	96	163	268	302	72
135°	96	114	162	238	270	74
145°	110	126	161	200	220	69
155°	125	135	156	177	184	58
165°	136	141	150	159	161	38
175°	142	142	144	146	145	13
180°	142	142	142	142	142	



TEST NUMBER: P332633-927

CATALOG NUMBER: SA4XXDIP-C1020D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1370.4	1369.8	1369.2	1368.7	1368.1	1366.7	1364.5	1362.4	1360.3	1358.1	1360.1
5°	1365.8	1364.9	1363.9	1362.9	1361.9	1360.1	1357.4	1354.7	1352.1	1349.4	1352.1
7.5°	1353.1	1352.1	1351.1	1350.2	1349.2	1347.3	1344.3	1341.3	1338.3	1335.4	1337.5
10°	1341.7	1340.8	1339.7	1338.8	1337.8	1335.8	1332.6	1329.4	1326.3	1323.1	1325.0
12.5°	1326.8	1325.9	1324.8	1323.9	1322.9	1320.7	1317.4	1314.1	1310.7	1307.3	1309.5
15°	1300.1	1299.1	1298.1	1297.2	1296.2	1293.9	1290.2	1286.6	1282.9	1279.3	1280.7
17.5°	1267.9	1266.7	1265.4	1264.2	1263.1	1260.7	1257.2	1253.8	1250.3	1246.9	1247.8
20°	1244.2	1243.0	1241.8	1240.6	1239.4	1236.9	1233.3	1229.6	1226.0	1222.3	1223.1
22.5°	1218.9	1217.2	1215.6	1214.0	1212.4	1209.7	1206.1	1202.5	1198.8	1195.2	1196.5
25°	1177.4	1175.8	1174.0	1172.3	1170.6	1168.1	1164.7	1161.3	1157.9	1154.4	1154.7
27.5°	1130.1	1128.4	1126.6	1124.8	1123.1	1120.6	1117.5	1114.3	1111.1	1107.9	1107.4
30°	1098.6	1096.6	1094.6	1092.7	1090.8	1088.2	1085.1	1081.9	1078.7	1075.5	1074.6
32.5°	1065.2	1063.5	1061.8	1060.0	1058.3	1055.7	1052.3	1049.0	1045.6	1042.3	1041.1
35°	1013.1	1011.5	1009.7	1008.1	1006.3	1003.8	1000.4	997.0	993.6	990.1	988.4
37.5°	958.1	956.6	955.1	953.5	951.9	949.4	945.6	942.0	938.3	934.7	932.9
40°	922.3	920.3	918.3	916.4	914.4	911.6	908.0	904.4	900.7	897.1	894.6
42.5°	883.7	882.5	881.3	880.2	879.0	876.4	872.4	868.3	864.3	860.2	857.4
45°	827.0	825.2	823.6	821.8	820.1	817.3	813.4	809.5	805.6	801.8	799.1
47.5°	767.5	766.4	765.2	764.1	762.9	760.5	756.9	753.3	749.7	746.1	743.1
50°	727.3	726.3	725.3	724.4	723.3	721.2	717.8	714.4	711.0	707.6	704.2
52.5°	687.9	686.7	685.5	684.4	683.2	680.8	677.2	673.6	669.9	666.4	663.4
55°	625.4	624.6	623.9	623.2	622.5	620.4	617.0	613.6	610.2	606.8	603.9
57.5°	565.9	565.0	564.2	563.3	562.5	560.4	557.1	553.7	550.3	547.0	544.2
60°	524.7	523.4	522.2	521.0	519.8	517.6	514.4	511.3	508.1	504.9	502.7
62.5°	484.3	483.3	482.3	481.3	480.2	478.1	474.7	471.3	467.9	464.6	462.6
65°	423.9	422.6	421.4	420.3	419.0	417.2	414.7	412.3	409.9	407.4	405.0
67.5°	363.0	361.9	360.8	359.7	358.5	356.8	354.4	352.1	349.7	347.5	345.1
70°	325.3	323.6	321.9	320.2	318.5	316.6	314.7	312.8	310.9	308.9	306.9
72.5°	285.0	283.3	281.6	279.9	278.2	276.6	275.0	273.5	271.9	270.3	268.8
75°	225.6	224.4	223.2	222.0	220.8	219.5	218.3	217.1	215.9	214.7	213.7
77.5°	168.9	168.3	167.8	167.3	166.8	166.0	164.9	163.8	162.7	161.7	161.4
80°	134.8	134.0	133.2	132.5	131.8	131.2	130.7	130.2	129.8	129.2	128.7
82.5°	101.4	101.1	100.8	100.4	100.1	99.8	99.7	99.7	99.6	99.4	99.2
85°	59.2	59.2	59.2	59.2	59.2	58.9	58.4	57.9	57.4	57.0	57.0
87.5°	22.8	22.7	22.7	22.6	22.4	22.3	22.4	22.2	22.1	22.0	21.9
90°	0.3	0.9	1.7	2.0	2.2	2.2	3.9	3.9	4.5	5.1	4.8
92.5°	3.2	4.7	7.3	10.7	14.8	20.6	34.9	56.6	77.7	88.8	74.0
95°	9.3	10.1	12.9	16.6	23.2	35.0	59.3	105.3	172.2	228.1	234.6
97.5°	16.6	16.6	19.0	22.3	28.1	37.9	56.7	94.7	161.1	240.3	294.8
100°	21.3	21.3	23.2	26.6	31.9	40.9	57.4	89.0	146.2	225.1	296.8
102.5°	25.7	26.2	28.0	31.1	36.2	44.7	59.7	87.5	136.1	206.0	280.0
105°	32.8	33.6	35.0	38.3	43.4	51.5	65.0	88.2	127.4	183.6	249.5
107.5°	40.5	41.0	42.5	46.0	50.9	58.9	71.1	92.4	125.8	171.1	224.8
110°	45.6	46.2	47.6	50.9	56.0	63.5	75.9	95.5	126.3	166.8	212.5



TEST NUMBER: P332633-927

CATALOG NUMBER: SA4XXDIP-C1020D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	50.5	51.1	52.8	55.8	60.9	68.4	80.3	98.9	127.6	164.9	205.6
115°	57.7	58.5	60.4	63.3	68.6	76.1	87.4	104.2	130.2	163.8	199.1
117.5°	65.0	65.8	67.6	70.7	75.7	83.5	94.1	109.6	132.9	163.5	196.1
120°	70.0	70.6	72.5	75.6	80.3	88.2	98.9	113.4	135.0	163.5	194.6
122.5°	74.5	75.0	77.0	79.9	85.1	92.7	103.3	117.0	137.0	163.3	192.8
125°	80.3	81.4	83.2	86.3	91.6	99.4	109.5	122.3	140.0	163.0	189.8
127.5°	85.6	86.4	88.5	92.0	97.5	105.4	115.2	127.0	142.4	162.3	185.8
130°	88.5	89.6	91.8	96.0	101.3	109.5	119.0	129.9	144.2	162.1	183.4
132.5°	91.4	92.3	95.2	99.2	105.0	112.6	122.2	132.8	145.8	161.9	181.2
135°	95.5	96.6	99.4	104.2	110.0	117.3	126.5	136.7	148.1	161.5	177.8
137.5°	99.6	100.6	103.7	108.2	114.3	121.3	129.9	139.3	149.5	161.5	174.9
140°	102.5	103.3	106.4	111.1	117.0	123.7	132.1	141.1	150.6	161.3	173.3
142.5°	105.6	106.5	109.3	113.8	119.5	126.0	134.2	142.4	151.5	161.3	172.0
145°	110.0	110.9	113.7	117.6	122.9	129.0	136.3	143.9	152.0	160.7	169.7
147.5°	115.0	115.3	117.8	121.8	126.2	131.7	138.6	145.2	152.3	159.7	167.6
150°	118.1	118.4	120.6	124.1	128.3	133.6	139.7	145.8	152.3	159.0	166.0
152.5°	121.0	121.1	123.3	126.5	130.2	135.1	140.6	146.3	151.9	157.9	164.2
155°	125.2	125.4	127.1	129.9	133.0	137.2	142.0	146.7	151.2	156.2	161.5
157.5°	129.1	129.1	130.7	132.8	135.5	138.9	142.9	146.7	150.4	154.5	158.8
160°	131.6	131.6	132.7	134.7	136.9	140.0	143.4	146.7	149.8	153.1	156.8
162.5°	133.8	133.6	134.5	136.3	138.2	140.7	143.8	146.7	149.1	151.8	155.0
165°	136.3	136.3	136.9	138.3	139.7	141.4	143.9	146.2	147.8	149.8	152.0
167.5°	138.9	138.6	138.9	139.9	140.7	142.0	143.9	145.4	146.5	147.7	149.3
170°	140.0	139.7	140.0	140.9	141.4	142.2	143.6	145.0	145.6	146.4	147.6
172.5°	141.1	140.9	140.9	141.5	141.8	142.4	143.4	144.6	144.7	145.0	146.0
175°	142.2	142.0	142.0	142.2	142.5	142.5	143.1	143.9	143.6	143.6	144.2
177.5°	142.8	142.5	142.3	142.5	142.5	142.5	142.8	143.1	142.8	142.8	143.0
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5



TEST NUMBER: P332633-927

CATALOG NUMBER: SA4XXDIP-C1020D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1362.0	1364.0	1366.0	1366.8	1366.6	1366.4	1366.2	1366.0
5°	1354.7	1357.4	1360.1	1361.2	1360.7	1360.2	1359.7	1359.2
7.5°	1339.7	1341.8	1343.9	1344.9	1344.6	1344.3	1343.9	1343.7
10°	1327.0	1329.0	1330.9	1331.6	1331.1	1330.6	1330.2	1329.7
12.5°	1311.6	1313.8	1315.9	1316.6	1316.0	1315.3	1314.5	1313.9
15°	1282.2	1283.7	1285.2	1285.5	1284.8	1284.0	1283.3	1282.5
17.5°	1248.7	1249.7	1250.5	1250.8	1250.3	1249.8	1249.4	1248.8
20°	1223.8	1224.6	1225.3	1225.3	1224.9	1224.4	1223.9	1223.4
22.5°	1197.8	1199.1	1200.4	1200.6	1199.8	1198.9	1198.0	1197.1
25°	1154.9	1155.2	1155.4	1155.0	1154.1	1153.1	1152.1	1151.1
27.5°	1106.8	1106.2	1105.6	1104.8	1103.5	1102.3	1101.1	1099.9
30°	1073.6	1072.6	1071.7	1070.6	1069.4	1068.1	1066.9	1065.7
32.5°	1039.9	1038.8	1037.6	1036.4	1035.1	1034.0	1032.8	1031.5
35°	986.7	985.0	983.3	981.8	980.6	979.5	978.2	977.0
37.5°	931.0	929.2	927.3	925.6	924.0	922.3	920.8	919.2
40°	892.2	889.7	887.3	885.5	884.2	883.0	881.9	880.6
42.5°	854.6	851.8	848.9	847.1	846.3	845.4	844.6	843.8
45°	796.4	793.7	791.0	789.3	788.6	787.9	787.1	786.4
47.5°	740.1	737.0	734.0	731.6	729.8	727.9	726.0	724.2
50°	700.8	697.4	694.0	691.5	690.0	688.6	687.1	685.6
52.5°	660.4	657.3	654.3	651.9	650.0	648.2	646.3	644.4
55°	600.9	598.0	595.1	592.9	591.4	590.0	588.5	587.1
57.5°	541.5	538.7	535.9	533.8	532.3	531.0	529.6	528.1
60°	500.6	498.4	496.1	494.5	493.2	492.0	490.8	489.6
62.5°	460.7	458.6	456.6	455.0	453.8	452.6	451.4	450.2
65°	402.6	400.1	397.7	395.9	394.7	393.5	392.2	391.0
67.5°	342.8	340.4	338.1	336.8	336.4	336.0	335.7	335.4
70°	305.0	303.0	301.1	299.8	299.0	298.3	297.5	296.8
72.5°	267.2	265.6	264.1	262.9	262.2	261.5	260.8	260.0
75°	212.7	211.8	210.8	210.2	209.9	209.7	209.5	209.2
77.5°	161.1	160.8	160.5	160.0	159.4	158.8	158.1	157.5
80°	128.3	127.8	127.3	126.9	126.7	126.4	126.2	126.0
82.5°	98.9	98.5	98.3	98.0	97.8	97.5	97.3	97.0
85°	57.0	57.0	57.0	56.8	56.6	56.3	56.1	55.8
87.5°	22.0	22.1	22.2	22.2	22.2	22.3	22.2	22.2
90°	5.1	5.3	5.6	5.6	5.9	6.2	5.9	5.9
92.5°	55.0	41.4	33.0	27.3	24.0	22.5	21.5	21.5
95°	207.5	164.1	126.5	99.4	85.6	77.0	71.9	68.3
97.5°	306.5	290.4	263.0	233.8	213.7	196.9	188.5	182.6
100°	337.6	343.3	329.5	308.8	284.5	267.4	259.0	256.7
102.5°	336.1	363.8	367.8	359.2	344.3	331.9	323.1	321.2
105°	313.5	362.0	389.8	401.2	401.8	399.5	395.6	394.0
107.5°	281.6	333.2	372.2	397.2	411.0	417.4	420.2	420.9
110°	262.4	310.8	351.4	382.1	402.0	413.8	418.8	421.4



TEST NUMBER: P332633-927

CATALOG NUMBER: SA4XXDIP-C1020D365U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	248.2	291.0	329.4	360.2	382.8	397.0	404.1	408.1
115°	234.1	268.5	301.3	328.1	350.2	367.0	376.0	378.3
117.5°	227.1	255.6	281.4	304.2	323.1	337.2	346.2	347.9
120°	223.9	250.0	272.4	292.3	308.2	320.6	327.9	331.0
122.5°	221.3	246.4	266.8	284.2	297.7	308.2	314.4	317.5
125°	216.7	240.7	260.1	275.5	286.7	294.9	300.2	301.8
127.5°	211.1	234.1	253.4	268.0	279.2	286.5	291.0	292.6
130°	206.6	228.8	247.8	262.6	274.1	281.1	285.6	287.2
132.5°	201.9	222.7	241.3	256.1	267.4	275.3	279.6	281.2
135°	195.4	213.7	230.7	244.7	255.9	263.7	268.2	269.9
137.5°	189.6	204.9	219.4	232.0	242.5	250.2	253.9	255.9
140°	186.2	199.3	211.9	223.7	233.5	239.6	243.6	245.8
142.5°	183.1	194.6	205.4	215.6	224.3	230.0	233.5	235.0
145°	178.6	188.1	196.5	204.4	211.4	216.1	219.0	220.3
147.5°	175.0	182.5	189.3	195.4	200.6	204.7	206.8	207.3
150°	172.8	179.2	184.8	189.8	194.3	198.0	199.6	199.9
152.5°	170.3	175.9	181.0	185.1	188.9	191.9	192.9	193.2
155°	166.6	171.0	175.2	178.6	181.4	183.6	184.5	184.5
157.5°	162.6	166.4	169.9	172.6	174.7	176.4	176.9	176.9
160°	160.2	163.2	166.3	168.6	170.2	171.9	172.2	172.2
162.5°	157.7	160.3	162.7	164.8	166.0	167.6	167.9	167.7
165°	154.2	156.0	157.9	159.3	160.4	161.5	161.3	161.0
167.5°	151.0	152.3	153.8	154.6	155.2	156.0	155.9	155.7
170°	148.9	149.8	150.9	151.8	152.3	152.6	152.3	152.3
172.5°	147.2	147.7	148.5	149.1	149.4	149.6	149.4	148.9
175°	144.7	145.0	145.6	145.6	145.6	146.2	145.6	145.0
177.5°	143.1	143.4	143.4	143.6	143.4	143.6	143.1	142.8
180°	142.5	142.5	142.5	142.5	142.5	142.5	142.5	142.5

(END OF REPORT)