

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332965

Luminaire Tested: **SA4XXRDIP-C1020D590U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332965
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D590U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6220.1 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332965
CATALOG NUMBER: SA4XXRDIP-C1020D590U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332965

CATALOG NUMBER: SA4XXRDIP-C1020D590U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	61	57				
2	93	86	80	74	88	81	76	71	72	68	64	64	61	58	57	54	52	49				
3	85	76	68	62	80	72	65	60	64	59	55	57	53	50	51	48	45	41				
4	78	67	59	53	73	64	57	51	57	51	47	51	47	43	45	42	39	36				
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31				
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	37	33	30	28				
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	25				
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	32	27	24	22				
9	53	41	33	28	50	39	32	27	36	30	26	32	27	24	29	25	22	20				
10	50	38	30	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14577	14577	14577
5°	14610	14431	14521
10°	14519	14258	14258
15°	14352	13959	13855
20°	14123	13564	13315
25°	13831	13104	12772
30°	13546	12618	12089
35°	13231	12113	11404
40°	12852	11540	10666
45°	12501	10970	9913
50°	12103	10315	9117
55°	11676	9633	8251
60°	11207	8885	7367
65°	10776	7950	6497
70°	10150	6918	5516
75°	9357	5736	4485
80°	8164	4370	4114
85°	6919	3974	3714



TEST NUMBER: P332965

CATALOG NUMBER: SA4XXRDIP-C1020D590U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.6	2.7
10°-20°	473.0	7.6
20°-30°	683.0	11.0
30°-40°	774.2	12.4
40°-50°	747.6	12.0
50°-60°	621.7	10.0
60°-70°	429.3	6.9
70°-80°	217.6	3.5
80°-90°	58.0	0.9
90°-100°	48.6	0.8
100°-110°	144.1	2.3
110°-120°	244.6	3.9
120°-130°	322.5	5.2
130°-140°	362.2	5.8
140°-150°	355.9	5.7
150°-160°	299.3	4.8
160°-170°	199.1	3.2
170°-180°	69.7	1.1
0°-30°	1325.6	21.3
0°-40°	2099.9	33.8
0°-60°	3469.2	55.8
0°-90°	4174.1	67.1
90°-120°	437.3	7.0
90°-150°	1477.8	23.8
90°-180°	2046.0	32.9
0°-180°	6220.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1806	1806	1806	1806	1806	
5°	1803	1797	1781	1794	1792	171
15°	1717	1704	1670	1667	1658	484
25°	1553	1526	1471	1448	1434	715
35°	1342	1297	1229	1183	1157	839
45°	1095	1042	961	896	868	844
55°	830	772	684	615	586	742
65°	564	503	416	359	340	557
75°	300	248	184	153	144	317
85°	75	48	43	40	40	84
90°	2	8	12	16	17	6
95°	34	39	43	45	45	38
105°	133	134	136	137	139	141
115°	249	249	248	247	246	245
125°	362	362	362	360	359	323
135°	467	470	470	469	468	361
145°	568	570	570	570	568	355
155°	650	650	650	652	650	299
165°	708	706	705	708	706	199
175°	736	734	733	736	733	70
180°	738	738	738	738	738	



TEST NUMBER: P332965

CATALOG NUMBER: SA4XXRDIP-C1020D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1810.1	1809.1	1808.1	1807.2	1806.2	1804.3	1801.6	1798.9	1796.2	1793.5	1796.2
5°	1802.9	1801.7	1800.5	1799.2	1798.0	1795.5	1791.9	1788.2	1784.5	1780.8	1783.9
7.5°	1786.6	1785.3	1784.0	1782.7	1781.4	1778.4	1773.6	1768.8	1764.0	1759.2	1761.2
10°	1771.1	1769.6	1768.0	1766.5	1765.0	1761.4	1755.9	1750.4	1744.8	1739.3	1740.5
12.5°	1751.2	1749.4	1747.6	1745.9	1744.1	1739.9	1733.4	1726.9	1720.4	1713.9	1714.6
15°	1717.2	1714.4	1711.7	1708.9	1706.1	1700.9	1693.2	1685.5	1677.9	1670.2	1669.6
17.5°	1676.0	1672.0	1668.0	1664.0	1660.0	1653.4	1644.2	1635.0	1625.8	1616.5	1614.8
20°	1643.9	1639.9	1635.9	1631.9	1627.9	1620.7	1610.3	1599.8	1589.4	1578.9	1576.5
22.5°	1608.5	1604.0	1599.5	1595.1	1590.6	1582.7	1571.6	1560.4	1549.2	1538.0	1534.3
25°	1552.7	1547.1	1541.6	1536.1	1530.5	1521.5	1508.9	1496.3	1483.7	1471.1	1465.9
27.5°	1494.0	1487.1	1480.2	1473.2	1466.3	1456.1	1442.6	1429.2	1415.7	1402.2	1395.8
30°	1453.1	1445.4	1437.8	1430.1	1422.4	1411.3	1396.9	1382.4	1368.0	1353.6	1345.9
32.5°	1410.0	1401.3	1392.6	1384.0	1375.3	1363.5	1348.6	1333.7	1318.7	1303.8	1294.9
35°	1342.5	1332.7	1322.8	1313.0	1303.2	1290.6	1275.2	1259.9	1244.5	1229.1	1218.7
37.5°	1270.3	1260.2	1250.1	1239.9	1229.8	1216.2	1199.2	1182.2	1165.1	1148.1	1136.4
40°	1219.5	1209.3	1199.2	1189.0	1178.9	1165.1	1147.6	1130.0	1112.5	1095.0	1082.1
42.5°	1170.8	1160.2	1149.5	1138.9	1128.3	1113.8	1095.6	1077.3	1059.1	1040.8	1027.7
45°	1095.0	1083.7	1072.3	1060.9	1049.5	1034.6	1016.2	997.8	979.3	960.9	945.9
47.5°	1016.8	1005.0	993.3	981.6	969.8	954.4	935.2	916.0	896.8	877.7	862.1
50°	963.7	951.7	939.7	927.7	915.7	899.9	880.3	860.6	840.9	821.3	805.9
52.5°	909.5	897.7	886.0	874.3	862.5	846.6	826.4	806.3	786.1	766.0	750.4
55°	829.6	817.3	805.0	792.7	780.4	764.3	744.3	724.3	704.4	684.4	668.4
57.5°	750.5	737.7	724.9	712.1	699.4	683.1	663.5	643.8	624.1	604.5	588.3
60°	694.1	681.8	669.5	657.2	644.9	628.9	609.3	589.6	569.9	550.3	534.3
62.5°	643.2	630.4	617.6	604.8	592.1	575.6	555.4	535.3	515.1	495.0	480.2
65°	564.1	550.9	537.7	524.5	511.3	494.8	475.2	455.5	435.8	416.2	403.0
67.5°	482.0	469.3	456.7	444.0	431.3	415.9	397.6	379.4	361.1	342.9	331.5
70°	430.0	417.1	404.2	391.3	378.4	363.2	345.7	328.1	310.6	293.1	283.0
72.5°	374.7	363.0	351.3	339.7	328.0	313.9	297.4	280.8	264.3	247.8	239.1
75°	300.0	288.7	277.3	265.9	254.6	241.6	227.2	212.8	198.3	183.9	176.8
77.5°	224.3	214.6	205.0	195.3	185.7	175.0	163.3	151.7	140.0	128.3	124.2
80°	175.6	166.7	157.8	148.9	140.0	130.9	121.7	112.5	103.2	94.0	93.1
82.5°	133.6	125.4	117.2	109.0	100.9	94.1	88.9	83.6	78.3	73.0	72.3
85°	74.7	68.5	62.4	56.2	50.1	46.5	45.6	44.7	43.8	42.9	42.2
87.5°	25.8	24.1	22.4	20.7	19.0	18.2	18.1	18.1	18.0	18.0	17.9
90°	1.7	3.1	4.5	5.9	7.3	8.5	9.5	10.5	11.5	12.5	13.3
92.5°	12.2	13.8	15.4	17.0	18.6	19.7	20.5	21.2	21.9	22.6	23.0
95°	34.2	35.4	36.5	37.6	38.8	39.8	40.7	41.6	42.5	43.3	43.7
97.5°	59.8	60.7	61.6	62.5	63.4	64.4	65.4	66.5	67.5	68.6	69.0
100°	79.8	80.4	80.9	81.4	81.9	82.7	83.8	85.0	86.1	87.3	87.5
102.5°	100.8	101.0	101.2	101.4	101.6	102.3	103.3	104.3	105.4	106.4	106.8
105°	132.9	133.0	133.1	133.3	133.4	133.7	134.2	134.7	135.2	135.7	136.1
107.5°	166.5	166.7	166.8	167.0	167.2	167.3	167.3	167.4	167.5	167.6	167.9
110°	189.4	189.6	189.9	190.1	190.4	190.4	190.3	190.2	190.1	189.9	189.7



TEST NUMBER: P332965

CATALOG NUMBER: SA4XXRDIP-C1020D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	213.1	213.1	213.2	213.2	213.3	213.2	213.0	212.7	212.5	212.3	212.2
115°	248.7	248.7	248.7	248.7	248.7	248.5	248.3	248.0	247.8	247.5	247.4
117.5°	282.2	282.3	282.4	282.5	282.6	282.6	282.4	282.2	282.0	281.9	281.4
120°	304.6	305.1	305.6	306.1	306.6	306.7	306.3	305.9	305.5	305.1	304.5
122.5°	327.8	328.0	328.2	328.4	328.6	328.7	328.5	328.3	328.1	328.0	327.5
125°	362.2	362.2	362.2	362.2	362.2	362.1	362.0	361.9	361.7	361.6	361.3
127.5°	393.3	393.7	394.1	394.5	394.8	394.9	394.7	394.5	394.3	394.1	393.9
130°	415.2	415.6	416.0	416.4	416.7	416.9	416.9	416.9	416.9	416.9	416.7
132.5°	437.6	437.9	438.1	438.4	438.7	438.8	438.7	438.6	438.5	438.4	438.1
135°	467.1	467.9	468.6	469.4	470.2	470.5	470.5	470.5	470.5	470.5	470.3
137.5°	499.3	499.6	500.0	500.3	500.7	501.0	501.2	501.4	501.6	501.8	501.5
140°	520.7	521.0	521.2	521.5	521.7	521.9	521.9	521.9	521.9	521.9	521.7
142.5°	540.3	540.6	540.9	541.1	541.4	541.4	541.3	541.2	541.1	541.0	541.0
145°	567.5	568.0	568.5	569.0	569.5	569.8	570.0	570.1	570.2	570.3	570.2
147.5°	594.4	595.0	595.6	596.2	596.9	597.1	597.0	596.9	596.8	596.7	596.6
150°	610.8	611.4	611.9	612.4	612.9	613.1	613.1	613.1	613.1	613.1	613.1
152.5°	626.4	626.7	627.0	627.3	627.6	627.8	627.9	628.0	628.1	628.2	628.5
155°	650.2	650.2	650.2	650.2	650.2	650.1	650.0	649.9	649.8	649.6	650.1
157.5°	670.3	670.0	669.8	669.6	669.4	669.2	669.2	669.2	669.2	669.1	669.5
160°	682.1	682.0	681.9	681.8	681.6	681.5	681.4	681.3	681.1	681.0	681.4
162.5°	693.1	692.8	692.4	692.1	691.8	691.5	691.4	691.3	691.2	691.0	691.7
165°	707.8	707.4	707.0	706.7	706.3	706.0	705.7	705.5	705.2	705.0	705.7
167.5°	719.1	718.6	718.0	717.5	717.0	716.7	716.7	716.8	716.8	716.8	717.6
170°	725.5	724.9	724.2	723.6	722.9	722.7	722.8	722.9	723.1	723.2	724.0
172.5°	730.0	729.5	729.0	728.5	727.9	727.7	727.7	727.7	727.7	727.8	728.6
175°	736.3	735.7	735.1	734.4	733.8	733.4	733.3	733.2	733.0	732.9	733.8
177.5°	738.4	737.9	737.4	736.9	736.3	736.1	736.1	736.1	736.1	736.1	736.8
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5



TEST NUMBER: P332965

CATALOG NUMBER: SA4XXRDIP-C1020D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1798.9	1801.6	1804.3	1805.6	1805.3	1805.1	1804.8	1804.6
5°	1786.9	1790.0	1793.1	1794.3	1793.7	1793.1	1792.5	1791.9
7.5°	1763.2	1765.1	1767.1	1767.6	1766.6	1765.6	1764.6	1763.6
10°	1741.8	1743.0	1744.2	1744.2	1743.0	1741.8	1740.5	1739.3
12.5°	1715.3	1716.1	1716.8	1716.3	1714.6	1712.9	1711.2	1709.5
15°	1669.0	1668.3	1667.7	1666.3	1664.2	1662.0	1659.9	1657.7
17.5°	1613.1	1611.4	1609.7	1607.2	1603.9	1600.7	1597.4	1594.1
20°	1574.0	1571.6	1569.1	1565.9	1561.9	1557.9	1553.9	1549.9
22.5°	1530.6	1526.9	1523.3	1519.8	1516.5	1513.3	1510.0	1506.8
25°	1460.6	1455.4	1450.2	1446.0	1443.0	1439.9	1436.8	1433.8
27.5°	1389.3	1382.9	1376.4	1371.0	1366.6	1362.1	1357.7	1353.3
30°	1338.2	1330.5	1322.8	1316.5	1311.6	1306.7	1301.8	1296.9
32.5°	1286.0	1277.1	1268.2	1261.4	1256.7	1252.0	1247.4	1242.7
35°	1208.2	1197.8	1187.3	1179.4	1173.8	1168.3	1162.8	1157.2
37.5°	1124.8	1113.1	1101.4	1092.8	1087.3	1081.7	1076.2	1070.7
40°	1069.2	1056.3	1043.4	1034.2	1028.7	1023.1	1017.6	1012.1
42.5°	1014.5	1001.4	988.2	978.8	973.0	967.2	961.4	955.7
45°	930.8	915.7	900.7	890.4	884.9	879.3	873.8	868.3
47.5°	846.5	830.9	815.2	804.4	798.3	792.2	786.1	780.1
50°	790.5	775.2	759.8	749.2	743.4	737.5	731.7	725.9
52.5°	734.7	719.1	703.5	692.7	686.6	680.5	674.4	668.4
55°	652.4	636.5	620.5	609.6	603.7	597.9	592.1	586.2
57.5°	572.0	555.8	539.6	529.3	524.8	520.4	516.0	511.6
60°	518.3	502.3	486.4	475.9	471.0	466.1	461.2	456.3
62.5°	465.5	450.7	436.0	426.6	422.7	418.8	414.8	410.9
65°	389.7	376.5	363.3	354.9	351.2	347.5	343.8	340.1
67.5°	320.1	308.8	297.4	289.7	285.6	281.6	277.5	273.5
70°	272.8	262.7	252.6	245.9	242.9	239.8	236.7	233.7
72.5°	230.4	221.8	213.1	207.4	204.5	201.7	198.9	196.1
75°	169.8	162.7	155.6	151.2	149.3	147.5	145.6	143.8
77.5°	120.1	116.0	111.8	109.5	108.9	108.4	107.8	107.3
80°	92.2	91.3	90.3	89.7	89.4	89.1	88.8	88.5
82.5°	71.6	71.0	70.3	69.8	69.5	69.2	68.9	68.6
85°	41.6	41.0	40.4	40.1	40.1	40.1	40.1	40.1
87.5°	17.8	17.7	17.6	17.7	18.0	18.3	18.6	18.9
90°	14.1	14.8	15.6	16.1	16.4	16.6	16.9	17.1
92.5°	23.5	24.0	24.4	24.7	24.9	25.0	25.2	25.3
95°	44.1	44.5	44.9	45.1	45.1	45.1	45.1	45.1
97.5°	69.5	69.9	70.4	70.6	70.6	70.6	70.6	70.6
100°	87.8	88.0	88.3	88.4	88.4	88.4	88.4	88.4
102.5°	107.1	107.5	107.8	108.1	108.2	108.3	108.4	108.5
105°	136.5	136.9	137.3	137.6	138.0	138.4	138.8	139.2
107.5°	168.3	168.6	169.0	169.2	169.1	169.1	169.1	169.1
110°	189.4	189.2	188.9	189.0	189.4	189.7	190.1	190.5



TEST NUMBER: P332965

CATALOG NUMBER: SA4XXRDIP-C1020D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	212.2	212.1	212.1	212.1	212.2	212.2	212.3	212.4
115°	247.3	247.2	247.0	246.9	246.8	246.6	246.5	246.4
117.5°	281.0	280.6	280.1	279.8	279.5	279.3	279.0	278.8
120°	303.9	303.2	302.6	302.4	302.7	302.9	303.2	303.4
122.5°	327.1	326.7	326.2	325.8	325.3	324.9	324.4	324.0
125°	361.1	360.8	360.6	360.3	360.1	359.8	359.6	359.3
127.5°	393.6	393.4	393.1	392.9	392.7	392.5	392.3	392.1
130°	416.4	416.2	415.9	415.5	415.0	414.5	414.0	413.5
132.5°	437.9	437.6	437.4	437.1	436.9	436.7	436.5	436.3
135°	470.0	469.8	469.5	469.2	468.8	468.4	468.1	467.7
137.5°	501.1	500.8	500.5	500.3	500.4	500.5	500.6	500.7
140°	521.6	521.5	521.4	521.2	521.1	521.0	520.9	520.7
142.5°	541.0	541.0	540.9	540.9	540.9	540.9	540.8	540.8
145°	570.1	570.0	569.8	569.6	569.2	568.8	568.4	568.1
147.5°	596.5	596.4	596.3	596.2	596.1	595.9	595.8	595.7
150°	613.1	613.1	613.1	613.1	612.9	612.8	612.7	612.6
152.5°	628.8	629.1	629.4	629.4	629.1	628.7	628.4	628.1
155°	650.6	651.1	651.7	651.7	651.1	650.6	650.1	649.6
157.5°	669.9	670.3	670.7	670.6	670.2	669.8	669.3	668.9
160°	681.8	682.1	682.5	682.4	681.8	681.1	680.5	679.9
162.5°	692.4	693.1	693.8	693.8	693.2	692.5	691.9	691.3
165°	706.5	707.2	708.0	708.1	707.6	707.1	706.6	706.1
167.5°	718.3	719.1	719.9	719.8	719.1	718.3	717.5	716.7
170°	724.7	725.5	726.2	726.2	725.3	724.4	723.5	722.6
172.5°	729.5	730.4	731.2	731.2	730.3	729.4	728.5	727.7
175°	734.7	735.6	736.4	736.4	735.6	734.7	733.8	732.9
177.5°	737.5	738.2	738.9	738.9	738.1	737.3	736.4	735.6
180°	737.5	737.5	737.5	737.5	737.5	737.5	737.5	737.5

(END OF REPORT)