

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332970

Luminaire Tested: **SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332970
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7408.6 lumens
Efficiency: N/A
Efficacy: 136.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332970
CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332970

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	100	95	91	88	92	89	86	83	77	74	72	66	64	62	55	54	53	48
2	91	84	77	72	84	78	73	68	68	64	60	58	55	52	49	47	45	41
3	83	74	66	61	77	69	62	57	60	55	51	51	48	45	44	41	39	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	38	39	36	34	30
5	70	58	50	44	65	55	48	42	48	42	38	41	37	34	35	32	29	26
6	65	53	44	39	60	49	42	37	43	37	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	31	27	24	27	24	21	19
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	22	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14577	14577	14577
5°	14610	14431	14521
10°	14519	14258	14258
15°	14352	13959	13855
20°	14123	13564	13315
25°	13831	13104	12772
30°	13546	12618	12089
35°	13231	12113	11404
40°	12852	11540	10666
45°	12501	10970	9913
50°	12103	10315	9117
55°	11676	9633	8251
60°	11207	8885	7367
65°	10776	7950	6497
70°	10150	6918	5516
75°	9357	5736	4485
80°	8164	4370	4114
85°	6919	3974	3714



TEST NUMBER: P332970

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.6	2.3
10°-20°	473.0	6.4
20°-30°	683.0	9.2
30°-40°	774.2	10.5
40°-50°	747.6	10.1
50°-60°	621.7	8.4
60°-70°	429.3	5.8
70°-80°	217.6	2.9
80°-90°	58.8	0.8
90°-100°	35.8	0.5
100°-110°	228.0	3.1
110°-120°	436.1	5.9
120°-130°	553.6	7.5
130°-140°	592.3	8.0
140°-150°	553.9	7.5
150°-160°	446.7	6.0
160°-170°	288.1	3.9
170°-180°	99.3	1.3
0°-30°	1325.6	17.9
0°-40°	2099.9	28.3
0°-60°	3469.2	46.8
0°-90°	4174.9	56.4
90°-120°	699.8	9.4
90°-150°	2399.6	32.4
90°-180°	3234.0	43.7
0°-180°	7408.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1806	1806	1806	1806	1806	
5°	1803	1797	1781	1794	1792	171
15°	1717	1704	1670	1667	1658	484
25°	1553	1526	1471	1448	1434	715
35°	1342	1297	1229	1183	1157	839
45°	1095	1042	961	896	868	844
55°	830	772	684	615	586	742
65°	564	503	416	359	340	557
75°	300	248	184	153	144	317
85°	75	48	43	40	40	84
90°	2	11	17	22	24	6
95°	43	18	17	22	23	55
105°	235	240	244	249	223	246
115°	439	442	441	442	443	432
125°	618	621	619	622	622	551
135°	766	766	769	770	772	590
145°	884	886	886	887	888	552
155°	969	969	967	970	968	446
165°	1022	1018	1018	1024	1017	289
175°	1045	1041	1042	1048	1039	100
180°	1045	1045	1045	1045	1045	



TEST NUMBER: P332970

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1810.1	1809.1	1808.1	1807.2	1806.2	1804.3	1801.6	1798.9	1796.2	1793.5	1796.2
5°	1802.9	1801.7	1800.5	1799.2	1798.0	1795.5	1791.9	1788.2	1784.5	1780.8	1783.9
7.5°	1786.6	1785.3	1784.0	1782.7	1781.4	1778.4	1773.6	1768.8	1764.0	1759.2	1761.2
10°	1771.1	1769.6	1768.0	1766.5	1765.0	1761.4	1755.9	1750.4	1744.8	1739.3	1740.5
12.5°	1751.2	1749.4	1747.6	1745.9	1744.1	1739.9	1733.4	1726.9	1720.4	1713.9	1714.6
15°	1717.2	1714.4	1711.7	1708.9	1706.1	1700.9	1693.2	1685.5	1677.9	1670.2	1669.6
17.5°	1676.0	1672.0	1668.0	1664.0	1660.0	1653.4	1644.2	1635.0	1625.8	1616.5	1614.8
20°	1643.9	1639.9	1635.9	1631.9	1627.9	1620.7	1610.3	1599.8	1589.4	1578.9	1576.5
22.5°	1608.5	1604.0	1599.5	1595.1	1590.6	1582.7	1571.6	1560.4	1549.2	1538.0	1534.3
25°	1552.7	1547.1	1541.6	1536.1	1530.5	1521.5	1508.9	1496.3	1483.7	1471.1	1465.9
27.5°	1494.0	1487.1	1480.2	1473.2	1466.3	1456.1	1442.6	1429.2	1415.7	1402.2	1395.8
30°	1453.1	1445.4	1437.8	1430.1	1422.4	1411.3	1396.9	1382.4	1368.0	1353.6	1345.9
32.5°	1410.0	1401.3	1392.6	1384.0	1375.3	1363.5	1348.6	1333.7	1318.7	1303.8	1294.9
35°	1342.5	1332.7	1322.8	1313.0	1303.2	1290.6	1275.2	1259.9	1244.5	1229.1	1218.7
37.5°	1270.3	1260.2	1250.1	1239.9	1229.8	1216.2	1199.2	1182.2	1165.1	1148.1	1136.4
40°	1219.5	1209.3	1199.2	1189.0	1178.9	1165.1	1147.6	1130.0	1112.5	1095.0	1082.1
42.5°	1170.8	1160.2	1149.5	1138.9	1128.3	1113.8	1095.6	1077.3	1059.1	1040.8	1027.7
45°	1095.0	1083.7	1072.3	1060.9	1049.5	1034.6	1016.2	997.8	979.3	960.9	945.9
47.5°	1016.8	1005.0	993.3	981.6	969.8	954.4	935.2	916.0	896.8	877.7	862.1
50°	963.7	951.7	939.7	927.7	915.7	899.9	880.3	860.6	840.9	821.3	805.9
52.5°	909.5	897.7	886.0	874.3	862.5	846.6	826.4	806.3	786.1	766.0	750.4
55°	829.6	817.3	805.0	792.7	780.4	764.3	744.3	724.3	704.4	684.4	668.4
57.5°	750.5	737.7	724.9	712.1	699.4	683.1	663.5	643.8	624.1	604.5	588.3
60°	694.1	681.8	669.5	657.2	644.9	628.9	609.3	589.6	569.9	550.3	534.3
62.5°	643.2	630.4	617.6	604.8	592.1	575.6	555.4	535.3	515.1	495.0	480.2
65°	564.1	550.9	537.7	524.5	511.3	494.8	475.2	455.5	435.8	416.2	403.0
67.5°	482.0	469.3	456.7	444.0	431.3	415.9	397.6	379.4	361.1	342.9	331.5
70°	430.0	417.1	404.2	391.3	378.4	363.2	345.7	328.1	310.6	293.1	283.0
72.5°	374.7	363.0	351.3	339.7	328.0	313.9	297.4	280.8	264.3	247.8	239.1
75°	300.0	288.7	277.3	265.9	254.6	241.6	227.2	212.8	198.3	183.9	176.8
77.5°	224.3	214.6	205.0	195.3	185.7	175.0	163.3	151.7	140.0	128.3	124.2
80°	175.6	166.7	157.8	148.9	140.0	130.9	121.7	112.5	103.2	94.0	93.1
82.5°	133.6	125.4	117.2	109.0	100.9	94.1	88.9	83.6	78.3	73.0	72.3
85°	74.7	68.5	62.4	56.2	50.1	46.5	45.6	44.7	43.8	42.9	42.2
87.5°	25.9	24.3	22.7	21.2	19.6	18.8	18.8	18.9	18.9	18.9	18.9
90°	2.3	4.3	6.2	8.1	10.0	11.6	13.0	14.4	15.8	17.2	18.2
92.5°	9.9	10.0	10.1	10.2	10.3	11.0	12.4	13.8	15.2	16.6	17.6
95°	43.0	37.1	31.2	25.3	19.4	16.5	16.7	16.9	17.0	17.2	18.2
97.5°	91.3	95.0	98.7	102.4	106.1	98.2	78.8	59.4	40.0	20.6	20.7
100°	128.2	131.4	134.5	137.6	140.7	130.3	106.3	82.4	58.4	34.4	31.4
102.5°	169.5	171.8	174.1	176.4	178.7	178.3	175.1	172.0	168.9	165.8	133.9
105°	235.3	236.4	237.4	238.5	239.5	240.5	241.3	242.2	243.1	243.9	245.5
107.5°	296.5	297.0	297.5	298.1	298.6	299.4	300.6	301.8	303.0	304.2	304.9
110°	337.8	338.3	338.8	339.3	339.9	340.6	341.7	342.7	343.8	344.8	345.2



TEST NUMBER: P332970

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	377.8	378.7	379.7	380.6	381.6	382.3	382.8	383.2	383.7	384.2	384.2
115°	439.4	439.9	440.5	441.0	441.5	441.7	441.5	441.3	441.2	441.0	441.3
117.5°	494.9	495.6	496.3	497.0	497.7	498.3	498.6	499.0	499.4	499.8	499.7
120°	532.5	533.2	533.9	534.6	535.2	535.5	535.3	535.2	535.0	534.8	535.2
122.5°	567.5	567.9	568.3	568.7	569.2	569.5	569.7	570.0	570.2	570.5	570.7
125°	617.7	618.4	619.1	619.8	620.5	620.6	620.3	620.0	619.6	619.3	619.8
127.5°	665.2	665.4	665.6	665.8	665.9	666.4	667.2	668.0	668.8	669.6	669.5
130°	695.9	696.1	696.2	696.4	696.6	696.9	697.4	698.0	698.5	699.0	699.2
132.5°	724.0	724.3	724.7	725.0	725.3	725.8	726.4	727.1	727.7	728.4	728.6
135°	766.3	766.1	765.9	765.7	765.6	765.8	766.5	767.2	767.9	768.6	768.9
137.5°	803.6	803.7	803.8	803.8	803.9	804.3	805.1	805.9	806.6	807.4	807.8
140°	828.0	828.4	828.7	829.1	829.4	829.8	830.1	830.5	830.8	831.1	831.7
142.5°	849.9	850.5	851.2	851.8	852.4	852.8	853.0	853.3	853.5	853.7	854.1
145°	883.5	884.1	884.6	885.1	885.6	885.9	885.9	885.9	885.9	885.9	886.1
147.5°	910.3	911.3	912.2	913.2	914.2	914.6	914.4	914.2	914.0	913.9	914.0
150°	929.7	930.4	931.1	931.8	932.4	932.7	932.5	932.4	932.2	932.0	932.0
152.5°	945.9	946.5	947.0	947.6	948.2	948.3	948.0	947.7	947.3	947.0	947.3
155°	968.8	968.9	969.1	969.3	969.5	969.3	968.8	968.2	967.7	967.2	967.9
157.5°	988.0	987.9	987.8	987.7	987.6	987.2	986.6	986.1	985.5	984.9	985.8
160°	999.3	998.7	998.2	997.7	997.2	996.8	996.7	996.5	996.3	996.1	997.2
162.5°	1009.3	1008.6	1007.9	1007.3	1006.6	1006.2	1006.0	1005.9	1005.7	1005.5	1006.6
165°	1021.9	1021.1	1020.2	1019.3	1018.5	1018.0	1018.0	1018.0	1018.0	1018.0	1019.4
167.5°	1031.9	1031.0	1030.1	1029.2	1028.3	1027.8	1027.7	1027.6	1027.5	1027.4	1028.9
170°	1037.6	1036.5	1035.5	1034.4	1033.4	1033.0	1033.1	1033.3	1033.5	1033.7	1035.0
172.5°	1041.3	1040.3	1039.2	1038.2	1037.2	1036.7	1036.9	1037.1	1037.2	1037.4	1038.8
175°	1045.4	1044.3	1043.3	1042.3	1041.2	1040.8	1041.0	1041.1	1041.3	1041.5	1043.0
177.5°	1047.3	1046.3	1045.3	1044.3	1043.4	1043.0	1043.3	1043.6	1043.9	1044.1	1045.2
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4



TEST NUMBER: P332970

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1798.9	1801.6	1804.3	1805.6	1805.3	1805.1	1804.8	1804.6
5°	1786.9	1790.0	1793.1	1794.3	1793.7	1793.1	1792.5	1791.9
7.5°	1763.2	1765.1	1767.1	1767.6	1766.6	1765.6	1764.6	1763.6
10°	1741.8	1743.0	1744.2	1744.2	1743.0	1741.8	1740.5	1739.3
12.5°	1715.3	1716.1	1716.8	1716.3	1714.6	1712.9	1711.2	1709.5
15°	1669.0	1668.3	1667.7	1666.3	1664.2	1662.0	1659.9	1657.7
17.5°	1613.1	1611.4	1609.7	1607.2	1603.9	1600.7	1597.4	1594.1
20°	1574.0	1571.6	1569.1	1565.9	1561.9	1557.9	1553.9	1549.9
22.5°	1530.6	1526.9	1523.3	1519.8	1516.5	1513.3	1510.0	1506.8
25°	1460.6	1455.4	1450.2	1446.0	1443.0	1439.9	1436.8	1433.8
27.5°	1389.3	1382.9	1376.4	1371.0	1366.6	1362.1	1357.7	1353.3
30°	1338.2	1330.5	1322.8	1316.5	1311.6	1306.7	1301.8	1296.9
32.5°	1286.0	1277.1	1268.2	1261.4	1256.7	1252.0	1247.4	1242.7
35°	1208.2	1197.8	1187.3	1179.4	1173.8	1168.3	1162.8	1157.2
37.5°	1124.8	1113.1	1101.4	1092.8	1087.3	1081.7	1076.2	1070.7
40°	1069.2	1056.3	1043.4	1034.2	1028.7	1023.1	1017.6	1012.1
42.5°	1014.5	1001.4	988.2	978.8	973.0	967.2	961.4	955.7
45°	930.8	915.7	900.7	890.4	884.9	879.3	873.8	868.3
47.5°	846.5	830.9	815.2	804.4	798.3	792.2	786.1	780.1
50°	790.5	775.2	759.8	749.2	743.4	737.5	731.7	725.9
52.5°	734.7	719.1	703.5	692.7	686.6	680.5	674.4	668.4
55°	652.4	636.5	620.5	609.6	603.7	597.9	592.1	586.2
57.5°	572.0	555.8	539.6	529.3	524.8	520.4	516.0	511.6
60°	518.3	502.3	486.4	475.9	471.0	466.1	461.2	456.3
62.5°	465.5	450.7	436.0	426.6	422.7	418.8	414.8	410.9
65°	389.7	376.5	363.3	354.9	351.2	347.5	343.8	340.1
67.5°	320.1	308.8	297.4	289.7	285.6	281.6	277.5	273.5
70°	272.8	262.7	252.6	245.9	242.9	239.8	236.7	233.7
72.5°	230.4	221.8	213.1	207.4	204.5	201.7	198.9	196.1
75°	169.8	162.7	155.6	151.2	149.3	147.5	145.6	143.8
77.5°	120.1	116.0	111.8	109.5	108.9	108.4	107.8	107.3
80°	92.2	91.3	90.3	89.7	89.4	89.1	88.8	88.5
82.5°	71.6	71.0	70.3	69.8	69.5	69.2	68.9	68.6
85°	41.6	41.0	40.4	40.1	40.1	40.1	40.1	40.1
87.5°	18.9	18.8	18.8	18.9	19.2	19.5	19.9	20.2
90°	19.3	20.3	21.4	22.1	22.4	22.8	23.1	23.5
92.5°	18.7	19.7	20.7	21.3	21.4	21.4	21.5	21.6
95°	19.3	20.3	21.4	22.0	22.2	22.3	22.5	22.7
97.5°	20.9	21.0	21.1	21.2	21.4	21.5	21.7	21.9
100°	28.5	25.5	22.6	21.2	21.4	21.5	21.7	21.9
102.5°	102.0	70.2	38.3	22.4	22.4	22.4	22.5	22.5
105°	247.1	248.6	250.2	247.9	241.6	235.3	229.1	222.8
107.5°	305.7	306.4	307.2	307.9	308.6	309.2	309.9	310.6
110°	345.5	345.9	346.2	346.6	347.2	347.7	348.2	348.7



TEST NUMBER: P332970

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	384.1	384.0	383.9	384.2	384.9	385.6	386.2	386.9
115°	441.7	442.0	442.4	442.6	442.6	442.6	442.6	442.6
117.5°	499.6	499.6	499.5	499.4	499.4	499.3	499.2	499.2
120°	535.5	535.9	536.2	536.2	535.9	535.5	535.2	534.8
122.5°	570.9	571.1	571.3	571.2	570.9	570.5	570.2	569.8
125°	620.3	620.8	621.3	621.7	621.9	622.0	622.2	622.4
127.5°	669.4	669.3	669.2	669.1	668.9	668.8	668.7	668.5
130°	699.4	699.5	699.7	699.8	699.8	699.8	699.8	699.8
132.5°	728.8	728.9	729.1	729.1	729.0	728.8	728.7	728.6
135°	769.3	769.6	770.0	770.3	770.7	771.0	771.4	771.7
137.5°	808.1	808.5	808.9	809.0	808.9	808.8	808.7	808.6
140°	832.2	832.7	833.2	833.6	833.8	833.9	834.1	834.3
142.5°	854.4	854.8	855.2	855.4	855.4	855.5	855.5	855.5
145°	886.2	886.4	886.6	886.8	887.2	887.5	887.9	888.2
147.5°	914.2	914.3	914.4	914.6	914.8	914.9	915.1	915.3
150°	932.0	932.0	932.0	932.1	932.3	932.4	932.6	932.8
152.5°	947.6	947.9	948.1	948.2	948.1	948.0	947.9	947.8
155°	968.6	969.3	970.0	970.1	969.5	969.0	968.5	968.0
157.5°	986.7	987.6	988.5	988.5	987.6	986.7	985.8	984.9
160°	998.2	999.3	1000.3	1000.3	999.3	998.2	997.2	996.1
162.5°	1007.6	1008.6	1009.7	1009.6	1008.4	1007.2	1006.1	1004.9
165°	1020.8	1022.2	1023.6	1023.5	1021.9	1020.4	1018.8	1017.2
167.5°	1030.5	1032.0	1033.5	1033.4	1031.7	1029.9	1028.2	1026.5
170°	1036.4	1037.8	1039.2	1039.0	1037.3	1035.6	1033.8	1032.1
172.5°	1040.2	1041.6	1043.0	1042.7	1040.9	1039.0	1037.1	1035.2
175°	1044.6	1046.2	1047.7	1047.5	1045.4	1043.3	1041.2	1039.1
177.5°	1046.4	1047.5	1048.6	1048.3	1046.6	1045.0	1043.3	1041.6
180°	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4

(END OF REPORT)