

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332971

Luminaire Tested: **SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P332971  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6979.4 lumens  
Efficiency: N/A  
Efficacy: 128.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332971  
CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332971

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60				
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51				
2	92	84	78	73	85	79	74	69	69	65	62	60	57	54	52	49	47	43				
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37				
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35	32				
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31	28				
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27	25				
7	60	48	40	35	56	45	38	33	40	34	30	36	31	27	31	27	24	22				
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20				
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18				
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14577	14577	14577
5°	14610	14431	14521
10°	14519	14258	14258
15°	14352	13959	13855
20°	14123	13564	13315
25°	13831	13104	12772
30°	13546	12618	12089
35°	13231	12113	11404
40°	12852	11540	10666
45°	12501	10970	9913
50°	12103	10315	9117
55°	11676	9633	8251
60°	11207	8885	7367
65°	10776	7950	6497
70°	10150	6918	5516
75°	9357	5736	4485
80°	8164	4370	4114
85°	6919	3974	3714



TEST NUMBER: P332971

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	169.6	2.4
10°-20°	473.0	6.8
20°-30°	683.0	9.8
30°-40°	774.2	11.1
40°-50°	747.6	10.7
50°-60°	621.7	8.9
60°-70°	429.3	6.2
70°-80°	217.6	3.1
80°-90°	58.8	0.8
90°-100°	66.7	1.0
100°-110°	197.5	2.8
110°-120°	335.2	4.8
120°-130°	442.0	6.3
130°-140°	496.4	7.1
140°-150°	487.8	7.0
150°-160°	410.3	5.9
160°-170°	273.0	3.9
170°-180°	95.6	1.4
0°-30°	1325.6	19.0
0°-40°	2099.9	30.1
0°-60°	3469.2	49.7
0°-90°	4174.9	59.8
90°-120°	599.4	8.6
90°-150°	2025.7	29.0
90°-180°	2805.0	40.2
0°-180°	6979.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1806	1806	1806	1806	1806	
5°	1803	1797	1781	1794	1792	171
15°	1717	1704	1670	1667	1658	484
25°	1553	1526	1471	1448	1434	715
35°	1342	1297	1229	1183	1157	839
45°	1095	1042	961	896	868	844
55°	830	772	684	615	586	742
65°	564	503	416	359	340	557
75°	300	248	184	153	144	317
85°	75	48	43	40	40	84
90°	2	11	17	22	24	6
95°	47	54	59	62	62	52
105°	182	183	186	188	191	193
115°	341	341	339	338	338	336
125°	496	496	496	494	492	442
135°	640	645	645	643	641	495
145°	778	781	782	781	779	487
155°	891	891	890	893	890	410
165°	970	968	966	971	968	273
175°	1009	1006	1005	1010	1005	96
180°	1011	1011	1011	1011	1011	



TEST NUMBER: P332971

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1810.1	1809.1	1808.1	1807.2	1806.2	1804.3	1801.6	1798.9	1796.2	1793.5	1796.2
5°	1802.9	1801.7	1800.5	1799.2	1798.0	1795.5	1791.9	1788.2	1784.5	1780.8	1783.9
7.5°	1786.6	1785.3	1784.0	1782.7	1781.4	1778.4	1773.6	1768.8	1764.0	1759.2	1761.2
10°	1771.1	1769.6	1768.0	1766.5	1765.0	1761.4	1755.9	1750.4	1744.8	1739.3	1740.5
12.5°	1751.2	1749.4	1747.6	1745.9	1744.1	1739.9	1733.4	1726.9	1720.4	1713.9	1714.6
15°	1717.2	1714.4	1711.7	1708.9	1706.1	1700.9	1693.2	1685.5	1677.9	1670.2	1669.6
17.5°	1676.0	1672.0	1668.0	1664.0	1660.0	1653.4	1644.2	1635.0	1625.8	1616.5	1614.8
20°	1643.9	1639.9	1635.9	1631.9	1627.9	1620.7	1610.3	1599.8	1589.4	1578.9	1576.5
22.5°	1608.5	1604.0	1599.5	1595.1	1590.6	1582.7	1571.6	1560.4	1549.2	1538.0	1534.3
25°	1552.7	1547.1	1541.6	1536.1	1530.5	1521.5	1508.9	1496.3	1483.7	1471.1	1465.9
27.5°	1494.0	1487.1	1480.2	1473.2	1466.3	1456.1	1442.6	1429.2	1415.7	1402.2	1395.8
30°	1453.1	1445.4	1437.8	1430.1	1422.4	1411.3	1396.9	1382.4	1368.0	1353.6	1345.9
32.5°	1410.0	1401.3	1392.6	1384.0	1375.3	1363.5	1348.6	1333.7	1318.7	1303.8	1294.9
35°	1342.5	1332.7	1322.8	1313.0	1303.2	1290.6	1275.2	1259.9	1244.5	1229.1	1218.7
37.5°	1270.3	1260.2	1250.1	1239.9	1229.8	1216.2	1199.2	1182.2	1165.1	1148.1	1136.4
40°	1219.5	1209.3	1199.2	1189.0	1178.9	1165.1	1147.6	1130.0	1112.5	1095.0	1082.1
42.5°	1170.8	1160.2	1149.5	1138.9	1128.3	1113.8	1095.6	1077.3	1059.1	1040.8	1027.7
45°	1095.0	1083.7	1072.3	1060.9	1049.5	1034.6	1016.2	997.8	979.3	960.9	945.9
47.5°	1016.8	1005.0	993.3	981.6	969.8	954.4	935.2	916.0	896.8	877.7	862.1
50°	963.7	951.7	939.7	927.7	915.7	899.9	880.3	860.6	840.9	821.3	805.9
52.5°	909.5	897.7	886.0	874.3	862.5	846.6	826.4	806.3	786.1	766.0	750.4
55°	829.6	817.3	805.0	792.7	780.4	764.3	744.3	724.3	704.4	684.4	668.4
57.5°	750.5	737.7	724.9	712.1	699.4	683.1	663.5	643.8	624.1	604.5	588.3
60°	694.1	681.8	669.5	657.2	644.9	628.9	609.3	589.6	569.9	550.3	534.3
62.5°	643.2	630.4	617.6	604.8	592.1	575.6	555.4	535.3	515.1	495.0	480.2
65°	564.1	550.9	537.7	524.5	511.3	494.8	475.2	455.5	435.8	416.2	403.0
67.5°	482.0	469.3	456.7	444.0	431.3	415.9	397.6	379.4	361.1	342.9	331.5
70°	430.0	417.1	404.2	391.3	378.4	363.2	345.7	328.1	310.6	293.1	283.0
72.5°	374.7	363.0	351.3	339.7	328.0	313.9	297.4	280.8	264.3	247.8	239.1
75°	300.0	288.7	277.3	265.9	254.6	241.6	227.2	212.8	198.3	183.9	176.8
77.5°	224.3	214.6	205.0	195.3	185.7	175.0	163.3	151.7	140.0	128.3	124.2
80°	175.6	166.7	157.8	148.9	140.0	130.9	121.7	112.5	103.2	94.0	93.1
82.5°	133.6	125.4	117.2	109.0	100.9	94.1	88.9	83.6	78.3	73.0	72.3
85°	74.7	68.5	62.4	56.2	50.1	46.5	45.6	44.7	43.8	42.9	42.2
87.5°	25.9	24.3	22.7	21.2	19.6	18.8	18.8	18.9	18.9	18.9	18.9
90°	2.3	4.3	6.2	8.1	10.0	11.6	13.0	14.4	15.8	17.2	18.2
92.5°	16.7	18.9	21.1	23.3	25.5	27.1	28.0	29.0	30.0	31.0	31.6
95°	46.9	48.5	50.0	51.6	53.2	54.6	55.8	57.0	58.2	59.4	59.9
97.5°	81.9	83.2	84.4	85.7	86.9	88.3	89.7	91.1	92.5	94.0	94.6
100°	109.5	110.1	110.8	111.5	112.2	113.4	114.9	116.5	118.0	119.6	120.0
102.5°	138.2	138.5	138.8	139.1	139.3	140.2	141.6	143.0	144.5	145.9	146.4
105°	182.2	182.3	182.5	182.7	182.9	183.3	184.0	184.7	185.4	186.1	186.6
107.5°	228.3	228.5	228.7	228.9	229.1	229.3	229.4	229.5	229.6	229.7	230.2
110°	259.6	259.9	260.2	260.6	260.9	261.0	260.9	260.7	260.5	260.3	260.0



TEST NUMBER: P332971

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.1	292.1	292.2	292.3	292.4	292.2	291.9	291.6	291.3	291.0	290.9
115°	340.9	340.9	340.9	340.9	340.9	340.7	340.3	340.0	339.6	339.3	339.1
117.5°	386.8	387.0	387.1	387.2	387.4	387.3	387.1	386.8	386.6	386.4	385.8
120°	417.5	418.2	418.9	419.6	420.3	420.3	419.8	419.3	418.8	418.3	417.4
122.5°	449.4	449.6	449.9	450.2	450.5	450.5	450.3	450.0	449.8	449.5	448.9
125°	496.4	496.4	496.4	496.4	496.4	496.3	496.2	496.0	495.8	495.7	495.3
127.5°	539.1	539.6	540.2	540.7	541.2	541.3	541.0	540.8	540.5	540.2	539.9
130°	569.1	569.7	570.2	570.7	571.2	571.5	571.5	571.5	571.5	571.5	571.1
132.5°	599.8	600.2	600.6	600.9	601.3	601.4	601.3	601.2	601.0	600.9	600.5
135°	640.3	641.3	642.4	643.4	644.5	645.0	645.0	645.0	645.0	645.0	644.6
137.5°	684.4	684.9	685.3	685.8	686.3	686.7	687.0	687.3	687.5	687.8	687.4
140°	713.8	714.1	714.5	714.8	715.2	715.3	715.3	715.3	715.3	715.3	715.2
142.5°	740.7	741.0	741.4	741.7	742.1	742.2	742.0	741.9	741.7	741.6	741.6
145°	777.9	778.6	779.3	780.0	780.7	781.1	781.3	781.4	781.6	781.8	781.6
147.5°	814.8	815.6	816.4	817.3	818.1	818.5	818.3	818.2	818.0	817.9	817.8
150°	837.3	838.0	838.7	839.4	840.1	840.4	840.4	840.4	840.4	840.4	840.4
152.5°	858.6	859.0	859.4	859.8	860.2	860.5	860.6	860.8	860.9	861.1	861.5
155°	891.2	891.2	891.2	891.2	891.2	891.1	891.0	890.8	890.6	890.5	891.1
157.5°	918.8	918.4	918.1	917.8	917.5	917.3	917.3	917.3	917.2	917.2	917.7
160°	935.0	934.8	934.7	934.5	934.3	934.1	934.0	933.8	933.6	933.5	934.0
162.5°	950.0	949.6	949.1	948.7	948.2	947.9	947.7	947.6	947.4	947.2	948.2
165°	970.2	969.7	969.2	968.6	968.1	967.7	967.3	967.0	966.6	966.3	967.3
167.5°	985.7	984.9	984.2	983.5	982.8	982.4	982.4	982.5	982.5	982.5	983.6
170°	994.4	993.6	992.7	991.8	991.0	990.6	990.8	991.0	991.1	991.3	992.3
172.5°	1000.7	1000.0	999.2	998.5	997.8	997.4	997.5	997.5	997.5	997.6	998.7
175°	1009.3	1008.4	1007.5	1006.7	1005.8	1005.3	1005.1	1004.9	1004.8	1004.6	1005.8
177.5°	1012.1	1011.4	1010.7	1010.0	1009.3	1009.0	1009.0	1009.0	1009.0	1009.0	1009.9
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8



TEST NUMBER: P332971

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7	1805.7
2.5°	1798.9	1801.6	1804.3	1805.6	1805.3	1805.1	1804.8	1804.6
5°	1786.9	1790.0	1793.1	1794.3	1793.7	1793.1	1792.5	1791.9
7.5°	1763.2	1765.1	1767.1	1767.6	1766.6	1765.6	1764.6	1763.6
10°	1741.8	1743.0	1744.2	1744.2	1743.0	1741.8	1740.5	1739.3
12.5°	1715.3	1716.1	1716.8	1716.3	1714.6	1712.9	1711.2	1709.5
15°	1669.0	1668.3	1667.7	1666.3	1664.2	1662.0	1659.9	1657.7
17.5°	1613.1	1611.4	1609.7	1607.2	1603.9	1600.7	1597.4	1594.1
20°	1574.0	1571.6	1569.1	1565.9	1561.9	1557.9	1553.9	1549.9
22.5°	1530.6	1526.9	1523.3	1519.8	1516.5	1513.3	1510.0	1506.8
25°	1460.6	1455.4	1450.2	1446.0	1443.0	1439.9	1436.8	1433.8
27.5°	1389.3	1382.9	1376.4	1371.0	1366.6	1362.1	1357.7	1353.3
30°	1338.2	1330.5	1322.8	1316.5	1311.6	1306.7	1301.8	1296.9
32.5°	1286.0	1277.1	1268.2	1261.4	1256.7	1252.0	1247.4	1242.7
35°	1208.2	1197.8	1187.3	1179.4	1173.8	1168.3	1162.8	1157.2
37.5°	1124.8	1113.1	1101.4	1092.8	1087.3	1081.7	1076.2	1070.7
40°	1069.2	1056.3	1043.4	1034.2	1028.7	1023.1	1017.6	1012.1
42.5°	1014.5	1001.4	988.2	978.8	973.0	967.2	961.4	955.7
45°	930.8	915.7	900.7	890.4	884.9	879.3	873.8	868.3
47.5°	846.5	830.9	815.2	804.4	798.3	792.2	786.1	780.1
50°	790.5	775.2	759.8	749.2	743.4	737.5	731.7	725.9
52.5°	734.7	719.1	703.5	692.7	686.6	680.5	674.4	668.4
55°	652.4	636.5	620.5	609.6	603.7	597.9	592.1	586.2
57.5°	572.0	555.8	539.6	529.3	524.8	520.4	516.0	511.6
60°	518.3	502.3	486.4	475.9	471.0	466.1	461.2	456.3
62.5°	465.5	450.7	436.0	426.6	422.7	418.8	414.8	410.9
65°	389.7	376.5	363.3	354.9	351.2	347.5	343.8	340.1
67.5°	320.1	308.8	297.4	289.7	285.6	281.6	277.5	273.5
70°	272.8	262.7	252.6	245.9	242.9	239.8	236.7	233.7
72.5°	230.4	221.8	213.1	207.4	204.5	201.7	198.9	196.1
75°	169.8	162.7	155.6	151.2	149.3	147.5	145.6	143.8
77.5°	120.1	116.0	111.8	109.5	108.9	108.4	107.8	107.3
80°	92.2	91.3	90.3	89.7	89.4	89.1	88.8	88.5
82.5°	71.6	71.0	70.3	69.8	69.5	69.2	68.9	68.6
85°	41.6	41.0	40.4	40.1	40.1	40.1	40.1	40.1
87.5°	18.9	18.8	18.8	18.9	19.2	19.5	19.9	20.2
90°	19.3	20.3	21.4	22.1	22.4	22.8	23.1	23.5
92.5°	32.2	32.8	33.5	33.9	34.1	34.3	34.5	34.7
95°	60.5	61.0	61.5	61.8	61.8	61.8	61.8	61.8
97.5°	95.2	95.8	96.5	96.8	96.8	96.8	96.8	96.8
100°	120.3	120.7	121.0	121.2	121.2	121.2	121.2	121.2
102.5°	146.9	147.3	147.8	148.1	148.3	148.4	148.6	148.7
105°	187.1	187.6	188.1	188.7	189.2	189.7	190.2	190.8
107.5°	230.7	231.1	231.6	231.9	231.8	231.8	231.8	231.7
110°	259.6	259.3	258.9	259.0	259.6	260.1	260.6	261.1





TEST NUMBER: P332971

CATALOG NUMBER: SA4XXRDIP-C1020D810U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	290.8	290.8	290.7	290.7	290.8	290.9	291.0	291.1
115°	338.9	338.8	338.6	338.4	338.3	338.1	337.9	337.7
117.5°	385.2	384.6	384.0	383.5	383.2	382.8	382.5	382.1
120°	416.5	415.6	414.8	414.5	414.9	415.2	415.6	415.9
122.5°	448.3	447.8	447.2	446.6	445.9	445.3	444.7	444.1
125°	495.0	494.6	494.3	493.9	493.6	493.2	492.9	492.5
127.5°	539.5	539.2	538.8	538.5	538.2	538.0	537.7	537.4
130°	570.8	570.4	570.1	569.6	568.9	568.2	567.5	566.8
132.5°	600.2	599.8	599.5	599.2	598.9	598.6	598.3	598.1
135°	644.3	643.9	643.6	643.1	642.6	642.1	641.6	641.1
137.5°	686.9	686.5	686.0	685.8	685.9	686.0	686.1	686.3
140°	715.0	714.8	714.6	714.5	714.3	714.1	713.9	713.8
142.5°	741.5	741.5	741.5	741.4	741.4	741.4	741.3	741.3
145°	781.4	781.3	781.1	780.7	780.2	779.7	779.2	778.7
147.5°	817.6	817.5	817.3	817.2	817.0	816.8	816.7	816.5
150°	840.4	840.4	840.4	840.3	840.2	840.0	839.8	839.6
152.5°	861.9	862.3	862.7	862.7	862.3	861.8	861.4	860.9
155°	891.8	892.5	893.2	893.2	892.5	891.8	891.1	890.5
157.5°	918.2	918.8	919.3	919.2	918.7	918.1	917.5	916.9
160°	934.5	935.0	935.5	935.4	934.5	933.6	932.8	931.9
162.5°	949.1	950.0	951.0	951.0	950.1	949.3	948.4	947.5
165°	968.4	969.4	970.5	970.6	969.9	969.2	968.5	967.9
167.5°	984.6	985.7	986.7	986.7	985.6	984.5	983.5	982.4
170°	993.4	994.4	995.5	995.4	994.2	993.0	991.7	990.5
172.5°	999.9	1001.1	1002.3	1002.3	1001.1	999.8	998.6	997.4
175°	1007.0	1008.2	1009.5	1009.5	1008.2	1007.0	1005.8	1004.6
177.5°	1010.9	1011.9	1012.9	1012.8	1011.7	1010.6	1009.5	1008.3
180°	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8	1010.8

(END OF REPORT)